

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999730

Luminaire Tested: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999730
REPORT IS A COMBINATION OF REPORTS P988285 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2993.5 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999730

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999730

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	55	54
2	91	84	78	73	85	79	74	69	68	64	61	59	56	53	50	48	46
3	84	75	67	62	78	70	63	58	61	56	52	52	49	46	45	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	43	38	35	37	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	31	35	31	28	31	27	25
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20
10	49	37	30	25	46	35	29	24	32	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13069	13069	13069
5°	13090	12434	12342
10°	12961	11793	11403
15°	12784	11036	10334
20°	12548	10176	9216
25°	12306	9292	8192
30°	11982	8432	7075
35°	11665	7564	6115
40°	11342	6713	5127
45°	10966	5834	4265
50°	10577	4986	3472
55°	10174	4138	2757
60°	9704	3310	2086
65°	9165	2523	1696
70°	8510	1831	1348
75°	7692	1397	1030
80°	6499	946	692
85°	4534	433	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10966 cd/sqm

TEST NUMBER: P999730

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	2.6
10°-20°	212.4	7.1
20°-30°	298.2	10.0
30°-40°	325.1	10.9
40°-50°	298.8	10.0
50°-60°	234.7	7.8
60°-70°	152.7	5.1
70°-80°	78.6	2.6
80°-90°	21.3	0.7
90°-100°	75.3	2.5
100°-110°	254.4	8.5
110°-120°	267.4	8.9
120°-130°	219.9	7.3
130°-140°	176.7	5.9
140°-150°	133.5	4.5
150°-160°	93.9	3.1
160°-170°	55.3	1.8
170°-180°	18.0	0.6
0°-30°	588.0	19.6
0°-40°	913.1	30.5
0°-60°	1446.5	48.3
0°-90°	1699.2	56.8
90°-120°	597.1	19.9
90°-150°	1127.2	37.7
90°-180°	1294.0	43.2
0°-180°	2993.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	826	826	826	826	826	
5°	826	822	812	819	817	78
15°	785	777	752	738	730	221
25°	713	689	640	609	598	328
35°	614	576	510	463	447	384
45°	502	452	374	320	303	388
55°	382	324	243	198	184	341
65°	258	197	130	105	102	256
75°	138	85	60	54	54	145
85°	32	16	14	14	14	37
90°	0	5	12	12	12	2
95°	12	31	140	53	41	13
105°	44	66	264	473	402	46
115°	77	97	221	457	529	76
125°	107	127	213	370	430	95
135°	126	150	210	311	356	97
145°	144	165	209	260	284	90
155°	163	176	203	230	239	75
165°	178	183	195	206	210	50
175°	185	185	187	189	189	18
180°	186	186	186	186	186	

TEST NUMBER: P999730

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	825.6	825.6	825.6	825.6	825.6
2.5°	829.4	825.6	817.4	824.9	823.4
5°	825.6	821.9	812.2	818.9	816.7
7.5°	818.9	814.4	804.0	806.9	803.2
10°	809.9	804.7	789.8	787.5	783.0
12.5°	798.7	792.0	771.8	767.3	759.1
15°	785.3	777.1	751.7	737.5	730.0
17.5°	769.6	757.6	726.2	709.8	697.9
20°	751.7	736.7	699.4	680.7	664.2
22.5°	732.2	715.0	671.7	646.3	635.1
25°	712.8	688.9	639.6	608.9	597.7
27.5°	689.6	664.2	609.7	574.6	557.4
30°	665.0	636.6	576.8	538.7	518.5
32.5°	641.1	606.7	545.4	500.6	481.9
35°	614.2	576.1	510.3	463.2	446.8
37.5°	588.0	546.9	477.4	425.9	407.2
40°	560.4	515.5	443.1	390.0	370.6
42.5°	532.0	484.2	408.7	353.4	334.7
45°	502.1	452.0	373.6	320.5	302.6
47.5°	473.7	420.7	340.0	286.9	270.5
50°	442.3	389.3	307.1	255.5	239.8
52.5°	411.7	355.7	275.7	226.4	212.2
55°	381.8	323.5	242.8	198.0	183.8
57.5°	351.2	291.4	213.7	171.8	159.9
60°	319.8	260.0	183.1	145.0	133.0
62.5°	289.2	229.4	156.9	121.0	115.1
65°	257.8	197.3	130.0	104.6	102.4
67.5°	227.9	167.4	104.6	91.9	89.7
70°	196.5	138.2	86.7	79.2	76.2
72.5°	166.6	111.3	72.5	66.5	65.0
75°	137.5	85.2	59.8	54.5	53.8
77.5°	108.3	60.5	47.1	44.1	42.6
80°	81.4	43.3	35.9	32.9	32.9
82.5°	56.8	29.1	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.4	4.8	12.1	11.6	11.8
92.5°	5.4	17.0	55.0	25.4	21.8
95°	12.5	30.7	139.9	52.8	40.7
97.5°	18.6	40.5	228.1	106.0	68.2
100°	27.5	49.6	282.0	211.2	127.8
102.5°	35.7	57.8	283.8	357.0	249.2
105°	43.6	65.7	264.5	472.8	402.3
107.5°	52.1	73.5	246.7	514.8	505.5
110°	60.7	81.6	234.5	508.0	547.6



TEST NUMBER: P999730

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.5	89.2	226.7	485.0	546.9
115°	76.8	96.9	221.3	456.8	529.4
117.5°	85.3	104.6	218.5	429.8	503.0
120°	93.2	112.1	216.0	405.8	477.7
122.5°	100.7	119.8	214.6	387.0	451.2
125°	107.1	126.7	212.8	370.0	429.5
127.5°	112.5	133.4	211.7	355.6	409.1
130°	117.1	139.2	211.0	341.0	392.3
132.5°	121.4	144.9	210.6	325.8	374.9
135°	125.7	149.9	210.3	311.0	355.9
137.5°	129.6	154.2	210.3	296.0	337.7
140°	134.2	158.2	209.9	282.8	318.8
142.5°	138.9	161.4	209.9	270.0	299.9
145°	143.5	165.0	209.2	259.7	284.2
147.5°	148.5	167.8	208.1	250.6	270.3
150°	153.5	170.6	207.1	242.8	258.1
152.5°	158.5	173.5	205.3	236.2	247.8
155°	163.1	176.2	203.1	229.8	238.8
157.5°	167.1	178.3	201.0	223.7	231.0
160°	171.0	180.4	198.8	217.6	223.5
162.5°	174.9	182.0	197.1	211.9	216.3
165°	177.8	183.1	194.6	206.4	209.6
167.5°	180.3	184.2	192.4	201.4	203.1
170°	182.8	184.8	190.6	196.8	197.4
172.5°	184.2	185.2	188.5	192.6	192.8
175°	185.3	185.4	187.1	189.4	188.9
177.5°	186.0	185.6	185.6	187.1	186.0
180°	185.6	185.6	185.6	185.6	185.6

(END OF REPORT)