

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999735

Luminaire Tested: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999735
REPORT IS A COMBINATION OF REPORTS P988290 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2853.0 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999735

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999735

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	49	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12939	12939	12939
5°	12960	12308	12218
10°	12831	11675	11289
15°	12655	10925	10231
20°	12421	10072	9124
25°	12184	9199	8111
30°	11861	8347	7004
35°	11547	7489	6054
40°	11229	6645	5076
45°	10857	5774	4223
50°	10472	4936	3437
55°	10072	4097	2730
60°	9607	3276	2065
65°	9072	2498	1678
70°	8423	1812	1334
75°	7613	1383	1020
80°	6435	936	683
85°	4492	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10857 cd/sqm

TEST NUMBER: P999735

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.6	2.7
10°-20°	210.3	7.4
20°-30°	295.2	10.3
30°-40°	321.8	11.3
40°-50°	295.8	10.4
50°-60°	232.3	8.1
60°-70°	151.2	5.3
70°-80°	77.8	2.7
80°-90°	21.1	0.7
90°-100°	25.9	0.9
100°-110°	82.3	2.9
110°-120°	140.9	4.9
120°-130°	185.3	6.5
130°-140°	208.0	7.3
140°-150°	204.0	7.2
150°-160°	171.1	6.0
160°-170°	113.5	4.0
170°-180°	39.7	1.4
0°-30°	582.1	20.4
0°-40°	904.0	31.7
0°-60°	1432.1	50.2
0°-90°	1682.2	59.0
90°-120°	249.2	8.7
90°-150°	846.5	29.7
90°-180°	1171.0	41.0
0°-180°	2853.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	817	817	817	817	817	
5°	817	814	804	811	808	78
15°	777	769	744	730	723	219
25°	706	682	633	603	592	325
35°	608	570	505	459	442	381
45°	497	448	370	317	300	384
55°	378	320	240	196	182	338
65°	255	195	129	104	101	253
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	0	5	12	12	12	3
95°	18	22	23	23	22	21
105°	76	77	78	78	78	80
115°	141	144	143	142	141	140
125°	206	209	208	207	206	184
135°	266	270	271	270	269	206
145°	323	326	328	328	326	202
155°	369	370	371	373	372	170
165°	402	402	402	404	402	113
175°	418	417	416	419	417	40
180°	419	419	419	419	419	

TEST NUMBER: P999735

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	817.4	817.4	817.4	817.4	817.4
2.5°	821.1	817.4	809.2	816.6	815.1
5°	817.4	813.7	804.0	810.7	808.5
7.5°	810.7	806.3	795.9	798.9	795.2
10°	801.8	796.6	781.9	779.6	775.2
12.5°	790.7	784.1	764.1	759.7	751.5
15°	777.4	769.3	744.1	730.1	722.7
17.5°	761.9	750.0	719.0	702.7	690.9
20°	744.1	729.3	692.3	673.9	657.6
22.5°	724.9	707.9	665.0	639.8	628.7
25°	705.7	682.0	633.2	602.8	591.8
27.5°	682.7	657.6	603.6	568.8	551.8
30°	658.3	630.2	571.0	533.3	513.3
32.5°	634.7	600.6	540.0	495.6	477.1
35°	608.0	570.3	505.2	458.6	442.3
37.5°	582.1	541.5	472.7	421.6	403.1
40°	554.8	510.4	438.6	386.1	366.9
42.5°	526.7	479.3	404.6	349.9	331.4
45°	497.1	447.5	369.8	317.3	299.6
47.5°	469.0	416.4	336.6	284.0	267.8
50°	437.9	385.4	304.0	253.0	237.4
52.5°	407.6	352.1	272.9	224.1	210.1
55°	378.0	320.3	240.4	196.0	182.0
57.5°	347.7	288.5	211.6	170.1	158.3
60°	316.6	257.4	181.2	143.5	131.7
62.5°	286.3	227.1	155.3	119.8	113.9
65°	255.2	195.3	128.7	103.6	101.3
67.5°	225.6	165.7	103.6	91.0	88.8
70°	194.5	136.8	85.8	78.4	75.4
72.5°	165.0	110.2	71.7	65.8	64.4
75°	136.1	84.3	59.2	54.0	53.3
77.5°	107.3	59.9	46.6	43.6	42.2
80°	80.6	42.9	35.5	32.5	32.5
82.5°	56.2	28.8	24.4	22.9	22.9
85°	31.8	16.3	14.1	14.1	14.1
87.5°	11.8	5.9	5.9	5.2	5.2
90°	0.4	4.6	12.4	11.7	12.0
92.5°	7.8	10.6	11.0	11.3	11.3
95°	18.4	21.9	22.6	22.6	21.9
97.5°	30.7	33.9	35.3	35.3	35.3
100°	44.9	47.7	48.8	48.8	48.4
102.5°	59.7	61.8	63.3	63.6	63.3
105°	76.0	77.0	77.7	78.5	78.5
107.5°	92.2	93.6	93.6	94.0	92.2
110°	107.8	109.9	109.9	109.9	108.8



TEST NUMBER: P999735

CATALOG NUMBER: SA2XXRDIP-B485D330UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	124.7	126.9	126.5	125.5	124.7
115°	141.4	143.5	142.8	142.4	141.4
117.5°	158.0	160.8	159.0	158.0	156.9
120°	174.6	177.4	174.6	174.6	173.5
122.5°	189.8	193.3	191.5	190.5	189.8
125°	205.7	208.9	207.8	206.7	206.4
127.5°	221.2	225.1	223.7	222.3	221.2
130°	235.7	240.3	239.6	238.9	237.5
132.5°	252.0	255.5	255.9	254.1	253.0
135°	266.1	270.0	270.7	270.3	269.3
137.5°	281.7	284.8	285.5	285.2	283.8
140°	295.4	298.6	300.4	300.4	299.0
142.5°	309.6	312.8	313.8	314.2	312.8
145°	323.0	325.5	327.6	328.0	326.5
147.5°	335.0	338.2	339.6	340.3	338.9
150°	347.4	349.5	350.9	352.0	350.9
152.5°	358.3	360.5	362.2	363.6	362.2
155°	369.3	370.4	371.4	373.2	372.1
157.5°	378.8	379.5	380.3	382.7	381.0
160°	387.3	388.0	388.4	390.5	389.1
162.5°	395.1	395.1	395.4	397.9	396.2
165°	401.8	401.5	401.5	403.9	402.2
167.5°	407.8	406.8	406.8	409.2	407.5
170°	412.4	411.4	411.0	413.5	411.4
172.5°	415.6	414.5	414.2	416.7	414.5
175°	418.1	417.0	416.3	418.8	416.7
177.5°	419.5	418.4	417.7	419.8	417.7
180°	418.8	418.8	418.8	418.8	418.8

(END OF REPORT)