

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998720

Luminaire Tested: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998720
REPORT IS A COMBINATION OF REPORTS P984465 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6875.8 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998720

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P998720

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	93	89	84	81	84	80	76	73	64	61	59	49	47	46	36	34	33
2	85	77	70	65	76	69	64	59	55	51	48	43	40	37	31	29	27
3	77	67	60	54	69	61	54	49	48	44	40	37	34	31	27	25	23
4	70	59	51	45	63	53	46	41	43	38	34	33	29	26	24	21	19
5	64	52	44	38	57	47	40	35	38	33	29	29	26	23	21	19	17
6	59	47	39	33	53	42	35	30	34	29	25	26	23	20	19	17	15
7	54	42	34	28	49	38	31	26	31	26	22	24	20	17	17	15	13
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	13	11
9	47	35	27	22	42	31	25	20	26	20	17	20	16	14	15	12	10
10	44	32	24	20	39	29	22	18	23	19	15	18	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11147	11147	11147
5°	11197	10672	10612
10°	11122	10301	10152
15°	10965	9919	9680
20°	10767	9518	9232
25°	10573	9134	8827
30°	10297	8743	8425
35°	10020	8366	8130
40°	9729	8041	7836
45°	9450	7745	7580
50°	9152	7473	7328
55°	8839	7184	7072
60°	8454	6883	6801
65°	8055	6537	6491
70°	7600	6165	6156
75°	7021	5793	5842
80°	6108	5405	5514
85°	5184	5040	5232

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9450 cd/sqm

TEST NUMBER: P998720

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.8	1.0
10°-20°	191.5	2.8
20°-30°	290.1	4.2
30°-40°	353.3	5.1
40°-50°	380.1	5.5
50°-60°	369.1	5.4
60°-70°	322.4	4.7
70°-80°	248.1	3.6
80°-90°	170.0	2.5
90°-100°	358.0	5.2
100°-110°	906.3	13.2
110°-120°	920.0	13.4
120°-130°	741.9	10.8
130°-140°	584.3	8.5
140°-150°	433.8	6.3
150°-160°	303.4	4.4
160°-170°	178.7	2.6
170°-180°	58.1	0.8
0°-30°	548.3	8.0
0°-40°	901.6	13.1
0°-60°	1650.8	24.0
0°-90°	2391.3	34.8
90°-120°	2184.3	31.8
90°-150°	3944.2	57.4
90°-180°	4484.0	65.2
0°-180°	6875.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	704	704	704	704	704	
5°	706	703	697	703	702	67
15°	674	676	676	685	684	190
25°	612	620	629	641	644	282
35°	528	545	564	587	594	330
45°	433	460	496	528	538	334
55°	332	368	422	458	472	297
65°	227	277	337	379	392	225
75°	126	183	248	292	305	133
85°	37	100	165	208	222	39
90°	11	85	174	213	226	10
95°	49	155	570	327	300	48
105°	146	247	943	1652	1436	155
115°	252	329	777	1569	1815	250
125°	348	412	723	1259	1460	310
135°	407	486	691	1038	1192	315
145°	464	533	676	846	930	291
155°	528	570	657	743	772	243
165°	575	592	629	667	678	162
175°	599	600	605	612	611	57
180°	600	600	600	600	600	

TEST NUMBER: P998720

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	704.2	704.2	704.2	704.2	704.2
2.5°	709.3	706.2	699.1	704.2	702.2
5°	706.2	703.2	697.1	703.2	702.2
7.5°	701.1	699.1	694.0	701.1	700.1
10°	695.0	693.0	689.9	698.1	697.1
12.5°	684.8	685.8	683.8	692.0	690.9
15°	673.6	675.6	675.6	684.8	683.8
17.5°	659.3	663.4	666.4	675.6	675.6
20°	645.0	650.1	654.2	665.4	665.4
22.5°	629.7	635.8	641.9	653.2	655.2
25°	612.4	619.5	628.7	640.9	644.0
27.5°	591.9	603.2	613.4	628.7	630.7
30°	571.5	584.8	598.1	614.4	617.5
32.5°	549.1	564.4	580.7	600.1	606.2
35°	527.6	545.0	564.4	586.8	594.0
37.5°	504.2	523.6	548.1	572.5	579.7
40°	480.7	503.1	530.7	557.2	566.4
42.5°	458.2	480.7	513.4	543.0	552.1
45°	432.7	460.3	496.0	527.6	537.8
47.5°	408.2	437.8	478.7	511.3	522.5
50°	382.7	414.4	460.3	495.0	506.2
52.5°	358.2	391.9	440.9	476.6	488.9
55°	331.7	368.4	421.5	458.2	471.5
57.5°	306.2	347.0	400.1	439.9	453.1
60°	278.6	322.5	380.7	419.5	433.7
62.5°	254.1	300.1	358.2	400.1	413.3
65°	226.6	276.6	336.8	378.6	391.9
67.5°	202.1	254.1	315.4	357.2	371.5
70°	175.5	228.6	291.9	335.8	348.0
72.5°	151.0	206.2	270.5	313.3	328.6
75°	125.5	182.7	248.0	291.9	305.2
77.5°	101.0	160.2	226.6	270.5	284.7
80°	76.5	138.8	205.1	248.0	262.3
82.5°	56.1	117.4	184.7	227.6	240.9
85°	36.7	100.0	165.3	208.2	222.5
87.5°	22.5	83.7	149.0	190.8	204.1
90°	11.4	85.0	173.9	213.0	225.9
92.5°	26.5	118.2	303.3	247.2	248.0
95°	48.6	155.4	569.9	326.9	300.0
97.5°	67.1	182.0	847.8	490.8	380.7
100°	96.0	205.4	1014.0	822.6	564.2
102.5°	121.5	226.8	1012.6	1286.0	948.6
105°	145.9	247.1	943.2	1652.4	1435.6
107.5°	173.6	267.4	878.2	1779.8	1761.1
110°	200.3	288.2	832.9	1749.8	1889.1

TEST NUMBER: P998720

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.7	309.0	800.4	1668.2	1879.6
115°	252.3	328.7	776.9	1568.9	1815.0
117.5°	279.0	349.4	760.5	1474.5	1721.3
120°	304.4	369.6	746.4	1388.4	1632.3
122.5°	328.6	391.4	735.5	1320.7	1537.7
125°	348.3	411.8	722.7	1258.8	1460.1
127.5°	365.6	432.2	713.1	1203.8	1386.2
130°	380.6	451.2	704.7	1149.3	1323.7
132.5°	394.5	469.6	697.4	1093.1	1260.0
135°	407.3	485.8	691.1	1038.1	1191.7
137.5°	420.0	499.7	686.0	982.4	1124.7
140°	435.0	511.4	680.7	932.6	1055.3
142.5°	450.0	521.8	678.7	885.4	986.9
145°	464.0	533.3	676.4	845.8	930.0
147.5°	480.2	542.6	673.0	811.3	877.9
150°	496.4	551.8	669.5	785.0	834.6
152.5°	512.5	561.0	663.7	763.6	801.1
155°	527.5	569.6	656.8	742.8	772.2
157.5°	540.2	576.6	649.9	723.2	746.8
160°	552.9	583.6	643.0	703.6	722.6
162.5°	565.6	588.7	637.2	685.1	699.5
165°	574.9	592.2	629.1	667.2	677.6
167.5°	582.9	595.6	622.2	651.0	656.8
170°	591.0	597.4	616.4	636.0	638.3
172.5°	595.6	599.0	609.5	622.8	623.3
175°	599.1	599.7	604.9	612.3	610.6
177.5°	601.4	600.2	600.2	604.9	601.4
180°	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P998720

CATALOG NUMBER: SA2XXDIP-B675D1080UB40-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.01	12.78	13.08	13.85	15.32	15.08	15.85	16.15	16.93	18.40
	3H	13.46	14.16	14.54	15.24	16.73	17.67	18.36	18.74	19.45	20.93
	4H	13.93	14.60	15.02	15.68	17.17	18.91	19.58	20.00	20.66	22.16
	6H	14.21	14.82	15.31	15.91	17.42	20.21	20.82	21.30	21.91	23.41
	8H	14.27	14.85	15.37	15.96	17.46	20.86	21.45	21.97	22.55	24.05
	12H	14.28	14.84	15.39	15.94	17.46	21.59	22.14	22.69	23.24	24.77
4H	2H	13.05	13.71	14.14	14.80	16.29	15.40	16.06	16.50	17.15	18.64
	3H	14.75	15.31	15.85	16.42	17.93	18.19	18.75	19.29	19.86	21.36
	4H	15.37	15.88	16.47	16.99	18.51	19.60	20.12	20.71	21.22	22.74
	6H	15.78	16.22	16.89	17.35	18.87	21.06	21.51	22.18	22.64	24.15
	8H	15.88	16.30	17.00	17.42	18.96	21.82	22.24	22.93	23.35	24.89
	12H	15.92	16.30	17.05	17.43	18.97	22.64	23.02	23.77	24.15	25.69
8H	4H	16.15	16.57	17.26	17.69	19.22	19.74	20.16	20.85	21.27	22.81
	6H	16.78	17.13	17.91	18.29	19.82	21.36	21.71	22.50	22.87	24.40
	8H	17.00	17.31	18.14	18.45	20.00	22.25	22.56	23.39	23.70	25.25
	12H	17.13	17.40	18.27	18.54	20.12	23.24	23.51	24.39	24.65	26.24
12H	4H	16.34	16.72	17.47	17.85	19.40	19.71	20.09	20.84	21.22	22.76
	6H	17.11	17.42	18.25	18.56	20.11	21.39	21.70	22.53	22.83	24.39
	8H	17.41	17.68	18.56	18.82	20.41	22.31	22.58	23.46	23.72	25.31