

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999748

Luminaire Tested: SA2XXRDIP-B485D530UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999748
REPORT IS A COMBINATION OF REPORTS P988303 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D530UB27-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3731.3 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999748

CATALOG NUMBER: SA2XXRDIP-B485D530UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999748

CATALOG NUMBER: SA2XXRDIP-B485D530UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45	45	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39	39	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	39	38	33	33	33
3	81	72	65	60	74	66	60	56	56	51	48	46	43	40	37	35	33	29	29	29
4	74	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25	25	25
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22	22	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	27	25	22	19	19	19
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17	17	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16	14	14	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12899	12899	12899
5°	12920	12273	12182
10°	12793	11639	11256
15°	12618	10892	10200
20°	12385	10043	9096
25°	12147	9172	8087
30°	11827	8322	6983
35°	11513	7466	6036
40°	11194	6626	5061
45°	10824	5757	4210
50°	10441	4921	3427
55°	10043	4085	2721
60°	9577	3267	2059
65°	9044	2490	1673
70°	8402	1806	1330
75°	7591	1378	1016
80°	6419	933	681
85°	4478	427	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10824 cd/sqm

TEST NUMBER: P999748

CATALOG NUMBER: SA2XXRDIP-B485D530UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	2.0
10°-20°	209.7	5.6
20°-30°	294.4	7.9
30°-40°	320.9	8.6
40°-50°	294.9	7.9
50°-60°	231.6	6.2
60°-70°	150.7	4.0
70°-80°	77.6	2.1
80°-90°	21.7	0.6
90°-100°	119.4	3.2
100°-110°	403.6	10.8
110°-120°	424.3	11.4
120°-130°	348.9	9.4
130°-140°	280.4	7.5
140°-150°	211.8	5.7
150°-160°	148.9	4.0
160°-170°	87.7	2.3
170°-180°	28.5	0.8
0°-30°	580.4	15.6
0°-40°	901.3	24.2
0°-60°	1427.8	38.3
0°-90°	1677.8	45.0
90°-120°	947.3	25.4
90°-150°	1788.4	47.9
90°-180°	2053.0	55.0
0°-180°	3731.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	815	815	815	815	815	
5°	815	811	802	808	806	77
15°	775	767	742	728	720	218
25°	704	680	631	601	590	324
35°	606	569	504	457	441	379
45°	496	446	369	316	299	383
55°	377	319	240	195	181	337
65°	254	195	128	103	101	252
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	1	8	19	18	19	3
95°	20	49	222	84	65	20
105°	69	104	420	750	638	73
115°	122	154	351	725	840	121
125°	170	201	338	587	681	151
135°	199	238	334	493	565	154
145°	228	262	332	412	451	143
155°	259	280	322	364	379	119
165°	282	291	309	327	332	80
175°	294	294	297	300	300	28
180°	294	294	294	294	294	

TEST NUMBER: P999748

CATALOG NUMBER: SA2XXRDIP-B485D530UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	814.9	814.9	814.9	814.9	814.9
2.5°	818.6	814.9	806.8	814.2	812.7
5°	814.9	811.2	801.7	808.3	806.1
7.5°	808.3	803.9	793.5	796.5	792.8
10°	799.4	794.3	779.5	777.3	772.9
12.5°	788.4	781.7	761.8	757.4	749.3
15°	775.1	767.0	741.9	727.9	720.5
17.5°	759.6	747.8	716.8	700.6	688.8
20°	741.9	727.2	690.3	671.9	655.6
22.5°	722.7	705.8	663.0	637.9	626.9
25°	703.6	680.0	631.3	601.1	590.0
27.5°	680.7	655.6	601.8	567.1	550.2
30°	656.4	628.3	569.3	531.7	511.8
32.5°	632.8	598.8	538.4	494.1	475.7
35°	606.2	568.6	503.7	457.2	441.0
37.5°	580.4	539.8	471.3	420.4	401.9
40°	553.1	508.9	437.3	385.0	365.8
42.5°	525.1	477.9	403.4	348.8	330.4
45°	495.6	446.2	368.7	316.4	298.7
47.5°	467.6	415.2	335.6	283.2	267.0
50°	436.6	384.2	303.1	252.2	236.7
52.5°	406.4	351.0	272.1	223.5	209.4
55°	376.9	319.3	239.7	195.4	181.4
57.5°	346.6	287.6	210.9	169.6	157.8
60°	315.6	256.6	180.7	143.1	131.3
62.5°	285.4	226.4	154.9	119.5	113.6
65°	254.4	194.7	128.3	103.2	101.0
67.5°	224.9	165.2	103.2	90.7	88.5
70°	194.0	136.4	85.5	78.2	75.2
72.5°	164.5	109.9	71.5	65.6	64.2
75°	135.7	84.1	59.0	53.8	53.1
77.5°	106.9	59.7	46.5	43.5	42.0
80°	80.4	42.8	35.4	32.4	32.4
82.5°	56.0	28.8	24.3	22.9	22.9
85°	31.7	16.2	14.0	14.0	14.0
87.5°	11.8	5.9	5.9	5.2	5.2
90°	0.6	7.6	19.3	18.4	18.7
92.5°	8.5	26.9	87.2	40.2	34.6
95°	19.8	48.7	222.0	83.8	64.6
97.5°	29.5	64.2	361.9	168.2	108.2
100°	43.6	78.8	447.5	335.0	202.8
102.5°	56.6	91.8	450.3	566.4	395.3
105°	69.1	104.2	419.7	750.2	638.3
107.5°	82.7	116.6	391.4	816.8	802.0
110°	96.3	129.4	372.1	806.0	868.9

TEST NUMBER: P999748

CATALOG NUMBER: SA2XXRDIP-B485D530UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	108.7	141.6	359.7	769.4	867.7
115°	121.8	153.8	351.2	724.7	840.0
117.5°	135.4	166.0	346.6	682.0	798.1
120°	147.8	177.9	342.7	643.7	757.8
122.5°	159.7	190.0	340.4	614.0	715.9
125°	169.9	201.0	337.6	587.0	681.4
127.5°	178.4	211.6	335.9	564.2	649.1
130°	185.8	220.9	334.7	540.9	622.5
132.5°	192.6	230.0	334.2	516.8	594.7
135°	199.4	237.9	333.6	493.4	564.7
137.5°	205.6	244.6	333.6	469.6	535.8
140°	213.0	251.0	333.0	448.6	505.8
142.5°	220.3	256.0	333.0	428.5	475.8
145°	227.7	261.6	331.9	412.0	450.9
147.5°	235.6	266.2	330.2	397.6	428.8
150°	243.6	270.7	328.5	385.2	409.5
152.5°	251.5	275.2	325.7	374.6	393.1
155°	258.8	279.6	322.3	364.5	378.9
157.5°	265.1	282.9	318.9	354.8	366.5
160°	271.3	286.3	315.5	345.2	354.6
162.5°	277.5	288.8	312.7	336.2	343.2
165°	282.1	290.6	308.7	327.4	332.5
167.5°	286.0	292.2	305.3	319.5	322.3
170°	290.0	293.2	302.5	312.1	313.2
172.5°	292.3	294.0	299.1	305.6	305.9
175°	294.0	294.2	296.8	300.5	299.6
177.5°	295.1	294.5	294.5	296.8	295.1
180°	294.5	294.5	294.5	294.5	294.5

(END OF REPORT)