

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999770

Luminaire Tested: SA2XXRDIP-B485D530UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999770
REPORT IS A COMBINATION OF REPORTS P988325 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D530UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3780.4 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999770

CATALOG NUMBER: SA2XXRDIP-B485D530UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999770

CATALOG NUMBER: SA2XXRDIP-B485D530UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	39	38
3	81	72	65	60	74	66	60	56	56	51	48	46	43	40	37	35	33
4	74	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	27	25	22
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13069	13069	13069
5°	13090	12434	12342
10°	12961	11793	11403
15°	12784	11036	10334
20°	12548	10176	9216
25°	12306	9292	8192
30°	11982	8432	7075
35°	11665	7564	6115
40°	11342	6713	5127
45°	10966	5834	4265
50°	10577	4986	3472
55°	10174	4138	2757
60°	9704	3310	2086
65°	9165	2523	1696
70°	8510	1831	1348
75°	7692	1397	1030
80°	6499	946	692
85°	4534	433	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10966 cd/sqm

TEST NUMBER: P999770

CATALOG NUMBER: SA2XXRDIP-B485D530UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	2.0
10°-20°	212.4	5.6
20°-30°	298.2	7.9
30°-40°	325.1	8.6
40°-50°	298.8	7.9
50°-60°	234.7	6.2
60°-70°	152.7	4.0
70°-80°	78.6	2.1
80°-90°	22.0	0.6
90°-100°	121.0	3.2
100°-110°	409.0	10.8
110°-120°	429.9	11.4
120°-130°	353.5	9.4
130°-140°	284.1	7.5
140°-150°	214.6	5.7
150°-160°	150.9	4.0
160°-170°	88.8	2.3
170°-180°	28.9	0.8
0°-30°	588.0	15.6
0°-40°	913.1	24.2
0°-60°	1446.5	38.3
0°-90°	1699.9	45.0
90°-120°	959.8	25.4
90°-150°	1811.9	47.9
90°-180°	2080.0	55.0
0°-180°	3780.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	826	826	826	826	826	
5°	826	822	812	819	817	78
15°	785	777	752	738	730	221
25°	713	689	640	609	598	328
35°	614	576	510	463	447	384
45°	502	452	374	320	303	388
55°	382	324	243	198	184	341
65°	258	197	130	105	102	256
75°	138	85	60	54	54	145
85°	32	16	14	14	14	37
90°	1	8	20	19	19	3
95°	20	49	225	85	65	21
105°	70	106	425	760	647	74
115°	123	156	356	734	851	122
125°	172	204	342	595	690	153
135°	202	241	338	500	572	156
145°	231	265	336	418	457	145
155°	262	283	326	369	384	121
165°	286	294	313	332	337	81
175°	298	298	301	304	304	28
180°	298	298	298	298	298	

TEST NUMBER: P999770

CATALOG NUMBER: SA2XXRDIP-B485D530UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	825.6	825.6	825.6	825.6	825.6
2.5°	829.4	825.6	817.4	824.9	823.4
5°	825.6	821.9	812.2	818.9	816.7
7.5°	818.9	814.4	804.0	806.9	803.2
10°	809.9	804.7	789.8	787.5	783.0
12.5°	798.7	792.0	771.8	767.3	759.1
15°	785.3	777.1	751.7	737.5	730.0
17.5°	769.6	757.6	726.2	709.8	697.9
20°	751.7	736.7	699.4	680.7	664.2
22.5°	732.2	715.0	671.7	646.3	635.1
25°	712.8	688.9	639.6	608.9	597.7
27.5°	689.6	664.2	609.7	574.6	557.4
30°	665.0	636.6	576.8	538.7	518.5
32.5°	641.1	606.7	545.4	500.6	481.9
35°	614.2	576.1	510.3	463.2	446.8
37.5°	588.0	546.9	477.4	425.9	407.2
40°	560.4	515.5	443.1	390.0	370.6
42.5°	532.0	484.2	408.7	353.4	334.7
45°	502.1	452.0	373.6	320.5	302.6
47.5°	473.7	420.7	340.0	286.9	270.5
50°	442.3	389.3	307.1	255.5	239.8
52.5°	411.7	355.7	275.7	226.4	212.2
55°	381.8	323.5	242.8	198.0	183.8
57.5°	351.2	291.4	213.7	171.8	159.9
60°	319.8	260.0	183.1	145.0	133.0
62.5°	289.2	229.4	156.9	121.0	115.1
65°	257.8	197.3	130.0	104.6	102.4
67.5°	227.9	167.4	104.6	91.9	89.7
70°	196.5	138.2	86.7	79.2	76.2
72.5°	166.6	111.3	72.5	66.5	65.0
75°	137.5	85.2	59.8	54.5	53.8
77.5°	108.3	60.5	47.1	44.1	42.6
80°	81.4	43.3	35.9	32.9	32.9
82.5°	56.8	29.1	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.6	7.8	19.5	18.6	18.9
92.5°	8.6	27.2	88.4	40.7	35.0
95°	20.1	49.4	224.9	84.9	65.4
97.5°	29.8	65.2	366.7	170.4	109.6
100°	44.2	79.8	453.3	339.4	205.4
102.5°	57.4	93.0	456.2	573.9	400.5
105°	70.0	105.6	425.2	760.0	646.7
107.5°	83.8	118.2	396.5	827.5	812.6
110°	97.6	131.1	377.0	816.6	880.3

TEST NUMBER: P999770

CATALOG NUMBER: SA2XXRDIP-B485D530UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	110.2	143.5	364.4	779.6	879.1
115°	123.4	155.8	355.8	734.2	851.0
117.5°	137.2	168.1	351.2	690.9	808.6
120°	149.8	180.2	347.2	652.2	767.8
122.5°	161.8	192.5	344.9	622.0	725.3
125°	172.2	203.8	342.0	594.8	690.3
127.5°	180.8	214.4	340.3	571.6	657.6
130°	188.2	223.8	339.1	548.0	630.7
132.5°	195.1	233.0	338.6	523.6	602.5
135°	202.0	241.0	338.0	499.8	572.1
137.5°	208.3	247.9	338.0	475.8	542.9
140°	215.8	254.2	337.4	454.5	512.4
142.5°	223.2	259.4	337.4	434.2	482.0
145°	230.7	265.1	336.3	417.5	456.8
147.5°	238.7	269.7	334.6	402.8	434.4
150°	246.8	274.3	332.8	390.2	414.9
152.5°	254.8	278.9	330.0	379.6	398.3
155°	262.2	283.2	326.5	369.2	383.9
157.5°	268.6	286.6	323.1	359.5	371.3
160°	274.9	290.0	319.6	349.8	359.2
162.5°	281.2	292.7	316.8	340.6	347.8
165°	285.8	294.4	312.7	331.6	336.9
167.5°	289.8	296.2	309.3	323.6	326.5
170°	293.8	297.0	306.4	316.2	317.3
172.5°	296.1	297.8	303.0	309.6	309.9
175°	297.8	298.1	300.7	304.4	303.6
177.5°	299.0	298.4	298.4	300.7	299.0
180°	298.4	298.4	298.4	298.4	298.4

(END OF REPORT)