

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998757

Luminaire Tested: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998757
REPORT IS A COMBINATION OF REPORTS P984503 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4125.0 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	74	72	68	67	65
2	95	87	81	76	89	83	78	73	75	71	67	68	64	62	61	58	56
3	87	77	70	64	82	74	67	62	67	62	57	60	56	53	55	51	49
4	80	69	61	55	75	66	59	53	60	54	50	54	50	46	49	46	43
5	74	62	54	48	70	59	52	46	54	48	43	49	44	40	45	41	38
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	33
7	63	51	43	37	60	49	42	36	45	39	34	41	36	32	38	33	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25
10	52	40	32	27	49	38	31	27	35	29	25	32	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21137	21137	21137	21137
5°	21187	22537	21268	17929
10°	20941	24603	21073	14781
15°	20433	25949	20718	12452
20°	20114	24365	20114	10822
25°	19473	20932	19562	9678
30°	18418	16454	18769	8766
35°	17484	11378	17776	8020
40°	16410	8590	16596	7427
45°	15085	7060	15332	6785
50°	13942	6196	13965	6211
55°	12636	5279	12716	5588
60°	11243	4410	11397	4877
65°	9996	3587	10178	4165
70°	8757	2815	8978	3359
75°	7351	2042	7636	2437
80°	5732	1295	6148	1446
85°	3772	651	4054	482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21850 cd/sqm

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	3.1
10°-20°	370.2	9.0
20°-30°	537.2	13.0
30°-40°	566.3	13.7
40°-50°	501.2	12.1
50°-60°	400.2	9.7
60°-70°	271.8	6.6
70°-80°	139.1	3.4
80°-90°	34.1	0.8
90°-100°	26.1	0.6
100°-110°	82.9	2.0
110°-120°	141.8	3.4
120°-130°	186.4	4.5
130°-140°	209.3	5.1
140°-150°	205.2	5.0
150°-160°	172.1	4.2
160°-170°	114.2	2.8
170°-180°	39.9	1.0
0°-30°	1034.6	25.1
0°-40°	1600.9	38.8
0°-60°	2502.3	60.7
0°-90°	2947.2	71.4
90°-120°	250.7	6.1
90°-150°	851.6	20.6
90°-180°	1178.0	28.6
0°-180°	4125.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1335	1335	1335	1335	1335	
5°	1336	1491	1341	1186	1336	127
15°	1255	1833	1273	880	1255	355
25°	1128	1527	1133	706	1128	516
35°	921	831	936	586	921	576
45°	691	501	702	481	691	536
55°	474	352	477	373	474	423
65°	281	217	286	252	281	280
75°	131	107	136	127	131	141
85°	27	28	29	20	27	31
90°	0	12	0	12	0	3
95°	18	22	18	22	18	21
105°	76	79	76	79	76	81
115°	142	142	142	142	142	141
125°	207	208	207	208	207	185
135°	268	271	268	271	268	207
145°	325	328	325	328	325	203
155°	372	374	372	374	372	171
165°	404	405	404	405	404	114
175°	421	419	421	419	421	40
180°	421	421	421	421	421	

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1342.4	1345.5	1350.7	1351.7	1361.9	1370.2	1379.4	1379.4	1382.5	1381.4	1373.2
5°	1336.3	1345.5	1358.9	1370.2	1388.6	1396.8	1409.2	1418.4	1426.6	1432.8	1431.7
7.5°	1326.0	1342.4	1361.9	1383.5	1408.1	1422.5	1440.0	1456.4	1467.7	1477.9	1485.1
10°	1308.6	1336.3	1363.0	1391.7	1423.5	1443.0	1463.6	1485.1	1502.6	1522.1	1540.5
12.5°	1285.0	1325.0	1357.8	1395.8	1434.8	1456.4	1489.2	1505.6	1539.5	1588.8	1602.1
15°	1255.2	1309.6	1340.4	1388.6	1440.0	1457.4	1502.6	1529.2	1599.0	1629.8	1666.8
17.5°	1227.5	1288.1	1329.1	1384.5	1434.8	1468.7	1512.8	1567.2	1625.7	1669.9	1710.9
20°	1204.9	1263.4	1312.7	1374.3	1437.9	1481.0	1527.2	1592.9	1656.5	1701.7	1733.5
22.5°	1153.6	1228.5	1286.0	1354.8	1431.7	1491.3	1535.4	1607.2	1676.0	1703.7	1731.4
25°	1127.9	1192.6	1259.3	1337.3	1427.6	1498.5	1536.4	1616.5	1677.0	1687.3	1693.5
27.5°	1080.7	1153.6	1231.6	1320.9	1426.6	1486.1	1534.4	1607.2	1655.5	1648.3	1629.8
30°	1022.2	1111.5	1197.7	1294.2	1412.2	1476.9	1522.1	1588.8	1613.4	1576.5	1543.6
32.5°	979.1	1063.3	1158.7	1270.6	1395.8	1457.4	1501.5	1553.9	1559.0	1492.3	1436.9
35°	920.6	1014.0	1121.8	1239.8	1368.1	1423.5	1464.6	1496.4	1471.8	1378.4	1312.7
37.5°	868.3	960.7	1075.6	1195.7	1330.1	1384.5	1417.4	1422.5	1361.9	1279.8	1183.4
40°	810.8	906.3	1026.3	1152.6	1288.1	1335.3	1355.8	1340.4	1253.2	1157.7	1045.8
42.5°	753.3	847.8	977.1	1106.4	1234.7	1274.7	1282.9	1240.8	1134.1	1022.2	892.9
45°	690.7	789.3	918.6	1048.9	1173.1	1195.7	1196.7	1136.2	1009.9	892.9	772.8
47.5°	639.4	730.8	859.0	989.4	1094.1	1109.5	1103.3	1033.5	896.0	764.6	659.9
50°	583.0	670.2	797.5	925.8	1015.0	1019.2	1003.8	904.2	769.8	649.7	566.5
52.5°	522.4	610.7	727.7	850.8	930.9	924.7	895.0	788.2	662.0	562.4	498.8
55°	474.2	552.2	662.0	782.1	838.5	821.1	788.2	679.4	579.9	495.7	440.3
57.5°	420.8	489.6	597.3	702.0	734.9	718.4	685.6	584.0	491.6	428.0	391.0
60°	370.5	433.1	527.5	614.8	640.4	623.0	585.0	493.7	427.0	373.6	345.9
62.5°	324.3	378.7	457.7	537.8	548.1	530.6	497.8	423.9	366.4	324.3	303.8
65°	281.2	332.5	396.2	456.7	466.0	447.5	413.6	360.2	312.0	285.3	265.8
67.5°	239.1	280.2	336.6	380.8	385.9	368.5	340.7	297.6	267.9	239.1	224.8
70°	202.2	233.0	277.1	313.0	315.1	298.7	284.3	245.3	222.7	202.2	190.9
72.5°	166.3	187.8	221.7	248.4	249.4	239.1	225.8	201.2	181.7	167.3	156.0
75°	131.4	149.8	170.4	194.0	193.0	184.7	174.5	159.1	142.7	133.4	128.3
77.5°	100.6	111.9	128.3	143.7	143.7	139.6	133.4	122.1	111.9	102.6	97.5
80°	71.8	79.0	92.4	97.5	99.6	98.5	93.4	85.2	81.1	73.9	71.8
82.5°	46.2	51.3	57.5	62.6	65.7	63.6	62.6	58.5	52.3	50.3	48.2
85°	26.7	28.7	31.8	34.9	35.9	34.9	36.9	33.9	30.8	30.8	29.8
87.5°	11.3	12.3	14.4	14.4	15.4	15.4	14.4	15.4	15.4	14.4	13.3
90°	0.4	1.3	2.3	3.2	4.1	4.6	5.5	7.2	8.9	10.7	12.4
92.5°	7.8	8.4	9.1	9.7	10.4	10.7	10.7	10.8	10.9	10.9	11.0
95°	18.5	19.3	20.1	20.8	21.6	22.0	22.1	22.3	22.4	22.6	22.8
97.5°	30.9	31.6	32.3	33.0	33.7	34.1	34.3	34.6	34.9	35.3	35.6
100°	45.1	45.7	46.4	47.0	47.7	48.0	48.1	48.4	48.6	48.9	49.1
102.5°	60.1	60.6	61.0	61.5	62.0	62.2	62.4	62.7	63.0	63.3	63.6
105°	76.4	76.6	76.9	77.1	77.4	77.5	77.6	77.7	77.9	78.0	78.2
107.5°	92.8	93.1	93.4	93.7	94.0	94.2	94.2	94.2	94.2	94.2	94.2
110°	108.4	108.9	109.4	109.9	110.4	110.6	110.6	110.6	110.6	110.6	110.6

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	125.5	126.0	126.4	126.9	127.4	127.6	127.6	127.5	127.4	127.4	127.3
115°	142.2	142.7	143.1	143.6	144.1	144.3	144.2	144.1	143.9	143.8	143.6
117.5°	158.9	159.5	160.2	160.8	161.5	161.8	161.6	161.2	160.8	160.4	160.0
120°	175.6	176.2	176.9	177.5	178.2	178.5	178.2	177.5	176.9	176.2	175.6
122.5°	190.9	191.7	192.5	193.3	194.1	194.5	194.3	193.9	193.5	193.1	192.7
125°	206.9	207.6	208.3	209.0	209.7	210.1	210.0	209.7	209.5	209.2	209.0
127.5°	222.5	223.4	224.3	225.2	226.1	226.5	226.3	226.0	225.7	225.3	225.0
130°	237.1	238.1	239.1	240.2	241.2	241.7	241.6	241.5	241.3	241.2	241.0
132.5°	253.5	254.3	255.1	255.8	256.6	257.0	257.0	257.1	257.2	257.3	257.4
135°	267.7	268.6	269.4	270.3	271.2	271.6	271.7	271.8	272.0	272.1	272.3
137.5°	283.3	284.0	284.7	285.4	286.1	286.5	286.6	286.7	286.9	287.0	287.2
140°	297.2	297.9	298.6	299.3	300.0	300.4	300.6	301.0	301.4	301.8	302.2
142.5°	311.4	312.1	312.8	313.5	314.2	314.6	314.7	315.0	315.2	315.5	315.7
145°	324.9	325.5	326.0	326.6	327.1	327.4	327.6	328.1	328.6	329.1	329.6
147.5°	337.0	337.7	338.4	339.1	339.8	340.2	340.4	340.7	341.0	341.3	341.6
150°	349.5	350.0	350.4	350.9	351.4	351.6	351.8	352.1	352.4	352.7	353.0
152.5°	360.5	361.0	361.4	361.9	362.4	362.6	362.8	363.2	363.6	364.0	364.4
155°	371.5	371.7	372.0	372.2	372.5	372.6	372.7	372.9	373.2	373.4	373.6
157.5°	381.1	381.3	381.4	381.6	381.7	381.8	381.9	382.0	382.2	382.3	382.5
160°	389.6	389.8	389.9	390.1	390.2	390.3	390.3	390.4	390.5	390.6	390.7
162.5°	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.6	397.7	397.7	397.8
165°	404.2	404.1	404.1	404.0	403.9	403.9	403.9	403.9	403.9	403.9	403.9
167.5°	410.3	410.1	409.8	409.6	409.3	409.2	409.2	409.2	409.2	409.2	409.2
170°	414.9	414.7	414.4	414.2	413.9	413.8	413.8	413.7	413.6	413.6	413.5
172.5°	418.1	417.9	417.6	417.4	417.1	417.0	417.0	416.9	416.8	416.8	416.7
175°	420.6	420.4	420.1	419.9	419.6	419.5	419.4	419.3	419.1	419.0	418.8
177.5°	422.0	421.8	421.5	421.3	421.0	420.9	420.8	420.7	420.5	420.4	420.2
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1387.6	1388.6	1390.7	1400.9	1406.1	1407.1	1403.0	1412.2	1415.3	1412.2	1410.2
5°	1453.3	1459.5	1471.8	1485.1	1484.1	1485.1	1491.3	1497.4	1499.5	1491.3	1494.3
7.5°	1510.8	1523.1	1536.4	1557.0	1557.0	1567.2	1571.3	1576.5	1588.8	1582.6	1580.6
10°	1576.5	1592.9	1617.5	1650.3	1651.4	1661.6	1671.9	1688.3	1693.5	1689.4	1691.4
12.5°	1658.6	1690.4	1692.4	1728.4	1744.8	1746.8	1763.2	1760.2	1770.4	1770.4	1787.9
15°	1694.5	1743.7	1771.5	1806.4	1816.6	1804.3	1817.6	1832.0	1833.0	1833.0	1832.0
17.5°	1759.1	1778.6	1806.4	1824.8	1828.9	1828.9	1830.0	1836.1	1832.0	1823.8	1830.0
20°	1772.5	1780.7	1791.0	1788.9	1791.0	1780.7	1770.4	1760.2	1761.2	1756.1	1771.5
22.5°	1747.9	1745.8	1722.2	1706.8	1706.8	1686.3	1666.8	1657.5	1648.3	1651.4	1656.5
25°	1686.3	1654.5	1625.7	1603.1	1598.0	1565.2	1538.5	1530.3	1514.9	1527.2	1529.2
27.5°	1587.7	1551.8	1505.6	1486.1	1459.5	1446.1	1427.6	1403.0	1371.2	1389.7	1386.6
30°	1482.0	1428.7	1390.7	1343.5	1301.4	1298.3	1263.4	1222.4	1205.9	1205.9	1215.2
32.5°	1364.0	1293.2	1237.8	1171.1	1130.0	1112.5	1070.5	1029.4	1038.7	1007.9	1019.2
35°	1226.5	1133.1	1063.3	998.6	967.8	947.3	892.9	870.3	845.7	831.3	858.0
37.5°	1095.1	987.3	898.0	827.2	815.9	779.0	742.0	727.7	713.3	719.5	718.4
40°	935.0	839.5	759.5	704.1	684.6	667.1	642.5	625.0	615.8	620.9	622.0
42.5°	790.3	710.2	650.7	611.7	595.3	583.0	570.6	556.3	553.2	553.2	557.3
45°	678.4	612.7	572.7	540.9	531.6	522.4	513.2	507.0	505.0	500.9	503.9
47.5°	589.1	536.8	512.1	488.5	478.3	476.2	468.0	464.9	460.8	459.8	460.8
50°	514.2	481.4	458.8	445.4	438.2	435.2	431.1	424.9	422.9	428.0	425.9
52.5°	461.9	431.1	418.7	405.4	401.3	397.2	391.0	392.1	391.0	389.0	389.0
55°	409.5	390.0	377.7	367.4	366.4	362.3	357.2	355.1	354.1	352.0	355.1
57.5°	367.4	352.0	340.7	331.5	327.4	327.4	322.3	318.2	318.2	317.1	318.2
60°	325.3	310.0	302.8	293.5	290.5	289.4	286.3	284.3	281.2	281.2	281.2
62.5°	286.3	274.0	265.8	257.6	258.6	253.5	249.4	247.3	247.3	248.4	248.4
65°	249.4	241.2	230.9	223.7	221.7	220.7	218.6	217.6	214.5	216.6	216.6
67.5°	215.5	204.2	198.1	195.0	191.9	190.9	188.8	186.8	185.8	184.7	186.8
70°	181.7	172.4	167.3	165.2	162.2	161.1	160.1	157.0	158.1	159.1	160.1
72.5°	150.9	142.7	141.6	135.5	135.5	135.5	131.4	133.4	132.4	130.3	132.4
75°	119.1	114.9	112.9	109.8	110.8	109.8	108.8	105.7	105.7	106.7	107.8
77.5°	94.4	90.3	89.3	86.2	84.2	86.2	84.2	83.1	83.1	84.2	84.2
80°	69.8	67.7	64.7	64.7	64.7	63.6	63.6	63.6	62.6	61.6	62.6
82.5°	46.2	46.2	45.2	44.1	45.2	43.1	44.1	44.1	44.1	44.1	44.1
85°	29.8	28.7	28.7	27.7	27.7	27.7	28.7	26.7	26.7	27.7	27.7
87.5°	13.3	13.3	13.3	14.4	13.3	13.3	13.3	14.4	13.3	13.3	13.3
90°	12.2	12.1	11.9	11.8	11.7	11.7	11.8	11.9	12.0	12.1	12.0
92.5°	11.1	11.2	11.3	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.8	22.8	22.8	22.8	22.8	22.7	22.5	22.4	22.2	22.0	22.2
97.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6
100°	49.1	49.1	49.1	49.1	49.1	49.1	49.0	48.9	48.8	48.7	48.8
102.5°	63.7	63.8	63.9	64.0	64.0	64.0	63.9	63.8	63.7	63.6	63.7
105°	78.4	78.5	78.7	78.8	78.9	78.9	78.9	78.9	78.9	78.9	78.9
107.5°	94.3	94.4	94.5	94.6	94.6	94.4	94.0	93.6	93.2	92.8	93.2
110°	110.6	110.6	110.6	110.6	110.6	110.5	110.2	110.0	109.7	109.5	109.7

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	127.1	126.8	126.6	126.3	126.2	126.1	126.0	125.8	125.7	125.5	125.7
115°	143.5	143.5	143.4	143.3	143.3	143.2	142.9	142.7	142.4	142.2	142.4
117.5°	159.8	159.5	159.3	159.0	158.9	158.8	158.5	158.3	158.0	157.8	158.0
120°	175.6	175.6	175.6	175.6	175.6	175.5	175.3	175.0	174.8	174.6	174.8
122.5°	192.5	192.2	192.0	191.7	191.6	191.5	191.4	191.2	191.1	190.9	191.1
125°	208.8	208.6	208.3	208.1	208.0	208.0	207.9	207.8	207.7	207.6	207.7
127.5°	224.7	224.4	224.1	223.8	223.6	223.5	223.2	223.0	222.7	222.5	222.7
130°	240.8	240.7	240.5	240.4	240.3	240.1	239.8	239.5	239.2	238.9	239.2
132.5°	257.0	256.6	256.2	255.8	255.6	255.5	255.2	255.0	254.7	254.5	254.7
135°	272.2	272.2	272.1	272.0	272.0	271.9	271.6	271.4	271.1	270.9	271.1
137.5°	287.1	287.1	287.0	286.9	286.9	286.7	286.4	286.1	285.8	285.5	285.8
140°	302.2	302.2	302.2	302.2	302.2	302.0	301.7	301.4	301.1	300.8	301.1
142.5°	315.8	315.8	315.9	316.0	316.0	315.8	315.5	315.2	314.9	314.6	314.9
145°	329.7	329.7	329.8	329.9	329.9	329.7	329.4	329.1	328.8	328.5	328.8
147.5°	341.8	342.0	342.1	342.3	342.4	342.2	341.9	341.6	341.2	340.9	341.2
150°	353.2	353.5	353.7	354.0	354.1	354.0	353.7	353.5	353.2	353.0	353.2
152.5°	364.7	365.0	365.3	365.6	365.8	365.6	365.3	365.0	364.7	364.4	364.7
155°	374.0	374.4	374.8	375.2	375.4	375.3	375.0	374.8	374.5	374.3	374.5
157.5°	383.1	383.6	384.2	384.7	385.0	384.8	384.4	384.0	383.6	383.2	383.6
160°	391.2	391.6	392.1	392.6	392.8	392.6	392.3	392.0	391.7	391.4	391.7
162.5°	398.4	398.9	399.5	400.0	400.3	400.1	399.7	399.3	398.9	398.5	398.9
165°	404.4	405.0	405.5	406.0	406.3	406.1	405.7	405.4	405.0	404.6	405.0
167.5°	409.8	410.3	410.9	411.4	411.7	411.5	411.1	410.7	410.3	409.9	410.3
170°	414.0	414.6	415.1	415.6	415.9	415.7	415.2	414.7	414.3	413.8	414.3
172.5°	417.2	417.8	418.3	418.8	419.1	418.9	418.4	417.9	417.5	417.0	417.5
175°	419.4	419.9	420.5	421.0	421.3	421.1	420.6	420.1	419.6	419.1	419.6
177.5°	420.7	421.1	421.6	422.1	422.3	422.1	421.6	421.1	420.7	420.2	420.7
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1415.3	1408.1	1402.0	1403.0	1408.1	1404.0	1393.8	1380.4	1375.3	1369.1	1375.3
5°	1500.5	1494.3	1482.0	1483.1	1480.0	1475.9	1459.5	1438.9	1438.9	1422.5	1420.5
7.5°	1584.7	1575.4	1567.2	1565.2	1553.9	1545.7	1531.3	1502.6	1491.3	1471.8	1460.5
10°	1679.1	1671.9	1662.7	1651.4	1645.2	1630.8	1607.2	1565.2	1544.6	1518.0	1498.5
12.5°	1774.5	1773.5	1753.0	1730.4	1729.4	1706.8	1690.4	1633.9	1606.2	1570.3	1524.1
15°	1835.1	1830.0	1818.7	1807.4	1810.5	1785.8	1748.9	1682.2	1663.7	1620.6	1571.3
17.5°	1834.1	1834.1	1831.0	1828.9	1825.9	1818.7	1798.1	1754.0	1724.2	1669.9	1623.7
20°	1775.6	1788.9	1792.0	1791.0	1801.2	1806.4	1805.3	1777.6	1754.0	1705.8	1658.6
22.5°	1658.6	1689.4	1702.7	1710.9	1732.5	1743.7	1770.4	1760.2	1754.0	1718.1	1678.1
25°	1549.8	1560.0	1600.1	1602.1	1631.9	1659.6	1686.3	1703.7	1726.3	1713.0	1679.1
27.5°	1409.2	1432.8	1461.5	1483.1	1489.2	1545.7	1589.8	1622.6	1674.0	1678.1	1666.8
30°	1250.1	1261.4	1308.6	1337.3	1370.2	1411.2	1474.8	1531.3	1577.5	1619.6	1633.9
32.5°	1056.1	1102.3	1130.0	1164.9	1193.6	1266.5	1344.5	1417.4	1470.7	1541.6	1572.3
35°	878.5	914.5	961.7	976.0	1028.4	1090.0	1191.6	1285.0	1366.1	1437.9	1500.5
37.5°	731.8	760.5	810.8	833.4	864.2	943.2	1028.4	1144.4	1241.9	1330.1	1408.1
40°	631.2	652.8	690.7	697.9	723.6	795.4	864.2	973.0	1102.3	1221.3	1306.5
42.5°	562.4	572.7	598.4	607.6	624.0	672.3	733.8	836.5	956.5	1079.7	1199.8
45°	513.2	520.4	535.7	544.0	564.5	586.0	636.3	718.4	812.9	937.0	1066.4
47.5°	469.0	478.3	484.4	489.6	500.9	524.5	557.3	617.9	708.2	822.1	947.3
50°	432.1	435.2	446.5	447.5	454.7	470.1	500.9	537.8	609.6	702.0	823.1
52.5°	395.1	398.2	405.4	412.6	415.7	428.0	448.5	479.3	532.7	605.5	713.3
55°	358.2	362.3	369.5	374.6	377.7	388.0	400.3	430.0	472.1	523.4	611.7
57.5°	321.2	330.5	332.5	335.6	340.7	352.0	363.3	380.8	413.6	460.8	525.5
60°	286.3	289.4	296.6	299.7	304.8	311.0	325.3	338.7	362.3	399.2	457.7
62.5°	250.4	257.6	260.7	263.8	267.9	275.1	284.3	298.7	319.2	349.0	395.1
65°	219.6	220.7	226.8	230.9	235.0	240.2	249.4	262.7	275.1	302.8	336.6
67.5°	189.9	191.9	194.0	198.1	203.2	208.3	216.6	223.7	239.1	257.6	284.3
70°	161.1	161.1	166.3	169.3	168.3	174.5	180.6	188.8	200.1	217.6	239.1
72.5°	135.5	134.5	138.6	139.6	141.6	145.7	149.8	158.1	164.2	177.6	194.0
75°	107.8	109.8	111.9	111.9	114.9	118.0	122.1	126.2	133.4	141.6	154.0
77.5°	85.2	85.2	87.2	88.3	91.3	90.3	94.4	98.5	103.7	110.8	120.1
80°	62.6	64.7	64.7	64.7	65.7	66.7	70.8	73.9	77.0	82.1	86.2
82.5°	44.1	44.1	46.2	46.2	46.2	48.2	48.2	49.3	51.3	54.4	57.5
85°	27.7	27.7	27.7	28.7	27.7	28.7	30.8	29.8	30.8	32.8	32.8
87.5°	13.3	13.3	13.3	13.3	13.3	14.4	13.3	14.4	15.4	15.4	15.4
90°	11.9	11.8	11.7	11.7	11.8	11.9	12.1	12.2	12.4	10.7	8.9
92.5°	11.4	11.4	11.4	11.4	11.4	11.3	11.2	11.1	11.0	10.9	10.9
95°	22.4	22.5	22.7	22.8	22.8	22.8	22.8	22.8	22.8	22.6	22.4
97.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.3	34.9
100°	48.9	49.0	49.1	49.1	49.1	49.1	49.1	49.1	49.1	48.9	48.6
102.5°	63.8	63.9	64.0	64.0	64.0	63.9	63.8	63.7	63.6	63.3	63.0
105°	78.9	78.9	78.9	78.9	78.8	78.7	78.5	78.4	78.2	78.0	77.9
107.5°	93.6	94.0	94.4	94.6	94.6	94.5	94.4	94.3	94.2	94.2	94.2
110°	110.0	110.2	110.5	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	125.8	126.0	126.1	126.2	126.3	126.6	126.8	127.1	127.3	127.4	127.4
115°	142.7	142.9	143.2	143.3	143.3	143.4	143.5	143.5	143.6	143.8	143.9
117.5°	158.3	158.5	158.8	158.9	159.0	159.3	159.5	159.8	160.0	160.4	160.8
120°	175.0	175.3	175.5	175.6	175.6	175.6	175.6	175.6	175.6	176.2	176.9
122.5°	191.2	191.4	191.5	191.6	191.7	192.0	192.2	192.5	192.7	193.1	193.5
125°	207.8	207.9	208.0	208.0	208.1	208.3	208.6	208.8	209.0	209.2	209.5
127.5°	223.0	223.2	223.5	223.6	223.8	224.1	224.4	224.7	225.0	225.3	225.7
130°	239.5	239.8	240.1	240.3	240.4	240.5	240.7	240.8	241.0	241.2	241.3
132.5°	255.0	255.2	255.5	255.6	255.8	256.2	256.6	257.0	257.4	257.3	257.2
135°	271.4	271.6	271.9	272.0	272.0	272.1	272.2	272.2	272.3	272.1	272.0
137.5°	286.1	286.4	286.7	286.9	286.9	287.0	287.1	287.1	287.2	287.0	286.9
140°	301.4	301.7	302.0	302.2	302.2	302.2	302.2	302.2	302.2	301.8	301.4
142.5°	315.2	315.5	315.8	316.0	316.0	315.9	315.8	315.8	315.7	315.5	315.2
145°	329.1	329.4	329.7	329.9	329.9	329.8	329.7	329.7	329.6	329.1	328.6
147.5°	341.6	341.9	342.2	342.4	342.3	342.1	342.0	341.8	341.6	341.3	341.0
150°	353.5	353.7	354.0	354.1	354.0	353.7	353.5	353.2	353.0	352.7	352.4
152.5°	365.0	365.3	365.6	365.8	365.6	365.3	365.0	364.7	364.4	364.0	363.6
155°	374.8	375.0	375.3	375.4	375.2	374.8	374.4	374.0	373.6	373.4	373.2
157.5°	384.0	384.4	384.8	385.0	384.7	384.2	383.6	383.1	382.5	382.3	382.2
160°	392.0	392.3	392.6	392.8	392.6	392.1	391.6	391.2	390.7	390.6	390.5
162.5°	399.3	399.7	400.1	400.3	400.0	399.5	398.9	398.4	397.8	397.7	397.7
165°	405.4	405.7	406.1	406.3	406.0	405.5	405.0	404.4	403.9	403.9	403.9
167.5°	410.7	411.1	411.5	411.7	411.4	410.9	410.3	409.8	409.2	409.2	409.2
170°	414.7	415.2	415.7	415.9	415.6	415.1	414.6	414.0	413.5	413.6	413.6
172.5°	417.9	418.4	418.9	419.1	418.8	418.3	417.8	417.2	416.7	416.8	416.8
175°	420.1	420.6	421.1	421.3	421.0	420.5	419.9	419.4	418.8	419.0	419.1
177.5°	421.1	421.6	422.1	422.3	422.1	421.6	421.1	420.7	420.2	420.4	420.5
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1370.2	1365.0	1361.9	1364.0	1357.8	1342.4	1342.4	1347.6	1341.4	1335.3	1326.0
5°	1408.1	1397.9	1391.7	1390.7	1376.3	1351.7	1346.6	1341.4	1328.1	1313.7	1298.3
7.5°	1445.1	1426.6	1416.3	1409.2	1388.6	1356.8	1343.5	1332.2	1310.6	1289.1	1269.6
10°	1475.9	1449.2	1436.9	1425.6	1398.9	1358.9	1337.3	1316.8	1289.1	1261.4	1236.7
12.5°	1500.5	1469.7	1454.3	1437.9	1405.1	1352.7	1326.0	1293.2	1265.5	1228.5	1203.9
15°	1541.6	1477.9	1463.6	1448.2	1414.3	1342.4	1309.6	1272.7	1234.7	1185.4	1158.7
17.5°	1574.4	1489.2	1488.2	1455.3	1411.2	1338.3	1288.1	1239.8	1198.8	1149.5	1107.4
20°	1593.9	1506.7	1490.2	1456.4	1400.9	1310.6	1258.3	1204.9	1160.8	1101.3	1059.2
22.5°	1610.3	1531.3	1488.2	1447.1	1379.4	1301.4	1224.4	1174.1	1113.6	1048.9	1008.9
25°	1616.5	1536.4	1491.3	1444.1	1364.0	1274.7	1187.5	1133.1	1065.3	1006.8	952.4
27.5°	1617.5	1535.4	1480.0	1430.7	1342.4	1239.8	1150.5	1093.0	1018.1	950.4	896.0
30°	1607.2	1524.1	1473.8	1420.5	1321.9	1208.0	1105.4	1041.7	961.7	893.9	837.5
32.5°	1576.5	1501.5	1460.5	1402.0	1295.2	1163.9	1062.3	991.4	907.3	840.6	786.2
35°	1525.1	1473.8	1428.7	1374.3	1260.3	1122.8	1019.2	936.0	850.8	787.2	735.9
37.5°	1461.5	1433.8	1391.7	1338.3	1220.3	1085.9	970.9	878.5	793.4	731.8	681.5
40°	1375.3	1382.5	1341.4	1293.2	1173.1	1035.6	908.3	820.0	740.0	682.5	633.2
42.5°	1281.9	1311.7	1288.1	1241.9	1120.8	980.2	862.1	764.6	686.6	627.1	586.0
45°	1181.3	1232.6	1218.3	1184.4	1066.4	921.7	796.4	702.0	633.2	575.8	539.9
47.5°	1071.5	1144.4	1144.4	1119.7	1005.8	863.1	740.0	643.5	575.8	534.7	499.8
50°	959.6	1041.7	1055.1	1038.7	938.1	796.4	671.2	584.0	525.5	485.5	459.8
52.5°	842.6	938.1	962.7	954.5	866.2	732.8	614.8	529.6	476.2	441.3	418.7
55°	730.8	841.6	868.3	871.4	789.3	663.0	552.2	477.2	425.9	402.3	382.8
57.5°	625.0	731.8	761.5	766.7	711.3	599.4	493.7	428.0	381.8	362.3	346.9
60°	534.7	624.0	663.0	674.3	626.1	525.5	439.3	375.6	340.7	322.3	307.9
62.5°	460.8	532.7	573.7	576.8	555.2	460.8	382.8	329.5	299.7	283.3	276.1
65°	389.0	453.6	478.3	490.6	473.1	399.2	330.5	286.3	262.7	248.4	241.2
67.5°	331.5	372.6	393.1	409.5	392.1	336.6	281.2	245.3	227.8	213.5	209.4
70°	272.0	305.8	321.2	337.7	322.3	280.2	240.2	207.3	191.9	180.6	175.5
72.5°	217.6	244.3	258.6	268.9	259.7	224.8	191.9	169.3	158.1	149.8	146.8
75°	172.4	190.9	199.1	206.3	202.2	175.5	155.0	136.5	126.2	119.1	117.0
77.5°	131.4	144.7	154.0	156.0	150.9	133.4	116.0	104.7	96.5	92.4	90.3
80°	93.4	101.6	106.7	109.8	104.7	97.5	85.2	77.0	69.8	64.7	63.6
82.5°	62.6	66.7	70.8	69.8	67.7	61.6	54.4	50.3	47.2	43.1	43.1
85°	35.9	36.9	39.0	40.0	39.0	34.9	30.8	28.7	26.7	23.6	23.6
87.5°	15.4	16.4	16.4	17.4	15.4	15.4	13.3	11.3	11.3	10.3	9.2
90°	7.2	5.5	4.6	4.1	3.2	2.3	1.3	0.4	1.3	2.3	3.2
92.5°	10.8	10.7	10.7	10.4	9.7	9.1	8.4	7.8	8.4	9.1	9.7
95°	22.3	22.1	22.0	21.6	20.8	20.1	19.3	18.5	19.3	20.1	20.8
97.5°	34.6	34.3	34.1	33.7	33.0	32.3	31.6	30.9	31.6	32.3	33.0
100°	48.4	48.1	48.0	47.7	47.0	46.4	45.7	45.1	45.7	46.4	47.0
102.5°	62.7	62.4	62.2	62.0	61.5	61.0	60.6	60.1	60.6	61.0	61.5
105°	77.7	77.6	77.5	77.4	77.1	76.9	76.6	76.4	76.6	76.9	77.1
107.5°	94.2	94.2	94.2	94.0	93.7	93.4	93.1	92.8	93.1	93.4	93.7
110°	110.6	110.6	110.6	110.4	109.9	109.4	108.9	108.4	108.9	109.4	109.9

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	127.5	127.6	127.6	127.4	126.9	126.4	126.0	125.5	126.0	126.4	126.9
115°	144.1	144.2	144.3	144.1	143.6	143.1	142.7	142.2	142.7	143.1	143.6
117.5°	161.2	161.6	161.8	161.5	160.8	160.2	159.5	158.9	159.5	160.2	160.8
120°	177.5	178.2	178.5	178.2	177.5	176.9	176.2	175.6	176.2	176.9	177.5
122.5°	193.9	194.3	194.5	194.1	193.3	192.5	191.7	190.9	191.7	192.5	193.3
125°	209.7	210.0	210.1	209.7	209.0	208.3	207.6	206.9	207.6	208.3	209.0
127.5°	226.0	226.3	226.5	226.1	225.2	224.3	223.4	222.5	223.4	224.3	225.2
130°	241.5	241.6	241.7	241.2	240.2	239.1	238.1	237.1	238.1	239.1	240.2
132.5°	257.1	257.0	257.0	256.6	255.8	255.1	254.3	253.5	254.3	255.1	255.8
135°	271.8	271.7	271.6	271.2	270.3	269.4	268.6	267.7	268.6	269.4	270.3
137.5°	286.7	286.6	286.5	286.1	285.4	284.7	284.0	283.3	284.0	284.7	285.4
140°	301.0	300.6	300.4	300.0	299.3	298.6	297.9	297.2	297.9	298.6	299.3
142.5°	315.0	314.7	314.6	314.2	313.5	312.8	312.1	311.4	312.1	312.8	313.5
145°	328.1	327.6	327.4	327.1	326.6	326.0	325.5	324.9	325.5	326.0	326.6
147.5°	340.7	340.4	340.2	339.8	339.1	338.4	337.7	337.0	337.7	338.4	339.1
150°	352.1	351.8	351.6	351.4	350.9	350.4	350.0	349.5	350.0	350.4	350.9
152.5°	363.2	362.8	362.6	362.4	361.9	361.4	361.0	360.5	361.0	361.4	361.9
155°	372.9	372.7	372.6	372.5	372.2	372.0	371.7	371.5	371.7	372.0	372.2
157.5°	382.0	381.9	381.8	381.7	381.6	381.4	381.3	381.1	381.3	381.4	381.6
160°	390.4	390.3	390.3	390.2	390.1	389.9	389.8	389.6	389.8	389.9	390.1
162.5°	397.6	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5
165°	403.9	403.9	403.9	403.9	404.0	404.1	404.1	404.2	404.1	404.1	404.0
167.5°	409.2	409.2	409.2	409.3	409.6	409.8	410.1	410.3	410.1	409.8	409.6
170°	413.7	413.8	413.8	413.9	414.2	414.4	414.7	414.9	414.7	414.4	414.2
172.5°	416.9	417.0	417.0	417.1	417.4	417.6	417.9	418.1	417.9	417.6	417.4
175°	419.3	419.4	419.5	419.6	419.9	420.1	420.4	420.6	420.4	420.1	419.9
177.5°	420.7	420.8	420.9	421.0	421.3	421.5	421.8	422.0	421.8	421.5	421.3
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1320.9	1326.0	1325.0	1314.7	1303.4	1294.2	1276.8	1278.8	1272.7	1273.7	1279.8
5°	1288.1	1288.1	1283.9	1269.6	1251.1	1240.8	1221.3	1216.2	1203.9	1202.9	1201.8
7.5°	1253.2	1248.0	1242.9	1222.4	1199.8	1183.4	1156.7	1150.5	1138.2	1130.0	1125.9
10°	1212.1	1204.9	1194.7	1171.1	1143.3	1122.8	1095.1	1086.9	1063.3	1053.0	1046.9
12.5°	1166.9	1162.8	1146.4	1126.9	1081.8	1059.2	1019.2	1027.4	1003.8	983.2	980.2
15°	1121.8	1106.4	1097.2	1065.3	1010.9	1000.7	968.9	952.4	930.9	914.5	914.5
17.5°	1077.7	1054.0	1033.5	999.7	959.6	930.9	907.3	899.1	872.4	856.0	852.9
20°	1019.2	992.5	987.3	939.1	911.4	879.6	857.0	836.5	817.0	809.8	804.6
22.5°	963.7	932.9	924.7	883.7	856.0	824.1	801.6	787.2	772.8	767.7	758.5
25°	904.2	885.7	873.4	829.3	798.5	768.7	753.3	743.1	729.7	728.7	722.5
27.5°	846.7	829.3	817.0	774.9	752.3	724.6	712.3	701.0	693.8	690.7	687.6
30°	797.5	778.0	763.6	732.8	705.1	682.5	672.3	665.1	661.0	655.8	654.8
32.5°	743.1	731.8	712.3	688.7	667.1	645.6	639.4	634.3	628.1	626.1	625.0
35°	696.9	681.5	669.2	642.5	633.2	614.8	607.6	603.5	595.3	593.2	591.2
37.5°	651.7	637.4	624.0	607.6	590.1	579.9	575.8	569.6	565.5	566.5	564.5
40°	606.6	595.3	585.0	567.6	557.3	552.2	544.0	537.8	535.7	536.8	535.7
42.5°	562.4	552.2	546.0	532.7	522.4	517.3	512.1	506.0	509.1	509.1	512.1
45°	522.4	513.2	509.1	498.8	492.6	484.4	479.3	478.3	482.4	481.4	481.4
47.5°	481.4	478.3	473.1	463.9	455.7	450.6	449.5	449.5	453.6	455.7	454.7
50°	449.5	443.4	437.2	430.0	423.9	421.8	418.7	420.8	424.9	424.9	427.0
52.5°	409.5	405.4	403.4	397.2	393.1	393.1	393.1	394.1	397.2	400.3	399.2
55°	374.6	371.5	369.5	366.4	361.3	362.3	361.3	363.3	366.4	369.5	371.5
57.5°	337.7	336.6	334.6	329.5	329.5	328.4	331.5	332.5	337.7	339.7	342.8
60°	304.8	301.7	301.7	297.6	297.6	297.6	300.7	303.8	307.9	308.9	311.0
62.5°	269.9	269.9	268.9	265.8	265.8	268.9	269.9	274.0	276.1	276.1	279.2
65°	237.1	236.1	235.0	236.1	237.1	237.1	240.2	242.2	244.3	245.3	246.3
67.5°	204.2	203.2	205.3	204.2	206.3	210.4	209.4	212.5	215.5	215.5	216.6
70°	173.5	175.5	174.5	176.5	175.5	177.6	180.6	181.7	181.7	182.7	185.8
72.5°	144.7	144.7	144.7	143.7	144.7	146.8	148.8	149.8	151.9	152.9	156.0
75°	117.0	117.0	114.9	117.0	117.0	119.1	121.1	121.1	121.1	123.2	126.2
77.5°	88.3	89.3	88.3	90.3	90.3	91.3	93.4	92.4	94.4	95.4	96.5
80°	64.7	63.6	63.6	63.6	64.7	64.7	66.7	67.7	67.7	70.8	68.8
82.5°	41.1	42.1	41.1	42.1	42.1	43.1	42.1	43.1	44.1	46.2	45.2
85°	23.6	22.6	22.6	23.6	22.6	22.6	23.6	22.6	23.6	22.6	23.6
87.5°	9.2	8.2	8.2	8.2	8.2	7.2	7.2	6.2	6.2	6.2	5.1
90°	4.1	4.6	5.5	7.2	8.9	10.7	12.4	12.2	12.1	11.9	11.8
92.5°	10.4	10.7	10.7	10.8	10.9	10.9	11.0	11.1	11.2	11.3	11.4
95°	21.6	22.0	22.1	22.3	22.4	22.6	22.8	22.8	22.8	22.8	22.8
97.5°	33.7	34.1	34.3	34.6	34.9	35.3	35.6	35.6	35.6	35.6	35.6
100°	47.7	48.0	48.1	48.4	48.6	48.9	49.1	49.1	49.1	49.1	49.1
102.5°	62.0	62.2	62.4	62.7	63.0	63.3	63.6	63.7	63.8	63.9	64.0
105°	77.4	77.5	77.6	77.7	77.9	78.0	78.2	78.4	78.5	78.7	78.8
107.5°	94.0	94.2	94.2	94.2	94.2	94.2	94.2	94.3	94.4	94.5	94.6
110°	110.4	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	127.4	127.6	127.6	127.5	127.4	127.4	127.3	127.1	126.8	126.6	126.3
115°	144.1	144.3	144.2	144.1	143.9	143.8	143.6	143.5	143.5	143.4	143.3
117.5°	161.5	161.8	161.6	161.2	160.8	160.4	160.0	159.8	159.5	159.3	159.0
120°	178.2	178.5	178.2	177.5	176.9	176.2	175.6	175.6	175.6	175.6	175.6
122.5°	194.1	194.5	194.3	193.9	193.5	193.1	192.7	192.5	192.2	192.0	191.7
125°	209.7	210.1	210.0	209.7	209.5	209.2	209.0	208.8	208.6	208.3	208.1
127.5°	226.1	226.5	226.3	226.0	225.7	225.3	225.0	224.7	224.4	224.1	223.8
130°	241.2	241.7	241.6	241.5	241.3	241.2	241.0	240.8	240.7	240.5	240.4
132.5°	256.6	257.0	257.0	257.1	257.2	257.3	257.4	257.0	256.6	256.2	255.8
135°	271.2	271.6	271.7	271.8	272.0	272.1	272.3	272.2	272.2	272.1	272.0
137.5°	286.1	286.5	286.6	286.7	286.9	287.0	287.2	287.1	287.1	287.0	286.9
140°	300.0	300.4	300.6	301.0	301.4	301.8	302.2	302.2	302.2	302.2	302.2
142.5°	314.2	314.6	314.7	315.0	315.2	315.5	315.7	315.8	315.8	315.9	316.0
145°	327.1	327.4	327.6	328.1	328.6	329.1	329.6	329.7	329.7	329.8	329.9
147.5°	339.8	340.2	340.4	340.7	341.0	341.3	341.6	341.8	342.0	342.1	342.3
150°	351.4	351.6	351.8	352.1	352.4	352.7	353.0	353.2	353.5	353.7	354.0
152.5°	362.4	362.6	362.8	363.2	363.6	364.0	364.4	364.7	365.0	365.3	365.6
155°	372.5	372.6	372.7	372.9	373.2	373.4	373.6	374.0	374.4	374.8	375.2
157.5°	381.7	381.8	381.9	382.0	382.2	382.3	382.5	383.1	383.6	384.2	384.7
160°	390.2	390.3	390.3	390.4	390.5	390.6	390.7	391.2	391.6	392.1	392.6
162.5°	397.5	397.5	397.5	397.6	397.7	397.7	397.8	398.4	398.9	399.5	400.0
165°	403.9	403.9	403.9	403.9	403.9	403.9	403.9	404.4	405.0	405.5	406.0
167.5°	409.3	409.2	409.2	409.2	409.2	409.2	409.2	409.8	410.3	410.9	411.4
170°	413.9	413.8	413.8	413.7	413.6	413.6	413.5	414.0	414.6	415.1	415.6
172.5°	417.1	417.0	417.0	416.9	416.8	416.8	416.7	417.2	417.8	418.3	418.8
175°	419.6	419.5	419.4	419.3	419.1	419.0	418.8	419.4	419.9	420.5	421.0
177.5°	421.0	420.9	420.8	420.7	420.5	420.4	420.2	420.7	421.1	421.6	422.1
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1272.7	1275.7	1268.6	1266.5	1268.6	1261.4	1263.4	1265.5	1265.5	1268.6	1270.6
5°	1198.8	1194.7	1187.5	1185.4	1183.4	1186.4	1184.4	1187.5	1188.5	1195.7	1196.7
7.5°	1125.9	1119.7	1113.6	1107.4	1105.4	1100.2	1105.4	1105.4	1112.5	1110.5	1115.6
10°	1039.7	1038.7	1030.4	1027.4	1023.3	1015.0	1026.3	1023.3	1028.4	1037.6	1039.7
12.5°	976.0	964.8	969.9	955.5	960.7	952.4	953.5	953.5	961.7	962.7	960.7
15°	915.5	906.3	892.9	886.8	883.7	879.6	892.9	893.9	887.8	902.2	897.0
17.5°	853.9	853.9	841.6	838.5	830.3	834.4	832.4	833.4	831.3	841.6	846.7
20°	800.5	795.4	791.3	792.3	782.1	780.0	778.0	780.0	787.2	794.4	796.4
22.5°	757.4	754.4	744.1	746.1	737.9	741.0	739.0	744.1	745.1	745.1	752.3
25°	716.4	712.3	713.3	709.2	706.1	706.1	703.0	706.1	710.2	712.3	713.3
27.5°	685.6	682.5	677.4	674.3	676.4	671.2	675.3	678.4	678.4	676.4	678.4
30°	648.6	650.7	650.7	640.4	644.5	642.5	645.6	647.6	647.6	648.6	646.6
32.5°	624.0	617.9	616.8	615.8	615.8	611.7	611.7	614.8	615.8	616.8	619.9
35°	591.2	591.2	586.0	589.1	585.0	586.0	585.0	586.0	588.1	585.0	588.1
37.5°	561.4	562.4	560.4	562.4	563.5	561.4	559.4	563.5	561.4	561.4	559.4
40°	535.7	534.7	535.7	535.7	535.7	536.8	534.7	534.7	534.7	532.7	530.6
42.5°	514.2	508.0	510.1	511.1	508.0	508.0	509.1	508.0	511.1	505.0	505.0
45°	483.4	481.4	482.4	482.4	484.4	481.4	483.4	484.4	481.4	480.3	478.3
47.5°	455.7	457.7	455.7	457.7	457.7	459.8	455.7	456.7	457.7	453.6	450.6
50°	428.0	428.0	431.1	430.0	431.1	429.0	429.0	428.0	429.0	427.0	423.9
52.5°	402.3	399.2	404.4	403.4	402.3	401.3	400.3	401.3	399.2	397.2	397.2
55°	370.5	370.5	373.6	374.6	374.6	372.6	370.5	371.5	370.5	369.5	368.5
57.5°	344.8	340.7	342.8	343.8	343.8	340.7	342.8	340.7	340.7	341.8	338.7
60°	312.0	312.0	310.0	313.0	313.0	311.0	311.0	312.0	310.0	308.9	307.9
62.5°	277.1	278.1	281.2	282.2	283.3	281.2	279.2	280.2	280.2	277.1	278.1
65°	247.3	249.4	253.5	252.5	250.4	251.5	249.4	250.4	247.3	248.4	245.3
67.5°	218.6	217.6	218.6	218.6	220.7	219.6	217.6	217.6	216.6	219.6	216.6
70°	187.8	187.8	187.8	187.8	188.8	189.9	187.8	185.8	186.8	184.7	183.7
72.5°	156.0	157.0	156.0	158.1	155.0	157.0	157.0	156.0	155.0	155.0	155.0
75°	126.2	128.3	125.2	126.2	125.2	127.3	126.2	126.2	124.2	123.2	124.2
77.5°	96.5	97.5	95.4	96.5	95.4	96.5	96.5	95.4	95.4	95.4	95.4
80°	68.8	69.8	68.8	67.7	66.7	68.8	66.7	67.7	68.8	67.7	69.8
82.5°	44.1	44.1	43.1	44.1	42.1	42.1	43.1	43.1	42.1	44.1	42.1
85°	21.6	21.6	23.6	21.6	20.5	20.5	20.5	21.6	20.5	22.6	21.6
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.2	4.1
90°	11.7	11.7	11.8	11.9	12.0	12.1	12.0	11.9	11.8	11.7	11.7
92.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.8	22.7	22.5	22.4	22.2	22.0	22.2	22.4	22.5	22.7	22.8
97.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6
100°	49.1	49.1	49.0	48.9	48.8	48.7	48.8	48.9	49.0	49.1	49.1
102.5°	64.0	64.0	63.9	63.8	63.7	63.6	63.7	63.8	63.9	64.0	64.0
105°	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9
107.5°	94.6	94.4	94.0	93.6	93.2	92.8	93.2	93.6	94.0	94.4	94.6
110°	110.6	110.5	110.2	110.0	109.7	109.5	109.7	110.0	110.2	110.5	110.6

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	126.2	126.1	126.0	125.8	125.7	125.5	125.7	125.8	126.0	126.1	126.2
115°	143.3	143.2	142.9	142.7	142.4	142.2	142.4	142.7	142.9	143.2	143.3
117.5°	158.9	158.8	158.5	158.3	158.0	157.8	158.0	158.3	158.5	158.8	158.9
120°	175.6	175.5	175.3	175.0	174.8	174.6	174.8	175.0	175.3	175.5	175.6
122.5°	191.6	191.5	191.4	191.2	191.1	190.9	191.1	191.2	191.4	191.5	191.6
125°	208.0	208.0	207.9	207.8	207.7	207.6	207.7	207.8	207.9	208.0	208.0
127.5°	223.6	223.5	223.2	223.0	222.7	222.5	222.7	223.0	223.2	223.5	223.6
130°	240.3	240.1	239.8	239.5	239.2	238.9	239.2	239.5	239.8	240.1	240.3
132.5°	255.6	255.5	255.2	255.0	254.7	254.5	254.7	255.0	255.2	255.5	255.6
135°	272.0	271.9	271.6	271.4	271.1	270.9	271.1	271.4	271.6	271.9	272.0
137.5°	286.9	286.7	286.4	286.1	285.8	285.5	285.8	286.1	286.4	286.7	286.9
140°	302.2	302.0	301.7	301.4	301.1	300.8	301.1	301.4	301.7	302.0	302.2
142.5°	316.0	315.8	315.5	315.2	314.9	314.6	314.9	315.2	315.5	315.8	316.0
145°	329.9	329.7	329.4	329.1	328.8	328.5	328.8	329.1	329.4	329.7	329.9
147.5°	342.4	342.2	341.9	341.6	341.2	340.9	341.2	341.6	341.9	342.2	342.4
150°	354.1	354.0	353.7	353.5	353.2	353.0	353.2	353.5	353.7	354.0	354.1
152.5°	365.8	365.6	365.3	365.0	364.7	364.4	364.7	365.0	365.3	365.6	365.8
155°	375.4	375.3	375.0	374.8	374.5	374.3	374.5	374.8	375.0	375.3	375.4
157.5°	385.0	384.8	384.4	384.0	383.6	383.2	383.6	384.0	384.4	384.8	385.0
160°	392.8	392.6	392.3	392.0	391.7	391.4	391.7	392.0	392.3	392.6	392.8
162.5°	400.3	400.1	399.7	399.3	398.9	398.5	398.9	399.3	399.7	400.1	400.3
165°	406.3	406.1	405.7	405.4	405.0	404.6	405.0	405.4	405.7	406.1	406.3
167.5°	411.7	411.5	411.1	410.7	410.3	409.9	410.3	410.7	411.1	411.5	411.7
170°	415.9	415.7	415.2	414.7	414.3	413.8	414.3	414.7	415.2	415.7	415.9
172.5°	419.1	418.9	418.4	417.9	417.5	417.0	417.5	417.9	418.4	418.9	419.1
175°	421.3	421.1	420.6	420.1	419.6	419.1	419.6	420.1	420.6	421.1	421.3
177.5°	422.3	422.1	421.6	421.1	420.7	420.2	420.7	421.1	421.6	422.1	422.3
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1267.5	1275.7	1272.7	1261.4	1274.7	1274.7	1283.9	1283.9	1295.2	1299.3	1305.5
5°	1195.7	1201.8	1207.0	1201.8	1211.1	1225.4	1233.7	1240.8	1256.2	1262.4	1271.6
7.5°	1118.7	1130.0	1135.1	1135.1	1150.5	1166.9	1183.4	1193.6	1215.2	1223.4	1232.6
10°	1043.8	1057.1	1067.4	1066.4	1092.0	1102.3	1122.8	1146.4	1168.0	1180.3	1193.6
12.5°	964.8	971.9	986.3	1006.8	1013.0	1031.5	1055.1	1084.8	1123.8	1135.1	1154.6
15°	899.1	918.6	929.9	939.1	953.5	970.9	996.6	1025.3	1064.3	1088.9	1109.5
17.5°	843.6	869.3	876.5	874.4	892.9	919.6	949.4	970.9	1005.8	1035.6	1055.1
20°	798.5	808.8	821.1	826.2	840.6	869.3	898.0	922.7	951.4	975.0	997.6
22.5°	753.3	761.5	771.8	781.0	792.3	808.8	836.5	867.3	895.0	917.5	943.2
25°	716.4	721.5	730.8	737.9	750.3	761.5	781.0	814.9	847.8	861.1	883.7
27.5°	680.5	684.6	690.7	698.9	705.1	716.4	733.8	761.5	795.4	808.8	839.5
30°	648.6	651.7	657.9	662.0	665.1	678.4	691.8	713.3	739.0	757.4	780.0
32.5°	618.9	622.0	628.1	629.1	633.2	640.4	652.8	672.3	694.8	710.2	729.7
35°	586.0	588.1	594.2	596.3	599.4	605.5	614.8	629.1	649.7	661.0	678.4
37.5°	560.4	559.4	563.5	566.5	570.6	573.7	576.8	591.2	606.6	616.8	630.2
40°	532.7	530.6	531.6	535.7	537.8	541.9	541.9	556.3	566.5	574.7	585.0
42.5°	505.0	503.9	501.9	503.9	506.0	507.0	508.0	518.3	528.6	535.7	547.0
45°	477.2	476.2	474.2	475.2	475.2	477.2	480.3	484.4	491.6	497.8	503.9
47.5°	451.6	449.5	446.5	445.4	447.5	447.5	447.5	451.6	458.8	460.8	467.0
50°	424.9	421.8	417.7	415.7	415.7	414.6	416.7	417.7	423.9	425.9	431.1
52.5°	396.2	394.1	390.0	385.9	386.9	384.9	385.9	386.9	389.0	392.1	395.1
55°	367.4	363.3	360.2	359.2	356.1	356.1	353.1	357.2	356.1	357.2	361.3
57.5°	339.7	335.6	330.5	328.4	325.3	324.3	322.3	321.2	322.3	325.3	328.4
60°	306.9	304.8	301.7	298.7	296.6	293.5	291.5	291.5	290.5	290.5	291.5
62.5°	275.1	274.0	269.9	268.9	266.8	264.8	261.7	259.7	259.7	261.7	262.7
65°	244.3	243.2	240.2	239.1	234.0	232.0	230.9	229.9	227.8	227.8	227.8
67.5°	215.5	212.5	212.5	207.3	203.2	201.2	199.1	198.1	198.1	198.1	199.1
70°	183.7	183.7	180.6	177.6	173.5	174.5	171.4	168.3	168.3	166.3	167.3
72.5°	152.9	151.9	148.8	147.8	144.7	141.6	139.6	141.6	138.6	137.5	138.6
75°	123.2	122.1	120.1	118.0	119.1	116.0	112.9	111.9	111.9	109.8	109.8
77.5°	94.4	96.5	92.4	91.3	89.3	87.2	86.2	85.2	85.2	85.2	87.2
80°	65.7	66.7	66.7	64.7	65.7	62.6	62.6	62.6	59.5	60.6	61.6
82.5°	42.1	42.1	41.1	42.1	41.1	41.1	40.0	40.0	39.0	39.0	40.0
85°	23.6	22.6	21.6	23.6	22.6	22.6	21.6	21.6	21.6	21.6	21.6
87.5°	5.1	6.2	6.2	6.2	6.2	7.2	7.2	7.2	8.2	8.2	8.2
90°	11.8	11.9	12.1	12.2	12.4	10.7	8.9	7.2	5.5	4.6	4.1
92.5°	11.4	11.3	11.2	11.1	11.0	10.9	10.9	10.8	10.7	10.7	10.4
95°	22.8	22.8	22.8	22.8	22.8	22.6	22.4	22.3	22.1	22.0	21.6
97.5°	35.6	35.6	35.6	35.6	35.6	35.3	34.9	34.6	34.3	34.1	33.7
100°	49.1	49.1	49.1	49.1	49.1	48.9	48.6	48.4	48.1	48.0	47.7
102.5°	64.0	63.9	63.8	63.7	63.6	63.3	63.0	62.7	62.4	62.2	62.0
105°	78.8	78.7	78.5	78.4	78.2	78.0	77.9	77.7	77.6	77.5	77.4
107.5°	94.6	94.5	94.4	94.3	94.2	94.2	94.2	94.2	94.2	94.2	94.0
110°	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.4

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	126.3	126.6	126.8	127.1	127.3	127.4	127.4	127.5	127.6	127.6	127.4
115°	143.3	143.4	143.5	143.5	143.6	143.8	143.9	144.1	144.2	144.3	144.1
117.5°	159.0	159.3	159.5	159.8	160.0	160.4	160.8	161.2	161.6	161.8	161.5
120°	175.6	175.6	175.6	175.6	175.6	176.2	176.9	177.5	178.2	178.5	178.2
122.5°	191.7	192.0	192.2	192.5	192.7	193.1	193.5	193.9	194.3	194.5	194.1
125°	208.1	208.3	208.6	208.8	209.0	209.2	209.5	209.7	210.0	210.1	209.7
127.5°	223.8	224.1	224.4	224.7	225.0	225.3	225.7	226.0	226.3	226.5	226.1
130°	240.4	240.5	240.7	240.8	241.0	241.2	241.3	241.5	241.6	241.7	241.2
132.5°	255.8	256.2	256.6	257.0	257.4	257.3	257.2	257.1	257.0	257.0	256.6
135°	272.0	272.1	272.2	272.2	272.3	272.1	272.0	271.8	271.7	271.6	271.2
137.5°	286.9	287.0	287.1	287.1	287.2	287.0	286.9	286.7	286.6	286.5	286.1
140°	302.2	302.2	302.2	302.2	302.2	301.8	301.4	301.0	300.6	300.4	300.0
142.5°	316.0	315.9	315.8	315.8	315.7	315.5	315.2	315.0	314.7	314.6	314.2
145°	329.9	329.8	329.7	329.7	329.6	329.1	328.6	328.1	327.6	327.4	327.1
147.5°	342.3	342.1	342.0	341.8	341.6	341.3	341.0	340.7	340.4	340.2	339.8
150°	354.0	353.7	353.5	353.2	353.0	352.7	352.4	352.1	351.8	351.6	351.4
152.5°	365.6	365.3	365.0	364.7	364.4	364.0	363.6	363.2	362.8	362.6	362.4
155°	375.2	374.8	374.4	374.0	373.6	373.4	373.2	372.9	372.7	372.6	372.5
157.5°	384.7	384.2	383.6	383.1	382.5	382.3	382.2	382.0	381.9	381.8	381.7
160°	392.6	392.1	391.6	391.2	390.7	390.6	390.5	390.4	390.3	390.3	390.2
162.5°	400.0	399.5	398.9	398.4	397.8	397.7	397.7	397.6	397.5	397.5	397.5
165°	406.0	405.5	405.0	404.4	403.9	403.9	403.9	403.9	403.9	403.9	403.9
167.5°	411.4	410.9	410.3	409.8	409.2	409.2	409.2	409.2	409.2	409.2	409.3
170°	415.6	415.1	414.6	414.0	413.5	413.6	413.6	413.7	413.8	413.8	413.9
172.5°	418.8	418.3	417.8	417.2	416.7	416.8	416.8	416.9	417.0	417.0	417.1
175°	421.0	420.5	419.9	419.4	418.8	419.0	419.1	419.3	419.4	419.5	419.6
177.5°	422.1	421.6	421.1	420.7	420.2	420.4	420.5	420.7	420.8	420.9	421.0
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1335.3	1335.3	1335.3	1335.3
2.5°	1310.6	1310.6	1326.0	1342.4
5°	1281.9	1289.1	1313.7	1336.3
7.5°	1254.2	1266.5	1297.3	1326.0
10°	1220.3	1236.7	1274.7	1308.6
12.5°	1187.5	1202.9	1247.0	1285.0
15°	1141.3	1160.8	1208.0	1255.2
17.5°	1095.1	1114.6	1172.1	1227.5
20°	1040.7	1066.4	1131.0	1204.9
22.5°	990.4	1022.2	1094.1	1153.6
25°	935.0	984.3	1051.0	1127.9
27.5°	885.7	935.0	1002.7	1080.7
30°	830.3	880.6	950.4	1022.2
32.5°	776.9	823.1	890.9	979.1
35°	721.5	765.6	831.3	920.6
37.5°	671.2	714.3	786.2	868.3
40°	622.0	667.1	728.7	810.8
42.5°	575.8	615.8	671.2	753.3
45°	533.7	562.4	613.7	690.7
47.5°	489.6	515.2	562.4	639.4
50°	448.5	470.1	511.1	583.0
52.5°	408.5	427.0	464.9	522.4
55°	372.6	390.0	417.7	474.2
57.5°	335.6	349.0	375.6	420.8
60°	299.7	312.0	333.6	370.5
62.5°	263.8	274.0	294.6	324.3
65°	232.0	240.2	255.6	281.2
67.5°	201.2	206.3	218.6	239.1
70°	171.4	175.5	185.8	202.2
72.5°	139.6	143.7	155.0	166.3
75°	112.9	113.9	122.1	131.4
77.5°	88.3	87.2	93.4	100.6
80°	60.6	63.6	68.8	71.8
82.5°	41.1	42.1	44.1	46.2
85°	22.6	23.6	23.6	26.7
87.5°	9.2	10.3	10.3	11.3
90°	3.2	2.3	1.3	0.4
92.5°	9.7	9.1	8.4	7.8
95°	20.8	20.1	19.3	18.5
97.5°	33.0	32.3	31.6	30.9
100°	47.0	46.4	45.7	45.1
102.5°	61.5	61.0	60.6	60.1
105°	77.1	76.9	76.6	76.4
107.5°	93.7	93.4	93.1	92.8
110°	109.9	109.4	108.9	108.4



TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	126.9	126.4	126.0	125.5
115°	143.6	143.1	142.7	142.2
117.5°	160.8	160.2	159.5	158.9
120°	177.5	176.9	176.2	175.6
122.5°	193.3	192.5	191.7	190.9
125°	209.0	208.3	207.6	206.9
127.5°	225.2	224.3	223.4	222.5
130°	240.2	239.1	238.1	237.1
132.5°	255.8	255.1	254.3	253.5
135°	270.3	269.4	268.6	267.7
137.5°	285.4	284.7	284.0	283.3
140°	299.3	298.6	297.9	297.2
142.5°	313.5	312.8	312.1	311.4
145°	326.6	326.0	325.5	324.9
147.5°	339.1	338.4	337.7	337.0
150°	350.9	350.4	350.0	349.5
152.5°	361.9	361.4	361.0	360.5
155°	372.2	372.0	371.7	371.5
157.5°	381.6	381.4	381.3	381.1
160°	390.1	389.9	389.8	389.6
162.5°	397.5	397.5	397.5	397.5
165°	404.0	404.1	404.1	404.2
167.5°	409.6	409.8	410.1	410.3
170°	414.2	414.4	414.7	414.9
172.5°	417.4	417.6	417.9	418.1
175°	419.9	420.1	420.4	420.6
177.5°	421.3	421.5	421.8	422.0
180°	421.3	421.3	421.3	421.3

TEST NUMBER: P998757

CATALOG NUMBER: SA2XXDIP-B675D330UB30-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.25	19.29	19.01	20.06	20.99	15.74	16.78	16.50	17.55	18.49
	3H	19.07	20.01	19.84	20.79	21.75	17.10	18.03	17.87	18.81	19.78
	4H	19.25	20.13	20.04	20.92	21.89	17.57	18.45	18.36	19.24	20.21
	6H	19.31	20.11	20.11	20.91	21.90	17.89	18.70	18.69	19.49	20.48
	8H	19.29	20.06	20.10	20.88	21.86	17.98	18.74	18.79	19.56	20.55
	12H	19.26	19.99	20.07	20.80	21.82	18.02	18.76	18.84	19.57	20.58
4H	2H	18.31	19.19	19.10	19.98	20.95	16.21	17.09	17.00	17.88	18.85
	3H	19.31	20.04	20.11	20.86	21.85	17.69	18.41	18.49	19.24	20.23
	4H	19.59	20.25	20.41	21.08	22.10	18.23	18.89	19.05	19.71	20.73
	6H	19.73	20.30	20.57	21.15	22.18	18.62	19.19	19.45	20.04	21.06
	8H	19.73	20.27	20.57	21.11	22.15	18.73	19.26	19.57	20.11	21.14
	12H	19.71	20.18	20.56	21.05	22.09	18.80	19.27	19.65	20.14	21.18
8H	4H	19.61	20.15	20.45	20.99	22.03	18.38	18.92	19.22	19.76	20.80
	6H	19.80	20.24	20.67	21.13	22.16	18.82	19.26	19.69	20.15	21.19
	8H	19.83	20.22	20.71	21.10	22.16	18.98	19.37	19.85	20.25	21.30
	12H	19.82	20.17	20.70	21.04	22.15	19.08	19.42	19.95	20.29	21.40
12H	4H	19.58	20.06	20.44	20.92	21.96	18.37	18.84	19.22	19.71	20.75
	6H	19.78	20.17	20.66	21.05	22.11	18.83	19.22	19.70	20.10	21.15
	8H	19.82	20.16	20.70	21.04	22.14	18.99	19.33	19.87	20.21	21.32