

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999784

Luminaire Tested: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999784
REPORT IS A COMBINATION OF REPORTS P988339 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4344.0 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	49	49	42
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	43	43	43	43	37
2	89	82	76	71	81	75	70	66	62	59	56	51	48	46	40	38	37	37	37	32
3	81	72	66	60	74	67	61	56	56	51	48	45	42	40	36	34	32	32	32	28
4	75	65	57	52	68	59	53	48	50	45	41	41	38	35	33	30	28	28	28	25
5	69	58	50	45	63	53	47	42	45	40	36	37	34	31	30	27	25	25	25	22
6	64	52	45	39	58	48	42	37	41	36	32	34	30	27	27	25	23	23	23	20
7	59	47	40	35	54	44	37	33	37	32	28	31	27	24	25	23	21	21	21	18
8	55	43	36	31	50	40	34	29	34	29	26	29	25	22	23	21	19	19	19	16
9	51	40	32	28	47	37	30	26	31	27	23	26	23	20	22	19	17	17	17	15
10	48	36	30	25	44	34	28	24	29	24	21	25	21	18	20	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16800	16800	16800	16800
5°	16838	17843	16897	14255
10°	16653	18861	16771	11771
15°	16292	18866	16568	8843
20°	15857	15595	16202	7295
25°	15331	9745	15661	6206
30°	14658	6240	15056	5343
35°	13839	4794	14287	4573
40°	12927	4030	13479	4000
45°	11951	3431	12451	3357
50°	10952	2914	11464	2904
55°	9846	2533	10376	2500
60°	8864	1932	9331	1908
65°	7945	1454	8415	1650
70°	6929	1161	7475	1344
75°	5857	890	6394	1016
80°	4655	605	5006	666
85°	3235	313	3546	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15368 cd/sqm

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.7	2.3
10°-20°	281.0	6.5
20°-30°	361.6	8.3
30°-40°	343.1	7.9
40°-50°	294.0	6.8
50°-60°	223.9	5.2
60°-70°	141.2	3.3
70°-80°	70.5	1.6
80°-90°	20.7	0.5
90°-100°	55.5	1.3
100°-110°	176.4	4.1
110°-120°	301.8	6.9
120°-130°	396.9	9.1
130°-140°	445.5	10.3
140°-150°	436.9	10.1
150°-160°	366.5	8.4
160°-170°	243.1	5.6
170°-180°	84.9	2.0
0°-30°	743.3	17.1
0°-40°	1086.3	25.0
0°-60°	1604.3	36.9
0°-90°	1836.6	42.3
90°-120°	533.6	12.3
90°-150°	1812.9	41.7
90°-180°	2507.0	57.7
0°-180°	4344.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1061	1061	1061	1061	1061	
5°	1062	1181	1066	943	1062	101
15°	1001	1333	1018	625	1001	282
25°	888	711	907	453	888	408
35°	729	350	752	334	729	456
45°	547	243	570	238	547	422
55°	370	169	389	167	370	333
65°	224	88	237	100	224	222
75°	105	46	114	53	105	113
85°	23	13	25	14	23	26
90°	1	26	1	26	1	4
95°	39	47	39	47	39	44
105°	163	168	163	168	163	172
115°	303	303	303	303	303	300
125°	440	442	440	442	440	394
135°	570	577	570	577	570	440
145°	692	699	692	699	692	432
155°	791	797	791	797	791	364
165°	860	861	860	861	860	243
175°	895	892	895	892	895	85
180°	897	897	897	897	897	

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.9	1072.3	1074.5	1077.5	1084.1	1088.6	1095.2	1096.7	1095.9	1098.9	1090.8
5°	1062.0	1071.6	1080.4	1087.8	1099.6	1107.0	1115.1	1124.7	1126.9	1138.0	1131.3
7.5°	1053.9	1067.9	1080.4	1095.2	1112.9	1122.5	1135.0	1149.8	1156.4	1169.7	1173.4
10°	1040.6	1060.5	1081.9	1097.4	1121.7	1138.7	1150.5	1174.1	1189.6	1209.5	1206.6
12.5°	1019.2	1045.0	1073.8	1099.6	1131.3	1142.4	1164.5	1188.9	1208.8	1227.2	1243.4
15°	1000.8	1030.3	1062.0	1093.7	1129.9	1150.5	1172.6	1204.3	1225.7	1258.2	1272.2
17.5°	975.7	1013.3	1050.9	1086.3	1129.1	1152.7	1180.0	1211.0	1242.7	1273.7	1284.7
20°	949.9	990.5	1031.0	1079.0	1127.6	1150.5	1178.5	1216.9	1247.9	1272.2	1272.2
22.5°	918.9	968.3	1014.8	1060.5	1113.6	1146.8	1175.6	1220.6	1242.7	1247.9	1227.9
25°	888.0	937.4	988.3	1045.0	1105.5	1135.0	1167.5	1209.5	1216.9	1196.2	1144.6
27.5°	851.1	906.4	963.9	1025.1	1088.6	1125.4	1154.9	1183.0	1168.9	1113.6	1033.2
30°	813.5	873.2	938.1	996.4	1073.1	1107.0	1132.1	1140.2	1095.9	1006.0	902.0
32.5°	774.4	832.6	901.2	971.3	1048.7	1081.2	1097.4	1076.0	994.9	881.3	754.5
35°	728.7	794.3	865.8	938.8	1015.5	1039.9	1049.5	997.1	893.1	746.4	620.2
37.5°	687.4	753.0	829.7	904.2	978.7	991.9	982.4	900.5	768.5	623.2	500.0
40°	638.7	708.7	784.0	867.3	928.5	932.2	908.6	802.4	638.7	502.2	426.3
42.5°	593.7	664.5	739.7	824.5	871.0	858.5	826.7	687.4	533.2	432.9	371.7
45°	547.2	614.3	695.5	770.7	803.9	774.4	726.4	578.2	447.7	372.4	325.2
47.5°	502.2	564.9	645.3	717.6	723.5	690.3	633.5	484.5	387.9	327.5	289.1
50°	458.0	520.7	595.9	655.6	649.7	604.0	539.9	421.1	337.0	289.1	257.4
52.5°	413.7	470.5	543.5	590.7	565.7	521.4	458.0	357.0	294.3	252.2	227.9
55°	369.5	422.6	485.3	524.4	484.5	433.7	388.7	306.1	255.2	221.3	202.8
57.5°	332.6	374.7	432.2	455.8	407.8	368.0	328.9	263.3	221.3	196.9	175.5
60°	292.1	330.4	377.6	391.6	342.2	309.8	276.6	222.7	189.5	168.2	154.1
62.5°	257.4	289.1	325.2	325.2	281.7	257.4	232.3	186.6	159.3	142.3	135.7
65°	223.5	246.3	272.1	269.2	232.3	210.9	191.0	154.1	133.5	121.7	115.1
67.5°	190.3	208.0	224.9	214.6	188.1	169.6	151.2	124.6	110.6	102.5	93.7
70°	160.0	174.1	182.9	173.3	146.8	131.3	118.0	100.3	89.2	78.9	73.8
72.5°	134.2	140.1	143.1	131.3	109.2	100.3	90.7	78.2	68.6	63.4	62.0
75°	104.7	109.9	107.7	98.8	80.4	73.8	66.4	57.5	55.3	52.4	50.9
77.5°	81.9	81.9	78.2	70.1	57.5	52.4	49.4	45.0	42.8	42.0	40.6
80°	58.3	57.5	55.3	46.5	39.1	36.1	36.1	33.2	32.5	31.0	31.0
82.5°	38.4	38.4	35.4	28.0	25.8	25.1	24.3	22.9	22.9	22.1	22.1
85°	22.9	21.4	17.7	15.5	14.8	14.8	14.0	13.3	14.0	13.3	13.3
87.5°	10.3	8.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.8	2.8	4.8	6.8	8.8	9.8	11.7	15.4	19.1	22.8	26.5
92.5°	16.7	18.0	19.4	20.7	22.0	22.7	22.8	23.0	23.1	23.3	23.5
95°	39.4	41.1	42.7	44.4	46.1	46.9	47.1	47.4	47.7	48.1	48.4
97.5°	65.8	67.3	68.9	70.4	71.9	72.7	73.0	73.7	74.4	75.0	75.7
100°	96.1	97.5	98.8	100.2	101.5	102.2	102.4	102.9	103.4	103.9	104.4
102.5°	127.9	128.9	129.9	130.9	131.9	132.4	132.7	133.4	134.1	134.8	135.5
105°	162.7	163.2	163.7	164.2	164.7	165.0	165.2	165.5	165.8	166.2	166.5
107.5°	197.5	198.2	198.9	199.6	200.3	200.6	200.6	200.6	200.6	200.6	200.6
110°	230.8	231.8	232.8	233.9	234.9	235.4	235.4	235.4	235.4	235.4	235.4

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	267.2	268.2	269.2	270.2	271.2	271.7	271.6	271.4	271.3	271.1	270.9
115°	302.7	303.7	304.7	305.8	306.8	307.3	307.1	306.8	306.5	306.1	305.8
117.5°	338.3	339.7	341.0	342.4	343.7	344.4	344.0	343.1	342.3	341.4	340.6
120°	373.9	375.2	376.6	377.9	379.2	379.9	379.2	377.9	376.6	375.2	373.9
122.5°	406.4	408.1	409.8	411.5	413.2	414.0	413.6	412.7	411.9	411.0	410.2
125°	440.5	442.0	443.5	445.0	446.5	447.3	447.0	446.5	446.0	445.5	445.0
127.5°	473.8	475.6	477.5	479.3	481.2	482.1	481.8	481.1	480.4	479.8	479.1
130°	504.8	507.0	509.2	511.4	513.6	514.7	514.5	514.2	513.8	513.5	513.1
132.5°	539.6	541.3	543.0	544.7	546.4	547.2	547.3	547.5	547.6	547.8	548.0
135°	569.9	571.7	573.6	575.4	577.3	578.2	578.4	578.7	579.0	579.4	579.7
137.5°	603.2	604.7	606.2	607.7	609.2	610.0	610.2	610.5	610.8	611.2	611.5
140°	632.7	634.2	635.7	637.2	638.7	639.5	639.9	640.8	641.6	642.5	643.3
142.5°	663.0	664.5	666.0	667.5	669.0	669.8	670.1	670.6	671.1	671.6	672.1
145°	691.8	693.0	694.2	695.3	696.5	697.1	697.6	698.6	699.6	700.6	701.6
147.5°	717.5	719.0	720.5	722.0	723.5	724.3	724.6	725.3	726.0	726.6	727.3
150°	744.0	745.0	746.0	747.0	748.0	748.5	748.8	749.5	750.2	750.8	751.5
152.5°	767.4	768.4	769.4	770.5	771.5	772.0	772.4	773.3	774.1	775.0	775.8
155°	790.9	791.4	791.9	792.4	792.9	793.2	793.4	793.9	794.4	794.9	795.4
157.5°	811.3	811.6	812.0	812.3	812.6	812.8	813.0	813.3	813.7	814.0	814.4
160°	829.5	829.8	830.2	830.5	830.8	831.0	831.1	831.3	831.4	831.6	831.8
162.5°	846.2	846.2	846.2	846.2	846.2	846.2	846.3	846.4	846.6	846.7	846.9
165°	860.5	860.3	860.2	860.0	859.9	859.8	859.8	859.8	859.8	859.8	859.8
167.5°	873.4	872.9	872.4	871.9	871.4	871.1	871.1	871.1	871.1	871.1	871.1
170°	883.2	882.7	882.2	881.7	881.2	881.0	880.9	880.7	880.6	880.4	880.2
172.5°	890.0	889.5	889.0	888.5	888.0	887.8	887.7	887.5	887.4	887.2	887.0
175°	895.3	894.8	894.3	893.8	893.3	893.1	892.9	892.6	892.3	891.9	891.6
177.5°	898.4	897.9	897.4	896.9	896.4	896.1	895.9	895.6	895.3	894.9	894.6
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1098.9	1100.4	1102.6	1112.9	1114.4	1117.3	1115.8	1115.8	1116.6	1115.1	1115.8
5°	1146.1	1148.3	1159.4	1171.9	1174.8	1171.9	1175.6	1180.7	1180.7	1180.7	1179.3
7.5°	1190.3	1198.4	1211.0	1229.4	1233.1	1236.8	1243.4	1239.0	1240.5	1247.1	1244.9
10°	1233.1	1244.9	1258.9	1274.4	1282.5	1287.7	1290.6	1297.3	1312.8	1295.1	1301.7
12.5°	1273.7	1290.6	1305.4	1322.3	1328.2	1334.9	1337.1	1343.0	1343.0	1342.3	1347.4
15°	1300.2	1315.7	1329.0	1340.0	1341.5	1340.0	1338.6	1339.3	1341.5	1332.7	1337.8
17.5°	1306.1	1307.6	1312.0	1307.6	1308.3	1292.8	1284.0	1281.8	1261.1	1261.9	1278.8
20°	1277.4	1252.3	1245.6	1221.3	1206.6	1166.7	1165.3	1154.2	1110.7	1124.0	1121.0
22.5°	1198.4	1155.7	1098.9	1070.9	1056.8	1014.8	982.4	959.5	944.0	928.5	921.9
25°	1094.5	1025.1	944.7	889.4	881.3	842.2	782.5	754.5	721.3	711.0	728.7
27.5°	960.2	870.3	779.5	694.7	679.2	643.8	613.6	593.7	555.3	553.1	554.6
30°	778.1	687.4	611.4	556.1	517.7	501.5	481.6	466.8	451.4	457.3	458.7
32.5°	639.4	553.1	482.3	452.8	435.1	424.8	407.8	398.3	391.6	389.4	388.7
35°	508.1	450.6	418.9	390.1	379.8	372.4	359.9	355.5	349.6	350.3	350.3
37.5°	435.1	387.2	363.6	348.8	339.3	335.6	327.5	323.0	319.3	317.9	320.1
40°	375.4	342.2	327.5	314.2	306.1	304.6	300.2	295.0	290.6	291.3	293.5
42.5°	331.9	312.7	295.0	284.7	278.8	276.6	272.9	269.2	269.2	267.0	266.2
45°	297.2	281.7	267.0	257.4	253.7	250.8	246.3	245.6	242.6	243.4	244.1
47.5°	266.2	253.7	242.6	233.1	229.4	228.6	224.2	221.3	221.3	220.5	219.8
50°	238.2	225.7	216.1	210.9	205.8	204.3	203.6	202.8	201.3	201.3	202.1
52.5°	215.4	202.8	195.4	191.0	188.1	186.6	186.6	185.9	185.9	185.9	185.1
55°	190.3	180.0	174.1	172.6	171.1	170.4	169.6	168.2	167.4	168.9	167.4
57.5°	166.7	163.0	157.8	156.4	152.7	152.7	150.5	149.0	147.5	149.0	149.0
60°	148.2	143.1	140.1	135.7	132.8	129.8	126.1	125.4	123.9	123.2	122.4
62.5°	129.1	124.6	117.3	110.6	106.2	103.3	101.8	101.0	101.0	100.3	100.3
65°	107.7	97.4	93.7	91.5	90.7	90.0	88.5	87.8	88.5	87.8	88.5
67.5°	84.1	82.6	80.4	78.9	78.2	77.4	77.4	76.7	76.7	76.7	76.7
70°	73.0	69.3	68.6	67.1	67.1	66.4	66.4	66.4	66.4	65.6	67.1
72.5°	60.5	58.3	57.5	56.8	56.8	56.8	56.1	56.1	56.1	55.3	56.1
75°	49.4	48.7	47.2	47.2	46.5	47.2	46.5	46.5	45.7	46.5	46.5
77.5°	39.8	39.1	38.4	38.4	37.6	37.6	37.6	37.6	37.6	37.6	38.4
80°	30.2	29.5	28.8	29.5	28.8	29.5	28.8	28.8	29.5	28.8	28.8
82.5°	22.1	21.4	21.4	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
85°	13.3	12.5	12.5	13.3	12.5	13.3	12.5	12.5	12.5	13.3	13.3
87.5°	5.9	6.6	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.6
90°	26.2	25.8	25.5	25.2	25.0	25.1	25.2	25.4	25.5	25.7	25.5
92.5°	23.7	23.8	24.0	24.1	24.2	24.2	24.2	24.2	24.2	24.2	24.2
95°	48.4	48.4	48.4	48.4	48.4	48.2	47.9	47.6	47.2	46.9	47.2
97.5°	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7
100°	104.4	104.4	104.4	104.4	104.4	104.3	104.2	104.0	103.9	103.7	103.9
102.5°	135.7	135.8	136.0	136.1	136.2	136.1	136.0	135.8	135.7	135.5	135.7
105°	166.8	167.2	167.5	167.8	168.0	168.0	168.0	168.0	168.0	168.0	168.0
107.5°	200.8	200.9	201.1	201.2	201.3	200.9	200.0	199.2	198.3	197.5	198.3
110°	235.4	235.4	235.4	235.4	235.4	235.1	234.6	234.1	233.6	233.1	233.6

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	270.4	269.9	269.4	268.9	268.7	268.5	268.2	267.9	267.5	267.2	267.5
115°	305.6	305.4	305.3	305.1	305.0	304.7	304.2	303.7	303.2	302.7	303.2
117.5°	340.1	339.6	339.1	338.6	338.3	338.0	337.5	337.0	336.5	336.0	336.5
120°	373.9	373.9	373.9	373.9	373.9	373.6	373.1	372.6	372.1	371.6	372.1
122.5°	409.7	409.2	408.7	408.2	407.9	407.7	407.4	407.1	406.7	406.4	406.7
125°	444.5	444.0	443.5	443.0	442.8	442.7	442.5	442.4	442.2	442.0	442.2
127.5°	478.4	477.8	477.1	476.4	476.1	475.8	475.3	474.8	474.3	473.8	474.3
130°	512.8	512.4	512.1	511.8	511.6	511.3	510.6	509.9	509.3	508.6	509.3
132.5°	547.2	546.3	545.5	544.6	544.2	543.9	543.4	542.9	542.4	541.9	542.4
135°	579.5	579.4	579.2	579.1	579.0	578.7	578.2	577.7	577.2	576.7	577.2
137.5°	611.3	611.2	611.0	610.9	610.8	610.5	609.8	609.1	608.4	607.7	608.4
140°	643.3	643.3	643.3	643.3	643.3	643.0	642.3	641.6	641.0	640.3	641.0
142.5°	672.3	672.4	672.6	672.7	672.8	672.5	671.8	671.1	670.5	669.8	670.5
145°	701.8	702.0	702.1	702.3	702.4	702.1	701.4	700.7	700.0	699.3	700.0
147.5°	727.6	728.0	728.3	728.6	728.8	728.5	727.8	727.1	726.5	725.8	726.5
150°	752.0	752.5	753.0	753.5	753.8	753.5	753.0	752.5	752.0	751.5	752.0
152.5°	776.5	777.1	777.8	778.5	778.8	778.5	777.8	777.1	776.5	775.8	776.5
155°	796.2	797.1	797.9	798.8	799.2	799.0	798.5	798.0	797.5	797.0	797.5
157.5°	815.6	816.8	817.9	819.1	819.7	819.3	818.4	817.6	816.7	815.9	816.7
160°	832.8	833.8	834.8	835.8	836.3	836.0	835.3	834.6	834.0	833.3	834.0
162.5°	848.1	849.3	850.4	851.6	852.2	851.8	850.9	850.1	849.2	848.4	849.2
165°	861.0	862.2	863.3	864.5	865.1	864.7	863.8	863.0	862.1	861.3	862.1
167.5°	872.3	873.5	874.6	875.8	876.4	876.0	875.1	874.3	873.4	872.6	873.4
170°	881.4	882.6	883.7	884.9	885.5	885.0	884.0	883.0	882.0	881.0	882.0
172.5°	888.2	889.4	890.5	891.7	892.3	891.8	890.8	889.8	888.8	887.8	888.8
175°	892.8	894.0	895.1	896.3	896.9	896.4	895.4	894.3	893.3	892.3	893.3
177.5°	895.6	896.6	897.6	898.6	899.1	898.6	897.6	896.6	895.6	894.6	895.6
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1118.8	1113.6	1112.2	1113.6	1112.2	1112.9	1107.7	1088.6	1093.7	1085.6	1090.0
5°	1182.2	1177.8	1168.2	1166.7	1165.3	1163.8	1156.4	1139.4	1132.8	1121.7	1121.0
7.5°	1242.7	1242.7	1235.3	1230.2	1223.5	1218.4	1208.8	1183.7	1173.4	1160.1	1152.7
10°	1302.4	1283.3	1291.4	1286.2	1270.0	1267.0	1249.3	1234.6	1214.7	1201.4	1189.6
12.5°	1345.2	1339.3	1331.9	1327.5	1323.1	1313.5	1301.7	1264.1	1253.8	1227.2	1213.9
15°	1343.7	1340.0	1342.3	1342.3	1340.8	1338.6	1329.0	1301.7	1284.0	1258.2	1235.3
17.5°	1271.5	1281.0	1290.6	1297.3	1312.0	1318.7	1327.5	1311.3	1300.2	1278.1	1253.8
20°	1145.3	1168.9	1197.0	1202.9	1216.1	1255.2	1272.9	1286.9	1291.4	1284.0	1264.1
22.5°	969.8	989.7	1057.6	1056.1	1075.3	1121.7	1173.4	1215.4	1248.6	1267.0	1259.7
25°	759.6	787.7	823.8	851.1	913.8	983.1	1047.3	1114.4	1171.9	1222.8	1235.3
27.5°	574.5	611.4	640.2	676.3	708.0	789.9	872.5	977.2	1044.3	1140.9	1191.1
30°	464.6	481.6	510.4	527.3	542.8	605.5	699.2	802.4	920.4	1031.8	1118.1
32.5°	396.8	408.6	430.0	437.3	453.6	495.6	554.6	649.0	770.7	905.7	1019.2
35°	356.2	368.8	373.2	379.8	393.1	419.6	460.2	528.8	638.7	770.7	906.4
37.5°	321.6	328.2	340.7	345.2	349.6	369.5	396.8	444.7	517.7	626.1	776.6
40°	297.2	300.9	307.5	311.2	314.2	328.2	352.5	385.0	438.8	521.4	660.1
42.5°	271.4	275.8	280.3	284.7	288.4	299.4	314.2	345.2	381.3	444.0	544.3
45°	246.3	249.3	254.4	257.4	262.6	271.4	284.7	306.1	338.5	378.3	459.5
47.5°	223.5	227.2	229.4	233.1	236.7	246.3	258.9	272.9	299.4	338.5	397.5
50°	202.8	207.2	210.2	210.9	213.9	222.7	233.1	248.5	265.5	295.7	347.4
52.5°	188.1	188.8	191.0	194.0	193.2	198.4	208.0	219.8	237.5	261.8	299.4
55°	171.1	173.3	174.8	175.5	175.5	180.0	185.1	196.2	210.2	230.1	261.8
57.5°	149.7	151.9	156.4	157.8	160.0	162.3	164.5	171.8	183.6	202.8	228.6
60°	127.6	129.1	133.5	136.4	137.9	143.8	146.8	152.7	159.3	173.3	197.7
62.5°	102.5	104.0	106.2	109.2	112.1	121.0	128.3	134.2	139.4	149.0	168.9
65°	89.2	90.0	91.5	92.2	92.9	96.6	103.3	111.4	121.0	128.3	140.1
67.5°	77.4	78.2	78.9	80.4	81.1	81.9	84.8	87.0	96.6	106.9	115.8
70°	66.4	67.9	68.6	68.6	69.3	70.8	72.3	75.2	78.2	83.3	94.4
72.5°	56.1	56.8	58.3	58.3	58.3	59.7	61.2	62.7	64.2	67.1	71.5
75°	46.5	47.9	47.9	47.9	48.7	48.7	50.2	51.6	53.1	55.3	56.8
77.5°	38.4	38.4	38.4	38.4	39.1	39.1	39.8	41.3	42.0	42.8	44.3
80°	28.8	29.5	29.5	29.5	30.2	30.2	30.2	31.7	32.5	32.5	33.9
82.5°	21.4	21.4	21.4	22.1	21.4	22.1	22.1	22.9	22.1	22.9	23.6
85°	13.3	13.3	13.3	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.8
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	7.4	6.6	6.6
90°	25.4	25.2	25.1	25.0	25.2	25.5	25.8	26.2	26.5	22.8	19.1
92.5°	24.2	24.2	24.2	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
95°	47.6	47.9	48.2	48.4	48.4	48.4	48.4	48.4	48.4	48.1	47.7
97.5°	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.0	74.4
100°	104.0	104.2	104.3	104.4	104.4	104.4	104.4	104.4	104.4	103.9	103.4
102.5°	135.8	136.0	136.1	136.2	136.1	136.0	135.8	135.7	135.5	134.8	134.1
105°	168.0	168.0	168.0	168.0	167.8	167.5	167.2	166.8	166.5	166.2	165.8
107.5°	199.2	200.0	200.9	201.3	201.2	201.1	200.9	200.8	200.6	200.6	200.6
110°	234.1	234.6	235.1	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	267.9	268.2	268.5	268.7	268.9	269.4	269.9	270.4	270.9	271.1	271.3
115°	303.7	304.2	304.7	305.0	305.1	305.3	305.4	305.6	305.8	306.1	306.5
117.5°	337.0	337.5	338.0	338.3	338.6	339.1	339.6	340.1	340.6	341.4	342.3
120°	372.6	373.1	373.6	373.9	373.9	373.9	373.9	373.9	373.9	375.2	376.6
122.5°	407.1	407.4	407.7	407.9	408.2	408.7	409.2	409.7	410.2	411.0	411.9
125°	442.4	442.5	442.7	442.8	443.0	443.5	444.0	444.5	445.0	445.5	446.0
127.5°	474.8	475.3	475.8	476.1	476.4	477.1	477.8	478.4	479.1	479.8	480.4
130°	509.9	510.6	511.3	511.6	511.8	512.1	512.4	512.8	513.1	513.5	513.8
132.5°	542.9	543.4	543.9	544.2	544.6	545.5	546.3	547.2	548.0	547.8	547.6
135°	577.7	578.2	578.7	579.0	579.1	579.2	579.4	579.5	579.7	579.4	579.0
137.5°	609.1	609.8	610.5	610.8	610.9	611.0	611.2	611.3	611.5	611.2	610.8
140°	641.6	642.3	643.0	643.3	643.3	643.3	643.3	643.3	643.3	642.5	641.6
142.5°	671.1	671.8	672.5	672.8	672.7	672.6	672.4	672.3	672.1	671.6	671.1
145°	700.7	701.4	702.1	702.4	702.3	702.1	702.0	701.8	701.6	700.6	699.6
147.5°	727.1	727.8	728.5	728.8	728.6	728.3	728.0	727.6	727.3	726.6	726.0
150°	752.5	753.0	753.5	753.8	753.5	753.0	752.5	752.0	751.5	750.8	750.2
152.5°	777.1	777.8	778.5	778.8	778.5	777.8	777.1	776.5	775.8	775.0	774.1
155°	798.0	798.5	799.0	799.2	798.8	797.9	797.1	796.2	795.4	794.9	794.4
157.5°	817.6	818.4	819.3	819.7	819.1	817.9	816.8	815.6	814.4	814.0	813.7
160°	834.6	835.3	836.0	836.3	835.8	834.8	833.8	832.8	831.8	831.6	831.4
162.5°	850.1	850.9	851.8	852.2	851.6	850.4	849.3	848.1	846.9	846.7	846.6
165°	863.0	863.8	864.7	865.1	864.5	863.3	862.2	861.0	859.8	859.8	859.8
167.5°	874.3	875.1	876.0	876.4	875.8	874.6	873.5	872.3	871.1	871.1	871.1
170°	883.0	884.0	885.0	885.5	884.9	883.7	882.6	881.4	880.2	880.4	880.6
172.5°	889.8	890.8	891.8	892.3	891.7	890.5	889.4	888.2	887.0	887.2	887.4
175°	894.3	895.4	896.4	896.9	896.3	895.1	894.0	892.8	891.6	891.9	892.3
177.5°	896.6	897.6	898.6	899.1	898.6	897.6	896.6	895.6	894.6	894.9	895.3
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1083.4	1079.7	1079.7	1077.5	1077.5	1065.7	1065.7	1069.4	1065.0	1059.8	1052.4
5°	1111.4	1103.3	1101.1	1098.1	1088.6	1073.8	1067.9	1065.7	1056.8	1045.8	1033.2
7.5°	1138.0	1124.7	1118.1	1111.4	1098.9	1078.2	1066.4	1058.3	1045.0	1028.1	1011.9
10°	1163.8	1146.8	1129.9	1121.7	1104.0	1078.2	1061.3	1048.0	1028.8	1006.0	983.1
12.5°	1187.4	1152.0	1149.0	1132.8	1107.0	1077.5	1051.7	1032.5	1008.2	981.6	955.1
15°	1208.0	1171.9	1154.2	1139.4	1105.5	1068.6	1041.4	1017.8	985.3	955.1	922.6
17.5°	1218.4	1179.3	1167.5	1143.1	1108.5	1060.5	1023.7	994.9	959.5	923.4	886.5
20°	1228.7	1183.0	1163.8	1146.8	1099.6	1045.0	1003.7	970.6	931.5	888.7	848.1
22.5°	1233.8	1183.0	1160.1	1136.5	1090.8	1028.1	979.4	940.3	894.6	851.1	802.4
25°	1225.0	1178.5	1151.2	1126.9	1075.3	1007.4	951.4	907.1	858.5	809.0	759.6
27.5°	1202.9	1168.2	1136.5	1111.4	1053.9	980.9	921.9	871.7	821.6	766.3	716.1
30°	1161.6	1146.1	1121.0	1093.0	1030.3	957.3	887.2	835.6	780.3	725.0	672.6
32.5°	1097.4	1110.7	1094.5	1070.1	1002.3	924.8	850.3	798.0	737.5	677.8	629.8
35°	1019.2	1066.4	1057.6	1040.6	972.8	890.2	815.7	752.3	691.8	631.3	583.4
37.5°	933.7	1005.2	1012.6	1002.3	938.8	854.8	772.9	711.0	649.0	587.8	539.1
40°	816.4	926.3	949.9	954.3	903.4	812.0	726.4	666.0	604.8	545.0	486.0
42.5°	708.7	847.4	876.9	895.3	858.5	770.0	683.7	616.6	556.1	502.2	443.2
45°	607.7	752.3	800.2	823.8	807.6	722.0	632.8	570.1	514.8	465.4	408.6
47.5°	503.7	649.0	716.1	753.7	753.7	673.3	584.1	522.2	469.1	427.0	376.9
50°	434.4	555.3	624.7	674.1	687.4	623.9	539.9	479.4	429.2	383.5	345.2
52.5°	370.2	478.6	536.2	587.8	626.1	570.8	490.4	435.9	386.5	343.7	313.4
55°	320.1	401.2	453.6	510.4	553.1	517.0	442.5	389.4	346.6	311.2	285.4
57.5°	272.1	342.9	385.7	435.9	481.6	454.3	394.6	348.8	311.2	280.3	257.4
60°	231.6	289.1	322.3	361.4	418.2	399.0	349.6	307.5	277.3	249.3	230.1
62.5°	196.9	242.6	270.7	298.7	350.3	341.5	303.1	270.7	244.9	221.3	205.0
65°	161.5	199.1	221.3	245.6	286.9	290.6	259.6	236.7	213.1	192.5	177.7
67.5°	130.5	160.0	180.0	200.6	233.8	244.1	222.7	203.6	183.6	166.7	153.4
70°	105.5	126.1	140.9	157.1	184.4	196.9	185.9	172.6	156.4	142.3	130.5
72.5°	83.3	96.6	105.5	118.0	140.1	152.7	151.9	140.1	128.3	118.7	109.2
75°	61.2	71.5	78.9	87.0	104.7	116.5	119.5	114.3	102.5	95.1	87.8
77.5°	46.5	52.4	56.1	62.0	74.5	84.8	89.2	87.8	79.7	73.8	68.6
80°	35.4	36.9	38.4	40.6	50.9	60.5	63.4	62.7	58.3	56.1	50.2
82.5°	25.1	25.8	26.6	27.3	31.0	39.1	42.0	43.5	39.8	37.6	32.5
85°	14.8	15.5	15.5	17.0	17.7	19.9	25.1	25.1	24.3	21.4	20.7
87.5°	7.4	7.4	6.6	6.6	7.4	8.1	9.6	11.1	9.6	8.9	8.1
90°	15.4	11.7	9.8	8.8	6.8	4.8	2.8	0.8	2.8	4.8	6.8
92.5°	23.0	22.8	22.7	22.0	20.7	19.4	18.0	16.7	18.0	19.4	20.7
95°	47.4	47.1	46.9	46.1	44.4	42.7	41.1	39.4	41.1	42.7	44.4
97.5°	73.7	73.0	72.7	71.9	70.4	68.9	67.3	65.8	67.3	68.9	70.4
100°	102.9	102.4	102.2	101.5	100.2	98.8	97.5	96.1	97.5	98.8	100.2
102.5°	133.4	132.7	132.4	131.9	130.9	129.9	128.9	127.9	128.9	129.9	130.9
105°	165.5	165.2	165.0	164.7	164.2	163.7	163.2	162.7	163.2	163.7	164.2
107.5°	200.6	200.6	200.6	200.3	199.6	198.9	198.2	197.5	198.2	198.9	199.6
110°	235.4	235.4	235.4	234.9	233.9	232.8	231.8	230.8	231.8	232.8	233.9

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	271.4	271.6	271.7	271.2	270.2	269.2	268.2	267.2	268.2	269.2	270.2
115°	306.8	307.1	307.3	306.8	305.8	304.7	303.7	302.7	303.7	304.7	305.8
117.5°	343.1	344.0	344.4	343.7	342.4	341.0	339.7	338.3	339.7	341.0	342.4
120°	377.9	379.2	379.9	379.2	377.9	376.6	375.2	373.9	375.2	376.6	377.9
122.5°	412.7	413.6	414.0	413.2	411.5	409.8	408.1	406.4	408.1	409.8	411.5
125°	446.5	447.0	447.3	446.5	445.0	443.5	442.0	440.5	442.0	443.5	445.0
127.5°	481.1	481.8	482.1	481.2	479.3	477.5	475.6	473.8	475.6	477.5	479.3
130°	514.2	514.5	514.7	513.6	511.4	509.2	507.0	504.8	507.0	509.2	511.4
132.5°	547.5	547.3	547.2	546.4	544.7	543.0	541.3	539.6	541.3	543.0	544.7
135°	578.7	578.4	578.2	577.3	575.4	573.6	571.7	569.9	571.7	573.6	575.4
137.5°	610.5	610.2	610.0	609.2	607.7	606.2	604.7	603.2	604.7	606.2	607.7
140°	640.8	639.9	639.5	638.7	637.2	635.7	634.2	632.7	634.2	635.7	637.2
142.5°	670.6	670.1	669.8	669.0	667.5	666.0	664.5	663.0	664.5	666.0	667.5
145°	698.6	697.6	697.1	696.5	695.3	694.2	693.0	691.8	693.0	694.2	695.3
147.5°	725.3	724.6	724.3	723.5	722.0	720.5	719.0	717.5	719.0	720.5	722.0
150°	749.5	748.8	748.5	748.0	747.0	746.0	745.0	744.0	745.0	746.0	747.0
152.5°	773.3	772.4	772.0	771.5	770.5	769.4	768.4	767.4	768.4	769.4	770.5
155°	793.9	793.4	793.2	792.9	792.4	791.9	791.4	790.9	791.4	791.9	792.4
157.5°	813.3	813.0	812.8	812.6	812.3	812.0	811.6	811.3	811.6	812.0	812.3
160°	831.3	831.1	831.0	830.8	830.5	830.2	829.8	829.5	829.8	830.2	830.5
162.5°	846.4	846.3	846.2	846.2	846.2	846.2	846.2	846.2	846.2	846.2	846.2
165°	859.8	859.8	859.8	859.9	860.0	860.2	860.3	860.5	860.3	860.2	860.0
167.5°	871.1	871.1	871.1	871.4	871.9	872.4	872.9	873.4	872.9	872.4	871.9
170°	880.7	880.9	881.0	881.2	881.7	882.2	882.7	883.2	882.7	882.2	881.7
172.5°	887.5	887.7	887.8	888.0	888.5	889.0	889.5	890.0	889.5	889.0	888.5
175°	892.6	892.9	893.1	893.3	893.8	894.3	894.8	895.3	894.8	894.3	893.8
177.5°	895.6	895.9	896.1	896.4	896.9	897.4	897.9	898.4	897.9	897.4	896.9
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1049.5	1050.2	1052.4	1045.8	1035.5	1031.0	1017.8	1015.5	1013.3	1013.3	1015.5
5°	1025.9	1022.9	1023.7	1011.1	996.4	987.5	969.1	972.0	962.4	956.5	958.0
7.5°	1000.1	991.9	991.2	975.0	956.5	940.3	921.1	916.7	907.9	897.5	893.1
10°	967.6	961.7	950.6	932.2	908.6	895.3	869.5	854.0	851.8	836.3	830.4
12.5°	934.4	924.1	913.0	887.2	860.7	839.3	820.1	803.1	791.3	778.1	769.2
15°	896.1	883.5	871.0	843.7	812.7	791.3	762.6	737.5	702.8	675.6	660.1
17.5°	854.0	840.0	823.1	792.8	762.6	733.1	680.0	650.5	626.1	609.9	600.3
20°	810.5	795.0	778.1	747.8	695.5	643.8	614.3	591.5	576.7	560.5	548.7
22.5°	764.8	748.6	730.1	682.9	627.6	591.5	568.6	547.2	525.8	517.0	511.1
25°	722.0	707.3	683.7	619.5	576.0	542.8	517.0	503.0	491.9	480.1	469.1
27.5°	677.8	650.5	617.3	563.5	536.2	502.2	483.8	473.5	454.3	446.2	441.0
30°	624.7	594.4	562.7	524.4	492.7	469.1	452.1	435.1	424.1	416.0	407.1
32.5°	570.8	542.1	522.2	482.3	458.7	434.4	418.2	407.8	391.6	386.5	382.8
35°	524.4	500.0	482.3	449.9	427.8	405.6	393.8	378.3	368.0	358.4	352.5
37.5°	478.6	465.4	446.9	419.6	396.0	378.3	362.1	357.0	342.9	337.8	331.9
40°	446.9	427.0	411.5	387.9	368.0	348.8	338.5	326.7	317.1	309.0	306.8
42.5°	408.6	393.8	385.0	359.2	338.5	327.5	314.9	301.6	294.3	287.6	279.5
45°	379.8	366.5	354.0	333.4	314.9	300.9	289.8	281.0	268.5	265.5	253.0
47.5°	349.6	336.3	326.7	306.1	289.1	275.8	267.7	255.9	245.6	239.0	233.1
50°	319.3	308.3	299.4	281.7	267.0	253.0	241.9	230.1	225.7	214.6	210.9
52.5°	290.6	283.2	273.6	256.7	241.9	230.1	218.3	208.7	202.1	196.2	191.8
55°	266.2	254.4	250.0	231.6	219.0	206.5	196.2	190.3	182.2	178.5	174.8
57.5°	239.0	232.3	224.9	210.9	196.9	185.1	177.7	168.9	164.5	160.0	157.1
60°	215.4	205.8	199.9	188.1	175.5	164.5	157.8	151.2	145.3	141.6	135.7
62.5°	188.1	180.7	177.0	164.5	154.1	143.8	137.9	131.3	126.9	120.2	112.8
65°	164.5	158.6	154.1	143.8	134.2	124.6	118.7	110.6	104.7	101.0	100.3
67.5°	143.8	139.4	132.8	123.2	113.6	106.2	99.6	92.9	92.2	90.7	90.7
70°	121.0	116.5	112.8	102.5	94.4	86.3	84.8	82.6	80.4	79.7	78.2
72.5°	101.0	97.4	92.9	84.1	76.0	73.8	72.3	70.8	68.6	67.9	67.1
75°	81.9	76.7	73.8	65.6	63.4	62.0	60.5	58.3	56.8	56.1	54.6
77.5°	62.7	57.5	57.5	53.1	51.6	49.4	47.9	46.5	45.7	44.3	44.3
80°	44.3	44.3	42.8	40.6	38.4	37.6	35.4	34.7	33.9	34.7	33.2
82.5°	32.5	29.5	29.5	28.0	26.6	25.8	24.3	24.3	23.6	23.6	23.6
85°	18.4	18.4	17.7	16.2	15.5	15.5	14.8	14.8	14.0	14.0	13.3
87.5°	7.4	6.6	7.4	6.6	6.6	5.9	5.9	5.9	5.2	5.9	5.2
90°	8.8	9.8	11.7	15.4	19.1	22.8	26.5	26.2	25.8	25.5	25.2
92.5°	22.0	22.7	22.8	23.0	23.1	23.3	23.5	23.7	23.8	24.0	24.1
95°	46.1	46.9	47.1	47.4	47.7	48.1	48.4	48.4	48.4	48.4	48.4
97.5°	71.9	72.7	73.0	73.7	74.4	75.0	75.7	75.7	75.7	75.7	75.7
100°	101.5	102.2	102.4	102.9	103.4	103.9	104.4	104.4	104.4	104.4	104.4
102.5°	131.9	132.4	132.7	133.4	134.1	134.8	135.5	135.7	135.8	136.0	136.1
105°	164.7	165.0	165.2	165.5	165.8	166.2	166.5	166.8	167.2	167.5	167.8
107.5°	200.3	200.6	200.6	200.6	200.6	200.6	200.6	200.8	200.9	201.1	201.2
110°	234.9	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	271.2	271.7	271.6	271.4	271.3	271.1	270.9	270.4	269.9	269.4	268.9
115°	306.8	307.3	307.1	306.8	306.5	306.1	305.8	305.6	305.4	305.3	305.1
117.5°	343.7	344.4	344.0	343.1	342.3	341.4	340.6	340.1	339.6	339.1	338.6
120°	379.2	379.9	379.2	377.9	376.6	375.2	373.9	373.9	373.9	373.9	373.9
122.5°	413.2	414.0	413.6	412.7	411.9	411.0	410.2	409.7	409.2	408.7	408.2
125°	446.5	447.3	447.0	446.5	446.0	445.5	445.0	444.5	444.0	443.5	443.0
127.5°	481.2	482.1	481.8	481.1	480.4	479.8	479.1	478.4	477.8	477.1	476.4
130°	513.6	514.7	514.5	514.2	513.8	513.5	513.1	512.8	512.4	512.1	511.8
132.5°	546.4	547.2	547.3	547.5	547.6	547.8	548.0	547.2	546.3	545.5	544.6
135°	577.3	578.2	578.4	578.7	579.0	579.4	579.7	579.5	579.4	579.2	579.1
137.5°	609.2	610.0	610.2	610.5	610.8	611.2	611.5	611.3	611.2	611.0	610.9
140°	638.7	639.5	639.9	640.8	641.6	642.5	643.3	643.3	643.3	643.3	643.3
142.5°	669.0	669.8	670.1	670.6	671.1	671.6	672.1	672.3	672.4	672.6	672.7
145°	696.5	697.1	697.6	698.6	699.6	700.6	701.6	701.8	702.0	702.1	702.3
147.5°	723.5	724.3	724.6	725.3	726.0	726.6	727.3	727.6	728.0	728.3	728.6
150°	748.0	748.5	748.8	749.5	750.2	750.8	751.5	752.0	752.5	753.0	753.5
152.5°	771.5	772.0	772.4	773.3	774.1	775.0	775.8	776.5	777.1	777.8	778.5
155°	792.9	793.2	793.4	793.9	794.4	794.9	795.4	796.2	797.1	797.9	798.8
157.5°	812.6	812.8	813.0	813.3	813.7	814.0	814.4	815.6	816.8	817.9	819.1
160°	830.8	831.0	831.1	831.3	831.4	831.6	831.8	832.8	833.8	834.8	835.8
162.5°	846.2	846.2	846.3	846.4	846.6	846.7	846.9	848.1	849.3	850.4	851.6
165°	859.9	859.8	859.8	859.8	859.8	859.8	859.8	861.0	862.2	863.3	864.5
167.5°	871.4	871.1	871.1	871.1	871.1	871.1	871.1	872.3	873.5	874.6	875.8
170°	881.2	881.0	880.9	880.7	880.6	880.4	880.2	881.4	882.6	883.7	884.9
172.5°	888.0	887.8	887.7	887.5	887.4	887.2	887.0	888.2	889.4	890.5	891.7
175°	893.3	893.1	892.9	892.6	892.3	891.9	891.6	892.8	894.0	895.1	896.3
177.5°	896.4	896.1	895.9	895.6	895.3	894.9	894.6	895.6	896.6	897.6	898.6
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1015.5	1014.1	1009.6	1011.1	1008.9	1008.9	1007.4	1007.4	1007.4	1011.1	1008.9
5°	960.2	955.1	949.9	947.7	945.5	943.3	943.3	942.5	949.2	947.7	953.6
7.5°	891.6	890.2	879.8	879.8	876.2	874.7	878.4	879.1	879.8	881.3	885.0
10°	830.4	826.7	812.0	813.5	811.3	808.3	810.5	809.0	814.2	815.7	814.2
12.5°	758.2	751.5	735.3	727.2	718.3	711.7	719.8	713.9	734.6	740.5	756.7
15°	662.3	649.7	638.7	638.7	630.6	624.7	628.4	635.0	639.4	646.1	649.0
17.5°	598.1	593.0	584.1	578.9	576.7	574.5	574.5	577.5	587.1	586.3	592.2
20°	543.5	540.6	536.2	529.5	527.3	525.8	525.8	525.8	532.5	538.4	542.1
22.5°	505.9	503.7	500.8	491.9	487.5	486.0	489.7	491.9	497.1	501.5	505.2
25°	468.3	463.2	458.0	455.0	452.8	452.8	454.3	455.0	457.3	459.5	463.9
27.5°	437.3	433.7	426.3	418.2	418.2	416.0	417.4	418.9	424.1	431.4	435.1
30°	402.7	401.9	399.0	396.0	393.1	391.6	394.6	396.8	397.5	401.2	401.2
32.5°	377.6	372.4	367.3	364.3	362.9	362.1	362.9	365.8	365.8	370.2	375.4
35°	352.5	349.6	344.4	339.3	337.8	334.1	337.0	340.0	345.2	347.4	349.6
37.5°	325.2	321.6	319.3	317.9	314.9	315.7	313.4	317.9	322.3	321.6	323.0
40°	304.6	298.0	291.3	290.6	289.8	289.1	289.1	289.8	292.8	295.7	300.2
42.5°	278.0	275.8	269.9	264.0	262.6	261.1	259.6	262.6	268.5	273.6	275.8
45°	250.8	247.8	246.3	241.9	239.0	238.2	236.7	240.4	245.6	247.8	249.3
47.5°	225.7	224.9	220.5	221.3	219.0	219.8	219.0	221.3	221.3	223.5	224.9
50°	208.7	206.5	204.3	202.8	200.6	200.6	199.9	200.6	203.6	206.5	205.8
52.5°	191.8	188.1	187.3	186.6	185.1	186.6	184.4	185.1	188.1	189.5	188.8
55°	171.8	171.1	169.6	168.2	167.4	166.7	166.7	166.7	169.6	171.8	172.6
57.5°	156.4	152.7	149.7	149.7	146.8	146.0	147.5	148.2	150.5	151.9	153.4
60°	135.0	133.5	129.1	126.9	122.4	121.7	121.7	124.6	128.3	133.5	135.0
62.5°	112.1	109.9	109.2	109.2	109.2	109.2	109.2	109.2	109.2	109.9	109.9
65°	99.6	100.3	99.6	98.8	99.6	99.6	98.8	98.8	98.8	99.6	100.3
67.5°	89.2	88.5	89.2	88.5	87.8	87.8	87.0	87.8	88.5	89.2	89.2
70°	77.4	77.4	76.7	77.4	76.7	76.0	75.2	75.2	76.7	77.4	77.4
72.5°	66.4	66.4	65.6	65.6	64.2	64.2	64.9	64.2	64.2	66.4	66.4
75°	55.3	54.6	53.8	53.8	53.1	53.1	53.1	52.4	53.8	53.8	54.6
77.5°	43.5	43.5	43.5	42.8	42.8	42.0	42.0	42.8	42.8	42.8	43.5
80°	33.2	33.2	33.2	32.5	31.7	31.7	31.7	31.7	31.7	32.5	31.7
82.5°	22.9	22.9	22.9	22.9	22.9	22.1	22.1	22.1	22.9	22.9	22.1
85°	14.0	13.3	14.0	14.0	13.3	14.0	13.3	13.3	12.5	12.5	13.3
87.5°	5.9	5.2	4.4	4.4	5.2	4.4	4.4	4.4	5.2	4.4	4.4
90°	25.0	25.1	25.2	25.4	25.5	25.7	25.5	25.4	25.2	25.1	25.0
92.5°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2
95°	48.4	48.2	47.9	47.6	47.2	46.9	47.2	47.6	47.9	48.2	48.4
97.5°	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7
100°	104.4	104.3	104.2	104.0	103.9	103.7	103.9	104.0	104.2	104.3	104.4
102.5°	136.2	136.1	136.0	135.8	135.7	135.5	135.7	135.8	136.0	136.1	136.2
105°	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0
107.5°	201.3	200.9	200.0	199.2	198.3	197.5	198.3	199.2	200.0	200.9	201.3
110°	235.4	235.1	234.6	234.1	233.6	233.1	233.6	234.1	234.6	235.1	235.4

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	268.7	268.5	268.2	267.9	267.5	267.2	267.5	267.9	268.2	268.5	268.7
115°	305.0	304.7	304.2	303.7	303.2	302.7	303.2	303.7	304.2	304.7	305.0
117.5°	338.3	338.0	337.5	337.0	336.5	336.0	336.5	337.0	337.5	338.0	338.3
120°	373.9	373.6	373.1	372.6	372.1	371.6	372.1	372.6	373.1	373.6	373.9
122.5°	407.9	407.7	407.4	407.1	406.7	406.4	406.7	407.1	407.4	407.7	407.9
125°	442.8	442.7	442.5	442.4	442.2	442.0	442.2	442.4	442.5	442.7	442.8
127.5°	476.1	475.8	475.3	474.8	474.3	473.8	474.3	474.8	475.3	475.8	476.1
130°	511.6	511.3	510.6	509.9	509.3	508.6	509.3	509.9	510.6	511.3	511.6
132.5°	544.2	543.9	543.4	542.9	542.4	541.9	542.4	542.9	543.4	543.9	544.2
135°	579.0	578.7	578.2	577.7	577.2	576.7	577.2	577.7	578.2	578.7	579.0
137.5°	610.8	610.5	609.8	609.1	608.4	607.7	608.4	609.1	609.8	610.5	610.8
140°	643.3	643.0	642.3	641.6	641.0	640.3	641.0	641.6	642.3	643.0	643.3
142.5°	672.8	672.5	671.8	671.1	670.5	669.8	670.5	671.1	671.8	672.5	672.8
145°	702.4	702.1	701.4	700.7	700.0	699.3	700.0	700.7	701.4	702.1	702.4
147.5°	728.8	728.5	727.8	727.1	726.5	725.8	726.5	727.1	727.8	728.5	728.8
150°	753.8	753.5	753.0	752.5	752.0	751.5	752.0	752.5	753.0	753.5	753.8
152.5°	778.8	778.5	777.8	777.1	776.5	775.8	776.5	777.1	777.8	778.5	778.8
155°	799.2	799.0	798.5	798.0	797.5	797.0	797.5	798.0	798.5	799.0	799.2
157.5°	819.7	819.3	818.4	817.6	816.7	815.9	816.7	817.6	818.4	819.3	819.7
160°	836.3	836.0	835.3	834.6	834.0	833.3	834.0	834.6	835.3	836.0	836.3
162.5°	852.2	851.8	850.9	850.1	849.2	848.4	849.2	850.1	850.9	851.8	852.2
165°	865.1	864.7	863.8	863.0	862.1	861.3	862.1	863.0	863.8	864.7	865.1
167.5°	876.4	876.0	875.1	874.3	873.4	872.6	873.4	874.3	875.1	876.0	876.4
170°	885.5	885.0	884.0	883.0	882.0	881.0	882.0	883.0	884.0	885.0	885.5
172.5°	892.3	891.8	890.8	889.8	888.8	887.8	888.8	889.8	890.8	891.8	892.3
175°	896.9	896.4	895.4	894.3	893.3	892.3	893.3	894.3	895.4	896.4	896.9
177.5°	899.1	898.6	897.6	896.6	895.6	894.6	895.6	896.6	897.6	898.6	899.1
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1011.1	1014.8	1013.3	1005.2	1013.3	1015.5	1020.0	1024.4	1027.3	1031.8	1035.5
5°	947.7	955.1	959.5	955.1	969.8	972.0	982.4	988.3	997.1	1004.5	1010.4
7.5°	888.0	893.9	902.7	904.2	913.0	923.4	938.1	952.9	966.9	974.2	980.9
10°	823.8	834.1	847.4	844.4	857.7	873.9	889.4	913.0	924.8	938.1	949.9
12.5°	759.6	766.3	784.0	789.9	809.0	821.6	843.0	857.7	887.2	902.7	913.0
15°	647.5	674.8	696.9	723.5	748.6	772.2	791.3	817.9	843.7	855.5	872.5
17.5°	596.6	609.2	622.5	635.7	668.2	710.2	744.1	772.9	795.0	810.5	830.4
20°	543.5	556.1	570.8	583.4	603.3	633.5	675.6	725.0	751.5	767.7	786.9
22.5°	505.9	517.7	527.3	538.4	553.9	576.0	607.7	668.9	704.3	724.2	741.2
25°	465.4	480.1	490.4	498.6	511.1	535.4	561.2	595.9	659.3	674.8	698.4
27.5°	437.3	441.8	453.6	466.1	478.6	491.9	518.5	548.0	590.7	624.7	653.4
30°	404.2	415.2	426.3	431.4	442.5	461.7	477.9	509.6	542.8	569.4	604.0
32.5°	379.1	385.7	393.1	405.6	416.0	429.2	445.5	472.0	500.0	517.0	543.5
35°	351.1	355.5	371.0	376.1	386.5	399.7	416.0	436.6	466.8	480.1	499.3
37.5°	324.5	334.8	339.3	351.1	360.6	373.9	385.7	409.3	429.2	444.7	462.4
40°	303.9	308.3	316.4	326.7	334.8	345.2	359.9	376.9	398.3	410.8	426.3
42.5°	278.8	282.5	292.8	298.7	312.0	321.6	330.4	351.1	370.2	379.8	395.3
45°	251.5	260.3	267.0	278.8	286.2	298.0	309.0	323.8	341.5	352.5	361.4
47.5°	227.9	236.7	243.4	254.4	266.2	271.4	283.2	298.7	314.9	323.8	336.3
50°	208.7	211.7	224.2	229.4	241.9	252.2	260.3	273.6	291.3	296.5	306.8
52.5°	190.3	192.5	200.6	207.2	218.3	227.2	237.5	250.0	264.8	272.9	281.0
55°	174.1	175.5	179.2	186.6	194.0	205.0	214.6	226.4	239.0	247.8	255.2
57.5°	155.6	158.6	161.5	165.9	173.3	183.6	194.0	205.0	215.4	221.3	230.8
60°	134.2	138.7	143.8	149.0	154.1	161.5	173.3	183.6	193.2	198.4	205.8
62.5°	111.4	120.2	124.6	130.5	135.0	141.6	150.5	162.3	168.9	175.5	181.4
65°	100.3	101.0	101.8	107.7	115.8	122.4	130.5	139.4	149.7	154.1	158.6
67.5°	89.2	90.0	91.5	92.2	95.1	102.5	111.4	121.0	129.1	132.0	136.4
70°	78.2	78.2	81.1	81.9	82.6	83.3	90.7	100.3	107.7	111.4	116.5
72.5°	66.4	67.1	68.6	69.3	70.8	72.3	74.5	79.7	88.5	92.2	98.1
75°	54.6	55.3	56.1	56.8	59.0	59.7	62.0	64.9	68.6	73.0	76.7
77.5°	43.5	43.5	44.3	45.7	47.2	47.9	50.2	51.6	53.1	55.3	58.3
80°	32.5	33.2	33.2	34.7	34.7	35.4	36.1	38.4	39.8	41.3	42.8
82.5°	22.1	23.6	23.6	23.6	24.3	25.1	25.8	25.8	27.3	28.0	30.2
85°	13.3	14.0	14.0	14.0	13.3	14.8	14.8	15.5	15.5	15.5	16.2
87.5°	5.2	4.4	5.2	5.2	5.2	5.9	5.2	5.2	5.9	6.6	6.6
90°	25.2	25.5	25.8	26.2	26.5	22.8	19.1	15.4	11.7	9.8	8.8
92.5°	24.1	24.0	23.8	23.7	23.5	23.3	23.1	23.0	22.8	22.7	22.0
95°	48.4	48.4	48.4	48.4	48.4	48.1	47.7	47.4	47.1	46.9	46.1
97.5°	75.7	75.7	75.7	75.7	75.7	75.0	74.4	73.7	73.0	72.7	71.9
100°	104.4	104.4	104.4	104.4	104.4	103.9	103.4	102.9	102.4	102.2	101.5
102.5°	136.1	136.0	135.8	135.7	135.5	134.8	134.1	133.4	132.7	132.4	131.9
105°	167.8	167.5	167.2	166.8	166.5	166.2	165.8	165.5	165.2	165.0	164.7
107.5°	201.2	201.1	200.9	200.8	200.6	200.6	200.6	200.6	200.6	200.6	200.3
110°	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	234.9

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	268.9	269.4	269.9	270.4	270.9	271.1	271.3	271.4	271.6	271.7	271.2
115°	305.1	305.3	305.4	305.6	305.8	306.1	306.5	306.8	307.1	307.3	306.8
117.5°	338.6	339.1	339.6	340.1	340.6	341.4	342.3	343.1	344.0	344.4	343.7
120°	373.9	373.9	373.9	373.9	373.9	375.2	376.6	377.9	379.2	379.9	379.2
122.5°	408.2	408.7	409.2	409.7	410.2	411.0	411.9	412.7	413.6	414.0	413.2
125°	443.0	443.5	444.0	444.5	445.0	445.5	446.0	446.5	447.0	447.3	446.5
127.5°	476.4	477.1	477.8	478.4	479.1	479.8	480.4	481.1	481.8	482.1	481.2
130°	511.8	512.1	512.4	512.8	513.1	513.5	513.8	514.2	514.5	514.7	513.6
132.5°	544.6	545.5	546.3	547.2	548.0	547.8	547.6	547.5	547.3	547.2	546.4
135°	579.1	579.2	579.4	579.5	579.7	579.4	579.0	578.7	578.4	578.2	577.3
137.5°	610.9	611.0	611.2	611.3	611.5	611.2	610.8	610.5	610.2	610.0	609.2
140°	643.3	643.3	643.3	643.3	643.3	642.5	641.6	640.8	639.9	639.5	638.7
142.5°	672.7	672.6	672.4	672.3	672.1	671.6	671.1	670.6	670.1	669.8	669.0
145°	702.3	702.1	702.0	701.8	701.6	700.6	699.6	698.6	697.6	697.1	696.5
147.5°	728.6	728.3	728.0	727.6	727.3	726.6	726.0	725.3	724.6	724.3	723.5
150°	753.5	753.0	752.5	752.0	751.5	750.8	750.2	749.5	748.8	748.5	748.0
152.5°	778.5	777.8	777.1	776.5	775.8	775.0	774.1	773.3	772.4	772.0	771.5
155°	798.8	797.9	797.1	796.2	795.4	794.9	794.4	793.9	793.4	793.2	792.9
157.5°	819.1	817.9	816.8	815.6	814.4	814.0	813.7	813.3	813.0	812.8	812.6
160°	835.8	834.8	833.8	832.8	831.8	831.6	831.4	831.3	831.1	831.0	830.8
162.5°	851.6	850.4	849.3	848.1	846.9	846.7	846.6	846.4	846.3	846.2	846.2
165°	864.5	863.3	862.2	861.0	859.8	859.8	859.8	859.8	859.8	859.8	859.9
167.5°	875.8	874.6	873.5	872.3	871.1	871.1	871.1	871.1	871.1	871.1	871.4
170°	884.9	883.7	882.6	881.4	880.2	880.4	880.6	880.7	880.9	881.0	881.2
172.5°	891.7	890.5	889.4	888.2	887.0	887.2	887.4	887.5	887.7	887.8	888.0
175°	896.3	895.1	894.0	892.8	891.6	891.9	892.3	892.6	892.9	893.1	893.3
177.5°	898.6	897.6	896.6	895.6	894.6	894.9	895.3	895.6	895.9	896.1	896.4
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1061.3	1061.3	1061.3	1061.3
2.5°	1042.1	1039.9	1053.2	1067.9
5°	1020.7	1024.4	1041.4	1062.0
7.5°	998.6	1006.7	1026.6	1053.9
10°	967.6	982.4	1012.6	1040.6
12.5°	937.4	957.3	986.0	1019.2
15°	903.4	925.6	961.0	1000.8
17.5°	865.8	890.9	932.2	975.7
20°	826.0	859.2	902.7	949.9
22.5°	781.8	821.6	866.6	918.9
25°	739.0	782.5	827.5	888.0
27.5°	696.9	739.7	789.9	851.1
30°	654.9	694.0	747.8	813.5
32.5°	609.9	650.5	707.3	774.4
35°	568.6	609.2	662.3	728.7
37.5°	524.4	567.9	618.8	687.4
40°	472.7	523.6	573.0	638.7
42.5°	430.0	483.8	531.7	593.7
45°	396.0	446.9	486.8	547.2
47.5°	364.3	405.6	446.2	502.2
50°	334.1	365.8	407.8	458.0
52.5°	303.1	330.4	366.5	413.7
55°	275.1	300.9	333.4	369.5
57.5°	249.3	267.7	300.2	332.6
60°	220.5	239.7	264.8	292.1
62.5°	196.2	210.9	234.5	257.4
65°	170.4	184.4	202.1	223.5
67.5°	146.8	159.3	173.3	190.3
70°	125.4	135.0	145.3	160.0
72.5°	102.5	112.8	122.4	134.2
75°	84.1	88.5	96.6	104.7
77.5°	64.9	70.8	75.2	81.9
80°	46.5	51.6	53.1	58.3
82.5°	31.0	33.9	36.9	38.4
85°	17.7	19.2	22.1	22.9
87.5°	6.6	7.4	8.9	10.3
90°	6.8	4.8	2.8	0.8
92.5°	20.7	19.4	18.0	16.7
95°	44.4	42.7	41.1	39.4
97.5°	70.4	68.9	67.3	65.8
100°	100.2	98.8	97.5	96.1
102.5°	130.9	129.9	128.9	127.9
105°	164.2	163.7	163.2	162.7
107.5°	199.6	198.9	198.2	197.5
110°	233.9	232.8	231.8	230.8

TEST NUMBER: P999784

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	270.2	269.2	268.2	267.2
115°	305.8	304.7	303.7	302.7
117.5°	342.4	341.0	339.7	338.3
120°	377.9	376.6	375.2	373.9
122.5°	411.5	409.8	408.1	406.4
125°	445.0	443.5	442.0	440.5
127.5°	479.3	477.5	475.6	473.8
130°	511.4	509.2	507.0	504.8
132.5°	544.7	543.0	541.3	539.6
135°	575.4	573.6	571.7	569.9
137.5°	607.7	606.2	604.7	603.2
140°	637.2	635.7	634.2	632.7
142.5°	667.5	666.0	664.5	663.0
145°	695.3	694.2	693.0	691.8
147.5°	722.0	720.5	719.0	717.5
150°	747.0	746.0	745.0	744.0
152.5°	770.5	769.4	768.4	767.4
155°	792.4	791.9	791.4	790.9
157.5°	812.3	812.0	811.6	811.3
160°	830.5	830.2	829.8	829.5
162.5°	846.2	846.2	846.2	846.2
165°	860.0	860.2	860.3	860.5
167.5°	871.9	872.4	872.9	873.4
170°	881.7	882.2	882.7	883.2
172.5°	888.5	889.0	889.5	890.0
175°	893.8	894.3	894.8	895.3
177.5°	896.9	897.4	897.9	898.4
180°	896.9	896.9	896.9	896.9

(END OF REPORT)