

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998791

Luminaire Tested: SA2XXDIP-B675D330UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998791
REPORT IS A COMBINATION OF REPORTS P984537 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D330UB50-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3851.4 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998791

CATALOG NUMBER: SA2XXDIP-B675D330UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P998791

CATALOG NUMBER: SA2XXDIP-B675D330UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	61
2	93	85	79	73	87	80	75	70	72	67	64	64	60	57	56	54	52
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	47	44
4	77	66	58	52	73	63	56	50	56	50	46	50	46	42	45	41	38
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	25	32	26	23	28	24	21
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16246	16246	16246
5°	16272	15485	15375
10°	16139	14779	14486
15°	15903	14068	13550
20°	15583	13295	12665
25°	15265	12487	11780
30°	14865	11728	10853
35°	14487	10926	9941
40°	14020	10138	9078
45°	13556	9353	8234
50°	13050	8556	7357
55°	12516	7703	6527
60°	11916	6780	5664
65°	11262	5842	4757
70°	10428	4815	3841
75°	9275	3712	2965
80°	7880	2522	1909
85°	5721	1174	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13556 cd/sqm

TEST NUMBER: P998791

CATALOG NUMBER: SA2XXDIP-B675D330UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	2.5
10°-20°	271.8	7.1
20°-30°	399.4	10.4
30°-40°	463.9	12.0
40°-50°	463.3	12.0
50°-60°	404.0	10.5
60°-70°	298.6	7.8
70°-80°	169.0	4.4
80°-90°	45.7	1.2
90°-100°	72.1	1.9
100°-110°	243.6	6.3
110°-120°	256.1	6.6
120°-130°	210.5	5.5
130°-140°	169.2	4.4
140°-150°	127.8	3.3
150°-160°	89.9	2.3
160°-170°	52.9	1.4
170°-180°	17.2	0.4
0°-30°	767.7	19.9
0°-40°	1231.6	32.0
0°-60°	2098.9	54.5
0°-90°	2612.2	67.8
90°-120°	571.7	14.8
90°-150°	1079.3	28.0
90°-180°	1239.0	32.2
0°-180°	3851.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1026	1022	1012	1019	1017	97
15°	977	971	958	962	957	275
25°	884	876	860	862	860	407
35°	763	753	737	731	726	476
45°	621	614	599	588	584	479
55°	470	464	452	440	435	420
65°	317	311	301	292	287	313
75°	166	164	159	153	155	177
85°	40	40	38	36	34	45
90°	0	5	12	11	11	3
95°	12	29	134	51	39	12
105°	42	63	253	453	385	44
115°	74	93	212	437	507	73
125°	102	121	204	354	411	91
135°	120	144	201	298	341	93
145°	137	158	200	249	272	86
155°	156	169	194	220	229	72
165°	170	175	186	198	201	48
175°	177	178	179	181	181	17
180°	178	178	178	178	178	

TEST NUMBER: P998791

CATALOG NUMBER: SA2XXDIP-B675D330UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1032.2	1027.3	1016.4	1026.3	1024.3
5°	1026.3	1022.3	1011.5	1019.4	1017.4
7.5°	1019.4	1013.4	1002.6	1010.5	1008.5
10°	1008.5	1001.6	989.8	997.7	994.7
12.5°	993.7	987.8	975.9	980.9	978.9
15°	976.9	971.0	958.2	962.1	957.2
17.5°	956.2	950.3	937.5	942.4	937.5
20°	933.5	927.6	913.8	916.7	912.8
22.5°	910.8	901.9	889.1	889.1	887.1
25°	884.2	876.3	859.5	861.5	859.5
27.5°	854.6	847.7	834.8	831.9	826.9
30°	825.0	817.1	802.3	799.3	795.4
32.5°	793.4	787.5	771.7	765.8	761.8
35°	762.8	752.9	737.1	731.2	726.3
37.5°	728.3	719.4	703.6	696.7	691.7
40°	692.7	684.8	669.1	660.2	656.2
42.5°	658.2	650.3	634.5	624.6	618.7
45°	620.7	613.8	599.0	588.1	584.2
47.5°	584.2	577.3	561.5	550.6	544.7
50°	545.7	540.8	527.0	513.1	508.2
52.5°	508.2	501.3	488.5	477.6	470.7
55°	469.7	463.8	452.0	440.1	435.2
57.5°	431.2	426.3	413.5	401.6	397.7
60°	392.7	388.8	375.0	364.1	361.2
62.5°	355.2	348.3	338.5	328.6	324.7
65°	316.8	310.8	301.0	292.1	287.2
67.5°	277.3	272.4	263.5	256.6	252.6
70°	240.8	236.8	228.0	221.0	217.1
72.5°	203.3	199.3	194.4	187.5	184.5
75°	165.8	163.8	158.9	153.0	154.9
77.5°	132.2	128.3	126.3	123.3	120.4
80°	98.7	97.7	95.7	92.8	90.8
82.5°	67.1	67.1	66.1	62.2	62.2
85°	40.5	39.5	38.5	35.5	34.5
87.5°	17.8	15.8	13.8	10.9	9.9
90°	0.3	4.6	11.6	11.1	11.3
92.5°	5.1	16.2	52.6	24.2	20.9
95°	12.0	29.4	134.0	50.6	39.0
97.5°	17.8	38.8	218.4	101.6	65.3
100°	26.3	47.5	270.0	202.2	122.4
102.5°	34.2	55.4	271.8	341.8	238.6
105°	41.7	62.9	253.3	452.8	385.2
107.5°	49.9	70.4	236.2	493.0	484.0
110°	58.1	78.2	224.6	486.4	524.4



TEST NUMBER: P998791

CATALOG NUMBER: SA2XXDIP-B675D330UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.6	85.4	217.1	464.4	523.7
115°	73.5	92.8	211.9	437.4	506.9
117.5°	81.7	100.2	209.2	411.6	481.6
120°	89.2	107.3	206.8	388.4	457.4
122.5°	96.4	114.6	205.4	370.5	432.1
125°	102.5	121.4	203.7	354.3	411.2
127.5°	107.7	127.6	202.7	340.4	391.7
130°	112.1	133.3	202.0	326.4	375.7
132.5°	116.2	138.8	201.7	311.9	358.9
135°	120.3	143.6	201.3	297.8	340.8
137.5°	124.1	147.6	201.3	283.4	323.4
140°	128.5	151.4	201.0	270.7	305.3
142.5°	133.0	154.5	201.0	258.6	287.1
145°	137.4	158.0	200.3	248.6	272.1
147.5°	142.2	160.6	199.3	240.0	258.8
150°	147.0	163.4	198.3	232.4	247.1
152.5°	151.8	166.2	196.6	226.2	237.2
155°	156.2	168.7	194.5	220.0	228.7
157.5°	160.0	170.8	192.4	214.2	221.2
160°	163.7	172.8	190.4	208.3	214.0
162.5°	167.5	174.4	188.7	202.8	207.1
165°	170.2	175.4	186.3	197.6	200.7
167.5°	172.6	176.4	184.2	192.8	194.5
170°	175.0	176.9	182.5	188.4	189.0
172.5°	176.4	177.4	180.5	184.4	184.6
175°	177.4	177.6	179.1	181.4	180.8
177.5°	178.1	177.8	177.8	179.1	178.1
180°	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998791

CATALOG NUMBER: SA2XXDIP-B675D330UB50-4F0-XX-W2A-F4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.42	17.47	17.21	18.28	19.27	17.20	18.25	17.99	19.06	20.05
	3H	17.77	18.72	18.57	19.54	20.56	18.84	19.79	19.64	20.61	21.63
	4H	18.19	19.08	19.01	19.90	20.94	19.44	20.33	20.26	21.16	22.19
	6H	18.42	19.24	19.25	20.07	21.12	19.86	20.68	20.69	21.51	22.56
	8H	18.45	19.23	19.29	20.09	21.13	19.97	20.75	20.81	21.61	22.65
	12H	18.45	19.19	19.29	20.04	21.12	20.02	20.77	20.87	21.62	22.69
4H	2H	16.91	17.80	17.74	18.63	19.66	17.56	18.45	18.38	19.27	20.31
	3H	18.45	19.19	19.28	20.05	21.10	19.35	20.10	20.19	20.96	22.01
	4H	18.96	19.64	19.81	20.50	21.57	20.04	20.72	20.89	21.58	22.65
	6H	19.27	19.86	20.14	20.74	21.82	20.55	21.13	21.41	22.02	23.10
	8H	19.34	19.88	20.20	20.76	21.85	20.70	21.24	21.56	22.12	23.21
	12H	19.35	19.84	20.23	20.74	21.83	20.77	21.26	21.65	22.16	23.26
8H	4H	19.15	19.70	20.02	20.58	21.67	20.14	20.69	21.01	21.57	22.66
	6H	19.54	20.00	20.44	20.92	22.01	20.72	21.17	21.61	22.09	23.19
	8H	19.65	20.05	20.55	20.96	22.07	20.91	21.31	21.82	22.23	23.34
	12H	19.69	20.04	20.60	20.95	22.11	21.02	21.37	21.93	22.28	23.44
12H	4H	19.14	19.64	20.03	20.53	21.63	20.12	20.61	21.00	21.51	22.60
	6H	19.56	19.97	20.47	20.88	21.99	20.71	21.12	21.62	22.03	23.14
	8H	19.68	20.04	20.59	20.94	22.11	20.92	21.27	21.83	22.18	23.34