

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999787

Luminaire Tested: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999787
REPORT IS A COMBINATION OF REPORTS P988342 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4186.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999787

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999787

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	34	32	30
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	18	16
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12899	12899	12899
5°	12920	12273	12182
10°	12793	11639	11256
15°	12618	10892	10200
20°	12385	10043	9096
25°	12147	9172	8087
30°	11827	8322	6983
35°	11513	7466	6036
40°	11194	6626	5061
45°	10824	5757	4210
50°	10441	4921	3427
55°	10043	4085	2721
60°	9577	3267	2059
65°	9044	2490	1673
70°	8402	1806	1330
75°	7591	1378	1016
80°	6419	933	681
85°	4478	427	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10824 cd/sqm

TEST NUMBER: P999787

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	1.8
10°-20°	209.7	5.0
20°-30°	294.4	7.0
30°-40°	320.9	7.7
40°-50°	294.9	7.0
50°-60°	231.6	5.5
60°-70°	150.7	3.6
70°-80°	77.6	1.9
80°-90°	22.4	0.5
90°-100°	55.5	1.3
100°-110°	176.4	4.2
110°-120°	301.8	7.2
120°-130°	396.9	9.5
130°-140°	445.5	10.6
140°-150°	436.9	10.4
150°-160°	366.5	8.8
160°-170°	243.1	5.8
170°-180°	84.9	2.0
0°-30°	580.4	13.9
0°-40°	901.3	21.5
0°-60°	1427.8	34.1
0°-90°	1678.5	40.1
90°-120°	533.6	12.7
90°-150°	1813.0	43.3
90°-180°	2507.0	59.9
0°-180°	4186.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	815	815	815	815	815	
5°	815	811	802	808	806	77
15°	775	767	742	728	720	218
25°	704	680	631	601	590	324
35°	606	569	504	457	441	379
45°	496	446	369	316	299	383
55°	377	319	240	195	181	337
65°	254	195	128	103	101	252
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	1	10	26	25	26	4
95°	39	47	48	48	47	44
105°	163	165	166	168	168	172
115°	303	307	306	305	303	300
125°	440	447	445	443	442	394
135°	570	578	580	579	577	440
145°	692	697	702	702	699	432
155°	791	793	795	799	797	364
165°	860	860	860	865	861	243
175°	895	893	892	897	892	85
180°	897	897	897	897	897	

TEST NUMBER: P999787

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	814.9	814.9	814.9	814.9	814.9
2.5°	818.6	814.9	806.8	814.2	812.7
5°	814.9	811.2	801.7	808.3	806.1
7.5°	808.3	803.9	793.5	796.5	792.8
10°	799.4	794.3	779.5	777.3	772.9
12.5°	788.4	781.7	761.8	757.4	749.3
15°	775.1	767.0	741.9	727.9	720.5
17.5°	759.6	747.8	716.8	700.6	688.8
20°	741.9	727.2	690.3	671.9	655.6
22.5°	722.7	705.8	663.0	637.9	626.9
25°	703.6	680.0	631.3	601.1	590.0
27.5°	680.7	655.6	601.8	567.1	550.2
30°	656.4	628.3	569.3	531.7	511.8
32.5°	632.8	598.8	538.4	494.1	475.7
35°	606.2	568.6	503.7	457.2	441.0
37.5°	580.4	539.8	471.3	420.4	401.9
40°	553.1	508.9	437.3	385.0	365.8
42.5°	525.1	477.9	403.4	348.8	330.4
45°	495.6	446.2	368.7	316.4	298.7
47.5°	467.6	415.2	335.6	283.2	267.0
50°	436.6	384.2	303.1	252.2	236.7
52.5°	406.4	351.0	272.1	223.5	209.4
55°	376.9	319.3	239.7	195.4	181.4
57.5°	346.6	287.6	210.9	169.6	157.8
60°	315.6	256.6	180.7	143.1	131.3
62.5°	285.4	226.4	154.9	119.5	113.6
65°	254.4	194.7	128.3	103.2	101.0
67.5°	224.9	165.2	103.2	90.7	88.5
70°	194.0	136.4	85.5	78.2	75.2
72.5°	164.5	109.9	71.5	65.6	64.2
75°	135.7	84.1	59.0	53.8	53.1
77.5°	106.9	59.7	46.5	43.5	42.0
80°	80.4	42.8	35.4	32.4	32.4
82.5°	56.0	28.8	24.3	22.9	22.9
85°	31.7	16.2	14.0	14.0	14.0
87.5°	11.8	5.9	5.9	5.2	5.2
90°	0.8	9.8	26.5	25.0	25.7
92.5°	16.7	22.7	23.5	24.2	24.2
95°	39.4	46.9	48.4	48.4	46.9
97.5°	65.8	72.7	75.7	75.7	75.7
100°	96.1	102.2	104.4	104.4	103.7
102.5°	127.9	132.4	135.5	136.2	135.5
105°	162.7	165.0	166.5	168.0	168.0
107.5°	197.5	200.6	200.6	201.3	197.5
110°	230.8	235.4	235.4	235.4	233.1

TEST NUMBER: P999787

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.2	271.7	270.9	268.7	267.2
115°	302.7	307.3	305.8	305.0	302.7
117.5°	338.3	344.4	340.6	338.3	336.0
120°	373.9	379.9	373.9	373.9	371.6
122.5°	406.4	414.0	410.2	407.9	406.4
125°	440.5	447.3	445.0	442.8	442.0
127.5°	473.8	482.1	479.1	476.1	473.8
130°	504.8	514.7	513.1	511.6	508.6
132.5°	539.6	547.2	548.0	544.2	541.9
135°	569.9	578.2	579.7	579.0	576.7
137.5°	603.2	610.0	611.5	610.8	607.7
140°	632.7	639.5	643.3	643.3	640.3
142.5°	663.0	669.8	672.1	672.8	669.8
145°	691.8	697.1	701.6	702.4	699.3
147.5°	717.5	724.3	727.3	728.8	725.8
150°	744.0	748.5	751.5	753.8	751.5
152.5°	767.4	772.0	775.8	778.8	775.8
155°	790.9	793.2	795.4	799.2	797.0
157.5°	811.3	812.8	814.4	819.7	815.9
160°	829.5	831.0	831.8	836.3	833.3
162.5°	846.2	846.2	846.9	852.2	848.4
165°	860.5	859.8	859.8	865.1	861.3
167.5°	873.4	871.1	871.1	876.4	872.6
170°	883.2	881.0	880.2	885.5	881.0
172.5°	890.0	887.8	887.0	892.3	887.8
175°	895.3	893.1	891.6	896.9	892.3
177.5°	898.4	896.1	894.6	899.1	894.6
180°	896.9	896.9	896.9	896.9	896.9

(END OF REPORT)