

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999788

Luminaire Tested: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999788
REPORT IS A COMBINATION OF REPORTS P988343 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4422.1 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999788

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999788

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	88	84	87	83	80	77	68	65	64	53	52	51	40	39	39
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	43	61	51	45	40	42	37	34	34	30	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	20
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12899	12899	12899
5°	12920	12273	12182
10°	12793	11639	11256
15°	12618	10892	10200
20°	12385	10043	9096
25°	12147	9172	8087
30°	11827	8322	6983
35°	11513	7466	6036
40°	11194	6626	5061
45°	10824	5757	4210
50°	10441	4921	3427
55°	10043	4085	2721
60°	9577	3267	2059
65°	9044	2490	1673
70°	8402	1806	1330
75°	7591	1378	1016
80°	6419	933	681
85°	4478	427	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10824 cd/sqm

TEST NUMBER: P999788

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	1.7
10°-20°	209.7	4.7
20°-30°	294.4	6.7
30°-40°	320.9	7.3
40°-50°	294.9	6.7
50°-60°	231.6	5.2
60°-70°	150.7	3.4
70°-80°	77.6	1.8
80°-90°	22.3	0.5
90°-100°	159.5	3.6
100°-110°	539.3	12.2
110°-120°	566.9	12.8
120°-130°	466.2	10.5
130°-140°	374.6	8.5
140°-150°	283.0	6.4
150°-160°	198.9	4.5
160°-170°	117.1	2.6
170°-180°	38.1	0.9
0°-30°	580.4	13.1
0°-40°	901.3	20.4
0°-60°	1427.8	32.3
0°-90°	1678.5	38.0
90°-120°	1265.7	28.6
90°-150°	2389.4	54.0
90°-180°	2744.0	62.1
0°-180°	4422.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	815	815	815	815	815	
5°	815	811	802	808	806	77
15°	775	767	742	728	720	218
25°	704	680	631	601	590	324
35°	606	569	504	457	441	379
45°	496	446	369	316	299	383
55°	377	319	240	195	181	337
65°	254	195	128	103	101	252
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	1	10	26	25	25	3
95°	26	65	297	112	86	27
105°	92	139	561	1002	853	98
115°	163	205	469	968	1122	161
125°	227	269	451	784	910	202
135°	266	318	446	659	754	206
145°	304	350	444	551	602	191
155°	346	374	431	487	506	159
165°	377	388	412	437	444	106
175°	393	393	396	402	400	37
180°	394	394	394	394	394	

TEST NUMBER: P999788

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	814.9	814.9	814.9	814.9	814.9
2.5°	818.6	814.9	806.8	814.2	812.7
5°	814.9	811.2	801.7	808.3	806.1
7.5°	808.3	803.9	793.5	796.5	792.8
10°	799.4	794.3	779.5	777.3	772.9
12.5°	788.4	781.7	761.8	757.4	749.3
15°	775.1	767.0	741.9	727.9	720.5
17.5°	759.6	747.8	716.8	700.6	688.8
20°	741.9	727.2	690.3	671.9	655.6
22.5°	722.7	705.8	663.0	637.9	626.9
25°	703.6	680.0	631.3	601.1	590.0
27.5°	680.7	655.6	601.8	567.1	550.2
30°	656.4	628.3	569.3	531.7	511.8
32.5°	632.8	598.8	538.4	494.1	475.7
35°	606.2	568.6	503.7	457.2	441.0
37.5°	580.4	539.8	471.3	420.4	401.9
40°	553.1	508.9	437.3	385.0	365.8
42.5°	525.1	477.9	403.4	348.8	330.4
45°	495.6	446.2	368.7	316.4	298.7
47.5°	467.6	415.2	335.6	283.2	267.0
50°	436.6	384.2	303.1	252.2	236.7
52.5°	406.4	351.0	272.1	223.5	209.4
55°	376.9	319.3	239.7	195.4	181.4
57.5°	346.6	287.6	210.9	169.6	157.8
60°	315.6	256.6	180.7	143.1	131.3
62.5°	285.4	226.4	154.9	119.5	113.6
65°	254.4	194.7	128.3	103.2	101.0
67.5°	224.9	165.2	103.2	90.7	88.5
70°	194.0	136.4	85.5	78.2	75.2
72.5°	164.5	109.9	71.5	65.6	64.2
75°	135.7	84.1	59.0	53.8	53.1
77.5°	106.9	59.7	46.5	43.5	42.0
80°	80.4	42.8	35.4	32.4	32.4
82.5°	56.0	28.8	24.3	22.9	22.9
85°	31.7	16.2	14.0	14.0	14.0
87.5°	11.8	5.9	5.9	5.2	5.2
90°	0.8	10.2	25.7	24.6	25.0
92.5°	11.4	36.0	116.5	53.8	46.2
95°	26.5	65.1	296.7	112.0	86.3
97.5°	39.4	85.9	483.6	224.8	144.5
100°	58.3	105.2	597.8	447.6	270.9
102.5°	75.7	122.6	601.6	756.8	528.2
105°	92.3	139.2	560.8	1002.3	852.9
107.5°	110.5	155.9	522.9	1091.2	1071.6
110°	128.7	172.9	497.2	1076.9	1160.9

TEST NUMBER: P999788

CATALOG NUMBER: SA2XXRDIP-B485D725UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	145.3	189.2	480.5	1028.1	1159.4
115°	162.7	205.4	469.2	968.3	1122.3
117.5°	180.9	221.7	463.1	911.2	1066.3
120°	197.5	237.6	457.8	860.0	1012.6
122.5°	213.4	253.9	454.8	820.4	956.6
125°	227.0	268.6	451.0	784.4	910.4
127.5°	238.4	282.6	448.8	753.8	867.3
130°	248.2	295.1	447.2	722.7	831.7
132.5°	257.3	307.2	446.5	690.6	794.6
135°	266.4	317.8	445.7	659.2	754.5
137.5°	274.7	327.0	445.7	627.3	715.9
140°	284.5	335.2	445.0	599.4	675.8
142.5°	294.4	342.0	445.0	572.4	635.7
145°	304.2	349.6	443.5	550.6	602.4
147.5°	314.8	355.6	441.2	531.2	572.9
150°	325.4	361.7	438.9	514.6	547.1
152.5°	336.0	367.8	435.1	500.6	525.2
155°	345.8	373.5	430.6	487.0	506.3
157.5°	354.2	378.0	426.1	474.1	489.6
160°	362.5	382.5	421.5	461.2	473.7
162.5°	370.8	386.0	417.7	449.1	458.6
165°	376.9	388.2	412.4	437.4	444.2
167.5°	382.2	390.5	407.9	426.8	430.6
170°	387.5	391.6	404.1	417.0	418.5
172.5°	390.5	392.8	399.6	408.3	408.7
175°	392.8	393.2	396.5	401.5	400.3
177.5°	394.3	393.5	393.5	396.5	394.3
180°	393.5	393.5	393.5	393.5	393.5

(END OF REPORT)