

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999816

Luminaire Tested: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999816
REPORT IS A COMBINATION OF REPORTS P988371 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4436.1 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999816

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999816

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	88	84	87	83	80	77	68	65	64	53	52	51	40	39	39
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	43	61	51	45	39	42	37	34	34	30	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	20
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12939	12939	12939
5°	12960	12308	12218
10°	12831	11675	11289
15°	12655	10925	10231
20°	12421	10072	9124
25°	12184	9199	8111
30°	11861	8347	7004
35°	11547	7489	6054
40°	11229	6645	5076
45°	10857	5774	4223
50°	10472	4936	3437
55°	10072	4097	2730
60°	9607	3276	2065
65°	9072	2498	1678
70°	8423	1812	1334
75°	7613	1383	1020
80°	6435	936	683
85°	4492	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10857 cd/sqm

TEST NUMBER: P999816

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.6	1.7
10°-20°	210.3	4.7
20°-30°	295.2	6.7
30°-40°	321.8	7.3
40°-50°	295.8	6.7
50°-60°	232.3	5.2
60°-70°	151.2	3.4
70°-80°	77.8	1.8
80°-90°	22.4	0.5
90°-100°	160.1	3.6
100°-110°	541.1	12.2
110°-120°	568.7	12.8
120°-130°	467.7	10.5
130°-140°	375.8	8.5
140°-150°	283.9	6.4
150°-160°	199.6	4.5
160°-170°	117.5	2.6
170°-180°	38.2	0.9
0°-30°	582.1	13.1
0°-40°	904.0	20.4
0°-60°	1432.1	32.3
0°-90°	1683.5	38.0
90°-120°	1269.9	28.6
90°-150°	2397.3	54.0
90°-180°	2753.0	62.1
0°-180°	4436.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	817	817	817	817	817	
5°	817	814	804	811	808	78
15°	777	769	744	730	723	219
25°	706	682	633	603	592	325
35°	608	570	505	459	442	381
45°	497	448	370	317	300	384
55°	378	320	240	196	182	338
65°	255	195	129	104	101	253
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	1	10	26	25	25	3
95°	27	65	298	112	87	27
105°	93	140	563	1006	856	98
115°	163	206	471	972	1126	162
125°	228	270	452	787	913	202
135°	267	319	447	661	757	206
145°	305	351	445	552	604	191
155°	347	375	432	489	508	160
165°	378	390	414	439	446	107
175°	394	394	398	403	402	37
180°	395	395	395	395	395	

TEST NUMBER: P999816

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	817.4	817.4	817.4	817.4	817.4
2.5°	821.1	817.4	809.2	816.6	815.1
5°	817.4	813.7	804.0	810.7	808.5
7.5°	810.7	806.3	795.9	798.9	795.2
10°	801.8	796.6	781.9	779.6	775.2
12.5°	790.7	784.1	764.1	759.7	751.5
15°	777.4	769.3	744.1	730.1	722.7
17.5°	761.9	750.0	719.0	702.7	690.9
20°	744.1	729.3	692.3	673.9	657.6
22.5°	724.9	707.9	665.0	639.8	628.7
25°	705.7	682.0	633.2	602.8	591.8
27.5°	682.7	657.6	603.6	568.8	551.8
30°	658.3	630.2	571.0	533.3	513.3
32.5°	634.7	600.6	540.0	495.6	477.1
35°	608.0	570.3	505.2	458.6	442.3
37.5°	582.1	541.5	472.7	421.6	403.1
40°	554.8	510.4	438.6	386.1	366.9
42.5°	526.7	479.3	404.6	349.9	331.4
45°	497.1	447.5	369.8	317.3	299.6
47.5°	469.0	416.4	336.6	284.0	267.8
50°	437.9	385.4	304.0	253.0	237.4
52.5°	407.6	352.1	272.9	224.1	210.1
55°	378.0	320.3	240.4	196.0	182.0
57.5°	347.7	288.5	211.6	170.1	158.3
60°	316.6	257.4	181.2	143.5	131.7
62.5°	286.3	227.1	155.3	119.8	113.9
65°	255.2	195.3	128.7	103.6	101.3
67.5°	225.6	165.7	103.6	91.0	88.8
70°	194.5	136.8	85.8	78.4	75.4
72.5°	165.0	110.2	71.7	65.8	64.4
75°	136.1	84.3	59.2	54.0	53.3
77.5°	107.3	59.9	46.6	43.6	42.2
80°	80.6	42.9	35.5	32.5	32.5
82.5°	56.2	28.8	24.4	22.9	22.9
85°	31.8	16.3	14.1	14.1	14.1
87.5°	11.8	5.9	5.9	5.2	5.2
90°	0.8	10.2	25.8	24.7	25.1
92.5°	11.4	36.0	116.9	53.9	46.3
95°	26.6	65.3	297.6	112.4	86.6
97.5°	39.5	86.2	485.2	225.5	145.0
100°	58.5	105.6	599.8	449.1	271.8
102.5°	75.9	123.0	603.6	759.2	530.0
105°	92.6	139.7	562.6	1005.6	855.7
107.5°	110.9	156.4	524.6	1094.8	1075.1
110°	129.1	173.5	498.8	1080.4	1164.7

TEST NUMBER: P999816

CATALOG NUMBER: SA2XXRDIP-B485D725UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	145.8	189.8	482.1	1031.4	1163.2
115°	163.2	206.2	470.7	971.5	1126.0
117.5°	181.5	222.4	464.7	914.1	1069.8
120°	198.2	238.4	459.3	862.8	1015.9
122.5°	214.1	254.7	456.3	823.0	959.7
125°	227.8	269.5	452.5	787.0	913.4
127.5°	239.2	283.6	450.2	756.2	870.1
130°	249.0	296.1	448.7	725.0	834.4
132.5°	258.1	308.2	448.0	692.8	797.2
135°	267.3	318.9	447.2	661.3	757.0
137.5°	275.6	328.0	447.2	629.4	718.2
140°	285.5	336.4	446.4	601.3	678.0
142.5°	295.3	343.2	446.4	574.4	637.8
145°	305.2	350.8	444.9	552.3	604.4
147.5°	315.8	356.8	442.6	533.0	574.8
150°	326.5	363.0	440.4	516.3	548.9
152.5°	337.1	369.0	436.6	502.2	526.9
155°	347.0	374.7	432.0	488.6	507.9
157.5°	355.3	379.2	427.5	475.7	491.2
160°	363.7	383.8	422.9	462.8	475.3
162.5°	372.0	387.2	419.1	450.6	460.1
165°	378.1	389.5	413.8	438.8	445.7
167.5°	383.4	391.8	409.2	428.2	432.0
170°	388.7	393.0	405.4	418.4	419.9
172.5°	391.8	394.0	400.9	409.6	410.0
175°	394.1	394.5	397.8	402.8	401.6
177.5°	395.6	394.8	394.8	397.8	395.6
180°	394.8	394.8	394.8	394.8	394.8

(END OF REPORT)