

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998844

Luminaire Tested: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998844
REPORT IS A COMBINATION OF REPORTS P984590 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4654.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	97	93	90	94	91	87	84	79	77	75	69	67	66	59	58	57
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49
3	85	75	68	62	79	71	65	59	62	58	54	55	51	48	47	45	42
4	78	67	59	53	73	63	56	51	56	51	46	49	45	42	43	40	37
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33
6	66	54	46	41	62	51	44	39	46	40	36	40	36	32	36	32	29
7	61	49	41	36	57	47	40	34	42	36	32	37	32	29	33	29	26
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	26	24
9	53	41	34	29	50	39	32	28	35	30	26	31	27	24	28	24	21
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20318	20318	20318	20318
5°	20367	21665	20445	17235
10°	20130	23650	20257	14211
15°	19642	24945	19915	11969
20°	19336	23422	19336	10403
25°	18720	20122	18804	9304
30°	17706	15818	18043	8427
35°	16808	10938	17089	7711
40°	15774	8258	15954	7139
45°	14502	6787	14738	6522
50°	13401	5956	13425	5970
55°	12145	5075	12225	5371
60°	10809	4239	10957	4687
65°	9609	3448	9787	4003
70°	8419	2705	8631	3229
75°	7065	1964	7339	2341
80°	5517	1245	5908	1390
85°	3630	626	3899	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21003 cd/sqm

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	2.6
10°-20°	355.8	7.6
20°-30°	516.4	11.1
30°-40°	544.4	11.7
40°-50°	481.8	10.4
50°-60°	384.7	8.3
60°-70°	261.3	5.6
70°-80°	133.7	2.9
80°-90°	33.4	0.7
90°-100°	40.3	0.9
100°-110°	128.0	2.8
110°-120°	219.1	4.7
120°-130°	288.1	6.2
130°-140°	323.4	6.9
140°-150°	317.1	6.8
150°-160°	266.0	5.7
160°-170°	176.4	3.8
170°-180°	61.7	1.3
0°-30°	994.6	21.4
0°-40°	1539.0	33.1
0°-60°	2405.4	51.7
0°-90°	2833.9	60.9
90°-120°	387.4	8.3
90°-150°	1316.0	28.3
90°-180°	1820.0	39.1
0°-180°	4654.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1285	1434	1290	1140	1285	122
15°	1207	1762	1223	846	1207	341
25°	1084	1468	1089	679	1084	496
35°	885	799	900	563	885	554
45°	664	482	675	463	664	515
55°	456	338	459	358	456	407
65°	270	208	275	242	270	269
75°	126	103	131	122	126	136
85°	26	27	28	20	26	30
90°	0	19	0	19	0	3
95°	29	34	29	34	29	32
105°	118	122	118	122	118	125
115°	220	220	220	220	220	217
125°	320	321	320	321	320	286
135°	414	419	414	419	414	320
145°	502	508	502	508	502	314
155°	574	578	574	578	574	264
165°	625	625	625	625	625	176
175°	650	648	650	648	650	62
180°	651	651	651	651	651	

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1290.5	1293.5	1298.4	1299.4	1309.2	1317.1	1326.0	1326.0	1329.0	1328.0	1320.1
5°	1284.6	1293.5	1306.3	1317.1	1334.9	1342.8	1354.6	1363.5	1371.4	1377.3	1376.3
7.5°	1274.7	1290.5	1309.2	1330.0	1353.6	1367.5	1384.2	1400.0	1410.9	1420.7	1427.6
10°	1257.9	1284.6	1310.2	1337.9	1368.4	1387.2	1406.9	1427.6	1444.4	1463.2	1480.9
12.5°	1235.2	1273.7	1305.3	1341.8	1379.3	1400.0	1431.6	1447.4	1479.9	1527.3	1540.1
15°	1206.6	1258.9	1288.5	1334.9	1384.2	1401.0	1444.4	1470.1	1537.2	1566.8	1602.3
17.5°	1180.0	1238.2	1277.7	1331.0	1379.3	1411.9	1454.3	1506.6	1562.8	1605.2	1644.7
20°	1158.3	1214.5	1261.9	1321.1	1382.3	1423.7	1468.1	1531.2	1592.4	1635.8	1666.4
22.5°	1109.0	1181.0	1236.2	1302.3	1376.3	1433.6	1476.0	1545.0	1611.2	1637.8	1664.4
25°	1084.3	1146.5	1210.6	1285.6	1372.4	1440.5	1477.0	1553.9	1612.1	1622.0	1627.9
27.5°	1038.9	1109.0	1183.9	1269.8	1371.4	1428.6	1475.0	1545.0	1591.4	1584.5	1566.8
30°	982.7	1068.5	1151.4	1244.1	1357.6	1419.7	1463.2	1527.3	1551.0	1515.5	1483.9
32.5°	941.2	1022.1	1113.9	1221.4	1341.8	1401.0	1443.4	1493.7	1498.7	1434.5	1381.3
35°	885.0	974.8	1078.4	1191.8	1315.2	1368.4	1407.9	1438.5	1414.8	1325.0	1261.9
37.5°	834.7	923.5	1034.0	1149.4	1278.7	1331.0	1362.5	1367.5	1309.2	1230.3	1137.6
40°	779.4	871.2	986.6	1108.0	1238.2	1283.6	1303.3	1288.5	1204.7	1112.9	1005.4
42.5°	724.2	814.9	939.3	1063.6	1186.9	1225.4	1233.3	1192.8	1090.2	982.7	858.4
45°	664.0	758.7	883.0	1008.3	1127.7	1149.4	1150.4	1092.2	970.8	858.4	742.9
47.5°	614.7	702.5	825.8	951.1	1051.7	1066.5	1060.6	993.5	861.3	735.0	634.4
50°	560.4	644.3	766.6	889.9	975.8	979.7	964.9	869.2	740.0	624.5	544.6
52.5°	502.2	587.0	699.5	817.9	894.9	888.9	860.3	757.7	636.4	540.7	479.5
55°	455.8	530.8	636.4	751.8	806.1	789.3	757.7	653.1	557.4	476.5	423.3
57.5°	404.5	470.6	574.2	674.8	706.4	690.6	659.1	561.4	472.6	411.4	375.9
60°	356.2	416.4	507.1	591.0	615.7	598.9	562.4	474.6	410.4	359.1	332.5
62.5°	311.8	364.1	440.0	517.0	526.9	510.1	478.5	407.5	352.2	311.8	292.0
65°	270.3	319.7	380.8	439.0	447.9	430.2	397.6	346.3	299.9	274.3	255.5
67.5°	229.9	269.3	323.6	366.0	371.0	354.2	327.6	286.1	257.5	229.9	216.1
70°	194.4	224.0	266.4	300.9	302.9	287.1	273.3	235.8	214.1	194.4	183.5
72.5°	159.8	180.6	213.1	238.8	239.7	229.9	217.1	193.4	174.6	160.8	150.0
75°	126.3	144.0	163.8	186.5	185.5	177.6	167.7	152.9	137.1	128.3	123.3
77.5°	96.7	107.5	123.3	138.1	138.1	134.2	128.3	117.4	107.5	98.7	93.7
80°	69.1	76.0	88.8	93.7	95.7	94.7	89.8	81.9	77.9	71.0	69.1
82.5°	44.4	49.3	55.3	60.2	63.1	61.2	60.2	56.2	50.3	48.3	46.4
85°	25.7	27.6	30.6	33.5	34.5	33.5	35.5	32.6	29.6	29.6	28.6
87.5°	10.9	11.8	13.8	13.8	14.8	14.8	13.8	14.8	14.8	13.8	12.8
90°	0.5	2.0	3.4	4.9	6.4	7.1	8.4	11.1	13.8	16.5	19.2
92.5°	12.1	13.1	14.1	15.0	16.0	16.5	16.6	16.7	16.8	16.9	17.0
95°	28.6	29.8	31.0	32.3	33.5	34.1	34.2	34.5	34.7	35.0	35.2
97.5°	47.8	48.9	50.0	51.1	52.2	52.7	52.9	53.4	53.9	54.4	54.9
100°	69.8	70.8	71.8	72.7	73.7	74.2	74.4	74.7	75.1	75.4	75.8
102.5°	92.8	93.5	94.3	95.0	95.7	96.1	96.3	96.8	97.3	97.8	98.3
105°	118.1	118.5	118.9	119.2	119.6	119.8	119.9	120.2	120.4	120.7	120.9
107.5°	143.4	143.9	144.4	144.9	145.4	145.6	145.6	145.6	145.6	145.6	145.6
110°	167.6	168.3	169.1	169.8	170.5	170.9	170.9	170.9	170.9	170.9	170.9

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	193.9	194.6	195.4	196.1	196.8	197.2	197.1	197.0	196.9	196.8	196.7
115°	219.8	220.5	221.3	222.0	222.7	223.1	223.0	222.7	222.5	222.2	222.0
117.5°	245.6	246.6	247.6	248.5	249.5	250.0	249.7	249.1	248.4	247.8	247.2
120°	271.4	272.4	273.4	274.3	275.3	275.8	275.3	274.3	273.4	272.4	271.4
122.5°	295.0	296.2	297.4	298.7	299.9	300.5	300.2	299.6	299.0	298.4	297.8
125°	319.7	320.8	321.9	323.0	324.1	324.7	324.5	324.1	323.8	323.4	323.0
127.5°	343.9	345.3	346.6	348.0	349.3	350.0	349.8	349.3	348.8	348.3	347.8
130°	366.4	368.0	369.6	371.2	372.8	373.6	373.5	373.2	373.0	372.7	372.5
132.5°	391.7	392.9	394.1	395.4	396.6	397.2	397.3	397.4	397.5	397.7	397.8
135°	413.7	415.0	416.4	417.7	419.0	419.7	419.8	420.1	420.3	420.6	420.8
137.5°	437.9	439.0	440.1	441.2	442.3	442.8	442.9	443.2	443.4	443.7	443.9
140°	459.3	460.4	461.5	462.6	463.7	464.2	464.5	465.1	465.8	466.4	467.0
142.5°	481.3	482.4	483.5	484.6	485.7	486.2	486.4	486.8	487.1	487.5	487.9
145°	502.1	503.0	503.8	504.7	505.6	506.0	506.4	507.1	507.8	508.6	509.3
147.5°	520.8	521.9	523.0	524.1	525.2	525.8	526.0	526.5	527.0	527.5	528.0
150°	540.1	540.8	541.5	542.2	542.9	543.3	543.5	544.0	544.5	545.0	545.5
152.5°	557.1	557.8	558.6	559.3	560.0	560.4	560.7	561.3	561.9	562.5	563.1
155°	574.1	574.5	574.9	575.2	575.6	575.8	576.0	576.3	576.7	577.0	577.4
157.5°	588.9	589.1	589.4	589.6	589.9	590.0	590.1	590.4	590.6	590.9	591.1
160°	602.1	602.3	602.6	602.8	603.1	603.2	603.3	603.4	603.5	603.7	603.8
162.5°	614.2	614.2	614.2	614.2	614.2	614.2	614.3	614.4	614.5	614.7	614.8
165°	624.7	624.6	624.4	624.3	624.2	624.1	624.1	624.1	624.1	624.1	624.1
167.5°	634.0	633.6	633.2	632.9	632.5	632.3	632.3	632.3	632.3	632.3	632.3
170°	641.1	640.7	640.4	640.0	639.7	639.5	639.4	639.3	639.2	639.0	638.9
172.5°	646.1	645.7	645.3	645.0	644.6	644.4	644.3	644.2	644.1	644.0	643.9
175°	649.9	649.5	649.2	648.8	648.5	648.3	648.2	647.9	647.7	647.4	647.2
177.5°	652.1	651.7	651.4	651.0	650.7	650.5	650.4	650.1	649.9	649.6	649.4
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1333.9	1334.9	1336.9	1346.7	1351.7	1352.7	1348.7	1357.6	1360.6	1357.6	1355.6
5°	1397.1	1403.0	1414.8	1427.6	1426.7	1427.6	1433.6	1439.5	1441.5	1433.6	1436.5
7.5°	1452.3	1464.1	1477.0	1496.7	1496.7	1506.6	1510.5	1515.5	1527.3	1521.4	1519.4
10°	1515.5	1531.2	1554.9	1586.5	1587.5	1597.3	1607.2	1623.0	1627.9	1624.0	1626.0
12.5°	1594.4	1625.0	1626.9	1661.5	1677.3	1679.2	1695.0	1692.1	1701.9	1701.9	1718.7
15°	1628.9	1676.3	1702.9	1736.5	1746.3	1734.5	1747.3	1761.1	1762.1	1762.1	1761.1
17.5°	1691.1	1709.8	1736.5	1754.2	1758.2	1758.2	1759.1	1765.1	1761.1	1753.2	1759.1
20°	1703.9	1711.8	1721.7	1719.7	1721.7	1711.8	1701.9	1692.1	1693.0	1688.1	1702.9
22.5°	1680.2	1678.2	1655.6	1640.8	1640.8	1621.0	1602.3	1593.4	1584.5	1587.5	1592.4
25°	1621.0	1590.4	1562.8	1541.1	1536.2	1504.6	1478.9	1471.1	1456.3	1468.1	1470.1
27.5°	1526.3	1491.8	1447.4	1428.6	1403.0	1390.1	1372.4	1348.7	1318.1	1335.9	1332.9
30°	1424.7	1373.4	1336.9	1291.5	1251.0	1248.1	1214.5	1175.1	1159.3	1159.3	1168.2
32.5°	1311.2	1243.1	1189.9	1125.7	1086.3	1069.5	1029.0	989.6	998.5	968.9	979.7
35°	1179.0	1089.2	1022.1	960.0	930.4	910.7	858.4	836.7	813.0	799.2	824.8
37.5°	1052.7	949.1	863.3	795.2	784.4	748.8	713.3	699.5	685.7	691.6	690.6
40°	898.8	807.1	730.1	676.8	658.1	641.3	617.6	600.9	592.0	596.9	597.9
42.5°	759.7	682.7	625.5	588.0	572.2	560.4	548.6	534.7	531.8	531.8	535.7
45°	652.2	589.0	550.5	519.9	511.1	502.2	493.3	487.4	485.4	481.5	484.4
47.5°	566.3	516.0	492.3	469.6	459.8	457.8	449.9	446.9	443.0	442.0	443.0
50°	494.3	462.7	441.0	428.2	421.3	418.3	414.4	408.5	406.5	411.4	409.4
52.5°	444.0	414.4	402.5	389.7	385.8	381.8	375.9	376.9	375.9	373.9	373.9
55°	393.7	374.9	363.1	353.2	352.2	348.3	343.3	341.4	340.4	338.4	341.4
57.5°	353.2	338.4	327.6	318.7	314.7	314.7	309.8	305.9	305.9	304.9	305.9
60°	312.8	298.0	291.1	282.2	279.2	278.2	275.3	273.3	270.3	270.3	270.3
62.5°	275.3	263.4	255.5	247.6	248.6	243.7	239.7	237.8	237.8	238.8	238.8
65°	239.7	231.9	222.0	215.1	213.1	212.1	210.2	209.2	206.2	208.2	208.2
67.5°	207.2	196.3	190.4	187.5	184.5	183.5	181.5	179.6	178.6	177.6	179.6
70°	174.6	165.8	160.8	158.8	155.9	154.9	153.9	151.0	151.9	152.9	153.9
72.5°	145.0	137.1	136.2	130.2	130.2	130.2	126.3	128.3	127.3	125.3	127.3
75°	114.4	110.5	108.5	105.6	106.6	105.6	104.6	101.6	101.6	102.6	103.6
77.5°	90.8	86.8	85.8	82.9	80.9	82.9	80.9	79.9	79.9	80.9	80.9
80°	67.1	65.1	62.2	62.2	62.2	61.2	61.2	61.2	60.2	59.2	60.2
82.5°	44.4	44.4	43.4	42.4	43.4	41.4	42.4	42.4	42.4	42.4	42.4
85°	28.6	27.6	27.6	26.6	26.6	26.6	27.6	25.7	25.7	26.6	26.6
87.5°	12.8	12.8	12.8	13.8	12.8	12.8	12.8	13.8	12.8	12.8	12.8
90°	19.0	18.7	18.5	18.2	18.1	18.2	18.3	18.4	18.6	18.7	18.6
92.5°	17.1	17.3	17.4	17.5	17.6	17.6	17.6	17.6	17.6	17.6	17.6
95°	35.2	35.2	35.2	35.2	35.2	35.1	34.8	34.6	34.3	34.1	34.3
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9
100°	75.8	75.8	75.8	75.8	75.8	75.7	75.6	75.5	75.4	75.3	75.4
102.5°	98.4	98.6	98.7	98.8	98.9	98.8	98.7	98.6	98.4	98.3	98.4
105°	121.1	121.4	121.6	121.9	122.0	122.0	122.0	122.0	122.0	122.0	122.0
107.5°	145.7	145.8	145.9	146.0	146.1	145.8	145.2	144.6	144.0	143.4	144.0
110°	170.9	170.9	170.9	170.9	170.9	170.7	170.3	170.0	169.6	169.2	169.6

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	196.3	195.9	195.6	195.2	195.0	194.9	194.6	194.4	194.1	193.9	194.1
115°	221.9	221.7	221.6	221.5	221.4	221.2	220.9	220.5	220.2	219.8	220.2
117.5°	246.8	246.5	246.1	245.8	245.6	245.4	245.0	244.7	244.3	243.9	244.3
120°	271.4	271.4	271.4	271.4	271.4	271.2	270.9	270.5	270.2	269.8	270.2
122.5°	297.4	297.0	296.7	296.3	296.1	296.0	295.7	295.5	295.2	295.0	295.2
125°	322.6	322.3	321.9	321.6	321.4	321.3	321.2	321.1	320.9	320.8	320.9
127.5°	347.3	346.8	346.3	345.8	345.6	345.4	345.0	344.7	344.3	343.9	344.3
130°	372.3	372.0	371.8	371.5	371.4	371.2	370.7	370.2	369.7	369.2	369.7
132.5°	397.2	396.6	395.9	395.3	395.0	394.8	394.5	394.1	393.8	393.4	393.8
135°	420.7	420.6	420.5	420.4	420.3	420.1	419.7	419.4	419.0	418.6	419.0
137.5°	443.8	443.7	443.6	443.5	443.4	443.2	442.7	442.2	441.7	441.2	441.7
140°	467.0	467.0	467.0	467.0	467.0	466.8	466.3	465.8	465.3	464.8	465.3
142.5°	488.0	488.1	488.2	488.3	488.4	488.2	487.7	487.2	486.7	486.2	486.7
145°	509.4	509.5	509.6	509.7	509.8	509.6	509.1	508.6	508.1	507.6	508.1
147.5°	528.2	528.5	528.7	529.0	529.1	528.9	528.4	527.9	527.4	526.9	527.4
150°	545.9	546.3	546.6	547.0	547.2	547.0	546.6	546.3	545.9	545.5	545.9
152.5°	563.6	564.1	564.6	565.1	565.3	565.1	564.6	564.1	563.6	563.1	563.6
155°	578.0	578.6	579.3	579.9	580.2	580.0	579.6	579.3	578.9	578.5	578.9
157.5°	592.0	592.8	593.7	594.6	595.0	594.7	594.1	593.4	592.8	592.2	592.8
160°	604.5	605.3	606.0	606.7	607.1	606.9	606.4	605.9	605.4	604.9	605.4
162.5°	615.6	616.5	617.3	618.2	618.6	618.3	617.7	617.1	616.5	615.9	616.5
165°	625.0	625.8	626.7	627.6	628.0	627.7	627.1	626.4	625.8	625.2	625.8
167.5°	633.2	634.0	634.9	635.8	636.2	635.9	635.3	634.6	634.0	633.4	634.0
170°	639.8	640.6	641.5	642.4	642.8	642.4	641.7	641.0	640.2	639.5	640.2
172.5°	644.7	645.6	646.4	647.3	647.7	647.3	646.6	645.9	645.1	644.4	645.1
175°	648.0	648.9	649.7	650.6	651.0	650.6	649.9	649.2	648.4	647.7	648.4
177.5°	650.1	650.9	651.6	652.3	652.7	652.3	651.6	650.9	650.1	649.4	650.1
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1360.6	1353.6	1347.7	1348.7	1353.6	1349.7	1339.8	1327.0	1322.1	1316.2	1322.1
5°	1442.4	1436.5	1424.7	1425.7	1422.7	1418.8	1403.0	1383.2	1383.2	1367.5	1365.5
7.5°	1523.3	1514.5	1506.6	1504.6	1493.7	1485.9	1472.0	1444.4	1433.6	1414.8	1404.0
10°	1614.1	1607.2	1598.3	1587.5	1581.6	1567.7	1545.0	1504.6	1484.9	1459.2	1440.5
12.5°	1705.9	1704.9	1685.1	1663.4	1662.5	1640.8	1625.0	1570.7	1544.1	1509.5	1465.1
15°	1764.1	1759.1	1748.3	1737.4	1740.4	1716.7	1681.2	1617.1	1599.3	1557.9	1510.5
17.5°	1763.1	1763.1	1760.1	1758.2	1755.2	1748.3	1728.6	1686.1	1657.5	1605.2	1560.8
20°	1706.9	1719.7	1722.6	1721.7	1731.5	1736.5	1735.5	1708.8	1686.1	1639.8	1594.4
22.5°	1594.4	1624.0	1636.8	1644.7	1665.4	1676.3	1701.9	1692.1	1686.1	1651.6	1613.1
25°	1489.8	1499.7	1538.1	1540.1	1568.7	1595.4	1621.0	1637.8	1659.5	1646.7	1614.1
27.5°	1354.6	1377.3	1404.9	1425.7	1431.6	1485.9	1528.3	1559.8	1609.2	1613.1	1602.3
30°	1201.7	1212.6	1257.9	1285.6	1317.1	1356.6	1417.8	1472.0	1516.4	1556.9	1570.7
32.5°	1015.2	1059.6	1086.3	1119.8	1147.4	1217.5	1292.5	1362.5	1413.8	1481.9	1511.5
35°	844.5	879.1	924.5	938.3	988.6	1047.8	1145.5	1235.2	1313.2	1382.3	1442.4
37.5°	703.5	731.1	779.4	801.1	830.7	906.7	988.6	1100.1	1193.8	1278.7	1353.6
40°	606.8	627.5	664.0	670.9	695.6	764.6	830.7	935.3	1059.6	1174.1	1256.0
42.5°	540.7	550.5	575.2	584.1	599.9	646.2	705.4	804.1	919.5	1037.9	1153.4
45°	493.3	500.2	515.0	522.9	542.6	563.4	611.7	690.6	781.4	900.8	1025.1
47.5°	450.9	459.8	465.7	470.6	481.5	504.2	535.7	593.9	680.8	790.3	910.7
50°	415.4	418.3	429.2	430.2	437.1	451.9	481.5	517.0	586.1	674.8	791.3
52.5°	379.8	382.8	389.7	396.6	399.6	411.4	431.2	460.8	512.1	582.1	685.7
55°	344.3	348.3	355.2	360.1	363.1	372.9	384.8	413.4	453.8	503.2	588.0
57.5°	308.8	317.7	319.7	322.6	327.6	338.4	349.3	366.0	397.6	443.0	505.2
60°	275.3	278.2	285.1	288.1	293.0	298.9	312.8	325.6	348.3	383.8	440.0
62.5°	240.7	247.6	250.6	253.6	257.5	264.4	273.3	287.1	306.8	335.5	379.8
65°	211.1	212.1	218.0	222.0	225.9	230.9	239.7	252.6	264.4	291.1	323.6
67.5°	182.5	184.5	186.5	190.4	195.4	200.3	208.2	215.1	229.9	247.6	273.3
70°	154.9	154.9	159.8	162.8	161.8	167.7	173.6	181.5	192.4	209.2	229.9
72.5°	130.2	129.2	133.2	134.2	136.2	140.1	144.0	151.9	157.9	170.7	186.5
75°	103.6	105.6	107.5	107.5	110.5	113.5	117.4	121.4	128.3	136.2	148.0
77.5°	81.9	81.9	83.9	84.8	87.8	86.8	90.8	94.7	99.6	106.6	115.4
80°	60.2	62.2	62.2	62.2	63.1	64.1	68.1	71.0	74.0	78.9	82.9
82.5°	42.4	42.4	44.4	44.4	44.4	46.4	46.4	47.4	49.3	52.3	55.3
85°	26.6	26.6	26.6	27.6	26.6	27.6	29.6	28.6	29.6	31.6	31.6
87.5°	12.8	12.8	12.8	12.8	12.8	13.8	12.8	13.8	14.8	14.8	14.8
90°	18.4	18.3	18.2	18.1	18.2	18.5	18.7	19.0	19.2	16.5	13.8
92.5°	17.6	17.6	17.6	17.6	17.5	17.4	17.3	17.1	17.0	16.9	16.8
95°	34.6	34.8	35.1	35.2	35.2	35.2	35.2	35.2	35.2	35.0	34.7
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.4	53.9
100°	75.5	75.6	75.7	75.8	75.8	75.8	75.8	75.8	75.8	75.4	75.1
102.5°	98.6	98.7	98.8	98.9	98.8	98.7	98.6	98.4	98.3	97.8	97.3
105°	122.0	122.0	122.0	122.0	121.9	121.6	121.4	121.1	120.9	120.7	120.4
107.5°	144.6	145.2	145.8	146.1	146.0	145.9	145.8	145.7	145.6	145.6	145.6
110°	170.0	170.3	170.7	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	194.4	194.6	194.9	195.0	195.2	195.6	195.9	196.3	196.7	196.8	196.9
115°	220.5	220.9	221.2	221.4	221.5	221.6	221.7	221.9	222.0	222.2	222.5
117.5°	244.7	245.0	245.4	245.6	245.8	246.1	246.5	246.8	247.2	247.8	248.4
120°	270.5	270.9	271.2	271.4	271.4	271.4	271.4	271.4	271.4	272.4	273.4
122.5°	295.5	295.7	296.0	296.1	296.3	296.7	297.0	297.4	297.8	298.4	299.0
125°	321.1	321.2	321.3	321.4	321.6	321.9	322.3	322.6	323.0	323.4	323.8
127.5°	344.7	345.0	345.4	345.6	345.8	346.3	346.8	347.3	347.8	348.3	348.8
130°	370.2	370.7	371.2	371.4	371.5	371.8	372.0	372.3	372.5	372.7	373.0
132.5°	394.1	394.5	394.8	395.0	395.3	395.9	396.6	397.2	397.8	397.7	397.5
135°	419.4	419.7	420.1	420.3	420.4	420.5	420.6	420.7	420.8	420.6	420.3
137.5°	442.2	442.7	443.2	443.4	443.5	443.6	443.7	443.8	443.9	443.7	443.4
140°	465.8	466.3	466.8	467.0	467.0	467.0	467.0	467.0	467.0	466.4	465.8
142.5°	487.2	487.7	488.2	488.4	488.3	488.2	488.1	488.0	487.9	487.5	487.1
145°	508.6	509.1	509.6	509.8	509.7	509.6	509.5	509.4	509.3	508.6	507.8
147.5°	527.9	528.4	528.9	529.1	529.0	528.7	528.5	528.2	528.0	527.5	527.0
150°	546.3	546.6	547.0	547.2	547.0	546.6	546.3	545.9	545.5	545.0	544.5
152.5°	564.1	564.6	565.1	565.3	565.1	564.6	564.1	563.6	563.1	562.5	561.9
155°	579.3	579.6	580.0	580.2	579.9	579.3	578.6	578.0	577.4	577.0	576.7
157.5°	593.4	594.1	594.7	595.0	594.6	593.7	592.8	592.0	591.1	590.9	590.6
160°	605.9	606.4	606.9	607.1	606.7	606.0	605.3	604.5	603.8	603.7	603.5
162.5°	617.1	617.7	618.3	618.6	618.2	617.3	616.5	615.6	614.8	614.7	614.5
165°	626.4	627.1	627.7	628.0	627.6	626.7	625.8	625.0	624.1	624.1	624.1
167.5°	634.6	635.3	635.9	636.2	635.8	634.9	634.0	633.2	632.3	632.3	632.3
170°	641.0	641.7	642.4	642.8	642.4	641.5	640.6	639.8	638.9	639.0	639.2
172.5°	645.9	646.6	647.3	647.7	647.3	646.4	645.6	644.7	643.9	644.0	644.1
175°	649.2	649.9	650.6	651.0	650.6	649.7	648.9	648.0	647.2	647.4	647.7
177.5°	650.9	651.6	652.3	652.7	652.3	651.6	650.9	650.1	649.4	649.6	649.9
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1317.1	1312.2	1309.2	1311.2	1305.3	1290.5	1290.5	1295.4	1289.5	1283.6	1274.7
5°	1353.6	1343.8	1337.9	1336.9	1323.1	1299.4	1294.4	1289.5	1276.7	1262.9	1248.1
7.5°	1389.2	1371.4	1361.5	1354.6	1334.9	1304.3	1291.5	1280.6	1259.9	1239.2	1220.5
10°	1418.8	1393.1	1381.3	1370.4	1344.8	1306.3	1285.6	1265.8	1239.2	1212.6	1188.9
12.5°	1442.4	1412.8	1398.0	1382.3	1350.7	1300.4	1274.7	1243.1	1216.5	1181.0	1157.3
15°	1481.9	1420.7	1406.9	1392.1	1359.6	1290.5	1258.9	1223.4	1186.9	1139.5	1113.9
17.5°	1513.5	1431.6	1430.6	1399.0	1356.6	1286.6	1238.2	1191.8	1152.4	1105.0	1064.6
20°	1532.2	1448.4	1432.6	1400.0	1346.7	1259.9	1209.6	1158.3	1115.9	1058.6	1018.2
22.5°	1548.0	1472.0	1430.6	1391.1	1326.0	1251.0	1177.0	1128.7	1070.5	1008.3	969.8
25°	1553.9	1477.0	1433.6	1388.2	1311.2	1225.4	1141.5	1089.2	1024.1	967.9	915.6
27.5°	1554.9	1476.0	1422.7	1375.4	1290.5	1191.8	1106.0	1050.8	978.7	913.6	861.3
30°	1545.0	1465.1	1416.8	1365.5	1270.8	1161.3	1062.6	1001.4	924.5	859.3	805.1
32.5°	1515.5	1443.4	1404.0	1347.7	1245.1	1118.8	1021.2	953.1	872.2	808.0	755.8
35°	1466.1	1416.8	1373.4	1321.1	1211.6	1079.4	979.7	899.8	817.9	756.7	707.4
37.5°	1404.9	1378.3	1337.9	1286.6	1173.1	1043.8	933.3	844.5	762.7	703.5	655.1
40°	1322.1	1329.0	1289.5	1243.1	1127.7	995.5	873.2	788.3	711.4	656.1	608.7
42.5°	1232.3	1260.9	1238.2	1193.8	1077.4	942.2	828.8	735.0	660.0	602.8	563.4
45°	1135.6	1184.9	1171.1	1138.6	1025.1	886.0	765.6	674.8	608.7	553.5	519.0
47.5°	1030.0	1100.1	1100.1	1076.4	966.9	829.7	711.4	618.6	553.5	514.0	480.5
50°	922.5	1001.4	1014.2	998.5	901.8	765.6	645.3	561.4	505.2	466.7	442.0
52.5°	810.0	901.8	925.5	917.6	832.7	704.4	591.0	509.1	457.8	424.2	402.5
55°	702.5	809.0	834.7	837.6	758.7	637.4	530.8	458.8	409.4	386.8	368.0
57.5°	600.9	703.5	732.1	737.0	683.7	576.2	474.6	411.4	367.0	348.3	333.5
60°	514.0	599.9	637.4	648.2	601.8	505.2	422.3	361.1	327.6	309.8	296.0
62.5°	443.0	512.1	551.5	554.5	533.8	443.0	368.0	316.7	288.1	272.3	265.4
65°	373.9	436.1	459.8	471.6	454.8	383.8	317.7	275.3	252.6	238.8	231.9
67.5°	318.7	358.1	377.9	393.7	376.9	323.6	270.3	235.8	219.0	205.2	201.3
70°	261.5	294.0	308.8	324.6	309.8	269.3	230.9	199.3	184.5	173.6	168.7
72.5°	209.2	234.8	248.6	258.5	249.6	216.1	184.5	162.8	151.9	144.0	141.1
75°	165.8	183.5	191.4	198.3	194.4	168.7	149.0	131.2	121.4	114.4	112.5
77.5°	126.3	139.1	148.0	150.0	145.0	128.3	111.5	100.6	92.7	88.8	86.8
80°	89.8	97.7	102.6	105.6	100.6	93.7	81.9	74.0	67.1	62.2	61.2
82.5°	60.2	64.1	68.1	67.1	65.1	59.2	52.3	48.3	45.4	41.4	41.4
85°	34.5	35.5	37.5	38.5	37.5	33.5	29.6	27.6	25.7	22.7	22.7
87.5°	14.8	15.8	15.8	16.8	14.8	14.8	12.8	10.9	10.9	9.9	8.9
90°	11.1	8.4	7.1	6.4	4.9	3.4	2.0	0.5	2.0	3.4	4.9
92.5°	16.7	16.6	16.5	16.0	15.0	14.1	13.1	12.1	13.1	14.1	15.0
95°	34.5	34.2	34.1	33.5	32.3	31.0	29.8	28.6	29.8	31.0	32.3
97.5°	53.4	52.9	52.7	52.2	51.1	50.0	48.9	47.8	48.9	50.0	51.1
100°	74.7	74.4	74.2	73.7	72.7	71.8	70.8	69.8	70.8	71.8	72.7
102.5°	96.8	96.3	96.1	95.7	95.0	94.3	93.5	92.8	93.5	94.3	95.0
105°	120.2	119.9	119.8	119.6	119.2	118.9	118.5	118.1	118.5	118.9	119.2
107.5°	145.6	145.6	145.6	145.4	144.9	144.4	143.9	143.4	143.9	144.4	144.9
110°	170.9	170.9	170.9	170.5	169.8	169.1	168.3	167.6	168.3	169.1	169.8

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	197.0	197.1	197.2	196.8	196.1	195.4	194.6	193.9	194.6	195.4	196.1
115°	222.7	223.0	223.1	222.7	222.0	221.3	220.5	219.8	220.5	221.3	222.0
117.5°	249.1	249.7	250.0	249.5	248.5	247.6	246.6	245.6	246.6	247.6	248.5
120°	274.3	275.3	275.8	275.3	274.3	273.4	272.4	271.4	272.4	273.4	274.3
122.5°	299.6	300.2	300.5	299.9	298.7	297.4	296.2	295.0	296.2	297.4	298.7
125°	324.1	324.5	324.7	324.1	323.0	321.9	320.8	319.7	320.8	321.9	323.0
127.5°	349.3	349.8	350.0	349.3	348.0	346.6	345.3	343.9	345.3	346.6	348.0
130°	373.2	373.5	373.6	372.8	371.2	369.6	368.0	366.4	368.0	369.6	371.2
132.5°	397.4	397.3	397.2	396.6	395.4	394.1	392.9	391.7	392.9	394.1	395.4
135°	420.1	419.8	419.7	419.0	417.7	416.4	415.0	413.7	415.0	416.4	417.7
137.5°	443.2	442.9	442.8	442.3	441.2	440.1	439.0	437.9	439.0	440.1	441.2
140°	465.1	464.5	464.2	463.7	462.6	461.5	460.4	459.3	460.4	461.5	462.6
142.5°	486.8	486.4	486.2	485.7	484.6	483.5	482.4	481.3	482.4	483.5	484.6
145°	507.1	506.4	506.0	505.6	504.7	503.8	503.0	502.1	503.0	503.8	504.7
147.5°	526.5	526.0	525.8	525.2	524.1	523.0	521.9	520.8	521.9	523.0	524.1
150°	544.0	543.5	543.3	542.9	542.2	541.5	540.8	540.1	540.8	541.5	542.2
152.5°	561.3	560.7	560.4	560.0	559.3	558.6	557.8	557.1	557.8	558.6	559.3
155°	576.3	576.0	575.8	575.6	575.2	574.9	574.5	574.1	574.5	574.9	575.2
157.5°	590.4	590.1	590.0	589.9	589.6	589.4	589.1	588.9	589.1	589.4	589.6
160°	603.4	603.3	603.2	603.1	602.8	602.6	602.3	602.1	602.3	602.6	602.8
162.5°	614.4	614.3	614.2	614.2	614.2	614.2	614.2	614.2	614.2	614.2	614.2
165°	624.1	624.1	624.1	624.2	624.3	624.4	624.6	624.7	624.6	624.4	624.3
167.5°	632.3	632.3	632.3	632.5	632.9	633.2	633.6	634.0	633.6	633.2	632.9
170°	639.3	639.4	639.5	639.7	640.0	640.4	640.7	641.1	640.7	640.4	640.0
172.5°	644.2	644.3	644.4	644.6	645.0	645.3	645.7	646.1	645.7	645.3	645.0
175°	647.9	648.2	648.3	648.5	648.8	649.2	649.5	649.9	649.5	649.2	648.8
177.5°	650.1	650.4	650.5	650.7	651.0	651.4	651.7	652.1	651.7	651.4	651.0
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1269.8	1274.7	1273.7	1263.9	1253.0	1244.1	1227.4	1229.3	1223.4	1224.4	1230.3
5°	1238.2	1238.2	1234.3	1220.5	1202.7	1192.8	1174.1	1169.1	1157.3	1156.3	1155.3
7.5°	1204.7	1199.7	1194.8	1175.1	1153.4	1137.6	1111.9	1106.0	1094.2	1086.3	1082.3
10°	1165.2	1158.3	1148.4	1125.7	1099.1	1079.4	1052.7	1044.8	1022.1	1012.3	1006.4
12.5°	1121.8	1117.8	1102.1	1083.3	1039.9	1018.2	979.7	987.6	964.9	945.2	942.2
15°	1078.4	1063.6	1054.7	1024.1	971.8	962.0	931.4	915.6	894.9	879.1	879.1
17.5°	1036.0	1013.3	993.5	961.0	922.5	894.9	872.2	864.3	838.6	822.8	819.9
20°	979.7	954.1	949.1	902.8	876.1	845.5	823.8	804.1	785.4	778.4	773.5
22.5°	926.4	896.8	888.9	849.5	822.8	792.3	770.6	756.7	742.9	738.0	729.1
25°	869.2	851.5	839.6	797.2	767.6	739.0	724.2	714.3	701.5	700.5	694.6
27.5°	814.0	797.2	785.4	744.9	723.2	696.6	684.7	673.9	667.0	664.0	661.0
30°	766.6	747.9	734.0	704.4	677.8	656.1	646.2	639.3	635.4	630.5	629.5
32.5°	714.3	703.5	684.7	662.0	641.3	620.6	614.7	609.7	603.8	601.8	600.9
35°	669.9	655.1	643.3	617.6	608.7	591.0	584.1	580.1	572.2	570.3	568.3
37.5°	626.5	612.7	599.9	584.1	567.3	557.4	553.5	547.6	543.6	544.6	542.6
40°	583.1	572.2	562.4	545.6	535.7	530.8	522.9	517.0	515.0	516.0	515.0
42.5°	540.7	530.8	524.9	512.1	502.2	497.3	492.3	486.4	489.4	489.4	492.3
45°	502.2	493.3	489.4	479.5	473.6	465.7	460.8	459.8	463.7	462.7	462.7
47.5°	462.7	459.8	454.8	446.0	438.1	433.1	432.1	432.1	436.1	438.1	437.1
50°	432.1	426.2	420.3	413.4	407.5	405.5	402.5	404.5	408.5	408.5	410.4
52.5°	393.7	389.7	387.7	381.8	377.9	377.9	377.9	378.9	381.8	384.8	383.8
55°	360.1	357.2	355.2	352.2	347.3	348.3	347.3	349.3	352.2	355.2	357.2
57.5°	324.6	323.6	321.6	316.7	316.7	315.7	318.7	319.7	324.6	326.6	329.5
60°	293.0	290.1	290.1	286.1	286.1	286.1	289.1	292.0	296.0	297.0	298.9
62.5°	259.5	259.5	258.5	255.5	255.5	258.5	259.5	263.4	265.4	265.4	268.4
65°	227.9	226.9	225.9	226.9	227.9	227.9	230.9	232.8	234.8	235.8	236.8
67.5°	196.3	195.4	197.3	196.3	198.3	202.3	201.3	204.2	207.2	207.2	208.2
70°	166.7	168.7	167.7	169.7	168.7	170.7	173.6	174.6	174.6	175.6	178.6
72.5°	139.1	139.1	139.1	138.1	139.1	141.1	143.1	144.0	146.0	147.0	150.0
75°	112.5	112.5	110.5	112.5	112.5	114.4	116.4	116.4	116.4	118.4	121.4
77.5°	84.8	85.8	84.8	86.8	86.8	87.8	89.8	88.8	90.8	91.8	92.7
80°	62.2	61.2	61.2	61.2	62.2	62.2	64.1	65.1	65.1	68.1	66.1
82.5°	39.5	40.5	39.5	40.5	40.5	41.4	40.5	41.4	42.4	44.4	43.4
85°	22.7	21.7	21.7	22.7	21.7	21.7	22.7	21.7	22.7	21.7	22.7
87.5°	8.9	7.9	7.9	7.9	7.9	6.9	6.9	5.9	5.9	5.9	4.9
90°	6.4	7.1	8.4	11.1	13.8	16.5	19.2	19.0	18.7	18.5	18.2
92.5°	16.0	16.5	16.6	16.7	16.8	16.9	17.0	17.1	17.3	17.4	17.5
95°	33.5	34.1	34.2	34.5	34.7	35.0	35.2	35.2	35.2	35.2	35.2
97.5°	52.2	52.7	52.9	53.4	53.9	54.4	54.9	54.9	54.9	54.9	54.9
100°	73.7	74.2	74.4	74.7	75.1	75.4	75.8	75.8	75.8	75.8	75.8
102.5°	95.7	96.1	96.3	96.8	97.3	97.8	98.3	98.4	98.6	98.7	98.8
105°	119.6	119.8	119.9	120.2	120.4	120.7	120.9	121.1	121.4	121.6	121.9
107.5°	145.4	145.6	145.6	145.6	145.6	145.6	145.6	145.7	145.8	145.9	146.0
110°	170.5	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	196.8	197.2	197.1	197.0	196.9	196.8	196.7	196.3	195.9	195.6	195.2
115°	222.7	223.1	223.0	222.7	222.5	222.2	222.0	221.9	221.7	221.6	221.5
117.5°	249.5	250.0	249.7	249.1	248.4	247.8	247.2	246.8	246.5	246.1	245.8
120°	275.3	275.8	275.3	274.3	273.4	272.4	271.4	271.4	271.4	271.4	271.4
122.5°	299.9	300.5	300.2	299.6	299.0	298.4	297.8	297.4	297.0	296.7	296.3
125°	324.1	324.7	324.5	324.1	323.8	323.4	323.0	322.6	322.3	321.9	321.6
127.5°	349.3	350.0	349.8	349.3	348.8	348.3	347.8	347.3	346.8	346.3	345.8
130°	372.8	373.6	373.5	373.2	373.0	372.7	372.5	372.3	372.0	371.8	371.5
132.5°	396.6	397.2	397.3	397.4	397.5	397.7	397.8	397.2	396.6	395.9	395.3
135°	419.0	419.7	419.8	420.1	420.3	420.6	420.8	420.7	420.6	420.5	420.4
137.5°	442.3	442.8	442.9	443.2	443.4	443.7	443.9	443.8	443.7	443.6	443.5
140°	463.7	464.2	464.5	465.1	465.8	466.4	467.0	467.0	467.0	467.0	467.0
142.5°	485.7	486.2	486.4	486.8	487.1	487.5	487.9	488.0	488.1	488.2	488.3
145°	505.6	506.0	506.4	507.1	507.8	508.6	509.3	509.4	509.5	509.6	509.7
147.5°	525.2	525.8	526.0	526.5	527.0	527.5	528.0	528.2	528.5	528.7	529.0
150°	542.9	543.3	543.5	544.0	544.5	545.0	545.5	545.9	546.3	546.6	547.0
152.5°	560.0	560.4	560.7	561.3	561.9	562.5	563.1	563.6	564.1	564.6	565.1
155°	575.6	575.8	576.0	576.3	576.7	577.0	577.4	578.0	578.6	579.3	579.9
157.5°	589.9	590.0	590.1	590.4	590.6	590.9	591.1	592.0	592.8	593.7	594.6
160°	603.1	603.2	603.3	603.4	603.5	603.7	603.8	604.5	605.3	606.0	606.7
162.5°	614.2	614.2	614.3	614.4	614.5	614.7	614.8	615.6	616.5	617.3	618.2
165°	624.2	624.1	624.1	624.1	624.1	624.1	624.1	625.0	625.8	626.7	627.6
167.5°	632.5	632.3	632.3	632.3	632.3	632.3	632.3	633.2	634.0	634.9	635.8
170°	639.7	639.5	639.4	639.3	639.2	639.0	638.9	639.8	640.6	641.5	642.4
172.5°	644.6	644.4	644.3	644.2	644.1	644.0	643.9	644.7	645.6	646.4	647.3
175°	648.5	648.3	648.2	647.9	647.7	647.4	647.2	648.0	648.9	649.7	650.6
177.5°	650.7	650.5	650.4	650.1	649.9	649.6	649.4	650.1	650.9	651.6	652.3
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1223.4	1226.4	1219.5	1217.5	1219.5	1212.6	1214.5	1216.5	1216.5	1219.5	1221.4
5°	1152.4	1148.4	1141.5	1139.5	1137.6	1140.5	1138.6	1141.5	1142.5	1149.4	1150.4
7.5°	1082.3	1076.4	1070.5	1064.6	1062.6	1057.7	1062.6	1062.6	1069.5	1067.5	1072.5
10°	999.4	998.5	990.6	987.6	983.7	975.8	986.6	983.7	988.6	997.5	999.4
12.5°	938.3	927.4	932.4	918.5	923.5	915.6	916.6	916.6	924.5	925.5	923.5
15°	880.1	871.2	858.4	852.4	849.5	845.5	858.4	859.3	853.4	867.2	862.3
17.5°	820.9	820.9	809.0	806.1	798.2	802.1	800.1	801.1	799.2	809.0	814.0
20°	769.6	764.6	760.7	761.7	751.8	749.8	747.9	749.8	756.7	763.6	765.6
22.5°	728.1	725.2	715.3	717.3	709.4	712.3	710.4	715.3	716.3	716.3	723.2
25°	688.7	684.7	685.7	681.8	678.8	678.8	675.8	678.8	682.7	684.7	685.7
27.5°	659.1	656.1	651.2	648.2	650.2	645.3	649.2	652.2	652.2	650.2	652.2
30°	623.5	625.5	625.5	615.7	619.6	617.6	620.6	622.6	622.6	623.5	621.6
32.5°	599.9	593.9	593.0	592.0	592.0	588.0	588.0	591.0	592.0	593.0	595.9
35°	568.3	568.3	563.4	566.3	562.4	563.4	562.4	563.4	565.3	562.4	565.3
37.5°	539.7	540.7	538.7	540.7	541.7	539.7	537.7	541.7	539.7	539.7	537.7
40°	515.0	514.0	515.0	515.0	515.0	516.0	514.0	514.0	514.0	512.1	510.1
42.5°	494.3	488.4	490.4	491.3	488.4	488.4	489.4	488.4	491.3	485.4	485.4
45°	464.7	462.7	463.7	463.7	465.7	462.7	464.7	465.7	462.7	461.7	459.8
47.5°	438.1	440.0	438.1	440.0	440.0	442.0	438.1	439.0	440.0	436.1	433.1
50°	411.4	411.4	414.4	413.4	414.4	412.4	412.4	411.4	412.4	410.4	407.5
52.5°	386.8	383.8	388.7	387.7	386.8	385.8	384.8	385.8	383.8	381.8	381.8
55°	356.2	356.2	359.1	360.1	360.1	358.1	356.2	357.2	356.2	355.2	354.2
57.5°	331.5	327.6	329.5	330.5	330.5	327.6	329.5	327.6	327.6	328.5	325.6
60°	299.9	299.9	298.0	300.9	300.9	298.9	298.9	299.9	298.0	297.0	296.0
62.5°	266.4	267.4	270.3	271.3	272.3	270.3	268.4	269.3	269.3	266.4	267.4
65°	237.8	239.7	243.7	242.7	240.7	241.7	239.7	240.7	237.8	238.8	235.8
67.5°	210.2	209.2	210.2	210.2	212.1	211.1	209.2	209.2	208.2	211.1	208.2
70°	180.6	180.6	180.6	180.6	181.5	182.5	180.6	178.6	179.6	177.6	176.6
72.5°	150.0	151.0	150.0	151.9	149.0	151.0	151.0	150.0	149.0	149.0	149.0
75°	121.4	123.3	120.4	121.4	120.4	122.3	121.4	121.4	119.4	118.4	119.4
77.5°	92.7	93.7	91.8	92.7	91.8	92.7	92.7	91.8	91.8	91.8	91.8
80°	66.1	67.1	66.1	65.1	64.1	66.1	64.1	65.1	66.1	65.1	67.1
82.5°	42.4	42.4	41.4	42.4	40.5	40.5	41.4	41.4	40.5	42.4	40.5
85°	20.7	20.7	22.7	20.7	19.7	19.7	19.7	20.7	19.7	21.7	20.7
87.5°	4.9	3.9	4.9	4.9	3.9	3.9	4.9	3.9	4.9	5.9	3.9
90°	18.1	18.2	18.3	18.4	18.6	18.7	18.6	18.4	18.3	18.2	18.1
92.5°	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6
95°	35.2	35.1	34.8	34.6	34.3	34.1	34.3	34.6	34.8	35.1	35.2
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9
100°	75.8	75.7	75.6	75.5	75.4	75.3	75.4	75.5	75.6	75.7	75.8
102.5°	98.9	98.8	98.7	98.6	98.4	98.3	98.4	98.6	98.7	98.8	98.9
105°	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0
107.5°	146.1	145.8	145.2	144.6	144.0	143.4	144.0	144.6	145.2	145.8	146.1
110°	170.9	170.7	170.3	170.0	169.6	169.2	169.6	170.0	170.3	170.7	170.9

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	195.0	194.9	194.6	194.4	194.1	193.9	194.1	194.4	194.6	194.9	195.0
115°	221.4	221.2	220.9	220.5	220.2	219.8	220.2	220.5	220.9	221.2	221.4
117.5°	245.6	245.4	245.0	244.7	244.3	243.9	244.3	244.7	245.0	245.4	245.6
120°	271.4	271.2	270.9	270.5	270.2	269.8	270.2	270.5	270.9	271.2	271.4
122.5°	296.1	296.0	295.7	295.5	295.2	295.0	295.2	295.5	295.7	296.0	296.1
125°	321.4	321.3	321.2	321.1	320.9	320.8	320.9	321.1	321.2	321.3	321.4
127.5°	345.6	345.4	345.0	344.7	344.3	343.9	344.3	344.7	345.0	345.4	345.6
130°	371.4	371.2	370.7	370.2	369.7	369.2	369.7	370.2	370.7	371.2	371.4
132.5°	395.0	394.8	394.5	394.1	393.8	393.4	393.8	394.1	394.5	394.8	395.0
135°	420.3	420.1	419.7	419.4	419.0	418.6	419.0	419.4	419.7	420.1	420.3
137.5°	443.4	443.2	442.7	442.2	441.7	441.2	441.7	442.2	442.7	443.2	443.4
140°	467.0	466.8	466.3	465.8	465.3	464.8	465.3	465.8	466.3	466.8	467.0
142.5°	488.4	488.2	487.7	487.2	486.7	486.2	486.7	487.2	487.7	488.2	488.4
145°	509.8	509.6	509.1	508.6	508.1	507.6	508.1	508.6	509.1	509.6	509.8
147.5°	529.1	528.9	528.4	527.9	527.4	526.9	527.4	527.9	528.4	528.9	529.1
150°	547.2	547.0	546.6	546.3	545.9	545.5	545.9	546.3	546.6	547.0	547.2
152.5°	565.3	565.1	564.6	564.1	563.6	563.1	563.6	564.1	564.6	565.1	565.3
155°	580.2	580.0	579.6	579.3	578.9	578.5	578.9	579.3	579.6	580.0	580.2
157.5°	595.0	594.7	594.1	593.4	592.8	592.2	592.8	593.4	594.1	594.7	595.0
160°	607.1	606.9	606.4	605.9	605.4	604.9	605.4	605.9	606.4	606.9	607.1
162.5°	618.6	618.3	617.7	617.1	616.5	615.9	616.5	617.1	617.7	618.3	618.6
165°	628.0	627.7	627.1	626.4	625.8	625.2	625.8	626.4	627.1	627.7	628.0
167.5°	636.2	635.9	635.3	634.6	634.0	633.4	634.0	634.6	635.3	635.9	636.2
170°	642.8	642.4	641.7	641.0	640.2	639.5	640.2	641.0	641.7	642.4	642.8
172.5°	647.7	647.3	646.6	645.9	645.1	644.4	645.1	645.9	646.6	647.3	647.7
175°	651.0	650.6	649.9	649.2	648.4	647.7	648.4	649.2	649.9	650.6	651.0
177.5°	652.7	652.3	651.6	650.9	650.1	649.4	650.1	650.9	651.6	652.3	652.7
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1218.5	1226.4	1223.4	1212.6	1225.4	1225.4	1234.3	1234.3	1245.1	1249.1	1255.0
5°	1149.4	1155.3	1160.3	1155.3	1164.2	1178.0	1185.9	1192.8	1207.6	1213.5	1222.4
7.5°	1075.4	1086.3	1091.2	1091.2	1106.0	1121.8	1137.6	1147.4	1168.2	1176.1	1184.9
10°	1003.4	1016.2	1026.1	1025.1	1049.8	1059.6	1079.4	1102.1	1122.8	1134.6	1147.4
12.5°	927.4	934.3	948.1	967.9	973.8	991.6	1014.2	1042.9	1080.4	1091.2	1109.9
15°	864.3	883.0	893.9	902.8	916.6	933.3	958.0	985.6	1023.1	1046.8	1066.5
17.5°	811.0	835.7	842.6	840.6	858.4	884.0	912.6	933.3	966.9	995.5	1014.2
20°	767.6	777.5	789.3	794.2	808.0	835.7	863.3	887.0	914.6	937.3	959.0
22.5°	724.2	732.1	741.9	750.8	761.7	777.5	804.1	833.7	860.3	882.0	906.7
25°	688.7	693.6	702.5	709.4	721.2	732.1	750.8	783.4	814.9	827.8	849.5
27.5°	654.1	658.1	664.0	671.9	677.8	688.7	705.4	732.1	764.6	777.5	807.1
30°	623.5	626.5	632.4	636.4	639.3	652.2	665.0	685.7	710.4	728.1	749.8
32.5°	594.9	597.9	603.8	604.8	608.7	615.7	627.5	646.2	667.9	682.7	701.5
35°	563.4	565.3	571.3	573.2	576.2	582.1	591.0	604.8	624.5	635.4	652.2
37.5°	538.7	537.7	541.7	544.6	548.6	551.5	554.5	568.3	583.1	593.0	605.8
40°	512.1	510.1	511.1	515.0	517.0	520.9	520.9	534.7	544.6	552.5	562.4
42.5°	485.4	484.4	482.5	484.4	486.4	487.4	488.4	498.2	508.1	515.0	525.9
45°	458.8	457.8	455.8	456.8	456.8	458.8	461.7	465.7	472.6	478.5	484.4
47.5°	434.1	432.1	429.2	428.2	430.2	430.2	430.2	434.1	441.0	443.0	448.9
50°	408.5	405.5	401.6	399.6	399.6	398.6	400.6	401.6	407.5	409.4	414.4
52.5°	380.8	378.9	374.9	371.0	372.0	370.0	371.0	372.0	373.9	376.9	379.8
55°	353.2	349.3	346.3	345.3	342.4	342.4	339.4	343.3	342.4	343.3	347.3
57.5°	326.6	322.6	317.7	315.7	312.8	311.8	309.8	308.8	309.8	312.8	315.7
60°	295.0	293.0	290.1	287.1	285.1	282.2	280.2	280.2	279.2	279.2	280.2
62.5°	264.4	263.4	259.5	258.5	256.5	254.5	251.6	249.6	249.6	251.6	252.6
65°	234.8	233.8	230.9	229.9	224.9	223.0	222.0	221.0	219.0	219.0	219.0
67.5°	207.2	204.2	204.2	199.3	195.4	193.4	191.4	190.4	190.4	190.4	191.4
70°	176.6	176.6	173.6	170.7	166.7	167.7	164.8	161.8	161.8	159.8	160.8
72.5°	147.0	146.0	143.1	142.1	139.1	136.2	134.2	136.2	133.2	132.2	133.2
75°	118.4	117.4	115.4	113.5	114.4	111.5	108.5	107.5	107.5	105.6	105.6
77.5°	90.8	92.7	88.8	87.8	85.8	83.9	82.9	81.9	81.9	81.9	83.9
80°	63.1	64.1	64.1	62.2	63.1	60.2	60.2	60.2	57.2	58.2	59.2
82.5°	40.5	40.5	39.5	40.5	39.5	39.5	38.5	38.5	37.5	37.5	38.5
85°	22.7	21.7	20.7	22.7	21.7	21.7	20.7	20.7	20.7	20.7	20.7
87.5°	4.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9
90°	18.2	18.5	18.7	19.0	19.2	16.5	13.8	11.1	8.4	7.1	6.4
92.5°	17.5	17.4	17.3	17.1	17.0	16.9	16.8	16.7	16.6	16.5	16.0
95°	35.2	35.2	35.2	35.2	35.2	35.0	34.7	34.5	34.2	34.1	33.5
97.5°	54.9	54.9	54.9	54.9	54.9	54.4	53.9	53.4	52.9	52.7	52.2
100°	75.8	75.8	75.8	75.8	75.8	75.4	75.1	74.7	74.4	74.2	73.7
102.5°	98.8	98.7	98.6	98.4	98.3	97.8	97.3	96.8	96.3	96.1	95.7
105°	121.9	121.6	121.4	121.1	120.9	120.7	120.4	120.2	119.9	119.8	119.6
107.5°	146.0	145.9	145.8	145.7	145.6	145.6	145.6	145.6	145.6	145.6	145.4
110°	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.5

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	195.2	195.6	195.9	196.3	196.7	196.8	196.9	197.0	197.1	197.2	196.8
115°	221.5	221.6	221.7	221.9	222.0	222.2	222.5	222.7	223.0	223.1	222.7
117.5°	245.8	246.1	246.5	246.8	247.2	247.8	248.4	249.1	249.7	250.0	249.5
120°	271.4	271.4	271.4	271.4	271.4	272.4	273.4	274.3	275.3	275.8	275.3
122.5°	296.3	296.7	297.0	297.4	297.8	298.4	299.0	299.6	300.2	300.5	299.9
125°	321.6	321.9	322.3	322.6	323.0	323.4	323.8	324.1	324.5	324.7	324.1
127.5°	345.8	346.3	346.8	347.3	347.8	348.3	348.8	349.3	349.8	350.0	349.3
130°	371.5	371.8	372.0	372.3	372.5	372.7	373.0	373.2	373.5	373.6	372.8
132.5°	395.3	395.9	396.6	397.2	397.8	397.7	397.5	397.4	397.3	397.2	396.6
135°	420.4	420.5	420.6	420.7	420.8	420.6	420.3	420.1	419.8	419.7	419.0
137.5°	443.5	443.6	443.7	443.8	443.9	443.7	443.4	443.2	442.9	442.8	442.3
140°	467.0	467.0	467.0	467.0	467.0	466.4	465.8	465.1	464.5	464.2	463.7
142.5°	488.3	488.2	488.1	488.0	487.9	487.5	487.1	486.8	486.4	486.2	485.7
145°	509.7	509.6	509.5	509.4	509.3	508.6	507.8	507.1	506.4	506.0	505.6
147.5°	529.0	528.7	528.5	528.2	528.0	527.5	527.0	526.5	526.0	525.8	525.2
150°	547.0	546.6	546.3	545.9	545.5	545.0	544.5	544.0	543.5	543.3	542.9
152.5°	565.1	564.6	564.1	563.6	563.1	562.5	561.9	561.3	560.7	560.4	560.0
155°	579.9	579.3	578.6	578.0	577.4	577.0	576.7	576.3	576.0	575.8	575.6
157.5°	594.6	593.7	592.8	592.0	591.1	590.9	590.6	590.4	590.1	590.0	589.9
160°	606.7	606.0	605.3	604.5	603.8	603.7	603.5	603.4	603.3	603.2	603.1
162.5°	618.2	617.3	616.5	615.6	614.8	614.7	614.5	614.4	614.3	614.2	614.2
165°	627.6	626.7	625.8	625.0	624.1	624.1	624.1	624.1	624.1	624.1	624.2
167.5°	635.8	634.9	634.0	633.2	632.3	632.3	632.3	632.3	632.3	632.3	632.5
170°	642.4	641.5	640.6	639.8	638.9	639.0	639.2	639.3	639.4	639.5	639.7
172.5°	647.3	646.4	645.6	644.7	643.9	644.0	644.1	644.2	644.3	644.4	644.6
175°	650.6	649.7	648.9	648.0	647.2	647.4	647.7	647.9	648.2	648.3	648.5
177.5°	652.3	651.6	650.9	650.1	649.4	649.6	649.9	650.1	650.4	650.5	650.7
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1283.6	1283.6	1283.6	1283.6
2.5°	1259.9	1259.9	1274.7	1290.5
5°	1232.3	1239.2	1262.9	1284.6
7.5°	1205.7	1217.5	1247.1	1274.7
10°	1173.1	1188.9	1225.4	1257.9
12.5°	1141.5	1156.3	1198.7	1235.2
15°	1097.1	1115.9	1161.3	1206.6
17.5°	1052.7	1071.5	1126.7	1180.0
20°	1000.4	1025.1	1087.3	1158.3
22.5°	952.1	982.7	1051.7	1109.0
25°	898.8	946.2	1010.3	1084.3
27.5°	851.5	898.8	963.9	1038.9
30°	798.2	846.5	913.6	982.7
32.5°	746.9	791.3	856.4	941.2
35°	693.6	736.0	799.2	885.0
37.5°	645.3	686.7	755.8	834.7
40°	597.9	641.3	700.5	779.4
42.5°	553.5	592.0	645.3	724.2
45°	513.0	540.7	590.0	664.0
47.5°	470.6	495.3	540.7	614.7
50°	431.2	451.9	491.3	560.4
52.5°	392.7	410.4	446.9	502.2
55°	358.1	374.9	401.6	455.8
57.5°	322.6	335.5	361.1	404.5
60°	288.1	299.9	320.7	356.2
62.5°	253.6	263.4	283.2	311.8
65°	223.0	230.9	245.7	270.3
67.5°	193.4	198.3	210.2	229.9
70°	164.8	168.7	178.6	194.4
72.5°	134.2	138.1	149.0	159.8
75°	108.5	109.5	117.4	126.3
77.5°	84.8	83.9	89.8	96.7
80°	58.2	61.2	66.1	69.1
82.5°	39.5	40.5	42.4	44.4
85°	21.7	22.7	22.7	25.7
87.5°	8.9	9.9	9.9	10.9
90°	4.9	3.4	2.0	0.5
92.5°	15.0	14.1	13.1	12.1
95°	32.3	31.0	29.8	28.6
97.5°	51.1	50.0	48.9	47.8
100°	72.7	71.8	70.8	69.8
102.5°	95.0	94.3	93.5	92.8
105°	119.2	118.9	118.5	118.1
107.5°	144.9	144.4	143.9	143.4
110°	169.8	169.1	168.3	167.6

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	196.1	195.4	194.6	193.9
115°	222.0	221.3	220.5	219.8
117.5°	248.5	247.6	246.6	245.6
120°	274.3	273.4	272.4	271.4
122.5°	298.7	297.4	296.2	295.0
125°	323.0	321.9	320.8	319.7
127.5°	348.0	346.6	345.3	343.9
130°	371.2	369.6	368.0	366.4
132.5°	395.4	394.1	392.9	391.7
135°	417.7	416.4	415.0	413.7
137.5°	441.2	440.1	439.0	437.9
140°	462.6	461.5	460.4	459.3
142.5°	484.6	483.5	482.4	481.3
145°	504.7	503.8	503.0	502.1
147.5°	524.1	523.0	521.9	520.8
150°	542.2	541.5	540.8	540.1
152.5°	559.3	558.6	557.8	557.1
155°	575.2	574.9	574.5	574.1
157.5°	589.6	589.4	589.1	588.9
160°	602.8	602.6	602.3	602.1
162.5°	614.2	614.2	614.2	614.2
165°	624.3	624.4	624.6	624.7
167.5°	632.9	633.2	633.6	634.0
170°	640.0	640.4	640.7	641.1
172.5°	645.0	645.3	645.7	646.1
175°	648.8	649.2	649.5	649.9
177.5°	651.0	651.4	651.7	652.1
180°	651.0	651.0	651.0	651.0

TEST NUMBER: P998844

CATALOG NUMBER: SA2XXDIP-B675D530UB50-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.27	18.19	18.13	19.07	20.18	14.76	15.69	15.63	16.57	17.68
	3H	18.08	18.91	18.96	19.80	20.94	16.11	16.94	16.99	17.83	18.96
	4H	18.25	19.04	19.15	19.93	21.08	16.58	17.36	17.47	18.25	19.40
	6H	18.30	19.02	19.21	19.93	21.09	16.89	17.60	17.79	18.51	19.67
	8H	18.28	18.97	19.20	19.89	21.05	16.97	17.66	17.88	18.58	19.73
	12H	18.25	18.90	19.17	19.81	21.00	17.02	17.67	17.93	18.58	19.76
4H	2H	17.32	18.10	18.21	18.99	20.14	15.21	15.99	16.11	16.89	18.04
	3H	18.30	18.95	19.21	19.88	21.04	16.68	17.33	17.59	18.26	19.42
	4H	18.58	19.17	19.50	20.10	21.28	17.22	17.81	18.14	18.73	19.92
	6H	18.72	19.22	19.65	20.17	21.36	17.60	18.11	18.53	19.06	20.25
	8H	18.71	19.19	19.65	20.13	21.33	17.71	18.19	18.65	19.13	20.33
	12H	18.68	19.11	19.64	20.07	21.28	17.77	18.20	18.73	19.16	20.37
8H	4H	18.60	19.07	19.53	20.01	21.21	17.36	17.84	18.30	18.78	19.98
	6H	18.78	19.17	19.74	20.15	21.35	17.80	18.19	18.76	19.18	20.38
	8H	18.81	19.15	19.78	20.13	21.35	17.95	18.30	18.92	19.27	20.49
	12H	18.79	19.10	19.77	20.07	21.33	18.05	18.35	19.02	19.32	20.59
12H	4H	18.56	18.98	19.51	19.94	21.15	17.34	17.77	18.30	18.73	19.94
	6H	18.76	19.10	19.73	20.08	21.29	17.80	18.15	18.77	19.12	20.34
	8H	18.79	19.10	19.76	20.06	21.33	17.96	18.27	18.94	19.23	20.50