

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998898

Luminaire Tested: SA2XXDIP-B675D725UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998898
REPORT IS A COMBINATION OF REPORTS P984644 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D725UB40-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5204.0 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998898

CATALOG NUMBER: SA2XXDIP-B675D725UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998898

CATALOG NUMBER: SA2XXDIP-B675D725UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46		
1	95	91	86	82	87	83	79	76	69	66	64	56	54	52	44	43	41	36		
2	86	78	72	66	79	72	66	61	60	55	52	48	45	43	38	36	34	29		
3	78	68	61	54	71	63	56	50	52	47	43	42	39	35	33	31	28	24		
4	72	60	52	46	65	55	48	42	46	40	36	37	33	30	29	26	24	20		
5	66	53	45	39	60	49	42	36	41	35	31	33	29	26	26	23	21	17		
6	60	48	39	33	55	44	36	31	37	31	27	30	26	22	24	21	18	15		
7	56	43	35	29	51	40	32	27	33	27	23	27	23	20	22	18	16	13		
8	52	39	31	25	47	36	29	24	30	25	21	25	20	17	20	17	14	12		
9	48	35	28	23	44	33	26	21	28	22	18	23	19	15	18	15	13	10		
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	14	11	9		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11147	11147	11147
5°	11197	10672	10612
10°	11122	10301	10152
15°	10965	9919	9680
20°	10767	9518	9232
25°	10573	9134	8827
30°	10297	8743	8425
35°	10020	8366	8130
40°	9729	8041	7836
45°	9450	7745	7580
50°	9152	7473	7328
55°	8839	7184	7072
60°	8454	6883	6801
65°	8055	6537	6491
70°	7600	6165	6156
75°	7021	5793	5842
80°	6108	5405	5514
85°	5184	5040	5232

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9450 cd/sqm

TEST NUMBER: P998898

CATALOG NUMBER: SA2XXDIP-B675D725UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.8	1.3
10°-20°	191.5	3.7
20°-30°	290.1	5.6
30°-40°	353.3	6.8
40°-50°	380.1	7.3
50°-60°	369.1	7.1
60°-70°	322.4	6.2
70°-80°	248.1	4.8
80°-90°	168.7	3.2
90°-100°	170.3	3.3
100°-110°	260.6	5.0
110°-120°	357.9	6.9
120°-130°	428.8	8.2
130°-140°	459.7	8.8
140°-150°	440.3	8.5
150°-160°	367.5	7.1
160°-170°	243.7	4.7
170°-180°	85.2	1.6
0°-30°	548.3	10.5
0°-40°	901.6	17.3
0°-60°	1650.8	31.7
0°-90°	2390.0	45.9
90°-120°	788.8	15.2
90°-150°	2117.6	40.7
90°-180°	2814.0	54.1
0°-180°	5204.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	704	704	704	704	704	
5°	706	703	697	703	702	67
15°	674	676	676	685	684	190
25°	612	620	629	641	644	282
35°	528	545	564	587	594	330
45°	433	460	496	528	538	334
55°	332	368	422	458	472	297
65°	227	277	337	379	392	225
75°	126	183	248	292	305	133
85°	37	100	165	208	222	39
90°	11	79	161	200	214	10
95°	48	103	166	205	216	50
105°	168	200	255	292	303	178
115°	308	323	368	398	407	304
125°	444	450	481	506	515	397
135°	572	581	593	613	619	443
145°	694	699	704	710	712	434
155°	793	795	798	802	799	365
165°	863	862	862	868	864	243
175°	898	896	894	899	895	85
180°	899	899	899	899	899	

TEST NUMBER: P998898

CATALOG NUMBER: SA2XXDIP-B675D725UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	704.2	704.2	704.2	704.2	704.2
2.5°	709.3	706.2	699.1	704.2	702.2
5°	706.2	703.2	697.1	703.2	702.2
7.5°	701.1	699.1	694.0	701.1	700.1
10°	695.0	693.0	689.9	698.1	697.1
12.5°	684.8	685.8	683.8	692.0	690.9
15°	673.6	675.6	675.6	684.8	683.8
17.5°	659.3	663.4	666.4	675.6	675.6
20°	645.0	650.1	654.2	665.4	665.4
22.5°	629.7	635.8	641.9	653.2	655.2
25°	612.4	619.5	628.7	640.9	644.0
27.5°	591.9	603.2	613.4	628.7	630.7
30°	571.5	584.8	598.1	614.4	617.5
32.5°	549.1	564.4	580.7	600.1	606.2
35°	527.6	545.0	564.4	586.8	594.0
37.5°	504.2	523.6	548.1	572.5	579.7
40°	480.7	503.1	530.7	557.2	566.4
42.5°	458.2	480.7	513.4	543.0	552.1
45°	432.7	460.3	496.0	527.6	537.8
47.5°	408.2	437.8	478.7	511.3	522.5
50°	382.7	414.4	460.3	495.0	506.2
52.5°	358.2	391.9	440.9	476.6	488.9
55°	331.7	368.4	421.5	458.2	471.5
57.5°	306.2	347.0	400.1	439.9	453.1
60°	278.6	322.5	380.7	419.5	433.7
62.5°	254.1	300.1	358.2	400.1	413.3
65°	226.6	276.6	336.8	378.6	391.9
67.5°	202.1	254.1	315.4	357.2	371.5
70°	175.5	228.6	291.9	335.8	348.0
72.5°	151.0	206.2	270.5	313.3	328.6
75°	125.5	182.7	248.0	291.9	305.2
77.5°	101.0	160.2	226.6	270.5	284.7
80°	76.5	138.8	205.1	248.0	262.3
82.5°	56.1	117.4	184.7	227.6	240.9
85°	36.7	100.0	165.3	208.2	222.5
87.5°	22.5	83.7	149.0	190.8	204.1
90°	11.0	79.3	161.3	200.5	213.6
92.5°	25.9	86.1	149.0	189.6	201.9
95°	47.7	103.2	166.0	204.7	215.5
97.5°	73.1	123.9	186.1	223.9	236.1
100°	103.5	147.4	206.8	244.5	255.0
102.5°	134.4	172.6	230.8	268.3	278.8
105°	168.3	200.2	254.8	292.0	303.2
107.5°	203.2	230.7	281.7	317.2	324.7
110°	235.6	260.5	310.5	343.2	352.2

TEST NUMBER: P998898

CATALOG NUMBER: SA2XXDIP-B675D725UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	272.0	292.9	339.1	369.4	379.1
115°	307.7	323.4	367.8	397.8	406.7
117.5°	342.4	356.5	395.6	424.0	431.9
120°	378.0	388.1	422.9	451.4	460.4
122.5°	410.7	419.2	453.2	478.5	486.2
125°	443.7	450.5	481.0	506.3	514.6
127.5°	477.1	484.5	509.0	531.5	538.4
130°	508.2	517.1	537.1	560.0	565.1
132.5°	543.1	549.7	565.8	585.5	591.4
135°	572.5	580.8	592.6	613.3	619.1
137.5°	605.9	612.7	619.3	638.0	642.1
140°	635.5	641.3	647.1	663.5	666.6
142.5°	665.8	671.7	674.0	686.9	689.0
145°	693.7	699.0	703.6	710.4	712.5
147.5°	719.5	726.3	729.4	731.9	731.9
150°	746.1	750.6	753.6	755.9	753.6
152.5°	769.6	774.1	777.9	781.0	777.9
155°	793.1	795.4	797.7	801.5	799.2
157.5°	813.6	815.1	816.6	821.9	818.2
160°	831.8	833.3	834.1	838.6	835.6
162.5°	848.5	848.5	849.3	854.6	850.8
165°	862.9	862.2	862.2	867.5	863.7
167.5°	875.8	873.6	873.6	878.9	875.1
170°	885.7	883.4	882.7	888.0	883.4
172.5°	892.5	890.3	889.5	894.8	890.3
175°	897.8	895.6	894.0	899.4	894.8
177.5°	900.9	898.6	897.1	901.6	897.1
180°	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P998898

CATALOG NUMBER: SA2XXDIP-B675D725UB40-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.20	14.07	14.18	15.07	16.40	16.28	17.15	17.26	18.15	19.47
	3H	14.66	15.45	15.65	16.46	17.80	18.87	19.65	19.86	20.66	22.01
	4H	15.14	15.89	16.14	16.90	18.25	20.12	20.87	21.12	21.88	23.23
	6H	15.42	16.12	16.44	17.13	18.50	21.42	22.11	22.43	23.13	24.49
	8H	15.48	16.14	16.50	17.18	18.54	22.08	22.74	23.10	23.77	25.14
	12H	15.50	16.13	16.52	17.16	18.55	22.80	23.43	23.83	24.46	25.85
4H	2H	14.25	15.00	15.26	16.02	17.37	16.61	17.36	17.62	18.37	19.72
	3H	15.96	16.60	16.98	17.64	19.00	19.40	20.03	20.42	21.08	22.44
	4H	16.58	17.17	17.61	18.20	19.59	20.82	21.40	21.84	22.43	23.82
	6H	17.00	17.51	18.03	18.56	19.95	22.29	22.79	23.32	23.85	25.23
	8H	17.11	17.59	18.14	18.64	20.03	23.04	23.52	24.08	24.57	25.97
	12H	17.15	17.59	18.21	18.65	20.06	23.87	24.31	24.93	25.37	26.78
8H	4H	17.38	17.85	18.41	18.90	20.30	20.96	21.44	22.00	22.49	23.89
	6H	18.01	18.41	19.07	19.50	20.90	22.59	22.99	23.65	24.08	25.48
	8H	18.23	18.59	19.30	19.66	21.07	23.48	23.84	24.55	24.91	26.33
	12H	18.36	18.68	19.44	19.75	21.20	24.48	24.79	25.55	25.86	27.32
12H	4H	17.57	18.01	18.63	19.07	20.48	20.94	21.37	21.99	22.43	23.84
	6H	18.34	18.70	19.41	19.77	21.19	22.62	22.97	23.68	24.05	25.46
	8H	18.65	18.96	19.72	20.03	21.49	23.55	23.86	24.62	24.93	26.39