

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998905

Luminaire Tested: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998905
REPORT IS A COMBINATION OF REPORTS P984651 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5493.0 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52		
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	44		
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38		
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	33		
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	34	32	29		
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	25		
6	64	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22		
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	20		
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18		
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19	16		
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20318	20318	20318	20318
5°	20367	21665	20445	17235
10°	20130	23650	20257	14211
15°	19642	24945	19915	11969
20°	19336	23422	19336	10403
25°	18720	20122	18804	9304
30°	17706	15818	18043	8427
35°	16808	10938	17089	7711
40°	15774	8258	15954	7139
45°	14502	6787	14738	6522
50°	13401	5956	13425	5970
55°	12145	5075	12225	5371
60°	10809	4239	10957	4687
65°	9609	3448	9787	4003
70°	8419	2705	8631	3229
75°	7065	1964	7339	2341
80°	5517	1245	5908	1390
85°	3630	626	3899	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21003 cd/sqm

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	2.2
10°-20°	355.8	6.5
20°-30°	516.4	9.4
30°-40°	544.4	9.9
40°-50°	481.8	8.8
50°-60°	384.7	7.0
60°-70°	261.3	4.8
70°-80°	133.7	2.4
80°-90°	34.0	0.6
90°-100°	148.8	2.7
100°-110°	524.1	9.5
110°-120°	550.4	10.0
120°-130°	452.8	8.2
130°-140°	363.8	6.6
140°-150°	274.8	5.0
150°-160°	193.2	3.5
160°-170°	113.7	2.1
170°-180°	37.0	0.7
0°-30°	994.6	18.1
0°-40°	1539.0	28.0
0°-60°	2405.4	43.8
0°-90°	2834.5	51.6
90°-120°	1223.3	22.3
90°-150°	2314.7	42.1
90°-180°	2659.0	48.4
0°-180°	5493.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1285	1434	1290	1140	1285	122
15°	1207	1762	1223	846	1207	341
25°	1084	1468	1089	679	1084	496
35°	885	799	900	563	885	554
45°	664	482	675	463	664	515
55°	456	338	459	358	456	407
65°	270	208	275	242	270	269
75°	126	103	131	122	126	136
85°	26	27	28	20	26	30
90°	1	24	1	24	1	3
95°	26	84	26	84	26	27
105°	90	827	90	827	90	95
115°	158	1089	158	1089	158	157
125°	220	883	220	883	220	196
135°	258	732	258	732	258	200
145°	295	584	295	584	295	185
155°	336	491	336	491	336	154
165°	366	431	366	431	366	103
175°	381	388	381	388	381	36
180°	382	382	382	382	382	

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1290.5	1293.5	1298.4	1299.4	1309.2	1317.1	1326.0	1326.0	1329.0	1328.0	1320.1
5°	1284.6	1293.5	1306.3	1317.1	1334.9	1342.8	1354.6	1363.5	1371.4	1377.3	1376.3
7.5°	1274.7	1290.5	1309.2	1330.0	1353.6	1367.5	1384.2	1400.0	1410.9	1420.7	1427.6
10°	1257.9	1284.6	1310.2	1337.9	1368.4	1387.2	1406.9	1427.6	1444.4	1463.2	1480.9
12.5°	1235.2	1273.7	1305.3	1341.8	1379.3	1400.0	1431.6	1447.4	1479.9	1527.3	1540.1
15°	1206.6	1258.9	1288.5	1334.9	1384.2	1401.0	1444.4	1470.1	1537.2	1566.8	1602.3
17.5°	1180.0	1238.2	1277.7	1331.0	1379.3	1411.9	1454.3	1506.6	1562.8	1605.2	1644.7
20°	1158.3	1214.5	1261.9	1321.1	1382.3	1423.7	1468.1	1531.2	1592.4	1635.8	1666.4
22.5°	1109.0	1181.0	1236.2	1302.3	1376.3	1433.6	1476.0	1545.0	1611.2	1637.8	1664.4
25°	1084.3	1146.5	1210.6	1285.6	1372.4	1440.5	1477.0	1553.9	1612.1	1622.0	1627.9
27.5°	1038.9	1109.0	1183.9	1269.8	1371.4	1428.6	1475.0	1545.0	1591.4	1584.5	1566.8
30°	982.7	1068.5	1151.4	1244.1	1357.6	1419.7	1463.2	1527.3	1551.0	1515.5	1483.9
32.5°	941.2	1022.1	1113.9	1221.4	1341.8	1401.0	1443.4	1493.7	1498.7	1434.5	1381.3
35°	885.0	974.8	1078.4	1191.8	1315.2	1368.4	1407.9	1438.5	1414.8	1325.0	1261.9
37.5°	834.7	923.5	1034.0	1149.4	1278.7	1331.0	1362.5	1367.5	1309.2	1230.3	1137.6
40°	779.4	871.2	986.6	1108.0	1238.2	1283.6	1303.3	1288.5	1204.7	1112.9	1005.4
42.5°	724.2	814.9	939.3	1063.6	1186.9	1225.4	1233.3	1192.8	1090.2	982.7	858.4
45°	664.0	758.7	883.0	1008.3	1127.7	1149.4	1150.4	1092.2	970.8	858.4	742.9
47.5°	614.7	702.5	825.8	951.1	1051.7	1066.5	1060.6	993.5	861.3	735.0	634.4
50°	560.4	644.3	766.6	889.9	975.8	979.7	964.9	869.2	740.0	624.5	544.6
52.5°	502.2	587.0	699.5	817.9	894.9	888.9	860.3	757.7	636.4	540.7	479.5
55°	455.8	530.8	636.4	751.8	806.1	789.3	757.7	653.1	557.4	476.5	423.3
57.5°	404.5	470.6	574.2	674.8	706.4	690.6	659.1	561.4	472.6	411.4	375.9
60°	356.2	416.4	507.1	591.0	615.7	598.9	562.4	474.6	410.4	359.1	332.5
62.5°	311.8	364.1	440.0	517.0	526.9	510.1	478.5	407.5	352.2	311.8	292.0
65°	270.3	319.7	380.8	439.0	447.9	430.2	397.6	346.3	299.9	274.3	255.5
67.5°	229.9	269.3	323.6	366.0	371.0	354.2	327.6	286.1	257.5	229.9	216.1
70°	194.4	224.0	266.4	300.9	302.9	287.1	273.3	235.8	214.1	194.4	183.5
72.5°	159.8	180.6	213.1	238.8	239.7	229.9	217.1	193.4	174.6	160.8	150.0
75°	126.3	144.0	163.8	186.5	185.5	177.6	167.7	152.9	137.1	128.3	123.3
77.5°	96.7	107.5	123.3	138.1	138.1	134.2	128.3	117.4	107.5	98.7	93.7
80°	69.1	76.0	88.8	93.7	95.7	94.7	89.8	81.9	77.9	71.0	69.1
82.5°	44.4	49.3	55.3	60.2	63.1	61.2	60.2	56.2	50.3	48.3	46.4
85°	25.7	27.6	30.6	33.5	34.5	33.5	35.5	32.6	29.6	29.6	28.6
87.5°	10.9	11.8	13.8	13.8	14.8	14.8	13.8	14.8	14.8	13.8	12.8
90°	0.7	2.9	5.9	7.3	8.8	9.9	11.0	14.7	19.8	24.2	25.0
92.5°	11.0	15.4	21.3	25.0	30.8	34.8	38.9	58.7	86.6	111.6	113.1
95°	25.7	28.6	36.0	42.6	54.3	63.1	71.9	105.7	169.6	254.7	287.8
97.5°	38.2	42.6	50.7	60.2	73.4	83.3	93.2	136.6	225.4	362.7	469.1
100°	56.5	58.7	65.3	77.1	91.8	102.0	112.3	151.2	240.8	399.4	580.0
102.5°	73.4	74.9	81.5	93.2	108.7	119.0	129.2	164.4	241.5	385.4	583.6
105°	89.6	92.5	97.6	108.7	124.8	135.1	145.4	179.9	245.2	366.3	544.0
107.5°	107.2	109.4	114.5	124.8	141.0	151.2	161.5	195.3	253.3	356.1	507.3
110°	124.8	127.7	132.1	141.7	157.1	167.8	178.4	210.7	263.6	353.1	482.3

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	141.0	143.9	149.0	157.8	172.5	183.5	194.5	225.4	274.6	353.9	466.2
115°	157.8	161.5	165.9	174.7	189.4	199.3	209.2	240.8	285.6	356.8	455.2
117.5°	175.5	178.4	182.8	190.9	204.8	215.1	225.4	254.7	297.3	361.2	449.3
120°	191.6	194.5	199.0	205.6	220.2	230.5	240.8	269.4	309.1	365.6	444.2
122.5°	207.0	209.2	213.6	221.0	235.7	246.3	256.9	283.4	319.4	370.7	441.2
125°	220.2	222.4	226.9	235.7	250.3	260.6	270.9	297.3	330.4	375.9	437.5
127.5°	231.3	234.2	240.1	249.6	263.6	274.2	284.8	310.5	340.6	381.0	435.3
130°	240.8	243.7	251.1	261.4	276.0	286.3	296.6	322.3	350.2	386.9	433.9
132.5°	249.6	253.3	261.4	272.4	287.8	298.0	308.3	332.6	359.7	392.8	433.1
135°	258.4	261.4	270.2	281.2	298.1	308.4	318.6	342.1	367.8	397.2	432.4
137.5°	266.5	270.2	279.0	290.7	307.6	317.2	326.7	350.2	374.4	401.6	432.4
140°	276.0	279.0	287.8	299.5	315.7	325.2	334.8	356.8	379.6	404.5	431.7
142.5°	285.6	287.8	295.9	307.6	323.0	331.8	340.6	361.9	384.0	406.7	431.7
145°	295.1	298.1	305.4	316.4	331.1	339.2	347.2	367.1	387.6	408.2	430.2
147.5°	305.4	307.6	314.9	325.2	337.7	345.0	352.4	371.5	389.8	408.9	428.0
150°	315.7	317.9	323.8	333.3	344.3	350.9	357.5	374.4	391.3	408.2	425.8
152.5°	326.0	326.7	332.6	340.6	350.9	356.8	362.7	377.3	392.0	406.7	422.1
155°	335.5	336.2	340.6	348.7	356.8	362.3	367.8	380.3	392.8	405.2	417.7
157.5°	343.6	344.3	348.0	355.3	361.9	366.7	371.5	382.5	392.8	402.3	413.3
160°	351.7	352.4	355.3	361.2	367.1	371.1	375.1	384.0	392.8	400.1	408.9
162.5°	359.7	359.0	361.9	366.3	371.5	374.4	377.3	384.7	392.0	397.9	405.2
165°	365.6	364.9	366.3	370.7	374.4	376.6	378.8	385.4	390.6	395.0	400.1
167.5°	370.7	370.0	371.5	374.4	377.3	378.8	380.3	385.4	389.8	392.0	395.7
170°	375.9	374.4	375.1	377.3	378.8	379.9	381.0	384.7	388.4	389.8	392.0
172.5°	378.8	378.1	377.3	379.6	380.3	381.0	381.8	384.0	386.2	386.9	387.6
175°	381.0	380.3	379.6	381.0	381.0	381.4	381.8	383.2	384.7	384.0	384.7
177.5°	382.5	381.0	380.3	381.8	381.8	381.8	381.8	382.5	384.0	382.5	381.8
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1333.9	1334.9	1336.9	1346.7	1351.7	1352.7	1348.7	1357.6	1360.6	1357.6	1355.6
5°	1397.1	1403.0	1414.8	1427.6	1426.7	1427.6	1433.6	1439.5	1441.5	1433.6	1436.5
7.5°	1452.3	1464.1	1477.0	1496.7	1496.7	1506.6	1510.5	1515.5	1527.3	1521.4	1519.4
10°	1515.5	1531.2	1554.9	1586.5	1587.5	1597.3	1607.2	1623.0	1627.9	1624.0	1626.0
12.5°	1594.4	1625.0	1626.9	1661.5	1677.3	1679.2	1695.0	1692.1	1701.9	1701.9	1718.7
15°	1628.9	1676.3	1702.9	1736.5	1746.3	1734.5	1747.3	1761.1	1762.1	1762.1	1761.1
17.5°	1691.1	1709.8	1736.5	1754.2	1758.2	1758.2	1759.1	1765.1	1761.1	1753.2	1759.1
20°	1703.9	1711.8	1721.7	1719.7	1721.7	1711.8	1701.9	1692.1	1693.0	1688.1	1702.9
22.5°	1680.2	1678.2	1655.6	1640.8	1640.8	1621.0	1602.3	1593.4	1584.5	1587.5	1592.4
25°	1621.0	1590.4	1562.8	1541.1	1536.2	1504.6	1478.9	1471.1	1456.3	1468.1	1470.1
27.5°	1526.3	1491.8	1447.4	1428.6	1403.0	1390.1	1372.4	1348.7	1318.1	1335.9	1332.9
30°	1424.7	1373.4	1336.9	1291.5	1251.0	1248.1	1214.5	1175.1	1159.3	1159.3	1168.2
32.5°	1311.2	1243.1	1189.9	1125.7	1086.3	1069.5	1029.0	989.6	998.5	968.9	979.7
35°	1179.0	1089.2	1022.1	960.0	930.4	910.7	858.4	836.7	813.0	799.2	824.8
37.5°	1052.7	949.1	863.3	795.2	784.4	748.8	713.3	699.5	685.7	691.6	690.6
40°	898.8	807.1	730.1	676.8	658.1	641.3	617.6	600.9	592.0	596.9	597.9
42.5°	759.7	682.7	625.5	588.0	572.2	560.4	548.6	534.7	531.8	531.8	535.7
45°	652.2	589.0	550.5	519.9	511.1	502.2	493.3	487.4	485.4	481.5	484.4
47.5°	566.3	516.0	492.3	469.6	459.8	457.8	449.9	446.9	443.0	442.0	443.0
50°	494.3	462.7	441.0	428.2	421.3	418.3	414.4	408.5	406.5	411.4	409.4
52.5°	444.0	414.4	402.5	389.7	385.8	381.8	375.9	376.9	375.9	373.9	373.9
55°	393.7	374.9	363.1	353.2	352.2	348.3	343.3	341.4	340.4	338.4	341.4
57.5°	353.2	338.4	327.6	318.7	314.7	314.7	309.8	305.9	305.9	304.9	305.9
60°	312.8	298.0	291.1	282.2	279.2	278.2	275.3	273.3	270.3	270.3	270.3
62.5°	275.3	263.4	255.5	247.6	248.6	243.7	239.7	237.8	237.8	238.8	238.8
65°	239.7	231.9	222.0	215.1	213.1	212.1	210.2	209.2	206.2	208.2	208.2
67.5°	207.2	196.3	190.4	187.5	184.5	183.5	181.5	179.6	178.6	177.6	179.6
70°	174.6	165.8	160.8	158.8	155.9	154.9	153.9	151.0	151.9	152.9	153.9
72.5°	145.0	137.1	136.2	130.2	130.2	130.2	126.3	128.3	127.3	125.3	127.3
75°	114.4	110.5	108.5	105.6	106.6	105.6	104.6	101.6	101.6	102.6	103.6
77.5°	90.8	86.8	85.8	82.9	80.9	82.9	80.9	79.9	79.9	80.9	80.9
80°	67.1	65.1	62.2	62.2	62.2	61.2	61.2	61.2	60.2	59.2	60.2
82.5°	44.4	44.4	43.4	42.4	43.4	41.4	42.4	42.4	42.4	42.4	42.4
85°	28.6	27.6	27.6	26.6	26.6	26.6	27.6	25.7	25.7	26.6	26.6
87.5°	12.8	12.8	12.8	13.8	12.8	12.8	12.8	13.8	12.8	12.8	12.8
90°	24.2	23.5	22.0	23.5	23.8	24.2	24.2	24.2	24.2	24.2	24.2
92.5°	94.7	74.1	63.1	55.1	52.2	49.2	48.5	45.5	46.3	44.8	46.3
95°	251.8	192.3	147.6	116.7	108.6	100.6	91.0	85.2	83.0	83.7	83.0
97.5°	472.8	393.5	314.2	240.1	218.0	196.0	167.4	152.7	144.6	140.2	144.6
100°	685.7	670.3	579.2	478.7	434.2	389.8	328.9	297.3	276.0	262.8	276.0
102.5°	765.0	851.6	848.7	781.9	734.2	686.4	618.9	559.4	531.5	512.4	531.5
105°	739.3	892.0	974.9	984.5	972.4	960.3	914.7	869.2	837.7	827.4	837.7
107.5°	685.0	848.7	972.0	1044.0	1058.6	1073.3	1072.6	1066.0	1056.4	1039.5	1056.4
110°	634.3	789.2	920.6	1014.6	1044.7	1074.8	1106.4	1120.3	1126.9	1126.2	1126.9

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	599.1	734.9	859.7	961.7	997.3	1032.9	1079.9	1105.6	1119.6	1124.7	1119.6
115°	571.2	692.3	805.4	901.5	939.3	977.1	1029.3	1063.0	1082.1	1088.7	1082.1
117.5°	552.1	657.1	758.4	847.9	883.9	919.9	973.5	1009.4	1029.3	1034.4	1029.3
120°	537.4	632.1	723.1	800.9	834.4	867.8	919.1	953.7	974.9	982.3	974.9
122.5°	524.9	612.3	693.8	766.4	795.8	825.2	870.0	903.7	922.1	928.0	922.1
125°	513.2	593.2	668.8	733.4	761.0	788.5	831.0	858.9	877.3	883.2	877.3
127.5°	502.2	574.1	643.8	705.5	731.2	756.9	794.3	820.8	836.9	841.3	836.9
130°	491.1	555.7	618.9	676.9	701.1	725.3	761.3	786.3	800.9	806.8	800.9
132.5°	482.3	538.1	595.4	647.5	669.9	692.3	727.5	752.5	765.7	770.8	765.7
135°	474.3	522.0	570.4	618.9	639.4	660.0	691.6	715.8	729.0	731.9	729.0
137.5°	468.4	508.8	550.6	590.3	608.6	627.0	657.1	678.3	690.1	694.5	690.1
140°	463.2	496.3	531.5	565.3	581.4	597.6	621.1	640.2	651.2	655.6	651.2
142.5°	458.1	486.0	514.6	542.5	555.4	568.2	590.3	607.1	616.7	616.7	616.7
145°	453.7	476.5	500.7	523.4	534.0	544.7	562.4	574.8	582.2	584.4	582.2
147.5°	449.3	469.1	488.9	507.3	515.4	523.4	538.9	549.1	554.3	555.7	554.3
150°	443.4	461.0	477.2	492.6	499.2	505.8	516.8	525.6	530.1	530.8	530.1
152.5°	438.3	453.0	467.6	480.1	485.6	491.1	499.2	506.6	509.5	509.5	509.5
155°	431.7	445.6	457.4	468.4	472.4	476.5	484.5	489.7	492.6	491.1	492.6
157.5°	425.8	436.8	447.1	456.6	459.9	463.2	469.1	473.5	475.0	475.0	475.0
160°	419.2	428.7	436.8	444.9	447.4	450.0	455.2	458.8	459.6	459.6	459.6
162.5°	413.3	420.7	427.3	433.9	435.7	437.5	442.7	444.9	445.6	444.9	445.6
165°	406.7	412.6	417.7	422.9	424.4	425.8	428.7	431.7	431.7	430.9	431.7
167.5°	400.1	404.5	408.9	412.6	414.0	415.5	417.0	418.5	418.5	417.7	418.5
170°	395.0	398.6	400.8	403.8	404.5	405.2	406.0	408.2	407.4	406.0	407.4
172.5°	389.8	392.0	393.5	395.7	396.0	396.4	397.2	397.9	397.2	396.4	397.2
175°	385.4	387.6	388.4	389.1	389.5	389.8	389.8	390.6	389.8	388.4	389.8
177.5°	382.5	384.0	384.0	384.7	384.7	384.7	384.7	384.7	384.0	382.5	384.0
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1360.6	1353.6	1347.7	1348.7	1353.6	1349.7	1339.8	1327.0	1322.1	1316.2	1322.1
5°	1442.4	1436.5	1424.7	1425.7	1422.7	1418.8	1403.0	1383.2	1383.2	1367.5	1365.5
7.5°	1523.3	1514.5	1506.6	1504.6	1493.7	1485.9	1472.0	1444.4	1433.6	1414.8	1404.0
10°	1614.1	1607.2	1598.3	1587.5	1581.6	1567.7	1545.0	1504.6	1484.9	1459.2	1440.5
12.5°	1705.9	1704.9	1685.1	1663.4	1662.5	1640.8	1625.0	1570.7	1544.1	1509.5	1465.1
15°	1764.1	1759.1	1748.3	1737.4	1740.4	1716.7	1681.2	1617.1	1599.3	1557.9	1510.5
17.5°	1763.1	1763.1	1760.1	1758.2	1755.2	1748.3	1728.6	1686.1	1657.5	1605.2	1560.8
20°	1706.9	1719.7	1722.6	1721.7	1731.5	1736.5	1735.5	1708.8	1686.1	1639.8	1594.4
22.5°	1594.4	1624.0	1636.8	1644.7	1665.4	1676.3	1701.9	1692.1	1686.1	1651.6	1613.1
25°	1489.8	1499.7	1538.1	1540.1	1568.7	1595.4	1621.0	1637.8	1659.5	1646.7	1614.1
27.5°	1354.6	1377.3	1404.9	1425.7	1431.6	1485.9	1528.3	1559.8	1609.2	1613.1	1602.3
30°	1201.7	1212.6	1257.9	1285.6	1317.1	1356.6	1417.8	1472.0	1516.4	1556.9	1570.7
32.5°	1015.2	1059.6	1086.3	1119.8	1147.4	1217.5	1292.5	1362.5	1413.8	1481.9	1511.5
35°	844.5	879.1	924.5	938.3	988.6	1047.8	1145.5	1235.2	1313.2	1382.3	1442.4
37.5°	703.5	731.1	779.4	801.1	830.7	906.7	988.6	1100.1	1193.8	1278.7	1353.6
40°	606.8	627.5	664.0	670.9	695.6	764.6	830.7	935.3	1059.6	1174.1	1256.0
42.5°	540.7	550.5	575.2	584.1	599.9	646.2	705.4	804.1	919.5	1037.9	1153.4
45°	493.3	500.2	515.0	522.9	542.6	563.4	611.7	690.6	781.4	900.8	1025.1
47.5°	450.9	459.8	465.7	470.6	481.5	504.2	535.7	593.9	680.8	790.3	910.7
50°	415.4	418.3	429.2	430.2	437.1	451.9	481.5	517.0	586.1	674.8	791.3
52.5°	379.8	382.8	389.7	396.6	399.6	411.4	431.2	460.8	512.1	582.1	685.7
55°	344.3	348.3	355.2	360.1	363.1	372.9	384.8	413.4	453.8	503.2	588.0
57.5°	308.8	317.7	319.7	322.6	327.6	338.4	349.3	366.0	397.6	443.0	505.2
60°	275.3	278.2	285.1	288.1	293.0	298.9	312.8	325.6	348.3	383.8	440.0
62.5°	240.7	247.6	250.6	253.6	257.5	264.4	273.3	287.1	306.8	335.5	379.8
65°	211.1	212.1	218.0	222.0	225.9	230.9	239.7	252.6	264.4	291.1	323.6
67.5°	182.5	184.5	186.5	190.4	195.4	200.3	208.2	215.1	229.9	247.6	273.3
70°	154.9	154.9	159.8	162.8	161.8	167.7	173.6	181.5	192.4	209.2	229.9
72.5°	130.2	129.2	133.2	134.2	136.2	140.1	144.0	151.9	157.9	170.7	186.5
75°	103.6	105.6	107.5	107.5	110.5	113.5	117.4	121.4	128.3	136.2	148.0
77.5°	81.9	81.9	83.9	84.8	87.8	86.8	90.8	94.7	99.6	106.6	115.4
80°	60.2	62.2	62.2	62.2	63.1	64.1	68.1	71.0	74.0	78.9	82.9
82.5°	42.4	42.4	44.4	44.4	44.4	46.4	46.4	47.4	49.3	52.3	55.3
85°	26.6	26.6	26.6	27.6	26.6	27.6	29.6	28.6	29.6	31.6	31.6
87.5°	12.8	12.8	12.8	12.8	12.8	13.8	12.8	13.8	14.8	14.8	14.8
90°	24.2	24.2	24.2	23.8	23.5	22.0	23.5	24.2	25.0	24.2	19.8
92.5°	45.5	48.5	49.2	52.2	55.1	63.1	74.1	94.7	113.1	111.6	86.6
95°	85.2	91.0	100.6	108.6	116.7	147.6	192.3	251.8	287.8	254.7	169.6
97.5°	152.7	167.4	196.0	218.0	240.1	314.2	393.5	472.8	469.1	362.7	225.4
100°	297.3	328.9	389.8	434.2	478.7	579.2	670.3	685.7	580.0	399.4	240.8
102.5°	559.4	618.9	686.4	734.2	781.9	848.7	851.6	765.0	583.6	385.4	241.5
105°	869.2	914.7	960.3	972.4	984.5	974.9	892.0	739.3	544.0	366.3	245.2
107.5°	1066.0	1072.6	1073.3	1058.6	1044.0	972.0	848.7	685.0	507.3	356.1	253.3
110°	1120.3	1106.4	1074.8	1044.7	1014.6	920.6	789.2	634.3	482.3	353.1	263.6

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1105.6	1079.9	1032.9	997.3	961.7	859.7	734.9	599.1	466.2	353.9	274.6
115°	1063.0	1029.3	977.1	939.3	901.5	805.4	692.3	571.2	455.2	356.8	285.6
117.5°	1009.4	973.5	919.9	883.9	847.9	758.4	657.1	552.1	449.3	361.2	297.3
120°	953.7	919.1	867.8	834.4	800.9	723.1	632.1	537.4	444.2	365.6	309.1
122.5°	903.7	870.0	825.2	795.8	766.4	693.8	612.3	524.9	441.2	370.7	319.4
125°	858.9	831.0	788.5	761.0	733.4	668.8	593.2	513.2	437.5	375.9	330.4
127.5°	820.8	794.3	756.9	731.2	705.5	643.8	574.1	502.2	435.3	381.0	340.6
130°	786.3	761.3	725.3	701.1	676.9	618.9	555.7	491.1	433.9	386.9	350.2
132.5°	752.5	727.5	692.3	669.9	647.5	595.4	538.1	482.3	433.1	392.8	359.7
135°	715.8	691.6	660.0	639.4	618.9	570.4	522.0	474.3	432.4	397.2	367.8
137.5°	678.3	657.1	627.0	608.6	590.3	550.6	508.8	468.4	432.4	401.6	374.4
140°	640.2	621.1	597.6	581.4	565.3	531.5	496.3	463.2	431.7	404.5	379.6
142.5°	607.1	590.3	568.2	555.4	542.5	514.6	486.0	458.1	431.7	406.7	384.0
145°	574.8	562.4	544.7	534.0	523.4	500.7	476.5	453.7	430.2	408.2	387.6
147.5°	549.1	538.9	523.4	515.4	507.3	488.9	469.1	449.3	428.0	408.9	389.8
150°	525.6	516.8	505.8	499.2	492.6	477.2	461.0	443.4	425.8	408.2	391.3
152.5°	506.6	499.2	491.1	485.6	480.1	467.6	453.0	438.3	422.1	406.7	392.0
155°	489.7	484.5	476.5	472.4	468.4	457.4	445.6	431.7	417.7	405.2	392.8
157.5°	473.5	469.1	463.2	459.9	456.6	447.1	436.8	425.8	413.3	402.3	392.8
160°	458.8	455.2	450.0	447.4	444.9	436.8	428.7	419.2	408.9	400.1	392.8
162.5°	444.9	442.7	437.5	435.7	433.9	427.3	420.7	413.3	405.2	397.9	392.0
165°	431.7	428.7	425.8	424.4	422.9	417.7	412.6	406.7	400.1	395.0	390.6
167.5°	418.5	417.0	415.5	414.0	412.6	408.9	404.5	400.1	395.7	392.0	389.8
170°	408.2	406.0	405.2	404.5	403.8	400.8	398.6	395.0	392.0	389.8	388.4
172.5°	397.9	397.2	396.4	396.0	395.7	393.5	392.0	389.8	387.6	386.9	386.2
175°	390.6	389.8	389.8	389.5	389.1	388.4	387.6	385.4	384.7	384.0	384.7
177.5°	384.7	384.7	384.7	384.7	384.7	384.0	384.0	382.5	381.8	382.5	384.0
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1317.1	1312.2	1309.2	1311.2	1305.3	1290.5	1290.5	1295.4	1289.5	1283.6	1274.7
5°	1353.6	1343.8	1337.9	1336.9	1323.1	1299.4	1294.4	1289.5	1276.7	1262.9	1248.1
7.5°	1389.2	1371.4	1361.5	1354.6	1334.9	1304.3	1291.5	1280.6	1259.9	1239.2	1220.5
10°	1418.8	1393.1	1381.3	1370.4	1344.8	1306.3	1285.6	1265.8	1239.2	1212.6	1188.9
12.5°	1442.4	1412.8	1398.0	1382.3	1350.7	1300.4	1274.7	1243.1	1216.5	1181.0	1157.3
15°	1481.9	1420.7	1406.9	1392.1	1359.6	1290.5	1258.9	1223.4	1186.9	1139.5	1113.9
17.5°	1513.5	1431.6	1430.6	1399.0	1356.6	1286.6	1238.2	1191.8	1152.4	1105.0	1064.6
20°	1532.2	1448.4	1432.6	1400.0	1346.7	1259.9	1209.6	1158.3	1115.9	1058.6	1018.2
22.5°	1548.0	1472.0	1430.6	1391.1	1326.0	1251.0	1177.0	1128.7	1070.5	1008.3	969.8
25°	1553.9	1477.0	1433.6	1388.2	1311.2	1225.4	1141.5	1089.2	1024.1	967.9	915.6
27.5°	1554.9	1476.0	1422.7	1375.4	1290.5	1191.8	1106.0	1050.8	978.7	913.6	861.3
30°	1545.0	1465.1	1416.8	1365.5	1270.8	1161.3	1062.6	1001.4	924.5	859.3	805.1
32.5°	1515.5	1443.4	1404.0	1347.7	1245.1	1118.8	1021.2	953.1	872.2	808.0	755.8
35°	1466.1	1416.8	1373.4	1321.1	1211.6	1079.4	979.7	899.8	817.9	756.7	707.4
37.5°	1404.9	1378.3	1337.9	1286.6	1173.1	1043.8	933.3	844.5	762.7	703.5	655.1
40°	1322.1	1329.0	1289.5	1243.1	1127.7	995.5	873.2	788.3	711.4	656.1	608.7
42.5°	1232.3	1260.9	1238.2	1193.8	1077.4	942.2	828.8	735.0	660.0	602.8	563.4
45°	1135.6	1184.9	1171.1	1138.6	1025.1	886.0	765.6	674.8	608.7	553.5	519.0
47.5°	1030.0	1100.1	1100.1	1076.4	966.9	829.7	711.4	618.6	553.5	514.0	480.5
50°	922.5	1001.4	1014.2	998.5	901.8	765.6	645.3	561.4	505.2	466.7	442.0
52.5°	810.0	901.8	925.5	917.6	832.7	704.4	591.0	509.1	457.8	424.2	402.5
55°	702.5	809.0	834.7	837.6	758.7	637.4	530.8	458.8	409.4	386.8	368.0
57.5°	600.9	703.5	732.1	737.0	683.7	576.2	474.6	411.4	367.0	348.3	333.5
60°	514.0	599.9	637.4	648.2	601.8	505.2	422.3	361.1	327.6	309.8	296.0
62.5°	443.0	512.1	551.5	554.5	533.8	443.0	368.0	316.7	288.1	272.3	265.4
65°	373.9	436.1	459.8	471.6	454.8	383.8	317.7	275.3	252.6	238.8	231.9
67.5°	318.7	358.1	377.9	393.7	376.9	323.6	270.3	235.8	219.0	205.2	201.3
70°	261.5	294.0	308.8	324.6	309.8	269.3	230.9	199.3	184.5	173.6	168.7
72.5°	209.2	234.8	248.6	258.5	249.6	216.1	184.5	162.8	151.9	144.0	141.1
75°	165.8	183.5	191.4	198.3	194.4	168.7	149.0	131.2	121.4	114.4	112.5
77.5°	126.3	139.1	148.0	150.0	145.0	128.3	111.5	100.6	92.7	88.8	86.8
80°	89.8	97.7	102.6	105.6	100.6	93.7	81.9	74.0	67.1	62.2	61.2
82.5°	60.2	64.1	68.1	67.1	65.1	59.2	52.3	48.3	45.4	41.4	41.4
85°	34.5	35.5	37.5	38.5	37.5	33.5	29.6	27.6	25.7	22.7	22.7
87.5°	14.8	15.8	15.8	16.8	14.8	14.8	12.8	10.9	10.9	9.9	8.9
90°	14.7	11.0	9.9	8.8	7.3	5.9	2.9	0.7	2.9	5.9	7.3
92.5°	58.7	38.9	34.8	30.8	25.0	21.3	15.4	11.0	15.4	21.3	25.0
95°	105.7	71.9	63.1	54.3	42.6	36.0	28.6	25.7	28.6	36.0	42.6
97.5°	136.6	93.2	83.3	73.4	60.2	50.7	42.6	38.2	42.6	50.7	60.2
100°	151.2	112.3	102.0	91.8	77.1	65.3	58.7	56.5	58.7	65.3	77.1
102.5°	164.4	129.2	119.0	108.7	93.2	81.5	74.9	73.4	74.9	81.5	93.2
105°	179.9	145.4	135.1	124.8	108.7	97.6	92.5	89.6	92.5	97.6	108.7
107.5°	195.3	161.5	151.2	141.0	124.8	114.5	109.4	107.2	109.4	114.5	124.8
110°	210.7	178.4	167.8	157.1	141.7	132.1	127.7	124.8	127.7	132.1	141.7

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	225.4	194.5	183.5	172.5	157.8	149.0	143.9	141.0	143.9	149.0	157.8
115°	240.8	209.2	199.3	189.4	174.7	165.9	161.5	157.8	161.5	165.9	174.7
117.5°	254.7	225.4	215.1	204.8	190.9	182.8	178.4	175.5	178.4	182.8	190.9
120°	269.4	240.8	230.5	220.2	205.6	199.0	194.5	191.6	194.5	199.0	205.6
122.5°	283.4	256.9	246.3	235.7	221.0	213.6	209.2	207.0	209.2	213.6	221.0
125°	297.3	270.9	260.6	250.3	235.7	226.9	222.4	220.2	222.4	226.9	235.7
127.5°	310.5	284.8	274.2	263.6	249.6	240.1	234.2	231.3	234.2	240.1	249.6
130°	322.3	296.6	286.3	276.0	261.4	251.1	243.7	240.8	243.7	251.1	261.4
132.5°	332.6	308.3	298.0	287.8	272.4	261.4	253.3	249.6	253.3	261.4	272.4
135°	342.1	318.6	308.4	298.1	281.2	270.2	261.4	258.4	261.4	270.2	281.2
137.5°	350.2	326.7	317.2	307.6	290.7	279.0	270.2	266.5	270.2	279.0	290.7
140°	356.8	334.8	325.2	315.7	299.5	287.8	279.0	276.0	279.0	287.8	299.5
142.5°	361.9	340.6	331.8	323.0	307.6	295.9	287.8	285.6	287.8	295.9	307.6
145°	367.1	347.2	339.2	331.1	316.4	305.4	298.1	295.1	298.1	305.4	316.4
147.5°	371.5	352.4	345.0	337.7	325.2	314.9	307.6	305.4	307.6	314.9	325.2
150°	374.4	357.5	350.9	344.3	333.3	323.8	317.9	315.7	317.9	323.8	333.3
152.5°	377.3	362.7	356.8	350.9	340.6	332.6	326.7	326.0	326.7	332.6	340.6
155°	380.3	367.8	362.3	356.8	348.7	340.6	336.2	335.5	336.2	340.6	348.7
157.5°	382.5	371.5	366.7	361.9	355.3	348.0	344.3	343.6	344.3	348.0	355.3
160°	384.0	375.1	371.1	367.1	361.2	355.3	352.4	351.7	352.4	355.3	361.2
162.5°	384.7	377.3	374.4	371.5	366.3	361.9	359.0	359.7	359.0	361.9	366.3
165°	385.4	378.8	376.6	374.4	370.7	366.3	364.9	365.6	364.9	366.3	370.7
167.5°	385.4	380.3	378.8	377.3	374.4	371.5	370.0	370.7	370.0	371.5	374.4
170°	384.7	381.0	379.9	378.8	377.3	375.1	374.4	375.9	374.4	375.1	377.3
172.5°	384.0	381.8	381.0	380.3	379.6	377.3	378.1	378.8	378.1	377.3	379.6
175°	383.2	381.8	381.4	381.0	381.0	379.6	380.3	381.0	380.3	379.6	381.0
177.5°	382.5	381.8	381.8	381.8	381.8	380.3	381.0	382.5	381.0	380.3	381.8
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1269.8	1274.7	1273.7	1263.9	1253.0	1244.1	1227.4	1229.3	1223.4	1224.4	1230.3
5°	1238.2	1238.2	1234.3	1220.5	1202.7	1192.8	1174.1	1169.1	1157.3	1156.3	1155.3
7.5°	1204.7	1199.7	1194.8	1175.1	1153.4	1137.6	1111.9	1106.0	1094.2	1086.3	1082.3
10°	1165.2	1158.3	1148.4	1125.7	1099.1	1079.4	1052.7	1044.8	1022.1	1012.3	1006.4
12.5°	1121.8	1117.8	1102.1	1083.3	1039.9	1018.2	979.7	987.6	964.9	945.2	942.2
15°	1078.4	1063.6	1054.7	1024.1	971.8	962.0	931.4	915.6	894.9	879.1	879.1
17.5°	1036.0	1013.3	993.5	961.0	922.5	894.9	872.2	864.3	838.6	822.8	819.9
20°	979.7	954.1	949.1	902.8	876.1	845.5	823.8	804.1	785.4	778.4	773.5
22.5°	926.4	896.8	888.9	849.5	822.8	792.3	770.6	756.7	742.9	738.0	729.1
25°	869.2	851.5	839.6	797.2	767.6	739.0	724.2	714.3	701.5	700.5	694.6
27.5°	814.0	797.2	785.4	744.9	723.2	696.6	684.7	673.9	667.0	664.0	661.0
30°	766.6	747.9	734.0	704.4	677.8	656.1	646.2	639.3	635.4	630.5	629.5
32.5°	714.3	703.5	684.7	662.0	641.3	620.6	614.7	609.7	603.8	601.8	600.9
35°	669.9	655.1	643.3	617.6	608.7	591.0	584.1	580.1	572.2	570.3	568.3
37.5°	626.5	612.7	599.9	584.1	567.3	557.4	553.5	547.6	543.6	544.6	542.6
40°	583.1	572.2	562.4	545.6	535.7	530.8	522.9	517.0	515.0	516.0	515.0
42.5°	540.7	530.8	524.9	512.1	502.2	497.3	492.3	486.4	489.4	489.4	492.3
45°	502.2	493.3	489.4	479.5	473.6	465.7	460.8	459.8	463.7	462.7	462.7
47.5°	462.7	459.8	454.8	446.0	438.1	433.1	432.1	432.1	436.1	438.1	437.1
50°	432.1	426.2	420.3	413.4	407.5	405.5	402.5	404.5	408.5	408.5	410.4
52.5°	393.7	389.7	387.7	381.8	377.9	377.9	377.9	378.9	381.8	384.8	383.8
55°	360.1	357.2	355.2	352.2	347.3	348.3	347.3	349.3	352.2	355.2	357.2
57.5°	324.6	323.6	321.6	316.7	316.7	315.7	318.7	319.7	324.6	326.6	329.5
60°	293.0	290.1	290.1	286.1	286.1	286.1	289.1	292.0	296.0	297.0	298.9
62.5°	259.5	259.5	258.5	255.5	255.5	258.5	259.5	263.4	265.4	265.4	268.4
65°	227.9	226.9	225.9	226.9	227.9	227.9	230.9	232.8	234.8	235.8	236.8
67.5°	196.3	195.4	197.3	196.3	198.3	202.3	201.3	204.2	207.2	207.2	208.2
70°	166.7	168.7	167.7	169.7	168.7	170.7	173.6	174.6	174.6	175.6	178.6
72.5°	139.1	139.1	139.1	138.1	139.1	141.1	143.1	144.0	146.0	147.0	150.0
75°	112.5	112.5	110.5	112.5	112.5	114.4	116.4	116.4	116.4	118.4	121.4
77.5°	84.8	85.8	84.8	86.8	86.8	87.8	89.8	88.8	90.8	91.8	92.7
80°	62.2	61.2	61.2	61.2	62.2	62.2	64.1	65.1	65.1	68.1	66.1
82.5°	39.5	40.5	39.5	40.5	40.5	41.4	40.5	41.4	42.4	44.4	43.4
85°	22.7	21.7	21.7	22.7	21.7	21.7	22.7	21.7	22.7	21.7	22.7
87.5°	8.9	7.9	7.9	7.9	7.9	6.9	6.9	5.9	5.9	5.9	4.9
90°	8.8	9.9	11.0	14.7	19.8	24.2	25.0	24.2	23.5	22.0	23.5
92.5°	30.8	34.8	38.9	58.7	86.6	111.6	113.1	94.7	74.1	63.1	55.1
95°	54.3	63.1	71.9	105.7	169.6	254.7	287.8	251.8	192.3	147.6	116.7
97.5°	73.4	83.3	93.2	136.6	225.4	362.7	469.1	472.8	393.5	314.2	240.1
100°	91.8	102.0	112.3	151.2	240.8	399.4	580.0	685.7	670.3	579.2	478.7
102.5°	108.7	119.0	129.2	164.4	241.5	385.4	583.6	765.0	851.6	848.7	781.9
105°	124.8	135.1	145.4	179.9	245.2	366.3	544.0	739.3	892.0	974.9	984.5
107.5°	141.0	151.2	161.5	195.3	253.3	356.1	507.3	685.0	848.7	972.0	1044.0
110°	157.1	167.8	178.4	210.7	263.6	353.1	482.3	634.3	789.2	920.6	1014.6

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	172.5	183.5	194.5	225.4	274.6	353.9	466.2	599.1	734.9	859.7	961.7
115°	189.4	199.3	209.2	240.8	285.6	356.8	455.2	571.2	692.3	805.4	901.5
117.5°	204.8	215.1	225.4	254.7	297.3	361.2	449.3	552.1	657.1	758.4	847.9
120°	220.2	230.5	240.8	269.4	309.1	365.6	444.2	537.4	632.1	723.1	800.9
122.5°	235.7	246.3	256.9	283.4	319.4	370.7	441.2	524.9	612.3	693.8	766.4
125°	250.3	260.6	270.9	297.3	330.4	375.9	437.5	513.2	593.2	668.8	733.4
127.5°	263.6	274.2	284.8	310.5	340.6	381.0	435.3	502.2	574.1	643.8	705.5
130°	276.0	286.3	296.6	322.3	350.2	386.9	433.9	491.1	555.7	618.9	676.9
132.5°	287.8	298.0	308.3	332.6	359.7	392.8	433.1	482.3	538.1	595.4	647.5
135°	298.1	308.4	318.6	342.1	367.8	397.2	432.4	474.3	522.0	570.4	618.9
137.5°	307.6	317.2	326.7	350.2	374.4	401.6	432.4	468.4	508.8	550.6	590.3
140°	315.7	325.2	334.8	356.8	379.6	404.5	431.7	463.2	496.3	531.5	565.3
142.5°	323.0	331.8	340.6	361.9	384.0	406.7	431.7	458.1	486.0	514.6	542.5
145°	331.1	339.2	347.2	367.1	387.6	408.2	430.2	453.7	476.5	500.7	523.4
147.5°	337.7	345.0	352.4	371.5	389.8	408.9	428.0	449.3	469.1	488.9	507.3
150°	344.3	350.9	357.5	374.4	391.3	408.2	425.8	443.4	461.0	477.2	492.6
152.5°	350.9	356.8	362.7	377.3	392.0	406.7	422.1	438.3	453.0	467.6	480.1
155°	356.8	362.3	367.8	380.3	392.8	405.2	417.7	431.7	445.6	457.4	468.4
157.5°	361.9	366.7	371.5	382.5	392.8	402.3	413.3	425.8	436.8	447.1	456.6
160°	367.1	371.1	375.1	384.0	392.8	400.1	408.9	419.2	428.7	436.8	444.9
162.5°	371.5	374.4	377.3	384.7	392.0	397.9	405.2	413.3	420.7	427.3	433.9
165°	374.4	376.6	378.8	385.4	390.6	395.0	400.1	406.7	412.6	417.7	422.9
167.5°	377.3	378.8	380.3	385.4	389.8	392.0	395.7	400.1	404.5	408.9	412.6
170°	378.8	379.9	381.0	384.7	388.4	389.8	392.0	395.0	398.6	400.8	403.8
172.5°	380.3	381.0	381.8	384.0	386.2	386.9	387.6	389.8	392.0	393.5	395.7
175°	381.0	381.4	381.8	383.2	384.7	384.0	384.7	385.4	387.6	388.4	389.1
177.5°	381.8	381.8	381.8	382.5	384.0	382.5	381.8	382.5	384.0	384.0	384.7
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1223.4	1226.4	1219.5	1217.5	1219.5	1212.6	1214.5	1216.5	1216.5	1219.5	1221.4
5°	1152.4	1148.4	1141.5	1139.5	1137.6	1140.5	1138.6	1141.5	1142.5	1149.4	1150.4
7.5°	1082.3	1076.4	1070.5	1064.6	1062.6	1057.7	1062.6	1062.6	1069.5	1067.5	1072.5
10°	999.4	998.5	990.6	987.6	983.7	975.8	986.6	983.7	988.6	997.5	999.4
12.5°	938.3	927.4	932.4	918.5	923.5	915.6	916.6	916.6	924.5	925.5	923.5
15°	880.1	871.2	858.4	852.4	849.5	845.5	858.4	859.3	853.4	867.2	862.3
17.5°	820.9	820.9	809.0	806.1	798.2	802.1	800.1	801.1	799.2	809.0	814.0
20°	769.6	764.6	760.7	761.7	751.8	749.8	747.9	749.8	756.7	763.6	765.6
22.5°	728.1	725.2	715.3	717.3	709.4	712.3	710.4	715.3	716.3	716.3	723.2
25°	688.7	684.7	685.7	681.8	678.8	678.8	675.8	678.8	682.7	684.7	685.7
27.5°	659.1	656.1	651.2	648.2	650.2	645.3	649.2	652.2	652.2	650.2	652.2
30°	623.5	625.5	625.5	615.7	619.6	617.6	620.6	622.6	622.6	623.5	621.6
32.5°	599.9	593.9	593.0	592.0	592.0	588.0	588.0	591.0	592.0	593.0	595.9
35°	568.3	568.3	563.4	566.3	562.4	563.4	562.4	563.4	565.3	562.4	565.3
37.5°	539.7	540.7	538.7	540.7	541.7	539.7	537.7	541.7	539.7	539.7	537.7
40°	515.0	514.0	515.0	515.0	515.0	516.0	514.0	514.0	514.0	512.1	510.1
42.5°	494.3	488.4	490.4	491.3	488.4	488.4	489.4	488.4	491.3	485.4	485.4
45°	464.7	462.7	463.7	463.7	465.7	462.7	464.7	465.7	462.7	461.7	459.8
47.5°	438.1	440.0	438.1	440.0	440.0	442.0	438.1	439.0	440.0	436.1	433.1
50°	411.4	411.4	414.4	413.4	414.4	412.4	412.4	411.4	412.4	410.4	407.5
52.5°	386.8	383.8	388.7	387.7	386.8	385.8	384.8	385.8	383.8	381.8	381.8
55°	356.2	356.2	359.1	360.1	360.1	358.1	356.2	357.2	356.2	355.2	354.2
57.5°	331.5	327.6	329.5	330.5	330.5	327.6	329.5	327.6	327.6	328.5	325.6
60°	299.9	299.9	298.0	300.9	300.9	298.9	298.9	299.9	298.0	297.0	296.0
62.5°	266.4	267.4	270.3	271.3	272.3	270.3	268.4	269.3	269.3	266.4	267.4
65°	237.8	239.7	243.7	242.7	240.7	241.7	239.7	240.7	237.8	238.8	235.8
67.5°	210.2	209.2	210.2	210.2	212.1	211.1	209.2	209.2	208.2	211.1	208.2
70°	180.6	180.6	180.6	180.6	181.5	182.5	180.6	178.6	179.6	177.6	176.6
72.5°	150.0	151.0	150.0	151.9	149.0	151.0	151.0	150.0	149.0	149.0	149.0
75°	121.4	123.3	120.4	121.4	120.4	122.3	121.4	121.4	119.4	118.4	119.4
77.5°	92.7	93.7	91.8	92.7	91.8	92.7	92.7	91.8	91.8	91.8	91.8
80°	66.1	67.1	66.1	65.1	64.1	66.1	64.1	65.1	66.1	65.1	67.1
82.5°	42.4	42.4	41.4	42.4	40.5	40.5	41.4	41.4	40.5	42.4	40.5
85°	20.7	20.7	22.7	20.7	19.7	19.7	19.7	20.7	19.7	21.7	20.7
87.5°	4.9	3.9	4.9	4.9	3.9	3.9	4.9	3.9	4.9	5.9	3.9
90°	23.8	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	23.8
92.5°	52.2	49.2	48.5	45.5	46.3	44.8	46.3	45.5	48.5	49.2	52.2
95°	108.6	100.6	91.0	85.2	83.0	83.7	83.0	85.2	91.0	100.6	108.6
97.5°	218.0	196.0	167.4	152.7	144.6	140.2	144.6	152.7	167.4	196.0	218.0
100°	434.2	389.8	328.9	297.3	276.0	262.8	276.0	297.3	328.9	389.8	434.2
102.5°	734.2	686.4	618.9	559.4	531.5	512.4	531.5	559.4	618.9	686.4	734.2
105°	972.4	960.3	914.7	869.2	837.7	827.4	837.7	869.2	914.7	960.3	972.4
107.5°	1058.6	1073.3	1072.6	1066.0	1056.4	1039.5	1056.4	1066.0	1072.6	1073.3	1058.6
110°	1044.7	1074.8	1106.4	1120.3	1126.9	1126.2	1126.9	1120.3	1106.4	1074.8	1044.7

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	997.3	1032.9	1079.9	1105.6	1119.6	1124.7	1119.6	1105.6	1079.9	1032.9	997.3
115°	939.3	977.1	1029.3	1063.0	1082.1	1088.7	1082.1	1063.0	1029.3	977.1	939.3
117.5°	883.9	919.9	973.5	1009.4	1029.3	1034.4	1029.3	1009.4	973.5	919.9	883.9
120°	834.4	867.8	919.1	953.7	974.9	982.3	974.9	953.7	919.1	867.8	834.4
122.5°	795.8	825.2	870.0	903.7	922.1	928.0	922.1	903.7	870.0	825.2	795.8
125°	761.0	788.5	831.0	858.9	877.3	883.2	877.3	858.9	831.0	788.5	761.0
127.5°	731.2	756.9	794.3	820.8	836.9	841.3	836.9	820.8	794.3	756.9	731.2
130°	701.1	725.3	761.3	786.3	800.9	806.8	800.9	786.3	761.3	725.3	701.1
132.5°	669.9	692.3	727.5	752.5	765.7	770.8	765.7	752.5	727.5	692.3	669.9
135°	639.4	660.0	691.6	715.8	729.0	731.9	729.0	715.8	691.6	660.0	639.4
137.5°	608.6	627.0	657.1	678.3	690.1	694.5	690.1	678.3	657.1	627.0	608.6
140°	581.4	597.6	621.1	640.2	651.2	655.6	651.2	640.2	621.1	597.6	581.4
142.5°	555.4	568.2	590.3	607.1	616.7	616.7	616.7	607.1	590.3	568.2	555.4
145°	534.0	544.7	562.4	574.8	582.2	584.4	582.2	574.8	562.4	544.7	534.0
147.5°	515.4	523.4	538.9	549.1	554.3	555.7	554.3	549.1	538.9	523.4	515.4
150°	499.2	505.8	516.8	525.6	530.1	530.8	530.1	525.6	516.8	505.8	499.2
152.5°	485.6	491.1	499.2	506.6	509.5	509.5	509.5	506.6	499.2	491.1	485.6
155°	472.4	476.5	484.5	489.7	492.6	491.1	492.6	489.7	484.5	476.5	472.4
157.5°	459.9	463.2	469.1	473.5	475.0	475.0	475.0	473.5	469.1	463.2	459.9
160°	447.4	450.0	455.2	458.8	459.6	459.6	459.6	458.8	455.2	450.0	447.4
162.5°	435.7	437.5	442.7	444.9	445.6	444.9	445.6	444.9	442.7	437.5	435.7
165°	424.4	425.8	428.7	431.7	431.7	430.9	431.7	431.7	428.7	425.8	424.4
167.5°	414.0	415.5	417.0	418.5	418.5	417.7	418.5	418.5	417.0	415.5	414.0
170°	404.5	405.2	406.0	408.2	407.4	406.0	407.4	408.2	406.0	405.2	404.5
172.5°	396.0	396.4	397.2	397.9	397.2	396.4	397.2	397.9	397.2	396.4	396.0
175°	389.5	389.8	389.8	390.6	389.8	388.4	389.8	390.6	389.8	389.8	389.5
177.5°	384.7	384.7	384.7	384.7	384.0	382.5	384.0	384.7	384.7	384.7	384.7
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1218.5	1226.4	1223.4	1212.6	1225.4	1225.4	1234.3	1234.3	1245.1	1249.1	1255.0
5°	1149.4	1155.3	1160.3	1155.3	1164.2	1178.0	1185.9	1192.8	1207.6	1213.5	1222.4
7.5°	1075.4	1086.3	1091.2	1091.2	1106.0	1121.8	1137.6	1147.4	1168.2	1176.1	1184.9
10°	1003.4	1016.2	1026.1	1025.1	1049.8	1059.6	1079.4	1102.1	1122.8	1134.6	1147.4
12.5°	927.4	934.3	948.1	967.9	973.8	991.6	1014.2	1042.9	1080.4	1091.2	1109.9
15°	864.3	883.0	893.9	902.8	916.6	933.3	958.0	985.6	1023.1	1046.8	1066.5
17.5°	811.0	835.7	842.6	840.6	858.4	884.0	912.6	933.3	966.9	995.5	1014.2
20°	767.6	777.5	789.3	794.2	808.0	835.7	863.3	887.0	914.6	937.3	959.0
22.5°	724.2	732.1	741.9	750.8	761.7	777.5	804.1	833.7	860.3	882.0	906.7
25°	688.7	693.6	702.5	709.4	721.2	732.1	750.8	783.4	814.9	827.8	849.5
27.5°	654.1	658.1	664.0	671.9	677.8	688.7	705.4	732.1	764.6	777.5	807.1
30°	623.5	626.5	632.4	636.4	639.3	652.2	665.0	685.7	710.4	728.1	749.8
32.5°	594.9	597.9	603.8	604.8	608.7	615.7	627.5	646.2	667.9	682.7	701.5
35°	563.4	565.3	571.3	573.2	576.2	582.1	591.0	604.8	624.5	635.4	652.2
37.5°	538.7	537.7	541.7	544.6	548.6	551.5	554.5	568.3	583.1	593.0	605.8
40°	512.1	510.1	511.1	515.0	517.0	520.9	520.9	534.7	544.6	552.5	562.4
42.5°	485.4	484.4	482.5	484.4	486.4	487.4	488.4	498.2	508.1	515.0	525.9
45°	458.8	457.8	455.8	456.8	456.8	458.8	461.7	465.7	472.6	478.5	484.4
47.5°	434.1	432.1	429.2	428.2	430.2	430.2	430.2	434.1	441.0	443.0	448.9
50°	408.5	405.5	401.6	399.6	399.6	398.6	400.6	401.6	407.5	409.4	414.4
52.5°	380.8	378.9	374.9	371.0	372.0	370.0	371.0	372.0	373.9	376.9	379.8
55°	353.2	349.3	346.3	345.3	342.4	342.4	339.4	343.3	342.4	343.3	347.3
57.5°	326.6	322.6	317.7	315.7	312.8	311.8	309.8	308.8	309.8	312.8	315.7
60°	295.0	293.0	290.1	287.1	285.1	282.2	280.2	280.2	279.2	279.2	280.2
62.5°	264.4	263.4	259.5	258.5	256.5	254.5	251.6	249.6	249.6	251.6	252.6
65°	234.8	233.8	230.9	229.9	224.9	223.0	222.0	221.0	219.0	219.0	219.0
67.5°	207.2	204.2	204.2	199.3	195.4	193.4	191.4	190.4	190.4	190.4	191.4
70°	176.6	176.6	173.6	170.7	166.7	167.7	164.8	161.8	161.8	159.8	160.8
72.5°	147.0	146.0	143.1	142.1	139.1	136.2	134.2	136.2	133.2	132.2	133.2
75°	118.4	117.4	115.4	113.5	114.4	111.5	108.5	107.5	107.5	105.6	105.6
77.5°	90.8	92.7	88.8	87.8	85.8	83.9	82.9	81.9	81.9	81.9	83.9
80°	63.1	64.1	64.1	62.2	63.1	60.2	60.2	60.2	57.2	58.2	59.2
82.5°	40.5	40.5	39.5	40.5	39.5	39.5	38.5	38.5	37.5	37.5	38.5
85°	22.7	21.7	20.7	22.7	21.7	21.7	20.7	20.7	20.7	20.7	20.7
87.5°	4.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9
90°	23.5	22.0	23.5	24.2	25.0	24.2	19.8	14.7	11.0	9.9	8.8
92.5°	55.1	63.1	74.1	94.7	113.1	111.6	86.6	58.7	38.9	34.8	30.8
95°	116.7	147.6	192.3	251.8	287.8	254.7	169.6	105.7	71.9	63.1	54.3
97.5°	240.1	314.2	393.5	472.8	469.1	362.7	225.4	136.6	93.2	83.3	73.4
100°	478.7	579.2	670.3	685.7	580.0	399.4	240.8	151.2	112.3	102.0	91.8
102.5°	781.9	848.7	851.6	765.0	583.6	385.4	241.5	164.4	129.2	119.0	108.7
105°	984.5	974.9	892.0	739.3	544.0	366.3	245.2	179.9	145.4	135.1	124.8
107.5°	1044.0	972.0	848.7	685.0	507.3	356.1	253.3	195.3	161.5	151.2	141.0
110°	1014.6	920.6	789.2	634.3	482.3	353.1	263.6	210.7	178.4	167.8	157.1

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	961.7	859.7	734.9	599.1	466.2	353.9	274.6	225.4	194.5	183.5	172.5
115°	901.5	805.4	692.3	571.2	455.2	356.8	285.6	240.8	209.2	199.3	189.4
117.5°	847.9	758.4	657.1	552.1	449.3	361.2	297.3	254.7	225.4	215.1	204.8
120°	800.9	723.1	632.1	537.4	444.2	365.6	309.1	269.4	240.8	230.5	220.2
122.5°	766.4	693.8	612.3	524.9	441.2	370.7	319.4	283.4	256.9	246.3	235.7
125°	733.4	668.8	593.2	513.2	437.5	375.9	330.4	297.3	270.9	260.6	250.3
127.5°	705.5	643.8	574.1	502.2	435.3	381.0	340.6	310.5	284.8	274.2	263.6
130°	676.9	618.9	555.7	491.1	433.9	386.9	350.2	322.3	296.6	286.3	276.0
132.5°	647.5	595.4	538.1	482.3	433.1	392.8	359.7	332.6	308.3	298.0	287.8
135°	618.9	570.4	522.0	474.3	432.4	397.2	367.8	342.1	318.6	308.4	298.1
137.5°	590.3	550.6	508.8	468.4	432.4	401.6	374.4	350.2	326.7	317.2	307.6
140°	565.3	531.5	496.3	463.2	431.7	404.5	379.6	356.8	334.8	325.2	315.7
142.5°	542.5	514.6	486.0	458.1	431.7	406.7	384.0	361.9	340.6	331.8	323.0
145°	523.4	500.7	476.5	453.7	430.2	408.2	387.6	367.1	347.2	339.2	331.1
147.5°	507.3	488.9	469.1	449.3	428.0	408.9	389.8	371.5	352.4	345.0	337.7
150°	492.6	477.2	461.0	443.4	425.8	408.2	391.3	374.4	357.5	350.9	344.3
152.5°	480.1	467.6	453.0	438.3	422.1	406.7	392.0	377.3	362.7	356.8	350.9
155°	468.4	457.4	445.6	431.7	417.7	405.2	392.8	380.3	367.8	362.3	356.8
157.5°	456.6	447.1	436.8	425.8	413.3	402.3	392.8	382.5	371.5	366.7	361.9
160°	444.9	436.8	428.7	419.2	408.9	400.1	392.8	384.0	375.1	371.1	367.1
162.5°	433.9	427.3	420.7	413.3	405.2	397.9	392.0	384.7	377.3	374.4	371.5
165°	422.9	417.7	412.6	406.7	400.1	395.0	390.6	385.4	378.8	376.6	374.4
167.5°	412.6	408.9	404.5	400.1	395.7	392.0	389.8	385.4	380.3	378.8	377.3
170°	403.8	400.8	398.6	395.0	392.0	389.8	388.4	384.7	381.0	379.9	378.8
172.5°	395.7	393.5	392.0	389.8	387.6	386.9	386.2	384.0	381.8	381.0	380.3
175°	389.1	388.4	387.6	385.4	384.7	384.0	384.7	383.2	381.8	381.4	381.0
177.5°	384.7	384.0	384.0	382.5	381.8	382.5	384.0	382.5	381.8	381.8	381.8
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1283.6	1283.6	1283.6	1283.6
2.5°	1259.9	1259.9	1274.7	1290.5
5°	1232.3	1239.2	1262.9	1284.6
7.5°	1205.7	1217.5	1247.1	1274.7
10°	1173.1	1188.9	1225.4	1257.9
12.5°	1141.5	1156.3	1198.7	1235.2
15°	1097.1	1115.9	1161.3	1206.6
17.5°	1052.7	1071.5	1126.7	1180.0
20°	1000.4	1025.1	1087.3	1158.3
22.5°	952.1	982.7	1051.7	1109.0
25°	898.8	946.2	1010.3	1084.3
27.5°	851.5	898.8	963.9	1038.9
30°	798.2	846.5	913.6	982.7
32.5°	746.9	791.3	856.4	941.2
35°	693.6	736.0	799.2	885.0
37.5°	645.3	686.7	755.8	834.7
40°	597.9	641.3	700.5	779.4
42.5°	553.5	592.0	645.3	724.2
45°	513.0	540.7	590.0	664.0
47.5°	470.6	495.3	540.7	614.7
50°	431.2	451.9	491.3	560.4
52.5°	392.7	410.4	446.9	502.2
55°	358.1	374.9	401.6	455.8
57.5°	322.6	335.5	361.1	404.5
60°	288.1	299.9	320.7	356.2
62.5°	253.6	263.4	283.2	311.8
65°	223.0	230.9	245.7	270.3
67.5°	193.4	198.3	210.2	229.9
70°	164.8	168.7	178.6	194.4
72.5°	134.2	138.1	149.0	159.8
75°	108.5	109.5	117.4	126.3
77.5°	84.8	83.9	89.8	96.7
80°	58.2	61.2	66.1	69.1
82.5°	39.5	40.5	42.4	44.4
85°	21.7	22.7	22.7	25.7
87.5°	8.9	9.9	9.9	10.9
90°	7.3	5.9	2.9	0.7
92.5°	25.0	21.3	15.4	11.0
95°	42.6	36.0	28.6	25.7
97.5°	60.2	50.7	42.6	38.2
100°	77.1	65.3	58.7	56.5
102.5°	93.2	81.5	74.9	73.4
105°	108.7	97.6	92.5	89.6
107.5°	124.8	114.5	109.4	107.2
110°	141.7	132.1	127.7	124.8



TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	157.8	149.0	143.9	141.0
115°	174.7	165.9	161.5	157.8
117.5°	190.9	182.8	178.4	175.5
120°	205.6	199.0	194.5	191.6
122.5°	221.0	213.6	209.2	207.0
125°	235.7	226.9	222.4	220.2
127.5°	249.6	240.1	234.2	231.3
130°	261.4	251.1	243.7	240.8
132.5°	272.4	261.4	253.3	249.6
135°	281.2	270.2	261.4	258.4
137.5°	290.7	279.0	270.2	266.5
140°	299.5	287.8	279.0	276.0
142.5°	307.6	295.9	287.8	285.6
145°	316.4	305.4	298.1	295.1
147.5°	325.2	314.9	307.6	305.4
150°	333.3	323.8	317.9	315.7
152.5°	340.6	332.6	326.7	326.0
155°	348.7	340.6	336.2	335.5
157.5°	355.3	348.0	344.3	343.6
160°	361.2	355.3	352.4	351.7
162.5°	366.3	361.9	359.0	359.7
165°	370.7	366.3	364.9	365.6
167.5°	374.4	371.5	370.0	370.7
170°	377.3	375.1	374.4	375.9
172.5°	379.6	377.3	378.1	378.8
175°	381.0	379.6	380.3	381.0
177.5°	381.8	380.3	381.0	382.5
180°	381.8	381.8	381.8	381.8

TEST NUMBER: P998905

CATALOG NUMBER: SA2XXDIP-B675D725UB50-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.45	17.30	17.40	18.26	19.51	13.95	14.79	14.90	15.75	17.00
	3H	17.26	18.02	18.23	18.99	20.26	15.29	16.04	16.25	17.01	18.29
	4H	17.43	18.14	18.41	19.12	20.40	15.75	16.46	16.73	17.44	18.72
	6H	17.48	18.13	18.46	19.11	20.41	16.06	16.71	17.05	17.69	18.99
	8H	17.46	18.08	18.45	19.07	20.37	16.14	16.76	17.13	17.76	19.05
	12H	17.42	18.01	18.42	19.00	20.32	16.18	16.78	17.18	17.77	19.08
4H	2H	16.49	17.20	17.48	18.18	19.46	14.39	15.10	15.37	16.08	17.36
	3H	17.47	18.06	18.46	19.07	20.36	15.85	16.44	16.84	17.45	18.74
	4H	17.75	18.29	18.75	19.29	20.61	16.38	16.92	17.38	17.92	19.24
	6H	17.88	18.34	18.89	19.36	20.68	16.76	17.23	17.77	18.25	19.57
	8H	17.88	18.31	18.89	19.32	20.65	16.87	17.31	17.88	18.32	19.65
	12H	17.84	18.23	18.87	19.26	20.60	16.93	17.32	17.96	18.35	19.69
8H	4H	17.76	18.19	18.77	19.20	20.54	16.53	16.96	17.54	17.97	19.30
	6H	17.93	18.29	18.97	19.35	20.68	16.96	17.32	18.00	18.37	19.70
	8H	17.96	18.28	19.01	19.32	20.67	17.11	17.42	18.15	18.47	19.82
	12H	17.95	18.22	18.99	19.26	20.65	17.20	17.48	18.25	18.51	19.91
12H	4H	17.71	18.10	18.74	19.13	20.47	16.50	16.89	17.53	17.92	19.26
	6H	17.91	18.23	18.96	19.27	20.62	16.96	17.27	18.00	18.32	19.67
	8H	17.94	18.22	18.99	19.26	20.65	17.12	17.39	18.16	18.43	19.82