

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999899

Luminaire Tested: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999899
REPORT IS A COMBINATION OF REPORTS P988456 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5944.0 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999899

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999899

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	68	65	63	53	52	51	40	39	39
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	43	61	51	45	39	42	37	33	34	30	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17256	17256	17256
5°	17284	16417	16295
10°	17114	15571	15057
15°	16879	14572	13645
20°	16568	13435	12168
25°	16249	12269	10817
30°	15820	11133	9342
35°	15400	9988	8075
40°	14975	8863	6769
45°	14480	7703	5632
50°	13965	6584	4585
55°	13432	5464	3640
60°	12811	4370	2754
65°	12101	3332	2239
70°	11238	2416	1780
75°	10153	1843	1359
80°	8583	1249	912
85°	5989	570	440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14480 cd/sqm

TEST NUMBER: P999899

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.2	1.7
10°-20°	280.5	4.7
20°-30°	393.8	6.6
30°-40°	429.2	7.2
40°-50°	394.5	6.6
50°-60°	309.8	5.2
60°-70°	201.7	3.4
70°-80°	103.8	1.7
80°-90°	30.3	0.5
90°-100°	81.8	1.4
100°-110°	260.1	4.4
110°-120°	445.1	7.5
120°-130°	585.4	9.8
130°-140°	657.1	11.1
140°-150°	644.4	10.8
150°-160°	540.5	9.1
160°-170°	358.5	6.0
170°-180°	125.3	2.1
0°-30°	776.4	13.1
0°-40°	1205.7	20.3
0°-60°	1910.0	32.1
0°-90°	2245.8	37.8
90°-120°	787.0	13.2
90°-150°	2673.9	45.0
90°-180°	3698.0	62.2
0°-180°	5944.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1090	1090	1090	1090	1090	
5°	1090	1085	1072	1081	1078	103
15°	1037	1026	992	974	964	292
25°	941	910	844	804	789	433
35°	811	761	674	612	590	508
45°	663	597	493	423	400	512
55°	504	427	321	261	243	450
65°	340	260	172	138	135	337
75°	182	112	79	72	71	192
85°	42	22	19	19	19	49
90°	1	14	39	37	38	6
95°	58	69	71	71	69	65
105°	240	243	246	248	248	253
115°	446	453	451	450	446	442
125°	650	660	656	653	652	581
135°	840	853	855	854	851	650
145°	1020	1028	1035	1036	1031	637
155°	1166	1170	1173	1179	1175	537
165°	1269	1268	1268	1276	1270	358
175°	1320	1317	1315	1323	1316	125
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P999899

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1090.1	1090.1	1090.1	1090.1	1090.1
2.5°	1095.1	1090.1	1079.3	1089.1	1087.2
5°	1090.1	1085.2	1072.4	1081.3	1078.3
7.5°	1081.3	1075.3	1061.5	1065.5	1060.5
10°	1069.4	1062.5	1042.8	1039.8	1033.9
12.5°	1054.6	1045.7	1019.1	1013.2	1002.3
15°	1036.9	1026.0	992.5	973.7	963.9
17.5°	1016.1	1000.4	958.9	937.2	921.4
20°	992.5	972.7	923.4	898.7	877.0
22.5°	966.8	944.1	886.9	853.4	838.6
25°	941.2	909.6	844.5	804.0	789.2
27.5°	910.6	877.0	805.0	758.7	736.0
30°	878.0	840.5	761.6	711.3	684.7
32.5°	846.5	801.1	720.2	661.0	636.3
35°	810.9	760.6	673.8	611.7	590.0
37.5°	776.4	722.2	630.4	562.3	537.7
40°	739.9	680.7	585.0	515.0	489.3
42.5°	702.4	639.3	539.6	466.6	442.0
45°	663.0	596.9	493.3	423.2	399.6
47.5°	625.5	555.4	448.9	378.8	357.1
50°	584.0	514.0	405.5	337.4	316.7
52.5°	543.6	469.6	364.0	298.9	280.2
55°	504.1	427.2	320.6	261.4	242.7
57.5°	463.7	384.8	282.2	226.9	211.1
60°	422.2	343.3	241.7	191.4	175.6
62.5°	381.8	302.9	207.2	159.8	151.9
65°	340.4	260.4	171.7	138.1	135.2
67.5°	300.9	221.0	138.1	121.3	118.4
70°	259.5	182.5	114.4	104.6	100.6
72.5°	220.0	147.0	95.7	87.8	85.8
75°	181.5	112.5	78.9	72.0	71.0
77.5°	143.0	79.9	62.2	58.2	56.2
80°	107.5	57.2	47.4	43.4	43.4
82.5°	75.0	38.5	32.6	30.6	30.6
85°	42.4	21.7	18.7	18.7	18.7
87.5°	15.8	7.9	7.9	6.9	6.9
90°	1.1	14.5	39.1	36.8	38.0
92.5°	24.6	33.5	34.6	35.7	35.7
95°	58.0	69.2	71.4	71.4	69.2
97.5°	97.1	107.2	111.6	111.6	111.6
100°	141.8	150.7	154.0	154.0	152.9
102.5°	188.6	195.3	199.8	200.9	199.8
105°	240.0	243.3	245.6	247.8	247.8
107.5°	291.3	295.8	295.8	296.9	291.3
110°	340.5	347.2	347.2	347.2	343.8

TEST NUMBER: P999899

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	394.0	400.7	399.6	396.3	394.0
115°	446.5	453.2	451.0	449.9	446.5
117.5°	499.0	507.9	502.3	499.0	495.6
120°	551.4	560.4	551.4	551.4	548.1
122.5°	599.4	610.6	605.0	601.7	599.4
125°	649.7	659.7	656.4	653.0	651.9
127.5°	698.8	711.1	706.6	702.1	698.8
130°	744.6	759.1	756.8	754.6	750.1
132.5°	795.9	807.1	808.2	802.6	799.2
135°	840.5	852.8	855.1	853.9	850.6
137.5°	889.7	899.7	901.9	900.8	896.4
140°	933.2	943.2	948.8	948.8	944.4
142.5°	977.9	987.9	991.2	992.4	987.9
145°	1020.3	1028.1	1034.8	1035.9	1031.4
147.5°	1058.2	1068.3	1072.7	1075.0	1070.5
150°	1097.3	1104.0	1108.5	1111.8	1108.5
152.5°	1131.9	1138.6	1144.2	1148.6	1144.2
155°	1166.5	1169.8	1173.2	1178.8	1175.4
157.5°	1196.6	1198.9	1201.1	1208.9	1203.3
160°	1223.4	1225.7	1226.8	1233.5	1229.0
162.5°	1248.0	1248.0	1249.1	1256.9	1251.3
165°	1269.2	1268.1	1268.1	1275.9	1270.3
167.5°	1288.2	1284.8	1284.8	1292.6	1287.1
170°	1302.7	1299.3	1298.2	1306.0	1299.3
172.5°	1312.7	1309.4	1308.3	1316.1	1309.4
175°	1320.5	1317.2	1315.0	1322.8	1316.1
177.5°	1325.0	1321.7	1319.4	1326.1	1319.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)