

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998949

Luminaire Tested: SA2XXDIP-B675D925UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998949
REPORT IS A COMBINATION OF REPORTS P984695 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D925UB35-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6004.9 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998949

CATALOG NUMBER: SA2XXDIP-B675D925UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998949

CATALOG NUMBER: SA2XXDIP-B675D925UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	94	90	85	81	86	82	78	75	66	64	61	53	51	49	40	38	37
2	85	78	71	65	77	71	65	60	57	53	50	45	42	40	34	32	31
3	78	68	60	54	70	62	55	50	50	45	41	40	36	33	30	28	25
4	71	60	51	45	64	54	47	42	44	39	35	35	31	28	27	24	22
5	65	53	45	38	59	48	41	35	39	34	30	31	27	24	24	21	19
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	42	34	29	50	39	32	27	32	26	22	26	21	18	20	17	14
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13
9	47	35	27	22	43	32	25	21	27	21	18	21	17	14	16	14	11
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11259	11259	11259
5°	11309	10779	10717
10°	11234	10404	10254
15°	11076	10019	9778
20°	10876	9614	9325
25°	10678	9225	8916
30°	10402	8831	8510
35°	10121	8451	8212
40°	9826	8121	7915
45°	9546	7823	7658
50°	9245	7548	7402
55°	8926	7255	7142
60°	8539	6952	6870
65°	8134	6603	6555
70°	7678	6226	6218
75°	7093	5851	5899
80°	6171	5460	5569
85°	5241	5092	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9546 cd/sqm

TEST NUMBER: P998949

CATALOG NUMBER: SA2XXDIP-B675D925UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	1.1
10°-20°	193.4	3.2
20°-30°	293.0	4.9
30°-40°	356.8	5.9
40°-50°	383.9	6.4
50°-60°	372.8	6.2
60°-70°	325.6	5.4
70°-80°	250.6	4.2
80°-90°	171.2	2.9
90°-100°	188.5	3.1
100°-110°	315.8	5.3
110°-120°	451.5	7.5
120°-130°	551.5	9.2
130°-140°	597.2	9.9
140°-150°	575.0	9.6
150°-160°	480.5	8.0
160°-170°	318.7	5.3
170°-180°	111.4	1.9
0°-30°	553.8	9.2
0°-40°	910.7	15.2
0°-60°	1667.4	27.8
0°-90°	2414.8	40.2
90°-120°	955.9	15.9
90°-150°	2679.6	44.6
90°-180°	3590.0	59.8
0°-180°	6004.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	711	711	711	711	711	
5°	713	710	704	710	709	68
15°	680	682	682	692	691	192
25°	618	626	635	647	650	284
35°	533	550	570	593	600	333
45°	437	465	501	533	543	337
55°	335	372	426	463	476	300
65°	229	279	340	382	396	227
75°	127	184	250	295	308	134
85°	37	101	167	210	225	39
90°	11	83	171	210	223	10
95°	60	118	182	221	232	64
105°	219	251	307	345	356	231
115°	401	418	463	493	501	396
125°	580	589	618	643	652	518
135°	748	759	771	792	797	579
145°	907	914	920	927	928	567
155°	1037	1040	1043	1048	1045	477
165°	1128	1127	1127	1134	1129	318
175°	1174	1171	1169	1176	1170	112
180°	1176	1176	1176	1176	1176	

TEST NUMBER: P998949

CATALOG NUMBER: SA2XXDIP-B675D925UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.3	711.3	711.3	711.3	711.3
2.5°	716.4	713.3	706.1	711.3	709.2
5°	713.3	710.3	704.1	710.3	709.2
7.5°	708.2	706.1	701.0	708.2	707.2
10°	702.0	699.9	696.8	705.1	704.1
12.5°	691.7	692.7	690.7	698.9	697.9
15°	680.4	682.4	682.4	691.7	690.7
17.5°	665.9	670.0	673.1	682.4	682.4
20°	651.5	656.6	660.8	672.1	672.1
22.5°	636.0	642.2	648.4	659.7	661.8
25°	618.5	625.7	635.0	647.4	650.5
27.5°	597.9	609.2	619.5	635.0	637.1
30°	577.3	590.7	604.1	620.6	623.7
32.5°	554.6	570.1	586.5	606.1	612.3
35°	532.9	550.5	570.1	592.7	600.0
37.5°	509.2	528.8	553.6	578.3	585.5
40°	485.5	508.2	536.0	562.8	572.1
42.5°	462.8	485.5	518.5	548.4	557.7
45°	437.1	464.9	501.0	532.9	543.3
47.5°	412.3	442.2	483.5	516.5	527.8
50°	386.6	418.5	464.9	500.0	511.3
52.5°	361.8	395.8	445.3	481.4	493.8
55°	335.0	372.1	425.7	462.8	476.2
57.5°	309.3	350.5	404.1	444.3	457.7
60°	281.4	325.7	384.5	423.7	438.1
62.5°	256.7	303.1	361.8	404.1	417.5
65°	228.8	279.4	340.2	382.4	395.8
67.5°	204.1	256.7	318.5	360.8	375.2
70°	177.3	230.9	294.8	339.1	351.5
72.5°	152.6	208.2	273.2	316.5	331.9
75°	126.8	184.5	250.5	294.8	308.2
77.5°	102.1	161.8	228.8	273.2	287.6
80°	77.3	140.2	207.2	250.5	264.9
82.5°	56.7	118.5	186.6	229.9	243.3
85°	37.1	101.0	167.0	210.3	224.7
87.5°	22.7	84.5	150.5	192.8	206.2
90°	11.3	83.0	170.8	210.0	223.4
92.5°	31.1	93.7	157.6	198.8	211.2
95°	59.8	118.2	182.0	221.2	231.6
97.5°	93.5	146.8	210.5	248.7	261.0
100°	133.2	179.4	240.0	278.1	288.6
102.5°	173.9	213.9	273.5	311.6	321.9
105°	218.6	251.3	307.0	345.0	356.4
107.5°	264.2	292.9	344.4	380.5	386.8
110°	306.8	333.3	383.9	416.8	425.2

TEST NUMBER: P998949

CATALOG NUMBER: SA2XXDIP-B675D925UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	376.8	423.3	453.3	462.7
115°	401.0	418.4	462.8	492.7	501.0
117.5°	446.7	462.8	501.2	529.2	536.5
120°	493.3	505.4	538.6	567.5	575.9
122.5°	536.0	546.9	580.1	605.0	612.3
125°	579.6	588.6	618.5	643.4	651.7
127.5°	623.3	633.1	657.1	678.8	685.1
130°	664.0	675.8	695.5	718.2	722.6
132.5°	709.6	718.5	735.0	753.7	758.9
135°	748.2	759.1	771.4	792.1	797.4
137.5°	791.9	800.8	808.0	826.6	829.8
140°	830.6	838.5	845.6	862.1	864.2
142.5°	870.3	878.2	881.2	894.6	895.7
145°	907.0	913.9	919.9	927.1	928.2
147.5°	940.7	949.7	953.6	956.6	955.8
150°	975.5	981.4	985.4	988.4	985.4
152.5°	1006.2	1012.2	1017.1	1021.1	1017.1
155°	1037.0	1040.0	1042.9	1047.9	1044.9
157.5°	1063.8	1065.8	1067.8	1074.7	1069.7
160°	1087.6	1089.6	1090.6	1096.5	1092.6
162.5°	1109.4	1109.4	1110.4	1117.4	1112.4
165°	1128.3	1127.3	1127.3	1134.2	1129.3
167.5°	1145.2	1142.2	1142.2	1149.1	1144.2
170°	1158.1	1155.1	1154.1	1161.0	1155.1
172.5°	1167.0	1164.0	1163.0	1170.0	1164.0
175°	1173.9	1171.0	1169.0	1175.9	1170.0
177.5°	1177.9	1174.9	1172.9	1178.9	1172.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P998949

CATALOG NUMBER: SA2XXDIP-B675D925UB35-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.66	13.47	13.68	14.51	15.92	15.73	16.55	16.76	17.59	18.99
	3H	14.11	14.85	15.15	15.90	17.32	18.32	19.06	19.35	20.11	21.52
	4H	14.59	15.29	15.64	16.34	17.77	19.57	20.27	20.62	21.32	22.75
	6H	14.87	15.52	15.93	16.58	18.01	20.86	21.51	21.92	22.57	24.01
	8H	14.93	15.55	15.99	16.62	18.05	21.52	22.14	22.58	23.21	24.65
	12H	14.94	15.53	16.01	16.60	18.06	22.24	22.84	23.31	23.90	25.36
4H	2H	13.70	14.40	14.76	15.46	16.88	16.06	16.76	17.11	17.81	19.24
	3H	15.41	16.00	16.47	17.08	18.52	18.84	19.44	19.91	20.52	21.96
	4H	16.03	16.57	17.09	17.64	19.11	20.26	20.81	21.33	21.88	23.34
	6H	16.44	16.92	17.52	18.01	19.46	21.72	22.20	22.80	23.29	24.75
	8H	16.55	16.99	17.62	18.08	19.55	22.48	22.93	23.56	24.01	25.48
	12H	16.59	16.99	17.68	18.09	19.57	23.31	23.71	24.40	24.81	26.29
8H	4H	16.81	17.26	17.89	18.34	19.82	20.40	20.85	21.48	21.93	23.40
	6H	17.44	17.82	18.54	18.94	20.41	22.03	22.40	23.13	23.53	24.99
	8H	17.67	18.00	18.77	19.10	20.59	22.92	23.25	24.02	24.36	25.84
	12H	17.80	18.09	18.91	19.19	20.72	23.91	24.20	25.02	25.31	26.83
12H	4H	17.01	17.41	18.10	18.51	19.99	20.37	20.78	21.47	21.88	23.35
	6H	17.78	18.11	18.88	19.22	20.70	22.05	22.38	23.16	23.49	24.98
	8H	18.08	18.37	19.19	19.48	21.00	22.98	23.27	24.09	24.38	25.90