

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999945

Luminaire Tested: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999945
REPORT IS A COMBINATION OF REPORTS P988502 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4191.0 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999945

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999945

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55		
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	54	52	48		
2	91	84	78	73	84	78	73	69	68	64	60	58	55	53	49	47	45	41		
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35		
4	77	66	58	52	71	62	55	50	54	49	44	46	42	39	39	36	34	31		
5	71	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30	27		
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24		
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21		
8	56	44	36	31	52	41	35	30	37	31	27	32	28	24	28	24	22	19		
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20	18		
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17795	17795	17795
5°	17824	16930	16805
10°	17648	16056	15527
15°	17405	15027	14070
20°	17086	13854	12548
25°	16757	12653	11155
30°	16314	11481	9633
35°	15883	10299	8327
40°	15442	9141	6981
45°	14932	7943	5807
50°	14403	6788	4728
55°	13853	5634	3754
60°	13212	4507	2840
65°	12478	3435	2309
70°	11589	2492	1836
75°	10472	1901	1401
80°	8854	1286	942
85°	6173	588	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14932 cd/sqm

TEST NUMBER: P999945

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	2.5
10°-20°	289.2	6.9
20°-30°	406.1	9.7
30°-40°	442.6	10.6
40°-50°	406.8	9.7
50°-60°	319.5	7.6
60°-70°	208.0	5.0
70°-80°	107.1	2.6
80°-90°	29.2	0.7
90°-100°	41.5	1.0
100°-110°	132.0	3.2
110°-120°	225.9	5.4
120°-130°	297.1	7.1
130°-140°	333.5	8.0
140°-150°	327.1	7.8
150°-160°	274.3	6.5
160°-170°	182.0	4.3
170°-180°	63.6	1.5
0°-30°	800.7	19.1
0°-40°	1243.3	29.7
0°-60°	1969.7	47.0
0°-90°	2313.9	55.2
90°-120°	399.5	9.5
90°-150°	1357.2	32.4
90°-180°	1877.0	44.8
0°-180°	4191.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1124	1119	1106	1115	1112	107
15°	1069	1058	1024	1004	994	301
25°	971	938	871	829	814	446
35°	836	784	695	631	608	523
45°	684	616	509	436	412	528
55°	520	440	331	270	250	465
65°	351	269	177	142	139	348
75°	187	116	81	74	73	198
85°	44	22	19	19	19	50
90°	1	7	20	19	19	4
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	230	229	228	227	224
125°	330	335	333	331	331	295
135°	427	433	434	433	432	330
145°	518	522	525	526	524	324
155°	592	594	596	598	597	273
165°	644	644	644	648	645	182
175°	670	669	667	671	668	64
180°	671	671	671	671	671	

TEST NUMBER: P999945

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1124.2	1124.2	1124.2	1124.2	1124.2
2.5°	1129.3	1124.2	1113.0	1123.2	1121.1
5°	1124.2	1119.1	1105.9	1115.0	1112.0
7.5°	1115.0	1108.9	1094.7	1098.7	1093.6
10°	1102.8	1095.7	1075.3	1072.3	1066.2
12.5°	1087.5	1078.4	1050.9	1044.8	1033.6
15°	1069.2	1058.0	1023.5	1004.1	993.9
17.5°	1047.9	1031.6	988.9	966.5	950.2
20°	1023.5	1003.1	952.2	926.8	904.4
22.5°	997.0	973.6	914.6	880.0	864.7
25°	970.6	938.0	870.9	829.1	813.9
27.5°	939.0	904.4	830.2	782.3	758.9
30°	905.4	866.8	785.4	733.5	706.0
32.5°	872.9	826.1	742.7	681.6	656.2
35°	836.3	784.4	694.8	630.8	608.4
37.5°	800.7	744.7	650.1	579.9	554.5
40°	763.0	702.0	603.3	531.1	504.6
42.5°	724.4	659.2	556.5	481.2	455.8
45°	683.7	615.5	508.7	436.4	412.0
47.5°	645.0	572.8	462.9	390.7	368.3
50°	602.3	530.0	418.1	347.9	326.6
52.5°	560.6	484.3	375.4	308.3	288.9
55°	519.9	440.5	330.6	269.6	250.3
57.5°	478.2	396.8	291.0	234.0	217.7
60°	435.4	354.0	249.3	197.4	181.1
62.5°	393.7	312.3	213.6	164.8	156.7
65°	351.0	268.6	177.0	142.4	139.4
67.5°	310.3	227.9	142.4	125.1	122.1
70°	267.6	188.2	118.0	107.8	103.8
72.5°	226.9	151.6	98.7	90.5	88.5
75°	187.2	116.0	81.4	74.3	73.2
77.5°	147.5	82.4	64.1	60.0	58.0
80°	110.9	59.0	48.8	44.8	44.8
82.5°	77.3	39.7	33.6	31.5	31.5
85°	43.7	22.4	19.3	19.3	19.3
87.5°	16.3	8.1	8.1	7.1	7.1
90°	0.6	7.4	19.8	18.7	19.3
92.5°	12.5	17.0	17.6	18.1	18.1
95°	29.5	35.1	36.3	36.3	35.1
97.5°	49.3	54.4	56.7	56.7	56.7
100°	72.0	76.5	78.2	78.2	77.6
102.5°	95.8	99.2	101.4	102.0	101.4
105°	121.8	123.5	124.6	125.8	125.8
107.5°	147.9	150.1	150.1	150.7	147.9
110°	172.8	176.2	176.2	176.2	174.5

TEST NUMBER: P999945

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.0	203.4	202.8	201.1	200.0
115°	226.6	230.0	228.9	228.3	226.6
117.5°	253.3	257.8	255.0	253.3	251.6
120°	279.9	284.4	279.9	279.9	278.2
122.5°	304.3	309.9	307.1	305.4	304.3
125°	329.7	334.8	333.1	331.4	330.9
127.5°	354.7	360.9	358.6	356.4	354.7
130°	377.9	385.3	384.1	383.0	380.7
132.5°	404.0	409.6	410.2	407.4	405.7
135°	426.6	432.9	434.0	433.4	431.7
137.5°	451.6	456.7	457.8	457.2	455.0
140°	473.7	478.8	481.6	481.6	479.3
142.5°	496.3	501.4	503.1	503.7	501.4
145°	517.9	521.8	525.2	525.8	523.5
147.5°	537.1	542.2	544.5	545.6	543.3
150°	556.9	560.3	562.6	564.3	562.6
152.5°	574.5	577.9	580.7	583.0	580.7
155°	592.1	593.8	595.5	598.3	596.6
157.5°	607.4	608.5	609.6	613.6	610.8
160°	621.0	622.1	622.7	626.1	623.8
162.5°	633.4	633.4	634.0	638.0	635.1
165°	644.2	643.6	643.6	647.6	644.8
167.5°	653.8	652.1	652.1	656.1	653.3
170°	661.2	659.5	658.9	662.9	659.5
172.5°	666.3	664.6	664.0	668.0	664.6
175°	670.3	668.6	667.4	671.4	668.0
177.5°	672.5	670.8	669.7	673.1	669.7
180°	671.4	671.4	671.4	671.4	671.4

(END OF REPORT)