

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999946

Luminaire Tested: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999946
REPORT IS A COMBINATION OF REPORTS P988503 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4367.3 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999946

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999946

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51
2	91	83	77	73	84	78	72	68	67	63	59	56	54	51	47	45	43
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17795	17795	17795
5°	17824	16930	16805
10°	17648	16056	15527
15°	17405	15027	14070
20°	17086	13854	12548
25°	16757	12653	11155
30°	16314	11481	9633
35°	15883	10299	8327
40°	15442	9141	6981
45°	14932	7943	5807
50°	14403	6788	4728
55°	13853	5634	3754
60°	13212	4507	2840
65°	12478	3435	2309
70°	11589	2492	1836
75°	10472	1901	1401
80°	8854	1286	942
85°	6173	588	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14932 cd/sqm

TEST NUMBER: P999946

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	2.4
10°-20°	289.2	6.6
20°-30°	406.1	9.3
30°-40°	442.6	10.1
40°-50°	406.8	9.3
50°-60°	319.5	7.3
60°-70°	208.0	4.8
70°-80°	107.1	2.5
80°-90°	29.2	0.7
90°-100°	119.4	2.7
100°-110°	403.6	9.2
110°-120°	424.3	9.7
120°-130°	348.9	8.0
130°-140°	280.4	6.4
140°-150°	211.8	4.8
150°-160°	148.9	3.4
160°-170°	87.7	2.0
170°-180°	28.5	0.7
0°-30°	800.7	18.3
0°-40°	1243.3	28.5
0°-60°	1969.7	45.1
0°-90°	2313.9	53.0
90°-120°	947.3	21.7
90°-150°	1788.4	40.9
90°-180°	2053.0	47.0
0°-180°	4367.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1124	1119	1106	1115	1112	107
15°	1069	1058	1024	1004	994	301
25°	971	938	871	829	814	446
35°	836	784	695	631	608	523
45°	684	616	509	436	412	528
55°	520	440	331	270	250	465
65°	351	269	177	142	139	348
75°	187	116	81	74	73	198
85°	44	22	19	19	19	50
90°	1	8	19	18	19	4
95°	20	49	222	84	65	20
105°	69	104	420	750	638	73
115°	122	154	351	725	840	121
125°	170	201	338	587	681	151
135°	199	238	334	493	565	154
145°	228	262	332	412	451	143
155°	259	280	322	364	379	119
165°	282	291	309	327	332	80
175°	294	294	297	300	300	28
180°	294	294	294	294	294	

TEST NUMBER: P999946

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1124.2	1124.2	1124.2	1124.2	1124.2
2.5°	1129.3	1124.2	1113.0	1123.2	1121.1
5°	1124.2	1119.1	1105.9	1115.0	1112.0
7.5°	1115.0	1108.9	1094.7	1098.7	1093.6
10°	1102.8	1095.7	1075.3	1072.3	1066.2
12.5°	1087.5	1078.4	1050.9	1044.8	1033.6
15°	1069.2	1058.0	1023.5	1004.1	993.9
17.5°	1047.9	1031.6	988.9	966.5	950.2
20°	1023.5	1003.1	952.2	926.8	904.4
22.5°	997.0	973.6	914.6	880.0	864.7
25°	970.6	938.0	870.9	829.1	813.9
27.5°	939.0	904.4	830.2	782.3	758.9
30°	905.4	866.8	785.4	733.5	706.0
32.5°	872.9	826.1	742.7	681.6	656.2
35°	836.3	784.4	694.8	630.8	608.4
37.5°	800.7	744.7	650.1	579.9	554.5
40°	763.0	702.0	603.3	531.1	504.6
42.5°	724.4	659.2	556.5	481.2	455.8
45°	683.7	615.5	508.7	436.4	412.0
47.5°	645.0	572.8	462.9	390.7	368.3
50°	602.3	530.0	418.1	347.9	326.6
52.5°	560.6	484.3	375.4	308.3	288.9
55°	519.9	440.5	330.6	269.6	250.3
57.5°	478.2	396.8	291.0	234.0	217.7
60°	435.4	354.0	249.3	197.4	181.1
62.5°	393.7	312.3	213.6	164.8	156.7
65°	351.0	268.6	177.0	142.4	139.4
67.5°	310.3	227.9	142.4	125.1	122.1
70°	267.6	188.2	118.0	107.8	103.8
72.5°	226.9	151.6	98.7	90.5	88.5
75°	187.2	116.0	81.4	74.3	73.2
77.5°	147.5	82.4	64.1	60.0	58.0
80°	110.9	59.0	48.8	44.8	44.8
82.5°	77.3	39.7	33.6	31.5	31.5
85°	43.7	22.4	19.3	19.3	19.3
87.5°	16.3	8.1	8.1	7.1	7.1
90°	0.6	7.6	19.3	18.4	18.7
92.5°	8.5	26.9	87.2	40.2	34.6
95°	19.8	48.7	222.0	83.8	64.6
97.5°	29.5	64.2	361.9	168.2	108.2
100°	43.6	78.8	447.5	335.0	202.8
102.5°	56.6	91.8	450.3	566.4	395.3
105°	69.1	104.2	419.7	750.2	638.3
107.5°	82.7	116.6	391.4	816.8	802.0
110°	96.3	129.4	372.1	806.0	868.9

TEST NUMBER: P999946

CATALOG NUMBER: SA2XXRDIP-B675D530UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	108.7	141.6	359.7	769.4	867.7
115°	121.8	153.8	351.2	724.7	840.0
117.5°	135.4	166.0	346.6	682.0	798.1
120°	147.8	177.9	342.7	643.7	757.8
122.5°	159.7	190.0	340.4	614.0	715.9
125°	169.9	201.0	337.6	587.0	681.4
127.5°	178.4	211.6	335.9	564.2	649.1
130°	185.8	220.9	334.7	540.9	622.5
132.5°	192.6	230.0	334.2	516.8	594.7
135°	199.4	237.9	333.6	493.4	564.7
137.5°	205.6	244.6	333.6	469.6	535.8
140°	213.0	251.0	333.0	448.6	505.8
142.5°	220.3	256.0	333.0	428.5	475.8
145°	227.7	261.6	331.9	412.0	450.9
147.5°	235.6	266.2	330.2	397.6	428.8
150°	243.6	270.7	328.5	385.2	409.5
152.5°	251.5	275.2	325.7	374.6	393.1
155°	258.8	279.6	322.3	364.5	378.9
157.5°	265.1	282.9	318.9	354.8	366.5
160°	271.3	286.3	315.5	345.2	354.6
162.5°	277.5	288.8	312.7	336.2	343.2
165°	282.1	290.6	308.7	327.4	332.5
167.5°	286.0	292.2	305.3	319.5	322.3
170°	290.0	293.2	302.5	312.1	313.2
172.5°	292.3	294.0	299.1	305.6	305.9
175°	294.0	294.2	296.8	300.5	299.6
177.5°	295.1	294.5	294.5	296.8	295.1
180°	294.5	294.5	294.5	294.5	294.5

(END OF REPORT)