

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999967

Luminaire Tested: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999967
REPORT IS A COMBINATION OF REPORTS P988524 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4245.0 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999967

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999967

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	54	52
2	91	84	78	73	84	78	73	69	68	64	60	58	55	53	49	47	45
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39
4	77	66	58	52	71	62	55	50	54	49	44	46	42	39	39	36	34
5	71	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	27	24
8	56	44	36	31	52	41	35	30	37	31	27	32	28	24	28	24	22
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18026	18026	18026
5°	18056	17149	17022
10°	17877	16265	15728
15°	17631	15221	14253
20°	17306	14034	12712
25°	16973	12817	11299
30°	16526	11630	9758
35°	16088	10434	8435
40°	15643	9259	7072
45°	15124	8046	5883
50°	14590	6877	4789
55°	14032	5708	3802
60°	13385	4565	2876
65°	12638	3480	2339
70°	11736	2524	1859
75°	10606	1925	1420
80°	8966	1304	952
85°	6258	598	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15124 cd/sqm

TEST NUMBER: P999967

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	2.5
10°-20°	293.0	6.9
20°-30°	411.3	9.7
30°-40°	448.4	10.6
40°-50°	412.1	9.7
50°-60°	323.6	7.6
60°-70°	210.7	5.0
70°-80°	108.4	2.6
80°-90°	29.6	0.7
90°-100°	42.1	1.0
100°-110°	133.7	3.2
110°-120°	228.8	5.4
120°-130°	300.9	7.1
130°-140°	337.8	8.0
140°-150°	331.2	7.8
150°-160°	277.9	6.5
160°-170°	184.3	4.3
170°-180°	64.4	1.5
0°-30°	811.1	19.1
0°-40°	1259.4	29.7
0°-60°	1995.2	47.0
0°-90°	2343.9	55.2
90°-120°	404.6	9.5
90°-150°	1374.5	32.4
90°-180°	1901.0	44.8
0°-180°	4245.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1120	1130	1126	108
15°	1083	1072	1037	1017	1007	305
25°	983	950	882	840	824	452
35°	847	795	704	639	616	530
45°	692	624	515	442	417	535
55°	527	446	335	273	254	471
65°	356	272	179	144	141	352
75°	190	118	82	75	74	201
85°	44	23	20	20	20	51
90°	1	8	20	19	20	4
95°	30	36	37	37	36	33
105°	123	125	126	127	127	130
115°	230	233	232	231	230	227
125°	334	339	337	336	335	298
135°	432	438	440	439	437	334
145°	524	528	532	532	530	328
155°	600	601	603	606	604	276
165°	652	652	652	656	653	184
175°	679	677	676	680	676	64
180°	680	680	680	680	680	

TEST NUMBER: P999967

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1138.8	1138.8	1138.8	1138.8	1138.8
2.5°	1143.9	1138.8	1127.4	1137.7	1135.7
5°	1138.8	1133.6	1120.2	1129.5	1126.4
7.5°	1129.5	1123.3	1108.9	1113.0	1107.8
10°	1117.1	1109.9	1089.3	1086.2	1080.0
12.5°	1101.7	1092.4	1064.6	1058.4	1047.0
15°	1083.1	1071.8	1036.7	1017.2	1006.8
17.5°	1061.5	1045.0	1001.7	979.0	962.5
20°	1036.7	1016.1	964.6	938.8	916.2
22.5°	1009.9	986.2	926.5	891.4	876.0
25°	983.1	950.2	882.2	839.9	824.4
27.5°	951.2	916.2	840.9	792.5	768.8
30°	917.2	878.0	795.6	743.0	715.2
32.5°	884.2	836.8	752.3	690.5	664.7
35°	847.1	794.6	703.9	638.9	616.3
37.5°	811.0	754.4	658.5	587.4	561.6
40°	772.9	711.1	611.1	537.9	511.2
42.5°	733.8	667.8	563.7	487.4	461.7
45°	692.5	623.5	515.3	442.1	417.4
47.5°	653.4	580.2	468.9	395.7	373.1
50°	610.1	536.9	423.6	352.4	330.8
52.5°	567.8	490.5	380.3	312.3	292.7
55°	526.6	446.2	334.9	273.1	253.5
57.5°	484.4	401.9	294.7	237.0	220.5
60°	441.1	358.6	252.5	199.9	183.4
62.5°	398.8	316.4	216.4	166.9	158.7
65°	355.5	272.1	179.3	144.3	141.2
67.5°	314.3	230.8	144.3	126.8	123.7
70°	271.0	190.7	119.5	109.2	105.1
72.5°	229.8	153.6	100.0	91.7	89.7
75°	189.6	117.5	82.4	75.2	74.2
77.5°	149.4	83.5	64.9	60.8	58.7
80°	112.3	59.8	49.5	45.3	45.3
82.5°	78.3	40.2	34.0	31.9	31.9
85°	44.3	22.7	19.6	19.6	19.6
87.5°	16.5	8.2	8.2	7.2	7.2
90°	0.6	7.5	20.1	18.9	19.5
92.5°	12.6	17.2	17.8	18.4	18.4
95°	29.8	35.6	36.7	36.7	35.6
97.5°	49.9	55.1	57.4	57.4	57.4
100°	72.9	77.5	79.2	79.2	78.6
102.5°	97.0	100.4	102.7	103.3	102.7
105°	123.4	125.1	126.2	127.4	127.4
107.5°	149.8	152.1	152.1	152.6	149.8
110°	175.0	178.5	178.5	178.5	176.7



TEST NUMBER: P999967

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	202.6	206.0	205.4	203.7	202.6
115°	229.5	233.0	231.8	231.2	229.5
117.5°	256.5	261.1	258.2	256.5	254.8
120°	283.5	288.1	283.5	283.5	281.7
122.5°	308.1	313.9	311.0	309.3	308.1
125°	334.0	339.1	337.4	335.7	335.1
127.5°	359.2	365.5	363.2	360.9	359.2
130°	382.7	390.2	389.0	387.9	385.6
132.5°	409.1	414.9	415.4	412.6	410.9
135°	432.1	438.4	439.5	439.0	437.2
137.5°	457.3	462.5	463.6	463.1	460.8
140°	479.7	484.9	487.7	487.7	485.4
142.5°	502.7	507.8	509.5	510.1	507.8
145°	524.5	528.5	531.9	532.5	530.2
147.5°	544.0	549.1	551.4	552.6	550.3
150°	564.1	567.5	569.8	571.5	569.8
152.5°	581.8	585.3	588.2	590.5	588.2
155°	599.6	601.4	603.1	605.9	604.2
157.5°	615.1	616.3	617.4	621.4	618.6
160°	628.9	630.0	630.6	634.1	631.8
162.5°	641.5	641.5	642.1	646.1	643.2
165°	652.4	651.9	651.9	655.9	653.0
167.5°	662.2	660.5	660.5	664.5	661.6
170°	669.6	667.9	667.3	671.4	667.9
172.5°	674.8	673.1	672.5	676.5	673.1
175°	678.8	677.1	676.0	680.0	676.5
177.5°	681.1	679.4	678.2	681.7	678.2
180°	680.0	680.0	680.0	680.0	680.0

(END OF REPORT)