

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999973

Luminaire Tested: SA2XXRDIP-B675D530UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999973
REPORT IS A COMBINATION OF REPORTS P988530 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4203.0 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999973

CATALOG NUMBER: SA2XXRDIP-B675D530UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999973

CATALOG NUMBER: SA2XXRDIP-B675D530UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	54	52
2	91	84	78	73	84	78	73	69	68	64	60	58	55	53	49	47	45
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39
4	77	66	58	52	71	62	55	50	54	49	44	46	42	39	39	36	34
5	71	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	27	24
8	56	44	36	31	52	41	35	30	37	31	27	32	28	24	28	24	22
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17849	17849	17849
5°	17878	16981	16854
10°	17701	16105	15574
15°	17459	15072	14114
20°	17137	13896	12587
25°	16807	12690	11188
30°	16364	11516	9663
35°	15930	10332	8352
40°	15489	9168	7002
45°	14976	7967	5825
50°	14446	6809	4743
55°	13893	5651	3764
60°	13251	4520	2848
65°	12513	3447	2315
70°	11624	2501	1842
75°	10506	1906	1407
80°	8878	1291	944
85°	6201	592	456

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14976 cd/sqm

TEST NUMBER: P999973

CATALOG NUMBER: SA2XXRDIP-B675D530UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.7	2.5
10°-20°	290.1	6.9
20°-30°	407.3	9.7
30°-40°	444.0	10.6
40°-50°	408.1	9.7
50°-60°	320.5	7.6
60°-70°	208.6	5.0
70°-80°	107.4	2.6
80°-90°	29.3	0.7
90°-100°	41.6	1.0
100°-110°	132.4	3.1
110°-120°	226.5	5.4
120°-130°	297.9	7.1
130°-140°	334.4	8.0
140°-150°	327.9	7.8
150°-160°	275.1	6.5
160°-170°	182.4	4.3
170°-180°	63.8	1.5
0°-30°	803.1	19.1
0°-40°	1247.1	29.7
0°-60°	1975.6	47.0
0°-90°	2320.9	55.2
90°-120°	400.5	9.5
90°-150°	1360.8	32.4
90°-180°	1882.0	44.8
0°-180°	4203.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1109	1118	1115	107
15°	1072	1061	1027	1007	997	302
25°	974	941	874	832	816	448
35°	839	787	697	633	610	525
45°	686	617	510	438	413	530
55°	521	442	332	270	251	466
65°	352	269	178	143	140	349
75°	188	116	82	74	74	199
85°	44	22	19	19	19	50
90°	1	7	20	19	19	4
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	231	230	229	227	225
125°	331	336	334	332	332	295
135°	428	434	435	435	433	331
145°	519	523	527	527	525	324
155°	594	595	597	600	598	273
165°	646	645	645	649	646	182
175°	672	670	669	673	670	64
180°	673	673	673	673	673	

TEST NUMBER: P999973

CATALOG NUMBER: SA2XXRDIP-B675D530UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1127.6	1127.6	1127.6	1127.6	1127.6
2.5°	1132.7	1127.6	1116.3	1126.6	1124.5
5°	1127.6	1122.5	1109.2	1118.4	1115.3
7.5°	1118.4	1112.3	1098.0	1102.1	1097.0
10°	1106.1	1099.0	1078.6	1075.5	1069.4
12.5°	1090.8	1081.7	1054.1	1048.0	1036.8
15°	1072.5	1061.2	1026.6	1007.2	997.0
17.5°	1051.0	1034.7	991.9	969.4	953.1
20°	1026.6	1006.1	955.1	929.6	907.2
22.5°	1000.0	976.6	917.4	882.7	867.4
25°	973.5	940.8	873.5	831.6	816.3
27.5°	941.9	907.2	832.7	784.7	761.2
30°	908.2	869.4	787.8	735.7	708.2
32.5°	875.5	828.6	744.9	683.7	658.2
35°	838.8	786.8	697.0	632.7	610.2
37.5°	803.1	747.0	652.1	581.6	556.1
40°	765.3	704.1	605.1	532.7	506.1
42.5°	726.5	661.2	558.2	482.7	457.2
45°	685.7	617.4	510.2	437.8	413.3
47.5°	647.0	574.5	464.3	391.8	369.4
50°	604.1	531.6	419.4	349.0	327.6
52.5°	562.3	485.7	376.5	309.2	289.8
55°	521.4	441.8	331.6	270.4	251.0
57.5°	479.6	398.0	291.8	234.7	218.4
60°	436.7	355.1	250.0	198.0	181.6
62.5°	394.9	313.3	214.3	165.3	157.1
65°	352.0	269.4	177.6	142.9	139.8
67.5°	311.2	228.6	142.9	125.5	122.5
70°	268.4	188.8	118.4	108.2	104.1
72.5°	227.6	152.0	99.0	90.8	88.8
75°	187.8	116.3	81.6	74.5	73.5
77.5°	148.0	82.7	64.3	60.2	58.2
80°	111.2	59.2	49.0	44.9	44.9
82.5°	77.6	39.8	33.7	31.6	31.6
85°	43.9	22.4	19.4	19.4	19.4
87.5°	16.3	8.2	8.2	7.1	7.1
90°	0.6	7.4	19.9	18.7	19.3
92.5°	12.5	17.0	17.6	18.2	18.2
95°	29.5	35.2	36.4	36.4	35.2
97.5°	49.4	54.5	56.8	56.8	56.8
100°	72.1	76.7	78.4	78.4	77.8
102.5°	96.0	99.4	101.7	102.3	101.7
105°	122.1	123.8	125.0	126.1	126.1
107.5°	148.3	150.5	150.5	151.1	148.3
110°	173.3	176.7	176.7	176.7	175.0

TEST NUMBER: P999973

CATALOG NUMBER: SA2XXRDIP-B675D530UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.5	203.9	203.4	201.7	200.5
115°	227.2	230.6	229.5	228.9	227.2
117.5°	253.9	258.5	255.6	253.9	252.2
120°	280.6	285.2	280.6	280.6	278.9
122.5°	305.1	310.7	307.9	306.2	305.1
125°	330.6	335.7	334.0	332.3	331.8
127.5°	355.6	361.9	359.6	357.3	355.6
130°	378.9	386.3	385.2	384.0	381.8
132.5°	405.0	410.7	411.3	408.5	406.7
135°	427.8	434.0	435.2	434.6	432.9
137.5°	452.8	457.9	459.0	458.4	456.2
140°	474.9	480.0	482.9	482.9	480.6
142.5°	497.6	502.8	504.5	505.0	502.8
145°	519.2	523.2	526.6	527.2	524.9
147.5°	538.5	543.7	545.9	547.1	544.8
150°	558.4	561.8	564.1	565.8	564.1
152.5°	576.0	579.4	582.3	584.6	582.3
155°	593.6	595.4	597.1	599.9	598.2
157.5°	609.0	610.1	611.3	615.2	612.4
160°	622.6	623.8	624.3	627.7	625.5
162.5°	635.1	635.1	635.7	639.7	636.8
165°	645.9	645.3	645.3	649.3	646.5
167.5°	655.6	653.9	653.9	657.8	655.0
170°	663.0	661.3	660.7	664.7	661.3
172.5°	668.1	666.4	665.8	669.8	666.4
175°	672.0	670.3	669.2	673.2	669.8
177.5°	674.3	672.6	671.5	674.9	671.5
180°	673.2	673.2	673.2	673.2	673.2

(END OF REPORT)