

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998974

Luminaire Tested: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998974
REPORT IS A COMBINATION OF REPORTS P984720 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7926.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47
1	98	94	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	43	41	40	35	35	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30	30	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26	26	26
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	31	29	26	23	23	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	21	21	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17	17	17
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	19	17	15	15	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26934	26934	26934	26934
5°	26998	28717	27101	22848
10°	26685	31350	26851	18836
15°	26038	33067	26399	15866
20°	25631	31047	25631	13791
25°	24814	26673	24926	12333
30°	23470	20967	23917	11171
35°	22279	14498	22651	10221
40°	20911	10946	21150	9463
45°	19224	8995	19538	8646
50°	17763	7896	17796	7915
55°	16100	6728	16204	7120
60°	14326	5619	14526	6215
65°	12737	4571	12972	5307
70°	11156	3586	11442	4279
75°	9364	2603	9728	3105
80°	7305	1650	7832	1842
85°	4803	830	5170	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 27842 cd/sqm

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.1	2.0
10°-20°	471.7	6.0
20°-30°	684.6	8.6
30°-40°	721.7	9.1
40°-50°	638.6	8.1
50°-60°	509.9	6.4
60°-70°	346.4	4.4
70°-80°	177.2	2.2
80°-90°	45.7	0.6
90°-100°	233.3	2.9
100°-110°	821.7	10.4
110°-120°	863.0	10.9
120°-130°	709.9	9.0
130°-140°	570.3	7.2
140°-150°	430.8	5.4
150°-160°	302.9	3.8
160°-170°	178.3	2.2
170°-180°	58.0	0.7
0°-30°	1318.3	16.6
0°-40°	2040.0	25.7
0°-60°	3188.6	40.2
0°-90°	3757.8	47.4
90°-120°	1918.0	24.2
90°-150°	3629.0	45.8
90°-180°	4168.0	52.6
0°-180°	7926.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1702	1702	1702	1702	1702	
5°	1703	1900	1709	1512	1703	161
15°	1600	2336	1622	1121	1600	452
25°	1437	1946	1444	900	1437	657
35°	1173	1059	1193	747	1173	734
45°	880	638	895	613	880	683
55°	604	449	608	475	604	539
65°	358	276	365	320	358	356
75°	167	136	174	162	167	180
85°	34	35	37	26	34	40
90°	1	38	1	38	1	5
95°	40	131	40	131	40	42
105°	140	1297	140	1297	140	149
115°	248	1707	248	1707	248	245
125°	345	1385	345	1385	345	307
135°	405	1148	405	1148	405	313
145°	463	916	463	916	463	290
155°	526	770	526	770	526	242
165°	573	676	573	676	573	162
175°	597	609	597	609	597	57
180°	598	598	598	598	598	

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1710.6	1714.6	1721.1	1722.4	1735.5	1746.0	1757.7	1757.7	1761.6	1760.3	1749.9
5°	1702.8	1714.6	1731.6	1746.0	1769.5	1780.0	1795.7	1807.4	1817.9	1825.7	1824.4
7.5°	1689.7	1710.6	1735.5	1763.0	1794.3	1812.7	1834.9	1855.8	1870.2	1883.3	1892.4
10°	1667.5	1702.8	1736.8	1773.4	1814.0	1838.8	1865.0	1892.4	1914.7	1939.5	1963.1
12.5°	1637.4	1688.4	1730.3	1778.6	1828.3	1855.8	1897.7	1918.6	1961.7	2024.5	2041.5
15°	1599.5	1668.8	1708.0	1769.5	1834.9	1857.1	1914.7	1948.7	2037.6	2076.8	2123.9
17.5°	1564.2	1641.3	1693.6	1764.3	1828.3	1871.5	1927.7	1997.1	2071.6	2127.8	2180.2
20°	1535.4	1609.9	1672.7	1751.2	1832.3	1887.2	1946.1	2029.8	2110.8	2168.4	2208.9
22.5°	1470.0	1565.5	1638.7	1726.3	1824.4	1900.3	1956.5	2048.1	2135.7	2171.0	2206.3
25°	1437.3	1519.7	1604.7	1704.1	1819.2	1909.4	1957.8	2059.8	2137.0	2150.1	2157.9
27.5°	1377.1	1470.0	1569.4	1683.2	1817.9	1893.7	1955.2	2048.1	2109.5	2100.4	2076.8
30°	1302.6	1416.4	1526.2	1649.2	1799.6	1882.0	1939.5	2024.5	2055.9	2008.8	1967.0
32.5°	1247.7	1354.9	1476.5	1619.1	1778.6	1857.1	1913.4	1980.1	1986.6	1901.6	1831.0
35°	1173.1	1292.1	1429.5	1579.9	1743.3	1814.0	1866.3	1906.8	1875.4	1756.4	1672.7
37.5°	1106.4	1224.1	1370.6	1523.6	1694.9	1764.3	1806.1	1812.7	1735.5	1630.9	1507.9
40°	1033.2	1154.8	1307.8	1468.7	1641.3	1701.5	1727.6	1708.0	1596.9	1475.2	1332.7
42.5°	959.9	1080.3	1245.1	1409.8	1573.3	1624.3	1634.8	1581.2	1445.2	1302.6	1137.8
45°	880.2	1005.7	1170.5	1336.6	1494.9	1523.6	1524.9	1447.8	1286.9	1137.8	984.8
47.5°	814.8	931.2	1094.7	1260.7	1394.1	1413.8	1405.9	1317.0	1141.7	974.3	840.9
50°	742.8	854.0	1016.2	1179.7	1293.4	1298.7	1279.1	1152.2	980.9	827.9	721.9
52.5°	665.7	778.2	927.3	1084.2	1186.2	1178.4	1140.4	1004.4	843.6	716.7	635.6
55°	604.2	703.6	843.6	996.6	1068.5	1046.3	1004.4	865.8	738.9	631.7	561.1
57.5°	536.2	623.8	761.2	894.6	936.4	915.5	873.6	744.2	626.5	545.4	498.3
60°	472.1	551.9	672.2	783.4	816.1	793.9	745.5	629.1	544.1	476.1	440.7
62.5°	413.3	482.6	583.3	685.3	698.4	676.1	634.3	540.1	466.9	413.3	387.1
65°	358.3	423.7	504.8	582.0	593.8	570.2	527.1	459.0	397.6	363.6	338.7
67.5°	304.7	357.0	429.0	485.2	491.7	469.5	434.2	379.3	341.3	304.7	286.4
70°	257.6	296.9	353.1	398.9	401.5	380.6	362.3	312.6	283.8	257.6	243.3
72.5°	211.9	239.3	282.5	316.5	317.8	304.7	287.7	256.3	231.5	213.2	198.8
75°	167.4	190.9	217.1	247.2	245.9	235.4	222.3	202.7	181.8	170.0	163.5
77.5°	128.2	142.6	163.5	183.1	183.1	177.9	170.0	155.6	142.6	130.8	124.2
80°	91.5	100.7	117.7	124.2	126.9	125.6	119.0	108.5	103.3	94.2	91.5
82.5°	58.9	65.4	73.2	79.8	83.7	81.1	79.8	74.5	66.7	64.1	61.5
85°	34.0	36.6	40.5	44.5	45.8	44.5	47.1	43.2	39.2	39.2	37.9
87.5°	14.4	15.7	18.3	18.3	19.6	19.6	18.3	19.6	19.6	18.3	17.0
90°	1.2	4.6	9.2	11.5	13.8	15.6	17.3	23.0	31.1	38.0	39.1
92.5°	17.3	24.2	33.4	39.1	48.3	54.6	61.0	92.1	135.8	175.0	177.3
95°	40.3	44.9	56.4	66.8	85.2	99.0	112.8	165.7	265.9	399.4	451.2
97.5°	59.9	66.8	79.4	94.4	115.1	130.6	146.2	214.1	353.4	568.6	735.5
100°	88.6	92.1	102.4	120.9	143.9	160.0	176.1	237.1	377.5	626.2	909.3
102.5°	115.1	117.4	127.8	146.2	170.3	186.4	202.6	257.8	378.7	604.3	915.1
105°	140.4	145.0	153.1	170.3	195.7	211.8	227.9	282.0	384.4	574.4	852.9
107.5°	168.0	171.5	179.6	195.7	221.0	237.1	253.2	306.2	397.1	558.2	795.3
110°	195.7	200.3	207.2	222.1	246.3	263.0	279.7	330.3	413.2	553.6	756.2

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	221.0	225.6	233.7	247.5	270.5	287.8	305.0	353.4	430.5	554.8	730.9
115°	247.5	253.2	260.1	273.9	297.0	312.5	328.0	377.5	447.7	559.4	713.6
117.5°	275.1	279.7	286.6	299.3	321.1	337.2	353.4	399.4	466.2	566.3	704.4
120°	300.4	305.0	311.9	322.3	345.3	361.4	377.5	422.4	484.6	573.2	696.4
122.5°	324.6	328.0	334.9	346.5	369.5	386.2	402.9	444.3	500.7	581.3	691.8
125°	345.3	348.8	355.7	369.5	392.5	408.6	424.7	466.2	518.0	589.3	686.0
127.5°	362.6	367.2	376.4	391.3	413.2	429.9	446.6	486.9	534.1	597.4	682.6
130°	377.5	382.1	393.6	409.8	432.8	448.9	465.0	505.3	549.0	606.6	680.2
132.5°	391.3	397.1	409.8	427.0	451.2	467.3	483.4	521.4	564.0	615.8	679.1
135°	405.2	409.8	423.6	440.8	467.3	483.4	499.5	536.4	576.7	622.7	677.9
137.5°	417.8	423.6	437.4	455.8	482.3	497.2	512.2	549.0	587.0	629.6	677.9
140°	432.8	437.4	451.2	469.6	494.9	509.9	524.9	559.4	595.1	634.2	676.8
142.5°	447.7	451.2	463.9	482.3	506.4	520.2	534.1	567.4	602.0	637.7	676.8
145°	462.7	467.3	478.8	496.1	519.1	531.8	544.4	575.5	607.7	640.0	674.5
147.5°	478.8	482.3	493.8	509.9	529.5	541.0	552.5	582.4	611.2	641.1	671.0
150°	494.9	498.4	507.6	522.6	539.8	550.2	560.5	587.0	613.5	640.0	667.6
152.5°	511.0	512.2	521.4	534.1	550.2	559.4	568.6	591.6	614.6	637.7	661.8
155°	526.0	527.2	534.1	546.7	559.4	568.0	576.7	596.2	615.8	635.4	654.9
157.5°	538.7	539.8	545.6	557.1	567.4	574.9	582.4	599.7	615.8	630.8	648.0
160°	551.3	552.5	557.1	566.3	575.5	581.8	588.2	602.0	615.8	627.3	641.1
162.5°	564.0	562.8	567.4	574.4	582.4	587.0	591.6	603.1	614.6	623.8	635.4
165°	573.2	572.1	574.4	581.3	587.0	590.4	593.9	604.3	612.3	619.2	627.3
167.5°	581.3	580.1	582.4	587.0	591.6	593.9	596.2	604.3	611.2	614.6	620.4
170°	589.3	587.0	588.2	591.6	593.9	595.6	597.4	603.1	608.9	611.2	614.6
172.5°	593.9	592.8	591.6	595.1	596.2	597.4	598.5	602.0	605.4	606.6	607.7
175°	597.4	596.2	595.1	597.4	597.4	598.0	598.5	600.8	603.1	602.0	603.1
177.5°	599.7	597.4	596.2	598.5	598.5	598.5	598.5	599.7	602.0	599.7	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1768.2	1769.5	1772.1	1785.2	1791.7	1793.0	1787.8	1799.6	1803.5	1799.6	1797.0
5°	1851.9	1859.7	1875.4	1892.4	1891.1	1892.4	1900.3	1908.1	1910.7	1900.3	1904.2
7.5°	1925.1	1940.8	1957.8	1984.0	1984.0	1997.1	2002.3	2008.8	2024.5	2016.7	2014.1
10°	2008.8	2029.8	2061.1	2103.0	2104.3	2117.4	2130.5	2151.4	2157.9	2152.7	2155.3
12.5°	2113.5	2154.0	2156.6	2202.4	2223.3	2225.9	2246.9	2242.9	2256.0	2256.0	2278.2
15°	2159.2	2222.0	2257.3	2301.8	2314.9	2299.2	2316.2	2334.5	2335.8	2335.8	2334.5
17.5°	2241.6	2266.5	2301.8	2325.3	2330.6	2330.6	2331.9	2339.7	2334.5	2324.0	2331.9
20°	2258.6	2269.1	2282.2	2279.5	2282.2	2269.1	2256.0	2242.9	2244.2	2237.7	2257.3
22.5°	2227.2	2224.6	2194.5	2174.9	2174.9	2148.8	2123.9	2112.1	2100.4	2104.3	2110.8
25°	2148.8	2108.2	2071.6	2042.8	2036.3	1994.4	1960.4	1950.0	1930.4	1946.1	1948.7
27.5°	2023.2	1977.4	1918.6	1893.7	1859.7	1842.7	1819.2	1787.8	1747.3	1770.8	1766.9
30°	1888.5	1820.5	1772.1	1712.0	1658.3	1654.4	1609.9	1557.6	1536.7	1536.7	1548.5
32.5°	1738.1	1647.9	1577.2	1492.2	1439.9	1417.7	1364.1	1311.8	1323.5	1284.3	1298.7
35°	1562.9	1443.8	1354.9	1272.5	1233.3	1207.1	1137.8	1109.0	1077.7	1059.3	1093.3
37.5°	1395.5	1258.1	1144.4	1054.1	1039.7	992.6	945.6	927.3	908.9	916.8	915.5
40°	1191.4	1069.8	967.8	897.2	872.3	850.1	818.7	796.5	784.7	791.2	792.5
42.5°	1007.0	905.0	829.2	779.5	758.5	742.8	727.2	708.8	704.9	704.9	710.2
45°	864.5	780.8	729.8	689.2	677.5	665.7	653.9	646.1	643.5	638.2	642.1
47.5°	750.7	684.0	652.6	622.5	609.4	606.8	596.4	592.4	587.2	585.9	587.2
50°	655.2	613.4	584.6	567.6	558.4	554.5	549.3	541.4	538.8	545.4	542.7
52.5°	588.5	549.3	533.6	516.6	511.4	506.1	498.3	499.6	498.3	495.7	495.7
55°	521.8	497.0	481.3	468.2	466.9	461.7	455.1	452.5	451.2	448.6	452.5
57.5°	468.2	448.6	434.2	422.4	417.2	417.2	410.7	405.4	405.4	404.1	405.4
60°	414.6	395.0	385.8	374.0	370.1	368.8	364.9	362.3	358.3	358.3	358.3
62.5°	364.9	349.2	338.7	328.3	329.6	323.0	317.8	315.2	315.2	316.5	316.5
65°	317.8	307.3	294.3	285.1	282.5	281.2	278.6	277.3	273.3	276.0	276.0
67.5°	274.6	260.3	252.4	248.5	244.6	243.3	240.6	238.0	236.7	235.4	238.0
70°	231.5	219.7	213.2	210.6	206.6	205.3	204.0	200.1	201.4	202.7	204.0
72.5°	192.3	181.8	180.5	172.6	172.6	172.6	167.4	170.0	168.7	166.1	168.7
75°	151.7	146.5	143.9	139.9	141.2	139.9	138.6	134.7	134.7	136.0	137.3
77.5°	120.3	115.1	113.8	109.9	107.2	109.9	107.2	105.9	105.9	107.2	107.2
80°	88.9	86.3	82.4	82.4	82.4	81.1	81.1	81.1	79.8	78.5	79.8
82.5°	58.9	58.9	57.5	56.2	57.5	54.9	56.2	56.2	56.2	56.2	56.2
85°	37.9	36.6	36.6	35.3	35.3	35.3	36.6	34.0	34.0	35.3	35.3
87.5°	17.0	17.0	17.0	18.3	17.0	17.0	17.0	18.3	17.0	17.0	17.0
90°	38.0	36.8	34.5	36.8	37.4	38.0	38.0	38.0	38.0	38.0	38.0
92.5°	148.5	116.3	99.0	86.3	81.7	77.1	76.0	71.4	72.5	70.2	72.5
95°	394.8	301.6	231.4	183.0	170.4	157.7	142.7	133.5	130.1	131.2	130.1
97.5°	741.3	616.9	492.6	376.4	341.8	307.3	262.4	239.4	226.7	219.8	226.7
100°	1075.0	1050.9	908.1	750.5	680.8	611.2	515.7	466.2	432.8	412.1	432.8
102.5°	1199.4	1335.2	1330.6	1225.8	1151.0	1076.2	970.3	877.1	833.3	803.4	833.3
105°	1159.1	1398.5	1528.5	1543.5	1524.5	1505.5	1434.2	1362.8	1313.3	1297.2	1313.3
107.5°	1073.9	1330.6	1523.9	1636.7	1659.8	1682.8	1681.6	1671.3	1656.3	1629.8	1656.3
110°	994.5	1237.3	1443.4	1590.7	1637.9	1685.1	1734.6	1756.4	1766.8	1765.7	1766.8

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	939.2	1152.2	1347.8	1507.8	1563.6	1619.5	1693.1	1733.4	1755.3	1763.4	1755.3
115°	895.5	1085.4	1262.7	1413.4	1472.7	1532.0	1613.7	1666.7	1696.6	1707.0	1696.6
117.5°	865.6	1030.2	1189.0	1329.4	1385.8	1442.2	1526.2	1582.6	1613.7	1621.8	1613.7
120°	842.5	991.0	1133.7	1255.8	1308.2	1360.5	1441.1	1495.2	1528.5	1540.1	1528.5
122.5°	823.0	959.9	1087.7	1201.7	1247.7	1293.7	1363.9	1416.9	1445.7	1454.9	1445.7
125°	804.6	930.0	1048.6	1149.9	1193.1	1236.2	1302.9	1346.7	1375.5	1384.7	1375.5
127.5°	787.3	900.1	1009.4	1106.1	1146.4	1186.7	1245.4	1286.8	1312.2	1319.1	1312.2
130°	770.0	871.3	970.3	1061.2	1099.2	1137.2	1193.6	1232.7	1255.8	1265.0	1255.8
132.5°	756.2	843.7	933.5	1015.2	1050.3	1085.4	1140.7	1179.8	1200.5	1208.6	1200.5
135°	743.6	818.4	894.3	970.3	1002.6	1034.8	1084.3	1122.2	1143.0	1147.6	1143.0
137.5°	734.3	797.7	863.3	925.4	954.2	983.0	1030.2	1063.5	1082.0	1088.9	1082.0
140°	726.3	778.1	833.3	886.3	911.6	936.9	973.8	1003.7	1020.9	1027.9	1020.9
142.5°	718.2	762.0	806.9	850.6	870.8	890.9	925.4	951.9	966.9	966.9	966.9
145°	711.3	747.0	785.0	820.7	837.4	854.1	881.7	901.2	912.8	916.2	912.8
147.5°	704.4	735.5	766.6	795.3	808.0	820.7	844.8	861.0	869.0	871.3	869.0
150°	695.2	722.8	748.2	772.3	782.6	793.0	810.3	824.1	831.0	832.2	831.0
152.5°	687.2	710.2	733.2	752.8	761.4	770.0	782.7	794.2	798.8	798.8	798.8
155°	676.8	698.7	717.1	734.3	740.6	747.0	759.7	767.7	772.3	770.0	772.3
157.5°	667.6	684.9	701.0	715.9	721.1	726.3	735.5	742.4	744.7	744.7	744.7
160°	657.2	672.2	684.9	697.5	701.6	705.6	713.6	719.4	720.5	720.5	720.5
162.5°	648.0	659.5	669.9	680.2	683.1	686.0	694.1	697.5	698.7	697.5	698.7
165°	637.7	646.9	654.9	663.0	665.3	667.6	672.2	676.8	676.8	675.6	676.8
167.5°	627.3	634.2	641.1	646.9	649.2	651.5	653.8	656.1	656.1	654.9	656.1
170°	619.2	625.0	628.5	633.1	634.2	635.4	636.5	640.0	638.8	636.5	638.8
172.5°	611.2	614.6	616.9	620.4	621.0	621.5	622.7	623.8	622.7	621.5	622.7
175°	604.3	607.7	608.9	610.0	610.6	611.2	611.2	612.3	611.2	608.9	611.2
177.5°	599.7	602.0	602.0	603.1	603.1	603.1	603.1	603.1	602.0	599.7	602.0
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1803.5	1794.3	1786.5	1787.8	1794.3	1789.1	1776.0	1759.0	1752.5	1744.6	1752.5
5°	1912.0	1904.2	1888.5	1889.8	1885.9	1880.7	1859.7	1833.6	1833.6	1812.7	1810.0
7.5°	2019.3	2007.5	1997.1	1994.4	1980.1	1969.6	1951.3	1914.7	1900.3	1875.4	1861.0
10°	2139.6	2130.5	2118.7	2104.3	2096.5	2078.1	2048.1	1994.4	1968.3	1934.3	1909.4
12.5°	2261.2	2259.9	2233.8	2205.0	2203.7	2174.9	2154.0	2082.1	2046.8	2001.0	1942.1
15°	2338.4	2331.9	2317.5	2303.1	2307.0	2275.6	2228.5	2143.5	2120.0	2065.1	2002.3
17.5°	2337.1	2337.1	2333.2	2330.6	2326.6	2317.5	2291.3	2235.1	2197.2	2127.8	2069.0
20°	2262.5	2279.5	2283.5	2282.2	2295.2	2301.8	2300.5	2265.2	2235.1	2173.6	2113.5
22.5°	2113.5	2152.7	2169.7	2180.2	2207.6	2222.0	2256.0	2242.9	2235.1	2189.3	2138.3
25°	1974.8	1987.9	2038.9	2041.5	2079.5	2114.8	2148.8	2171.0	2199.8	2182.8	2139.6
27.5°	1795.7	1825.7	1862.4	1889.8	1897.7	1969.6	2025.8	2067.7	2133.1	2138.3	2123.9
30°	1592.9	1607.3	1667.5	1704.1	1746.0	1798.3	1879.4	1951.3	2010.1	2063.8	2082.1
32.5°	1345.8	1404.6	1439.9	1484.4	1521.0	1613.9	1713.3	1806.1	1874.1	1964.4	2003.6
35°	1119.5	1165.3	1225.4	1243.7	1310.4	1388.9	1518.4	1637.4	1740.7	1832.3	1912.0
37.5°	932.5	969.1	1033.2	1062.0	1101.2	1201.9	1310.4	1458.2	1582.5	1694.9	1794.3
40°	804.3	831.8	880.2	889.3	922.0	1013.6	1101.2	1239.8	1404.6	1556.3	1664.9
42.5°	716.7	729.8	762.5	774.2	795.2	856.6	935.1	1065.9	1218.9	1375.8	1528.9
45°	653.9	663.1	682.7	693.2	719.3	746.8	810.9	915.5	1035.8	1194.0	1358.8
47.5°	597.7	609.4	617.3	623.8	638.2	668.3	710.2	787.3	902.4	1047.6	1207.1
50°	550.6	554.5	568.9	570.2	579.4	599.0	638.2	685.3	776.9	894.6	1048.9
52.5°	503.5	507.4	516.6	525.7	529.7	545.4	571.5	610.8	678.8	771.6	908.9
55°	456.4	461.7	470.8	477.4	481.3	494.4	510.1	548.0	601.6	667.0	779.5
57.5°	409.4	421.1	423.7	427.7	434.2	448.6	463.0	485.2	527.1	587.2	669.6
60°	364.9	368.8	378.0	381.9	388.4	396.3	414.6	431.6	461.7	508.7	583.3
62.5°	319.1	328.3	332.2	336.1	341.3	350.5	362.3	380.6	406.7	444.7	503.5
65°	279.9	281.2	289.0	294.3	299.5	306.0	317.8	334.8	350.5	385.8	429.0
67.5°	241.9	244.6	247.2	252.4	259.0	265.5	276.0	285.1	304.7	328.3	362.3
70°	205.3	205.3	211.9	215.8	214.5	222.3	230.2	240.6	255.0	277.3	304.7
72.5°	172.6	171.3	176.6	177.9	180.5	185.7	190.9	201.4	209.3	226.3	247.2
75°	137.3	139.9	142.6	142.6	146.5	150.4	155.6	160.9	170.0	180.5	196.2
77.5°	108.5	108.5	111.2	112.5	116.4	115.1	120.3	125.6	132.1	141.2	153.0
80°	79.8	82.4	82.4	82.4	83.7	85.0	90.2	94.2	98.1	104.6	109.9
82.5°	56.2	56.2	58.9	58.9	58.9	61.5	61.5	62.8	65.4	69.3	73.2
85°	35.3	35.3	35.3	36.6	35.3	36.6	39.2	37.9	39.2	41.9	41.9
87.5°	17.0	17.0	17.0	17.0	17.0	18.3	17.0	18.3	19.6	19.6	19.6
90°	38.0	38.0	38.0	37.4	36.8	34.5	36.8	38.0	39.1	38.0	31.1
92.5°	71.4	76.0	77.1	81.7	86.3	99.0	116.3	148.5	177.3	175.0	135.8
95°	133.5	142.7	157.7	170.4	183.0	231.4	301.6	394.8	451.2	399.4	265.9
97.5°	239.4	262.4	307.3	341.8	376.4	492.6	616.9	741.3	735.5	568.6	353.4
100°	466.2	515.7	611.2	680.8	750.5	908.1	1050.9	1075.0	909.3	626.2	377.5
102.5°	877.1	970.3	1076.2	1151.0	1225.8	1330.6	1335.2	1199.4	915.1	604.3	378.7
105°	1362.8	1434.2	1505.5	1524.5	1543.5	1528.5	1398.5	1159.1	852.9	574.4	384.4
107.5°	1671.3	1681.6	1682.8	1659.8	1636.7	1523.9	1330.6	1073.9	795.3	558.2	397.1
110°	1756.4	1734.6	1685.1	1637.9	1590.7	1443.4	1237.3	994.5	756.2	553.6	413.2

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1733.4	1693.1	1619.5	1563.6	1507.8	1347.8	1152.2	939.2	730.9	554.8	430.5
115°	1666.7	1613.7	1532.0	1472.7	1413.4	1262.7	1085.4	895.5	713.6	559.4	447.7
117.5°	1582.6	1526.2	1442.2	1385.8	1329.4	1189.0	1030.2	865.6	704.4	566.3	466.2
120°	1495.2	1441.1	1360.5	1308.2	1255.8	1133.7	991.0	842.5	696.4	573.2	484.6
122.5°	1416.9	1363.9	1293.7	1247.7	1201.7	1087.7	959.9	823.0	691.8	581.3	500.7
125°	1346.7	1302.9	1236.2	1193.1	1149.9	1048.6	930.0	804.6	686.0	589.3	518.0
127.5°	1286.8	1245.4	1186.7	1146.4	1106.1	1009.4	900.1	787.3	682.6	597.4	534.1
130°	1232.7	1193.6	1137.2	1099.2	1061.2	970.3	871.3	770.0	680.2	606.6	549.0
132.5°	1179.8	1140.7	1085.4	1050.3	1015.2	933.5	843.7	756.2	679.1	615.8	564.0
135°	1122.2	1084.3	1034.8	1002.6	970.3	894.3	818.4	743.6	677.9	622.7	576.7
137.5°	1063.5	1030.2	983.0	954.2	925.4	863.3	797.7	734.3	677.9	629.6	587.0
140°	1003.7	973.8	936.9	911.6	886.3	833.3	778.1	726.3	676.8	634.2	595.1
142.5°	951.9	925.4	890.9	870.8	850.6	806.9	762.0	718.2	676.8	637.7	602.0
145°	901.2	881.7	854.1	837.4	820.7	785.0	747.0	711.3	674.5	640.0	607.7
147.5°	861.0	844.8	820.7	808.0	795.3	766.6	735.5	704.4	671.0	641.1	611.2
150°	824.1	810.3	793.0	782.6	772.3	748.2	722.8	695.2	667.6	640.0	613.5
152.5°	794.2	782.7	770.0	761.4	752.8	733.2	710.2	687.2	661.8	637.7	614.6
155°	767.7	759.7	747.0	740.6	734.3	717.1	698.7	676.8	654.9	635.4	615.8
157.5°	742.4	735.5	726.3	721.1	715.9	701.0	684.9	667.6	648.0	630.8	615.8
160°	719.4	713.6	705.6	701.6	697.5	684.9	672.2	657.2	641.1	627.3	615.8
162.5°	697.5	694.1	686.0	683.1	680.2	669.9	659.5	648.0	635.4	623.8	614.6
165°	676.8	672.2	667.6	665.3	663.0	654.9	646.9	637.7	627.3	619.2	612.3
167.5°	656.1	653.8	651.5	649.2	646.9	641.1	634.2	627.3	620.4	614.6	611.2
170°	640.0	636.5	635.4	634.2	633.1	628.5	625.0	619.2	614.6	611.2	608.9
172.5°	623.8	622.7	621.5	621.0	620.4	616.9	614.6	611.2	607.7	606.6	605.4
175°	612.3	611.2	611.2	610.6	610.0	608.9	607.7	604.3	603.1	602.0	603.1
177.5°	603.1	603.1	603.1	603.1	603.1	602.0	602.0	599.7	598.5	599.7	602.0
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1746.0	1739.4	1735.5	1738.1	1730.3	1710.6	1710.6	1717.2	1709.3	1701.5	1689.7
5°	1794.3	1781.3	1773.4	1772.1	1753.8	1722.4	1715.9	1709.3	1692.3	1674.0	1654.4
7.5°	1841.4	1817.9	1804.8	1795.7	1769.5	1729.0	1712.0	1697.6	1670.1	1642.6	1617.8
10°	1880.7	1846.7	1831.0	1816.6	1782.6	1731.6	1704.1	1677.9	1642.6	1607.3	1575.9
12.5°	1912.0	1872.8	1853.2	1832.3	1790.4	1723.7	1689.7	1647.9	1612.6	1565.5	1534.1
15°	1964.4	1883.3	1865.0	1845.3	1802.2	1710.6	1668.8	1621.7	1573.3	1510.5	1476.5
17.5°	2006.2	1897.7	1896.4	1854.5	1798.3	1705.4	1641.3	1579.9	1527.5	1464.8	1411.1
20°	2031.1	1919.9	1899.0	1855.8	1785.2	1670.1	1603.4	1535.4	1479.2	1403.3	1349.7
22.5°	2052.0	1951.3	1896.4	1844.0	1757.7	1658.3	1560.2	1496.2	1419.0	1336.6	1285.6
25°	2059.8	1957.8	1900.3	1840.1	1738.1	1624.3	1513.2	1443.8	1357.5	1283.0	1213.7
27.5°	2061.1	1956.5	1885.9	1823.1	1710.6	1579.9	1466.1	1392.8	1297.4	1211.1	1141.7
30°	2048.1	1942.1	1878.0	1810.0	1684.5	1539.3	1408.5	1327.4	1225.4	1139.1	1067.2
32.5°	2008.8	1913.4	1861.0	1786.5	1650.5	1483.1	1353.6	1263.4	1156.1	1071.1	1001.8
35°	1943.4	1878.0	1820.5	1751.2	1606.0	1430.8	1298.7	1192.7	1084.2	1003.1	937.7
37.5°	1862.4	1827.0	1773.4	1705.4	1555.0	1383.7	1237.2	1119.5	1011.0	932.5	868.4
40°	1752.5	1761.6	1709.3	1647.9	1494.9	1319.6	1157.4	1045.0	942.9	869.7	806.9
42.5°	1633.5	1671.4	1641.3	1582.5	1428.2	1249.0	1098.6	974.3	874.9	799.1	746.8
45°	1505.3	1570.7	1552.4	1509.2	1358.8	1174.4	1014.9	894.6	806.9	733.7	687.9
47.5°	1365.4	1458.2	1458.2	1426.8	1281.7	1099.9	942.9	820.0	733.7	681.4	636.9
50°	1222.8	1327.4	1344.4	1323.5	1195.4	1014.9	855.3	744.2	669.6	618.6	585.9
52.5°	1073.7	1195.4	1226.7	1216.3	1103.8	933.8	783.4	674.8	606.8	562.4	533.6
55°	931.2	1072.4	1106.4	1110.3	1005.7	844.9	703.6	608.1	542.7	512.7	487.8
57.5°	796.5	932.5	970.4	976.9	906.3	763.8	629.1	545.4	486.5	461.7	442.0
60°	681.4	795.2	844.9	859.2	797.8	669.6	559.8	478.7	434.2	410.7	392.3
62.5°	587.2	678.8	731.1	735.0	707.5	587.2	487.8	419.8	381.9	361.0	351.8
65°	495.7	578.1	609.4	625.1	602.9	508.7	421.1	364.9	334.8	316.5	307.3
67.5°	422.4	474.7	500.9	521.8	499.6	429.0	358.3	312.6	290.3	272.0	266.8
70°	346.6	389.7	409.4	430.3	410.7	357.0	306.0	264.2	244.6	230.2	223.6
72.5°	277.3	311.3	329.6	342.7	330.9	286.4	244.6	215.8	201.4	190.9	187.0
75°	219.7	243.3	253.7	262.9	257.6	223.6	197.5	173.9	160.9	151.7	149.1
77.5°	167.4	184.4	196.2	198.8	192.3	170.0	147.8	133.4	122.9	117.7	115.1
80°	119.0	129.5	136.0	139.9	133.4	124.2	108.5	98.1	88.9	82.4	81.1
82.5°	79.8	85.0	90.2	88.9	86.3	78.5	69.3	64.1	60.2	54.9	54.9
85°	45.8	47.1	49.7	51.0	49.7	44.5	39.2	36.6	34.0	30.1	30.1
87.5°	19.6	20.9	20.9	22.2	19.6	19.6	17.0	14.4	14.4	13.1	11.8
90°	23.0	17.3	15.6	13.8	11.5	9.2	4.6	1.2	4.6	9.2	11.5
92.5°	92.1	61.0	54.6	48.3	39.1	33.4	24.2	17.3	24.2	33.4	39.1
95°	165.7	112.8	99.0	85.2	66.8	56.4	44.9	40.3	44.9	56.4	66.8
97.5°	214.1	146.2	130.6	115.1	94.4	79.4	66.8	59.9	66.8	79.4	94.4
100°	237.1	176.1	160.0	143.9	120.9	102.4	92.1	88.6	92.1	102.4	120.9
102.5°	257.8	202.6	186.4	170.3	146.2	127.8	117.4	115.1	117.4	127.8	146.2
105°	282.0	227.9	211.8	195.7	170.3	153.1	145.0	140.4	145.0	153.1	170.3
107.5°	306.2	253.2	237.1	221.0	195.7	179.6	171.5	168.0	171.5	179.6	195.7
110°	330.3	279.7	263.0	246.3	222.1	207.2	200.3	195.7	200.3	207.2	222.1

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	353.4	305.0	287.8	270.5	247.5	233.7	225.6	221.0	225.6	233.7	247.5
115°	377.5	328.0	312.5	297.0	273.9	260.1	253.2	247.5	253.2	260.1	273.9
117.5°	399.4	353.4	337.2	321.1	299.3	286.6	279.7	275.1	279.7	286.6	299.3
120°	422.4	377.5	361.4	345.3	322.3	311.9	305.0	300.4	305.0	311.9	322.3
122.5°	444.3	402.9	386.2	369.5	346.5	334.9	328.0	324.6	328.0	334.9	346.5
125°	466.2	424.7	408.6	392.5	369.5	355.7	348.8	345.3	348.8	355.7	369.5
127.5°	486.9	446.6	429.9	413.2	391.3	376.4	367.2	362.6	367.2	376.4	391.3
130°	505.3	465.0	448.9	432.8	409.8	393.6	382.1	377.5	382.1	393.6	409.8
132.5°	521.4	483.4	467.3	451.2	427.0	409.8	397.1	391.3	397.1	409.8	427.0
135°	536.4	499.5	483.4	467.3	440.8	423.6	409.8	405.2	409.8	423.6	440.8
137.5°	549.0	512.2	497.2	482.3	455.8	437.4	423.6	417.8	423.6	437.4	455.8
140°	559.4	524.9	509.9	494.9	469.6	451.2	437.4	432.8	437.4	451.2	469.6
142.5°	567.4	534.1	520.2	506.4	482.3	463.9	451.2	447.7	451.2	463.9	482.3
145°	575.5	544.4	531.8	519.1	496.1	478.8	467.3	462.7	467.3	478.8	496.1
147.5°	582.4	552.5	541.0	529.5	509.9	493.8	482.3	478.8	482.3	493.8	509.9
150°	587.0	560.5	550.2	539.8	522.6	507.6	498.4	494.9	498.4	507.6	522.6
152.5°	591.6	568.6	559.4	550.2	534.1	521.4	512.2	511.0	512.2	521.4	534.1
155°	596.2	576.7	568.0	559.4	546.7	534.1	527.2	526.0	527.2	534.1	546.7
157.5°	599.7	582.4	574.9	567.4	557.1	545.6	539.8	538.7	539.8	545.6	557.1
160°	602.0	588.2	581.8	575.5	566.3	557.1	552.5	551.3	552.5	557.1	566.3
162.5°	603.1	591.6	587.0	582.4	574.4	567.4	562.8	564.0	562.8	567.4	574.4
165°	604.3	593.9	590.4	587.0	581.3	574.4	572.1	573.2	572.1	574.4	581.3
167.5°	604.3	596.2	593.9	591.6	587.0	582.4	580.1	581.3	580.1	582.4	587.0
170°	603.1	597.4	595.6	593.9	591.6	588.2	587.0	589.3	587.0	588.2	591.6
172.5°	602.0	598.5	597.4	596.2	595.1	591.6	592.8	593.9	592.8	591.6	595.1
175°	600.8	598.5	598.0	597.4	597.4	595.1	596.2	597.4	596.2	595.1	597.4
177.5°	599.7	598.5	598.5	598.5	598.5	596.2	597.4	599.7	597.4	596.2	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1683.2	1689.7	1688.4	1675.3	1660.9	1649.2	1626.9	1629.6	1621.7	1623.0	1630.9
5°	1641.3	1641.3	1636.1	1617.8	1594.2	1581.2	1556.3	1549.8	1534.1	1532.8	1531.5
7.5°	1596.9	1590.3	1583.8	1557.6	1528.9	1507.9	1473.9	1466.1	1450.4	1439.9	1434.7
10°	1544.5	1535.4	1522.3	1492.2	1456.9	1430.8	1395.5	1385.0	1354.9	1341.8	1334.0
12.5°	1487.0	1481.8	1460.8	1436.0	1378.5	1349.7	1298.7	1309.1	1279.1	1252.9	1249.0
15°	1429.5	1409.8	1398.1	1357.5	1288.2	1275.1	1234.6	1213.7	1186.2	1165.3	1165.3
17.5°	1373.2	1343.1	1317.0	1273.8	1222.8	1186.2	1156.1	1145.7	1111.7	1090.7	1086.8
20°	1298.7	1264.7	1258.1	1196.7	1161.4	1120.8	1092.0	1065.9	1041.0	1031.9	1025.3
22.5°	1228.1	1188.8	1178.4	1126.0	1090.7	1050.2	1021.4	1003.1	984.8	978.3	966.5
25°	1152.2	1128.7	1113.0	1056.7	1017.5	979.6	959.9	946.9	929.9	928.6	920.7
27.5°	1079.0	1056.7	1041.0	987.4	958.6	923.3	907.6	893.2	884.1	880.2	876.2
30°	1016.2	991.3	973.0	933.8	898.5	869.7	856.6	847.5	842.2	835.7	834.4
32.5°	946.9	932.5	907.6	877.6	850.1	822.6	814.8	808.2	800.4	797.8	796.5
35°	888.0	868.4	852.7	818.7	806.9	783.4	774.2	769.0	758.5	755.9	753.3
37.5°	830.5	812.2	795.2	774.2	752.0	738.9	733.7	725.8	720.6	721.9	719.3
40°	772.9	758.5	745.5	723.2	710.2	703.6	693.2	685.3	682.7	684.0	682.7
42.5°	716.7	703.6	695.8	678.8	665.7	659.1	652.6	644.8	648.7	648.7	652.6
45°	665.7	653.9	648.7	635.6	627.8	617.3	610.8	609.4	614.7	613.4	613.4
47.5°	613.4	609.4	602.9	591.1	580.7	574.1	572.8	572.8	578.1	580.7	579.4
50°	572.8	565.0	557.1	548.0	540.1	537.5	533.6	536.2	541.4	541.4	544.1
52.5°	521.8	516.6	514.0	506.1	500.9	500.9	500.9	502.2	506.1	510.1	508.7
55°	477.4	473.4	470.8	466.9	460.4	461.7	460.4	463.0	466.9	470.8	473.4
57.5°	430.3	429.0	426.4	419.8	419.8	418.5	422.4	423.7	430.3	432.9	436.8
60°	388.4	384.5	384.5	379.3	379.3	379.3	383.2	387.1	392.3	393.7	396.3
62.5°	344.0	344.0	342.7	338.7	338.7	342.7	344.0	349.2	351.8	351.8	355.7
65°	302.1	300.8	299.5	300.8	302.1	302.1	306.0	308.6	311.3	312.6	313.9
67.5°	260.3	259.0	261.6	260.3	262.9	268.1	266.8	270.7	274.6	274.6	276.0
70°	221.0	223.6	222.3	224.9	223.6	226.3	230.2	231.5	231.5	232.8	236.7
72.5°	184.4	184.4	184.4	183.1	184.4	187.0	189.6	190.9	193.6	194.9	198.8
75°	149.1	149.1	146.5	149.1	149.1	151.7	154.3	154.3	154.3	156.9	160.9
77.5°	112.5	113.8	112.5	115.1	115.1	116.4	119.0	117.7	120.3	121.6	122.9
80°	82.4	81.1	81.1	81.1	82.4	82.4	85.0	86.3	86.3	90.2	87.6
82.5°	52.3	53.6	52.3	53.6	53.6	54.9	53.6	54.9	56.2	58.9	57.5
85°	30.1	28.8	28.8	30.1	28.8	28.8	30.1	28.8	30.1	28.8	30.1
87.5°	11.8	10.5	10.5	10.5	10.5	9.2	9.2	7.8	7.8	7.8	6.5
90°	13.8	15.6	17.3	23.0	31.1	38.0	39.1	38.0	36.8	34.5	36.8
92.5°	48.3	54.6	61.0	92.1	135.8	175.0	177.3	148.5	116.3	99.0	86.3
95°	85.2	99.0	112.8	165.7	265.9	399.4	451.2	394.8	301.6	231.4	183.0
97.5°	115.1	130.6	146.2	214.1	353.4	568.6	735.5	741.3	616.9	492.6	376.4
100°	143.9	160.0	176.1	237.1	377.5	626.2	909.3	1075.0	1050.9	908.1	750.5
102.5°	170.3	186.4	202.6	257.8	378.7	604.3	915.1	1199.4	1335.2	1330.6	1225.8
105°	195.7	211.8	227.9	282.0	384.4	574.4	852.9	1159.1	1398.5	1528.5	1543.5
107.5°	221.0	237.1	253.2	306.2	397.1	558.2	795.3	1073.9	1330.6	1523.9	1636.7
110°	246.3	263.0	279.7	330.3	413.2	553.6	756.2	994.5	1237.3	1443.4	1590.7

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	270.5	287.8	305.0	353.4	430.5	554.8	730.9	939.2	1152.2	1347.8	1507.8
115°	297.0	312.5	328.0	377.5	447.7	559.4	713.6	895.5	1085.4	1262.7	1413.4
117.5°	321.1	337.2	353.4	399.4	466.2	566.3	704.4	865.6	1030.2	1189.0	1329.4
120°	345.3	361.4	377.5	422.4	484.6	573.2	696.4	842.5	991.0	1133.7	1255.8
122.5°	369.5	386.2	402.9	444.3	500.7	581.3	691.8	823.0	959.9	1087.7	1201.7
125°	392.5	408.6	424.7	466.2	518.0	589.3	686.0	804.6	930.0	1048.6	1149.9
127.5°	413.2	429.9	446.6	486.9	534.1	597.4	682.6	787.3	900.1	1009.4	1106.1
130°	432.8	448.9	465.0	505.3	549.0	606.6	680.2	770.0	871.3	970.3	1061.2
132.5°	451.2	467.3	483.4	521.4	564.0	615.8	679.1	756.2	843.7	933.5	1015.2
135°	467.3	483.4	499.5	536.4	576.7	622.7	677.9	743.6	818.4	894.3	970.3
137.5°	482.3	497.2	512.2	549.0	587.0	629.6	677.9	734.3	797.7	863.3	925.4
140°	494.9	509.9	524.9	559.4	595.1	634.2	676.8	726.3	778.1	833.3	886.3
142.5°	506.4	520.2	534.1	567.4	602.0	637.7	676.8	718.2	762.0	806.9	850.6
145°	519.1	531.8	544.4	575.5	607.7	640.0	674.5	711.3	747.0	785.0	820.7
147.5°	529.5	541.0	552.5	582.4	611.2	641.1	671.0	704.4	735.5	766.6	795.3
150°	539.8	550.2	560.5	587.0	613.5	640.0	667.6	695.2	722.8	748.2	772.3
152.5°	550.2	559.4	568.6	591.6	614.6	637.7	661.8	687.2	710.2	733.2	752.8
155°	559.4	568.0	576.7	596.2	615.8	635.4	654.9	676.8	698.7	717.1	734.3
157.5°	567.4	574.9	582.4	599.7	615.8	630.8	648.0	667.6	684.9	701.0	715.9
160°	575.5	581.8	588.2	602.0	615.8	627.3	641.1	657.2	672.2	684.9	697.5
162.5°	582.4	587.0	591.6	603.1	614.6	623.8	635.4	648.0	659.5	669.9	680.2
165°	587.0	590.4	593.9	604.3	612.3	619.2	627.3	637.7	646.9	654.9	663.0
167.5°	591.6	593.9	596.2	604.3	611.2	614.6	620.4	627.3	634.2	641.1	646.9
170°	593.9	595.6	597.4	603.1	608.9	611.2	614.6	619.2	625.0	628.5	633.1
172.5°	596.2	597.4	598.5	602.0	605.4	606.6	607.7	611.2	614.6	616.9	620.4
175°	597.4	598.0	598.5	600.8	603.1	602.0	603.1	604.3	607.7	608.9	610.0
177.5°	598.5	598.5	598.5	599.7	602.0	599.7	598.5	599.7	602.0	602.0	603.1
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1621.7	1625.6	1616.5	1613.9	1616.5	1607.3	1609.9	1612.6	1612.6	1616.5	1619.1
5°	1527.5	1522.3	1513.2	1510.5	1507.9	1511.9	1509.2	1513.2	1514.5	1523.6	1524.9
7.5°	1434.7	1426.8	1419.0	1411.1	1408.5	1402.0	1408.5	1408.5	1417.7	1415.1	1421.6
10°	1324.8	1323.5	1313.1	1309.1	1303.9	1293.4	1307.8	1303.9	1310.4	1322.2	1324.8
12.5°	1243.7	1229.4	1235.9	1217.6	1224.1	1213.7	1215.0	1215.0	1225.4	1226.7	1224.1
15°	1166.6	1154.8	1137.8	1130.0	1126.0	1120.8	1137.8	1139.1	1131.3	1149.6	1143.0
17.5°	1088.1	1088.1	1072.4	1068.5	1058.0	1063.3	1060.7	1062.0	1059.3	1072.4	1079.0
20°	1020.1	1013.6	1008.3	1009.6	996.6	994.0	991.3	994.0	1003.1	1012.3	1014.9
22.5°	965.2	961.3	948.2	950.8	940.3	944.3	941.6	948.2	949.5	949.5	958.6
25°	912.9	907.6	908.9	903.7	899.8	899.8	895.9	899.8	905.0	907.6	908.9
27.5°	873.6	869.7	863.2	859.2	861.9	855.3	860.6	864.5	864.5	861.9	864.5
30°	826.5	829.2	829.2	816.1	821.3	818.7	822.6	825.2	825.2	826.5	823.9
32.5°	795.2	787.3	786.0	784.7	784.7	779.5	779.5	783.4	784.7	786.0	789.9
35°	753.3	753.3	746.8	750.7	745.5	746.8	745.5	746.8	749.4	745.5	749.4
37.5°	715.4	716.7	714.1	716.7	718.0	715.4	712.8	718.0	715.4	715.4	712.8
40°	682.7	681.4	682.7	682.7	682.7	684.0	681.4	681.4	681.4	678.8	676.1
42.5°	655.2	647.4	650.0	651.3	647.4	647.4	648.7	647.4	651.3	643.5	643.5
45°	616.0	613.4	614.7	614.7	617.3	613.4	616.0	617.3	613.4	612.1	609.4
47.5°	580.7	583.3	580.7	583.3	583.3	585.9	580.7	582.0	583.3	578.1	574.1
50°	545.4	545.4	549.3	548.0	549.3	546.7	546.7	545.4	546.7	544.1	540.1
52.5°	512.7	508.7	515.3	514.0	512.7	511.4	510.1	511.4	508.7	506.1	506.1
55°	472.1	472.1	476.1	477.4	477.4	474.7	472.1	473.4	472.1	470.8	469.5
57.5°	439.4	434.2	436.8	438.1	438.1	434.2	436.8	434.2	434.2	435.5	431.6
60°	397.6	397.6	395.0	398.9	398.9	396.3	396.3	397.6	395.0	393.7	392.3
62.5°	353.1	354.4	358.3	359.7	361.0	358.3	355.7	357.0	357.0	353.1	354.4
65°	315.2	317.8	323.0	321.7	319.1	320.4	317.8	319.1	315.2	316.5	312.6
67.5°	278.6	277.3	278.6	278.6	281.2	279.9	277.3	277.3	276.0	279.9	276.0
70°	239.3	239.3	239.3	239.3	240.6	241.9	239.3	236.7	238.0	235.4	234.1
72.5°	198.8	200.1	198.8	201.4	197.5	200.1	200.1	198.8	197.5	197.5	197.5
75°	160.9	163.5	159.6	160.9	159.6	162.2	160.9	160.9	158.2	156.9	158.2
77.5°	122.9	124.2	121.6	122.9	121.6	122.9	122.9	121.6	121.6	121.6	121.6
80°	87.6	88.9	87.6	86.3	85.0	87.6	85.0	86.3	87.6	86.3	88.9
82.5°	56.2	56.2	54.9	56.2	53.6	53.6	54.9	54.9	53.6	56.2	53.6
85°	27.5	27.5	30.1	27.5	26.2	26.2	26.2	27.5	26.2	28.8	27.5
87.5°	6.5	5.2	6.5	6.5	5.2	5.2	6.5	5.2	6.5	7.8	5.2
90°	37.4	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.4
92.5°	81.7	77.1	76.0	71.4	72.5	70.2	72.5	71.4	76.0	77.1	81.7
95°	170.4	157.7	142.7	133.5	130.1	131.2	130.1	133.5	142.7	157.7	170.4
97.5°	341.8	307.3	262.4	239.4	226.7	219.8	226.7	239.4	262.4	307.3	341.8
100°	680.8	611.2	515.7	466.2	432.8	412.1	432.8	466.2	515.7	611.2	680.8
102.5°	1151.0	1076.2	970.3	877.1	833.3	803.4	833.3	877.1	970.3	1076.2	1151.0
105°	1524.5	1505.5	1434.2	1362.8	1313.3	1297.2	1313.3	1362.8	1434.2	1505.5	1524.5
107.5°	1659.8	1682.8	1681.6	1671.3	1656.3	1629.8	1656.3	1671.3	1681.6	1682.8	1659.8
110°	1637.9	1685.1	1734.6	1756.4	1766.8	1765.7	1766.8	1756.4	1734.6	1685.1	1637.9

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1563.6	1619.5	1693.1	1733.4	1755.3	1763.4	1755.3	1733.4	1693.1	1619.5	1563.6
115°	1472.7	1532.0	1613.7	1666.7	1696.6	1707.0	1696.6	1666.7	1613.7	1532.0	1472.7
117.5°	1385.8	1442.2	1526.2	1582.6	1613.7	1621.8	1613.7	1582.6	1526.2	1442.2	1385.8
120°	1308.2	1360.5	1441.1	1495.2	1528.5	1540.1	1528.5	1495.2	1441.1	1360.5	1308.2
122.5°	1247.7	1293.7	1363.9	1416.9	1445.7	1454.9	1445.7	1416.9	1363.9	1293.7	1247.7
125°	1193.1	1236.2	1302.9	1346.7	1375.5	1384.7	1375.5	1346.7	1302.9	1236.2	1193.1
127.5°	1146.4	1186.7	1245.4	1286.8	1312.2	1319.1	1312.2	1286.8	1245.4	1186.7	1146.4
130°	1099.2	1137.2	1193.6	1232.7	1255.8	1265.0	1255.8	1232.7	1193.6	1137.2	1099.2
132.5°	1050.3	1085.4	1140.7	1179.8	1200.5	1208.6	1200.5	1179.8	1140.7	1085.4	1050.3
135°	1002.6	1034.8	1084.3	1122.2	1143.0	1147.6	1143.0	1122.2	1084.3	1034.8	1002.6
137.5°	954.2	983.0	1030.2	1063.5	1082.0	1088.9	1082.0	1063.5	1030.2	983.0	954.2
140°	911.6	936.9	973.8	1003.7	1020.9	1027.9	1020.9	1003.7	973.8	936.9	911.6
142.5°	870.8	890.9	925.4	951.9	966.9	966.9	966.9	951.9	925.4	890.9	870.8
145°	837.4	854.1	881.7	901.2	912.8	916.2	912.8	901.2	881.7	854.1	837.4
147.5°	808.0	820.7	844.8	861.0	869.0	871.3	869.0	861.0	844.8	820.7	808.0
150°	782.6	793.0	810.3	824.1	831.0	832.2	831.0	824.1	810.3	793.0	782.6
152.5°	761.4	770.0	782.7	794.2	798.8	798.8	798.8	794.2	782.7	770.0	761.4
155°	740.6	747.0	759.7	767.7	772.3	770.0	772.3	767.7	759.7	747.0	740.6
157.5°	721.1	726.3	735.5	742.4	744.7	744.7	744.7	742.4	735.5	726.3	721.1
160°	701.6	705.6	713.6	719.4	720.5	720.5	720.5	719.4	713.6	705.6	701.6
162.5°	683.1	686.0	694.1	697.5	698.7	697.5	698.7	697.5	694.1	686.0	683.1
165°	665.3	667.6	672.2	676.8	676.8	675.6	676.8	676.8	672.2	667.6	665.3
167.5°	649.2	651.5	653.8	656.1	656.1	654.9	656.1	656.1	653.8	651.5	649.2
170°	634.2	635.4	636.5	640.0	638.8	636.5	638.8	640.0	636.5	635.4	634.2
172.5°	621.0	621.5	622.7	623.8	622.7	621.5	622.7	623.8	622.7	621.5	621.0
175°	610.6	611.2	611.2	612.3	611.2	608.9	611.2	612.3	611.2	611.2	610.6
177.5°	603.1	603.1	603.1	603.1	602.0	599.7	602.0	603.1	603.1	603.1	603.1
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1615.2	1625.6	1621.7	1607.3	1624.3	1624.3	1636.1	1636.1	1650.5	1655.7	1663.6
5°	1523.6	1531.5	1538.0	1531.5	1543.2	1561.5	1572.0	1581.2	1600.8	1608.6	1620.4
7.5°	1425.5	1439.9	1446.5	1446.5	1466.1	1487.0	1507.9	1521.0	1548.5	1558.9	1570.7
10°	1330.1	1347.1	1360.1	1358.8	1391.5	1404.6	1430.8	1460.8	1488.3	1504.0	1521.0
12.5°	1229.4	1238.5	1256.8	1283.0	1290.8	1314.4	1344.4	1382.4	1432.1	1446.5	1471.3
15°	1145.7	1170.5	1184.9	1196.7	1215.0	1237.2	1269.9	1306.5	1356.2	1387.6	1413.8
17.5°	1075.0	1107.7	1116.9	1114.3	1137.8	1171.8	1209.7	1237.2	1281.7	1319.6	1344.4
20°	1017.5	1030.6	1046.3	1052.8	1071.1	1107.7	1144.4	1175.7	1212.4	1242.4	1271.2
22.5°	959.9	970.4	983.5	995.3	1009.6	1030.6	1065.9	1105.1	1140.4	1169.2	1201.9
25°	912.9	919.4	931.2	940.3	956.0	970.4	995.3	1038.4	1080.3	1097.3	1126.0
27.5°	867.1	872.3	880.2	890.6	898.5	912.9	935.1	970.4	1013.6	1030.6	1069.8
30°	826.5	830.5	838.3	843.6	847.5	864.5	881.5	908.9	941.6	965.2	994.0
32.5°	788.6	792.5	800.4	801.7	806.9	816.1	831.8	856.6	885.4	905.0	929.9
35°	746.8	749.4	757.2	759.8	763.8	771.6	783.4	801.7	827.9	842.2	864.5
37.5°	714.1	712.8	718.0	721.9	727.2	731.1	735.0	753.3	772.9	786.0	803.0
40°	678.8	676.1	677.5	682.7	685.3	690.5	690.5	708.8	721.9	732.4	745.5
42.5°	643.5	642.1	639.5	642.1	644.8	646.1	647.4	660.5	673.5	682.7	697.1
45°	608.1	606.8	604.2	605.5	605.5	608.1	612.1	617.3	626.5	634.3	642.1
47.5°	575.4	572.8	568.9	567.6	570.2	570.2	570.2	575.4	584.6	587.2	595.1
50°	541.4	537.5	532.3	529.7	529.7	528.4	531.0	532.3	540.1	542.7	549.3
52.5°	504.8	502.2	497.0	491.7	493.1	490.4	491.7	493.1	495.7	499.6	503.5
55°	468.2	463.0	459.0	457.7	453.8	453.8	449.9	455.1	453.8	455.1	460.4
57.5°	432.9	427.7	421.1	418.5	414.6	413.3	410.7	409.4	410.7	414.6	418.5
60°	391.0	388.4	384.5	380.6	378.0	374.0	371.4	371.4	370.1	370.1	371.4
62.5°	350.5	349.2	344.0	342.7	340.0	337.4	333.5	330.9	330.9	333.5	334.8
65°	311.3	310.0	306.0	304.7	298.2	295.6	294.3	293.0	290.3	290.3	290.3
67.5°	274.6	270.7	270.7	264.2	259.0	256.3	253.7	252.4	252.4	252.4	253.7
70°	234.1	234.1	230.2	226.3	221.0	222.3	218.4	214.5	214.5	211.9	213.2
72.5°	194.9	193.6	189.6	188.3	184.4	180.5	177.9	180.5	176.6	175.2	176.6
75°	156.9	155.6	153.0	150.4	151.7	147.8	143.9	142.6	142.6	139.9	139.9
77.5°	120.3	122.9	117.7	116.4	113.8	111.2	109.9	108.5	108.5	108.5	111.2
80°	83.7	85.0	85.0	82.4	83.7	79.8	79.8	79.8	75.9	77.2	78.5
82.5°	53.6	53.6	52.3	53.6	52.3	52.3	51.0	51.0	49.7	49.7	51.0
85°	30.1	28.8	27.5	30.1	28.8	28.8	27.5	27.5	27.5	27.5	27.5
87.5°	6.5	7.8	7.8	7.8	7.8	9.2	9.2	9.2	10.5	10.5	10.5
90°	36.8	34.5	36.8	38.0	39.1	38.0	31.1	23.0	17.3	15.6	13.8
92.5°	86.3	99.0	116.3	148.5	177.3	175.0	135.8	92.1	61.0	54.6	48.3
95°	183.0	231.4	301.6	394.8	451.2	399.4	265.9	165.7	112.8	99.0	85.2
97.5°	376.4	492.6	616.9	741.3	735.5	568.6	353.4	214.1	146.2	130.6	115.1
100°	750.5	908.1	1050.9	1075.0	909.3	626.2	377.5	237.1	176.1	160.0	143.9
102.5°	1225.8	1330.6	1335.2	1199.4	915.1	604.3	378.7	257.8	202.6	186.4	170.3
105°	1543.5	1528.5	1398.5	1159.1	852.9	574.4	384.4	282.0	227.9	211.8	195.7
107.5°	1636.7	1523.9	1330.6	1073.9	795.3	558.2	397.1	306.2	253.2	237.1	221.0
110°	1590.7	1443.4	1237.3	994.5	756.2	553.6	413.2	330.3	279.7	263.0	246.3

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1507.8	1347.8	1152.2	939.2	730.9	554.8	430.5	353.4	305.0	287.8	270.5
115°	1413.4	1262.7	1085.4	895.5	713.6	559.4	447.7	377.5	328.0	312.5	297.0
117.5°	1329.4	1189.0	1030.2	865.6	704.4	566.3	466.2	399.4	353.4	337.2	321.1
120°	1255.8	1133.7	991.0	842.5	696.4	573.2	484.6	422.4	377.5	361.4	345.3
122.5°	1201.7	1087.7	959.9	823.0	691.8	581.3	500.7	444.3	402.9	386.2	369.5
125°	1149.9	1048.6	930.0	804.6	686.0	589.3	518.0	466.2	424.7	408.6	392.5
127.5°	1106.1	1009.4	900.1	787.3	682.6	597.4	534.1	486.9	446.6	429.9	413.2
130°	1061.2	970.3	871.3	770.0	680.2	606.6	549.0	505.3	465.0	448.9	432.8
132.5°	1015.2	933.5	843.7	756.2	679.1	615.8	564.0	521.4	483.4	467.3	451.2
135°	970.3	894.3	818.4	743.6	677.9	622.7	576.7	536.4	499.5	483.4	467.3
137.5°	925.4	863.3	797.7	734.3	677.9	629.6	587.0	549.0	512.2	497.2	482.3
140°	886.3	833.3	778.1	726.3	676.8	634.2	595.1	559.4	524.9	509.9	494.9
142.5°	850.6	806.9	762.0	718.2	676.8	637.7	602.0	567.4	534.1	520.2	506.4
145°	820.7	785.0	747.0	711.3	674.5	640.0	607.7	575.5	544.4	531.8	519.1
147.5°	795.3	766.6	735.5	704.4	671.0	641.1	611.2	582.4	552.5	541.0	529.5
150°	772.3	748.2	722.8	695.2	667.6	640.0	613.5	587.0	560.5	550.2	539.8
152.5°	752.8	733.2	710.2	687.2	661.8	637.7	614.6	591.6	568.6	559.4	550.2
155°	734.3	717.1	698.7	676.8	654.9	635.4	615.8	596.2	576.7	568.0	559.4
157.5°	715.9	701.0	684.9	667.6	648.0	630.8	615.8	599.7	582.4	574.9	567.4
160°	697.5	684.9	672.2	657.2	641.1	627.3	615.8	602.0	588.2	581.8	575.5
162.5°	680.2	669.9	659.5	648.0	635.4	623.8	614.6	603.1	591.6	587.0	582.4
165°	663.0	654.9	646.9	637.7	627.3	619.2	612.3	604.3	593.9	590.4	587.0
167.5°	646.9	641.1	634.2	627.3	620.4	614.6	611.2	604.3	596.2	593.9	591.6
170°	633.1	628.5	625.0	619.2	614.6	611.2	608.9	603.1	597.4	595.6	593.9
172.5°	620.4	616.9	614.6	611.2	607.7	606.6	605.4	602.0	598.5	597.4	596.2
175°	610.0	608.9	607.7	604.3	603.1	602.0	603.1	600.8	598.5	598.0	597.4
177.5°	603.1	602.0	602.0	599.7	598.5	599.7	602.0	599.7	598.5	598.5	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1701.5	1701.5	1701.5	1701.5
2.5°	1670.1	1670.1	1689.7	1710.6
5°	1633.5	1642.6	1674.0	1702.8
7.5°	1598.2	1613.9	1653.1	1689.7
10°	1555.0	1575.9	1624.3	1667.5
12.5°	1513.2	1532.8	1589.0	1637.4
15°	1454.3	1479.2	1539.3	1599.5
17.5°	1395.5	1420.3	1493.5	1564.2
20°	1326.1	1358.8	1441.2	1535.4
22.5°	1262.1	1302.6	1394.1	1470.0
25°	1191.4	1254.2	1339.2	1437.3
27.5°	1128.7	1191.4	1277.8	1377.1
30°	1058.0	1122.1	1211.1	1302.6
32.5°	990.0	1048.9	1135.2	1247.7
35°	919.4	975.6	1059.3	1173.1
37.5°	855.3	910.3	1001.8	1106.4
40°	792.5	850.1	928.6	1033.2
42.5°	733.7	784.7	855.3	959.9
45°	680.1	716.7	782.1	880.2
47.5°	623.8	656.5	716.7	814.8
50°	571.5	599.0	651.3	742.8
52.5°	520.5	544.1	592.4	665.7
55°	474.7	497.0	532.3	604.2
57.5°	427.7	444.7	478.7	536.2
60°	381.9	397.6	425.0	472.1
62.5°	336.1	349.2	375.3	413.3
65°	295.6	306.0	325.6	358.3
67.5°	256.3	262.9	278.6	304.7
70°	218.4	223.6	236.7	257.6
72.5°	177.9	183.1	197.5	211.9
75°	143.9	145.2	155.6	167.4
77.5°	112.5	111.2	119.0	128.2
80°	77.2	81.1	87.6	91.5
82.5°	52.3	53.6	56.2	58.9
85°	28.8	30.1	30.1	34.0
87.5°	11.8	13.1	13.1	14.4
90°	11.5	9.2	4.6	1.2
92.5°	39.1	33.4	24.2	17.3
95°	66.8	56.4	44.9	40.3
97.5°	94.4	79.4	66.8	59.9
100°	120.9	102.4	92.1	88.6
102.5°	146.2	127.8	117.4	115.1
105°	170.3	153.1	145.0	140.4
107.5°	195.7	179.6	171.5	168.0
110°	222.1	207.2	200.3	195.7



TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	247.5	233.7	225.6	221.0
115°	273.9	260.1	253.2	247.5
117.5°	299.3	286.6	279.7	275.1
120°	322.3	311.9	305.0	300.4
122.5°	346.5	334.9	328.0	324.6
125°	369.5	355.7	348.8	345.3
127.5°	391.3	376.4	367.2	362.6
130°	409.8	393.6	382.1	377.5
132.5°	427.0	409.8	397.1	391.3
135°	440.8	423.6	409.8	405.2
137.5°	455.8	437.4	423.6	417.8
140°	469.6	451.2	437.4	432.8
142.5°	482.3	463.9	451.2	447.7
145°	496.1	478.8	467.3	462.7
147.5°	509.9	493.8	482.3	478.8
150°	522.6	507.6	498.4	494.9
152.5°	534.1	521.4	512.2	511.0
155°	546.7	534.1	527.2	526.0
157.5°	557.1	545.6	539.8	538.7
160°	566.3	557.1	552.5	551.3
162.5°	574.4	567.4	562.8	564.0
165°	581.3	574.4	572.1	573.2
167.5°	587.0	582.4	580.1	581.3
170°	591.6	588.2	587.0	589.3
172.5°	595.1	591.6	592.8	593.9
175°	597.4	595.1	596.2	597.4
177.5°	598.5	596.2	597.4	599.7
180°	598.5	598.5	598.5	598.5

TEST NUMBER: P998974

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.04	17.85	18.02	18.84	20.15	14.53	15.34	15.52	16.33	17.64
	3H	17.85	18.57	18.84	19.57	20.90	15.87	16.59	16.87	17.60	18.93
	4H	18.01	18.70	19.02	19.70	21.04	16.33	17.01	17.34	18.02	19.36
	6H	18.05	18.68	19.07	19.69	21.05	16.64	17.26	17.66	18.28	19.63
	8H	18.03	18.63	19.06	19.66	21.01	16.72	17.32	17.74	18.34	19.69
	12H	17.99	18.56	19.02	19.58	20.95	16.76	17.33	17.79	18.35	19.72
4H	2H	17.07	17.76	18.09	18.76	20.10	14.97	15.65	15.99	16.66	18.00
	3H	18.05	18.62	19.07	19.65	21.01	16.43	16.99	17.45	18.03	19.38
	4H	18.32	18.84	19.35	19.87	21.25	16.96	17.48	17.99	18.51	19.88
	6H	18.45	18.90	19.49	19.95	21.32	17.34	17.78	18.38	18.83	20.20
	8H	18.45	18.86	19.49	19.91	21.29	17.44	17.86	18.49	18.90	20.29
	12H	18.41	18.79	19.47	19.84	21.24	17.50	17.87	18.56	18.93	20.32
8H	4H	18.33	18.74	19.37	19.79	21.17	17.10	17.51	18.14	18.56	19.94
	6H	18.51	18.85	19.57	19.93	21.32	17.53	17.87	18.60	18.96	20.34
	8H	18.54	18.84	19.61	19.91	21.31	17.68	17.98	18.75	19.05	20.45
	12H	18.52	18.78	19.59	19.85	21.29	17.77	18.03	18.85	19.10	20.54
12H	4H	18.28	18.66	19.34	19.72	21.11	17.07	17.44	18.13	18.50	19.89
	6H	18.48	18.79	19.56	19.86	21.26	17.53	17.83	18.60	18.90	20.31
	8H	18.51	18.78	19.59	19.84	21.29	17.68	17.95	18.76	19.01	20.46