

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998979

Luminaire Tested: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998979
REPORT IS A COMBINATION OF REPORTS P984725 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7277.0 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998979

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P998979

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	89	86	82	79	72	69	67	59	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21528	21528	21528
5°	21563	20520	20374
10°	21386	19585	19195
15°	21074	18642	17956
20°	20651	17617	16783
25°	20229	16547	15611
30°	19697	15541	14381
35°	19197	14479	13172
40°	18579	13433	12031
45°	17963	12395	10911
50°	17292	11337	9750
55°	16587	10207	8649
60°	15794	8984	7505
65°	14924	7740	6302
70°	13819	6380	5090
75°	12290	4917	3930
80°	10443	3341	2529
85°	7571	1555	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17963 cd/sqm

TEST NUMBER: P998979

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	1.8
10°-20°	360.1	4.9
20°-30°	529.2	7.3
30°-40°	614.7	8.4
40°-50°	613.9	8.4
50°-60°	535.3	7.4
60°-70°	395.7	5.4
70°-80°	223.9	3.1
80°-90°	63.0	0.9
90°-100°	84.4	1.2
100°-110°	268.2	3.7
110°-120°	458.9	6.3
120°-130°	603.6	8.3
130°-140°	677.5	9.3
140°-150°	664.4	9.1
150°-160°	557.3	7.7
160°-170°	369.6	5.1
170°-180°	129.2	1.8
0°-30°	1017.4	14.0
0°-40°	1632.1	22.4
0°-60°	2781.3	38.2
0°-90°	3463.9	47.6
90°-120°	811.5	11.2
90°-150°	2757.0	37.9
90°-180°	3813.0	52.4
0°-180°	7277.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1360	1360	1360	1360	1360	
5°	1360	1355	1340	1351	1348	129
15°	1295	1287	1270	1275	1268	365
25°	1172	1161	1139	1142	1139	539
35°	1011	998	977	969	962	631
45°	822	813	794	779	774	635
55°	622	615	599	583	577	557
65°	420	412	399	387	380	415
75°	220	217	210	203	205	234
85°	54	52	51	47	46	60
90°	1	15	40	38	39	7
95°	60	71	74	74	71	67
105°	248	251	253	256	256	261
115°	460	467	465	464	460	455
125°	670	680	677	673	672	599
135°	867	879	882	880	877	670
145°	1052	1060	1067	1068	1064	657
155°	1203	1206	1210	1215	1212	554
165°	1309	1308	1308	1316	1310	369
175°	1362	1358	1356	1364	1357	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P998979

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1360.0	1360.0	1360.0	1360.0	1360.0
2.5°	1367.8	1361.3	1346.9	1360.0	1357.4
5°	1360.0	1354.7	1340.4	1350.8	1348.2
7.5°	1350.8	1343.0	1328.6	1339.1	1336.4
10°	1336.4	1327.3	1311.6	1322.1	1318.1
12.5°	1316.8	1309.0	1293.3	1299.8	1297.2
15°	1294.6	1286.7	1269.7	1275.0	1268.4
17.5°	1267.1	1259.3	1242.3	1248.8	1242.3
20°	1237.1	1229.2	1210.9	1214.8	1209.6
22.5°	1207.0	1195.2	1178.2	1178.2	1175.6
25°	1171.7	1161.2	1139.0	1141.6	1139.0
27.5°	1132.4	1123.3	1106.3	1102.4	1095.8
30°	1093.2	1082.8	1063.1	1059.2	1054.0
32.5°	1051.4	1043.5	1022.6	1014.8	1009.5
35°	1010.8	997.8	976.8	969.0	962.4
37.5°	965.1	953.3	932.4	923.2	916.7
40°	918.0	907.5	886.6	874.8	869.6
42.5°	872.2	861.8	840.8	827.8	819.9
45°	822.5	813.4	793.8	779.4	774.1
47.5°	774.1	765.0	744.1	729.7	721.8
50°	723.1	716.6	698.3	680.0	673.5
52.5°	673.5	664.3	647.3	632.9	623.8
55°	622.5	614.6	598.9	583.2	576.7
57.5°	571.5	564.9	547.9	532.2	527.0
60°	520.5	515.2	496.9	482.5	478.6
62.5°	470.8	461.6	448.5	435.5	430.2
65°	419.8	411.9	398.8	387.1	380.5
67.5°	367.5	360.9	349.1	340.0	334.8
70°	319.1	313.8	302.1	292.9	287.7
72.5°	269.4	264.1	257.6	248.5	244.5
75°	219.7	217.1	210.5	202.7	205.3
77.5°	175.2	170.0	167.4	163.5	159.5
80°	130.8	129.5	126.8	122.9	120.3
82.5°	88.9	88.9	87.6	82.4	82.4
85°	53.6	52.3	51.0	47.1	45.8
87.5°	23.5	20.9	18.3	14.4	13.1
90°	1.2	15.0	40.3	38.0	39.1
92.5°	25.3	34.5	35.7	36.8	36.8
95°	59.8	71.4	73.7	73.7	71.4
97.5°	100.1	110.5	115.1	115.1	115.1
100°	146.2	155.4	158.8	158.8	157.7
102.5°	194.5	201.4	206.0	207.2	206.0
105°	247.5	250.9	253.2	255.5	255.5
107.5°	300.4	305.0	305.0	306.2	300.4
110°	351.0	357.9	357.9	357.9	354.5

TEST NUMBER: P998979

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	406.3	413.2	412.0	408.6	406.3
115°	460.4	467.3	465.0	463.8	460.4
117.5°	514.5	523.7	517.9	514.5	511.0
120°	568.6	577.8	568.6	568.6	565.1
122.5°	618.1	629.6	623.8	620.4	618.1
125°	669.8	680.2	676.8	673.3	672.2
127.5°	720.5	733.2	728.5	723.9	720.5
130°	767.7	782.6	780.3	778.0	773.4
132.5°	820.6	832.1	833.3	827.5	824.1
135°	866.7	879.3	881.6	880.5	877.0
137.5°	917.3	927.7	930.0	928.8	924.2
140°	962.2	972.5	978.3	978.3	973.7
142.5°	1008.2	1018.6	1022.0	1023.2	1018.6
145°	1052.0	1060.0	1066.9	1068.1	1063.5
147.5°	1091.1	1101.5	1106.1	1108.4	1103.8
150°	1131.4	1138.3	1142.9	1146.3	1142.9
152.5°	1167.1	1174.0	1179.7	1184.3	1179.7
155°	1202.7	1206.2	1209.6	1215.4	1211.9
157.5°	1233.8	1236.1	1238.4	1246.5	1240.7
160°	1261.4	1263.7	1264.9	1271.8	1267.2
162.5°	1286.8	1286.8	1287.9	1296.0	1290.2
165°	1308.6	1307.5	1307.5	1315.5	1309.8
167.5°	1328.2	1324.7	1324.7	1332.8	1327.0
170°	1343.2	1339.7	1338.5	1346.6	1339.7
172.5°	1353.5	1350.1	1348.9	1357.0	1350.1
175°	1361.6	1358.1	1355.8	1363.9	1357.0
177.5°	1366.2	1362.7	1360.4	1367.3	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P998979

CATALOG NUMBER: SA2XXDIP-B865D1080UB27-4F0-XX-W2A-F1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.67	16.51	16.65	17.50	18.81	16.45	17.29	17.43	18.28	19.59
	3H	17.01	17.76	18.00	18.76	20.09	18.08	18.83	19.07	19.83	21.16
	4H	17.41	18.13	18.41	19.13	20.46	18.67	19.38	19.67	20.39	21.72
	6H	17.63	18.29	18.64	19.30	20.64	19.07	19.73	20.08	20.74	22.08
	8H	17.66	18.29	18.68	19.31	20.65	19.18	19.81	20.20	20.83	22.17
	12H	17.65	18.25	18.67	19.26	20.63	19.22	19.82	20.25	20.84	22.21
4H	2H	16.14	16.85	17.15	17.86	19.19	16.78	17.50	17.79	18.50	19.83
	3H	17.65	18.25	18.67	19.28	20.63	18.56	19.16	19.58	20.19	21.54
	4H	18.16	18.70	19.18	19.73	21.10	19.24	19.79	20.26	20.81	22.18
	6H	18.46	18.93	19.50	19.98	21.34	19.74	20.20	20.77	21.25	22.62
	8H	18.52	18.96	19.55	20.00	21.38	19.88	20.32	20.91	21.36	22.74
	12H	18.52	18.91	19.57	19.97	21.36	19.94	20.33	20.99	21.39	22.78
8H	4H	18.33	18.77	19.37	19.81	21.19	19.32	19.76	20.36	20.80	22.19
	6H	18.72	19.08	19.78	20.16	21.54	19.89	20.25	20.95	21.34	22.72
	8H	18.82	19.14	19.88	20.20	21.60	20.08	20.40	21.15	21.47	22.87
	12H	18.85	19.13	19.92	20.19	21.63	20.18	20.46	21.25	21.52	22.96
12H	4H	18.31	18.71	19.37	19.77	21.15	19.29	19.68	20.34	20.74	22.13
	6H	18.73	19.05	19.80	20.12	21.52	19.88	20.20	20.95	21.27	22.67
	8H	18.84	19.13	19.92	20.19	21.63	20.08	20.36	21.15	21.42	22.86

END OF REPORT