

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999985

Luminaire Tested: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999985
REPORT IS A COMBINATION OF REPORTS P988542 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4822.0 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999985

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999985

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	98	94	90	87	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	82	76	71	82	76	71	67	64	61	57	53	51	49	43	42	40
3	82	73	66	60	75	67	61	56	57	53	49	48	44	42	39	37	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	58	50	44	63	54	47	42	46	41	36	39	35	32	32	29	27
6	64	52	44	39	59	48	41	36	42	36	32	35	31	28	29	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	51	40	33	29	35	29	25	29	25	22	25	21	19
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	17
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17795	17795	17795
5°	17824	16930	16805
10°	17648	16056	15527
15°	17405	15027	14070
20°	17086	13854	12548
25°	16757	12653	11155
30°	16314	11481	9633
35°	15883	10299	8327
40°	15442	9141	6981
45°	14932	7943	5807
50°	14403	6788	4728
55°	13853	5634	3754
60°	13212	4507	2840
65°	12478	3435	2309
70°	11589	2492	1836
75°	10472	1901	1401
80°	8854	1286	942
85°	6173	588	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14932 cd/sqm

TEST NUMBER: P999985

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	2.2
10°-20°	289.2	6.0
20°-30°	406.1	8.4
30°-40°	442.6	9.2
40°-50°	406.8	8.4
50°-60°	319.5	6.6
60°-70°	208.0	4.3
70°-80°	107.1	2.2
80°-90°	29.9	0.6
90°-100°	55.5	1.2
100°-110°	176.4	3.7
110°-120°	301.8	6.3
120°-130°	396.9	8.2
130°-140°	445.5	9.2
140°-150°	436.9	9.1
150°-160°	366.5	7.6
160°-170°	243.1	5.0
170°-180°	84.9	1.8
0°-30°	800.7	16.6
0°-40°	1243.3	25.8
0°-60°	1969.7	40.8
0°-90°	2314.6	48.0
90°-120°	533.6	11.1
90°-150°	1813.0	37.6
90°-180°	2507.0	52.0
0°-180°	4822.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1124	1119	1106	1115	1112	107
15°	1069	1058	1024	1004	994	301
25°	971	938	871	829	814	446
35°	836	784	695	631	608	523
45°	684	616	509	436	412	528
55°	520	440	331	270	250	465
65°	351	269	177	142	139	348
75°	187	116	81	74	73	198
85°	44	22	19	19	19	50
90°	1	10	26	25	26	5
95°	39	47	48	48	47	44
105°	163	165	166	168	168	172
115°	303	307	306	305	303	300
125°	440	447	445	443	442	394
135°	570	578	580	579	577	440
145°	692	697	702	702	699	432
155°	791	793	795	799	797	364
165°	860	860	860	865	861	243
175°	895	893	892	897	892	85
180°	897	897	897	897	897	

TEST NUMBER: P999985

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1124.2	1124.2	1124.2	1124.2	1124.2
2.5°	1129.3	1124.2	1113.0	1123.2	1121.1
5°	1124.2	1119.1	1105.9	1115.0	1112.0
7.5°	1115.0	1108.9	1094.7	1098.7	1093.6
10°	1102.8	1095.7	1075.3	1072.3	1066.2
12.5°	1087.5	1078.4	1050.9	1044.8	1033.6
15°	1069.2	1058.0	1023.5	1004.1	993.9
17.5°	1047.9	1031.6	988.9	966.5	950.2
20°	1023.5	1003.1	952.2	926.8	904.4
22.5°	997.0	973.6	914.6	880.0	864.7
25°	970.6	938.0	870.9	829.1	813.9
27.5°	939.0	904.4	830.2	782.3	758.9
30°	905.4	866.8	785.4	733.5	706.0
32.5°	872.9	826.1	742.7	681.6	656.2
35°	836.3	784.4	694.8	630.8	608.4
37.5°	800.7	744.7	650.1	579.9	554.5
40°	763.0	702.0	603.3	531.1	504.6
42.5°	724.4	659.2	556.5	481.2	455.8
45°	683.7	615.5	508.7	436.4	412.0
47.5°	645.0	572.8	462.9	390.7	368.3
50°	602.3	530.0	418.1	347.9	326.6
52.5°	560.6	484.3	375.4	308.3	288.9
55°	519.9	440.5	330.6	269.6	250.3
57.5°	478.2	396.8	291.0	234.0	217.7
60°	435.4	354.0	249.3	197.4	181.1
62.5°	393.7	312.3	213.6	164.8	156.7
65°	351.0	268.6	177.0	142.4	139.4
67.5°	310.3	227.9	142.4	125.1	122.1
70°	267.6	188.2	118.0	107.8	103.8
72.5°	226.9	151.6	98.7	90.5	88.5
75°	187.2	116.0	81.4	74.3	73.2
77.5°	147.5	82.4	64.1	60.0	58.0
80°	110.9	59.0	48.8	44.8	44.8
82.5°	77.3	39.7	33.6	31.5	31.5
85°	43.7	22.4	19.3	19.3	19.3
87.5°	16.3	8.1	8.1	7.1	7.1
90°	0.8	9.8	26.5	25.0	25.7
92.5°	16.7	22.7	23.5	24.2	24.2
95°	39.4	46.9	48.4	48.4	46.9
97.5°	65.8	72.7	75.7	75.7	75.7
100°	96.1	102.2	104.4	104.4	103.7
102.5°	127.9	132.4	135.5	136.2	135.5
105°	162.7	165.0	166.5	168.0	168.0
107.5°	197.5	200.6	200.6	201.3	197.5
110°	230.8	235.4	235.4	235.4	233.1



TEST NUMBER: P999985

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.2	271.7	270.9	268.7	267.2
115°	302.7	307.3	305.8	305.0	302.7
117.5°	338.3	344.4	340.6	338.3	336.0
120°	373.9	379.9	373.9	373.9	371.6
122.5°	406.4	414.0	410.2	407.9	406.4
125°	440.5	447.3	445.0	442.8	442.0
127.5°	473.8	482.1	479.1	476.1	473.8
130°	504.8	514.7	513.1	511.6	508.6
132.5°	539.6	547.2	548.0	544.2	541.9
135°	569.9	578.2	579.7	579.0	576.7
137.5°	603.2	610.0	611.5	610.8	607.7
140°	632.7	639.5	643.3	643.3	640.3
142.5°	663.0	669.8	672.1	672.8	669.8
145°	691.8	697.1	701.6	702.4	699.3
147.5°	717.5	724.3	727.3	728.8	725.8
150°	744.0	748.5	751.5	753.8	751.5
152.5°	767.4	772.0	775.8	778.8	775.8
155°	790.9	793.2	795.4	799.2	797.0
157.5°	811.3	812.8	814.4	819.7	815.9
160°	829.5	831.0	831.8	836.3	833.3
162.5°	846.2	846.2	846.9	852.2	848.4
165°	860.5	859.8	859.8	865.1	861.3
167.5°	873.4	871.1	871.1	876.4	872.6
170°	883.2	881.0	880.2	885.5	881.0
172.5°	890.0	887.8	887.0	892.3	887.8
175°	895.3	893.1	891.6	896.9	892.3
177.5°	898.4	896.1	894.6	899.1	894.6
180°	896.9	896.9	896.9	896.9	896.9

(END OF REPORT)