

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999999

Luminaire Tested: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999999
REPORT IS A COMBINATION OF REPORTS P988556 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5319.0 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47
2	90	83	77	73	83	77	72	68	65	61	58	54	52	50	44	43	41
3	83	74	67	61	76	68	62	58	58	54	50	49	46	43	40	38	36
4	76	66	58	53	70	61	55	50	52	47	43	44	40	37	36	34	32
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28
6	65	53	46	40	60	50	43	38	43	38	34	36	32	29	30	28	25
7	60	49	41	36	55	45	39	34	39	34	30	33	29	26	28	25	23
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21
9	52	41	33	29	48	38	32	27	33	28	24	29	25	22	24	21	19
10	49	37	31	26	45	35	29	25	31	26	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23375	23375	23375	23375
5°	23431	24829	23511	19835
10°	23172	26244	23337	16379
15°	22670	26252	23054	12305
20°	22065	21700	22544	10152
25°	21332	13559	21793	8636
30°	20395	8682	20950	7435
35°	19256	6672	19880	6363
40°	17986	5609	18756	5566
45°	16631	4774	17326	4672
50°	15240	4056	15950	4041
55°	13699	3525	14437	3478
60°	12332	2688	12984	2655
65°	11052	2022	11710	2294
70°	9644	1615	10398	1870
75°	8151	1238	8900	1414
80°	6475	841	6962	927
85°	4492	435	4930	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21383 cd/sqm

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.1	2.6
10°-20°	391.0	7.4
20°-30°	503.2	9.5
30°-40°	477.4	9.0
40°-50°	409.1	7.7
50°-60°	311.6	5.9
60°-70°	196.5	3.7
70°-80°	98.0	1.8
80°-90°	27.8	0.5
90°-100°	154.7	2.9
100°-110°	545.0	10.2
110°-120°	572.3	10.8
120°-130°	470.9	8.9
130°-140°	378.3	7.1
140°-150°	285.7	5.4
150°-160°	200.9	3.8
160°-170°	118.2	2.2
170°-180°	38.5	0.7
0°-30°	1034.2	19.4
0°-40°	1511.6	28.4
0°-60°	2232.3	42.0
0°-90°	2554.5	48.0
90°-120°	1272.1	23.9
90°-150°	2406.9	45.3
90°-180°	2764.0	52.0
0°-180°	5319.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1477	1477	1477	1477	1477	
5°	1478	1643	1483	1312	1478	140
15°	1393	1854	1416	869	1393	392
25°	1236	989	1262	630	1236	567
35°	1014	488	1047	465	1014	634
45°	762	339	793	332	762	588
55°	514	235	542	232	514	463
65°	311	122	329	138	311	309
75°	146	65	159	74	146	158
85°	32	18	35	20	32	36
90°	1	25	1	25	1	4
95°	27	87	27	87	27	28
105°	93	860	93	860	93	99
115°	164	1132	164	1132	164	163
125°	229	918	229	918	229	204
135°	269	761	269	761	269	208
145°	307	608	307	608	307	193
155°	349	511	349	511	349	161
165°	380	448	380	448	380	107
175°	396	404	396	404	396	38
180°	397	397	397	397	397	

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1486.0	1492.1	1495.2	1499.3	1508.6	1514.7	1524.0	1526.0	1525.0	1529.1	1517.8
5°	1477.8	1491.1	1503.4	1513.7	1530.1	1540.4	1551.7	1565.0	1568.1	1583.5	1574.2
7.5°	1466.5	1486.0	1503.4	1524.0	1548.6	1561.9	1579.4	1599.9	1609.1	1627.6	1632.7
10°	1448.0	1475.7	1505.5	1527.0	1560.9	1584.5	1600.9	1633.8	1655.3	1683.0	1678.9
12.5°	1418.3	1454.2	1494.2	1530.1	1574.2	1589.6	1620.4	1654.3	1682.0	1707.6	1730.2
15°	1392.6	1433.6	1477.8	1521.9	1572.2	1600.9	1631.7	1675.8	1705.6	1750.7	1770.2
17.5°	1357.7	1410.0	1462.4	1511.6	1571.2	1604.0	1642.0	1685.1	1729.2	1772.3	1787.7
20°	1321.8	1378.2	1434.7	1501.4	1569.1	1600.9	1639.9	1693.3	1736.4	1770.2	1770.2
22.5°	1278.7	1347.4	1412.1	1475.7	1549.6	1595.8	1635.8	1698.4	1729.2	1736.4	1708.7
25°	1235.6	1304.3	1375.1	1454.2	1538.3	1579.4	1624.5	1683.0	1693.3	1664.5	1592.7
27.5°	1184.3	1261.2	1341.3	1426.5	1514.7	1566.0	1607.1	1646.1	1626.6	1549.6	1437.7
30°	1131.9	1215.1	1305.4	1386.4	1493.2	1540.4	1575.3	1586.6	1525.0	1399.8	1255.1
32.5°	1077.5	1158.6	1254.1	1351.5	1459.3	1504.5	1527.0	1497.3	1384.4	1226.3	1049.8
35°	1013.9	1105.3	1204.8	1306.4	1413.1	1447.0	1460.3	1387.5	1242.8	1038.5	863.1
37.5°	956.4	1047.8	1154.5	1258.2	1361.8	1380.3	1366.9	1253.0	1069.3	867.2	695.8
40°	888.7	986.2	1090.9	1206.8	1292.0	1297.2	1264.3	1116.5	888.7	698.9	593.2
42.5°	826.1	924.6	1029.3	1147.3	1212.0	1194.5	1150.4	956.4	742.0	602.4	517.2
45°	761.5	854.9	967.7	1072.4	1118.6	1077.5	1010.8	804.6	622.9	518.2	452.6
47.5°	698.9	786.1	898.0	998.5	1006.7	960.6	881.5	674.2	539.8	455.6	402.3
50°	637.3	724.5	829.2	912.3	904.1	840.5	751.2	586.0	469.0	402.3	358.2
52.5°	575.7	654.7	756.3	822.0	787.1	725.5	637.3	496.7	409.5	351.0	317.1
55°	514.1	588.0	675.3	729.6	674.2	603.4	540.8	425.9	355.1	307.9	282.2
57.5°	462.8	521.3	601.4	634.2	567.5	512.1	457.7	366.4	307.9	274.0	244.2
60°	406.4	459.8	525.4	544.9	476.2	431.0	384.8	309.9	263.7	234.0	214.5
62.5°	358.2	402.3	452.6	452.6	392.0	358.2	323.3	259.6	221.7	198.1	188.8
65°	310.9	342.8	378.7	374.6	323.3	293.5	265.8	214.5	185.7	169.3	160.1
67.5°	264.8	289.4	313.0	298.6	261.7	236.0	210.4	173.4	153.9	142.6	130.3
70°	222.7	242.2	254.5	241.2	204.2	182.7	164.2	139.6	124.2	109.8	102.6
72.5°	186.8	195.0	199.1	182.7	151.9	139.6	126.2	108.8	95.4	88.3	86.2
75°	145.7	152.9	149.8	137.5	111.9	102.6	92.4	80.0	77.0	72.9	70.8
77.5°	113.9	113.9	108.8	97.5	80.0	72.9	68.8	62.6	59.5	58.5	56.4
80°	81.1	80.0	77.0	64.7	54.4	50.3	50.3	46.2	45.2	43.1	43.1
82.5°	53.4	53.4	49.3	39.0	35.9	34.9	33.9	31.8	31.8	30.8	30.8
85°	31.8	29.8	24.6	21.6	20.5	20.5	19.5	18.5	19.5	18.5	18.5
87.5°	14.4	11.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	0.8	3.1	6.1	7.6	9.2	10.4	11.5	15.3	20.6	25.2	26.0
92.5°	11.5	16.0	22.1	26.0	32.1	36.3	40.5	61.1	90.1	116.0	117.6
95°	26.7	29.8	37.4	44.3	56.5	65.6	74.8	109.9	176.3	264.9	299.2
97.5°	39.7	44.3	52.7	62.6	76.3	86.6	97.0	142.0	234.4	377.1	487.8
100°	58.8	61.1	67.9	80.2	95.4	106.1	116.8	157.3	250.4	415.3	603.1
102.5°	76.3	77.9	84.7	97.0	113.0	123.7	134.4	171.0	251.2	400.8	606.9
105°	93.1	96.2	101.5	113.0	129.8	140.5	151.2	187.0	255.0	380.9	565.7
107.5°	111.5	113.7	119.1	129.8	146.6	157.2	167.9	203.1	263.4	370.2	527.5
110°	129.8	132.8	137.4	147.3	163.4	174.4	185.5	219.1	274.1	367.2	501.5

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	146.6	149.6	155.0	164.1	179.4	190.9	202.3	234.4	285.5	368.0	484.8
115°	164.1	167.9	172.5	181.7	197.0	207.3	217.6	250.4	297.0	371.0	473.3
117.5°	182.4	185.5	190.1	198.5	213.0	223.7	234.4	264.9	309.2	375.6	467.2
120°	199.2	202.3	206.9	213.7	229.0	239.7	250.4	280.2	321.4	380.2	461.8
122.5°	215.3	217.6	222.1	229.8	245.0	256.1	267.2	294.7	332.1	385.5	458.8
125°	229.0	231.3	235.9	245.0	260.3	271.0	281.7	309.2	343.5	390.9	455.0
127.5°	240.5	243.5	249.6	259.6	274.1	285.2	296.2	322.9	354.2	396.2	452.7
130°	250.4	253.4	261.1	271.8	287.0	297.7	308.4	335.1	364.1	402.3	451.2
132.5°	259.6	263.4	271.8	283.2	299.2	309.9	320.6	345.8	374.1	408.4	450.4
135°	268.7	271.8	280.9	292.4	309.9	320.6	331.3	355.7	382.5	413.0	449.6
137.5°	277.1	280.9	290.1	302.3	319.9	329.8	339.7	364.1	389.3	417.6	449.6
140°	287.0	290.1	299.2	311.5	328.3	338.2	348.1	371.0	394.7	420.6	448.9
142.5°	297.0	299.2	307.6	319.9	335.9	345.0	354.2	376.3	399.3	422.9	448.9
145°	306.9	309.9	317.6	329.0	344.3	352.7	361.1	381.7	403.1	424.4	447.3
147.5°	317.6	319.9	327.5	338.2	351.2	358.8	366.4	386.3	405.4	425.2	445.1
150°	328.3	330.5	336.7	346.6	358.0	364.9	371.8	389.3	406.9	424.4	442.8
152.5°	338.9	339.7	345.8	354.2	364.9	371.0	377.1	392.4	407.6	422.9	438.9
155°	348.9	349.6	354.2	362.6	371.0	376.8	382.5	395.4	408.4	421.4	434.4
157.5°	357.3	358.0	361.8	369.5	376.3	381.3	386.3	397.7	408.4	418.3	429.8
160°	365.7	366.4	369.5	375.6	381.7	385.9	390.1	399.3	408.4	416.0	425.2
162.5°	374.1	373.3	376.3	380.9	386.3	389.4	392.4	400.0	407.6	413.8	421.4
165°	380.2	379.4	380.9	385.5	389.3	391.6	393.9	400.8	406.1	410.7	416.0
167.5°	385.5	384.7	386.3	389.3	392.4	393.9	395.4	400.8	405.4	407.6	411.5
170°	390.9	389.3	390.1	392.4	393.9	395.0	396.2	400.0	403.8	405.4	407.6
172.5°	393.9	393.1	392.4	394.7	395.4	396.2	397.0	399.3	401.5	402.3	403.1
175°	396.2	395.4	394.7	396.2	396.2	396.6	397.0	398.5	400.0	399.3	400.0
177.5°	397.7	396.2	395.4	397.0	397.0	397.0	397.0	397.7	399.3	397.7	397.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1529.1	1531.1	1534.2	1548.6	1550.6	1554.7	1552.7	1552.7	1553.7	1551.7	1552.7
5°	1594.8	1597.8	1613.2	1630.7	1634.8	1630.7	1635.8	1643.0	1643.0	1643.0	1640.9
7.5°	1656.3	1667.6	1685.1	1710.7	1715.9	1721.0	1730.2	1724.1	1726.1	1735.4	1732.3
10°	1715.9	1732.3	1751.8	1773.3	1784.6	1791.8	1795.9	1805.1	1826.7	1802.1	1811.3
12.5°	1772.3	1795.9	1816.4	1840.0	1848.2	1857.5	1860.6	1868.8	1868.8	1867.7	1874.9
15°	1809.2	1830.8	1849.3	1864.7	1866.7	1864.7	1862.6	1863.6	1866.7	1854.4	1861.6
17.5°	1817.5	1819.5	1825.7	1819.5	1820.5	1799.0	1786.7	1783.6	1754.9	1755.9	1779.5
20°	1777.4	1742.5	1733.3	1699.4	1678.9	1623.5	1621.4	1606.1	1545.5	1564.0	1559.9
22.5°	1667.6	1608.1	1529.1	1490.1	1470.6	1412.1	1366.9	1335.1	1313.6	1292.0	1282.8
25°	1522.9	1426.5	1314.6	1237.6	1226.3	1172.0	1088.8	1049.8	1003.7	989.3	1013.9
27.5°	1336.2	1211.0	1084.7	966.7	945.2	895.9	853.8	826.1	772.8	769.7	771.7
30°	1082.7	956.4	850.7	773.8	720.4	697.8	670.1	649.6	628.1	636.3	638.3
32.5°	889.7	769.7	671.2	630.1	605.5	591.1	567.5	554.2	544.9	541.8	540.8
35°	707.1	627.0	582.9	542.9	528.5	518.2	500.8	494.6	486.4	487.5	487.5
37.5°	605.5	538.8	505.9	485.4	472.1	466.9	455.6	449.5	444.4	442.3	445.4
40°	522.4	476.2	455.6	437.2	425.9	423.8	417.7	410.5	404.3	405.4	408.4
42.5°	461.8	435.1	410.5	396.1	387.9	384.8	379.7	374.6	374.6	371.5	370.5
45°	413.6	392.0	371.5	358.2	353.0	348.9	342.8	341.7	337.6	338.7	339.7
47.5°	370.5	353.0	337.6	324.3	319.2	318.1	312.0	307.9	307.9	306.8	305.8
50°	331.5	314.0	300.7	293.5	286.3	284.3	283.2	282.2	280.2	280.2	281.2
52.5°	299.7	282.2	272.0	265.8	261.7	259.6	259.6	258.6	258.6	258.6	257.6
55°	264.8	250.4	242.2	240.1	238.1	237.1	236.0	234.0	233.0	235.0	233.0
57.5°	231.9	226.8	219.6	217.6	212.4	212.4	209.4	207.3	205.2	207.3	207.3
60°	206.3	199.1	195.0	188.8	184.7	180.6	175.5	174.5	172.4	171.4	170.4
62.5°	179.6	173.4	163.2	153.9	147.8	143.7	141.6	140.6	140.6	139.6	139.6
65°	149.8	135.5	130.3	127.3	126.2	125.2	123.1	122.1	123.1	122.1	123.1
67.5°	117.0	114.9	111.9	109.8	108.8	107.8	107.8	106.7	106.7	106.7	106.7
70°	101.6	96.5	95.4	93.4	93.4	92.4	92.4	92.4	92.4	91.3	93.4
72.5°	84.2	81.1	80.0	79.0	79.0	79.0	78.0	78.0	78.0	77.0	78.0
75°	68.8	67.7	65.7	65.7	64.7	65.7	64.7	64.7	63.6	64.7	64.7
77.5°	55.4	54.4	53.4	53.4	52.3	52.3	52.3	52.3	52.3	52.3	53.4
80°	42.1	41.0	40.0	41.0	40.0	41.0	40.0	40.0	41.0	40.0	40.0
82.5°	30.8	29.8	29.8	28.7	28.7	28.7	28.7	28.7	28.7	28.7	28.7
85°	18.5	17.4	17.4	18.5	17.4	18.5	17.4	17.4	17.4	18.5	18.5
87.5°	8.2	9.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.2
90°	25.2	24.4	22.9	24.4	24.8	25.2	25.2	25.2	25.2	25.2	25.2
92.5°	98.5	77.1	65.7	57.3	54.2	51.1	50.4	47.3	48.1	46.6	48.1
95°	261.8	200.0	153.4	121.4	113.0	104.6	94.7	88.6	86.3	87.0	86.3
97.5°	491.6	409.2	326.7	249.6	226.7	203.8	174.1	158.8	150.4	145.8	150.4
100°	713.0	697.0	602.3	497.7	451.6	405.4	342.0	309.2	287.0	273.3	287.0
102.5°	795.4	885.5	882.5	813.0	763.4	713.8	643.5	581.7	552.7	532.8	552.7
105°	768.7	927.5	1013.8	1023.7	1011.1	998.5	951.2	903.9	871.0	860.3	871.0
107.5°	712.2	882.5	1010.7	1085.5	1100.8	1116.1	1115.3	1108.4	1098.5	1081.0	1098.5
110°	659.6	820.6	957.3	1055.0	1086.3	1117.6	1150.4	1164.9	1171.8	1171.0	1171.8

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	622.9	764.2	893.9	1000.0	1037.0	1074.1	1122.9	1149.7	1164.2	1169.5	1164.2
115°	593.9	719.9	837.4	937.4	976.8	1016.1	1070.3	1105.4	1125.2	1132.1	1125.2
117.5°	574.1	683.2	788.6	881.7	919.1	956.5	1012.3	1049.7	1070.3	1075.6	1070.3
120°	558.8	657.3	751.9	832.9	867.6	902.3	955.8	991.6	1013.8	1021.4	1013.8
122.5°	545.8	636.7	721.4	797.0	827.5	858.0	904.6	939.7	958.8	964.9	958.8
125°	533.6	616.8	695.4	762.6	791.2	819.9	864.2	893.2	912.2	918.4	912.2
127.5°	522.2	597.0	669.5	733.6	760.4	787.1	826.0	853.5	870.3	874.8	870.3
130°	510.7	577.9	643.5	703.8	729.0	754.2	791.6	817.6	832.9	839.0	832.9
132.5°	501.5	559.6	619.1	673.3	696.6	719.9	756.5	782.5	796.2	801.6	796.2
135°	493.1	542.8	593.2	643.5	664.9	686.3	719.1	744.3	758.0	761.1	758.0
137.5°	487.0	529.0	572.5	613.8	632.8	651.9	683.2	705.4	717.6	722.2	717.6
140°	481.7	516.0	552.7	587.8	604.6	621.4	645.8	665.7	677.1	681.7	677.1
142.5°	476.4	505.4	535.1	564.1	577.5	590.9	613.8	631.3	641.2	641.2	641.2
145°	471.8	495.4	520.6	544.3	555.3	566.4	584.8	597.7	605.4	607.7	605.4
147.5°	467.2	487.8	508.4	527.5	535.9	544.3	560.3	571.0	576.4	577.9	576.4
150°	461.1	479.4	496.2	512.2	519.1	526.0	537.4	546.6	551.2	551.9	551.2
152.5°	455.7	471.0	486.3	499.3	505.0	510.7	519.1	526.7	529.8	529.8	529.8
155°	448.9	463.4	475.6	487.0	491.2	495.4	503.8	509.2	512.2	510.7	512.2
157.5°	442.8	454.2	464.9	474.8	478.2	481.7	487.8	492.4	493.9	493.9	493.9
160°	435.9	445.8	454.2	462.6	465.3	468.0	473.3	477.1	477.9	477.9	477.9
162.5°	429.8	437.4	444.3	451.2	453.1	455.0	460.3	462.6	463.4	462.6	463.4
165°	422.9	429.0	434.4	439.7	441.2	442.8	445.8	448.9	448.9	448.1	448.9
167.5°	416.0	420.6	425.2	429.0	430.6	432.1	433.6	435.1	435.1	434.4	435.1
170°	410.7	414.5	416.8	419.9	420.6	421.4	422.2	424.4	423.7	422.2	423.7
172.5°	405.4	407.6	409.2	411.5	411.8	412.2	413.0	413.8	413.0	412.2	413.0
175°	400.8	403.1	403.8	404.6	405.0	405.4	405.4	406.1	405.4	403.8	405.4
177.5°	397.7	399.3	399.3	400.0	400.0	400.0	400.0	400.0	399.3	397.7	399.3
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1556.8	1549.6	1547.6	1549.6	1547.6	1548.6	1541.4	1514.7	1521.9	1510.6	1516.8
5°	1645.0	1638.9	1625.5	1623.5	1621.4	1619.4	1609.1	1585.5	1576.3	1560.9	1559.9
7.5°	1729.2	1729.2	1718.9	1711.8	1702.5	1695.3	1682.0	1647.1	1632.7	1614.3	1604.0
10°	1812.3	1785.6	1796.9	1789.7	1767.2	1763.1	1738.4	1717.9	1690.2	1671.7	1655.3
12.5°	1871.8	1863.6	1853.4	1847.2	1841.1	1827.7	1811.3	1759.0	1744.6	1707.6	1689.2
15°	1869.8	1864.7	1867.7	1867.7	1865.7	1862.6	1849.3	1811.3	1786.7	1750.7	1718.9
17.5°	1769.2	1782.6	1795.9	1805.1	1825.7	1834.9	1847.2	1824.6	1809.2	1778.5	1744.6
20°	1593.7	1626.6	1665.6	1673.8	1692.3	1746.6	1771.3	1790.8	1796.9	1786.7	1759.0
22.5°	1349.5	1377.2	1471.6	1469.6	1496.2	1560.9	1632.7	1691.2	1737.4	1763.1	1752.8
25°	1057.0	1096.0	1146.3	1184.3	1271.5	1368.0	1457.2	1550.6	1630.7	1701.5	1718.9
27.5°	799.4	850.7	890.8	941.1	985.2	1099.1	1214.0	1359.8	1453.1	1587.6	1657.4
30°	646.5	670.1	710.2	733.8	755.3	842.5	972.9	1116.5	1280.7	1435.7	1555.8
32.5°	552.1	568.5	598.3	608.6	631.1	689.6	771.7	903.1	1072.4	1260.2	1418.3
35°	495.7	513.1	519.3	528.5	547.0	583.9	640.4	735.8	888.7	1072.4	1261.2
37.5°	447.4	456.7	474.1	480.3	486.4	514.1	552.1	618.8	720.4	871.3	1080.6
40°	413.6	418.7	427.9	433.1	437.2	456.7	490.5	535.7	610.6	725.5	918.5
42.5°	377.7	383.8	390.0	396.1	401.3	416.6	437.2	480.3	530.6	617.8	757.4
45°	342.8	346.9	354.0	358.2	365.3	377.7	396.1	425.9	471.0	526.5	639.3
47.5°	310.9	316.1	319.2	324.3	329.4	342.8	360.2	379.7	416.6	471.0	553.1
50°	282.2	288.4	292.5	293.5	297.6	309.9	324.3	345.8	369.4	411.5	483.4
52.5°	261.7	262.7	265.8	269.9	268.9	276.1	289.4	305.8	330.4	364.3	416.6
55°	238.1	241.2	243.2	244.2	244.2	250.4	257.6	273.0	292.5	320.2	364.3
57.5°	208.3	211.4	217.6	219.6	222.7	225.8	228.8	239.1	255.5	282.2	318.1
60°	177.5	179.6	185.7	189.9	191.9	200.1	204.2	212.4	221.7	241.2	275.0
62.5°	142.6	144.7	147.8	151.9	156.0	168.3	178.6	186.8	194.0	207.3	235.0
65°	124.2	125.2	127.3	128.3	129.3	134.4	143.7	155.0	168.3	178.6	195.0
67.5°	107.8	108.8	109.8	111.9	112.9	113.9	118.0	121.1	134.4	148.8	161.1
70°	92.4	94.4	95.4	95.4	96.5	98.5	100.6	104.7	108.8	116.0	131.4
72.5°	78.0	79.0	81.1	81.1	81.1	83.1	85.2	87.2	89.3	93.4	99.5
75°	64.7	66.7	66.7	66.7	67.7	67.7	69.8	71.8	73.9	77.0	79.0
77.5°	53.4	53.4	53.4	53.4	54.4	54.4	55.4	57.5	58.5	59.5	61.6
80°	40.0	41.0	41.0	41.0	42.1	42.1	42.1	44.1	45.2	45.2	47.2
82.5°	29.8	29.8	29.8	30.8	29.8	30.8	30.8	31.8	30.8	31.8	32.8
85°	18.5	18.5	18.5	19.5	19.5	19.5	19.5	19.5	19.5	19.5	20.5
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.3	9.2	9.2
90°	25.2	25.2	25.2	24.8	24.4	22.9	24.4	25.2	26.0	25.2	20.6
92.5°	47.3	50.4	51.1	54.2	57.3	65.7	77.1	98.5	117.6	116.0	90.1
95°	88.6	94.7	104.6	113.0	121.4	153.4	200.0	261.8	299.2	264.9	176.3
97.5°	158.8	174.1	203.8	226.7	249.6	326.7	409.2	491.6	487.8	377.1	234.4
100°	309.2	342.0	405.4	451.6	497.7	602.3	697.0	713.0	603.1	415.3	250.4
102.5°	581.7	643.5	713.8	763.4	813.0	882.5	885.5	795.4	606.9	400.8	251.2
105°	903.9	951.2	998.5	1011.1	1023.7	1013.8	927.5	768.7	565.7	380.9	255.0
107.5°	1108.4	1115.3	1116.1	1100.8	1085.5	1010.7	882.5	712.2	527.5	370.2	263.4
110°	1164.9	1150.4	1117.6	1086.3	1055.0	957.3	820.6	659.6	501.5	367.2	274.1

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1149.7	1122.9	1074.1	1037.0	1000.0	893.9	764.2	622.9	484.8	368.0	285.5
115°	1105.4	1070.3	1016.1	976.8	937.4	837.4	719.9	593.9	473.3	371.0	297.0
117.5°	1049.7	1012.3	956.5	919.1	881.7	788.6	683.2	574.1	467.2	375.6	309.2
120°	991.6	955.8	902.3	867.6	832.9	751.9	657.3	558.8	461.8	380.2	321.4
122.5°	939.7	904.6	858.0	827.5	797.0	721.4	636.7	545.8	458.8	385.5	332.1
125°	893.2	864.2	819.9	791.2	762.6	695.4	616.8	533.6	455.0	390.9	343.5
127.5°	853.5	826.0	787.1	760.4	733.6	669.5	597.0	522.2	452.7	396.2	354.2
130°	817.6	791.6	754.2	729.0	703.8	643.5	577.9	510.7	451.2	402.3	364.1
132.5°	782.5	756.5	719.9	696.6	673.3	619.1	559.6	501.5	450.4	408.4	374.1
135°	744.3	719.1	686.3	664.9	643.5	593.2	542.8	493.1	449.6	413.0	382.5
137.5°	705.4	683.2	651.9	632.8	613.8	572.5	529.0	487.0	449.6	417.6	389.3
140°	665.7	645.8	621.4	604.6	587.8	552.7	516.0	481.7	448.9	420.6	394.7
142.5°	631.3	613.8	590.9	577.5	564.1	535.1	505.4	476.4	448.9	422.9	399.3
145°	597.7	584.8	566.4	555.3	544.3	520.6	495.4	471.8	447.3	424.4	403.1
147.5°	571.0	560.3	544.3	535.9	527.5	508.4	487.8	467.2	445.1	425.2	405.4
150°	546.6	537.4	526.0	519.1	512.2	496.2	479.4	461.1	442.8	424.4	406.9
152.5°	526.7	519.1	510.7	505.0	499.3	486.3	471.0	455.7	438.9	422.9	407.6
155°	509.2	503.8	495.4	491.2	487.0	475.6	463.4	448.9	434.4	421.4	408.4
157.5°	492.4	487.8	481.7	478.2	474.8	464.9	454.2	442.8	429.8	418.3	408.4
160°	477.1	473.3	468.0	465.3	462.6	454.2	445.8	435.9	425.2	416.0	408.4
162.5°	462.6	460.3	455.0	453.1	451.2	444.3	437.4	429.8	421.4	413.8	407.6
165°	448.9	445.8	442.8	441.2	439.7	434.4	429.0	422.9	416.0	410.7	406.1
167.5°	435.1	433.6	432.1	430.6	429.0	425.2	420.6	416.0	411.5	407.6	405.4
170°	424.4	422.2	421.4	420.6	419.9	416.8	414.5	410.7	407.6	405.4	403.8
172.5°	413.8	413.0	412.2	411.8	411.5	409.2	407.6	405.4	403.1	402.3	401.5
175°	406.1	405.4	405.4	405.0	404.6	403.8	403.1	400.8	400.0	399.3	400.0
177.5°	400.0	400.0	400.0	400.0	400.0	399.3	399.3	397.7	397.0	397.7	399.3
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1507.5	1502.4	1502.4	1499.3	1499.3	1482.9	1482.9	1488.0	1481.9	1474.7	1464.4
5°	1546.5	1535.2	1532.2	1528.1	1514.7	1494.2	1486.0	1482.9	1470.6	1455.2	1437.7
7.5°	1583.5	1565.0	1555.8	1546.5	1529.1	1500.3	1483.9	1472.6	1454.2	1430.6	1408.0
10°	1619.4	1595.8	1572.2	1560.9	1536.3	1500.3	1476.7	1458.3	1431.6	1399.8	1368.0
12.5°	1652.2	1603.0	1598.9	1576.3	1540.4	1499.3	1463.4	1436.7	1402.9	1365.9	1329.0
15°	1681.0	1630.7	1606.1	1585.5	1538.3	1487.0	1449.0	1416.2	1371.0	1329.0	1283.8
17.5°	1695.3	1640.9	1624.5	1590.7	1542.4	1475.7	1424.4	1384.4	1335.1	1284.8	1233.5
20°	1709.7	1646.1	1619.4	1595.8	1530.1	1454.2	1396.7	1350.5	1296.1	1236.6	1180.2
22.5°	1716.9	1646.1	1614.3	1581.4	1517.8	1430.6	1362.8	1308.4	1244.8	1184.3	1116.5
25°	1704.6	1639.9	1601.9	1568.1	1496.2	1401.8	1323.8	1262.3	1194.5	1125.8	1057.0
27.5°	1673.8	1625.5	1581.4	1546.5	1466.5	1364.9	1282.8	1213.0	1143.2	1066.3	996.5
30°	1616.3	1594.8	1559.9	1520.9	1433.6	1332.0	1234.6	1162.7	1085.8	1008.8	935.9
32.5°	1527.0	1545.5	1522.9	1489.1	1394.6	1286.9	1183.2	1110.4	1026.2	943.1	876.4
35°	1418.3	1483.9	1471.6	1448.0	1353.6	1238.7	1135.0	1046.8	962.6	878.5	811.7
37.5°	1299.2	1398.8	1409.0	1394.6	1306.4	1189.4	1075.5	989.3	903.1	817.9	750.2
40°	1136.0	1288.9	1321.8	1327.9	1257.1	1129.9	1010.8	926.7	841.5	758.4	676.3
42.5°	986.2	1179.1	1220.2	1245.8	1194.5	1071.4	951.3	857.9	773.8	698.9	616.8
45°	845.6	1046.8	1113.5	1146.3	1123.7	1004.7	880.5	793.3	716.3	647.6	568.5
47.5°	700.9	903.1	996.5	1048.8	1048.8	936.9	812.8	726.6	652.7	594.2	524.4
50°	604.4	772.8	869.2	938.0	956.4	868.2	751.2	667.0	597.3	533.6	480.3
52.5°	515.2	666.0	746.1	817.9	871.3	794.3	682.4	606.5	537.7	478.2	436.1
55°	445.4	558.3	631.1	710.2	769.7	719.4	615.7	541.8	482.3	433.1	397.2
57.5°	378.7	477.2	536.7	606.5	670.1	632.2	549.0	485.4	433.1	390.0	358.2
60°	322.2	402.3	448.5	502.9	581.9	555.2	486.4	427.9	385.9	346.9	320.2
62.5°	274.0	337.6	376.6	415.6	487.5	475.1	421.8	376.6	340.7	307.9	285.3
65°	224.7	277.1	307.9	341.7	399.2	404.3	361.2	329.4	296.6	267.8	247.3
67.5°	181.6	222.7	250.4	279.1	325.3	339.7	309.9	283.2	255.5	231.9	213.5
70°	146.8	175.5	196.0	218.6	256.6	274.0	258.6	240.1	217.6	198.1	181.6
72.5°	116.0	134.4	146.8	164.2	195.0	212.4	211.4	195.0	178.6	165.2	151.9
75°	85.2	99.5	109.8	121.1	145.7	162.1	166.2	159.1	142.6	132.4	122.1
77.5°	64.7	72.9	78.0	86.2	103.6	118.0	124.2	122.1	110.8	102.6	95.4
80°	49.3	51.3	53.4	56.4	70.8	84.2	88.3	87.2	81.1	78.0	69.8
82.5°	34.9	35.9	36.9	38.0	43.1	54.4	58.5	60.5	55.4	52.3	45.2
85°	20.5	21.6	21.6	23.6	24.6	27.7	34.9	34.9	33.9	29.8	28.7
87.5°	10.3	10.3	9.2	9.2	10.3	11.3	13.3	15.4	13.3	12.3	11.3
90°	15.3	11.5	10.4	9.2	7.6	6.1	3.1	0.8	3.1	6.1	7.6
92.5°	61.1	40.5	36.3	32.1	26.0	22.1	16.0	11.5	16.0	22.1	26.0
95°	109.9	74.8	65.6	56.5	44.3	37.4	29.8	26.7	29.8	37.4	44.3
97.5°	142.0	97.0	86.6	76.3	62.6	52.7	44.3	39.7	44.3	52.7	62.6
100°	157.3	116.8	106.1	95.4	80.2	67.9	61.1	58.8	61.1	67.9	80.2
102.5°	171.0	134.4	123.7	113.0	97.0	84.7	77.9	76.3	77.9	84.7	97.0
105°	187.0	151.2	140.5	129.8	113.0	101.5	96.2	93.1	96.2	101.5	113.0
107.5°	203.1	167.9	157.2	146.6	129.8	119.1	113.7	111.5	113.7	119.1	129.8
110°	219.1	185.5	174.4	163.4	147.3	137.4	132.8	129.8	132.8	137.4	147.3

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	234.4	202.3	190.9	179.4	164.1	155.0	149.6	146.6	149.6	155.0	164.1
115°	250.4	217.6	207.3	197.0	181.7	172.5	167.9	164.1	167.9	172.5	181.7
117.5°	264.9	234.4	223.7	213.0	198.5	190.1	185.5	182.4	185.5	190.1	198.5
120°	280.2	250.4	239.7	229.0	213.7	206.9	202.3	199.2	202.3	206.9	213.7
122.5°	294.7	267.2	256.1	245.0	229.8	222.1	217.6	215.3	217.6	222.1	229.8
125°	309.2	281.7	271.0	260.3	245.0	235.9	231.3	229.0	231.3	235.9	245.0
127.5°	322.9	296.2	285.2	274.1	259.6	249.6	243.5	240.5	243.5	249.6	259.6
130°	335.1	308.4	297.7	287.0	271.8	261.1	253.4	250.4	253.4	261.1	271.8
132.5°	345.8	320.6	309.9	299.2	283.2	271.8	263.4	259.6	263.4	271.8	283.2
135°	355.7	331.3	320.6	309.9	292.4	280.9	271.8	268.7	271.8	280.9	292.4
137.5°	364.1	339.7	329.8	319.9	302.3	290.1	280.9	277.1	280.9	290.1	302.3
140°	371.0	348.1	338.2	328.3	311.5	299.2	290.1	287.0	290.1	299.2	311.5
142.5°	376.3	354.2	345.0	335.9	319.9	307.6	299.2	297.0	299.2	307.6	319.9
145°	381.7	361.1	352.7	344.3	329.0	317.6	309.9	306.9	309.9	317.6	329.0
147.5°	386.3	366.4	358.8	351.2	338.2	327.5	319.9	317.6	319.9	327.5	338.2
150°	389.3	371.8	364.9	358.0	346.6	336.7	330.5	328.3	330.5	336.7	346.6
152.5°	392.4	377.1	371.0	364.9	354.2	345.8	339.7	338.9	339.7	345.8	354.2
155°	395.4	382.5	376.8	371.0	362.6	354.2	349.6	348.9	349.6	354.2	362.6
157.5°	397.7	386.3	381.3	376.3	369.5	361.8	358.0	357.3	358.0	361.8	369.5
160°	399.3	390.1	385.9	381.7	375.6	369.5	366.4	365.7	366.4	369.5	375.6
162.5°	400.0	392.4	389.4	386.3	380.9	376.3	373.3	374.1	373.3	376.3	380.9
165°	400.8	393.9	391.6	389.3	385.5	380.9	379.4	380.2	379.4	380.9	385.5
167.5°	400.8	395.4	393.9	392.4	389.3	386.3	384.7	385.5	384.7	386.3	389.3
170°	400.0	396.2	395.0	393.9	392.4	390.1	389.3	390.9	389.3	390.1	392.4
172.5°	399.3	397.0	396.2	395.4	394.7	392.4	393.1	393.9	393.1	392.4	394.7
175°	398.5	397.0	396.6	396.2	396.2	394.7	395.4	396.2	395.4	394.7	396.2
177.5°	397.7	397.0	397.0	397.0	397.0	395.4	396.2	397.7	396.2	395.4	397.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1460.3	1461.4	1464.4	1455.2	1440.8	1434.7	1416.2	1413.1	1410.0	1410.0	1413.1
5°	1427.5	1423.4	1424.4	1407.0	1386.4	1374.1	1348.5	1352.6	1339.2	1331.0	1333.1
7.5°	1391.6	1380.3	1379.3	1356.7	1331.0	1308.4	1281.8	1275.6	1263.3	1248.9	1242.8
10°	1346.4	1338.2	1322.8	1297.2	1264.3	1245.8	1209.9	1188.4	1185.3	1163.7	1155.5
12.5°	1300.2	1285.9	1270.5	1234.6	1197.6	1167.9	1141.2	1117.6	1101.1	1082.7	1070.4
15°	1246.9	1229.4	1212.0	1174.0	1130.9	1101.1	1061.1	1026.2	978.0	940.0	918.5
17.5°	1188.4	1168.9	1145.3	1103.2	1061.1	1020.1	946.2	905.1	871.3	848.7	835.4
20°	1127.8	1106.3	1082.7	1040.6	967.7	895.9	854.9	823.0	802.5	779.9	763.5
22.5°	1064.2	1041.6	1016.0	950.3	873.3	823.0	791.2	761.5	731.7	719.4	711.2
25°	1004.7	984.2	951.3	862.0	801.5	755.3	719.4	699.9	684.5	668.1	652.7
27.5°	943.1	905.1	859.0	784.0	746.1	698.9	673.2	658.8	632.2	620.9	613.7
30°	869.2	827.1	783.0	729.6	685.5	652.7	629.1	605.5	590.1	578.8	566.5
32.5°	794.3	754.3	726.6	671.2	638.3	604.4	581.9	567.5	544.9	537.7	532.6
35°	729.6	695.8	671.2	626.0	595.2	564.4	548.0	526.5	512.1	498.7	490.5
37.5°	666.0	647.6	621.9	583.9	551.1	526.5	503.9	496.7	477.2	470.0	461.8
40°	621.9	594.2	572.6	539.8	512.1	485.4	471.0	454.6	441.3	430.0	426.9
42.5°	568.5	548.0	535.7	499.8	471.0	455.6	438.2	419.7	409.5	400.2	388.9
45°	528.5	510.0	492.6	463.9	438.2	418.7	403.3	391.0	373.5	369.4	352.0
47.5°	486.4	468.0	454.6	425.9	402.3	383.8	372.5	356.1	341.7	332.5	324.3
50°	444.4	429.0	416.6	392.0	371.5	352.0	336.6	320.2	314.0	298.6	293.5
52.5°	404.3	394.1	380.7	357.1	336.6	320.2	303.8	290.4	281.2	273.0	266.8
55°	370.5	354.0	347.9	322.2	304.8	287.3	273.0	264.8	253.5	248.3	243.2
57.5°	332.5	323.3	313.0	293.5	274.0	257.6	247.3	235.0	228.8	222.7	218.6
60°	299.7	286.3	278.1	261.7	244.2	228.8	219.6	210.4	202.2	197.0	188.8
62.5°	261.7	251.4	246.3	228.8	214.5	200.1	191.9	182.7	176.5	167.3	157.0
65°	228.8	220.6	214.5	200.1	186.8	173.4	165.2	153.9	145.7	140.6	139.6
67.5°	200.1	194.0	184.7	171.4	158.0	147.8	138.5	129.3	128.3	126.2	126.2
70°	168.3	162.1	157.0	142.6	131.4	120.1	118.0	114.9	111.9	110.8	108.8
72.5°	140.6	135.5	129.3	117.0	105.7	102.6	100.6	98.5	95.4	94.4	93.4
75°	113.9	106.7	102.6	91.3	88.3	86.2	84.2	81.1	79.0	78.0	75.9
77.5°	87.2	80.0	80.0	73.9	71.8	68.8	66.7	64.7	63.6	61.6	61.6
80°	61.6	61.6	59.5	56.4	53.4	52.3	49.3	48.2	47.2	48.2	46.2
82.5°	45.2	41.0	41.0	39.0	36.9	35.9	33.9	33.9	32.8	32.8	32.8
85°	25.7	25.7	24.6	22.6	21.6	21.6	20.5	20.5	19.5	19.5	18.5
87.5°	10.3	9.2	10.3	9.2	9.2	8.2	8.2	8.2	7.2	8.2	7.2
90°	9.2	10.4	11.5	15.3	20.6	25.2	26.0	25.2	24.4	22.9	24.4
92.5°	32.1	36.3	40.5	61.1	90.1	116.0	117.6	98.5	77.1	65.7	57.3
95°	56.5	65.6	74.8	109.9	176.3	264.9	299.2	261.8	200.0	153.4	121.4
97.5°	76.3	86.6	97.0	142.0	234.4	377.1	487.8	491.6	409.2	326.7	249.6
100°	95.4	106.1	116.8	157.3	250.4	415.3	603.1	713.0	697.0	602.3	497.7
102.5°	113.0	123.7	134.4	171.0	251.2	400.8	606.9	795.4	885.5	882.5	813.0
105°	129.8	140.5	151.2	187.0	255.0	380.9	565.7	768.7	927.5	1013.8	1023.7
107.5°	146.6	157.2	167.9	203.1	263.4	370.2	527.5	712.2	882.5	1010.7	1085.5
110°	163.4	174.4	185.5	219.1	274.1	367.2	501.5	659.6	820.6	957.3	1055.0

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	179.4	190.9	202.3	234.4	285.5	368.0	484.8	622.9	764.2	893.9	1000.0
115°	197.0	207.3	217.6	250.4	297.0	371.0	473.3	593.9	719.9	837.4	937.4
117.5°	213.0	223.7	234.4	264.9	309.2	375.6	467.2	574.1	683.2	788.6	881.7
120°	229.0	239.7	250.4	280.2	321.4	380.2	461.8	558.8	657.3	751.9	832.9
122.5°	245.0	256.1	267.2	294.7	332.1	385.5	458.8	545.8	636.7	721.4	797.0
125°	260.3	271.0	281.7	309.2	343.5	390.9	455.0	533.6	616.8	695.4	762.6
127.5°	274.1	285.2	296.2	322.9	354.2	396.2	452.7	522.2	597.0	669.5	733.6
130°	287.0	297.7	308.4	335.1	364.1	402.3	451.2	510.7	577.9	643.5	703.8
132.5°	299.2	309.9	320.6	345.8	374.1	408.4	450.4	501.5	559.6	619.1	673.3
135°	309.9	320.6	331.3	355.7	382.5	413.0	449.6	493.1	542.8	593.2	643.5
137.5°	319.9	329.8	339.7	364.1	389.3	417.6	449.6	487.0	529.0	572.5	613.8
140°	328.3	338.2	348.1	371.0	394.7	420.6	448.9	481.7	516.0	552.7	587.8
142.5°	335.9	345.0	354.2	376.3	399.3	422.9	448.9	476.4	505.4	535.1	564.1
145°	344.3	352.7	361.1	381.7	403.1	424.4	447.3	471.8	495.4	520.6	544.3
147.5°	351.2	358.8	366.4	386.3	405.4	425.2	445.1	467.2	487.8	508.4	527.5
150°	358.0	364.9	371.8	389.3	406.9	424.4	442.8	461.1	479.4	496.2	512.2
152.5°	364.9	371.0	377.1	392.4	407.6	422.9	438.9	455.7	471.0	486.3	499.3
155°	371.0	376.8	382.5	395.4	408.4	421.4	434.4	448.9	463.4	475.6	487.0
157.5°	376.3	381.3	386.3	397.7	408.4	418.3	429.8	442.8	454.2	464.9	474.8
160°	381.7	385.9	390.1	399.3	408.4	416.0	425.2	435.9	445.8	454.2	462.6
162.5°	386.3	389.4	392.4	400.0	407.6	413.8	421.4	429.8	437.4	444.3	451.2
165°	389.3	391.6	393.9	400.8	406.1	410.7	416.0	422.9	429.0	434.4	439.7
167.5°	392.4	393.9	395.4	400.8	405.4	407.6	411.5	416.0	420.6	425.2	429.0
170°	393.9	395.0	396.2	400.0	403.8	405.4	407.6	410.7	414.5	416.8	419.9
172.5°	395.4	396.2	397.0	399.3	401.5	402.3	403.1	405.4	407.6	409.2	411.5
175°	396.2	396.6	397.0	398.5	400.0	399.3	400.0	400.8	403.1	403.8	404.6
177.5°	397.0	397.0	397.0	397.7	399.3	397.7	397.0	397.7	399.3	399.3	400.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1413.1	1411.1	1404.9	1407.0	1403.9	1403.9	1401.8	1401.8	1401.8	1407.0	1403.9
5°	1336.2	1329.0	1321.8	1318.7	1315.6	1312.5	1312.5	1311.5	1320.8	1318.7	1326.9
7.5°	1240.7	1238.7	1224.3	1224.3	1219.2	1217.1	1222.2	1223.3	1224.3	1226.3	1231.5
10°	1155.5	1150.4	1129.9	1131.9	1128.9	1124.7	1127.8	1125.8	1133.0	1135.0	1133.0
12.5°	1055.0	1045.7	1023.2	1011.9	999.5	990.3	1001.6	993.4	1022.1	1030.3	1052.9
15°	921.6	904.1	888.7	888.7	877.4	869.2	874.3	883.6	889.7	899.0	903.1
17.5°	832.3	825.1	812.8	805.6	802.5	799.4	799.4	803.5	816.9	815.9	824.1
20°	756.3	752.2	746.1	736.8	733.8	731.7	731.7	731.7	740.9	749.1	754.3
22.5°	704.0	700.9	696.8	684.5	678.3	676.3	681.4	684.5	691.7	697.8	703.0
25°	651.7	644.5	637.3	633.2	630.1	630.1	632.2	633.2	636.3	639.3	645.5
27.5°	608.6	603.4	593.2	581.9	581.9	578.8	580.8	582.9	590.1	600.3	605.5
30°	560.3	559.3	555.2	551.1	547.0	544.9	549.0	552.1	553.1	558.3	558.3
32.5°	525.4	518.2	511.1	507.0	504.9	503.9	504.9	509.0	509.0	515.2	522.4
35°	490.5	486.4	479.2	472.1	470.0	464.9	469.0	473.1	480.3	483.4	486.4
37.5°	452.6	447.4	444.4	442.3	438.2	439.2	436.1	442.3	448.5	447.4	449.5
40°	423.8	414.6	405.4	404.3	403.3	402.3	402.3	403.3	407.4	411.5	417.7
42.5°	386.9	383.8	375.6	367.4	365.3	363.3	361.2	365.3	373.5	380.7	383.8
45°	348.9	344.8	342.8	336.6	332.5	331.5	329.4	334.6	341.7	344.8	346.9
47.5°	314.0	313.0	306.8	307.9	304.8	305.8	304.8	307.9	307.9	310.9	313.0
50°	290.4	287.3	284.3	282.2	279.1	279.1	278.1	279.1	283.2	287.3	286.3
52.5°	266.8	261.7	260.7	259.6	257.6	259.6	256.6	257.6	261.7	263.7	262.7
55°	239.1	238.1	236.0	234.0	233.0	231.9	231.9	231.9	236.0	239.1	240.1
57.5°	217.6	212.4	208.3	208.3	204.2	203.2	205.2	206.3	209.4	211.4	213.5
60°	187.8	185.7	179.6	176.5	170.4	169.3	169.3	173.4	178.6	185.7	187.8
62.5°	156.0	152.9	151.9	151.9	151.9	151.9	151.9	151.9	151.9	152.9	152.9
65°	138.5	139.6	138.5	137.5	138.5	138.5	137.5	137.5	137.5	138.5	139.6
67.5°	124.2	123.1	124.2	123.1	122.1	122.1	121.1	122.1	123.1	124.2	124.2
70°	107.8	107.8	106.7	107.8	106.7	105.7	104.7	104.7	106.7	107.8	107.8
72.5°	92.4	92.4	91.3	91.3	89.3	89.3	90.3	89.3	89.3	92.4	92.4
75°	77.0	75.9	74.9	74.9	73.9	73.9	73.9	72.9	74.9	74.9	75.9
77.5°	60.5	60.5	60.5	59.5	59.5	58.5	58.5	59.5	59.5	59.5	60.5
80°	46.2	46.2	46.2	45.2	44.1	44.1	44.1	44.1	44.1	45.2	44.1
82.5°	31.8	31.8	31.8	31.8	31.8	30.8	30.8	30.8	31.8	31.8	30.8
85°	19.5	18.5	19.5	19.5	18.5	19.5	18.5	18.5	17.4	17.4	18.5
87.5°	8.2	7.2	6.2	6.2	7.2	6.2	6.2	6.2	7.2	6.2	6.2
90°	24.8	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2	24.8
92.5°	54.2	51.1	50.4	47.3	48.1	46.6	48.1	47.3	50.4	51.1	54.2
95°	113.0	104.6	94.7	88.6	86.3	87.0	86.3	88.6	94.7	104.6	113.0
97.5°	226.7	203.8	174.1	158.8	150.4	145.8	150.4	158.8	174.1	203.8	226.7
100°	451.6	405.4	342.0	309.2	287.0	273.3	287.0	309.2	342.0	405.4	451.6
102.5°	763.4	713.8	643.5	581.7	552.7	532.8	552.7	581.7	643.5	713.8	763.4
105°	1011.1	998.5	951.2	903.9	871.0	860.3	871.0	903.9	951.2	998.5	1011.1
107.5°	1100.8	1116.1	1115.3	1108.4	1098.5	1081.0	1098.5	1108.4	1115.3	1116.1	1100.8
110°	1086.3	1117.6	1150.4	1164.9	1171.8	1171.0	1171.8	1164.9	1150.4	1117.6	1086.3

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1037.0	1074.1	1122.9	1149.7	1164.2	1169.5	1164.2	1149.7	1122.9	1074.1	1037.0
115°	976.8	1016.1	1070.3	1105.4	1125.2	1132.1	1125.2	1105.4	1070.3	1016.1	976.8
117.5°	919.1	956.5	1012.3	1049.7	1070.3	1075.6	1070.3	1049.7	1012.3	956.5	919.1
120°	867.6	902.3	955.8	991.6	1013.8	1021.4	1013.8	991.6	955.8	902.3	867.6
122.5°	827.5	858.0	904.6	939.7	958.8	964.9	958.8	939.7	904.6	858.0	827.5
125°	791.2	819.9	864.2	893.2	912.2	918.4	912.2	893.2	864.2	819.9	791.2
127.5°	760.4	787.1	826.0	853.5	870.3	874.8	870.3	853.5	826.0	787.1	760.4
130°	729.0	754.2	791.6	817.6	832.9	839.0	832.9	817.6	791.6	754.2	729.0
132.5°	696.6	719.9	756.5	782.5	796.2	801.6	796.2	782.5	756.5	719.9	696.6
135°	664.9	686.3	719.1	744.3	758.0	761.1	758.0	744.3	719.1	686.3	664.9
137.5°	632.8	651.9	683.2	705.4	717.6	722.2	717.6	705.4	683.2	651.9	632.8
140°	604.6	621.4	645.8	665.7	677.1	681.7	677.1	665.7	645.8	621.4	604.6
142.5°	577.5	590.9	613.8	631.3	641.2	641.2	641.2	631.3	613.8	590.9	577.5
145°	555.3	566.4	584.8	597.7	605.4	607.7	605.4	597.7	584.8	566.4	555.3
147.5°	535.9	544.3	560.3	571.0	576.4	577.9	576.4	571.0	560.3	544.3	535.9
150°	519.1	526.0	537.4	546.6	551.2	551.9	551.2	546.6	537.4	526.0	519.1
152.5°	505.0	510.7	519.1	526.7	529.8	529.8	529.8	526.7	519.1	510.7	505.0
155°	491.2	495.4	503.8	509.2	512.2	510.7	512.2	509.2	503.8	495.4	491.2
157.5°	478.2	481.7	487.8	492.4	493.9	493.9	493.9	492.4	487.8	481.7	478.2
160°	465.3	468.0	473.3	477.1	477.9	477.9	477.9	477.1	473.3	468.0	465.3
162.5°	453.1	455.0	460.3	462.6	463.4	462.6	463.4	462.6	460.3	455.0	453.1
165°	441.2	442.8	445.8	448.9	448.9	448.1	448.9	448.9	445.8	442.8	441.2
167.5°	430.6	432.1	433.6	435.1	435.1	434.4	435.1	435.1	433.6	432.1	430.6
170°	420.6	421.4	422.2	424.4	423.7	422.2	423.7	424.4	422.2	421.4	420.6
172.5°	411.8	412.2	413.0	413.8	413.0	412.2	413.0	413.8	413.0	412.2	411.8
175°	405.0	405.4	405.4	406.1	405.4	403.8	405.4	406.1	405.4	405.4	405.0
177.5°	400.0	400.0	400.0	400.0	399.3	397.7	399.3	400.0	400.0	400.0	400.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1407.0	1412.1	1410.0	1398.8	1410.0	1413.1	1419.3	1425.4	1429.5	1435.7	1440.8
5°	1318.7	1329.0	1335.1	1329.0	1349.5	1352.6	1366.9	1375.1	1387.5	1397.7	1405.9
7.5°	1235.6	1243.8	1256.1	1258.2	1270.5	1284.8	1305.4	1325.9	1345.4	1355.7	1364.9
10°	1146.3	1160.7	1179.1	1175.0	1193.5	1216.1	1237.6	1270.5	1286.9	1305.4	1321.8
12.5°	1057.0	1066.3	1090.9	1099.1	1125.8	1143.2	1173.0	1193.5	1234.6	1256.1	1270.5
15°	901.0	939.0	969.8	1006.7	1041.6	1074.5	1101.1	1138.1	1174.0	1190.4	1214.0
17.5°	830.2	847.7	866.1	884.6	929.8	988.3	1035.5	1075.5	1106.3	1127.8	1155.5
20°	756.3	773.8	794.3	811.7	839.5	881.5	940.0	1008.8	1045.7	1068.3	1095.0
22.5°	704.0	720.4	733.8	749.1	770.7	801.5	845.6	930.8	980.1	1007.8	1031.4
25°	647.6	668.1	682.4	693.7	711.2	745.0	781.0	829.2	917.5	939.0	971.8
27.5°	608.6	614.7	631.1	648.6	666.0	684.5	721.4	762.5	822.0	869.2	909.2
30°	562.4	577.8	593.2	600.3	615.7	642.4	665.0	709.1	755.3	792.3	840.5
32.5°	527.5	536.7	547.0	564.4	578.8	597.3	619.8	656.8	695.8	719.4	756.3
35°	488.5	494.6	516.2	523.4	537.7	556.2	578.8	607.5	649.6	668.1	694.8
37.5°	451.5	465.9	472.1	488.5	501.8	520.3	536.7	569.6	597.3	618.8	643.4
40°	422.8	429.0	440.3	454.6	465.9	480.3	500.8	524.4	554.2	571.6	593.2
42.5°	387.9	393.0	407.4	415.6	434.1	447.4	459.8	488.5	515.2	528.5	550.1
45°	349.9	362.3	371.5	387.9	398.2	414.6	430.0	450.5	475.1	490.5	502.9
47.5°	317.1	329.4	338.7	354.0	370.5	377.7	394.1	415.6	438.2	450.5	468.0
50°	290.4	294.5	312.0	319.2	336.6	351.0	362.3	380.7	405.4	412.5	426.9
52.5°	264.8	267.8	279.1	288.4	303.8	316.1	330.4	347.9	368.4	379.7	391.0
55°	242.2	244.2	249.4	259.6	269.9	285.3	298.6	315.1	332.5	344.8	355.1
57.5°	216.5	220.6	224.7	230.9	241.2	255.5	269.9	285.3	299.7	307.9	321.2
60°	186.8	192.9	200.1	207.3	214.5	224.7	241.2	255.5	268.9	276.1	286.3
62.5°	155.0	167.3	173.4	181.6	187.8	197.0	209.4	225.8	235.0	244.2	252.5
65°	139.6	140.6	141.6	149.8	161.1	170.4	181.6	194.0	208.3	214.5	220.6
67.5°	124.2	125.2	127.3	128.3	132.4	142.6	155.0	168.3	179.6	183.7	189.9
70°	108.8	108.8	112.9	113.9	114.9	116.0	126.2	139.6	149.8	155.0	162.1
72.5°	92.4	93.4	95.4	96.5	98.5	100.6	103.6	110.8	123.1	128.3	136.5
75°	75.9	77.0	78.0	79.0	82.1	83.1	86.2	90.3	95.4	101.6	106.7
77.5°	60.5	60.5	61.6	63.6	65.7	66.7	69.8	71.8	73.9	77.0	81.1
80°	45.2	46.2	46.2	48.2	48.2	49.3	50.3	53.4	55.4	57.5	59.5
82.5°	30.8	32.8	32.8	32.8	33.9	34.9	35.9	35.9	38.0	39.0	42.1
85°	18.5	19.5	19.5	19.5	18.5	20.5	20.5	21.6	21.6	21.6	22.6
87.5°	7.2	6.2	7.2	7.2	7.2	8.2	7.2	7.2	8.2	9.2	9.2
90°	24.4	22.9	24.4	25.2	26.0	25.2	20.6	15.3	11.5	10.4	9.2
92.5°	57.3	65.7	77.1	98.5	117.6	116.0	90.1	61.1	40.5	36.3	32.1
95°	121.4	153.4	200.0	261.8	299.2	264.9	176.3	109.9	74.8	65.6	56.5
97.5°	249.6	326.7	409.2	491.6	487.8	377.1	234.4	142.0	97.0	86.6	76.3
100°	497.7	602.3	697.0	713.0	603.1	415.3	250.4	157.3	116.8	106.1	95.4
102.5°	813.0	882.5	885.5	795.4	606.9	400.8	251.2	171.0	134.4	123.7	113.0
105°	1023.7	1013.8	927.5	768.7	565.7	380.9	255.0	187.0	151.2	140.5	129.8
107.5°	1085.5	1010.7	882.5	712.2	527.5	370.2	263.4	203.1	167.9	157.2	146.6
110°	1055.0	957.3	820.6	659.6	501.5	367.2	274.1	219.1	185.5	174.4	163.4

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1000.0	893.9	764.2	622.9	484.8	368.0	285.5	234.4	202.3	190.9	179.4
115°	937.4	837.4	719.9	593.9	473.3	371.0	297.0	250.4	217.6	207.3	197.0
117.5°	881.7	788.6	683.2	574.1	467.2	375.6	309.2	264.9	234.4	223.7	213.0
120°	832.9	751.9	657.3	558.8	461.8	380.2	321.4	280.2	250.4	239.7	229.0
122.5°	797.0	721.4	636.7	545.8	458.8	385.5	332.1	294.7	267.2	256.1	245.0
125°	762.6	695.4	616.8	533.6	455.0	390.9	343.5	309.2	281.7	271.0	260.3
127.5°	733.6	669.5	597.0	522.2	452.7	396.2	354.2	322.9	296.2	285.2	274.1
130°	703.8	643.5	577.9	510.7	451.2	402.3	364.1	335.1	308.4	297.7	287.0
132.5°	673.3	619.1	559.6	501.5	450.4	408.4	374.1	345.8	320.6	309.9	299.2
135°	643.5	593.2	542.8	493.1	449.6	413.0	382.5	355.7	331.3	320.6	309.9
137.5°	613.8	572.5	529.0	487.0	449.6	417.6	389.3	364.1	339.7	329.8	319.9
140°	587.8	552.7	516.0	481.7	448.9	420.6	394.7	371.0	348.1	338.2	328.3
142.5°	564.1	535.1	505.4	476.4	448.9	422.9	399.3	376.3	354.2	345.0	335.9
145°	544.3	520.6	495.4	471.8	447.3	424.4	403.1	381.7	361.1	352.7	344.3
147.5°	527.5	508.4	487.8	467.2	445.1	425.2	405.4	386.3	366.4	358.8	351.2
150°	512.2	496.2	479.4	461.1	442.8	424.4	406.9	389.3	371.8	364.9	358.0
152.5°	499.3	486.3	471.0	455.7	438.9	422.9	407.6	392.4	377.1	371.0	364.9
155°	487.0	475.6	463.4	448.9	434.4	421.4	408.4	395.4	382.5	376.8	371.0
157.5°	474.8	464.9	454.2	442.8	429.8	418.3	408.4	397.7	386.3	381.3	376.3
160°	462.6	454.2	445.8	435.9	425.2	416.0	408.4	399.3	390.1	385.9	381.7
162.5°	451.2	444.3	437.4	429.8	421.4	413.8	407.6	400.0	392.4	389.4	386.3
165°	439.7	434.4	429.0	422.9	416.0	410.7	406.1	400.8	393.9	391.6	389.3
167.5°	429.0	425.2	420.6	416.0	411.5	407.6	405.4	400.8	395.4	393.9	392.4
170°	419.9	416.8	414.5	410.7	407.6	405.4	403.8	400.0	396.2	395.0	393.9
172.5°	411.5	409.2	407.6	405.4	403.1	402.3	401.5	399.3	397.0	396.2	395.4
175°	404.6	403.8	403.1	400.8	400.0	399.3	400.0	398.5	397.0	396.6	396.2
177.5°	400.0	399.3	399.3	397.7	397.0	397.7	399.3	397.7	397.0	397.0	397.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1476.7	1476.7	1476.7	1476.7
2.5°	1450.1	1447.0	1465.5	1486.0
5°	1420.3	1425.4	1449.0	1477.8
7.5°	1389.5	1400.8	1428.5	1466.5
10°	1346.4	1366.9	1409.0	1448.0
12.5°	1304.3	1332.0	1372.1	1418.3
15°	1257.1	1287.9	1337.2	1392.6
17.5°	1204.8	1239.7	1297.2	1357.7
20°	1149.4	1195.6	1256.1	1321.8
22.5°	1087.8	1143.2	1205.8	1278.7
25°	1028.3	1088.8	1151.4	1235.6
27.5°	969.8	1029.3	1099.1	1184.3
30°	911.3	965.7	1040.6	1131.9
32.5°	848.7	905.1	984.2	1077.5
35°	791.2	847.7	921.6	1013.9
37.5°	729.6	790.2	861.0	956.4
40°	657.8	728.6	797.4	888.7
42.5°	598.3	673.2	739.9	826.1
45°	551.1	621.9	677.3	761.5
47.5°	507.0	564.4	620.9	698.9
50°	464.9	509.0	567.5	637.3
52.5°	421.8	459.8	510.0	575.7
55°	382.8	418.7	463.9	514.1
57.5°	346.9	372.5	417.7	462.8
60°	306.8	333.5	368.4	406.4
62.5°	273.0	293.5	326.3	358.2
65°	237.1	256.6	281.2	310.9
67.5°	204.2	221.7	241.2	264.8
70°	174.5	187.8	202.2	222.7
72.5°	142.6	157.0	170.4	186.8
75°	117.0	123.1	134.4	145.7
77.5°	90.3	98.5	104.7	113.9
80°	64.7	71.8	73.9	81.1
82.5°	43.1	47.2	51.3	53.4
85°	24.6	26.7	30.8	31.8
87.5°	9.2	10.3	12.3	14.4
90°	7.6	6.1	3.1	0.8
92.5°	26.0	22.1	16.0	11.5
95°	44.3	37.4	29.8	26.7
97.5°	62.6	52.7	44.3	39.7
100°	80.2	67.9	61.1	58.8
102.5°	97.0	84.7	77.9	76.3
105°	113.0	101.5	96.2	93.1
107.5°	129.8	119.1	113.7	111.5
110°	147.3	137.4	132.8	129.8

TEST NUMBER: P999999

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	164.1	155.0	149.6	146.6
115°	181.7	172.5	167.9	164.1
117.5°	198.5	190.1	185.5	182.4
120°	213.7	206.9	202.3	199.2
122.5°	229.8	222.1	217.6	215.3
125°	245.0	235.9	231.3	229.0
127.5°	259.6	249.6	243.5	240.5
130°	271.8	261.1	253.4	250.4
132.5°	283.2	271.8	263.4	259.6
135°	292.4	280.9	271.8	268.7
137.5°	302.3	290.1	280.9	277.1
140°	311.5	299.2	290.1	287.0
142.5°	319.9	307.6	299.2	297.0
145°	329.0	317.6	309.9	306.9
147.5°	338.2	327.5	319.9	317.6
150°	346.6	336.7	330.5	328.3
152.5°	354.2	345.8	339.7	338.9
155°	362.6	354.2	349.6	348.9
157.5°	369.5	361.8	358.0	357.3
160°	375.6	369.5	366.4	365.7
162.5°	380.9	376.3	373.3	374.1
165°	385.5	380.9	379.4	380.2
167.5°	389.3	386.3	384.7	385.5
170°	392.4	390.1	389.3	390.9
172.5°	394.7	392.4	393.1	393.9
175°	396.2	394.7	395.4	396.2
177.5°	397.0	395.4	396.2	397.7
180°	397.0	397.0	397.0	397.0

(END OF REPORT)