

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999005

Luminaire Tested: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999005
REPORT IS A COMBINATION OF REPORTS P984751 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8127.0 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53			47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46			40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39			35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34			30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30			26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26			23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23			20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19			16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17			15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16			14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27277	27277	27277	27277
5°	27344	29085	27448	23140
10°	27026	31750	27195	19078
15°	26370	33490	26736	16069
20°	25958	31444	25958	13968
25°	25132	27013	25246	12490
30°	23771	21235	24223	11314
35°	22564	14684	22942	10351
40°	21178	11087	21419	9583
45°	19468	9111	19787	8756
50°	17990	7996	18024	8016
55°	16305	6814	16411	7211
60°	14511	5691	14711	6293
65°	12901	4629	13139	5374
70°	11299	3632	11589	4334
75°	9482	2638	9857	3143
80°	7401	1671	7928	1865
85°	4859	842	5241	623

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 28197 cd/sqm

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	2.0
10°-20°	477.7	5.9
20°-30°	693.3	8.5
30°-40°	730.9	9.0
40°-50°	646.8	8.0
50°-60°	516.4	6.4
60°-70°	350.8	4.3
70°-80°	179.5	2.2
80°-90°	45.0	0.6
90°-100°	48.6	0.6
100°-110°	181.2	2.2
110°-120°	480.7	5.9
120°-130°	797.2	9.8
130°-140°	846.8	10.4
140°-150°	787.0	9.7
150°-160°	632.7	7.8
160°-170°	407.7	5.0
170°-180°	140.3	1.7
0°-30°	1335.2	16.4
0°-40°	2066.1	25.4
0°-60°	3229.3	39.7
0°-90°	3804.6	46.8
90°-120°	710.5	8.7
90°-150°	3141.6	38.7
90°-180°	4322.0	53.2
0°-180°	8127.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1925	1731	1531	1725	163
15°	1620	2366	1642	1135	1620	458
25°	1456	1971	1462	911	1456	665
35°	1188	1073	1208	756	1188	743
45°	891	646	906	621	891	692
55°	612	454	616	481	612	546
65°	363	280	370	324	363	361
75°	170	138	176	164	170	182
85°	34	36	37	26	34	40
90°	1	29	1	29	1	6
95°	69	46	69	46	69	82
105°	324	81	324	81	324	347
115°	613	88	613	88	613	604
125°	867	912	867	912	867	774
135°	1073	1108	1073	1108	1073	829
145°	1245	1264	1245	1264	1245	779
155°	1371	1372	1371	1372	1371	632
165°	1444	1441	1444	1441	1444	408
175°	1478	1469	1478	1469	1478	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1732.5	1736.5	1743.1	1744.4	1757.7	1768.3	1780.2	1780.2	1784.2	1782.8	1772.3
5°	1724.6	1736.5	1753.7	1768.3	1792.1	1802.7	1818.6	1830.5	1841.1	1849.1	1847.8
7.5°	1711.3	1732.5	1757.7	1785.5	1817.3	1835.8	1858.3	1879.5	1894.1	1907.4	1916.6
10°	1688.8	1724.6	1759.0	1796.1	1837.2	1862.3	1888.8	1916.6	1939.1	1964.3	1988.2
12.5°	1658.3	1710.0	1752.4	1801.4	1851.7	1879.5	1921.9	1943.1	1986.8	2050.4	2067.6
15°	1619.9	1690.1	1729.9	1792.1	1858.3	1880.9	1939.1	1973.6	2063.7	2103.4	2151.1
17.5°	1584.2	1662.3	1715.3	1786.8	1851.7	1895.4	1952.4	2022.6	2098.1	2155.0	2208.0
20°	1555.0	1630.5	1694.1	1773.6	1855.7	1911.3	1970.9	2055.7	2137.8	2196.1	2237.2
22.5°	1488.8	1585.5	1659.7	1748.4	1847.8	1924.6	1981.5	2074.3	2163.0	2198.8	2234.5
25°	1455.7	1539.1	1625.2	1725.9	1842.5	1933.8	1982.9	2086.2	2164.3	2177.6	2185.5
27.5°	1394.8	1488.8	1589.5	1704.7	1841.1	1918.0	1980.2	2074.3	2136.5	2127.2	2103.4
30°	1319.3	1434.5	1545.8	1670.3	1822.6	1906.0	1964.3	2050.4	2082.2	2034.5	1992.1
32.5°	1263.6	1372.2	1495.4	1639.8	1801.4	1880.9	1937.8	2005.4	2012.0	1925.9	1854.4
35°	1188.1	1308.7	1447.7	1600.1	1765.6	1837.2	1890.1	1931.2	1899.4	1778.9	1694.1
37.5°	1120.6	1239.8	1388.1	1543.1	1716.6	1786.8	1829.2	1835.8	1757.7	1651.7	1527.2
40°	1046.4	1169.6	1324.6	1487.5	1662.3	1723.2	1749.7	1729.9	1617.3	1494.1	1349.7
42.5°	972.2	1094.1	1261.0	1427.9	1593.4	1645.1	1655.7	1601.4	1463.6	1319.3	1152.4
45°	891.4	1018.6	1185.5	1353.7	1514.0	1543.1	1544.4	1466.3	1303.4	1152.4	997.4
47.5°	825.2	943.1	1108.7	1276.9	1412.0	1431.8	1423.9	1333.8	1156.3	986.8	851.7
50°	752.3	864.9	1029.2	1194.7	1310.0	1315.3	1295.4	1166.9	993.4	838.4	731.2
52.5°	674.2	788.1	939.1	1098.1	1201.4	1193.4	1155.0	1017.3	854.3	725.9	643.7
55°	611.9	712.6	854.3	1009.3	1082.2	1059.6	1017.3	876.9	748.4	639.8	568.2
57.5°	543.1	631.8	770.9	906.0	948.4	927.2	884.8	753.7	634.5	552.3	504.7
60°	478.2	559.0	680.8	793.4	826.5	804.0	755.0	637.1	551.0	482.1	446.4
62.5°	418.6	488.8	590.8	694.1	707.3	684.8	642.4	547.0	472.9	418.6	392.1
65°	362.9	429.2	511.3	589.4	601.3	577.5	533.8	464.9	402.7	368.2	343.1
67.5°	308.6	361.6	434.5	491.4	498.0	475.5	439.8	384.1	345.7	308.6	290.1
70°	260.9	300.7	357.6	404.0	406.6	385.4	366.9	316.6	287.4	260.9	246.4
72.5°	214.6	242.4	286.1	320.5	321.9	308.6	291.4	259.6	234.4	215.9	201.3
75°	169.5	193.4	219.9	250.3	249.0	238.4	225.2	205.3	184.1	172.2	165.6
77.5°	129.8	144.4	165.6	185.4	185.4	180.1	172.2	157.6	144.4	132.5	125.8
80°	92.7	102.0	119.2	125.8	128.5	127.2	120.5	109.9	104.6	95.4	92.7
82.5°	59.6	66.2	74.2	80.8	84.8	82.1	80.8	75.5	67.6	64.9	62.3
85°	34.4	37.1	41.1	45.0	46.4	45.0	47.7	43.7	39.7	39.7	38.4
87.5°	14.6	15.9	18.5	18.5	19.9	19.9	18.5	19.9	19.9	18.5	17.2
90°	1.1	3.7	6.3	8.9	11.5	12.8	13.7	15.6	17.5	19.4	21.3
92.5°	26.7	25.7	24.8	23.8	22.9	22.4	22.8	23.5	24.2	24.9	25.6
95°	69.3	61.5	53.7	45.8	38.0	34.1	34.9	36.6	38.3	39.9	41.6
97.5°	124.8	105.4	85.9	66.5	47.0	37.3	39.2	43.0	46.8	50.6	54.4
100°	188.8	156.3	123.9	91.4	58.9	42.7	44.7	48.7	52.8	56.8	60.8
102.5°	259.2	258.7	258.3	257.8	257.3	257.1	235.5	192.4	149.2	106.1	62.9
105°	324.3	331.4	338.5	345.6	352.7	356.3	323.9	259.2	194.5	129.8	65.1
107.5°	400.1	406.0	411.9	417.8	423.7	426.7	386.8	306.9	227.0	147.1	67.2
110°	472.6	477.6	482.6	487.5	492.5	495.0	460.7	392.2	323.7	255.2	186.7

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	540.9	545.2	549.4	553.7	558.0	560.1	558.1	554.1	550.0	546.0	542.0
115°	613.4	617.4	621.5	625.5	629.6	631.6	634.6	640.5	646.4	652.3	658.2
117.5°	676.4	681.1	685.9	690.6	695.3	697.7	699.7	703.8	707.8	711.9	715.9
120°	746.8	750.4	753.9	757.5	761.0	762.8	764.9	769.2	773.5	777.7	782.0
122.5°	806.5	810.3	814.1	817.9	821.7	823.6	826.0	830.7	835.4	840.2	844.9
125°	867.4	870.5	873.5	876.6	879.7	881.2	883.5	888.0	892.5	897.0	901.5
127.5°	922.8	926.1	929.5	932.8	936.1	937.8	939.6	943.1	946.7	950.2	953.8
130°	975.1	978.9	982.7	986.5	990.3	992.2	993.5	996.1	998.7	1001.3	1003.9
132.5°	1028.4	1031.5	1034.6	1037.7	1040.8	1042.3	1043.6	1046.2	1048.9	1051.5	1054.1
135°	1073.3	1077.1	1080.9	1084.6	1088.4	1090.3	1091.4	1093.5	1095.6	1097.8	1099.9
137.5°	1120.2	1123.0	1125.9	1128.7	1131.6	1133.0	1134.2	1136.6	1138.9	1141.3	1143.7
140°	1166.1	1168.0	1169.9	1171.8	1173.7	1174.6	1175.9	1178.5	1181.1	1183.7	1186.3
142.5°	1204.5	1206.1	1207.8	1209.4	1211.1	1211.9	1213.4	1216.5	1219.6	1222.7	1225.8
145°	1245.0	1244.8	1244.6	1244.3	1244.1	1244.0	1246.0	1250.0	1254.1	1258.1	1262.1
147.5°	1280.2	1279.5	1278.8	1278.1	1277.4	1277.0	1279.0	1283.1	1287.1	1291.2	1295.2
150°	1314.4	1312.7	1311.1	1309.4	1307.7	1306.9	1308.8	1312.6	1316.4	1320.2	1324.0
152.5°	1343.2	1341.3	1339.4	1337.5	1335.6	1334.6	1336.4	1339.9	1343.5	1347.0	1350.6
155°	1370.9	1368.8	1366.6	1364.5	1362.4	1361.3	1362.7	1365.6	1368.4	1371.3	1374.1
157.5°	1393.3	1391.4	1389.5	1387.6	1385.7	1384.8	1385.9	1388.0	1390.1	1392.3	1394.4
160°	1412.5	1411.1	1409.7	1408.2	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5
162.5°	1429.6	1428.2	1426.8	1425.3	1423.9	1423.2	1423.8	1425.0	1426.1	1427.3	1428.5
165°	1444.5	1443.1	1441.7	1440.2	1438.8	1438.1	1438.5	1439.2	1439.9	1440.6	1441.3
167.5°	1456.3	1454.9	1453.5	1452.0	1450.6	1449.9	1450.3	1451.0	1451.7	1452.4	1453.1
170°	1465.9	1464.5	1463.1	1461.6	1460.2	1459.5	1459.7	1460.2	1460.7	1461.1	1461.6
172.5°	1472.3	1470.9	1469.5	1468.0	1466.6	1465.9	1466.1	1466.6	1467.1	1467.5	1468.0
175°	1477.6	1475.9	1474.3	1472.6	1470.9	1470.1	1470.3	1470.8	1471.3	1471.8	1472.3
177.5°	1479.7	1478.1	1476.4	1474.8	1473.1	1472.3	1472.4	1472.6	1472.9	1473.1	1473.3
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1790.8	1792.1	1794.8	1808.0	1814.6	1816.0	1810.7	1822.6	1826.6	1822.6	1819.9
5°	1875.6	1883.5	1899.4	1916.6	1915.3	1916.6	1924.6	1932.5	1935.2	1924.6	1928.5
7.5°	1949.7	1965.6	1982.9	2009.3	2009.3	2022.6	2027.9	2034.5	2050.4	2042.5	2039.8
10°	2034.5	2055.7	2087.5	2129.9	2131.2	2144.5	2157.7	2178.9	2185.5	2180.2	2182.9
12.5°	2140.5	2181.5	2184.2	2230.5	2251.7	2254.4	2275.6	2271.6	2284.9	2284.9	2307.4
15°	2186.8	2250.4	2286.2	2331.2	2344.5	2328.6	2345.8	2364.3	2365.7	2365.7	2364.3
17.5°	2270.3	2295.5	2331.2	2355.1	2360.4	2360.4	2361.7	2369.6	2364.3	2353.7	2361.7
20°	2287.5	2298.1	2311.3	2308.7	2311.3	2298.1	2284.9	2271.6	2272.9	2266.3	2286.2
22.5°	2255.7	2253.1	2222.6	2202.7	2202.7	2176.2	2151.1	2139.2	2127.2	2131.2	2137.8
25°	2176.2	2135.2	2098.1	2069.0	2062.3	2019.9	1985.5	1974.9	1955.0	1970.9	1973.6
27.5°	2049.1	2002.7	1943.1	1918.0	1883.5	1866.3	1842.5	1810.7	1769.6	1793.4	1789.5
30°	1912.7	1843.8	1794.8	1733.8	1679.5	1675.6	1630.5	1577.5	1556.3	1556.3	1568.3
32.5°	1760.3	1668.9	1597.4	1511.3	1458.3	1435.8	1381.5	1328.5	1340.4	1300.7	1315.3
35°	1582.8	1462.3	1372.2	1288.8	1249.1	1222.6	1152.4	1123.2	1091.4	1072.9	1107.3
37.5°	1413.3	1274.2	1159.0	1067.6	1053.0	1005.3	957.7	939.1	920.6	928.5	927.2
40°	1206.7	1083.5	980.2	908.6	883.5	861.0	829.2	806.7	794.7	801.4	802.7
42.5°	1019.9	916.6	839.8	789.4	768.2	752.3	736.5	717.9	713.9	713.9	719.2
45°	875.5	790.8	739.1	698.0	686.1	674.2	662.3	654.3	651.7	646.4	650.4
47.5°	760.3	692.7	661.0	630.5	617.2	614.6	604.0	600.0	594.7	593.4	594.7
50°	663.6	621.2	592.1	574.9	565.6	561.6	556.3	548.4	545.7	552.3	549.7
52.5°	596.0	556.3	540.4	523.2	517.9	512.6	504.7	506.0	504.7	502.0	502.0
55°	528.5	503.3	487.4	474.2	472.9	467.6	460.9	458.3	457.0	454.3	458.3
57.5°	474.2	454.3	439.8	427.8	422.5	422.5	415.9	410.6	410.6	409.3	410.6
60°	419.9	400.0	390.7	378.8	374.8	373.5	369.6	366.9	362.9	362.9	362.9
62.5°	369.6	353.7	343.1	332.5	333.8	327.2	321.9	319.2	319.2	320.5	320.5
65°	321.9	311.3	298.0	288.8	286.1	284.8	282.1	280.8	276.8	279.5	279.5
67.5°	278.2	263.6	255.6	251.7	247.7	246.4	243.7	241.1	239.7	238.4	241.1
70°	234.4	222.5	215.9	213.3	209.3	208.0	206.6	202.7	204.0	205.3	206.6
72.5°	194.7	184.1	182.8	174.8	174.8	174.8	169.5	172.2	170.9	168.2	170.9
75°	153.6	148.3	145.7	141.7	143.1	141.7	140.4	136.4	136.4	137.8	139.1
77.5°	121.9	116.6	115.2	111.3	108.6	111.3	108.6	107.3	107.3	108.6	108.6
80°	90.1	87.4	83.4	83.4	83.4	82.1	82.1	82.1	80.8	79.5	80.8
82.5°	59.6	59.6	58.3	57.0	58.3	55.6	57.0	57.0	57.0	57.0	57.0
85°	38.4	37.1	37.1	35.8	35.8	35.8	37.1	34.4	34.4	35.8	35.8
87.5°	17.2	17.2	17.2	18.5	17.2	17.2	17.2	18.5	17.2	17.2	17.2
90°	22.5	23.7	24.9	26.1	26.7	26.9	27.4	27.9	28.3	28.8	28.3
92.5°	26.1	26.5	27.0	27.5	27.7	27.8	28.1	28.3	28.6	28.8	28.6
95°	42.8	44.0	45.1	46.3	46.9	46.8	46.6	46.3	46.1	45.9	46.1
97.5°	55.1	55.8	56.5	57.2	57.6	57.7	58.0	58.2	58.5	58.7	58.5
100°	62.7	64.6	66.5	68.4	69.3	69.5	70.0	70.5	71.0	71.5	71.0
102.5°	65.5	68.1	70.8	73.4	74.7	75.1	75.8	76.5	77.2	77.9	77.2
105°	67.7	70.3	72.9	75.5	76.8	77.3	78.2	79.2	80.1	81.1	80.1
107.5°	69.8	72.4	75.0	77.6	78.9	79.4	80.3	81.3	82.2	83.2	82.2
110°	163.0	139.3	115.6	91.9	80.0	80.5	81.4	82.4	83.3	84.3	83.3

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	439.8	337.6	235.4	133.2	82.1	82.5	83.2	83.9	84.6	85.3	84.6
115°	548.4	438.7	328.9	219.2	164.3	155.8	138.7	121.6	104.6	87.5	104.6
117.5°	682.0	648.1	614.2	580.3	563.3	532.2	470.1	408.0	345.9	283.8	345.9
120°	784.8	787.7	790.5	793.4	794.8	778.8	746.8	714.8	682.8	650.8	682.8
122.5°	846.3	847.8	849.2	850.7	851.4	851.5	851.7	852.0	852.2	852.4	852.2
125°	903.2	904.8	906.5	908.2	909.0	909.4	910.1	910.8	911.5	912.2	911.5
127.5°	956.2	958.5	960.9	963.2	964.4	964.5	964.8	965.0	965.3	965.5	965.3
130°	1006.5	1009.1	1011.7	1014.3	1015.6	1015.5	1015.3	1015.0	1014.8	1014.6	1014.8
132.5°	1056.2	1058.4	1060.5	1062.6	1063.7	1063.6	1063.3	1063.1	1062.8	1062.6	1062.8
135°	1102.3	1104.7	1107.0	1109.4	1110.6	1110.4	1109.9	1109.4	1109.0	1108.5	1109.0
137.5°	1146.1	1148.4	1150.8	1153.1	1154.3	1153.9	1153.2	1152.5	1151.8	1151.1	1151.8
140°	1188.4	1190.6	1192.7	1194.8	1195.9	1195.3	1194.1	1193.0	1191.8	1190.6	1191.8
142.5°	1227.7	1229.6	1231.5	1233.4	1234.4	1233.8	1232.6	1231.4	1230.2	1229.0	1230.2
145°	1263.8	1265.4	1267.1	1268.8	1269.6	1269.0	1267.8	1266.6	1265.4	1264.2	1265.4
147.5°	1296.4	1297.6	1298.7	1299.9	1300.5	1300.0	1299.1	1298.1	1297.2	1296.2	1297.2
150°	1325.4	1326.8	1328.3	1329.7	1330.4	1329.8	1328.6	1327.4	1326.2	1325.0	1326.2
152.5°	1352.0	1353.4	1354.9	1356.3	1357.0	1356.2	1354.5	1352.9	1351.2	1349.6	1351.2
155°	1375.5	1376.9	1378.4	1379.8	1380.5	1379.6	1377.7	1375.8	1373.9	1372.0	1373.9
157.5°	1396.0	1397.7	1399.3	1401.0	1401.8	1400.9	1399.0	1397.1	1395.2	1393.3	1395.2
160°	1413.9	1415.3	1416.8	1418.2	1418.9	1418.1	1416.4	1414.7	1413.1	1411.4	1413.1
162.5°	1430.2	1431.8	1433.5	1435.2	1436.0	1434.9	1432.8	1430.7	1428.5	1426.4	1428.5
165°	1443.0	1444.6	1446.3	1448.0	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1443.0
167.5°	1454.7	1456.4	1458.0	1459.7	1460.5	1459.4	1457.3	1455.2	1453.0	1450.9	1453.0
170°	1463.3	1464.9	1466.6	1468.3	1469.1	1468.0	1465.9	1463.8	1461.6	1459.5	1461.6
172.5°	1469.7	1471.3	1473.0	1474.7	1475.5	1474.4	1472.3	1470.2	1468.0	1465.9	1468.0
175°	1473.9	1475.6	1477.2	1478.9	1479.7	1478.5	1476.2	1473.8	1471.5	1469.1	1471.5
177.5°	1475.0	1476.6	1478.3	1480.0	1480.8	1479.7	1477.6	1475.5	1473.3	1471.2	1473.3
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1826.6	1817.3	1809.3	1810.7	1817.3	1812.0	1798.7	1781.5	1774.9	1767.0	1774.9
5°	1936.5	1928.5	1912.7	1914.0	1910.0	1904.7	1883.5	1857.0	1857.0	1835.8	1833.2
7.5°	2045.1	2033.2	2022.6	2019.9	2005.4	1994.8	1976.2	1939.1	1924.6	1899.4	1884.8
10°	2167.0	2157.7	2145.8	2131.2	2123.3	2104.7	2074.3	2019.9	1993.5	1959.0	1933.8
12.5°	2290.2	2288.8	2262.3	2233.2	2231.9	2202.7	2181.5	2108.7	2072.9	2026.6	1967.0
15°	2368.3	2361.7	2347.1	2332.5	2336.5	2304.7	2257.0	2170.9	2147.1	2091.5	2027.9
17.5°	2367.0	2367.0	2363.0	2360.4	2356.4	2347.1	2320.6	2263.7	2225.2	2155.0	2095.4
20°	2291.5	2308.7	2312.7	2311.3	2324.6	2331.2	2329.9	2294.1	2263.7	2201.4	2140.5
22.5°	2140.5	2180.2	2197.4	2208.0	2235.8	2250.4	2284.9	2271.6	2263.7	2217.3	2165.6
25°	2000.1	2013.3	2065.0	2067.6	2106.0	2141.8	2176.2	2198.8	2227.9	2210.7	2167.0
27.5°	1818.6	1849.1	1886.2	1914.0	1921.9	1994.8	2051.7	2094.1	2160.3	2165.6	2151.1
30°	1613.3	1627.9	1688.8	1725.9	1768.3	1821.3	1903.4	1976.2	2035.8	2090.1	2108.7
32.5°	1363.0	1422.6	1458.3	1503.4	1540.5	1634.5	1735.2	1829.2	1898.1	1989.5	2029.2
35°	1133.8	1180.2	1241.1	1259.6	1327.2	1406.7	1537.8	1658.3	1763.0	1855.7	1936.5
37.5°	944.4	981.5	1046.4	1075.5	1115.3	1217.3	1327.2	1476.9	1602.7	1716.6	1817.3
40°	814.6	842.4	891.4	900.7	933.8	1026.5	1115.3	1255.7	1422.6	1576.2	1686.2
42.5°	725.9	739.1	772.2	784.1	805.3	867.6	947.1	1079.5	1234.5	1393.4	1548.4
45°	662.3	671.5	691.4	702.0	728.5	756.3	821.2	927.2	1049.0	1209.3	1376.2
47.5°	605.3	617.2	625.2	631.8	646.4	676.8	719.2	797.4	913.9	1061.0	1222.6
50°	557.6	561.6	576.2	577.5	586.8	606.6	646.4	694.1	786.8	906.0	1062.3
52.5°	510.0	513.9	523.2	532.5	536.4	552.3	578.8	618.6	687.4	781.5	920.6
55°	462.3	467.6	476.8	483.5	487.4	500.7	516.6	555.0	609.3	675.5	789.4
57.5°	414.6	426.5	429.2	433.1	439.8	454.3	468.9	491.4	533.8	594.7	678.2
60°	369.6	373.5	382.8	386.8	393.4	401.3	419.9	437.1	467.6	515.3	590.8
62.5°	323.2	332.5	336.4	340.4	345.7	355.0	366.9	385.4	411.9	450.3	510.0
65°	283.5	284.8	292.7	298.0	303.3	309.9	321.9	339.1	355.0	390.7	434.5
67.5°	245.0	247.7	250.3	255.6	262.3	268.9	279.5	288.8	308.6	332.5	366.9
70°	208.0	208.0	214.6	218.6	217.2	225.2	233.1	243.7	258.3	280.8	308.6
72.5°	174.8	173.5	178.8	180.1	182.8	188.1	193.4	204.0	211.9	229.1	250.3
75°	139.1	141.7	144.4	144.4	148.3	152.3	157.6	162.9	172.2	182.8	198.7
77.5°	109.9	109.9	112.6	113.9	117.9	116.6	121.9	127.2	133.8	143.1	155.0
80°	80.8	83.4	83.4	83.4	84.8	86.1	91.4	95.4	99.3	106.0	111.3
82.5°	57.0	57.0	59.6	59.6	59.6	62.3	62.3	63.6	66.2	70.2	74.2
85°	35.8	35.8	35.8	37.1	35.8	37.1	39.7	38.4	39.7	42.4	42.4
87.5°	17.2	17.2	17.2	17.2	17.2	18.5	17.2	18.5	19.9	19.9	19.9
90°	27.9	27.4	26.9	26.7	26.1	24.9	23.7	22.5	21.3	19.4	17.5
92.5°	28.3	28.1	27.8	27.7	27.5	27.0	26.5	26.1	25.6	24.9	24.2
95°	46.3	46.6	46.8	46.9	46.3	45.1	44.0	42.8	41.6	39.9	38.3
97.5°	58.2	58.0	57.7	57.6	57.2	56.5	55.8	55.1	54.4	50.6	46.8
100°	70.5	70.0	69.5	69.3	68.4	66.5	64.6	62.7	60.8	56.8	52.8
102.5°	76.5	75.8	75.1	74.7	73.4	70.8	68.1	65.5	62.9	106.1	149.2
105°	79.2	78.2	77.3	76.8	75.5	72.9	70.3	67.7	65.1	129.8	194.5
107.5°	81.3	80.3	79.4	78.9	77.6	75.0	72.4	69.8	67.2	147.1	227.0
110°	82.4	81.4	80.5	80.0	91.9	115.6	139.3	163.0	186.7	255.2	323.7

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	83.9	83.2	82.5	82.1	133.2	235.4	337.6	439.8	542.0	546.0	550.0
115°	121.6	138.7	155.8	164.3	219.2	328.9	438.7	548.4	658.2	652.3	646.4
117.5°	408.0	470.1	532.2	563.3	580.3	614.2	648.1	682.0	715.9	711.9	707.8
120°	714.8	746.8	778.8	794.8	793.4	790.5	787.7	784.8	782.0	777.7	773.5
122.5°	852.0	851.7	851.5	851.4	850.7	849.2	847.8	846.3	844.9	840.2	835.4
125°	910.8	910.1	909.4	909.0	908.2	906.5	904.8	903.2	901.5	897.0	892.5
127.5°	965.0	964.8	964.5	964.4	963.2	960.9	958.5	956.2	953.8	950.2	946.7
130°	1015.0	1015.3	1015.5	1015.6	1014.3	1011.7	1009.1	1006.5	1003.9	1001.3	998.7
132.5°	1063.1	1063.3	1063.6	1063.7	1062.6	1060.5	1058.4	1056.2	1054.1	1051.5	1048.9
135°	1109.4	1109.9	1110.4	1110.6	1109.4	1107.0	1104.7	1102.3	1099.9	1097.8	1095.6
137.5°	1152.5	1153.2	1153.9	1154.3	1153.1	1150.8	1148.4	1146.1	1143.7	1141.3	1138.9
140°	1193.0	1194.1	1195.3	1195.9	1194.8	1192.7	1190.6	1188.4	1186.3	1183.7	1181.1
142.5°	1231.4	1232.6	1233.8	1234.4	1233.4	1231.5	1229.6	1227.7	1225.8	1222.7	1219.6
145°	1266.6	1267.8	1269.0	1269.6	1268.8	1267.1	1265.4	1263.8	1262.1	1258.1	1254.1
147.5°	1298.1	1299.1	1300.0	1300.5	1299.9	1298.7	1297.6	1296.4	1295.2	1291.2	1287.1
150°	1327.4	1328.6	1329.8	1330.4	1329.7	1328.3	1326.8	1325.4	1324.0	1320.2	1316.4
152.5°	1352.9	1354.5	1356.2	1357.0	1356.3	1354.9	1353.4	1352.0	1350.6	1347.0	1343.5
155°	1375.8	1377.7	1379.6	1380.5	1379.8	1378.4	1376.9	1375.5	1374.1	1371.3	1368.4
157.5°	1397.1	1399.0	1400.9	1401.8	1401.0	1399.3	1397.7	1396.0	1394.4	1392.3	1390.1
160°	1414.7	1416.4	1418.1	1418.9	1418.2	1416.8	1415.3	1413.9	1412.5	1411.1	1409.7
162.5°	1430.7	1432.8	1434.9	1436.0	1435.2	1433.5	1431.8	1430.2	1428.5	1427.3	1426.1
165°	1444.6	1446.3	1448.0	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1440.6	1439.9
167.5°	1455.2	1457.3	1459.4	1460.5	1459.7	1458.0	1456.4	1454.7	1453.1	1452.4	1451.7
170°	1463.8	1465.9	1468.0	1469.1	1468.3	1466.6	1464.9	1463.3	1461.6	1461.1	1460.7
172.5°	1470.2	1472.3	1474.4	1475.5	1474.7	1473.0	1471.3	1469.7	1468.0	1467.5	1467.1
175°	1473.8	1476.2	1478.5	1479.7	1478.9	1477.2	1475.6	1473.9	1472.3	1471.8	1471.3
177.5°	1475.5	1477.6	1479.7	1480.8	1480.0	1478.3	1476.6	1475.0	1473.3	1473.1	1472.9
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1768.3	1761.7	1757.7	1760.3	1752.4	1732.5	1732.5	1739.1	1731.2	1723.2	1711.3
5°	1817.3	1804.0	1796.1	1794.8	1776.2	1744.4	1737.8	1731.2	1714.0	1695.4	1675.6
7.5°	1865.0	1841.1	1827.9	1818.6	1792.1	1751.1	1733.8	1719.3	1691.5	1663.6	1638.5
10°	1904.7	1870.3	1854.4	1839.8	1805.4	1753.7	1725.9	1699.4	1663.6	1627.9	1596.1
12.5°	1936.5	1896.8	1876.9	1855.7	1813.3	1745.8	1711.3	1668.9	1633.2	1585.5	1553.7
15°	1989.5	1907.4	1888.8	1868.9	1825.2	1732.5	1690.1	1642.4	1593.4	1529.9	1495.4
17.5°	2031.9	1921.9	1920.6	1878.2	1821.3	1727.2	1662.3	1600.1	1547.1	1483.5	1429.2
20°	2057.0	1944.4	1923.3	1879.5	1808.0	1691.5	1623.9	1555.0	1498.1	1421.2	1366.9
22.5°	2078.2	1976.2	1920.6	1867.6	1780.2	1679.5	1580.2	1515.3	1437.1	1353.7	1302.0
25°	2086.2	1982.9	1924.6	1863.6	1760.3	1645.1	1532.5	1462.3	1374.9	1299.4	1229.2
27.5°	2087.5	1981.5	1910.0	1846.4	1732.5	1600.1	1484.8	1410.6	1314.0	1226.5	1156.3
30°	2074.3	1967.0	1902.1	1833.2	1706.0	1559.0	1426.5	1344.4	1241.1	1153.7	1080.8
32.5°	2034.5	1937.8	1884.8	1809.3	1671.6	1502.0	1370.9	1279.5	1170.9	1084.8	1014.6
35°	1968.3	1902.1	1843.8	1773.6	1626.6	1449.1	1315.3	1208.0	1098.1	1015.9	949.7
37.5°	1886.2	1850.4	1796.1	1727.2	1574.9	1401.4	1253.0	1133.8	1023.9	944.4	879.5
40°	1774.9	1784.2	1731.2	1668.9	1514.0	1336.5	1172.2	1058.3	955.0	880.8	817.2
42.5°	1654.4	1692.8	1662.3	1602.7	1446.4	1264.9	1112.6	986.8	886.1	809.3	756.3
45°	1524.6	1590.8	1572.2	1528.5	1376.2	1189.4	1027.9	906.0	817.2	743.1	696.7
47.5°	1382.8	1476.9	1476.9	1445.1	1298.1	1113.9	955.0	830.5	743.1	690.1	645.1
50°	1238.5	1344.4	1361.6	1340.4	1210.6	1027.9	866.3	753.7	678.2	626.5	593.4
52.5°	1087.5	1210.6	1242.4	1231.8	1117.9	945.7	793.4	683.5	614.6	569.6	540.4
55°	943.1	1086.1	1120.6	1124.5	1018.6	855.7	712.6	615.9	549.7	519.2	494.1
57.5°	806.7	944.4	982.8	989.4	917.9	773.5	637.1	552.3	492.7	467.6	447.7
60°	690.1	805.3	855.7	870.2	808.0	678.2	566.9	484.8	439.8	415.9	397.4
62.5°	594.7	687.4	740.4	744.4	716.6	594.7	494.1	425.2	386.8	365.6	356.3
65°	502.0	585.5	617.2	633.1	610.6	515.3	426.5	369.6	339.1	320.5	311.3
67.5°	427.8	480.8	507.3	528.5	506.0	434.5	362.9	316.6	294.1	275.5	270.2
70°	351.0	394.7	414.6	435.8	415.9	361.6	309.9	267.6	247.7	233.1	226.5
72.5°	280.8	315.2	333.8	347.0	335.1	290.1	247.7	218.6	204.0	193.4	189.4
75°	222.5	246.4	257.0	266.2	260.9	226.5	200.0	176.2	162.9	153.6	151.0
77.5°	169.5	186.8	198.7	201.3	194.7	172.2	149.7	135.1	124.5	119.2	116.6
80°	120.5	131.1	137.8	141.7	135.1	125.8	109.9	99.3	90.1	83.4	82.1
82.5°	80.8	86.1	91.4	90.1	87.4	79.5	70.2	64.9	60.9	55.6	55.6
85°	46.4	47.7	50.3	51.7	50.3	45.0	39.7	37.1	34.4	30.5	30.5
87.5°	19.9	21.2	21.2	22.5	19.9	19.9	17.2	14.6	14.6	13.2	11.9
90°	15.6	13.7	12.8	11.5	8.9	6.3	3.7	1.1	3.7	6.3	8.9
92.5°	23.5	22.8	22.4	22.9	23.8	24.8	25.7	26.7	25.7	24.8	23.8
95°	36.6	34.9	34.1	38.0	45.8	53.7	61.5	69.3	61.5	53.7	45.8
97.5°	43.0	39.2	37.3	47.0	66.5	85.9	105.4	124.8	105.4	85.9	66.5
100°	48.7	44.7	42.7	58.9	91.4	123.9	156.3	188.8	156.3	123.9	91.4
102.5°	192.4	235.5	257.1	257.3	257.8	258.3	258.7	259.2	258.7	258.3	257.8
105°	259.2	323.9	356.3	352.7	345.6	338.5	331.4	324.3	331.4	338.5	345.6
107.5°	306.9	386.8	426.7	423.7	417.8	411.9	406.0	400.1	406.0	411.9	417.8
110°	392.2	460.7	495.0	492.5	487.5	482.6	477.6	472.6	477.6	482.6	487.5

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	554.1	558.1	560.1	558.0	553.7	549.4	545.2	540.9	545.2	549.4	553.7
115°	640.5	634.6	631.6	629.6	625.5	621.5	617.4	613.4	617.4	621.5	625.5
117.5°	703.8	699.7	697.7	695.3	690.6	685.9	681.1	676.4	681.1	685.9	690.6
120°	769.2	764.9	762.8	761.0	757.5	753.9	750.4	746.8	750.4	753.9	757.5
122.5°	830.7	826.0	823.6	821.7	817.9	814.1	810.3	806.5	810.3	814.1	817.9
125°	888.0	883.5	881.2	879.7	876.6	873.5	870.5	867.4	870.5	873.5	876.6
127.5°	943.1	939.6	937.8	936.1	932.8	929.5	926.1	922.8	926.1	929.5	932.8
130°	996.1	993.5	992.2	990.3	986.5	982.7	978.9	975.1	978.9	982.7	986.5
132.5°	1046.2	1043.6	1042.3	1040.8	1037.7	1034.6	1031.5	1028.4	1031.5	1034.6	1037.7
135°	1093.5	1091.4	1090.3	1088.4	1084.6	1080.9	1077.1	1073.3	1077.1	1080.9	1084.6
137.5°	1136.6	1134.2	1133.0	1131.6	1128.7	1125.9	1123.0	1120.2	1123.0	1125.9	1128.7
140°	1178.5	1175.9	1174.6	1173.7	1171.8	1169.9	1168.0	1166.1	1168.0	1169.9	1171.8
142.5°	1216.5	1213.4	1211.9	1211.1	1209.4	1207.8	1206.1	1204.5	1206.1	1207.8	1209.4
145°	1250.0	1246.0	1244.0	1244.1	1244.3	1244.6	1244.8	1245.0	1244.8	1244.6	1244.3
147.5°	1283.1	1279.0	1277.0	1277.4	1278.1	1278.8	1279.5	1280.2	1279.5	1278.8	1278.1
150°	1312.6	1308.8	1306.9	1307.7	1309.4	1311.1	1312.7	1314.4	1312.7	1311.1	1309.4
152.5°	1339.9	1336.4	1334.6	1335.6	1337.5	1339.4	1341.3	1343.2	1341.3	1339.4	1337.5
155°	1365.6	1362.7	1361.3	1362.4	1364.5	1366.6	1368.8	1370.9	1368.8	1366.6	1364.5
157.5°	1388.0	1385.9	1384.8	1385.7	1387.6	1389.5	1391.4	1393.3	1391.4	1389.5	1387.6
160°	1408.2	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5	1411.1	1409.7	1408.2
162.5°	1425.0	1423.8	1423.2	1423.9	1425.3	1426.8	1428.2	1429.6	1428.2	1426.8	1425.3
165°	1439.2	1438.5	1438.1	1438.8	1440.2	1441.7	1443.1	1444.5	1443.1	1441.7	1440.2
167.5°	1451.0	1450.3	1449.9	1450.6	1452.0	1453.5	1454.9	1456.3	1454.9	1453.5	1452.0
170°	1460.2	1459.7	1459.5	1460.2	1461.6	1463.1	1464.5	1465.9	1464.5	1463.1	1461.6
172.5°	1466.6	1466.1	1465.9	1466.6	1468.0	1469.5	1470.9	1472.3	1470.9	1469.5	1468.0
175°	1470.8	1470.3	1470.1	1470.9	1472.6	1474.3	1475.9	1477.6	1475.9	1474.3	1472.6
177.5°	1472.6	1472.4	1472.3	1473.1	1474.8	1476.4	1478.1	1479.7	1478.1	1476.4	1474.8
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1704.7	1711.3	1710.0	1696.8	1682.2	1670.3	1647.7	1650.4	1642.4	1643.8	1651.7
5°	1662.3	1662.3	1657.0	1638.5	1614.6	1601.4	1576.2	1569.6	1553.7	1552.4	1551.1
7.5°	1617.3	1610.7	1604.0	1577.5	1548.4	1527.2	1492.8	1484.8	1468.9	1458.3	1453.0
10°	1564.3	1555.0	1541.8	1511.3	1475.6	1449.1	1413.3	1402.7	1372.2	1359.0	1351.0
12.5°	1506.0	1500.7	1479.5	1454.4	1396.1	1366.9	1315.3	1325.9	1295.4	1268.9	1264.9
15°	1447.7	1427.9	1415.9	1374.9	1304.7	1291.4	1250.4	1229.2	1201.4	1180.2	1180.2
17.5°	1390.8	1360.3	1333.8	1290.1	1238.5	1201.4	1170.9	1160.3	1125.9	1104.7	1100.7
20°	1315.3	1280.8	1274.2	1212.0	1176.2	1135.1	1106.0	1079.5	1054.3	1045.1	1038.4
22.5°	1243.8	1204.0	1193.4	1140.4	1104.7	1063.6	1034.5	1015.9	997.4	990.8	978.8
25°	1166.9	1143.1	1127.2	1070.2	1030.5	992.1	972.2	959.0	941.8	940.4	932.5
27.5°	1092.8	1070.2	1054.3	1000.0	970.9	935.1	919.2	904.7	895.4	891.4	887.5
30°	1029.2	1004.0	985.5	945.7	910.0	880.8	867.6	858.3	853.0	846.4	845.1
32.5°	959.0	944.4	919.2	888.8	861.0	833.1	825.2	818.6	810.6	808.0	806.7
35°	899.4	879.5	863.6	829.2	817.2	793.4	784.1	778.8	768.2	765.6	762.9
37.5°	841.1	822.5	805.3	784.1	761.6	748.4	743.1	735.1	729.8	731.2	728.5
40°	782.8	768.2	755.0	732.5	719.2	712.6	702.0	694.1	691.4	692.7	691.4
42.5°	725.9	712.6	704.7	687.4	674.2	667.6	661.0	653.0	657.0	657.0	661.0
45°	674.2	662.3	657.0	643.7	635.8	625.2	618.6	617.2	622.5	621.2	621.2
47.5°	621.2	617.2	610.6	598.7	588.1	581.5	580.2	580.2	585.5	588.1	586.8
50°	580.2	572.2	564.3	555.0	547.0	544.4	540.4	543.1	548.4	548.4	551.0
52.5°	528.5	523.2	520.5	512.6	507.3	507.3	507.3	508.6	512.6	516.6	515.3
55°	483.5	479.5	476.8	472.9	466.2	467.6	466.2	468.9	472.9	476.8	479.5
57.5°	435.8	434.5	431.8	425.2	425.2	423.9	427.8	429.2	435.8	438.4	442.4
60°	393.4	389.4	389.4	384.1	384.1	384.1	388.1	392.1	397.4	398.7	401.3
62.5°	348.4	348.4	347.0	343.1	343.1	347.0	348.4	353.7	356.3	356.3	360.3
65°	306.0	304.6	303.3	304.6	306.0	306.0	309.9	312.6	315.2	316.6	317.9
67.5°	263.6	262.3	264.9	263.6	266.2	271.5	270.2	274.2	278.2	278.2	279.5
70°	223.8	226.5	225.2	227.8	226.5	229.1	233.1	234.4	234.4	235.8	239.7
72.5°	186.8	186.8	186.8	185.4	186.8	189.4	192.1	193.4	196.0	197.4	201.3
75°	151.0	151.0	148.3	151.0	151.0	153.6	156.3	156.3	156.3	158.9	162.9
77.5°	113.9	115.2	113.9	116.6	116.6	117.9	120.5	119.2	121.9	123.2	124.5
80°	83.4	82.1	82.1	82.1	83.4	83.4	86.1	87.4	87.4	91.4	88.7
82.5°	53.0	54.3	53.0	54.3	54.3	55.6	54.3	55.6	57.0	59.6	58.3
85°	30.5	29.1	29.1	30.5	29.1	29.1	30.5	29.1	30.5	29.1	30.5
87.5°	11.9	10.6	10.6	10.6	10.6	9.3	9.3	7.9	7.9	7.9	6.6
90°	11.5	12.8	13.7	15.6	17.5	19.4	21.3	22.5	23.7	24.9	26.1
92.5°	22.9	22.4	22.8	23.5	24.2	24.9	25.6	26.1	26.5	27.0	27.5
95°	38.0	34.1	34.9	36.6	38.3	39.9	41.6	42.8	44.0	45.1	46.3
97.5°	47.0	37.3	39.2	43.0	46.8	50.6	54.4	55.1	55.8	56.5	57.2
100°	58.9	42.7	44.7	48.7	52.8	56.8	60.8	62.7	64.6	66.5	68.4
102.5°	257.3	257.1	235.5	192.4	149.2	106.1	62.9	65.5	68.1	70.8	73.4
105°	352.7	356.3	323.9	259.2	194.5	129.8	65.1	67.7	70.3	72.9	75.5
107.5°	423.7	426.7	386.8	306.9	227.0	147.1	67.2	69.8	72.4	75.0	77.6
110°	492.5	495.0	460.7	392.2	323.7	255.2	186.7	163.0	139.3	115.6	91.9

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	558.0	560.1	558.1	554.1	550.0	546.0	542.0	439.8	337.6	235.4	133.2
115°	629.6	631.6	634.6	640.5	646.4	652.3	658.2	548.4	438.7	328.9	219.2
117.5°	695.3	697.7	699.7	703.8	707.8	711.9	715.9	682.0	648.1	614.2	580.3
120°	761.0	762.8	764.9	769.2	773.5	777.7	782.0	784.8	787.7	790.5	793.4
122.5°	821.7	823.6	826.0	830.7	835.4	840.2	844.9	846.3	847.8	849.2	850.7
125°	879.7	881.2	883.5	888.0	892.5	897.0	901.5	903.2	904.8	906.5	908.2
127.5°	936.1	937.8	939.6	943.1	946.7	950.2	953.8	956.2	958.5	960.9	963.2
130°	990.3	992.2	993.5	996.1	998.7	1001.3	1003.9	1006.5	1009.1	1011.7	1014.3
132.5°	1040.8	1042.3	1043.6	1046.2	1048.9	1051.5	1054.1	1056.2	1058.4	1060.5	1062.6
135°	1088.4	1090.3	1091.4	1093.5	1095.6	1097.8	1099.9	1102.3	1104.7	1107.0	1109.4
137.5°	1131.6	1133.0	1134.2	1136.6	1138.9	1141.3	1143.7	1146.1	1148.4	1150.8	1153.1
140°	1173.7	1174.6	1175.9	1178.5	1181.1	1183.7	1186.3	1188.4	1190.6	1192.7	1194.8
142.5°	1211.1	1211.9	1213.4	1216.5	1219.6	1222.7	1225.8	1227.7	1229.6	1231.5	1233.4
145°	1244.1	1244.0	1246.0	1250.0	1254.1	1258.1	1262.1	1263.8	1265.4	1267.1	1268.8
147.5°	1277.4	1277.0	1279.0	1283.1	1287.1	1291.2	1295.2	1296.4	1297.6	1298.7	1299.9
150°	1307.7	1306.9	1308.8	1312.6	1316.4	1320.2	1324.0	1325.4	1326.8	1328.3	1329.7
152.5°	1335.6	1334.6	1336.4	1339.9	1343.5	1347.0	1350.6	1352.0	1353.4	1354.9	1356.3
155°	1362.4	1361.3	1362.7	1365.6	1368.4	1371.3	1374.1	1375.5	1376.9	1378.4	1379.8
157.5°	1385.7	1384.8	1385.9	1388.0	1390.1	1392.3	1394.4	1396.0	1397.7	1399.3	1401.0
160°	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5	1413.9	1415.3	1416.8	1418.2
162.5°	1423.9	1423.2	1423.8	1425.0	1426.1	1427.3	1428.5	1430.2	1431.8	1433.5	1435.2
165°	1438.8	1438.1	1438.5	1439.2	1439.9	1440.6	1441.3	1443.0	1444.6	1446.3	1448.0
167.5°	1450.6	1449.9	1450.3	1451.0	1451.7	1452.4	1453.1	1454.7	1456.4	1458.0	1459.7
170°	1460.2	1459.5	1459.7	1460.2	1460.7	1461.1	1461.6	1463.3	1464.9	1466.6	1468.3
172.5°	1466.6	1465.9	1466.1	1466.6	1467.1	1467.5	1468.0	1469.7	1471.3	1473.0	1474.7
175°	1470.9	1470.1	1470.3	1470.8	1471.3	1471.8	1472.3	1473.9	1475.6	1477.2	1478.9
177.5°	1473.1	1472.3	1472.4	1472.6	1472.9	1473.1	1473.3	1475.0	1476.6	1478.3	1480.0
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1642.4	1646.4	1637.1	1634.5	1637.1	1627.9	1630.5	1633.2	1633.2	1637.1	1639.8
5°	1547.1	1541.8	1532.5	1529.9	1527.2	1531.2	1528.5	1532.5	1533.8	1543.1	1544.4
7.5°	1453.0	1445.1	1437.1	1429.2	1426.5	1419.9	1426.5	1426.5	1435.8	1433.2	1439.8
10°	1341.8	1340.4	1329.9	1325.9	1320.6	1310.0	1324.6	1320.6	1327.2	1339.1	1341.8
12.5°	1259.6	1245.1	1251.7	1233.2	1239.8	1229.2	1230.5	1230.5	1241.1	1242.4	1239.8
15°	1181.5	1169.6	1152.4	1144.4	1140.4	1135.1	1152.4	1153.7	1145.7	1164.3	1157.7
17.5°	1102.0	1102.0	1086.1	1082.2	1071.6	1076.9	1074.2	1075.5	1072.9	1086.1	1092.8
20°	1033.2	1026.5	1021.2	1022.6	1009.3	1006.7	1004.0	1006.7	1015.9	1025.2	1027.9
22.5°	977.5	973.5	960.3	963.0	952.4	956.3	953.7	960.3	961.6	961.6	970.9
25°	924.5	919.2	920.6	915.3	911.3	911.3	907.3	911.3	916.6	919.2	920.6
27.5°	884.8	880.8	874.2	870.2	872.9	866.3	871.6	875.5	875.5	872.9	875.5
30°	837.1	839.8	839.8	826.5	831.8	829.2	833.1	835.8	835.8	837.1	834.5
32.5°	805.3	797.4	796.1	794.7	794.7	789.4	789.4	793.4	794.7	796.1	800.0
35°	762.9	762.9	756.3	760.3	755.0	756.3	755.0	756.3	759.0	755.0	759.0
37.5°	724.5	725.9	723.2	725.9	727.2	724.5	721.9	727.2	724.5	724.5	721.9
40°	691.4	690.1	691.4	691.4	691.4	692.7	690.1	690.1	690.1	687.4	684.8
42.5°	663.6	655.7	658.3	659.6	655.7	655.7	657.0	655.7	659.6	651.7	651.7
45°	623.9	621.2	622.5	622.5	625.2	621.2	623.9	625.2	621.2	619.9	617.2
47.5°	588.1	590.8	588.1	590.8	590.8	593.4	588.1	589.4	590.8	585.5	581.5
50°	552.3	552.3	556.3	555.0	556.3	553.7	553.7	552.3	553.7	551.0	547.0
52.5°	519.2	515.3	521.9	520.5	519.2	517.9	516.6	517.9	515.3	512.6	512.6
55°	478.2	478.2	482.1	483.5	483.5	480.8	478.2	479.5	478.2	476.8	475.5
57.5°	445.0	439.8	442.4	443.7	443.7	439.8	442.4	439.8	439.8	441.1	437.1
60°	402.7	402.7	400.0	404.0	404.0	401.3	401.3	402.7	400.0	398.7	397.4
62.5°	357.6	359.0	362.9	364.3	365.6	362.9	360.3	361.6	361.6	357.6	359.0
65°	319.2	321.9	327.2	325.8	323.2	324.5	321.9	323.2	319.2	320.5	316.6
67.5°	282.1	280.8	282.1	282.1	284.8	283.5	280.8	280.8	279.5	283.5	279.5
70°	242.4	242.4	242.4	242.4	243.7	245.0	242.4	239.7	241.1	238.4	237.1
72.5°	201.3	202.7	201.3	204.0	200.0	202.7	202.7	201.3	200.0	200.0	200.0
75°	162.9	165.6	161.6	162.9	161.6	164.2	162.9	162.9	160.3	158.9	160.3
77.5°	124.5	125.8	123.2	124.5	123.2	124.5	124.5	123.2	123.2	123.2	123.2
80°	88.7	90.1	88.7	87.4	86.1	88.7	86.1	87.4	88.7	87.4	90.1
82.5°	57.0	57.0	55.6	57.0	54.3	54.3	55.6	55.6	54.3	57.0	54.3
85°	27.8	27.8	30.5	27.8	26.5	26.5	26.5	27.8	26.5	29.1	27.8
87.5°	6.6	5.3	6.6	6.6	5.3	5.3	6.6	5.3	6.6	7.9	5.3
90°	26.7	26.9	27.4	27.9	28.3	28.8	28.3	27.9	27.4	26.9	26.7
92.5°	27.7	27.8	28.1	28.3	28.6	28.8	28.6	28.3	28.1	27.8	27.7
95°	46.9	46.8	46.6	46.3	46.1	45.9	46.1	46.3	46.6	46.8	46.9
97.5°	57.6	57.7	58.0	58.2	58.5	58.7	58.5	58.2	58.0	57.7	57.6
100°	69.3	69.5	70.0	70.5	71.0	71.5	71.0	70.5	70.0	69.5	69.3
102.5°	74.7	75.1	75.8	76.5	77.2	77.9	77.2	76.5	75.8	75.1	74.7
105°	76.8	77.3	78.2	79.2	80.1	81.1	80.1	79.2	78.2	77.3	76.8
107.5°	78.9	79.4	80.3	81.3	82.2	83.2	82.2	81.3	80.3	79.4	78.9
110°	80.0	80.5	81.4	82.4	83.3	84.3	83.3	82.4	81.4	80.5	80.0

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	82.1	82.5	83.2	83.9	84.6	85.3	84.6	83.9	83.2	82.5	82.1
115°	164.3	155.8	138.7	121.6	104.6	87.5	104.6	121.6	138.7	155.8	164.3
117.5°	563.3	532.2	470.1	408.0	345.9	283.8	345.9	408.0	470.1	532.2	563.3
120°	794.8	778.8	746.8	714.8	682.8	650.8	682.8	714.8	746.8	778.8	794.8
122.5°	851.4	851.5	851.7	852.0	852.2	852.4	852.2	852.0	851.7	851.5	851.4
125°	909.0	909.4	910.1	910.8	911.5	912.2	911.5	910.8	910.1	909.4	909.0
127.5°	964.4	964.5	964.8	965.0	965.3	965.5	965.3	965.0	964.8	964.5	964.4
130°	1015.6	1015.5	1015.3	1015.0	1014.8	1014.6	1014.8	1015.0	1015.3	1015.5	1015.6
132.5°	1063.7	1063.6	1063.3	1063.1	1062.8	1062.6	1062.8	1063.1	1063.3	1063.6	1063.7
135°	1110.6	1110.4	1109.9	1109.4	1109.0	1108.5	1109.0	1109.4	1109.9	1110.4	1110.6
137.5°	1154.3	1153.9	1153.2	1152.5	1151.8	1151.1	1151.8	1152.5	1153.2	1153.9	1154.3
140°	1195.9	1195.3	1194.1	1193.0	1191.8	1190.6	1191.8	1193.0	1194.1	1195.3	1195.9
142.5°	1234.4	1233.8	1232.6	1231.4	1230.2	1229.0	1230.2	1231.4	1232.6	1233.8	1234.4
145°	1269.6	1269.0	1267.8	1266.6	1265.4	1264.2	1265.4	1266.6	1267.8	1269.0	1269.6
147.5°	1300.5	1300.0	1299.1	1298.1	1297.2	1296.2	1297.2	1298.1	1299.1	1300.0	1300.5
150°	1330.4	1329.8	1328.6	1327.4	1326.2	1325.0	1326.2	1327.4	1328.6	1329.8	1330.4
152.5°	1357.0	1356.2	1354.5	1352.9	1351.2	1349.6	1351.2	1352.9	1354.5	1356.2	1357.0
155°	1380.5	1379.6	1377.7	1375.8	1373.9	1372.0	1373.9	1375.8	1377.7	1379.6	1380.5
157.5°	1401.8	1400.9	1399.0	1397.1	1395.2	1393.3	1395.2	1397.1	1399.0	1400.9	1401.8
160°	1418.9	1418.1	1416.4	1414.7	1413.1	1411.4	1413.1	1414.7	1416.4	1418.1	1418.9
162.5°	1436.0	1434.9	1432.8	1430.7	1428.5	1426.4	1428.5	1430.7	1432.8	1434.9	1436.0
165°	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1443.0	1444.6	1446.3	1448.0	1448.8
167.5°	1460.5	1459.4	1457.3	1455.2	1453.0	1450.9	1453.0	1455.2	1457.3	1459.4	1460.5
170°	1469.1	1468.0	1465.9	1463.8	1461.6	1459.5	1461.6	1463.8	1465.9	1468.0	1469.1
172.5°	1475.5	1474.4	1472.3	1470.2	1468.0	1465.9	1468.0	1470.2	1472.3	1474.4	1475.5
175°	1479.7	1478.5	1476.2	1473.8	1471.5	1469.1	1471.5	1473.8	1476.2	1478.5	1479.7
177.5°	1480.8	1479.7	1477.6	1475.5	1473.3	1471.2	1473.3	1475.5	1477.6	1479.7	1480.8
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1635.8	1646.4	1642.4	1627.9	1645.1	1645.1	1657.0	1657.0	1671.6	1676.9	1684.8
5°	1543.1	1551.1	1557.7	1551.1	1563.0	1581.5	1592.1	1601.4	1621.3	1629.2	1641.1
7.5°	1443.8	1458.3	1465.0	1465.0	1484.8	1506.0	1527.2	1540.5	1568.3	1578.9	1590.8
10°	1347.1	1364.3	1377.5	1376.2	1409.3	1422.6	1449.1	1479.5	1507.3	1523.2	1540.5
12.5°	1245.1	1254.4	1272.9	1299.4	1307.3	1331.2	1361.6	1400.1	1450.4	1465.0	1490.1
15°	1160.3	1185.5	1200.0	1212.0	1230.5	1253.0	1286.1	1323.2	1373.6	1405.4	1431.8
17.5°	1088.8	1121.9	1131.2	1128.5	1152.4	1186.8	1225.2	1253.0	1298.1	1336.5	1361.6
20°	1030.5	1043.7	1059.6	1066.3	1084.8	1121.9	1159.0	1190.8	1227.9	1258.3	1287.5
22.5°	972.2	982.8	996.1	1008.0	1022.6	1043.7	1079.5	1119.2	1155.0	1184.2	1217.3
25°	924.5	931.2	943.1	952.4	968.2	982.8	1008.0	1051.7	1094.1	1111.3	1140.4
27.5°	878.2	883.5	891.4	902.0	910.0	924.5	947.1	982.8	1026.5	1043.7	1083.5
30°	837.1	841.1	849.0	854.3	858.3	875.5	892.7	920.6	953.7	977.5	1006.7
32.5°	798.7	802.7	810.6	812.0	817.2	826.5	842.4	867.6	896.7	916.6	941.8
35°	756.3	759.0	766.9	769.6	773.5	781.5	793.4	812.0	838.4	853.0	875.5
37.5°	723.2	721.9	727.2	731.2	736.5	740.4	744.4	762.9	782.8	796.1	813.3
40°	687.4	684.8	686.1	691.4	694.1	699.4	699.4	717.9	731.2	741.7	755.0
42.5°	651.7	650.4	647.7	650.4	653.0	654.3	655.7	668.9	682.1	691.4	706.0
45°	615.9	614.6	611.9	613.3	613.3	615.9	619.9	625.2	634.5	642.4	650.4
47.5°	582.8	580.2	576.2	574.9	577.5	577.5	577.5	582.8	592.1	594.7	602.7
50°	548.4	544.4	539.1	536.4	536.4	535.1	537.8	539.1	547.0	549.7	556.3
52.5°	511.3	508.6	503.3	498.0	499.4	496.7	498.0	499.4	502.0	506.0	510.0
55°	474.2	468.9	464.9	463.6	459.6	459.6	455.6	460.9	459.6	460.9	466.2
57.5°	438.4	433.1	426.5	423.9	419.9	418.6	415.9	414.6	415.9	419.9	423.9
60°	396.0	393.4	389.4	385.4	382.8	378.8	376.2	376.2	374.8	374.8	376.2
62.5°	355.0	353.7	348.4	347.0	344.4	341.7	337.8	335.1	335.1	337.8	339.1
65°	315.2	313.9	309.9	308.6	302.0	299.3	298.0	296.7	294.1	294.1	294.1
67.5°	278.2	274.2	274.2	267.6	262.3	259.6	257.0	255.6	255.6	255.6	257.0
70°	237.1	237.1	233.1	229.1	223.8	225.2	221.2	217.2	217.2	214.6	215.9
72.5°	197.4	196.0	192.1	190.7	186.8	182.8	180.1	182.8	178.8	177.5	178.8
75°	158.9	157.6	155.0	152.3	153.6	149.7	145.7	144.4	144.4	141.7	141.7
77.5°	121.9	124.5	119.2	117.9	115.2	112.6	111.3	109.9	109.9	109.9	112.6
80°	84.8	86.1	86.1	83.4	84.8	80.8	80.8	80.8	76.8	78.1	79.5
82.5°	54.3	54.3	53.0	54.3	53.0	53.0	51.7	51.7	50.3	50.3	51.7
85°	30.5	29.1	27.8	30.5	29.1	29.1	27.8	27.8	27.8	27.8	27.8
87.5°	6.6	7.9	7.9	7.9	7.9	9.3	9.3	9.3	10.6	10.6	10.6
90°	26.1	24.9	23.7	22.5	21.3	19.4	17.5	15.6	13.7	12.8	11.5
92.5°	27.5	27.0	26.5	26.1	25.6	24.9	24.2	23.5	22.8	22.4	22.9
95°	46.3	45.1	44.0	42.8	41.6	39.9	38.3	36.6	34.9	34.1	38.0
97.5°	57.2	56.5	55.8	55.1	54.4	50.6	46.8	43.0	39.2	37.3	47.0
100°	68.4	66.5	64.6	62.7	60.8	56.8	52.8	48.7	44.7	42.7	58.9
102.5°	73.4	70.8	68.1	65.5	62.9	106.1	149.2	192.4	235.5	257.1	257.3
105°	75.5	72.9	70.3	67.7	65.1	129.8	194.5	259.2	323.9	356.3	352.7
107.5°	77.6	75.0	72.4	69.8	67.2	147.1	227.0	306.9	386.8	426.7	423.7
110°	91.9	115.6	139.3	163.0	186.7	255.2	323.7	392.2	460.7	495.0	492.5

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	133.2	235.4	337.6	439.8	542.0	546.0	550.0	554.1	558.1	560.1	558.0
115°	219.2	328.9	438.7	548.4	658.2	652.3	646.4	640.5	634.6	631.6	629.6
117.5°	580.3	614.2	648.1	682.0	715.9	711.9	707.8	703.8	699.7	697.7	695.3
120°	793.4	790.5	787.7	784.8	782.0	777.7	773.5	769.2	764.9	762.8	761.0
122.5°	850.7	849.2	847.8	846.3	844.9	840.2	835.4	830.7	826.0	823.6	821.7
125°	908.2	906.5	904.8	903.2	901.5	897.0	892.5	888.0	883.5	881.2	879.7
127.5°	963.2	960.9	958.5	956.2	953.8	950.2	946.7	943.1	939.6	937.8	936.1
130°	1014.3	1011.7	1009.1	1006.5	1003.9	1001.3	998.7	996.1	993.5	992.2	990.3
132.5°	1062.6	1060.5	1058.4	1056.2	1054.1	1051.5	1048.9	1046.2	1043.6	1042.3	1040.8
135°	1109.4	1107.0	1104.7	1102.3	1099.9	1097.8	1095.6	1093.5	1091.4	1090.3	1088.4
137.5°	1153.1	1150.8	1148.4	1146.1	1143.7	1141.3	1138.9	1136.6	1134.2	1133.0	1131.6
140°	1194.8	1192.7	1190.6	1188.4	1186.3	1183.7	1181.1	1178.5	1175.9	1174.6	1173.7
142.5°	1233.4	1231.5	1229.6	1227.7	1225.8	1222.7	1219.6	1216.5	1213.4	1211.9	1211.1
145°	1268.8	1267.1	1265.4	1263.8	1262.1	1258.1	1254.1	1250.0	1246.0	1244.0	1244.1
147.5°	1299.9	1298.7	1297.6	1296.4	1295.2	1291.2	1287.1	1283.1	1279.0	1277.0	1277.4
150°	1329.7	1328.3	1326.8	1325.4	1324.0	1320.2	1316.4	1312.6	1308.8	1306.9	1307.7
152.5°	1356.3	1354.9	1353.4	1352.0	1350.6	1347.0	1343.5	1339.9	1336.4	1334.6	1335.6
155°	1379.8	1378.4	1376.9	1375.5	1374.1	1371.3	1368.4	1365.6	1362.7	1361.3	1362.4
157.5°	1401.0	1399.3	1397.7	1396.0	1394.4	1392.3	1390.1	1388.0	1385.9	1384.8	1385.7
160°	1418.2	1416.8	1415.3	1413.9	1412.5	1411.1	1409.7	1408.2	1406.8	1406.1	1406.8
162.5°	1435.2	1433.5	1431.8	1430.2	1428.5	1427.3	1426.1	1425.0	1423.8	1423.2	1423.9
165°	1448.0	1446.3	1444.6	1443.0	1441.3	1440.6	1439.9	1439.2	1438.5	1438.1	1438.8
167.5°	1459.7	1458.0	1456.4	1454.7	1453.1	1452.4	1451.7	1451.0	1450.3	1449.9	1450.6
170°	1468.3	1466.6	1464.9	1463.3	1461.6	1461.1	1460.7	1460.2	1459.7	1459.5	1460.2
172.5°	1474.7	1473.0	1471.3	1469.7	1468.0	1467.5	1467.1	1466.6	1466.1	1465.9	1466.6
175°	1478.9	1477.2	1475.6	1473.9	1472.3	1471.8	1471.3	1470.8	1470.3	1470.1	1470.9
177.5°	1480.0	1478.3	1476.6	1475.0	1473.3	1473.1	1472.9	1472.6	1472.4	1472.3	1473.1
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1723.2	1723.2	1723.2	1723.2
2.5°	1691.5	1691.5	1711.3	1732.5
5°	1654.4	1663.6	1695.4	1724.6
7.5°	1618.6	1634.5	1674.2	1711.3
10°	1574.9	1596.1	1645.1	1688.8
12.5°	1532.5	1552.4	1609.3	1658.3
15°	1472.9	1498.1	1559.0	1619.9
17.5°	1413.3	1438.5	1512.6	1584.2
20°	1343.1	1376.2	1459.7	1555.0
22.5°	1278.2	1319.3	1412.0	1488.8
25°	1206.7	1270.2	1356.3	1455.7
27.5°	1143.1	1206.7	1294.1	1394.8
30°	1071.6	1136.5	1226.5	1319.3
32.5°	1002.7	1062.3	1149.7	1263.6
35°	931.2	988.1	1072.9	1188.1
37.5°	866.3	921.9	1014.6	1120.6
40°	802.7	861.0	940.4	1046.4
42.5°	743.1	794.7	866.3	972.2
45°	688.8	725.9	792.1	891.4
47.5°	631.8	664.9	725.9	825.2
50°	578.8	606.6	659.6	752.3
52.5°	527.2	551.0	600.0	674.2
55°	480.8	503.3	539.1	611.9
57.5°	433.1	450.3	484.8	543.1
60°	386.8	402.7	430.5	478.2
62.5°	340.4	353.7	380.1	418.6
65°	299.3	309.9	329.8	362.9
67.5°	259.6	266.2	282.1	308.6
70°	221.2	226.5	239.7	260.9
72.5°	180.1	185.4	200.0	214.6
75°	145.7	147.0	157.6	169.5
77.5°	113.9	112.6	120.5	129.8
80°	78.1	82.1	88.7	92.7
82.5°	53.0	54.3	57.0	59.6
85°	29.1	30.5	30.5	34.4
87.5°	11.9	13.2	13.2	14.6
90°	8.9	6.3	3.7	1.1
92.5°	23.8	24.8	25.7	26.7
95°	45.8	53.7	61.5	69.3
97.5°	66.5	85.9	105.4	124.8
100°	91.4	123.9	156.3	188.8
102.5°	257.8	258.3	258.7	259.2
105°	345.6	338.5	331.4	324.3
107.5°	417.8	411.9	406.0	400.1
110°	487.5	482.6	477.6	472.6



TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	553.7	549.4	545.2	540.9
115°	625.5	621.5	617.4	613.4
117.5°	690.6	685.9	681.1	676.4
120°	757.5	753.9	750.4	746.8
122.5°	817.9	814.1	810.3	806.5
125°	876.6	873.5	870.5	867.4
127.5°	932.8	929.5	926.1	922.8
130°	986.5	982.7	978.9	975.1
132.5°	1037.7	1034.6	1031.5	1028.4
135°	1084.6	1080.9	1077.1	1073.3
137.5°	1128.7	1125.9	1123.0	1120.2
140°	1171.8	1169.9	1168.0	1166.1
142.5°	1209.4	1207.8	1206.1	1204.5
145°	1244.3	1244.6	1244.8	1245.0
147.5°	1278.1	1278.8	1279.5	1280.2
150°	1309.4	1311.1	1312.7	1314.4
152.5°	1337.5	1339.4	1341.3	1343.2
155°	1364.5	1366.6	1368.8	1370.9
157.5°	1387.6	1389.5	1391.4	1393.3
160°	1408.2	1409.7	1411.1	1412.5
162.5°	1425.3	1426.8	1428.2	1429.6
165°	1440.2	1441.7	1443.1	1444.5
167.5°	1452.0	1453.5	1454.9	1456.3
170°	1461.6	1463.1	1464.5	1465.9
172.5°	1468.0	1469.5	1470.9	1472.3
175°	1472.6	1474.3	1475.9	1477.6
177.5°	1474.8	1476.4	1478.1	1479.7
180°	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P999005

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.02	17.83	18.02	18.83	20.14	14.52	15.32	15.51	16.32	17.64
	3H	17.83	18.55	18.83	19.56	20.90	15.86	16.58	16.86	17.58	18.92
	4H	18.00	18.68	19.01	19.69	21.04	16.32	17.00	17.33	18.01	19.36
	6H	18.04	18.67	19.07	19.68	21.04	16.62	17.25	17.65	18.26	19.62
	8H	18.02	18.61	19.05	19.64	21.00	16.70	17.30	17.74	18.33	19.69
	12H	17.98	18.54	19.01	19.57	20.95	16.75	17.31	17.78	18.34	19.71
4H	2H	17.06	17.74	18.08	18.75	20.10	14.96	15.64	15.98	16.65	17.99
	3H	18.03	18.60	19.06	19.64	21.00	16.41	16.98	17.44	18.02	19.38
	4H	18.31	18.83	19.35	19.86	21.24	16.95	17.46	17.98	18.49	19.88
	6H	18.44	18.88	19.48	19.93	21.31	17.32	17.76	18.37	18.82	20.20
	8H	18.43	18.85	19.48	19.89	21.29	17.43	17.85	18.48	18.89	20.29
	12H	18.40	18.77	19.46	19.83	21.23	17.49	17.86	18.55	18.92	20.32
8H	4H	18.31	18.73	19.36	19.78	21.17	17.08	17.50	18.13	18.54	19.94
	6H	18.49	18.83	19.56	19.92	21.31	17.52	17.86	18.59	18.95	20.34
	8H	18.52	18.82	19.60	19.89	21.31	17.67	17.97	18.74	19.04	20.45
	12H	18.50	18.77	19.58	19.83	21.29	17.76	18.02	18.84	19.09	20.54
12H	4H	18.27	18.64	19.33	19.70	21.10	17.05	17.43	18.12	18.49	19.89
	6H	18.47	18.77	19.55	19.84	21.25	17.52	17.82	18.59	18.89	20.30
	8H	18.50	18.76	19.58	19.83	21.28	17.67	17.93	18.75	19.00	20.46