

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999022

Luminaire Tested: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999022
REPORT IS A COMBINATION OF REPORTS P984771 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7686.0 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	43	41	40
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	31	29	26
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	19	17
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26115	26115	26115	26115
5°	26178	27845	26278	22153
10°	25874	30397	26037	18265
15°	25247	32063	25598	15385
20°	24853	30104	24853	13372
25°	24061	25863	24170	11959
30°	22757	20330	23191	10831
35°	21603	14059	21964	9910
40°	20276	10614	20506	9175
45°	18638	8722	18944	8382
50°	17225	7655	17256	7674
55°	15612	6524	15713	6904
60°	13892	5449	14083	6025
65°	12353	4432	12577	5146
70°	10818	3478	11095	4150
75°	9079	2525	9437	3009
80°	7090	1600	7593	1787
85°	4661	804	5015	597

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 26997 cd/sqm

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.1	2.0
10°-20°	457.4	6.0
20°-30°	663.8	8.6
30°-40°	699.8	9.1
40°-50°	619.2	8.1
50°-60°	494.4	6.4
60°-70°	335.8	4.4
70°-80°	171.8	2.2
80°-90°	44.3	0.6
90°-100°	226.3	2.9
100°-110°	796.9	10.4
110°-120°	836.9	10.9
120°-130°	688.5	9.0
130°-140°	553.1	7.2
140°-150°	417.8	5.4
150°-160°	293.7	3.8
160°-170°	172.9	2.2
170°-180°	56.2	0.7
0°-30°	1278.3	16.6
0°-40°	1978.1	25.7
0°-60°	3091.7	40.2
0°-90°	3643.7	47.4
90°-120°	1860.0	24.2
90°-150°	3519.4	45.8
90°-180°	4042.0	52.6
0°-180°	7686.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1650	1650	1650	1650	1650	
5°	1651	1843	1657	1466	1651	157
15°	1551	2265	1572	1087	1551	438
25°	1394	1887	1400	872	1394	637
35°	1138	1027	1156	724	1138	712
45°	853	619	867	595	853	662
55°	586	435	590	460	586	523
65°	348	268	354	311	348	345
75°	162	132	169	157	162	174
85°	33	34	36	25	33	38
90°	1	37	1	37	1	4
95°	39	127	39	127	39	40
105°	136	1258	136	1258	136	145
115°	240	1655	240	1655	240	238
125°	335	1343	335	1343	335	298
135°	393	1113	393	1113	393	304
145°	449	888	449	888	449	282
155°	510	747	510	747	510	235
165°	556	655	556	655	556	157
175°	579	590	579	590	579	55
180°	580	580	580	580	580	

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1658.7	1662.5	1668.8	1670.1	1682.8	1692.9	1704.3	1704.3	1708.2	1706.9	1696.7
5°	1651.1	1662.5	1679.0	1692.9	1715.8	1725.9	1741.1	1752.5	1762.7	1770.3	1769.0
7.5°	1638.4	1658.7	1682.8	1709.4	1739.9	1757.6	1779.2	1799.5	1813.4	1826.1	1835.0
10°	1616.8	1651.1	1684.1	1719.6	1758.9	1783.0	1808.3	1835.0	1856.5	1880.6	1903.4
12.5°	1587.7	1637.1	1677.7	1724.6	1772.8	1799.5	1840.0	1860.3	1902.2	1963.0	1979.5
15°	1550.9	1618.1	1656.2	1715.8	1779.2	1800.7	1856.5	1889.5	1975.7	2013.8	2059.4
17.5°	1516.7	1591.5	1642.2	1710.7	1772.8	1814.7	1869.2	1936.4	2008.7	2063.2	2113.9
20°	1488.8	1561.0	1621.9	1698.0	1776.6	1829.9	1887.0	1968.1	2046.7	2102.5	2141.8
22.5°	1425.4	1517.9	1588.9	1673.9	1769.0	1842.6	1897.1	1985.9	2070.8	2105.1	2139.3
25°	1393.7	1473.5	1556.0	1652.4	1763.9	1851.4	1898.4	1997.3	2072.1	2084.8	2092.4
27.5°	1335.3	1425.4	1521.7	1632.1	1762.7	1836.2	1895.8	1985.9	2045.5	2036.6	2013.8
30°	1263.0	1373.4	1479.9	1599.1	1744.9	1824.8	1880.6	1963.0	1993.5	1947.8	1907.2
32.5°	1209.8	1313.8	1431.7	1569.9	1724.6	1800.7	1855.3	1919.9	1926.3	1843.8	1775.4
35°	1137.5	1252.9	1386.0	1531.9	1690.4	1758.9	1809.6	1848.9	1818.5	1703.1	1621.9
37.5°	1072.8	1187.0	1329.0	1477.4	1643.5	1710.7	1751.3	1757.6	1682.8	1581.3	1462.1
40°	1001.8	1119.7	1268.1	1424.1	1591.5	1649.8	1675.2	1656.2	1548.4	1430.4	1292.2
42.5°	930.8	1047.5	1207.2	1367.0	1525.5	1575.0	1585.1	1533.2	1401.3	1263.0	1103.3
45°	853.4	975.2	1135.0	1296.0	1449.5	1477.4	1478.6	1403.8	1247.8	1103.3	954.9
47.5°	790.0	902.9	1061.4	1222.5	1351.8	1370.8	1363.2	1277.0	1107.1	944.7	815.4
50°	720.3	828.1	985.3	1143.8	1254.2	1259.2	1240.2	1117.2	951.1	802.7	700.0
52.5°	645.5	754.5	899.1	1051.3	1150.2	1142.6	1105.8	973.9	817.9	694.9	616.3
55°	585.9	682.2	817.9	966.3	1036.0	1014.5	973.9	839.5	716.5	612.5	544.0
57.5°	519.9	604.9	738.0	867.4	908.0	887.7	847.1	721.6	607.4	528.8	483.2
60°	457.8	535.1	651.8	759.6	791.3	769.7	722.8	610.0	527.5	461.6	427.4
62.5°	400.7	467.9	565.6	664.5	677.2	655.6	615.0	523.7	452.7	400.7	375.4
65°	347.5	410.9	489.5	564.3	575.7	552.9	511.1	445.1	385.5	352.5	328.4
67.5°	295.5	346.2	415.9	470.5	476.8	455.3	421.0	367.8	331.0	295.5	277.7
70°	249.8	287.9	342.4	386.8	389.3	369.0	351.3	303.1	275.2	249.8	235.9
72.5°	205.4	232.1	273.9	306.9	308.2	295.5	279.0	248.6	224.5	206.7	192.8
75°	162.3	185.1	210.5	239.7	238.4	228.3	215.6	196.6	176.3	164.9	158.5
77.5°	124.3	138.2	158.5	177.5	177.5	172.5	164.9	150.9	138.2	126.8	120.5
80°	88.8	97.6	114.1	120.5	123.0	121.7	115.4	105.3	100.2	91.3	88.8
82.5°	57.1	63.4	71.0	77.4	81.2	78.6	77.4	72.3	64.7	62.1	59.6
85°	33.0	35.5	39.3	43.1	44.4	43.1	45.7	41.8	38.0	38.0	36.8
87.5°	13.9	15.2	17.8	17.8	19.0	19.0	17.8	19.0	19.0	17.8	16.5
90°	1.1	4.5	8.9	11.2	13.4	15.0	16.7	22.3	30.1	36.8	38.0
92.5°	16.7	23.4	32.4	38.0	46.9	53.0	59.2	89.3	131.7	169.7	171.9
95°	39.1	43.5	54.7	64.7	82.6	96.0	109.4	160.7	257.9	387.3	437.6
97.5°	58.0	64.7	77.0	91.5	111.6	126.7	141.8	207.6	342.7	551.4	713.3
100°	86.0	89.3	99.3	117.2	139.5	155.2	170.8	229.9	366.1	607.2	881.8
102.5°	111.6	113.9	123.9	141.8	165.2	180.8	196.5	250.0	367.2	586.0	887.4
105°	136.2	140.6	148.5	165.2	189.8	205.4	221.0	273.5	372.8	557.0	827.1
107.5°	163.0	166.3	174.1	189.8	214.3	230.0	245.6	296.9	385.1	541.4	771.3
110°	189.8	194.2	200.9	215.4	238.9	255.0	271.2	320.4	400.7	536.9	733.4

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	214.3	218.8	226.6	240.0	262.3	279.0	295.8	342.7	417.5	538.0	708.8
115°	240.0	245.6	252.3	265.7	288.0	303.0	318.1	366.1	434.2	542.5	692.1
117.5°	266.8	271.2	277.9	290.2	311.4	327.0	342.7	387.3	452.1	549.2	683.1
120°	291.3	295.8	302.5	312.6	334.9	350.5	366.1	409.7	469.9	555.9	675.3
122.5°	314.8	318.1	324.8	336.0	358.3	374.5	390.7	430.9	485.6	563.7	670.9
125°	334.9	338.2	344.9	358.3	380.6	396.2	411.9	452.1	502.3	571.5	665.3
127.5°	351.6	356.1	365.0	379.5	400.7	416.9	433.1	472.2	517.9	579.3	661.9
130°	366.1	370.6	381.8	397.4	419.7	435.4	451.0	490.0	532.5	588.3	659.7
132.5°	379.5	385.1	397.4	414.1	437.6	453.2	468.8	505.7	547.0	597.2	658.6
135°	392.9	397.4	410.8	427.5	453.2	468.8	484.5	520.2	559.2	603.9	657.5
137.5°	405.2	410.8	424.2	442.0	467.7	482.2	496.7	532.5	569.3	610.6	657.5
140°	419.7	424.2	437.6	455.4	480.0	494.5	509.0	542.5	577.1	615.1	656.4
142.5°	434.2	437.6	449.8	467.7	491.2	504.6	517.9	550.3	583.8	618.4	656.4
145°	448.7	453.2	464.4	481.1	503.4	515.7	528.0	558.1	589.4	620.6	654.1
147.5°	464.4	467.7	478.9	494.5	513.5	524.6	535.8	564.8	592.7	621.8	650.8
150°	480.0	483.3	492.3	506.8	523.5	533.6	543.6	569.3	595.0	620.6	647.4
152.5°	495.6	496.7	505.7	517.9	533.6	542.5	551.4	573.8	596.1	618.4	641.8
155°	510.1	511.2	517.9	530.2	542.5	550.8	559.2	578.2	597.2	616.2	635.1
157.5°	522.4	523.5	529.1	540.3	550.3	557.6	564.8	581.6	597.2	611.7	628.4
160°	534.7	535.8	540.3	549.2	558.1	564.2	570.4	583.8	597.2	608.4	621.8
162.5°	547.0	545.8	550.3	557.0	564.8	569.3	573.8	584.9	596.1	605.0	616.2
165°	555.9	554.8	557.0	563.7	569.3	572.6	576.0	586.0	593.8	600.5	608.4
167.5°	563.7	562.6	564.8	569.3	573.8	576.0	578.2	586.0	592.7	596.1	601.7
170°	571.5	569.3	570.4	573.8	576.0	577.6	579.3	584.9	590.5	592.7	596.1
172.5°	576.0	574.9	573.8	577.1	578.2	579.4	580.5	583.8	587.1	588.3	589.4
175°	579.3	578.2	577.1	579.3	579.3	579.9	580.5	582.7	584.9	583.8	584.9
177.5°	581.6	579.3	578.2	580.5	580.5	580.5	580.5	581.6	583.8	581.6	580.5
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1714.5	1715.8	1718.3	1731.0	1737.3	1738.6	1733.5	1744.9	1748.7	1744.9	1742.4
5°	1795.7	1803.3	1818.5	1835.0	1833.7	1835.0	1842.6	1850.2	1852.7	1842.6	1846.4
7.5°	1866.7	1881.9	1898.4	1923.7	1923.7	1936.4	1941.5	1947.8	1963.0	1955.4	1952.9
10°	1947.8	1968.1	1998.5	2039.1	2040.4	2053.1	2065.8	2086.0	2092.4	2087.3	2089.9
12.5°	2049.3	2088.6	2091.1	2135.5	2155.8	2158.3	2178.6	2174.8	2187.5	2187.5	2209.1
15°	2093.7	2154.5	2188.8	2231.9	2244.6	2229.3	2245.8	2263.6	2264.9	2264.9	2263.6
17.5°	2173.5	2197.6	2231.9	2254.7	2259.8	2259.8	2261.0	2268.7	2263.6	2253.4	2261.0
20°	2190.0	2200.2	2212.9	2210.3	2212.9	2200.2	2187.5	2174.8	2176.1	2169.7	2188.8
22.5°	2159.6	2157.1	2127.9	2108.9	2108.9	2083.5	2059.4	2048.0	2036.6	2040.4	2046.7
25°	2083.5	2044.2	2008.7	1980.8	1974.5	1933.9	1900.9	1890.8	1871.7	1887.0	1889.5
27.5°	1961.8	1917.4	1860.3	1836.2	1803.3	1786.8	1763.9	1733.5	1694.2	1717.0	1713.2
30°	1831.2	1765.2	1718.3	1660.0	1608.0	1604.2	1561.0	1510.3	1490.0	1490.0	1501.4
32.5°	1685.3	1597.8	1529.3	1446.9	1396.2	1374.6	1322.6	1271.9	1283.3	1245.3	1259.2
35°	1515.4	1400.0	1313.8	1233.9	1195.8	1170.5	1103.3	1075.4	1044.9	1027.2	1060.1
37.5°	1353.1	1219.9	1109.6	1022.1	1008.2	962.5	916.8	899.1	881.3	888.9	887.7
40°	1155.3	1037.3	938.4	869.9	845.8	824.3	793.8	772.3	760.9	767.2	768.5
42.5°	976.4	877.5	804.0	755.8	735.5	720.3	705.1	687.3	683.5	683.5	688.6
45°	838.2	757.1	707.6	668.3	656.9	645.5	634.1	626.4	623.9	618.8	622.6
47.5°	727.9	663.2	632.8	603.6	590.9	588.4	578.3	574.5	569.4	568.1	569.4
50°	635.3	594.7	566.8	550.4	541.5	537.7	532.6	525.0	522.5	528.8	526.3
52.5°	570.7	532.6	517.4	500.9	495.8	490.8	483.2	484.4	483.2	480.6	480.6
55°	506.0	481.9	466.7	454.0	452.7	447.6	441.3	438.8	437.5	435.0	438.8
57.5°	454.0	435.0	421.0	409.6	404.5	404.5	398.2	393.1	393.1	391.8	393.1
60°	402.0	383.0	374.1	362.7	358.9	357.6	353.8	351.3	347.5	347.5	347.5
62.5°	353.8	338.6	328.4	318.3	319.6	313.2	308.2	305.6	305.6	306.9	306.9
65°	308.2	298.0	285.3	276.4	273.9	272.6	270.1	268.8	265.0	267.6	267.6
67.5°	266.3	252.4	244.7	240.9	237.1	235.9	233.3	230.8	229.5	228.3	230.8
70°	224.5	213.0	206.7	204.2	200.4	199.1	197.8	194.0	195.3	196.6	197.8
72.5°	186.4	176.3	175.0	167.4	167.4	167.4	162.3	164.9	163.6	161.1	163.6
75°	147.1	142.0	139.5	135.7	137.0	135.7	134.4	130.6	130.6	131.9	133.2
77.5°	116.7	111.6	110.3	106.5	104.0	106.5	104.0	102.7	102.7	104.0	104.0
80°	86.2	83.7	79.9	79.9	79.9	78.6	78.6	78.6	77.4	76.1	77.4
82.5°	57.1	57.1	55.8	54.5	55.8	53.3	54.5	54.5	54.5	54.5	54.5
85°	36.8	35.5	35.5	34.2	34.2	34.2	35.5	33.0	33.0	34.2	34.2
87.5°	16.5	16.5	16.5	17.8	16.5	16.5	16.5	17.8	16.5	16.5	16.5
90°	36.8	35.7	33.5	35.7	36.2	36.8	36.8	36.8	36.8	36.8	36.8
92.5°	144.0	112.7	96.0	83.7	79.2	74.8	73.7	69.2	70.3	68.1	70.3
95°	382.9	292.5	224.4	177.5	165.2	152.9	138.4	129.5	126.1	127.3	126.1
97.5°	718.9	598.3	477.8	365.0	331.5	298.0	254.5	232.2	219.9	213.2	219.9
100°	1042.6	1019.1	880.7	727.8	660.2	592.7	500.1	452.1	419.7	399.6	419.7
102.5°	1163.1	1294.9	1290.4	1188.8	1116.2	1043.7	941.0	850.6	808.2	779.1	808.2
105°	1124.1	1356.2	1482.4	1496.9	1478.5	1460.1	1390.8	1321.6	1273.6	1258.0	1273.6
107.5°	1041.5	1290.4	1477.9	1587.3	1609.6	1632.0	1630.8	1620.8	1606.3	1580.6	1606.3
110°	964.4	1200.0	1399.8	1542.7	1588.4	1634.2	1682.2	1703.4	1713.4	1712.3	1713.4

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	910.9	1117.4	1307.1	1462.3	1516.4	1570.6	1642.0	1681.1	1702.3	1710.1	1702.3
115°	868.4	1052.6	1224.5	1370.8	1428.2	1485.7	1565.0	1616.3	1645.4	1655.4	1645.4
117.5°	839.4	999.0	1153.1	1289.3	1344.0	1398.7	1480.1	1534.8	1565.0	1572.8	1565.0
120°	817.1	961.1	1099.5	1217.8	1268.6	1319.4	1397.5	1450.0	1482.4	1493.5	1482.4
122.5°	798.1	931.0	1054.9	1165.4	1210.1	1254.7	1322.8	1374.1	1402.0	1410.9	1402.0
125°	780.3	901.9	1016.9	1115.1	1157.0	1198.9	1263.6	1306.0	1333.9	1342.8	1333.9
127.5°	763.5	872.9	979.0	1072.7	1111.8	1150.9	1207.8	1248.0	1272.5	1279.2	1272.5
130°	746.8	845.0	941.0	1029.2	1066.1	1102.9	1157.6	1195.5	1217.8	1226.8	1217.8
132.5°	733.4	818.2	905.3	984.5	1018.6	1052.6	1106.2	1144.2	1164.2	1172.1	1164.2
135°	721.1	793.7	867.3	941.0	972.2	1003.5	1051.5	1088.3	1108.4	1112.9	1108.4
137.5°	712.2	773.6	837.2	897.5	925.4	953.3	999.0	1031.4	1049.3	1056.0	1049.3
140°	704.4	754.6	808.2	859.5	884.0	908.6	944.3	973.4	990.1	996.8	990.1
142.5°	696.5	739.0	782.5	824.9	844.4	864.0	897.5	923.1	937.7	937.7	937.7
145°	689.8	724.4	761.3	795.9	812.1	828.3	855.0	874.0	885.2	888.5	885.2
147.5°	683.1	713.3	743.4	771.3	783.6	795.9	819.3	835.0	842.8	845.0	842.8
150°	674.2	701.0	725.6	749.0	759.0	769.1	785.8	799.2	805.9	807.0	805.9
152.5°	666.4	688.7	711.1	730.0	738.4	746.8	759.1	770.2	774.7	774.7	774.7
155°	656.4	677.6	695.4	712.2	718.3	724.4	736.7	744.5	749.0	746.8	749.0
157.5°	647.4	664.2	679.8	694.3	699.3	704.4	713.3	720.0	722.2	722.2	722.2
160°	637.4	651.9	664.2	676.4	680.3	684.3	692.1	697.7	698.8	698.8	698.8
162.5°	628.4	639.6	649.7	659.7	662.5	665.3	673.1	676.4	677.6	676.4	677.6
165°	618.4	627.3	635.1	643.0	645.2	647.4	651.9	656.4	656.4	655.2	656.4
167.5°	608.4	615.1	621.8	627.3	629.6	631.8	634.0	636.3	636.3	635.1	636.3
170°	600.5	606.1	609.5	613.9	615.0	616.2	617.3	620.6	619.5	617.3	619.5
172.5°	592.7	596.1	598.3	601.7	602.2	602.8	603.9	605.0	603.9	602.8	603.9
175°	586.0	589.4	590.5	591.6	592.2	592.7	592.7	593.8	592.7	590.5	592.7
177.5°	581.6	583.8	583.8	584.9	584.9	584.9	584.9	584.9	583.8	581.6	583.8
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1748.7	1739.9	1732.2	1733.5	1739.9	1734.8	1722.1	1705.6	1699.3	1691.7	1699.3
5°	1854.0	1846.4	1831.2	1832.4	1828.6	1823.5	1803.3	1777.9	1777.9	1757.6	1755.1
7.5°	1958.0	1946.6	1936.4	1933.9	1919.9	1909.8	1892.0	1856.5	1842.6	1818.5	1804.5
10°	2074.6	2065.8	2054.3	2040.4	2032.8	2015.0	1985.9	1933.9	1908.5	1875.5	1851.4
12.5°	2192.6	2191.3	2165.9	2138.0	2136.8	2108.9	2088.6	2018.8	1984.6	1940.2	1883.2
15°	2267.4	2261.0	2247.1	2233.2	2237.0	2206.5	2160.9	2078.4	2055.6	2002.4	1941.5
17.5°	2266.1	2266.1	2262.3	2259.8	2256.0	2247.1	2221.7	2167.2	2130.4	2063.2	2006.2
20°	2193.8	2210.3	2214.1	2212.9	2225.5	2231.9	2230.6	2196.4	2167.2	2107.6	2049.3
22.5°	2049.3	2087.3	2103.8	2113.9	2140.6	2154.5	2187.5	2174.8	2167.2	2122.8	2073.4
25°	1914.9	1927.5	1977.0	1979.5	2016.3	2050.5	2083.5	2105.1	2133.0	2116.5	2074.6
27.5°	1741.1	1770.3	1805.8	1832.4	1840.0	1909.8	1964.3	2004.9	2068.3	2073.4	2059.4
30°	1544.6	1558.5	1616.8	1652.4	1692.9	1743.7	1822.3	1892.0	1949.1	2001.1	2018.8
32.5°	1304.9	1362.0	1396.2	1439.3	1474.8	1564.9	1661.2	1751.3	1817.2	1904.7	1942.8
35°	1085.5	1129.9	1188.2	1206.0	1270.7	1346.7	1472.3	1587.7	1687.9	1776.6	1854.0
37.5°	904.2	939.7	1001.8	1029.7	1067.8	1165.4	1270.7	1413.9	1534.4	1643.5	1739.9
40°	779.9	806.5	853.4	862.3	894.0	982.8	1067.8	1202.2	1362.0	1509.1	1614.3
42.5°	694.9	707.6	739.3	750.7	771.0	830.6	906.7	1033.5	1181.9	1334.1	1482.4
45°	634.1	642.9	662.0	672.1	697.5	724.1	786.2	887.7	1004.3	1157.8	1317.6
47.5°	579.5	590.9	598.6	604.9	618.8	648.0	688.6	763.4	875.0	1015.8	1170.5
50°	533.9	537.7	551.6	552.9	561.8	580.8	618.8	664.5	753.3	867.4	1017.0
52.5°	488.2	492.0	500.9	509.8	513.6	528.8	554.2	592.2	658.2	748.2	881.3
55°	442.6	447.6	456.5	462.9	466.7	479.3	494.6	531.3	583.3	646.7	755.8
57.5°	396.9	408.3	410.9	414.7	421.0	435.0	448.9	470.5	511.1	569.4	649.3
60°	353.8	357.6	366.5	370.3	376.6	384.2	402.0	418.5	447.6	493.3	565.6
62.5°	309.4	318.3	322.1	325.9	331.0	339.9	351.3	369.0	394.4	431.2	488.2
65°	271.4	272.6	280.3	285.3	290.4	296.7	308.2	324.6	339.9	374.1	415.9
67.5°	234.6	237.1	239.7	244.7	251.1	257.4	267.6	276.4	295.5	318.3	351.3
70°	199.1	199.1	205.4	209.2	208.0	215.6	223.2	233.3	247.3	268.8	295.5
72.5°	167.4	166.1	171.2	172.5	175.0	180.1	185.1	195.3	202.9	219.4	239.7
75°	133.2	135.7	138.2	138.2	142.0	145.8	150.9	156.0	164.9	175.0	190.2
77.5°	105.3	105.3	107.8	109.1	112.9	111.6	116.7	121.7	128.1	137.0	148.4
80°	77.4	79.9	79.9	79.9	81.2	82.4	87.5	91.3	95.1	101.4	106.5
82.5°	54.5	54.5	57.1	57.1	57.1	59.6	59.6	60.9	63.4	67.2	71.0
85°	34.2	34.2	34.2	35.5	34.2	35.5	38.0	36.8	38.0	40.6	40.6
87.5°	16.5	16.5	16.5	16.5	16.5	17.8	16.5	17.8	19.0	19.0	19.0
90°	36.8	36.8	36.8	36.2	35.7	33.5	35.7	36.8	38.0	36.8	30.1
92.5°	69.2	73.7	74.8	79.2	83.7	96.0	112.7	144.0	171.9	169.7	131.7
95°	129.5	138.4	152.9	165.2	177.5	224.4	292.5	382.9	437.6	387.3	257.9
97.5°	232.2	254.5	298.0	331.5	365.0	477.8	598.3	718.9	713.3	551.4	342.7
100°	452.1	500.1	592.7	660.2	727.8	880.7	1019.1	1042.6	881.8	607.2	366.1
102.5°	850.6	941.0	1043.7	1116.2	1188.8	1290.4	1294.9	1163.1	887.4	586.0	367.2
105°	1321.6	1390.8	1460.1	1478.5	1496.9	1482.4	1356.2	1124.1	827.1	557.0	372.8
107.5°	1620.8	1630.8	1632.0	1609.6	1587.3	1477.9	1290.4	1041.5	771.3	541.4	385.1
110°	1703.4	1682.2	1634.2	1588.4	1542.7	1399.8	1200.0	964.4	733.4	536.9	400.7

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1681.1	1642.0	1570.6	1516.4	1462.3	1307.1	1117.4	910.9	708.8	538.0	417.5
115°	1616.3	1565.0	1485.7	1428.2	1370.8	1224.5	1052.6	868.4	692.1	542.5	434.2
117.5°	1534.8	1480.1	1398.7	1344.0	1289.3	1153.1	999.0	839.4	683.1	549.2	452.1
120°	1450.0	1397.5	1319.4	1268.6	1217.8	1099.5	961.1	817.1	675.3	555.9	469.9
122.5°	1374.1	1322.8	1254.7	1210.1	1165.4	1054.9	931.0	798.1	670.9	563.7	485.6
125°	1306.0	1263.6	1198.9	1157.0	1115.1	1016.9	901.9	780.3	665.3	571.5	502.3
127.5°	1248.0	1207.8	1150.9	1111.8	1072.7	979.0	872.9	763.5	661.9	579.3	517.9
130°	1195.5	1157.6	1102.9	1066.1	1029.2	941.0	845.0	746.8	659.7	588.3	532.5
132.5°	1144.2	1106.2	1052.6	1018.6	984.5	905.3	818.2	733.4	658.6	597.2	547.0
135°	1088.3	1051.5	1003.5	972.2	941.0	867.3	793.7	721.1	657.5	603.9	559.2
137.5°	1031.4	999.0	953.3	925.4	897.5	837.2	773.6	712.2	657.5	610.6	569.3
140°	973.4	944.3	908.6	884.0	859.5	808.2	754.6	704.4	656.4	615.1	577.1
142.5°	923.1	897.5	864.0	844.4	824.9	782.5	739.0	696.5	656.4	618.4	583.8
145°	874.0	855.0	828.3	812.1	795.9	761.3	724.4	689.8	654.1	620.6	589.4
147.5°	835.0	819.3	795.9	783.6	771.3	743.4	713.3	683.1	650.8	621.8	592.7
150°	799.2	785.8	769.1	759.0	749.0	725.6	701.0	674.2	647.4	620.6	595.0
152.5°	770.2	759.1	746.8	738.4	730.0	711.1	688.7	666.4	641.8	618.4	596.1
155°	744.5	736.7	724.4	718.3	712.2	695.4	677.6	656.4	635.1	616.2	597.2
157.5°	720.0	713.3	704.4	699.3	694.3	679.8	664.2	647.4	628.4	611.7	597.2
160°	697.7	692.1	684.3	680.3	676.4	664.2	651.9	637.4	621.8	608.4	597.2
162.5°	676.4	673.1	665.3	662.5	659.7	649.7	639.6	628.4	616.2	605.0	596.1
165°	656.4	651.9	647.4	645.2	643.0	635.1	627.3	618.4	608.4	600.5	593.8
167.5°	636.3	634.0	631.8	629.6	627.3	621.8	615.1	608.4	601.7	596.1	592.7
170°	620.6	617.3	616.2	615.0	613.9	609.5	606.1	600.5	596.1	592.7	590.5
172.5°	605.0	603.9	602.8	602.2	601.7	598.3	596.1	592.7	589.4	588.3	587.1
175°	593.8	592.7	592.7	592.2	591.6	590.5	589.4	586.0	584.9	583.8	584.9
177.5°	584.9	584.9	584.9	584.9	584.9	583.8	583.8	581.6	580.5	581.6	583.8
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1692.9	1686.6	1682.8	1685.3	1677.7	1658.7	1658.7	1665.0	1657.4	1649.8	1638.4
5°	1739.9	1727.2	1719.6	1718.3	1700.5	1670.1	1663.8	1657.4	1640.9	1623.2	1604.2
7.5°	1785.5	1762.7	1750.0	1741.1	1715.8	1676.4	1660.0	1646.0	1619.4	1592.8	1568.7
10°	1823.5	1790.6	1775.4	1761.4	1728.4	1679.0	1652.4	1627.0	1592.8	1558.5	1528.1
12.5°	1854.0	1815.9	1796.9	1776.6	1736.0	1671.4	1638.4	1597.8	1563.6	1517.9	1487.5
15°	1904.7	1826.1	1808.3	1789.3	1747.5	1658.7	1618.1	1572.5	1525.5	1464.7	1431.7
17.5°	1945.3	1840.0	1838.8	1798.2	1743.7	1653.6	1591.5	1531.9	1481.2	1420.3	1368.3
20°	1969.4	1861.6	1841.3	1799.5	1731.0	1619.4	1554.7	1488.8	1434.2	1360.7	1308.7
22.5°	1989.7	1892.0	1838.8	1788.0	1704.3	1608.0	1512.9	1450.7	1375.9	1296.0	1246.6
25°	1997.3	1898.4	1842.6	1784.2	1685.3	1575.0	1467.2	1400.0	1316.3	1244.0	1176.8
27.5°	1998.5	1897.1	1828.6	1767.8	1658.7	1531.9	1421.6	1350.5	1258.0	1174.3	1107.1
30°	1985.9	1883.2	1821.0	1755.1	1633.3	1492.6	1365.8	1287.1	1188.2	1104.5	1034.8
32.5°	1947.8	1855.3	1804.5	1732.2	1600.4	1438.0	1312.5	1225.0	1121.0	1038.6	971.4
35°	1884.4	1821.0	1765.2	1698.0	1557.2	1387.3	1259.2	1156.5	1051.3	972.6	909.2
37.5°	1805.8	1771.6	1719.6	1653.6	1507.8	1341.7	1199.6	1085.5	980.3	904.2	842.0
40°	1699.3	1708.2	1657.4	1597.8	1449.5	1279.5	1122.3	1013.2	914.3	843.3	782.4
42.5°	1583.9	1620.7	1591.5	1534.4	1384.8	1211.0	1065.2	944.7	848.4	774.8	724.1
45°	1459.6	1523.0	1505.3	1463.4	1317.6	1138.8	984.1	867.4	782.4	711.4	667.0
47.5°	1323.9	1413.9	1413.9	1383.5	1242.8	1066.5	914.3	795.1	711.4	660.7	617.6
50°	1185.7	1287.1	1303.6	1283.3	1159.1	984.1	829.3	721.6	649.3	599.8	568.1
52.5°	1041.1	1159.1	1189.5	1179.3	1070.3	905.4	759.6	654.3	588.4	545.3	517.4
55°	902.9	1039.9	1072.8	1076.6	975.2	819.2	682.2	589.7	526.3	497.1	473.0
57.5°	772.3	904.2	940.9	947.3	878.8	740.6	610.0	528.8	471.7	447.6	428.6
60°	660.7	771.0	819.2	833.2	773.6	649.3	542.8	464.1	421.0	398.2	380.4
62.5°	569.4	658.2	708.9	712.7	686.1	569.4	473.0	407.1	370.3	350.0	341.1
65°	480.6	560.5	590.9	606.2	584.6	493.3	408.3	353.8	324.6	306.9	298.0
67.5°	409.6	460.3	485.7	506.0	484.4	415.9	347.5	303.1	281.5	263.8	258.7
70°	336.1	377.9	396.9	417.2	398.2	346.2	296.7	256.2	237.1	223.2	216.8
72.5°	268.8	301.8	319.6	332.2	320.8	277.7	237.1	209.2	195.3	185.1	181.3
75°	213.0	235.9	246.0	254.9	249.8	216.8	191.5	168.7	156.0	147.1	144.6
77.5°	162.3	178.8	190.2	192.8	186.4	164.9	143.3	129.3	119.2	114.1	111.6
80°	115.4	125.5	131.9	135.7	129.3	120.5	105.3	95.1	86.2	79.9	78.6
82.5°	77.4	82.4	87.5	86.2	83.7	76.1	67.2	62.1	58.3	53.3	53.3
85°	44.4	45.7	48.2	49.5	48.2	43.1	38.0	35.5	33.0	29.2	29.2
87.5°	19.0	20.3	20.3	21.6	19.0	19.0	16.5	13.9	13.9	12.7	11.4
90°	22.3	16.7	15.0	13.4	11.2	8.9	4.5	1.1	4.5	8.9	11.2
92.5°	89.3	59.2	53.0	46.9	38.0	32.4	23.4	16.7	23.4	32.4	38.0
95°	160.7	109.4	96.0	82.6	64.7	54.7	43.5	39.1	43.5	54.7	64.7
97.5°	207.6	141.8	126.7	111.6	91.5	77.0	64.7	58.0	64.7	77.0	91.5
100°	229.9	170.8	155.2	139.5	117.2	99.3	89.3	86.0	89.3	99.3	117.2
102.5°	250.0	196.5	180.8	165.2	141.8	123.9	113.9	111.6	113.9	123.9	141.8
105°	273.5	221.0	205.4	189.8	165.2	148.5	140.6	136.2	140.6	148.5	165.2
107.5°	296.9	245.6	230.0	214.3	189.8	174.1	166.3	163.0	166.3	174.1	189.8
110°	320.4	271.2	255.0	238.9	215.4	200.9	194.2	189.8	194.2	200.9	215.4

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	342.7	295.8	279.0	262.3	240.0	226.6	218.8	214.3	218.8	226.6	240.0
115°	366.1	318.1	303.0	288.0	265.7	252.3	245.6	240.0	245.6	252.3	265.7
117.5°	387.3	342.7	327.0	311.4	290.2	277.9	271.2	266.8	271.2	277.9	290.2
120°	409.7	366.1	350.5	334.9	312.6	302.5	295.8	291.3	295.8	302.5	312.6
122.5°	430.9	390.7	374.5	358.3	336.0	324.8	318.1	314.8	318.1	324.8	336.0
125°	452.1	411.9	396.2	380.6	358.3	344.9	338.2	334.9	338.2	344.9	358.3
127.5°	472.2	433.1	416.9	400.7	379.5	365.0	356.1	351.6	356.1	365.0	379.5
130°	490.0	451.0	435.4	419.7	397.4	381.8	370.6	366.1	370.6	381.8	397.4
132.5°	505.7	468.8	453.2	437.6	414.1	397.4	385.1	379.5	385.1	397.4	414.1
135°	520.2	484.5	468.8	453.2	427.5	410.8	397.4	392.9	397.4	410.8	427.5
137.5°	532.5	496.7	482.2	467.7	442.0	424.2	410.8	405.2	410.8	424.2	442.0
140°	542.5	509.0	494.5	480.0	455.4	437.6	424.2	419.7	424.2	437.6	455.4
142.5°	550.3	517.9	504.6	491.2	467.7	449.8	437.6	434.2	437.6	449.8	467.7
145°	558.1	528.0	515.7	503.4	481.1	464.4	453.2	448.7	453.2	464.4	481.1
147.5°	564.8	535.8	524.6	513.5	494.5	478.9	467.7	464.4	467.7	478.9	494.5
150°	569.3	543.6	533.6	523.5	506.8	492.3	483.3	480.0	483.3	492.3	506.8
152.5°	573.8	551.4	542.5	533.6	517.9	505.7	496.7	495.6	496.7	505.7	517.9
155°	578.2	559.2	550.8	542.5	530.2	517.9	511.2	510.1	511.2	517.9	530.2
157.5°	581.6	564.8	557.6	550.3	540.3	529.1	523.5	522.4	523.5	529.1	540.3
160°	583.8	570.4	564.2	558.1	549.2	540.3	535.8	534.7	535.8	540.3	549.2
162.5°	584.9	573.8	569.3	564.8	557.0	550.3	545.8	547.0	545.8	550.3	557.0
165°	586.0	576.0	572.6	569.3	563.7	557.0	554.8	555.9	554.8	557.0	563.7
167.5°	586.0	578.2	576.0	573.8	569.3	564.8	562.6	563.7	562.6	564.8	569.3
170°	584.9	579.3	577.6	576.0	573.8	570.4	569.3	571.5	569.3	570.4	573.8
172.5°	583.8	580.5	579.4	578.2	577.1	573.8	574.9	576.0	574.9	573.8	577.1
175°	582.7	580.5	579.9	579.3	579.3	577.1	578.2	579.3	578.2	577.1	579.3
177.5°	581.6	580.5	580.5	580.5	580.5	578.2	579.3	581.6	579.3	578.2	580.5
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1632.1	1638.4	1637.1	1624.5	1610.5	1599.1	1577.5	1580.1	1572.5	1573.7	1581.3
5°	1591.5	1591.5	1586.4	1568.7	1545.8	1533.2	1509.1	1502.7	1487.5	1486.2	1485.0
7.5°	1548.4	1542.0	1535.7	1510.3	1482.4	1462.1	1429.2	1421.6	1406.3	1396.2	1391.1
10°	1497.6	1488.8	1476.1	1446.9	1412.7	1387.3	1353.1	1342.9	1313.8	1301.1	1293.5
12.5°	1441.8	1436.8	1416.5	1392.4	1336.6	1308.7	1259.2	1269.4	1240.2	1214.9	1211.0
15°	1386.0	1367.0	1355.6	1316.3	1249.1	1236.4	1197.1	1176.8	1150.2	1129.9	1129.9
17.5°	1331.5	1302.4	1277.0	1235.1	1185.7	1150.2	1121.0	1110.9	1077.9	1057.6	1053.8
20°	1259.2	1226.3	1219.9	1160.3	1126.1	1086.8	1058.9	1033.5	1009.4	1000.5	994.2
22.5°	1190.8	1152.7	1142.6	1091.8	1057.6	1018.3	990.4	972.6	954.9	948.5	937.1
25°	1117.2	1094.4	1079.2	1024.6	986.6	949.8	930.8	918.1	901.6	900.4	892.8
27.5°	1046.2	1024.6	1009.4	957.4	929.5	895.3	880.1	866.1	857.2	853.4	849.6
30°	985.3	961.2	943.5	905.4	871.2	843.3	830.6	821.7	816.7	810.3	809.1
32.5°	918.1	904.2	880.1	850.9	824.3	797.6	790.0	783.7	776.1	773.6	772.3
35°	861.1	842.0	826.8	793.8	782.4	759.6	750.7	745.7	735.5	733.0	730.4
37.5°	805.3	787.5	771.0	750.7	729.2	716.5	711.4	703.8	698.7	700.0	697.5
40°	749.5	735.5	722.8	701.3	688.6	682.2	672.1	664.5	662.0	663.2	662.0
42.5°	694.9	682.2	674.6	658.2	645.5	639.1	632.8	625.2	629.0	629.0	632.8
45°	645.5	634.1	629.0	616.3	608.7	598.6	592.2	590.9	596.0	594.7	594.7
47.5°	594.7	590.9	584.6	573.2	563.0	556.7	555.4	555.4	560.5	563.0	561.8
50°	555.4	547.8	540.2	531.3	523.7	521.2	517.4	519.9	525.0	525.0	527.5
52.5°	506.0	500.9	498.4	490.8	485.7	485.7	485.7	487.0	490.8	494.6	493.3
55°	462.9	459.1	456.5	452.7	446.4	447.6	446.4	448.9	452.7	456.5	459.1
57.5°	417.2	415.9	413.4	407.1	407.1	405.8	409.6	410.9	417.2	419.7	423.6
60°	376.6	372.8	372.8	367.8	367.8	367.8	371.6	375.4	380.4	381.7	384.2
62.5°	333.5	333.5	332.2	328.4	328.4	332.2	333.5	338.6	341.1	341.1	344.9
65°	292.9	291.7	290.4	291.7	292.9	292.9	296.7	299.3	301.8	303.1	304.3
67.5°	252.4	251.1	253.6	252.4	254.9	260.0	258.7	262.5	266.3	266.3	267.6
70°	214.3	216.8	215.6	218.1	216.8	219.4	223.2	224.5	224.5	225.7	229.5
72.5°	178.8	178.8	178.8	177.5	178.8	181.3	183.9	185.1	187.7	188.9	192.8
75°	144.6	144.6	142.0	144.6	144.6	147.1	149.6	149.6	149.6	152.2	156.0
77.5°	109.1	110.3	109.1	111.6	111.6	112.9	115.4	114.1	116.7	117.9	119.2
80°	79.9	78.6	78.6	78.6	79.9	79.9	82.4	83.7	83.7	87.5	85.0
82.5°	50.7	52.0	50.7	52.0	52.0	53.3	52.0	53.3	54.5	57.1	55.8
85°	29.2	27.9	27.9	29.2	27.9	27.9	29.2	27.9	29.2	27.9	29.2
87.5°	11.4	10.1	10.1	10.1	10.1	8.9	8.9	7.6	7.6	7.6	6.3
90°	13.4	15.0	16.7	22.3	30.1	36.8	38.0	36.8	35.7	33.5	35.7
92.5°	46.9	53.0	59.2	89.3	131.7	169.7	171.9	144.0	112.7	96.0	83.7
95°	82.6	96.0	109.4	160.7	257.9	387.3	437.6	382.9	292.5	224.4	177.5
97.5°	111.6	126.7	141.8	207.6	342.7	551.4	713.3	718.9	598.3	477.8	365.0
100°	139.5	155.2	170.8	229.9	366.1	607.2	881.8	1042.6	1019.1	880.7	727.8
102.5°	165.2	180.8	196.5	250.0	367.2	586.0	887.4	1163.1	1294.9	1290.4	1188.8
105°	189.8	205.4	221.0	273.5	372.8	557.0	827.1	1124.1	1356.2	1482.4	1496.9
107.5°	214.3	230.0	245.6	296.9	385.1	541.4	771.3	1041.5	1290.4	1477.9	1587.3
110°	238.9	255.0	271.2	320.4	400.7	536.9	733.4	964.4	1200.0	1399.8	1542.7

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	262.3	279.0	295.8	342.7	417.5	538.0	708.8	910.9	1117.4	1307.1	1462.3
115°	288.0	303.0	318.1	366.1	434.2	542.5	692.1	868.4	1052.6	1224.5	1370.8
117.5°	311.4	327.0	342.7	387.3	452.1	549.2	683.1	839.4	999.0	1153.1	1289.3
120°	334.9	350.5	366.1	409.7	469.9	555.9	675.3	817.1	961.1	1099.5	1217.8
122.5°	358.3	374.5	390.7	430.9	485.6	563.7	670.9	798.1	931.0	1054.9	1165.4
125°	380.6	396.2	411.9	452.1	502.3	571.5	665.3	780.3	901.9	1016.9	1115.1
127.5°	400.7	416.9	433.1	472.2	517.9	579.3	661.9	763.5	872.9	979.0	1072.7
130°	419.7	435.4	451.0	490.0	532.5	588.3	659.7	746.8	845.0	941.0	1029.2
132.5°	437.6	453.2	468.8	505.7	547.0	597.2	658.6	733.4	818.2	905.3	984.5
135°	453.2	468.8	484.5	520.2	559.2	603.9	657.5	721.1	793.7	867.3	941.0
137.5°	467.7	482.2	496.7	532.5	569.3	610.6	657.5	712.2	773.6	837.2	897.5
140°	480.0	494.5	509.0	542.5	577.1	615.1	656.4	704.4	754.6	808.2	859.5
142.5°	491.2	504.6	517.9	550.3	583.8	618.4	656.4	696.5	739.0	782.5	824.9
145°	503.4	515.7	528.0	558.1	589.4	620.6	654.1	689.8	724.4	761.3	795.9
147.5°	513.5	524.6	535.8	564.8	592.7	621.8	650.8	683.1	713.3	743.4	771.3
150°	523.5	533.6	543.6	569.3	595.0	620.6	647.4	674.2	701.0	725.6	749.0
152.5°	533.6	542.5	551.4	573.8	596.1	618.4	641.8	666.4	688.7	711.1	730.0
155°	542.5	550.8	559.2	578.2	597.2	616.2	635.1	656.4	677.6	695.4	712.2
157.5°	550.3	557.6	564.8	581.6	597.2	611.7	628.4	647.4	664.2	679.8	694.3
160°	558.1	564.2	570.4	583.8	597.2	608.4	621.8	637.4	651.9	664.2	676.4
162.5°	564.8	569.3	573.8	584.9	596.1	605.0	616.2	628.4	639.6	649.7	659.7
165°	569.3	572.6	576.0	586.0	593.8	600.5	608.4	618.4	627.3	635.1	643.0
167.5°	573.8	576.0	578.2	586.0	592.7	596.1	601.7	608.4	615.1	621.8	627.3
170°	576.0	577.6	579.3	584.9	590.5	592.7	596.1	600.5	606.1	609.5	613.9
172.5°	578.2	579.4	580.5	583.8	587.1	588.3	589.4	592.7	596.1	598.3	601.7
175°	579.3	579.9	580.5	582.7	584.9	583.8	584.9	586.0	589.4	590.5	591.6
177.5°	580.5	580.5	580.5	581.6	583.8	581.6	580.5	581.6	583.8	583.8	584.9
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1572.5	1576.3	1567.4	1564.9	1567.4	1558.5	1561.0	1563.6	1563.6	1567.4	1569.9
5°	1481.2	1476.1	1467.2	1464.7	1462.1	1465.9	1463.4	1467.2	1468.5	1477.4	1478.6
7.5°	1391.1	1383.5	1375.9	1368.3	1365.8	1359.4	1365.8	1365.8	1374.6	1372.1	1378.4
10°	1284.6	1283.3	1273.2	1269.4	1264.3	1254.2	1268.1	1264.3	1270.7	1282.1	1284.6
12.5°	1206.0	1192.0	1198.4	1180.6	1187.0	1176.8	1178.1	1178.1	1188.2	1189.5	1187.0
15°	1131.2	1119.7	1103.3	1095.7	1091.8	1086.8	1103.3	1104.5	1096.9	1114.7	1108.3
17.5°	1055.1	1055.1	1039.9	1036.0	1025.9	1031.0	1028.4	1029.7	1027.2	1039.9	1046.2
20°	989.1	982.8	977.7	979.0	966.3	963.8	961.2	963.8	972.6	981.5	984.1
22.5°	935.9	932.1	919.4	921.9	911.8	915.6	913.0	919.4	920.7	920.7	929.5
25°	885.1	880.1	881.3	876.3	872.5	872.5	868.7	872.5	877.5	880.1	881.3
27.5°	847.1	843.3	837.0	833.2	835.7	829.3	834.4	838.2	838.2	835.7	838.2
30°	801.4	804.0	804.0	791.3	796.4	793.8	797.6	800.2	800.2	801.4	798.9
32.5°	771.0	763.4	762.1	760.9	760.9	755.8	755.8	759.6	760.9	762.1	765.9
35°	730.4	730.4	724.1	727.9	722.8	724.1	722.8	724.1	726.6	722.8	726.6
37.5°	693.7	694.9	692.4	694.9	696.2	693.7	691.1	696.2	693.7	693.7	691.1
40°	662.0	660.7	662.0	662.0	662.0	663.2	660.7	660.7	660.7	658.2	655.6
42.5°	635.3	627.7	630.3	631.5	627.7	627.7	629.0	627.7	631.5	623.9	623.9
45°	597.3	594.7	596.0	596.0	598.6	594.7	597.3	598.6	594.7	593.5	590.9
47.5°	563.0	565.6	563.0	565.6	565.6	568.1	563.0	564.3	565.6	560.5	556.7
50°	528.8	528.8	532.6	531.3	532.6	530.1	530.1	528.8	530.1	527.5	523.7
52.5°	497.1	493.3	499.6	498.4	497.1	495.8	494.6	495.8	493.3	490.8	490.8
55°	457.8	457.8	461.6	462.9	462.9	460.3	457.8	459.1	457.8	456.5	455.3
57.5°	426.1	421.0	423.6	424.8	424.8	421.0	423.6	421.0	421.0	422.3	418.5
60°	385.5	385.5	383.0	386.8	386.8	384.2	384.2	385.5	383.0	381.7	380.4
62.5°	342.4	343.7	347.5	348.7	350.0	347.5	344.9	346.2	346.2	342.4	343.7
65°	305.6	308.2	313.2	312.0	309.4	310.7	308.2	309.4	305.6	306.9	303.1
67.5°	270.1	268.8	270.1	270.1	272.6	271.4	268.8	268.8	267.6	271.4	267.6
70°	232.1	232.1	232.1	232.1	233.3	234.6	232.1	229.5	230.8	228.3	227.0
72.5°	192.8	194.0	192.8	195.3	191.5	194.0	194.0	192.8	191.5	191.5	191.5
75°	156.0	158.5	154.7	156.0	154.7	157.2	156.0	156.0	153.4	152.2	153.4
77.5°	119.2	120.5	117.9	119.2	117.9	119.2	119.2	117.9	117.9	117.9	117.9
80°	85.0	86.2	85.0	83.7	82.4	85.0	82.4	83.7	85.0	83.7	86.2
82.5°	54.5	54.5	53.3	54.5	52.0	52.0	53.3	53.3	52.0	54.5	52.0
85°	26.6	26.6	29.2	26.6	25.4	25.4	25.4	26.6	25.4	27.9	26.6
87.5°	6.3	5.1	6.3	6.3	5.1	5.1	6.3	5.1	6.3	7.6	5.1
90°	36.2	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.2
92.5°	79.2	74.8	73.7	69.2	70.3	68.1	70.3	69.2	73.7	74.8	79.2
95°	165.2	152.9	138.4	129.5	126.1	127.3	126.1	129.5	138.4	152.9	165.2
97.5°	331.5	298.0	254.5	232.2	219.9	213.2	219.9	232.2	254.5	298.0	331.5
100°	660.2	592.7	500.1	452.1	419.7	399.6	419.7	452.1	500.1	592.7	660.2
102.5°	1116.2	1043.7	941.0	850.6	808.2	779.1	808.2	850.6	941.0	1043.7	1116.2
105°	1478.5	1460.1	1390.8	1321.6	1273.6	1258.0	1273.6	1321.6	1390.8	1460.1	1478.5
107.5°	1609.6	1632.0	1630.8	1620.8	1606.3	1580.6	1606.3	1620.8	1630.8	1632.0	1609.6
110°	1588.4	1634.2	1682.2	1703.4	1713.4	1712.3	1713.4	1703.4	1682.2	1634.2	1588.4

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1516.4	1570.6	1642.0	1681.1	1702.3	1710.1	1702.3	1681.1	1642.0	1570.6	1516.4
115°	1428.2	1485.7	1565.0	1616.3	1645.4	1655.4	1645.4	1616.3	1565.0	1485.7	1428.2
117.5°	1344.0	1398.7	1480.1	1534.8	1565.0	1572.8	1565.0	1534.8	1480.1	1398.7	1344.0
120°	1268.6	1319.4	1397.5	1450.0	1482.4	1493.5	1482.4	1450.0	1397.5	1319.4	1268.6
122.5°	1210.1	1254.7	1322.8	1374.1	1402.0	1410.9	1402.0	1374.1	1322.8	1254.7	1210.1
125°	1157.0	1198.9	1263.6	1306.0	1333.9	1342.8	1333.9	1306.0	1263.6	1198.9	1157.0
127.5°	1111.8	1150.9	1207.8	1248.0	1272.5	1279.2	1272.5	1248.0	1207.8	1150.9	1111.8
130°	1066.1	1102.9	1157.6	1195.5	1217.8	1226.8	1217.8	1195.5	1157.6	1102.9	1066.1
132.5°	1018.6	1052.6	1106.2	1144.2	1164.2	1172.1	1164.2	1144.2	1106.2	1052.6	1018.6
135°	972.2	1003.5	1051.5	1088.3	1108.4	1112.9	1108.4	1088.3	1051.5	1003.5	972.2
137.5°	925.4	953.3	999.0	1031.4	1049.3	1056.0	1049.3	1031.4	999.0	953.3	925.4
140°	884.0	908.6	944.3	973.4	990.1	996.8	990.1	973.4	944.3	908.6	884.0
142.5°	844.4	864.0	897.5	923.1	937.7	937.7	937.7	923.1	897.5	864.0	844.4
145°	812.1	828.3	855.0	874.0	885.2	888.5	885.2	874.0	855.0	828.3	812.1
147.5°	783.6	795.9	819.3	835.0	842.8	845.0	842.8	835.0	819.3	795.9	783.6
150°	759.0	769.1	785.8	799.2	805.9	807.0	805.9	799.2	785.8	769.1	759.0
152.5°	738.4	746.8	759.1	770.2	774.7	774.7	774.7	770.2	759.1	746.8	738.4
155°	718.3	724.4	736.7	744.5	749.0	746.8	749.0	744.5	736.7	724.4	718.3
157.5°	699.3	704.4	713.3	720.0	722.2	722.2	722.2	720.0	713.3	704.4	699.3
160°	680.3	684.3	692.1	697.7	698.8	698.8	698.8	697.7	692.1	684.3	680.3
162.5°	662.5	665.3	673.1	676.4	677.6	676.4	677.6	676.4	673.1	665.3	662.5
165°	645.2	647.4	651.9	656.4	656.4	655.2	656.4	656.4	651.9	647.4	645.2
167.5°	629.6	631.8	634.0	636.3	636.3	635.1	636.3	636.3	634.0	631.8	629.6
170°	615.0	616.2	617.3	620.6	619.5	617.3	619.5	620.6	617.3	616.2	615.0
172.5°	602.2	602.8	603.9	605.0	603.9	602.8	603.9	605.0	603.9	602.8	602.2
175°	592.2	592.7	592.7	593.8	592.7	590.5	592.7	593.8	592.7	592.7	592.2
177.5°	584.9	584.9	584.9	584.9	583.8	581.6	583.8	584.9	584.9	584.9	584.9
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1566.1	1576.3	1572.5	1558.5	1575.0	1575.0	1586.4	1586.4	1600.4	1605.4	1613.0
5°	1477.4	1485.0	1491.3	1485.0	1496.4	1514.1	1524.3	1533.2	1552.2	1559.8	1571.2
7.5°	1382.2	1396.2	1402.5	1402.5	1421.6	1441.8	1462.1	1474.8	1501.4	1511.6	1523.0
10°	1289.7	1306.2	1318.8	1317.6	1349.3	1362.0	1387.3	1416.5	1443.1	1458.3	1474.8
12.5°	1192.0	1200.9	1218.7	1244.0	1251.6	1274.5	1303.6	1340.4	1388.6	1402.5	1426.6
15°	1110.9	1135.0	1148.9	1160.3	1178.1	1199.6	1231.3	1266.8	1315.0	1345.5	1370.8
17.5°	1042.4	1074.1	1083.0	1080.4	1103.3	1136.2	1173.0	1199.6	1242.8	1279.5	1303.6
20°	986.6	999.3	1014.5	1020.8	1038.6	1074.1	1109.6	1140.0	1175.5	1204.7	1232.6
22.5°	930.8	940.9	953.6	965.0	979.0	999.3	1033.5	1071.6	1105.8	1133.7	1165.4
25°	885.1	891.5	902.9	911.8	927.0	940.9	965.0	1006.9	1047.5	1063.9	1091.8
27.5°	840.8	845.8	853.4	863.6	871.2	885.1	906.7	940.9	982.8	999.3	1037.3
30°	801.4	805.3	812.9	817.9	821.7	838.2	854.7	881.3	913.0	935.9	963.8
32.5°	764.7	768.5	776.1	777.4	782.4	791.3	806.5	830.6	858.5	877.5	901.6
35°	724.1	726.6	734.2	736.8	740.6	748.2	759.6	777.4	802.7	816.7	838.2
37.5°	692.4	691.1	696.2	700.0	705.1	708.9	712.7	730.4	749.5	762.1	778.6
40°	658.2	655.6	656.9	662.0	664.5	669.6	669.6	687.3	700.0	710.1	722.8
42.5°	623.9	622.6	620.1	622.6	625.2	626.4	627.7	640.4	653.1	662.0	675.9
45°	589.7	588.4	585.9	587.1	587.1	589.7	593.5	598.6	607.4	615.0	622.6
47.5°	558.0	555.4	551.6	550.4	552.9	552.9	552.9	558.0	566.8	569.4	577.0
50°	525.0	521.2	516.1	513.6	513.6	512.3	514.9	516.1	523.7	526.3	532.6
52.5°	489.5	487.0	481.9	476.8	478.1	475.5	476.8	478.1	480.6	484.4	488.2
55°	454.0	448.9	445.1	443.8	440.0	440.0	436.2	441.3	440.0	441.3	446.4
57.5°	419.7	414.7	408.3	405.8	402.0	400.7	398.2	396.9	398.2	402.0	405.8
60°	379.2	376.6	372.8	369.0	366.5	362.7	360.1	360.1	358.9	358.9	360.1
62.5°	339.9	338.6	333.5	332.2	329.7	327.2	323.4	320.8	320.8	323.4	324.6
65°	301.8	300.5	296.7	295.5	289.1	286.6	285.3	284.1	281.5	281.5	281.5
67.5°	266.3	262.5	262.5	256.2	251.1	248.6	246.0	244.7	244.7	244.7	246.0
70°	227.0	227.0	223.2	219.4	214.3	215.6	211.8	208.0	208.0	205.4	206.7
72.5°	188.9	187.7	183.9	182.6	178.8	175.0	172.5	175.0	171.2	169.9	171.2
75°	152.2	150.9	148.4	145.8	147.1	143.3	139.5	138.2	138.2	135.7	135.7
77.5°	116.7	119.2	114.1	112.9	110.3	107.8	106.5	105.3	105.3	105.3	107.8
80°	81.2	82.4	82.4	79.9	81.2	77.4	77.4	77.4	73.6	74.8	76.1
82.5°	52.0	52.0	50.7	52.0	50.7	50.7	49.5	49.5	48.2	48.2	49.5
85°	29.2	27.9	26.6	29.2	27.9	27.9	26.6	26.6	26.6	26.6	26.6
87.5°	6.3	7.6	7.6	7.6	7.6	8.9	8.9	8.9	10.1	10.1	10.1
90°	35.7	33.5	35.7	36.8	38.0	36.8	30.1	22.3	16.7	15.0	13.4
92.5°	83.7	96.0	112.7	144.0	171.9	169.7	131.7	89.3	59.2	53.0	46.9
95°	177.5	224.4	292.5	382.9	437.6	387.3	257.9	160.7	109.4	96.0	82.6
97.5°	365.0	477.8	598.3	718.9	713.3	551.4	342.7	207.6	141.8	126.7	111.6
100°	727.8	880.7	1019.1	1042.6	881.8	607.2	366.1	229.9	170.8	155.2	139.5
102.5°	1188.8	1290.4	1294.9	1163.1	887.4	586.0	367.2	250.0	196.5	180.8	165.2
105°	1496.9	1482.4	1356.2	1124.1	827.1	557.0	372.8	273.5	221.0	205.4	189.8
107.5°	1587.3	1477.9	1290.4	1041.5	771.3	541.4	385.1	296.9	245.6	230.0	214.3
110°	1542.7	1399.8	1200.0	964.4	733.4	536.9	400.7	320.4	271.2	255.0	238.9

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1462.3	1307.1	1117.4	910.9	708.8	538.0	417.5	342.7	295.8	279.0	262.3
115°	1370.8	1224.5	1052.6	868.4	692.1	542.5	434.2	366.1	318.1	303.0	288.0
117.5°	1289.3	1153.1	999.0	839.4	683.1	549.2	452.1	387.3	342.7	327.0	311.4
120°	1217.8	1099.5	961.1	817.1	675.3	555.9	469.9	409.7	366.1	350.5	334.9
122.5°	1165.4	1054.9	931.0	798.1	670.9	563.7	485.6	430.9	390.7	374.5	358.3
125°	1115.1	1016.9	901.9	780.3	665.3	571.5	502.3	452.1	411.9	396.2	380.6
127.5°	1072.7	979.0	872.9	763.5	661.9	579.3	517.9	472.2	433.1	416.9	400.7
130°	1029.2	941.0	845.0	746.8	659.7	588.3	532.5	490.0	451.0	435.4	419.7
132.5°	984.5	905.3	818.2	733.4	658.6	597.2	547.0	505.7	468.8	453.2	437.6
135°	941.0	867.3	793.7	721.1	657.5	603.9	559.2	520.2	484.5	468.8	453.2
137.5°	897.5	837.2	773.6	712.2	657.5	610.6	569.3	532.5	496.7	482.2	467.7
140°	859.5	808.2	754.6	704.4	656.4	615.1	577.1	542.5	509.0	494.5	480.0
142.5°	824.9	782.5	739.0	696.5	656.4	618.4	583.8	550.3	517.9	504.6	491.2
145°	795.9	761.3	724.4	689.8	654.1	620.6	589.4	558.1	528.0	515.7	503.4
147.5°	771.3	743.4	713.3	683.1	650.8	621.8	592.7	564.8	535.8	524.6	513.5
150°	749.0	725.6	701.0	674.2	647.4	620.6	595.0	569.3	543.6	533.6	523.5
152.5°	730.0	711.1	688.7	666.4	641.8	618.4	596.1	573.8	551.4	542.5	533.6
155°	712.2	695.4	677.6	656.4	635.1	616.2	597.2	578.2	559.2	550.8	542.5
157.5°	694.3	679.8	664.2	647.4	628.4	611.7	597.2	581.6	564.8	557.6	550.3
160°	676.4	664.2	651.9	637.4	621.8	608.4	597.2	583.8	570.4	564.2	558.1
162.5°	659.7	649.7	639.6	628.4	616.2	605.0	596.1	584.9	573.8	569.3	564.8
165°	643.0	635.1	627.3	618.4	608.4	600.5	593.8	586.0	576.0	572.6	569.3
167.5°	627.3	621.8	615.1	608.4	601.7	596.1	592.7	586.0	578.2	576.0	573.8
170°	613.9	609.5	606.1	600.5	596.1	592.7	590.5	584.9	579.3	577.6	576.0
172.5°	601.7	598.3	596.1	592.7	589.4	588.3	587.1	583.8	580.5	579.4	578.2
175°	591.6	590.5	589.4	586.0	584.9	583.8	584.9	582.7	580.5	579.9	579.3
177.5°	584.9	583.8	583.8	581.6	580.5	581.6	583.8	581.6	580.5	580.5	580.5
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1649.8	1649.8	1649.8	1649.8
2.5°	1619.4	1619.4	1638.4	1658.7
5°	1583.9	1592.8	1623.2	1651.1
7.5°	1549.6	1564.9	1602.9	1638.4
10°	1507.8	1528.1	1575.0	1616.8
12.5°	1467.2	1486.2	1540.8	1587.7
15°	1410.1	1434.2	1492.6	1550.9
17.5°	1353.1	1377.2	1448.2	1516.7
20°	1285.9	1317.6	1397.5	1488.8
22.5°	1223.7	1263.0	1351.8	1425.4
25°	1155.3	1216.1	1298.5	1393.7
27.5°	1094.4	1155.3	1238.9	1335.3
30°	1025.9	1088.0	1174.3	1263.0
32.5°	960.0	1017.0	1100.7	1209.8
35°	891.5	946.0	1027.2	1137.5
37.5°	829.3	882.6	971.4	1072.8
40°	768.5	824.3	900.4	1001.8
42.5°	711.4	760.9	829.3	930.8
45°	659.4	694.9	758.3	853.4
47.5°	604.9	636.6	694.9	790.0
50°	554.2	580.8	631.5	720.3
52.5°	504.7	527.5	574.5	645.5
55°	460.3	481.9	516.1	585.9
57.5°	414.7	431.2	464.1	519.9
60°	370.3	385.5	412.1	457.8
62.5°	325.9	338.6	363.9	400.7
65°	286.6	296.7	315.8	347.5
67.5°	248.6	254.9	270.1	295.5
70°	211.8	216.8	229.5	249.8
72.5°	172.5	177.5	191.5	205.4
75°	139.5	140.8	150.9	162.3
77.5°	109.1	107.8	115.4	124.3
80°	74.8	78.6	85.0	88.8
82.5°	50.7	52.0	54.5	57.1
85°	27.9	29.2	29.2	33.0
87.5°	11.4	12.7	12.7	13.9
90°	11.2	8.9	4.5	1.1
92.5°	38.0	32.4	23.4	16.7
95°	64.7	54.7	43.5	39.1
97.5°	91.5	77.0	64.7	58.0
100°	117.2	99.3	89.3	86.0
102.5°	141.8	123.9	113.9	111.6
105°	165.2	148.5	140.6	136.2
107.5°	189.8	174.1	166.3	163.0
110°	215.4	200.9	194.2	189.8



TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	240.0	226.6	218.8	214.3
115°	265.7	252.3	245.6	240.0
117.5°	290.2	277.9	271.2	266.8
120°	312.6	302.5	295.8	291.3
122.5°	336.0	324.8	318.1	314.8
125°	358.3	344.9	338.2	334.9
127.5°	379.5	365.0	356.1	351.6
130°	397.4	381.8	370.6	366.1
132.5°	414.1	397.4	385.1	379.5
135°	427.5	410.8	397.4	392.9
137.5°	442.0	424.2	410.8	405.2
140°	455.4	437.6	424.2	419.7
142.5°	467.7	449.8	437.6	434.2
145°	481.1	464.4	453.2	448.7
147.5°	494.5	478.9	467.7	464.4
150°	506.8	492.3	483.3	480.0
152.5°	517.9	505.7	496.7	495.6
155°	530.2	517.9	511.2	510.1
157.5°	540.3	529.1	523.5	522.4
160°	549.2	540.3	535.8	534.7
162.5°	557.0	550.3	545.8	547.0
165°	563.7	557.0	554.8	555.9
167.5°	569.3	564.8	562.6	563.7
170°	573.8	570.4	569.3	571.5
172.5°	577.1	573.8	574.9	576.0
175°	579.3	577.1	578.2	579.3
177.5°	580.5	578.2	579.3	581.6
180°	580.5	580.5	580.5	580.5

TEST NUMBER: P999022

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.93	17.74	17.92	18.73	20.04	14.42	15.23	15.41	16.22	17.53
	3H	17.74	18.46	18.73	19.46	20.80	15.76	16.49	16.76	17.49	18.82
	4H	17.90	18.59	18.91	19.59	20.93	16.22	16.91	17.23	17.91	19.25
	6H	17.95	18.58	18.97	19.59	20.94	16.53	17.16	17.55	18.17	19.52
	8H	17.92	18.52	18.95	19.55	20.90	16.61	17.21	17.64	18.24	19.58
	12H	17.89	18.45	18.92	19.47	20.85	16.65	17.22	17.68	18.24	19.61
4H	2H	16.97	17.65	17.98	18.65	19.99	14.86	15.55	15.88	16.55	17.89
	3H	17.94	18.51	18.97	19.54	20.90	16.32	16.89	17.34	17.92	19.28
	4H	18.22	18.74	19.25	19.76	21.14	16.85	17.37	17.88	18.40	19.77
	6H	18.34	18.79	19.39	19.84	21.21	17.23	17.67	18.27	18.72	20.10
	8H	18.34	18.76	19.38	19.80	21.19	17.34	17.75	18.38	18.80	20.18
	12H	18.30	18.68	19.36	19.74	21.13	17.39	17.77	18.45	18.83	20.22
8H	4H	18.22	18.64	19.26	19.68	21.07	16.99	17.41	18.03	18.45	19.84
	6H	18.40	18.74	19.46	19.83	21.21	17.42	17.77	18.49	18.85	20.24
	8H	18.43	18.73	19.50	19.80	21.20	17.57	17.87	18.65	18.94	20.35
	12H	18.41	18.68	19.49	19.74	21.19	17.66	17.93	18.74	18.99	20.44
12H	4H	18.18	18.55	19.24	19.61	21.00	16.96	17.34	18.02	18.40	19.79
	6H	18.38	18.68	19.45	19.75	21.15	17.42	17.72	18.50	18.79	20.20
	8H	18.41	18.67	19.48	19.74	21.18	17.58	17.84	18.65	18.91	20.35