

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999027

Luminaire Tested: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999027
REPORT IS A COMBINATION OF REPORTS P984776 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7058.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999027

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999027

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	89	86	82	79	72	69	67	59	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20880	20880	20880
5°	20914	19903	19762
10°	20745	18996	18619
15°	20441	18082	17417
20°	20030	17088	16278
25°	19621	16049	15141
30°	19106	15074	13949
35°	18619	14045	12776
40°	18021	13030	11670
45°	17424	12022	10584
50°	16773	10997	9456
55°	16086	9900	8388
60°	15318	8714	7279
65°	14472	7509	6113
70°	13404	6188	4936
75°	11921	4770	3811
80°	10123	3241	2453
85°	7345	1509	1044

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17424 cd/sqm

TEST NUMBER: P999027

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	1.8
10°-20°	349.3	4.9
20°-30°	513.3	7.3
30°-40°	596.2	8.4
40°-50°	595.5	8.4
50°-60°	519.2	7.4
60°-70°	383.8	5.4
70°-80°	217.2	3.1
80°-90°	61.1	0.9
90°-100°	81.8	1.2
100°-110°	260.1	3.7
110°-120°	445.1	6.3
120°-130°	585.4	8.3
130°-140°	657.1	9.3
140°-150°	644.4	9.1
150°-160°	540.5	7.7
160°-170°	358.5	5.1
170°-180°	125.3	1.8
0°-30°	986.8	14.0
0°-40°	1583.0	22.4
0°-60°	2697.7	38.2
0°-90°	3359.8	47.6
90°-120°	787.0	11.2
90°-150°	2673.9	37.9
90°-180°	3698.0	52.4
0°-180°	7058.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1319	1314	1300	1310	1308	125
15°	1256	1248	1232	1237	1230	354
25°	1136	1126	1105	1107	1105	523
35°	980	968	948	940	934	612
45°	798	789	770	756	751	616
55°	604	596	581	566	559	540
65°	407	400	387	375	369	403
75°	213	210	204	197	199	227
85°	52	51	50	46	44	58
90°	1	14	39	37	38	7
95°	58	69	71	71	69	65
105°	240	243	246	248	248	253
115°	446	453	451	450	446	442
125°	650	660	656	653	652	581
135°	840	853	855	854	851	650
145°	1020	1028	1035	1036	1031	637
155°	1166	1170	1173	1179	1175	537
165°	1269	1268	1268	1276	1270	358
175°	1320	1317	1315	1323	1316	125
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P999027

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.1	1319.1	1319.1	1319.1	1319.1
2.5°	1326.7	1320.4	1306.4	1319.1	1316.6
5°	1319.1	1314.0	1300.1	1310.2	1307.7
7.5°	1310.2	1302.6	1288.7	1298.8	1296.3
10°	1296.3	1287.4	1272.2	1282.3	1278.5
12.5°	1277.2	1269.6	1254.4	1260.8	1258.2
15°	1255.7	1248.1	1231.6	1236.7	1230.3
17.5°	1229.0	1221.4	1204.9	1211.3	1204.9
20°	1199.9	1192.3	1174.5	1178.3	1173.2
22.5°	1170.7	1159.3	1142.8	1142.8	1140.3
25°	1136.5	1126.3	1104.7	1107.3	1104.7
27.5°	1098.4	1089.5	1073.0	1069.2	1062.9
30°	1060.4	1050.2	1031.2	1027.4	1022.3
32.5°	1019.8	1012.2	991.9	984.3	979.2
35°	980.4	967.8	947.5	939.9	933.5
37.5°	936.1	924.6	904.3	895.5	889.1
40°	890.4	880.2	860.0	848.5	843.5
42.5°	846.0	835.9	815.6	802.9	795.3
45°	797.8	788.9	769.9	755.9	750.9
47.5°	750.9	742.0	721.7	707.7	700.1
50°	701.4	695.1	677.3	659.5	653.2
52.5°	653.2	644.3	627.8	613.9	605.0
55°	603.7	596.1	580.9	565.7	559.3
57.5°	554.3	547.9	531.4	516.2	511.2
60°	504.8	499.7	482.0	468.0	464.2
62.5°	456.6	447.7	435.0	422.4	417.3
65°	407.1	399.5	386.9	375.4	369.1
67.5°	356.4	350.1	338.7	329.8	324.7
70°	309.5	304.4	293.0	284.1	279.0
72.5°	261.3	256.2	249.9	241.0	237.2
75°	213.1	210.5	204.2	196.6	199.1
77.5°	170.0	164.9	162.4	158.5	154.7
80°	126.8	125.6	123.0	119.2	116.7
82.5°	86.2	86.2	85.0	79.9	79.9
85°	52.0	50.7	49.5	45.7	44.4
87.5°	22.8	20.3	17.8	14.0	12.7
90°	1.1	14.5	39.1	36.8	38.0
92.5°	24.6	33.5	34.6	35.7	35.7
95°	58.0	69.2	71.4	71.4	69.2
97.5°	97.1	107.2	111.6	111.6	111.6
100°	141.8	150.7	154.0	154.0	152.9
102.5°	188.6	195.3	199.8	200.9	199.8
105°	240.0	243.3	245.6	247.8	247.8
107.5°	291.3	295.8	295.8	296.9	291.3
110°	340.5	347.2	347.2	347.2	343.8

TEST NUMBER: P999027

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	394.0	400.7	399.6	396.3	394.0
115°	446.5	453.2	451.0	449.9	446.5
117.5°	499.0	507.9	502.3	499.0	495.6
120°	551.4	560.4	551.4	551.4	548.1
122.5°	599.4	610.6	605.0	601.7	599.4
125°	649.7	659.7	656.4	653.0	651.9
127.5°	698.8	711.1	706.6	702.1	698.8
130°	744.6	759.1	756.8	754.6	750.1
132.5°	795.9	807.1	808.2	802.6	799.2
135°	840.5	852.8	855.1	853.9	850.6
137.5°	889.7	899.7	901.9	900.8	896.4
140°	933.2	943.2	948.8	948.8	944.4
142.5°	977.9	987.9	991.2	992.4	987.9
145°	1020.3	1028.1	1034.8	1035.9	1031.4
147.5°	1058.2	1068.3	1072.7	1075.0	1070.5
150°	1097.3	1104.0	1108.5	1111.8	1108.5
152.5°	1131.9	1138.6	1144.2	1148.6	1144.2
155°	1166.5	1169.8	1173.2	1178.8	1175.4
157.5°	1196.6	1198.9	1201.1	1208.9	1203.3
160°	1223.4	1225.7	1226.8	1233.5	1229.0
162.5°	1248.0	1248.0	1249.1	1256.9	1251.3
165°	1269.2	1268.1	1268.1	1275.9	1270.3
167.5°	1288.2	1284.8	1284.8	1292.6	1287.1
170°	1302.7	1299.3	1298.2	1306.0	1299.3
172.5°	1312.7	1309.4	1308.3	1316.1	1309.4
175°	1320.5	1317.2	1315.0	1322.8	1316.1
177.5°	1325.0	1321.7	1319.4	1326.1	1319.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P999027

CATALOG NUMBER: SA2XXDIP-B865D1080UB50-4F0-XX-W2A-F1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.57	16.41	16.54	17.40	18.70	16.35	17.19	17.33	18.18	19.48
	3H	16.90	17.66	17.89	18.66	19.98	17.97	18.73	18.96	19.73	21.05
	4H	17.31	18.02	18.31	19.02	20.36	18.56	19.28	19.56	20.28	21.61
	6H	17.52	18.18	18.54	19.19	20.54	18.97	19.62	19.98	20.63	21.98
	8H	17.55	18.18	18.57	19.20	20.55	19.07	19.70	20.09	20.72	22.07
	12H	17.54	18.14	18.57	19.16	20.53	19.12	19.71	20.14	20.73	22.10
4H	2H	16.03	16.75	17.04	17.75	19.08	16.68	17.39	17.68	18.39	19.73
	3H	17.55	18.14	18.56	19.18	20.52	18.45	19.05	19.47	20.08	21.43
	4H	18.05	18.60	19.08	19.62	20.99	19.13	19.68	20.16	20.70	22.08
	6H	18.35	18.82	19.39	19.87	21.24	19.63	20.10	20.66	21.15	22.51
	8H	18.41	18.85	19.45	19.89	21.27	19.77	20.21	20.81	21.25	22.63
	12H	18.41	18.81	19.46	19.86	21.25	19.83	20.23	20.89	21.28	22.67
8H	4H	18.23	18.66	19.26	19.71	21.09	19.22	19.66	20.25	20.70	22.08
	6H	18.61	18.97	19.67	20.05	21.43	19.79	20.15	20.85	21.23	22.61
	8H	18.71	19.03	19.78	20.10	21.50	19.97	20.29	21.04	21.36	22.76
	12H	18.74	19.02	19.81	20.08	21.53	20.07	20.35	21.14	21.42	22.86
12H	4H	18.21	18.60	19.26	19.66	21.05	19.18	19.58	20.24	20.63	22.02
	6H	18.63	18.95	19.69	20.01	21.41	19.78	20.10	20.85	21.16	22.56
	8H	18.74	19.02	19.81	20.08	21.52	19.97	20.25	21.04	21.32	22.76

END OF REPORT