

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000045

Luminaire Tested: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000045
REPORT IS A COMBINATION OF REPORTS P988602 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6160.0 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	97	93	89	86	88	85	82	79	70	68	66	56	55	54	44	43	42
2	88	82	76	71	81	75	70	66	62	59	56	50	48	46	39	38	37
3	81	72	65	60	74	66	61	56	55	51	48	45	42	40	36	34	32
4	75	64	57	51	68	59	53	48	50	45	41	41	37	35	32	30	28
5	69	58	50	45	63	53	47	42	45	40	36	37	33	30	29	27	25
6	64	52	44	39	58	48	41	37	41	36	32	34	30	27	27	24	22
7	59	47	40	34	54	44	37	32	37	32	28	31	27	24	25	22	20
8	55	43	36	31	50	40	33	29	34	29	25	28	25	22	23	20	18
9	51	39	32	28	47	37	30	26	31	26	23	26	23	20	21	19	17
10	48	36	29	25	44	34	28	24	29	24	21	24	21	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23476	23476	23476	23476
5°	23531	24936	23613	19921
10°	23273	26356	23438	16450
15°	22767	26365	23153	12359
20°	22160	21793	22641	10196
25°	21423	13618	21886	8673
30°	20483	8719	21040	7468
35°	19339	6701	19966	6390
40°	18063	5632	18837	5589
45°	16701	4794	17400	4692
50°	15305	4074	16020	4058
55°	13760	3540	14501	3493
60°	12384	2699	13042	2667
65°	11102	2031	11760	2304
70°	9688	1622	10446	1879
75°	8190	1242	8939	1420
80°	6499	845	6994	931
85°	4520	437	4944	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21476 cd/sqm

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.7	2.3
10°-20°	392.7	6.4
20°-30°	505.4	8.2
30°-40°	479.4	7.8
40°-50°	410.9	6.7
50°-60°	312.9	5.1
60°-70°	197.3	3.2
70°-80°	98.4	1.6
80°-90°	28.6	0.5
90°-100°	201.2	3.3
100°-110°	708.4	11.5
110°-120°	744.0	12.1
120°-130°	612.1	9.9
130°-140°	491.7	8.0
140°-150°	371.4	6.0
150°-160°	261.1	4.2
160°-170°	153.7	2.5
170°-180°	50.0	0.8
0°-30°	1038.7	16.9
0°-40°	1518.1	24.6
0°-60°	2241.9	36.4
0°-90°	2566.3	41.7
90°-120°	1653.6	26.8
90°-150°	3128.9	50.8
90°-180°	3594.0	58.3
0°-180°	6160.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1483	1483	1483	1483	1483	
5°	1484	1650	1489	1318	1484	141
15°	1399	1862	1422	873	1399	393
25°	1241	994	1268	633	1241	570
35°	1018	490	1051	467	1018	637
45°	765	340	797	333	765	590
55°	516	236	544	233	516	465
65°	312	123	331	139	312	310
75°	146	65	160	74	146	158
85°	32	19	35	20	32	36
90°	1	33	1	33	1	4
95°	35	113	35	113	35	36
105°	121	1118	121	1118	121	129
115°	213	1472	213	1472	213	212
125°	298	1194	298	1194	298	265
135°	349	989	349	989	349	270
145°	399	790	399	790	399	250
155°	454	664	454	664	454	209
165°	494	582	494	582	494	139
175°	515	525	515	525	515	49
180°	516	516	516	516	516	

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1492.4	1498.6	1501.7	1505.8	1515.1	1521.2	1530.5	1532.6	1531.6	1535.7	1524.3
5°	1484.1	1497.5	1509.9	1520.2	1536.7	1547.0	1558.3	1571.7	1574.8	1590.3	1581.0
7.5°	1472.8	1492.4	1509.9	1530.5	1555.3	1568.7	1586.2	1606.8	1616.1	1634.6	1639.8
10°	1454.3	1482.1	1512.0	1533.6	1567.6	1591.3	1607.8	1640.8	1662.4	1690.3	1686.1
12.5°	1424.4	1460.4	1500.6	1536.7	1581.0	1596.5	1627.4	1661.4	1689.2	1715.0	1737.7
15°	1398.6	1439.8	1484.1	1528.5	1579.0	1607.8	1638.7	1683.1	1712.9	1758.3	1777.9
17.5°	1363.6	1416.1	1468.7	1518.2	1577.9	1610.9	1649.0	1692.3	1736.7	1779.9	1795.4
20°	1327.5	1384.2	1440.9	1507.8	1575.9	1607.8	1647.0	1700.6	1743.9	1777.9	1777.9
22.5°	1284.2	1353.2	1418.2	1482.1	1556.3	1602.7	1642.9	1705.7	1736.7	1743.9	1716.0
25°	1240.9	1310.0	1381.1	1460.4	1545.0	1586.2	1631.5	1690.3	1700.6	1671.7	1599.6
27.5°	1189.4	1266.7	1347.1	1432.6	1521.2	1572.8	1614.0	1653.2	1633.6	1556.3	1443.9
30°	1136.8	1220.3	1311.0	1392.4	1499.6	1547.0	1582.1	1593.4	1531.6	1405.8	1260.5
32.5°	1082.2	1163.6	1259.5	1357.4	1465.6	1510.9	1533.6	1503.7	1390.4	1231.6	1054.4
35°	1018.3	1110.0	1210.0	1312.0	1419.2	1453.2	1466.6	1393.4	1248.1	1043.0	866.8
37.5°	960.6	1052.3	1159.5	1263.6	1367.7	1386.2	1372.8	1258.4	1073.9	870.9	698.8
40°	892.5	990.5	1095.6	1212.0	1297.6	1302.7	1269.8	1121.4	892.5	701.9	595.7
42.5°	829.7	928.6	1033.7	1152.3	1217.2	1199.7	1155.4	960.6	745.2	605.0	519.4
45°	764.7	858.5	971.9	1077.0	1123.4	1082.2	1015.2	808.0	625.6	520.5	454.5
47.5°	701.9	789.5	901.8	1002.8	1011.1	964.7	885.3	677.1	542.1	457.6	404.0
50°	640.0	727.6	832.8	916.3	908.0	844.1	754.4	588.5	471.0	404.0	359.7
52.5°	578.2	657.6	759.6	825.6	790.5	728.7	640.0	498.8	411.2	352.5	318.5
55°	516.4	590.6	678.2	732.8	677.1	606.0	543.2	427.7	356.6	309.2	283.4
57.5°	464.8	523.6	604.0	636.9	570.0	514.3	459.7	367.9	309.2	275.2	245.3
60°	408.1	461.7	527.7	547.3	478.2	432.9	386.5	311.3	264.9	235.0	215.4
62.5°	359.7	404.0	454.5	454.5	393.7	359.7	324.7	260.8	222.6	198.9	189.6
65°	312.3	344.2	380.3	376.2	324.7	294.8	266.9	215.4	186.5	170.1	160.8
67.5°	265.9	290.6	314.3	299.9	262.8	237.1	211.3	174.2	154.6	143.3	130.9
70°	223.7	243.2	255.6	242.2	205.1	183.5	164.9	140.2	124.7	110.3	103.1
72.5°	187.6	195.8	199.9	183.5	152.5	140.2	126.8	109.2	95.9	88.6	86.6
75°	146.4	153.6	150.5	138.1	112.3	103.1	92.8	80.4	77.3	73.2	71.1
77.5°	114.4	114.4	109.2	97.9	80.4	73.2	69.1	62.9	59.8	58.7	56.7
80°	81.4	80.4	77.3	64.9	54.6	50.5	50.5	46.4	45.3	43.3	43.3
82.5°	53.6	53.6	49.5	39.2	36.1	35.0	34.0	32.0	32.0	30.9	30.9
85°	32.0	29.9	24.7	21.6	20.6	20.6	19.6	18.6	19.6	18.6	18.6
87.5°	14.4	11.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	1.0	4.0	7.9	9.9	11.9	13.4	14.9	19.8	26.8	32.7	33.7
92.5°	14.9	20.8	28.8	33.7	41.7	47.2	52.6	79.4	117.1	150.8	152.8
95°	34.7	38.7	48.6	57.6	73.4	85.4	97.3	142.9	229.2	344.4	389.0
97.5°	51.6	57.6	68.5	81.4	99.2	112.6	126.0	184.6	304.7	490.2	634.1
100°	76.4	79.4	88.3	104.2	124.0	137.9	151.8	204.4	325.5	539.9	784.0
102.5°	99.2	101.2	110.2	126.0	146.9	160.8	174.7	222.3	326.5	521.0	788.9
105°	121.1	125.0	132.0	146.9	168.7	182.6	196.5	243.1	331.5	495.2	735.4
107.5°	144.9	147.9	154.8	168.7	190.5	204.4	218.3	264.0	342.4	481.3	685.7
110°	168.7	172.7	178.6	191.5	212.4	226.8	241.1	284.8	356.3	477.3	652.0

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	190.5	194.5	201.5	213.4	233.2	248.1	263.0	304.7	371.1	478.3	630.2
115°	213.4	218.3	224.3	236.2	256.0	269.4	282.8	325.5	386.0	482.3	615.3
117.5°	237.2	241.1	247.1	258.0	276.9	290.8	304.7	344.4	401.9	488.2	607.3
120°	259.0	263.0	268.9	277.9	297.7	311.6	325.5	364.2	417.8	494.2	600.4
122.5°	279.8	282.8	288.8	298.7	318.6	333.0	347.3	383.1	431.7	501.1	596.4
125°	297.7	300.7	306.6	318.6	338.4	352.3	366.2	401.9	446.6	508.1	591.5
127.5°	312.6	316.6	324.5	337.4	356.3	370.6	385.0	419.8	460.5	515.0	588.5
130°	325.5	329.5	339.4	353.3	373.1	387.0	400.9	435.7	473.4	523.0	586.5
132.5°	337.4	342.4	353.3	368.2	389.0	402.9	416.8	449.5	486.3	530.9	585.5
135°	349.3	353.3	365.2	380.1	402.9	416.8	430.7	462.4	497.2	536.9	584.5
137.5°	360.2	365.2	377.1	393.0	415.8	428.7	441.6	473.4	506.1	542.8	584.5
140°	373.1	377.1	389.0	404.9	426.7	439.6	452.5	482.3	513.1	546.8	583.5
142.5°	386.0	389.0	399.9	415.8	436.6	448.6	460.5	489.2	519.0	549.8	583.5
145°	398.9	402.9	412.8	427.7	447.6	458.5	469.4	496.2	524.0	551.8	581.5
147.5°	412.8	415.8	425.7	439.6	456.5	466.4	476.3	502.1	527.0	552.8	578.6
150°	426.7	429.7	437.6	450.5	465.4	474.4	483.3	506.1	528.9	551.8	575.6
152.5°	440.6	441.6	449.5	460.5	474.4	482.3	490.2	510.1	529.9	549.8	570.6
155°	453.5	454.5	460.5	471.4	482.3	489.8	497.2	514.1	530.9	547.8	564.7
157.5°	464.4	465.4	470.4	480.3	489.2	495.6	502.1	517.0	530.9	543.8	558.7
160°	475.3	476.3	480.3	488.2	496.2	501.6	507.1	519.0	530.9	540.8	552.8
162.5°	486.3	485.3	489.2	495.2	502.1	506.1	510.1	520.0	529.9	537.9	547.8
165°	494.2	493.2	495.2	501.1	506.1	509.1	512.1	521.0	527.9	533.9	540.8
167.5°	501.1	500.2	502.1	506.1	510.1	512.1	514.1	521.0	527.0	529.9	534.9
170°	508.1	506.1	507.1	510.1	512.1	513.6	515.0	520.0	525.0	527.0	529.9
172.5°	512.1	511.1	510.1	513.1	514.1	515.0	516.0	519.0	522.0	523.0	524.0
175°	515.0	514.1	513.1	515.0	515.0	515.5	516.0	518.0	520.0	519.0	520.0
177.5°	517.0	515.0	514.1	516.0	516.0	516.0	516.0	517.0	519.0	517.0	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1535.7	1537.7	1540.8	1555.3	1557.3	1561.4	1559.4	1559.4	1560.4	1558.3	1559.4
5°	1601.6	1604.7	1620.2	1637.7	1641.8	1637.7	1642.9	1650.1	1650.1	1650.1	1648.0
7.5°	1663.5	1674.8	1692.3	1718.1	1723.3	1728.4	1737.7	1731.5	1733.6	1742.8	1739.7
10°	1723.3	1739.7	1759.3	1781.0	1792.3	1799.5	1803.6	1812.9	1834.6	1809.8	1819.1
12.5°	1779.9	1803.6	1824.3	1848.0	1856.2	1865.5	1868.6	1876.8	1876.8	1875.8	1883.0
15°	1817.0	1838.7	1857.2	1872.7	1874.8	1872.7	1870.6	1871.7	1874.8	1862.4	1869.6
17.5°	1825.3	1827.3	1833.5	1827.3	1828.4	1806.7	1794.4	1791.3	1762.4	1763.4	1787.2
20°	1785.1	1750.1	1740.8	1706.8	1686.1	1630.5	1628.4	1613.0	1552.2	1570.7	1566.6
22.5°	1674.8	1615.0	1535.7	1496.5	1476.9	1418.2	1372.8	1340.9	1319.2	1297.6	1288.3
25°	1529.5	1432.6	1320.3	1243.0	1231.6	1177.0	1093.5	1054.4	1008.0	993.6	1018.3
27.5°	1341.9	1216.2	1089.4	970.9	949.2	899.8	857.5	829.7	776.1	773.0	775.1
30°	1087.3	960.6	854.4	777.1	723.5	700.8	673.0	652.4	630.8	639.0	641.1
32.5°	893.6	773.0	674.0	632.8	608.1	593.7	570.0	556.6	547.3	544.2	543.2
35°	710.1	629.7	585.4	545.2	530.8	520.5	503.0	496.8	488.5	489.6	489.6
37.5°	608.1	541.1	508.1	487.5	474.1	468.9	457.6	451.4	446.3	444.2	447.3
40°	524.6	478.2	457.6	439.1	427.7	425.7	419.5	412.3	406.1	407.1	410.2
42.5°	463.8	437.0	412.3	397.8	389.6	386.5	381.3	376.2	376.2	373.1	372.1
45°	415.4	393.7	373.1	359.7	354.5	350.4	344.2	343.2	339.1	340.1	341.1
47.5°	372.1	354.5	339.1	325.7	320.5	319.5	313.3	309.2	309.2	308.2	307.1
50°	332.9	315.4	302.0	294.8	287.6	285.5	284.5	283.4	281.4	281.4	282.4
52.5°	301.0	283.4	273.1	266.9	262.8	260.8	260.8	259.7	259.7	259.7	258.7
55°	265.9	251.5	243.2	241.2	239.1	238.1	237.1	235.0	234.0	236.0	234.0
57.5°	232.9	227.8	220.6	218.5	213.3	213.3	210.3	208.2	206.1	208.2	208.2
60°	207.2	199.9	195.8	189.6	185.5	181.4	176.2	175.2	173.1	172.1	171.1
62.5°	180.4	174.2	163.9	154.6	148.4	144.3	142.2	141.2	141.2	140.2	140.2
65°	150.5	136.0	130.9	127.8	126.8	125.7	123.7	122.6	123.7	122.6	123.7
67.5°	117.5	115.4	112.3	110.3	109.2	108.2	108.2	107.2	107.2	107.2	107.2
70°	102.0	96.9	95.9	93.8	93.8	92.8	92.8	92.8	92.8	91.7	93.8
72.5°	84.5	81.4	80.4	79.4	79.4	79.4	78.3	78.3	78.3	77.3	78.3
75°	69.1	68.0	66.0	66.0	64.9	66.0	64.9	64.9	63.9	64.9	64.9
77.5°	55.7	54.6	53.6	53.6	52.6	52.6	52.6	52.6	52.6	52.6	53.6
80°	42.3	41.2	40.2	41.2	40.2	41.2	40.2	40.2	41.2	40.2	40.2
82.5°	30.9	29.9	29.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9
85°	18.6	17.5	17.5	18.6	17.5	18.6	17.5	17.5	17.5	18.6	18.6
87.5°	8.2	9.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.3
90°	32.7	31.8	29.8	31.8	32.2	32.7	32.7	32.7	32.7	32.7	32.7
92.5°	128.0	100.2	85.3	74.4	70.4	66.5	65.5	61.5	62.5	60.5	62.5
95°	340.4	260.0	199.5	157.8	146.9	136.0	123.1	115.1	112.1	113.1	112.1
97.5°	639.1	531.9	424.7	324.5	294.8	265.0	226.3	206.4	195.5	189.5	195.5
100°	926.9	906.0	783.0	647.0	587.0	527.0	444.6	401.9	373.1	355.3	373.1
102.5°	1034.1	1151.2	1147.2	1056.9	992.4	927.9	836.6	756.2	718.5	692.7	718.5
105°	999.3	1205.7	1317.9	1330.8	1314.4	1298.0	1236.5	1175.0	1132.3	1118.4	1132.3
107.5°	925.9	1147.2	1313.9	1411.2	1431.1	1450.9	1449.9	1440.9	1428.0	1405.2	1428.0
110°	857.4	1066.8	1244.4	1371.5	1412.2	1452.8	1495.5	1514.4	1523.3	1522.3	1523.3

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	809.8	993.4	1162.1	1300.0	1348.2	1396.3	1459.8	1494.5	1513.4	1520.3	1513.4
115°	772.1	935.8	1088.6	1218.6	1269.8	1320.9	1391.3	1437.0	1462.8	1471.7	1462.8
117.5°	746.3	888.2	1025.1	1146.2	1194.8	1243.4	1315.9	1364.5	1391.3	1398.3	1391.3
120°	726.4	854.4	977.5	1082.7	1127.8	1173.0	1242.5	1289.1	1317.9	1327.8	1317.9
122.5°	709.5	827.6	937.8	1036.0	1075.7	1115.4	1176.0	1221.6	1246.4	1254.4	1246.4
125°	693.7	801.8	904.1	991.4	1028.6	1065.8	1123.4	1161.1	1185.9	1193.8	1185.9
127.5°	678.8	776.0	870.3	953.7	988.4	1023.1	1073.8	1109.5	1131.3	1137.3	1131.3
130°	663.9	751.2	836.6	915.0	947.8	980.5	1029.1	1062.8	1082.7	1090.6	1082.7
132.5°	652.0	727.4	804.8	875.3	905.6	935.8	983.4	1017.2	1035.0	1042.0	1035.0
135°	641.1	705.6	771.1	836.6	864.4	892.1	934.8	967.6	985.4	989.4	985.4
137.5°	633.1	687.7	744.3	797.9	822.7	847.5	888.2	917.0	932.8	938.8	932.8
140°	626.2	670.8	718.5	764.1	786.0	807.8	839.5	865.4	880.2	886.2	880.2
142.5°	619.2	657.0	695.7	733.4	750.8	768.1	797.9	820.7	833.6	833.6	833.6
145°	613.3	644.1	676.8	707.6	722.0	736.3	760.2	777.0	787.0	789.9	787.0
147.5°	607.3	634.1	660.9	685.7	696.7	707.6	728.4	742.3	749.2	751.2	749.2
150°	599.4	623.2	645.0	665.9	674.8	683.7	698.6	710.5	716.5	717.5	716.5
152.5°	592.4	612.3	632.1	649.0	656.4	663.9	674.8	684.7	688.7	688.7	688.7
155°	583.5	602.4	618.2	633.1	638.6	644.1	655.0	661.9	665.9	663.9	665.9
157.5°	575.6	590.5	604.4	617.3	621.8	626.2	634.1	640.1	642.1	642.1	642.1
160°	566.6	579.5	590.5	601.4	604.8	608.3	615.3	620.2	621.2	621.2	621.2
162.5°	558.7	568.6	577.6	586.5	589.0	591.5	598.4	601.4	602.4	601.4	602.4
165°	549.8	557.7	564.7	571.6	573.6	575.6	579.5	583.5	583.5	582.5	583.5
167.5°	540.8	546.8	552.8	557.7	559.7	561.7	563.7	565.7	565.7	564.7	565.7
170°	533.9	538.9	541.8	545.8	546.8	547.8	548.8	551.8	550.8	548.8	550.8
172.5°	527.0	529.9	531.9	534.9	535.4	535.9	536.9	537.9	536.9	535.9	536.9
175°	521.0	524.0	525.0	526.0	526.5	527.0	527.0	527.9	527.0	525.0	527.0
177.5°	517.0	519.0	519.0	520.0	520.0	520.0	520.0	520.0	519.0	517.0	519.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1563.5	1556.3	1554.2	1556.3	1554.2	1555.3	1548.0	1521.2	1528.5	1517.1	1523.3
5°	1652.1	1646.0	1632.6	1630.5	1628.4	1626.4	1616.1	1592.4	1583.1	1567.6	1566.6
7.5°	1736.7	1736.7	1726.3	1719.1	1709.9	1702.6	1689.2	1654.2	1639.8	1621.2	1610.9
10°	1820.1	1793.3	1804.7	1797.5	1774.8	1770.7	1745.9	1725.3	1697.5	1678.9	1662.4
12.5°	1879.9	1871.7	1861.4	1855.2	1849.0	1835.6	1819.1	1766.5	1752.1	1715.0	1696.5
15°	1877.9	1872.7	1875.8	1875.8	1873.7	1870.6	1857.2	1819.1	1794.4	1758.3	1726.3
17.5°	1776.8	1790.2	1803.6	1812.9	1833.5	1842.8	1855.2	1832.5	1817.0	1786.1	1752.1
20°	1600.6	1633.6	1672.8	1681.0	1699.5	1754.2	1778.9	1798.5	1804.7	1794.4	1766.5
22.5°	1355.3	1383.1	1478.0	1475.9	1502.7	1567.6	1639.8	1698.5	1744.9	1770.7	1760.4
25°	1061.6	1100.7	1151.2	1189.4	1277.0	1373.9	1463.5	1557.3	1637.7	1708.8	1726.3
27.5°	802.9	854.4	894.6	945.1	989.4	1103.8	1219.3	1365.6	1459.4	1594.4	1664.5
30°	649.3	673.0	713.2	736.9	758.6	846.2	977.1	1121.4	1286.3	1441.9	1562.5
32.5°	554.5	571.0	600.9	611.2	633.9	692.6	775.1	907.0	1077.0	1265.6	1424.4
35°	497.8	515.3	521.5	530.8	549.3	586.4	643.1	739.0	892.5	1077.0	1266.7
37.5°	449.4	458.6	476.2	482.3	488.5	516.4	554.5	621.5	723.5	875.0	1085.3
40°	415.4	420.5	429.8	434.9	439.1	458.6	492.7	538.0	613.2	728.7	922.4
42.5°	379.3	385.5	391.6	397.8	403.0	418.4	439.1	482.3	532.8	620.5	760.6
45°	344.2	348.4	355.6	359.7	366.9	379.3	397.8	427.7	473.1	528.7	642.1
47.5°	312.3	317.4	320.5	325.7	330.8	344.2	361.8	381.3	418.4	473.1	555.5
50°	283.4	289.6	293.7	294.8	298.9	311.3	325.7	347.3	371.0	413.3	485.4
52.5°	262.8	263.8	266.9	271.1	270.0	277.2	290.6	307.1	331.9	365.9	418.4
55°	239.1	242.2	244.3	245.3	245.3	251.5	258.7	274.2	293.7	321.6	365.9
57.5°	209.2	212.3	218.5	220.6	223.7	226.7	229.8	240.1	256.6	283.4	319.5
60°	178.3	180.4	186.5	190.7	192.7	201.0	205.1	213.3	222.6	242.2	276.2
62.5°	143.3	145.3	148.4	152.5	156.7	169.0	179.3	187.6	194.8	208.2	236.0
65°	124.7	125.7	127.8	128.8	129.9	135.0	144.3	155.6	169.0	179.3	195.8
67.5°	108.2	109.2	110.3	112.3	113.4	114.4	118.5	121.6	135.0	149.4	161.8
70°	92.8	94.8	95.9	95.9	96.9	98.9	101.0	105.1	109.2	116.5	131.9
72.5°	78.3	79.4	81.4	81.4	81.4	83.5	85.5	87.6	89.7	93.8	100.0
75°	64.9	67.0	67.0	67.0	68.0	68.0	70.1	72.1	74.2	77.3	79.4
77.5°	53.6	53.6	53.6	53.6	54.6	54.6	55.7	57.7	58.7	59.8	61.8
80°	40.2	41.2	41.2	41.2	42.3	42.3	42.3	44.3	45.3	45.3	47.4
82.5°	29.9	29.9	29.9	30.9	29.9	30.9	30.9	32.0	30.9	32.0	33.0
85°	18.6	18.6	18.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	20.6
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.3	9.3	9.3
90°	32.7	32.7	32.7	32.2	31.8	29.8	31.8	32.7	33.7	32.7	26.8
92.5°	61.5	65.5	66.5	70.4	74.4	85.3	100.2	128.0	152.8	150.8	117.1
95°	115.1	123.1	136.0	146.9	157.8	199.5	260.0	340.4	389.0	344.4	229.2
97.5°	206.4	226.3	265.0	294.8	324.5	424.7	531.9	639.1	634.1	490.2	304.7
100°	401.9	444.6	527.0	587.0	647.0	783.0	906.0	926.9	784.0	539.9	325.5
102.5°	756.2	836.6	927.9	992.4	1056.9	1147.2	1151.2	1034.1	788.9	521.0	326.5
105°	1175.0	1236.5	1298.0	1314.4	1330.8	1317.9	1205.7	999.3	735.4	495.2	331.5
107.5°	1440.9	1449.9	1450.9	1431.1	1411.2	1313.9	1147.2	925.9	685.7	481.3	342.4
110°	1514.4	1495.5	1452.8	1412.2	1371.5	1244.4	1066.8	857.4	652.0	477.3	356.3

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1494.5	1459.8	1396.3	1348.2	1300.0	1162.1	993.4	809.8	630.2	478.3	371.1
115°	1437.0	1391.3	1320.9	1269.8	1218.6	1088.6	935.8	772.1	615.3	482.3	386.0
117.5°	1364.5	1315.9	1243.4	1194.8	1146.2	1025.1	888.2	746.3	607.3	488.2	401.9
120°	1289.1	1242.5	1173.0	1127.8	1082.7	977.5	854.4	726.4	600.4	494.2	417.8
122.5°	1221.6	1176.0	1115.4	1075.7	1036.0	937.8	827.6	709.5	596.4	501.1	431.7
125°	1161.1	1123.4	1065.8	1028.6	991.4	904.1	801.8	693.7	591.5	508.1	446.6
127.5°	1109.5	1073.8	1023.1	988.4	953.7	870.3	776.0	678.8	588.5	515.0	460.5
130°	1062.8	1029.1	980.5	947.8	915.0	836.6	751.2	663.9	586.5	523.0	473.4
132.5°	1017.2	983.4	935.8	905.6	875.3	804.8	727.4	652.0	585.5	530.9	486.3
135°	967.6	934.8	892.1	864.4	836.6	771.1	705.6	641.1	584.5	536.9	497.2
137.5°	917.0	888.2	847.5	822.7	797.9	744.3	687.7	633.1	584.5	542.8	506.1
140°	865.4	839.5	807.8	786.0	764.1	718.5	670.8	626.2	583.5	546.8	513.1
142.5°	820.7	797.9	768.1	750.8	733.4	695.7	657.0	619.2	583.5	549.8	519.0
145°	777.0	760.2	736.3	722.0	707.6	676.8	644.1	613.3	581.5	551.8	524.0
147.5°	742.3	728.4	707.6	696.7	685.7	660.9	634.1	607.3	578.6	552.8	527.0
150°	710.5	698.6	683.7	674.8	665.9	645.0	623.2	599.4	575.6	551.8	528.9
152.5°	684.7	674.8	663.9	656.4	649.0	632.1	612.3	592.4	570.6	549.8	529.9
155°	661.9	655.0	644.1	638.6	633.1	618.2	602.4	583.5	564.7	547.8	530.9
157.5°	640.1	634.1	626.2	621.8	617.3	604.4	590.5	575.6	558.7	543.8	530.9
160°	620.2	615.3	608.3	604.8	601.4	590.5	579.5	566.6	552.8	540.8	530.9
162.5°	601.4	598.4	591.5	589.0	586.5	577.6	568.6	558.7	547.8	537.9	529.9
165°	583.5	579.5	575.6	573.6	571.6	564.7	557.7	549.8	540.8	533.9	527.9
167.5°	565.7	563.7	561.7	559.7	557.7	552.8	546.8	540.8	534.9	529.9	527.0
170°	551.8	548.8	547.8	546.8	545.8	541.8	538.9	533.9	529.9	527.0	525.0
172.5°	537.9	536.9	535.9	535.4	534.9	531.9	529.9	527.0	524.0	523.0	522.0
175°	527.9	527.0	527.0	526.5	526.0	525.0	524.0	521.0	520.0	519.0	520.0
177.5°	520.0	520.0	520.0	520.0	520.0	519.0	519.0	517.0	516.0	517.0	519.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1514.0	1508.9	1508.9	1505.8	1505.8	1489.3	1489.3	1494.4	1488.3	1481.0	1470.7
5°	1553.2	1541.9	1538.8	1534.6	1521.2	1500.6	1492.4	1489.3	1476.9	1461.5	1443.9
7.5°	1590.3	1571.7	1562.5	1553.2	1535.7	1506.8	1490.3	1479.0	1460.4	1436.7	1414.1
10°	1626.4	1602.7	1579.0	1567.6	1542.9	1506.8	1483.1	1464.6	1437.8	1405.8	1373.9
12.5°	1659.4	1609.9	1605.8	1583.1	1547.0	1505.8	1469.7	1442.9	1408.9	1371.8	1334.7
15°	1688.2	1637.7	1613.0	1592.4	1545.0	1493.4	1455.3	1422.3	1377.0	1334.7	1289.3
17.5°	1702.6	1648.0	1631.5	1597.5	1549.1	1482.1	1430.5	1390.4	1340.9	1290.4	1238.8
20°	1717.1	1653.2	1626.4	1602.7	1536.7	1460.4	1402.7	1356.3	1301.7	1241.9	1185.3
22.5°	1724.3	1653.2	1621.2	1588.2	1524.3	1436.7	1368.7	1314.1	1250.2	1189.4	1121.4
25°	1711.9	1647.0	1608.9	1574.8	1502.7	1407.9	1329.5	1267.7	1199.7	1130.6	1061.6
27.5°	1681.0	1632.6	1588.2	1553.2	1472.8	1370.8	1288.3	1218.2	1148.1	1070.8	1000.8
30°	1623.3	1601.6	1566.6	1527.4	1439.8	1337.8	1239.9	1167.7	1090.4	1013.1	940.0
32.5°	1533.6	1552.2	1529.5	1495.5	1400.7	1292.4	1188.3	1115.2	1030.7	947.2	880.2
35°	1424.4	1490.3	1478.0	1454.3	1359.4	1244.0	1139.9	1051.3	966.8	882.2	815.2
37.5°	1304.8	1404.8	1415.1	1400.7	1312.0	1194.5	1080.1	993.6	907.0	821.4	753.4
40°	1140.9	1294.5	1327.5	1333.7	1262.6	1134.8	1015.2	930.7	845.1	761.7	679.2
42.5°	990.5	1184.2	1225.4	1251.2	1199.7	1076.0	955.4	861.6	777.1	701.9	619.4
45°	849.3	1051.3	1118.3	1151.2	1128.6	1009.0	884.3	796.7	719.4	650.3	571.0
47.5°	703.9	907.0	1000.8	1053.3	1053.3	941.0	816.3	729.7	655.5	596.7	526.7
50°	607.1	776.1	873.0	942.0	960.6	871.9	754.4	669.9	599.8	535.9	482.3
52.5°	517.4	668.9	749.3	821.4	875.0	797.7	685.4	609.1	540.1	480.3	438.0
55°	447.3	560.7	633.9	713.2	773.0	722.5	618.4	544.2	484.4	434.9	398.9
57.5°	380.3	479.3	539.0	609.1	673.0	634.9	551.4	487.5	434.9	391.6	359.7
60°	323.6	404.0	450.4	505.0	584.4	557.6	488.5	429.8	387.5	348.4	321.6
62.5°	275.2	339.1	378.3	417.4	489.6	477.2	423.6	378.3	342.2	309.2	286.5
65°	225.7	278.3	309.2	343.2	400.9	406.1	362.8	330.8	297.9	269.0	248.4
67.5°	182.4	223.7	251.5	280.3	326.7	341.1	311.3	284.5	256.6	232.9	214.4
70°	147.4	176.2	196.9	219.5	257.7	275.2	259.7	241.2	218.5	198.9	182.4
72.5°	116.5	135.0	147.4	164.9	195.8	213.3	212.3	195.8	179.3	165.9	152.5
75°	85.5	100.0	110.3	121.6	146.4	162.8	167.0	159.8	143.3	133.0	122.6
77.5°	64.9	73.2	78.3	86.6	104.1	118.5	124.7	122.6	111.3	103.1	95.9
80°	49.5	51.5	53.6	56.7	71.1	84.5	88.6	87.6	81.4	78.3	70.1
82.5°	35.0	36.1	37.1	38.1	43.3	54.6	58.7	60.8	55.7	52.6	45.3
85°	20.6	21.6	21.6	23.7	24.7	27.8	35.0	35.0	34.0	29.9	28.9
87.5°	10.3	10.3	9.3	9.3	10.3	11.3	13.4	15.5	13.4	12.4	11.3
90°	19.8	14.9	13.4	11.9	9.9	7.9	4.0	1.0	4.0	7.9	9.9
92.5°	79.4	52.6	47.2	41.7	33.7	28.8	20.8	14.9	20.8	28.8	33.7
95°	142.9	97.3	85.4	73.4	57.6	48.6	38.7	34.7	38.7	48.6	57.6
97.5°	184.6	126.0	112.6	99.2	81.4	68.5	57.6	51.6	57.6	68.5	81.4
100°	204.4	151.8	137.9	124.0	104.2	88.3	79.4	76.4	79.4	88.3	104.2
102.5°	222.3	174.7	160.8	146.9	126.0	110.2	101.2	99.2	101.2	110.2	126.0
105°	243.1	196.5	182.6	168.7	146.9	132.0	125.0	121.1	125.0	132.0	146.9
107.5°	264.0	218.3	204.4	190.5	168.7	154.8	147.9	144.9	147.9	154.8	168.7
110°	284.8	241.1	226.8	212.4	191.5	178.6	172.7	168.7	172.7	178.6	191.5

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	304.7	263.0	248.1	233.2	213.4	201.5	194.5	190.5	194.5	201.5	213.4
115°	325.5	282.8	269.4	256.0	236.2	224.3	218.3	213.4	218.3	224.3	236.2
117.5°	344.4	304.7	290.8	276.9	258.0	247.1	241.1	237.2	241.1	247.1	258.0
120°	364.2	325.5	311.6	297.7	277.9	268.9	263.0	259.0	263.0	268.9	277.9
122.5°	383.1	347.3	333.0	318.6	298.7	288.8	282.8	279.8	282.8	288.8	298.7
125°	401.9	366.2	352.3	338.4	318.6	306.6	300.7	297.7	300.7	306.6	318.6
127.5°	419.8	385.0	370.6	356.3	337.4	324.5	316.6	312.6	316.6	324.5	337.4
130°	435.7	400.9	387.0	373.1	353.3	339.4	329.5	325.5	329.5	339.4	353.3
132.5°	449.5	416.8	402.9	389.0	368.2	353.3	342.4	337.4	342.4	353.3	368.2
135°	462.4	430.7	416.8	402.9	380.1	365.2	353.3	349.3	353.3	365.2	380.1
137.5°	473.4	441.6	428.7	415.8	393.0	377.1	365.2	360.2	365.2	377.1	393.0
140°	482.3	452.5	439.6	426.7	404.9	389.0	377.1	373.1	377.1	389.0	404.9
142.5°	489.2	460.5	448.6	436.6	415.8	399.9	389.0	386.0	389.0	399.9	415.8
145°	496.2	469.4	458.5	447.6	427.7	412.8	402.9	398.9	402.9	412.8	427.7
147.5°	502.1	476.3	466.4	456.5	439.6	425.7	415.8	412.8	415.8	425.7	439.6
150°	506.1	483.3	474.4	465.4	450.5	437.6	429.7	426.7	429.7	437.6	450.5
152.5°	510.1	490.2	482.3	474.4	460.5	449.5	441.6	440.6	441.6	449.5	460.5
155°	514.1	497.2	489.8	482.3	471.4	460.5	454.5	453.5	454.5	460.5	471.4
157.5°	517.0	502.1	495.6	489.2	480.3	470.4	465.4	464.4	465.4	470.4	480.3
160°	519.0	507.1	501.6	496.2	488.2	480.3	476.3	475.3	476.3	480.3	488.2
162.5°	520.0	510.1	506.1	502.1	495.2	489.2	485.3	486.3	485.3	489.2	495.2
165°	521.0	512.1	509.1	506.1	501.1	495.2	493.2	494.2	493.2	495.2	501.1
167.5°	521.0	514.1	512.1	510.1	506.1	502.1	500.2	501.1	500.2	502.1	506.1
170°	520.0	515.0	513.6	512.1	510.1	507.1	506.1	508.1	506.1	507.1	510.1
172.5°	519.0	516.0	515.0	514.1	513.1	510.1	511.1	512.1	511.1	510.1	513.1
175°	518.0	516.0	515.5	515.0	515.0	513.1	514.1	515.0	514.1	513.1	515.0
177.5°	517.0	516.0	516.0	516.0	516.0	514.1	515.0	517.0	515.0	514.1	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1466.6	1467.7	1470.7	1461.5	1447.0	1440.9	1422.3	1419.2	1416.1	1416.1	1419.2
5°	1433.6	1429.5	1430.5	1413.0	1392.4	1380.0	1354.3	1358.4	1345.0	1336.8	1338.8
7.5°	1397.6	1386.2	1385.2	1362.5	1336.8	1314.1	1287.3	1281.1	1268.7	1254.3	1248.1
10°	1352.2	1344.0	1328.5	1302.7	1269.8	1251.2	1215.1	1193.5	1190.4	1168.8	1160.5
12.5°	1305.8	1291.4	1275.9	1239.9	1202.8	1172.9	1146.1	1122.4	1105.9	1087.3	1075.0
15°	1252.2	1234.7	1217.2	1179.1	1135.8	1105.9	1065.7	1030.7	982.2	944.1	922.4
17.5°	1193.5	1173.9	1150.2	1108.0	1065.7	1024.5	950.3	909.0	875.0	852.4	839.0
20°	1132.7	1111.0	1087.3	1045.1	971.9	899.8	858.5	826.6	806.0	783.3	766.8
22.5°	1068.8	1046.1	1020.3	954.4	877.1	826.6	794.6	764.7	734.9	722.5	714.2
25°	1009.0	988.4	955.4	865.7	804.9	758.6	722.5	702.9	687.4	671.0	655.5
27.5°	947.2	909.0	862.7	787.4	749.3	701.9	676.1	661.7	634.9	623.5	616.3
30°	873.0	830.7	786.4	732.8	688.5	655.5	631.8	608.1	592.6	581.3	568.9
32.5°	797.7	757.5	729.7	674.0	641.1	607.1	584.4	570.0	547.3	540.1	534.9
35°	732.8	698.8	674.0	628.7	597.8	566.9	550.4	528.7	514.3	500.9	492.7
37.5°	668.9	650.3	624.6	586.4	553.5	528.7	506.1	498.8	479.3	472.0	463.8
40°	624.6	596.7	575.1	542.1	514.3	487.5	473.1	456.6	443.2	431.8	428.8
42.5°	571.0	550.4	538.0	501.9	473.1	457.6	440.1	421.5	411.2	402.0	390.6
45°	530.8	512.2	494.7	465.9	440.1	420.5	405.0	392.7	375.2	371.0	353.5
47.5°	488.5	470.0	456.6	427.7	404.0	385.5	374.1	357.6	343.2	333.9	325.7
50°	446.3	430.8	418.4	393.7	373.1	353.5	338.1	321.6	315.4	299.9	294.8
52.5°	406.1	395.8	382.4	358.7	338.1	321.6	305.1	291.7	282.4	274.2	268.0
55°	372.1	355.6	349.4	323.6	306.1	288.6	274.2	265.9	254.6	249.4	244.3
57.5°	333.9	324.7	314.3	294.8	275.2	258.7	248.4	236.0	229.8	223.7	219.5
60°	301.0	287.6	279.3	262.8	245.3	229.8	220.6	211.3	203.0	197.9	189.6
62.5°	262.8	252.5	247.4	229.8	215.4	201.0	192.7	183.5	177.3	168.0	157.7
65°	229.8	221.6	215.4	201.0	187.6	174.2	165.9	154.6	146.4	141.2	140.2
67.5°	201.0	194.8	185.5	172.1	158.7	148.4	139.1	129.9	128.8	126.8	126.8
70°	169.0	162.8	157.7	143.3	131.9	120.6	118.5	115.4	112.3	111.3	109.2
72.5°	141.2	136.0	129.9	117.5	106.2	103.1	101.0	98.9	95.9	94.8	93.8
75°	114.4	107.2	103.1	91.7	88.6	86.6	84.5	81.4	79.4	78.3	76.3
77.5°	87.6	80.4	80.4	74.2	72.1	69.1	67.0	64.9	63.9	61.8	61.8
80°	61.8	61.8	59.8	56.7	53.6	52.6	49.5	48.4	47.4	48.4	46.4
82.5°	45.3	41.2	41.2	39.2	37.1	36.1	34.0	34.0	33.0	33.0	33.0
85°	25.8	25.8	24.7	22.7	21.6	21.6	20.6	20.6	19.6	19.6	18.6
87.5°	10.3	9.3	10.3	9.3	9.3	8.2	8.2	8.2	7.2	8.2	7.2
90°	11.9	13.4	14.9	19.8	26.8	32.7	33.7	32.7	31.8	29.8	31.8
92.5°	41.7	47.2	52.6	79.4	117.1	150.8	152.8	128.0	100.2	85.3	74.4
95°	73.4	85.4	97.3	142.9	229.2	344.4	389.0	340.4	260.0	199.5	157.8
97.5°	99.2	112.6	126.0	184.6	304.7	490.2	634.1	639.1	531.9	424.7	324.5
100°	124.0	137.9	151.8	204.4	325.5	539.9	784.0	926.9	906.0	783.0	647.0
102.5°	146.9	160.8	174.7	222.3	326.5	521.0	788.9	1034.1	1151.2	1147.2	1056.9
105°	168.7	182.6	196.5	243.1	331.5	495.2	735.4	999.3	1205.7	1317.9	1330.8
107.5°	190.5	204.4	218.3	264.0	342.4	481.3	685.7	925.9	1147.2	1313.9	1411.2
110°	212.4	226.8	241.1	284.8	356.3	477.3	652.0	857.4	1066.8	1244.4	1371.5

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	233.2	248.1	263.0	304.7	371.1	478.3	630.2	809.8	993.4	1162.1	1300.0
115°	256.0	269.4	282.8	325.5	386.0	482.3	615.3	772.1	935.8	1088.6	1218.6
117.5°	276.9	290.8	304.7	344.4	401.9	488.2	607.3	746.3	888.2	1025.1	1146.2
120°	297.7	311.6	325.5	364.2	417.8	494.2	600.4	726.4	854.4	977.5	1082.7
122.5°	318.6	333.0	347.3	383.1	431.7	501.1	596.4	709.5	827.6	937.8	1036.0
125°	338.4	352.3	366.2	401.9	446.6	508.1	591.5	693.7	801.8	904.1	991.4
127.5°	356.3	370.6	385.0	419.8	460.5	515.0	588.5	678.8	776.0	870.3	953.7
130°	373.1	387.0	400.9	435.7	473.4	523.0	586.5	663.9	751.2	836.6	915.0
132.5°	389.0	402.9	416.8	449.5	486.3	530.9	585.5	652.0	727.4	804.8	875.3
135°	402.9	416.8	430.7	462.4	497.2	536.9	584.5	641.1	705.6	771.1	836.6
137.5°	415.8	428.7	441.6	473.4	506.1	542.8	584.5	633.1	687.7	744.3	797.9
140°	426.7	439.6	452.5	482.3	513.1	546.8	583.5	626.2	670.8	718.5	764.1
142.5°	436.6	448.6	460.5	489.2	519.0	549.8	583.5	619.2	657.0	695.7	733.4
145°	447.6	458.5	469.4	496.2	524.0	551.8	581.5	613.3	644.1	676.8	707.6
147.5°	456.5	466.4	476.3	502.1	527.0	552.8	578.6	607.3	634.1	660.9	685.7
150°	465.4	474.4	483.3	506.1	528.9	551.8	575.6	599.4	623.2	645.0	665.9
152.5°	474.4	482.3	490.2	510.1	529.9	549.8	570.6	592.4	612.3	632.1	649.0
155°	482.3	489.8	497.2	514.1	530.9	547.8	564.7	583.5	602.4	618.2	633.1
157.5°	489.2	495.6	502.1	517.0	530.9	543.8	558.7	575.6	590.5	604.4	617.3
160°	496.2	501.6	507.1	519.0	530.9	540.8	552.8	566.6	579.5	590.5	601.4
162.5°	502.1	506.1	510.1	520.0	529.9	537.9	547.8	558.7	568.6	577.6	586.5
165°	506.1	509.1	512.1	521.0	527.9	533.9	540.8	549.8	557.7	564.7	571.6
167.5°	510.1	512.1	514.1	521.0	527.0	529.9	534.9	540.8	546.8	552.8	557.7
170°	512.1	513.6	515.0	520.0	525.0	527.0	529.9	533.9	538.9	541.8	545.8
172.5°	514.1	515.0	516.0	519.0	522.0	523.0	524.0	527.0	529.9	531.9	534.9
175°	515.0	515.5	516.0	518.0	520.0	519.0	520.0	521.0	524.0	525.0	526.0
177.5°	516.0	516.0	516.0	517.0	519.0	517.0	516.0	517.0	519.0	519.0	520.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1419.2	1417.1	1411.0	1413.0	1409.9	1409.9	1407.9	1407.9	1407.9	1413.0	1409.9
5°	1341.9	1334.7	1327.5	1324.4	1321.3	1318.2	1318.2	1317.2	1326.5	1324.4	1332.6
7.5°	1246.1	1244.0	1229.6	1229.6	1224.4	1222.4	1227.5	1228.5	1229.6	1231.6	1236.8
10°	1160.5	1155.4	1134.8	1136.8	1133.7	1129.6	1132.7	1130.6	1137.8	1139.9	1137.8
12.5°	1059.5	1050.2	1027.6	1016.2	1003.9	994.6	1005.9	997.7	1026.5	1034.8	1057.5
15°	925.5	908.0	892.5	892.5	881.2	873.0	878.1	887.4	893.6	902.9	907.0
17.5°	835.9	828.6	816.3	809.1	806.0	802.9	802.9	807.0	820.4	819.4	827.6
20°	759.6	755.5	749.3	740.0	736.9	734.9	734.9	734.9	744.1	752.4	757.5
22.5°	707.0	703.9	699.8	687.4	681.3	679.2	684.4	687.4	694.7	700.8	706.0
25°	654.5	647.3	640.0	635.9	632.8	632.8	634.9	635.9	639.0	642.1	648.3
27.5°	611.2	606.0	595.7	584.4	584.4	581.3	583.4	585.4	592.6	602.9	608.1
30°	562.7	561.7	557.6	553.5	549.3	547.3	551.4	554.5	555.5	560.7	560.7
32.5°	527.7	520.5	513.3	509.1	507.1	506.1	507.1	511.2	511.2	517.4	524.6
35°	492.7	488.5	481.3	474.1	472.0	466.9	471.0	475.1	482.3	485.4	488.5
37.5°	454.5	449.4	446.3	444.2	440.1	441.1	438.0	444.2	450.4	449.4	451.4
40°	425.7	416.4	407.1	406.1	405.0	404.0	404.0	405.0	409.2	413.3	419.5
42.5°	388.6	385.5	377.2	369.0	366.9	364.9	362.8	366.9	375.2	382.4	385.5
45°	350.4	346.3	344.2	338.1	333.9	332.9	330.8	336.0	343.2	346.3	348.4
47.5°	315.4	314.3	308.2	309.2	306.1	307.1	306.1	309.2	309.2	312.3	314.3
50°	291.7	288.6	285.5	283.4	280.3	280.3	279.3	280.3	284.5	288.6	287.6
52.5°	268.0	262.8	261.8	260.8	258.7	260.8	257.7	258.7	262.8	264.9	263.8
55°	240.1	239.1	237.1	235.0	234.0	232.9	232.9	232.9	237.1	240.1	241.2
57.5°	218.5	213.3	209.2	209.2	205.1	204.1	206.1	207.2	210.3	212.3	214.4
60°	188.6	186.5	180.4	177.3	171.1	170.1	170.1	174.2	179.3	186.5	188.6
62.5°	156.7	153.6	152.5	152.5	152.5	152.5	152.5	152.5	152.5	153.6	153.6
65°	139.1	140.2	139.1	138.1	139.1	139.1	138.1	138.1	138.1	139.1	140.2
67.5°	124.7	123.7	124.7	123.7	122.6	122.6	121.6	122.6	123.7	124.7	124.7
70°	108.2	108.2	107.2	108.2	107.2	106.2	105.1	105.1	107.2	108.2	108.2
72.5°	92.8	92.8	91.7	91.7	89.7	89.7	90.7	89.7	89.7	92.8	92.8
75°	77.3	76.3	75.2	75.2	74.2	74.2	74.2	73.2	75.2	75.2	76.3
77.5°	60.8	60.8	60.8	59.8	59.8	58.7	58.7	59.8	59.8	59.8	60.8
80°	46.4	46.4	46.4	45.3	44.3	44.3	44.3	44.3	44.3	45.3	44.3
82.5°	32.0	32.0	32.0	32.0	32.0	30.9	30.9	30.9	32.0	32.0	30.9
85°	19.6	18.6	19.6	19.6	18.6	19.6	18.6	18.6	17.5	17.5	18.6
87.5°	8.2	7.2	6.2	6.2	7.2	6.2	6.2	6.2	7.2	6.2	6.2
90°	32.2	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.2
92.5°	70.4	66.5	65.5	61.5	62.5	60.5	62.5	61.5	65.5	66.5	70.4
95°	146.9	136.0	123.1	115.1	112.1	113.1	112.1	115.1	123.1	136.0	146.9
97.5°	294.8	265.0	226.3	206.4	195.5	189.5	195.5	206.4	226.3	265.0	294.8
100°	587.0	527.0	444.6	401.9	373.1	355.3	373.1	401.9	444.6	527.0	587.0
102.5°	992.4	927.9	836.6	756.2	718.5	692.7	718.5	756.2	836.6	927.9	992.4
105°	1314.4	1298.0	1236.5	1175.0	1132.3	1118.4	1132.3	1175.0	1236.5	1298.0	1314.4
107.5°	1431.1	1450.9	1449.9	1440.9	1428.0	1405.2	1428.0	1440.9	1449.9	1450.9	1431.1
110°	1412.2	1452.8	1495.5	1514.4	1523.3	1522.3	1523.3	1514.4	1495.5	1452.8	1412.2

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1348.2	1396.3	1459.8	1494.5	1513.4	1520.3	1513.4	1494.5	1459.8	1396.3	1348.2
115°	1269.8	1320.9	1391.3	1437.0	1462.8	1471.7	1462.8	1437.0	1391.3	1320.9	1269.8
117.5°	1194.8	1243.4	1315.9	1364.5	1391.3	1398.3	1391.3	1364.5	1315.9	1243.4	1194.8
120°	1127.8	1173.0	1242.5	1289.1	1317.9	1327.8	1317.9	1289.1	1242.5	1173.0	1127.8
122.5°	1075.7	1115.4	1176.0	1221.6	1246.4	1254.4	1246.4	1221.6	1176.0	1115.4	1075.7
125°	1028.6	1065.8	1123.4	1161.1	1185.9	1193.8	1185.9	1161.1	1123.4	1065.8	1028.6
127.5°	988.4	1023.1	1073.8	1109.5	1131.3	1137.3	1131.3	1109.5	1073.8	1023.1	988.4
130°	947.8	980.5	1029.1	1062.8	1082.7	1090.6	1082.7	1062.8	1029.1	980.5	947.8
132.5°	905.6	935.8	983.4	1017.2	1035.0	1042.0	1035.0	1017.2	983.4	935.8	905.6
135°	864.4	892.1	934.8	967.6	985.4	989.4	985.4	967.6	934.8	892.1	864.4
137.5°	822.7	847.5	888.2	917.0	932.8	938.8	932.8	917.0	888.2	847.5	822.7
140°	786.0	807.8	839.5	865.4	880.2	886.2	880.2	865.4	839.5	807.8	786.0
142.5°	750.8	768.1	797.9	820.7	833.6	833.6	833.6	820.7	797.9	768.1	750.8
145°	722.0	736.3	760.2	777.0	787.0	789.9	787.0	777.0	760.2	736.3	722.0
147.5°	696.7	707.6	728.4	742.3	749.2	751.2	749.2	742.3	728.4	707.6	696.7
150°	674.8	683.7	698.6	710.5	716.5	717.5	716.5	710.5	698.6	683.7	674.8
152.5°	656.4	663.9	674.8	684.7	688.7	688.7	688.7	684.7	674.8	663.9	656.4
155°	638.6	644.1	655.0	661.9	665.9	663.9	665.9	661.9	655.0	644.1	638.6
157.5°	621.8	626.2	634.1	640.1	642.1	642.1	642.1	640.1	634.1	626.2	621.8
160°	604.8	608.3	615.3	620.2	621.2	621.2	621.2	620.2	615.3	608.3	604.8
162.5°	589.0	591.5	598.4	601.4	602.4	601.4	602.4	601.4	598.4	591.5	589.0
165°	573.6	575.6	579.5	583.5	583.5	582.5	583.5	583.5	579.5	575.6	573.6
167.5°	559.7	561.7	563.7	565.7	565.7	564.7	565.7	565.7	563.7	561.7	559.7
170°	546.8	547.8	548.8	551.8	550.8	548.8	550.8	551.8	548.8	547.8	546.8
172.5°	535.4	535.9	536.9	537.9	536.9	535.9	536.9	537.9	536.9	535.9	535.4
175°	526.5	527.0	527.0	527.9	527.0	525.0	527.0	527.9	527.0	527.0	526.5
177.5°	520.0	520.0	520.0	520.0	519.0	517.0	519.0	520.0	520.0	520.0	520.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1413.0	1418.2	1416.1	1404.8	1416.1	1419.2	1425.4	1431.6	1435.7	1441.9	1447.0
5°	1324.4	1334.7	1340.9	1334.7	1355.3	1358.4	1372.8	1381.1	1393.4	1403.8	1412.0
7.5°	1240.9	1249.2	1261.5	1263.6	1275.9	1290.4	1311.0	1331.6	1351.2	1361.5	1370.8
10°	1151.2	1165.7	1184.2	1180.1	1198.7	1221.3	1243.0	1275.9	1292.4	1311.0	1327.5
12.5°	1061.6	1070.8	1095.6	1103.8	1130.6	1148.1	1178.0	1198.7	1239.9	1261.5	1275.9
15°	904.9	943.0	974.0	1011.1	1046.1	1079.1	1105.9	1143.0	1179.1	1195.6	1219.3
17.5°	833.8	851.3	869.9	888.4	933.8	992.5	1039.9	1080.1	1111.0	1132.7	1160.5
20°	759.6	777.1	797.7	815.2	843.1	885.3	944.1	1013.1	1050.2	1072.9	1099.7
22.5°	707.0	723.5	736.9	752.4	774.0	804.9	849.3	934.8	984.3	1012.1	1035.8
25°	650.3	671.0	685.4	696.7	714.2	748.3	784.3	832.8	921.4	943.0	976.0
27.5°	611.2	617.4	633.9	651.4	668.9	687.4	724.5	765.8	825.6	873.0	913.2
30°	564.8	580.3	595.7	602.9	618.4	645.2	667.9	712.2	758.6	795.7	844.1
32.5°	529.8	539.0	549.3	566.9	581.3	599.8	622.5	659.6	698.8	722.5	759.6
35°	490.6	496.8	518.4	525.6	540.1	558.6	581.3	610.1	652.4	671.0	697.8
37.5°	453.5	467.9	474.1	490.6	504.0	522.5	539.0	572.0	599.8	621.5	646.2
40°	424.6	430.8	442.2	456.6	467.9	482.3	503.0	526.7	556.6	574.1	595.7
42.5°	389.6	394.7	409.2	417.4	436.0	449.4	461.7	490.6	517.4	530.8	552.4
45°	351.5	363.8	373.1	389.6	399.9	416.4	431.8	452.5	477.2	492.7	505.0
47.5°	318.5	330.8	340.1	355.6	372.1	379.3	395.8	417.4	440.1	452.5	470.0
50°	291.7	295.8	313.3	320.5	338.1	352.5	363.8	382.4	407.1	414.3	428.8
52.5°	265.9	269.0	280.3	289.6	305.1	317.4	331.9	349.4	370.0	381.3	392.7
55°	243.2	245.3	250.4	260.8	271.1	286.5	299.9	316.4	333.9	346.3	356.6
57.5°	217.5	221.6	225.7	231.9	242.2	256.6	271.1	286.5	301.0	309.2	322.6
60°	187.6	193.8	201.0	208.2	215.4	225.7	242.2	256.6	270.0	277.2	287.6
62.5°	155.6	168.0	174.2	182.4	188.6	197.9	210.3	226.7	236.0	245.3	253.5
65°	140.2	141.2	142.2	150.5	161.8	171.1	182.4	194.8	209.2	215.4	221.6
67.5°	124.7	125.7	127.8	128.8	133.0	143.3	155.6	169.0	180.4	184.5	190.7
70°	109.2	109.2	113.4	114.4	115.4	116.5	126.8	140.2	150.5	155.6	162.8
72.5°	92.8	93.8	95.9	96.9	98.9	101.0	104.1	111.3	123.7	128.8	137.1
75°	76.3	77.3	78.3	79.4	82.5	83.5	86.6	90.7	95.9	102.0	107.2
77.5°	60.8	60.8	61.8	63.9	66.0	67.0	70.1	72.1	74.2	77.3	81.4
80°	45.3	46.4	46.4	48.4	48.4	49.5	50.5	53.6	55.7	57.7	59.8
82.5°	30.9	33.0	33.0	33.0	34.0	35.0	36.1	36.1	38.1	39.2	42.3
85°	18.6	19.6	19.6	19.6	18.6	20.6	20.6	21.6	21.6	21.6	22.7
87.5°	7.2	6.2	7.2	7.2	7.2	8.2	7.2	7.2	8.2	9.3	9.3
90°	31.8	29.8	31.8	32.7	33.7	32.7	26.8	19.8	14.9	13.4	11.9
92.5°	74.4	85.3	100.2	128.0	152.8	150.8	117.1	79.4	52.6	47.2	41.7
95°	157.8	199.5	260.0	340.4	389.0	344.4	229.2	142.9	97.3	85.4	73.4
97.5°	324.5	424.7	531.9	639.1	634.1	490.2	304.7	184.6	126.0	112.6	99.2
100°	647.0	783.0	906.0	926.9	784.0	539.9	325.5	204.4	151.8	137.9	124.0
102.5°	1056.9	1147.2	1151.2	1034.1	788.9	521.0	326.5	222.3	174.7	160.8	146.9
105°	1330.8	1317.9	1205.7	999.3	735.4	495.2	331.5	243.1	196.5	182.6	168.7
107.5°	1411.2	1313.9	1147.2	925.9	685.7	481.3	342.4	264.0	218.3	204.4	190.5
110°	1371.5	1244.4	1066.8	857.4	652.0	477.3	356.3	284.8	241.1	226.8	212.4

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1300.0	1162.1	993.4	809.8	630.2	478.3	371.1	304.7	263.0	248.1	233.2
115°	1218.6	1088.6	935.8	772.1	615.3	482.3	386.0	325.5	282.8	269.4	256.0
117.5°	1146.2	1025.1	888.2	746.3	607.3	488.2	401.9	344.4	304.7	290.8	276.9
120°	1082.7	977.5	854.4	726.4	600.4	494.2	417.8	364.2	325.5	311.6	297.7
122.5°	1036.0	937.8	827.6	709.5	596.4	501.1	431.7	383.1	347.3	333.0	318.6
125°	991.4	904.1	801.8	693.7	591.5	508.1	446.6	401.9	366.2	352.3	338.4
127.5°	953.7	870.3	776.0	678.8	588.5	515.0	460.5	419.8	385.0	370.6	356.3
130°	915.0	836.6	751.2	663.9	586.5	523.0	473.4	435.7	400.9	387.0	373.1
132.5°	875.3	804.8	727.4	652.0	585.5	530.9	486.3	449.5	416.8	402.9	389.0
135°	836.6	771.1	705.6	641.1	584.5	536.9	497.2	462.4	430.7	416.8	402.9
137.5°	797.9	744.3	687.7	633.1	584.5	542.8	506.1	473.4	441.6	428.7	415.8
140°	764.1	718.5	670.8	626.2	583.5	546.8	513.1	482.3	452.5	439.6	426.7
142.5°	733.4	695.7	657.0	619.2	583.5	549.8	519.0	489.2	460.5	448.6	436.6
145°	707.6	676.8	644.1	613.3	581.5	551.8	524.0	496.2	469.4	458.5	447.6
147.5°	685.7	660.9	634.1	607.3	578.6	552.8	527.0	502.1	476.3	466.4	456.5
150°	665.9	645.0	623.2	599.4	575.6	551.8	528.9	506.1	483.3	474.4	465.4
152.5°	649.0	632.1	612.3	592.4	570.6	549.8	529.9	510.1	490.2	482.3	474.4
155°	633.1	618.2	602.4	583.5	564.7	547.8	530.9	514.1	497.2	489.8	482.3
157.5°	617.3	604.4	590.5	575.6	558.7	543.8	530.9	517.0	502.1	495.6	489.2
160°	601.4	590.5	579.5	566.6	552.8	540.8	530.9	519.0	507.1	501.6	496.2
162.5°	586.5	577.6	568.6	558.7	547.8	537.9	529.9	520.0	510.1	506.1	502.1
165°	571.6	564.7	557.7	549.8	540.8	533.9	527.9	521.0	512.1	509.1	506.1
167.5°	557.7	552.8	546.8	540.8	534.9	529.9	527.0	521.0	514.1	512.1	510.1
170°	545.8	541.8	538.9	533.9	529.9	527.0	525.0	520.0	515.0	513.6	512.1
172.5°	534.9	531.9	529.9	527.0	524.0	523.0	522.0	519.0	516.0	515.0	514.1
175°	526.0	525.0	524.0	521.0	520.0	519.0	520.0	518.0	516.0	515.5	515.0
177.5°	520.0	519.0	519.0	517.0	516.0	517.0	519.0	517.0	516.0	516.0	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1483.1	1483.1	1483.1	1483.1
2.5°	1456.3	1453.2	1471.8	1492.4
5°	1426.4	1431.6	1455.3	1484.1
7.5°	1395.5	1406.8	1434.7	1472.8
10°	1352.2	1372.8	1415.1	1454.3
12.5°	1310.0	1337.8	1378.0	1424.4
15°	1262.6	1293.5	1342.9	1398.6
17.5°	1210.0	1245.0	1302.7	1363.6
20°	1154.3	1200.7	1261.5	1327.5
22.5°	1092.5	1148.1	1211.0	1284.2
25°	1032.7	1093.5	1156.4	1240.9
27.5°	974.0	1033.7	1103.8	1189.4
30°	915.2	969.8	1045.1	1136.8
32.5°	852.4	909.0	988.4	1082.2
35°	794.6	851.3	925.5	1018.3
37.5°	732.8	793.6	864.7	960.6
40°	660.6	731.8	800.8	892.5
42.5°	600.9	676.1	743.1	829.7
45°	553.5	624.6	680.2	764.7
47.5°	509.1	566.9	623.5	701.9
50°	466.9	511.2	570.0	640.0
52.5°	423.6	461.7	512.2	578.2
55°	384.4	420.5	465.9	516.4
57.5°	348.4	374.1	419.5	464.8
60°	308.2	335.0	370.0	408.1
62.5°	274.2	294.8	327.7	359.7
65°	238.1	257.7	282.4	312.3
67.5°	205.1	222.6	242.2	265.9
70°	175.2	188.6	203.0	223.7
72.5°	143.3	157.7	171.1	187.6
75°	117.5	123.7	135.0	146.4
77.5°	90.7	98.9	105.1	114.4
80°	64.9	72.1	74.2	81.4
82.5°	43.3	47.4	51.5	53.6
85°	24.7	26.8	30.9	32.0
87.5°	9.3	10.3	12.4	14.4
90°	9.9	7.9	4.0	1.0
92.5°	33.7	28.8	20.8	14.9
95°	57.6	48.6	38.7	34.7
97.5°	81.4	68.5	57.6	51.6
100°	104.2	88.3	79.4	76.4
102.5°	126.0	110.2	101.2	99.2
105°	146.9	132.0	125.0	121.1
107.5°	168.7	154.8	147.9	144.9
110°	191.5	178.6	172.7	168.7

TEST NUMBER: P1000045

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	213.4	201.5	194.5	190.5
115°	236.2	224.3	218.3	213.4
117.5°	258.0	247.1	241.1	237.2
120°	277.9	268.9	263.0	259.0
122.5°	298.7	288.8	282.8	279.8
125°	318.6	306.6	300.7	297.7
127.5°	337.4	324.5	316.6	312.6
130°	353.3	339.4	329.5	325.5
132.5°	368.2	353.3	342.4	337.4
135°	380.1	365.2	353.3	349.3
137.5°	393.0	377.1	365.2	360.2
140°	404.9	389.0	377.1	373.1
142.5°	415.8	399.9	389.0	386.0
145°	427.7	412.8	402.9	398.9
147.5°	439.6	425.7	415.8	412.8
150°	450.5	437.6	429.7	426.7
152.5°	460.5	449.5	441.6	440.6
155°	471.4	460.5	454.5	453.5
157.5°	480.3	470.4	465.4	464.4
160°	488.2	480.3	476.3	475.3
162.5°	495.2	489.2	485.3	486.3
165°	501.1	495.2	493.2	494.2
167.5°	506.1	502.1	500.2	501.1
170°	510.1	507.1	506.1	508.1
172.5°	513.1	510.1	511.1	512.1
175°	515.0	513.1	514.1	515.0
177.5°	516.0	514.1	515.0	517.0
180°	516.0	516.0	516.0	516.0

(END OF REPORT)