

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999094

Luminaire Tested: SA2XXDIP-B865D530UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999094
REPORT IS A COMBINATION OF REPORTS P984843 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D530UB27-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5498.3 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999094

CATALOG NUMBER: SA2XXDIP-B865D530UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P999094

CATALOG NUMBER: SA2XXDIP-B865D530UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	97	92	88	84	90	86	82	78	73	70	68	62	60	58	52	50	48
2	88	80	73	67	81	74	68	63	63	59	55	54	50	47	44	42	40
3	80	69	61	55	74	65	57	52	55	50	45	47	43	39	39	36	33
4	73	61	53	46	67	57	49	43	49	43	38	41	37	33	34	31	28
5	67	54	46	39	62	51	43	37	43	37	33	37	32	28	31	27	24
6	61	49	40	34	57	45	38	32	39	33	28	33	28	25	28	24	21
7	57	44	35	29	52	41	33	28	35	29	25	30	25	22	25	21	19
8	53	40	32	26	49	37	30	25	32	26	22	28	23	19	23	19	16
9	49	36	28	23	45	34	27	22	29	24	19	25	21	17	21	18	15
10	46	33	26	21	42	31	24	20	27	21	18	23	19	15	20	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14283	14283	14283
5°	14349	13674	13596
10°	14252	13200	13008
15°	14050	12710	12404
20°	13797	12196	11829
25°	13546	11704	11310
30°	13195	11202	10795
35°	12840	10720	10417
40°	12465	10303	10041
45°	12110	9925	9714
50°	11727	9576	9390
55°	11325	9205	9062
60°	10833	8819	8716
65°	10320	8376	8318
70°	9740	7899	7888
75°	9001	7423	7484
80°	7832	6928	7066
85°	6653	6461	6704

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12110 cd/sqm

TEST NUMBER: P999094

CATALOG NUMBER: SA2XXDIP-B865D530UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	1.6
10°-20°	245.3	4.5
20°-30°	371.7	6.8
30°-40°	452.7	8.2
40°-50°	487.0	8.9
50°-60°	473.0	8.6
60°-70°	413.1	7.5
70°-80°	317.9	5.8
80°-90°	214.8	3.9
90°-100°	266.3	4.8
100°-110°	510.9	9.3
110°-120°	495.1	9.0
120°-130°	388.3	7.1
130°-140°	296.9	5.4
140°-150°	214.6	3.9
150°-160°	148.9	2.7
160°-170°	87.7	1.6
170°-180°	28.5	0.5
0°-30°	702.6	12.8
0°-40°	1155.3	21.0
0°-60°	2115.3	38.5
0°-90°	3061.0	55.7
90°-120°	1272.3	23.1
90°-150°	2172.2	39.5
90°-180°	2437.0	44.3
0°-180°	5498.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	902	902	902	902	902	
5°	905	901	893	901	900	86
15°	863	866	866	878	876	243
25°	785	794	806	821	825	361
35°	676	698	723	752	761	423
45°	554	590	636	676	689	428
55°	425	472	540	587	604	380
65°	290	354	432	485	502	288
75°	161	234	318	374	391	170
85°	47	128	212	267	285	50
90°	14	97	192	243	259	10
95°	30	121	372	284	280	29
105°	76	149	532	908	811	81
115°	127	173	430	842	972	125
125°	172	204	382	667	773	154
135°	201	239	348	535	617	155
145°	228	262	332	420	465	143
155°	259	280	322	364	379	119
165°	282	291	309	327	332	80
175°	294	294	297	300	300	28
180°	294	294	294	294	294	

TEST NUMBER: P999094

CATALOG NUMBER: SA2XXDIP-B865D530UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	902.3	902.3	902.3	902.3	902.3
2.5°	908.9	905.0	895.8	902.3	899.7
5°	905.0	901.0	893.2	901.0	899.7
7.5°	898.4	895.8	889.3	898.4	897.1
10°	890.6	888.0	884.0	894.5	893.2
12.5°	877.5	878.8	876.2	886.6	885.3
15°	863.1	865.7	865.7	877.5	876.2
17.5°	844.8	850.0	854.0	865.7	865.7
20°	826.5	833.0	838.3	852.6	852.6
22.5°	806.9	814.7	822.6	836.9	839.6
25°	784.6	793.8	805.6	821.3	825.2
27.5°	758.5	772.9	785.9	805.6	808.2
30°	732.3	749.3	766.3	787.3	791.2
32.5°	703.6	723.2	744.1	768.9	776.8
35°	676.1	698.3	723.2	751.9	761.1
37.5°	646.0	670.9	702.3	733.6	742.8
40°	615.9	644.7	680.0	714.0	725.8
42.5°	587.2	615.9	657.8	695.7	707.5
45°	554.5	589.8	635.6	676.1	689.2
47.5°	523.1	561.0	613.3	655.2	669.6
50°	490.4	530.9	589.8	634.3	648.6
52.5°	459.0	502.2	564.9	610.7	626.4
55°	425.0	472.1	540.1	587.2	604.2
57.5°	392.3	444.6	512.6	563.6	580.6
60°	357.0	413.2	487.8	537.5	555.8
62.5°	325.6	384.5	459.0	512.6	529.6
65°	290.3	354.4	431.6	485.2	502.2
67.5°	258.9	325.6	404.1	457.7	476.0
70°	224.9	292.9	374.0	430.2	445.9
72.5°	193.5	264.2	346.5	401.5	421.1
75°	160.9	234.1	317.8	374.0	391.0
77.5°	129.5	205.3	290.3	346.5	364.9
80°	98.1	177.9	262.9	317.8	336.1
82.5°	71.9	150.4	236.7	291.6	308.6
85°	47.1	128.2	211.9	266.8	285.1
87.5°	28.8	107.2	190.9	244.5	261.5
90°	13.7	96.6	191.9	243.3	259.3
92.5°	20.3	108.0	248.1	252.1	262.1
95°	30.3	120.6	372.4	284.0	280.4
97.5°	38.7	129.6	503.1	357.8	313.5
100°	52.8	136.2	578.3	514.2	396.3
102.5°	64.4	142.8	571.9	735.1	578.4
105°	75.6	148.7	532.2	908.4	810.9
107.5°	89.2	154.6	494.7	964.6	964.2
110°	101.5	160.8	467.6	943.3	1020.6

TEST NUMBER: P999094

CATALOG NUMBER: SA2XXDIP-B865D530UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	113.9	167.8	446.0	897.6	1010.2
115°	127.0	173.4	429.7	842.4	972.1
117.5°	139.3	180.4	415.9	790.4	919.7
120°	151.7	187.0	404.2	741.8	870.3
122.5°	163.6	195.2	394.0	702.8	816.6
125°	172.5	203.6	382.1	666.8	772.9
127.5°	181.0	212.8	372.5	633.4	730.2
130°	188.4	222.2	363.5	601.1	693.1
132.5°	195.2	231.2	355.1	567.8	656.2
135°	200.7	239.2	348.0	535.2	617.0
137.5°	206.9	246.0	341.4	502.2	577.6
140°	214.3	251.0	335.6	472.1	537.2
142.5°	221.6	256.0	333.0	444.2	498.0
145°	227.7	261.6	331.9	419.8	465.3
147.5°	235.6	266.2	330.2	398.9	434.0
150°	243.6	270.7	328.5	385.2	409.5
152.5°	251.5	275.2	325.7	374.6	393.1
155°	258.8	279.6	322.3	364.5	378.9
157.5°	265.1	282.9	318.9	354.8	366.5
160°	271.3	286.3	315.5	345.2	354.6
162.5°	277.5	288.8	312.7	336.2	343.2
165°	282.1	290.6	308.7	327.4	332.5
167.5°	286.0	292.2	305.3	319.5	322.3
170°	290.0	293.2	302.5	312.1	313.2
172.5°	292.3	294.0	299.1	305.6	305.9
175°	294.0	294.2	296.8	300.5	299.6
177.5°	295.1	294.5	294.5	296.8	295.1
180°	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P999094

CATALOG NUMBER: SA2XXDIP-B865D530UB27-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.94	15.92	15.84	16.84	18.02	18.02	18.99	18.92	19.92	21.10
	3H	16.41	17.29	17.32	18.23	19.43	20.62	21.50	21.52	22.43	23.64
	4H	16.89	17.73	17.81	18.67	19.88	21.87	22.71	22.79	23.65	24.86
	6H	17.18	17.96	18.11	18.90	20.13	23.18	23.95	24.11	24.90	26.13
	8H	17.24	17.99	18.18	18.95	20.18	23.84	24.58	24.78	25.54	26.77
	12H	17.26	17.97	18.21	18.93	20.18	24.57	25.28	25.51	26.23	27.49
4H	2H	16.01	16.84	16.93	17.78	19.00	18.36	19.20	19.29	20.14	21.35
	3H	17.72	18.43	18.66	19.40	20.63	21.16	21.87	22.10	22.84	24.07
	4H	18.35	19.00	19.29	19.97	21.22	22.58	23.24	23.53	24.20	25.45
	6H	18.77	19.34	19.73	20.33	21.58	24.06	24.63	25.01	25.61	26.87
	8H	18.88	19.42	19.84	20.40	21.67	24.82	25.35	25.78	26.33	27.60
	12H	18.93	19.42	19.91	20.42	21.69	25.65	26.14	26.63	27.13	28.41
8H	4H	19.15	19.69	20.11	20.66	21.93	22.73	23.27	23.69	24.25	25.52
	6H	19.79	20.24	20.77	21.26	22.52	24.37	24.82	25.35	25.84	27.11
	8H	20.01	20.41	21.00	21.42	22.70	25.26	25.66	26.25	26.67	27.95
	12H	20.15	20.51	21.15	21.51	22.84	26.26	26.62	27.26	27.62	28.95
12H	4H	19.35	19.84	20.33	20.84	22.11	22.71	23.20	23.70	24.20	25.47
	6H	20.12	20.53	21.11	21.53	22.82	24.39	24.80	25.39	25.81	27.09
	8H	20.43	20.79	21.43	21.79	23.12	25.33	25.69	26.33	26.69	28.02