

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000066

Luminaire Tested: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000066
REPORT IS A COMBINATION OF REPORTS P988623 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7148.8 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000066

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000066

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	71	64	59	73	66	60	55	54	50	46	44	41	38	35	33	31
4	74	63	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	25	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22875	22875	22875
5°	22912	21762	21601
10°	22686	20640	19959
15°	22375	19315	18088
20°	21962	17809	16131
25°	21539	16263	14339
30°	20971	14759	12384
35°	20416	13240	10703
40°	19851	11750	8975
45°	19193	10211	7465
50°	18514	8727	6077
55°	17808	7243	4825
60°	16984	5793	3651
65°	16040	4417	2968
70°	14893	3204	2360
75°	13459	2443	1803
80°	11377	1655	1209
85°	7939	756	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19193 cd/sqm

TEST NUMBER: P1000066

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	1.9
10°-20°	371.8	5.2
20°-30°	522.0	7.3
30°-40°	569.0	8.0
40°-50°	523.0	7.3
50°-60°	410.7	5.7
60°-70°	267.3	3.7
70°-80°	137.6	1.9
80°-90°	39.0	0.5
90°-100°	242.6	3.4
100°-110°	820.3	11.5
110°-120°	862.2	12.1
120°-130°	709.0	9.9
130°-140°	569.7	8.0
140°-150°	430.4	6.0
150°-160°	302.6	4.2
160°-170°	178.2	2.5
170°-180°	58.0	0.8
0°-30°	1029.2	14.4
0°-40°	1598.2	22.4
0°-60°	2531.9	35.4
0°-90°	2975.8	41.6
90°-120°	1925.1	26.9
90°-150°	3634.3	50.8
90°-180°	4173.0	58.4
0°-180°	7148.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1438	1422	1433	1429	137
15°	1374	1360	1316	1291	1278	387
25°	1248	1206	1119	1066	1046	574
35°	1075	1008	893	811	782	673
45°	879	791	654	561	530	679
55°	668	566	425	347	322	597
65°	451	345	228	183	179	447
75°	241	149	105	96	94	254
85°	56	29	25	25	25	65
90°	1	16	39	37	38	6
95°	40	99	451	170	131	42
105°	140	212	853	1524	1297	149
115°	248	312	714	1473	1707	245
125°	345	409	686	1193	1385	307
135°	405	483	678	1003	1148	313
145°	463	532	674	837	916	290
155°	526	568	655	741	770	242
165°	573	590	627	665	676	162
175°	597	598	603	611	609	57
180°	598	598	598	598	598	

TEST NUMBER: P1000066

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1445.1	1445.1	1445.1	1445.1	1445.1
2.5°	1451.6	1445.1	1430.7	1443.8	1441.2
5°	1445.1	1438.5	1421.5	1433.3	1429.4
7.5°	1433.3	1425.5	1407.2	1412.4	1405.9
10°	1417.6	1408.5	1382.3	1378.4	1370.5
12.5°	1398.0	1386.2	1350.9	1343.1	1328.7
15°	1374.5	1360.1	1315.6	1290.8	1277.7
17.5°	1347.0	1326.1	1271.2	1242.4	1221.5
20°	1315.6	1289.5	1224.1	1191.4	1162.6
22.5°	1281.6	1251.5	1175.7	1131.2	1111.6
25°	1247.6	1205.8	1119.4	1065.8	1046.2
27.5°	1207.1	1162.6	1067.1	1005.7	975.6
30°	1163.9	1114.2	1009.6	942.9	907.6
32.5°	1122.1	1061.9	954.7	876.2	843.5
35°	1075.0	1008.3	893.2	810.8	782.0
37.5°	1029.2	957.3	835.7	745.4	712.7
40°	980.8	902.4	775.5	682.7	648.7
42.5°	931.1	847.4	715.3	618.6	585.9
45°	878.8	791.2	653.9	561.0	529.6
47.5°	829.1	736.3	595.0	502.2	473.4
50°	774.2	681.3	537.5	447.3	419.8
52.5°	720.6	622.5	482.6	396.3	371.4
55°	668.3	566.3	425.0	346.6	321.7
57.5°	614.7	510.0	374.0	300.8	279.9
60°	559.7	455.1	320.4	253.7	232.8
62.5°	506.1	401.5	274.6	211.9	201.4
65°	451.2	345.3	227.6	183.1	179.2
67.5°	398.9	292.9	183.1	160.9	156.9
70°	343.9	241.9	151.7	138.6	133.4
72.5°	291.6	194.9	126.9	116.4	113.8
75°	240.6	149.1	104.6	95.5	94.2
77.5°	189.6	105.9	82.4	77.2	74.5
80°	142.5	75.9	62.8	57.5	57.5
82.5°	99.4	51.0	43.2	40.5	40.5
85°	56.2	28.8	24.8	24.8	24.8
87.5°	20.9	10.5	10.5	9.2	9.2
90°	1.2	15.6	39.1	37.4	38.0
92.5°	17.3	54.6	177.3	81.7	70.2
95°	40.3	99.0	451.2	170.4	131.2
97.5°	59.9	130.6	735.5	341.8	219.8
100°	88.6	160.0	909.3	680.8	412.1
102.5°	115.1	186.4	915.1	1151.0	803.4
105°	140.4	211.8	852.9	1524.5	1297.2
107.5°	168.0	237.1	795.3	1659.8	1629.8
110°	195.7	263.0	756.2	1637.9	1765.7

TEST NUMBER: P1000066

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.0	287.8	730.9	1563.6	1763.4
115°	247.5	312.5	713.6	1472.7	1707.0
117.5°	275.1	337.2	704.4	1385.8	1621.8
120°	300.4	361.4	696.4	1308.2	1540.1
122.5°	324.6	386.2	691.8	1247.7	1454.9
125°	345.3	408.6	686.0	1193.1	1384.7
127.5°	362.6	429.9	682.6	1146.4	1319.1
130°	377.5	448.9	680.2	1099.2	1265.0
132.5°	391.3	467.3	679.1	1050.3	1208.6
135°	405.2	483.4	677.9	1002.6	1147.6
137.5°	417.8	497.2	677.9	954.2	1088.9
140°	432.8	509.9	676.8	911.6	1027.9
142.5°	447.7	520.2	676.8	870.8	966.9
145°	462.7	531.8	674.5	837.4	916.2
147.5°	478.8	541.0	671.0	808.0	871.3
150°	494.9	550.2	667.6	782.6	832.2
152.5°	511.0	559.4	661.8	761.4	798.8
155°	526.0	568.0	654.9	740.6	770.0
157.5°	538.7	574.9	648.0	721.1	744.7
160°	551.3	581.8	641.1	701.6	720.5
162.5°	564.0	587.0	635.4	683.1	697.5
165°	573.2	590.4	627.3	665.3	675.6
167.5°	581.3	593.9	620.4	649.2	654.9
170°	589.3	595.6	614.6	634.2	636.5
172.5°	593.9	597.4	607.7	621.0	621.5
175°	597.4	598.0	603.1	610.6	608.9
177.5°	599.7	598.5	598.5	603.1	599.7
180°	598.5	598.5	598.5	598.5	598.5

(END OF REPORT)