

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000088

Luminaire Tested: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000088
REPORT IS A COMBINATION OF REPORTS P988645 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7240.9 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000088

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000088

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	71	64	59	73	66	60	55	54	50	46	44	41	38	35	33	31
4	74	63	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	25	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23168	23168	23168
5°	23205	22040	21878
10°	22975	20905	20215
15°	22660	19562	18318
20°	22242	18036	16337
25°	21815	16472	14523
30°	21240	14947	12542
35°	20676	13409	10840
40°	20106	11900	9088
45°	19440	10340	7560
50°	18751	8839	6156
55°	18034	7337	4886
60°	17202	5867	3698
65°	16243	4474	3006
70°	15084	3244	2390
75°	13633	2476	1826
80°	11529	1676	1226
85°	8052	768	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19440 cd/sqm

TEST NUMBER: P1000088

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	1.9
10°-20°	376.6	5.2
20°-30°	528.7	7.3
30°-40°	576.3	8.0
40°-50°	529.7	7.3
50°-60°	416.0	5.7
60°-70°	270.7	3.7
70°-80°	139.4	1.9
80°-90°	39.5	0.5
90°-100°	245.8	3.4
100°-110°	830.9	11.5
110°-120°	873.4	12.1
120°-130°	718.2	9.9
130°-140°	577.1	8.0
140°-150°	436.0	6.0
150°-160°	306.5	4.2
160°-170°	180.5	2.5
170°-180°	58.7	0.8
0°-30°	1042.4	14.4
0°-40°	1618.7	22.4
0°-60°	2564.3	35.4
0°-90°	3013.9	41.6
90°-120°	1950.0	26.9
90°-150°	3681.3	50.8
90°-180°	4227.0	58.4
0°-180°	7240.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1464	1464	1464	1464	1464	
5°	1464	1457	1440	1452	1448	139
15°	1392	1378	1332	1307	1294	392
25°	1264	1221	1134	1080	1060	581
35°	1089	1021	905	821	792	681
45°	890	801	662	568	536	687
55°	677	574	430	351	326	605
65°	457	350	230	185	182	453
75°	244	151	106	97	95	258
85°	57	29	25	25	25	65
90°	1	16	40	38	38	6
95°	41	100	457	173	133	42
105°	142	215	864	1544	1314	151
115°	251	317	723	1492	1729	249
125°	350	414	695	1208	1403	311
135°	410	490	687	1016	1162	317
145°	469	539	683	848	928	294
155°	533	575	663	750	780	245
165°	581	598	635	674	684	164
175°	605	606	611	618	617	57
180°	606	606	606	606	606	

TEST NUMBER: P1000088

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1463.6	1463.6	1463.6	1463.6	1463.6
2.5°	1470.2	1463.6	1449.0	1462.2	1459.6
5°	1463.6	1456.9	1439.7	1451.6	1447.7
7.5°	1451.6	1443.7	1425.2	1430.4	1423.8
10°	1435.7	1426.5	1400.0	1396.0	1388.1
12.5°	1415.9	1404.0	1368.2	1360.3	1345.7
15°	1392.0	1377.5	1332.4	1307.3	1294.0
17.5°	1364.2	1343.0	1287.4	1258.3	1237.1
20°	1332.4	1305.9	1239.7	1206.6	1177.5
22.5°	1298.0	1267.5	1190.7	1145.7	1125.8
25°	1263.6	1221.2	1133.8	1079.5	1059.6
27.5°	1222.5	1177.5	1080.8	1018.5	988.1
30°	1178.8	1128.5	1022.5	955.0	919.2
32.5°	1136.4	1075.5	966.9	887.4	854.3
35°	1088.7	1021.2	904.6	821.2	792.0
37.5°	1042.4	969.5	846.3	755.0	721.8
40°	993.4	913.9	785.4	691.4	656.9
42.5°	943.0	858.3	724.5	626.5	593.4
45°	890.1	801.3	662.2	568.2	536.4
47.5°	839.7	745.7	602.6	508.6	479.5
50°	784.1	690.1	544.4	453.0	425.2
52.5°	729.8	630.5	488.7	401.3	376.2
55°	676.8	573.5	430.5	351.0	325.8
57.5°	622.5	516.6	378.8	304.6	283.4
60°	566.9	460.9	324.5	257.0	235.8
62.5°	512.6	406.6	278.1	214.6	204.0
65°	456.9	349.7	230.5	185.4	181.5
67.5°	404.0	296.7	185.4	162.9	158.9
70°	348.3	245.0	153.6	140.4	135.1
72.5°	295.4	197.3	128.5	117.9	115.2
75°	243.7	151.0	106.0	96.7	95.4
77.5°	192.1	107.3	83.4	78.1	75.5
80°	144.4	76.8	63.6	58.3	58.3
82.5°	100.7	51.7	43.7	41.1	41.1
85°	57.0	29.1	25.2	25.2	25.2
87.5°	21.2	10.6	10.6	9.3	9.3
90°	1.2	15.8	39.6	37.9	38.5
92.5°	17.5	55.4	179.6	82.8	71.1
95°	40.8	100.3	457.0	172.6	132.9
97.5°	60.6	132.4	745.0	346.3	222.7
100°	89.8	162.0	921.1	689.7	417.4
102.5°	116.6	188.9	926.9	1165.9	813.8
105°	142.2	214.6	863.9	1544.2	1314.0
107.5°	170.2	240.2	805.6	1681.2	1650.9
110°	198.2	266.4	766.0	1659.1	1788.5

TEST NUMBER: P1000088

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	291.5	740.4	1583.8	1786.2
115°	250.7	316.6	722.9	1491.8	1729.0
117.5°	278.7	341.6	713.5	1403.8	1642.8
120°	304.3	366.1	705.4	1325.0	1560.0
122.5°	328.8	391.2	700.7	1263.8	1473.7
125°	349.8	413.9	694.9	1208.4	1402.6
127.5°	367.3	435.5	691.4	1161.2	1336.1
130°	382.4	454.7	689.1	1113.4	1281.3
132.5°	396.4	473.4	687.9	1063.9	1224.2
135°	410.4	489.7	686.7	1015.6	1162.4
137.5°	423.2	503.6	686.7	966.6	1103.0
140°	438.4	516.5	685.6	923.4	1041.2
142.5°	453.5	527.0	685.6	882.0	979.4
145°	468.7	538.6	683.2	848.2	928.1
147.5°	485.0	548.0	679.7	818.4	882.6
150°	501.3	557.3	676.2	792.8	843.0
152.5°	517.7	566.6	670.4	771.2	809.1
155°	532.8	575.4	663.4	750.3	780.0
157.5°	545.6	582.4	656.4	730.4	754.3
160°	558.5	589.4	649.4	710.6	729.9
162.5°	571.3	594.6	643.6	692.0	706.5
165°	580.6	598.1	635.4	673.9	684.4
167.5°	588.8	601.6	628.4	657.6	663.4
170°	596.9	603.4	622.6	642.4	644.7
172.5°	601.6	605.1	615.6	629.0	629.6
175°	605.1	605.7	610.9	618.5	616.8
177.5°	607.4	606.3	606.3	610.9	607.4
180°	606.3	606.3	606.3	606.3	606.3

(END OF REPORT)