

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000101

Luminaire Tested: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000101
REPORT IS A COMBINATION OF REPORTS P988660 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4529.0 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	72
1	104	100	96	93	98	95	92	89	85	83	81	77	75	73	69	68	67	67	67	63
2	95	89	83	78	90	84	79	75	76	72	69	69	66	63	62	60	58	58	58	54
3	88	79	72	66	83	75	69	64	69	64	59	62	58	55	56	53	51	51	51	48
4	81	71	63	58	77	68	61	56	62	56	52	56	52	48	51	48	45	45	45	42
5	75	64	56	50	71	61	54	49	56	50	46	51	47	43	47	43	40	40	40	37
6	70	58	50	45	66	56	49	43	51	45	41	47	42	38	43	39	36	36	36	34
7	65	53	45	40	62	51	44	39	47	41	37	43	38	35	40	36	33	33	33	30
8	61	49	41	36	58	47	40	35	43	38	33	40	35	32	37	33	30	30	30	28
9	57	45	38	33	54	43	37	32	40	34	30	37	32	29	34	30	27	27	27	25
10	54	42	35	30	51	40	34	29	37	32	28	35	30	26	32	28	25	25	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29788	29788	29788	29788
5°	29857	31640	29961	25276
10°	29529	33442	29738	20873
15°	28888	33453	29378	15680
20°	28116	27652	28729	12937
25°	27183	17278	27770	11005
30°	25989	11063	26695	9475
35°	24537	8502	25333	8108
40°	22921	7146	23900	7092
45°	21191	6082	22078	5954
50°	19420	5168	20326	5150
55°	17459	4492	18399	4432
60°	15715	3425	16547	3384
65°	14085	2577	14924	2923
70°	12291	2059	13252	2383
75°	10388	1577	11339	1803
80°	8247	1072	8878	1181
85°	5721	553	6286	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27250 cd/sqm

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.5	3.9
10°-20°	498.2	11.0
20°-30°	641.2	14.2
30°-40°	608.3	13.4
40°-50°	521.3	11.5
50°-60°	397.0	8.8
60°-70°	250.4	5.5
70°-80°	124.9	2.8
80°-90°	33.3	0.7
90°-100°	71.4	1.6
100°-110°	251.5	5.6
110°-120°	264.1	5.8
120°-130°	217.3	4.8
130°-140°	174.6	3.9
140°-150°	131.9	2.9
150°-160°	92.7	2.0
160°-170°	54.6	1.2
170°-180°	17.8	0.4
0°-30°	1317.9	29.1
0°-40°	1926.2	42.5
0°-60°	2844.6	62.8
0°-90°	3253.2	71.8
90°-120°	587.1	13.0
90°-150°	1110.8	24.5
90°-180°	1276.0	28.2
0°-180°	4529.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1882	1882	1882	1882	1882	
5°	1883	2094	1890	1673	1883	179
15°	1775	2363	1805	1108	1775	499
25°	1574	1261	1608	803	1574	723
35°	1292	621	1334	592	1292	808
45°	970	432	1011	422	970	749
55°	655	300	690	296	655	590
65°	396	156	420	176	396	393
75°	186	82	203	94	186	201
85°	40	24	44	25	40	46
90°	0	12	0	12	0	3
95°	12	40	12	40	12	13
105°	43	397	43	397	43	46
115°	76	522	76	522	76	75
125°	106	424	106	424	106	94
135°	124	351	124	351	124	96
145°	142	280	142	280	142	89
155°	161	236	161	236	161	74
165°	176	207	176	207	176	49
175°	183	186	183	186	183	17
180°	183	183	183	183	183	

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1893.6	1901.4	1905.3	1910.6	1922.3	1930.2	1942.0	1944.6	1943.3	1948.5	1934.1
5°	1883.1	1900.1	1915.8	1928.9	1949.8	1962.9	1977.3	1994.3	1998.2	2017.8	2006.0
7.5°	1868.7	1893.6	1915.8	1942.0	1973.3	1990.4	2012.6	2038.7	2050.5	2074.0	2080.6
10°	1845.2	1880.5	1918.4	1945.9	1989.0	2019.1	2040.0	2081.9	2109.4	2144.7	2139.4
12.5°	1807.3	1853.0	1904.0	1949.8	2006.0	2025.7	2064.9	2108.0	2143.4	2176.0	2204.8
15°	1774.6	1826.9	1883.1	1939.3	2003.4	2040.0	2079.3	2135.5	2173.4	2231.0	2255.8
17.5°	1730.1	1796.8	1863.5	1926.3	2002.1	2044.0	2092.4	2147.3	2203.5	2258.4	2278.0
20°	1684.3	1756.3	1828.2	1913.2	1999.5	2040.0	2089.7	2157.7	2212.7	2255.8	2255.8
22.5°	1629.4	1717.0	1799.4	1880.5	1974.7	2033.5	2084.5	2164.3	2203.5	2212.7	2177.4
25°	1574.5	1662.1	1752.3	1853.0	1960.3	2012.6	2070.1	2144.7	2157.7	2121.1	2029.6
27.5°	1509.1	1607.2	1709.2	1817.7	1930.2	1995.6	2047.9	2097.6	2072.7	1974.7	1832.1
30°	1442.4	1548.3	1663.4	1766.7	1902.7	1962.9	2007.4	2021.7	1943.3	1783.7	1599.3
32.5°	1373.1	1476.4	1598.0	1722.3	1859.6	1917.1	1945.9	1908.0	1764.1	1562.7	1337.8
35°	1292.0	1408.4	1535.3	1664.7	1800.7	1843.9	1860.9	1768.0	1583.6	1323.4	1099.8
37.5°	1218.8	1335.2	1471.2	1603.3	1735.3	1758.9	1741.9	1596.7	1362.6	1105.0	886.6
40°	1132.5	1256.7	1390.1	1537.9	1646.4	1653.0	1611.1	1422.8	1132.5	890.6	755.9
42.5°	1052.7	1178.3	1311.6	1462.0	1544.4	1522.2	1466.0	1218.8	945.5	767.6	659.1
45°	970.3	1089.3	1233.2	1366.6	1425.4	1373.1	1288.1	1025.3	793.8	660.4	576.7
47.5°	890.6	1001.7	1144.3	1272.4	1282.9	1224.0	1123.3	859.2	687.9	580.6	512.6
50°	812.1	923.3	1056.6	1162.6	1152.1	1071.0	957.3	746.7	597.6	512.6	456.4
52.5°	733.6	834.3	963.8	1047.5	1003.0	924.6	812.1	632.9	521.8	447.2	404.1
55°	655.2	749.3	860.5	929.8	859.2	768.9	689.2	542.7	452.5	392.3	359.6
57.5°	589.8	664.3	766.3	808.2	723.2	652.6	583.2	466.9	392.3	349.2	311.2
60°	517.9	585.9	669.6	694.4	606.8	549.2	490.4	394.9	336.1	298.2	273.3
62.5°	456.4	512.6	576.7	576.7	499.5	456.4	411.9	330.9	282.5	252.4	240.6
65°	396.2	436.8	482.5	477.3	411.9	374.0	338.7	273.3	236.7	215.8	204.0
67.5°	337.4	368.8	398.9	380.5	333.5	300.8	268.1	221.0	196.2	181.8	166.1
70°	283.8	308.6	324.3	307.3	260.2	232.8	209.2	177.8	158.2	139.9	130.8
72.5°	238.0	248.5	253.7	232.8	193.5	177.8	160.8	138.6	121.6	112.5	109.8
75°	185.7	194.9	190.9	175.2	142.5	130.8	117.7	102.0	98.1	92.8	90.2
77.5°	145.2	145.2	138.6	124.2	102.0	92.8	87.6	79.8	75.8	74.5	71.9
80°	103.3	102.0	98.1	82.4	69.3	64.1	64.1	58.8	57.5	54.9	54.9
82.5°	68.0	68.0	62.8	49.7	45.8	44.5	43.2	40.5	40.5	39.2	39.2
85°	40.5	37.9	31.4	27.5	26.2	26.2	24.8	23.5	24.8	23.5	23.5
87.5°	18.3	14.4	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
90°	0.4	1.4	2.8	3.5	4.2	4.8	5.3	7.0	9.5	11.6	12.0
92.5°	5.3	7.4	10.2	12.0	14.8	16.8	18.7	28.2	41.6	53.6	54.3
95°	12.3	13.7	17.3	20.4	26.1	30.3	34.5	50.7	81.4	122.3	138.1
97.5°	18.3	20.4	24.3	28.9	35.2	40.0	44.7	65.5	108.2	174.0	225.1
100°	27.1	28.2	31.4	37.0	44.0	49.0	53.9	72.6	115.6	191.7	278.3
102.5°	35.2	35.9	39.1	44.7	52.1	57.0	62.0	78.9	115.9	185.0	280.1
105°	43.0	44.4	46.9	52.1	59.9	64.8	69.8	86.3	117.7	175.8	261.1
107.5°	51.4	52.5	55.0	59.9	67.6	72.6	77.5	93.7	121.5	170.9	243.4
110°	59.9	61.3	63.4	68.0	75.4	80.5	85.6	101.1	126.5	169.5	231.5

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	67.6	69.1	71.5	75.7	82.8	88.1	93.4	108.2	131.8	169.8	223.7
115°	75.7	77.5	79.6	83.9	90.9	95.6	100.4	115.6	137.0	171.2	218.4
117.5°	84.2	85.6	87.7	91.6	98.3	103.2	108.2	122.3	142.7	173.3	215.6
120°	92.0	93.4	95.5	98.6	105.7	110.6	115.6	129.3	148.3	175.5	213.1
122.5°	99.4	100.4	102.5	106.0	113.1	118.2	123.3	136.0	153.3	177.9	211.7
125°	105.7	106.8	108.9	113.1	120.1	125.0	130.0	142.7	158.5	180.4	210.0
127.5°	111.0	112.4	115.2	119.8	126.5	131.6	136.7	149.0	163.5	182.8	208.9
130°	115.6	117.0	120.5	125.4	132.5	137.4	142.3	154.7	168.1	185.7	208.2
132.5°	119.8	121.5	125.4	130.7	138.1	143.0	148.0	159.6	172.6	188.5	207.9
135°	124.0	125.4	129.7	134.9	143.0	148.0	152.9	164.2	176.5	190.6	207.5
137.5°	127.9	129.7	133.9	139.5	147.6	152.2	156.8	168.1	179.7	192.7	207.5
140°	132.5	133.9	138.1	143.7	151.5	156.1	160.7	171.2	182.1	194.1	207.2
142.5°	137.0	138.1	142.0	147.6	155.0	159.2	163.5	173.7	184.3	195.2	207.2
145°	141.6	143.0	146.6	151.8	158.9	162.8	166.6	176.2	186.0	195.9	206.5
147.5°	146.6	147.6	151.1	156.1	162.1	165.6	169.1	178.3	187.1	196.2	205.4
150°	151.5	152.6	155.4	159.9	165.2	168.4	171.6	179.7	187.8	195.9	204.3
152.5°	156.4	156.8	159.6	163.5	168.4	171.2	174.0	181.1	188.1	195.2	202.6
155°	161.0	161.4	163.5	167.3	171.2	173.8	176.5	182.5	188.5	194.5	200.5
157.5°	164.9	165.2	167.0	170.5	173.7	176.0	178.3	183.6	188.5	193.1	198.4
160°	168.8	169.1	170.5	173.3	176.2	178.1	180.0	184.3	188.5	192.0	196.2
162.5°	172.6	172.3	173.7	175.8	178.3	179.7	181.1	184.6	188.1	191.0	194.5
165°	175.5	175.1	175.8	177.9	179.7	180.8	181.8	185.0	187.4	189.5	192.0
167.5°	177.9	177.6	178.3	179.7	181.1	181.8	182.5	185.0	187.1	188.1	189.9
170°	180.4	179.7	180.0	181.1	181.8	182.3	182.8	184.6	186.4	187.1	188.1
172.5°	181.8	181.4	181.1	182.1	182.5	182.8	183.2	184.3	185.3	185.7	186.0
175°	182.8	182.5	182.1	182.8	182.8	183.0	183.2	183.9	184.6	184.3	184.6
177.5°	183.6	182.8	182.5	183.2	183.2	183.2	183.2	183.6	184.3	183.6	183.2
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1948.5	1951.1	1955.0	1973.3	1976.0	1981.2	1978.6	1978.6	1979.9	1977.3	1978.6
5°	2032.2	2036.1	2055.7	2078.0	2083.2	2078.0	2084.5	2093.7	2093.7	2093.7	2091.0
7.5°	2110.7	2125.0	2147.3	2180.0	2186.5	2193.0	2204.8	2197.0	2199.6	2211.4	2207.4
10°	2186.5	2207.4	2232.3	2259.7	2274.1	2283.3	2288.5	2300.3	2327.7	2296.4	2308.1
12.5°	2258.4	2288.5	2314.7	2344.7	2355.2	2367.0	2370.9	2381.4	2381.4	2380.1	2389.2
15°	2305.5	2333.0	2356.5	2376.1	2378.7	2376.1	2373.5	2374.8	2378.7	2363.1	2372.2
17.5°	2316.0	2318.6	2326.4	2318.6	2319.9	2292.4	2276.7	2272.8	2236.2	2237.5	2267.6
20°	2265.0	2220.5	2208.7	2165.6	2139.4	2068.8	2066.2	2046.6	1969.4	1993.0	1987.7
22.5°	2125.0	2049.2	1948.5	1898.8	1874.0	1799.4	1741.9	1701.3	1673.9	1646.4	1634.7
25°	1940.7	1817.7	1675.2	1577.1	1562.7	1493.4	1387.5	1337.8	1279.0	1260.6	1292.0
27.5°	1702.7	1543.1	1382.3	1231.9	1204.4	1141.6	1088.0	1052.7	984.7	980.8	983.4
30°	1379.6	1218.8	1084.1	986.0	918.0	889.2	853.9	827.8	800.3	810.8	813.4
32.5°	1133.8	980.8	855.2	802.9	771.6	753.2	723.2	706.2	694.4	690.5	689.2
35°	901.0	799.0	742.8	691.8	673.5	660.4	638.2	630.3	619.9	621.2	621.2
37.5°	771.6	686.6	644.7	618.6	601.6	595.0	580.6	572.8	566.2	563.6	567.6
40°	665.6	606.8	580.6	557.1	542.7	540.1	532.2	523.1	515.2	516.5	520.5
42.5°	588.5	554.5	523.1	504.8	494.3	490.4	483.9	477.3	477.3	473.4	472.1
45°	527.0	499.5	473.4	456.4	449.9	444.6	436.8	435.5	430.2	431.5	432.9
47.5°	472.1	449.9	430.2	413.2	406.7	405.4	397.5	392.3	392.3	391.0	389.7
50°	422.4	400.2	383.2	374.0	364.9	362.2	360.9	359.6	357.0	357.0	358.3
52.5°	381.9	359.6	346.5	338.7	333.5	330.9	330.9	329.5	329.5	329.5	328.2
55°	337.4	319.1	308.6	306.0	303.4	302.1	300.8	298.2	296.9	299.5	296.9
57.5°	295.5	289.0	279.9	277.2	270.7	270.7	266.8	264.2	261.5	264.2	264.2
60°	262.9	253.7	248.5	240.6	235.4	230.2	223.6	222.3	219.7	218.4	217.1
62.5°	228.9	221.0	207.9	196.2	188.3	183.1	180.5	179.2	179.2	177.8	177.8
65°	190.9	172.6	166.1	162.2	160.8	159.5	156.9	155.6	156.9	155.6	156.9
67.5°	149.1	146.5	142.5	139.9	138.6	137.3	137.3	136.0	136.0	136.0	136.0
70°	129.5	122.9	121.6	119.0	119.0	117.7	117.7	117.7	117.7	116.4	119.0
72.5°	107.2	103.3	102.0	100.7	100.7	100.7	99.4	99.4	99.4	98.1	99.4
75°	87.6	86.3	83.7	83.7	82.4	83.7	82.4	82.4	81.1	82.4	82.4
77.5°	70.6	69.3	68.0	68.0	66.7	66.7	66.7	66.7	66.7	66.7	68.0
80°	53.6	52.3	51.0	52.3	51.0	52.3	51.0	51.0	52.3	51.0	51.0
82.5°	39.2	37.9	37.9	36.6	36.6	36.6	36.6	36.6	36.6	36.6	36.6
85°	23.5	22.2	22.2	23.5	22.2	23.5	22.2	22.2	22.2	23.5	23.5
87.5°	10.5	11.8	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	11.8
90°	11.6	11.3	10.6	11.3	11.4	11.6	11.6	11.6	11.6	11.6	11.6
92.5°	45.4	35.6	30.3	26.4	25.0	23.6	23.3	21.8	22.2	21.5	22.2
95°	120.8	92.3	70.8	56.0	52.2	48.3	43.7	40.9	39.8	40.2	39.8
97.5°	226.9	188.8	150.8	115.2	104.6	94.1	80.3	73.3	69.4	67.3	69.4
100°	329.1	321.7	278.0	229.7	208.4	187.1	157.8	142.7	132.5	126.1	132.5
102.5°	367.1	408.7	407.3	375.2	352.3	329.4	297.0	268.5	255.1	245.9	255.1
105°	354.8	428.1	467.9	472.4	466.6	460.8	439.0	417.1	402.0	397.1	402.0
107.5°	328.7	407.3	466.5	501.0	508.0	515.1	514.7	511.6	507.0	498.9	507.0
110°	304.4	378.7	441.8	486.9	501.4	515.8	530.9	537.6	540.8	540.4	540.8

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	287.5	352.7	412.6	461.5	478.6	495.7	518.2	530.6	537.3	539.7	537.3
115°	274.1	332.2	386.5	432.6	450.8	468.9	493.9	510.1	519.3	522.5	519.3
117.5°	264.9	315.3	363.9	406.9	424.2	441.4	467.2	484.4	493.9	496.4	493.9
120°	257.9	303.3	347.0	384.4	400.4	416.4	441.1	457.7	467.9	471.4	467.9
122.5°	251.9	293.8	332.9	367.8	381.9	396.0	417.5	433.7	442.5	445.3	442.5
125°	246.3	284.7	321.0	352.0	365.2	378.4	398.8	412.2	421.0	423.8	421.0
127.5°	241.0	275.5	309.0	338.6	350.9	363.2	381.2	393.9	401.6	403.7	401.6
130°	235.7	266.7	297.0	324.8	336.5	348.1	365.3	377.3	384.4	387.2	384.4
132.5°	231.5	258.2	285.7	310.7	321.4	332.2	349.1	361.1	367.5	369.9	367.5
135°	227.6	250.5	273.7	297.0	306.8	316.7	331.9	343.5	349.8	351.3	349.8
137.5°	224.8	244.2	264.2	283.3	292.1	300.9	315.3	325.5	331.2	333.3	331.2
140°	222.3	238.2	255.1	271.3	279.0	286.8	298.1	307.2	312.5	314.6	312.5
142.5°	219.8	233.2	247.0	260.4	266.5	272.7	283.3	291.4	295.9	295.9	295.9
145°	217.7	228.7	240.3	251.2	256.3	261.4	269.9	275.9	279.4	280.4	279.4
147.5°	215.6	225.1	234.6	243.4	247.3	251.2	258.6	263.5	266.0	266.7	266.0
150°	212.8	221.3	229.0	236.4	239.6	242.7	248.0	252.3	254.4	254.7	254.4
152.5°	210.3	217.4	224.4	230.4	233.0	235.7	239.6	243.1	244.5	244.5	244.5
155°	207.2	213.9	219.5	224.8	226.8	228.7	232.5	235.0	236.4	235.7	236.4
157.5°	204.3	209.6	214.6	219.1	220.7	222.3	225.1	227.2	227.9	227.9	227.9
160°	201.2	205.7	209.6	213.5	214.8	216.0	218.4	220.2	220.5	220.5	220.5
162.5°	198.4	201.9	205.0	208.2	209.1	210.0	212.4	213.5	213.9	213.5	213.9
165°	195.2	198.0	200.5	202.9	203.6	204.3	205.7	207.2	207.2	206.8	207.2
167.5°	192.0	194.1	196.2	198.0	198.7	199.4	200.1	200.8	200.8	200.5	200.8
170°	189.5	191.3	192.4	193.8	194.2	194.5	194.8	195.9	195.5	194.8	195.5
172.5°	187.1	188.1	188.8	189.9	190.0	190.2	190.6	191.0	190.6	190.2	190.6
175°	185.0	186.0	186.4	186.7	186.9	187.1	187.1	187.4	187.1	186.4	187.1
177.5°	183.6	184.3	184.3	184.6	184.6	184.6	184.6	184.6	184.3	183.6	184.3
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1983.8	1974.7	1972.0	1974.7	1972.0	1973.3	1964.2	1930.2	1939.3	1925.0	1932.8
5°	2096.3	2088.4	2071.4	2068.8	2066.2	2063.6	2050.5	2020.4	2008.7	1989.0	1987.7
7.5°	2203.5	2203.5	2190.4	2181.3	2169.5	2160.4	2143.4	2098.9	2080.6	2057.0	2044.0
10°	2309.4	2275.4	2289.8	2280.7	2251.9	2246.7	2215.3	2189.1	2153.8	2130.3	2109.4
12.5°	2385.3	2374.8	2361.7	2353.9	2346.0	2329.0	2308.1	2241.4	2223.1	2176.0	2152.5
15°	2382.7	2376.1	2380.1	2380.1	2377.4	2373.5	2356.5	2308.1	2276.7	2231.0	2190.4
17.5°	2254.5	2271.5	2288.5	2300.3	2326.4	2338.2	2353.9	2325.1	2305.5	2266.3	2223.1
20°	2030.9	2072.7	2122.4	2132.9	2156.4	2225.7	2257.1	2282.0	2289.8	2276.7	2241.4
22.5°	1719.7	1755.0	1875.3	1872.7	1906.7	1989.0	2080.6	2155.1	2214.0	2246.7	2233.6
25°	1347.0	1396.6	1460.7	1509.1	1620.3	1743.2	1857.0	1976.0	2078.0	2168.2	2190.4
27.5°	1018.7	1084.1	1135.1	1199.2	1255.4	1400.6	1547.0	1732.7	1851.7	2023.0	2112.0
30°	823.9	853.9	904.9	935.0	962.5	1073.6	1239.7	1422.8	1632.0	1829.5	1982.5
32.5°	703.6	724.5	762.4	775.5	804.2	878.8	983.4	1150.8	1366.6	1605.9	1807.3
35°	631.6	653.9	661.7	673.5	697.0	744.1	816.0	937.6	1132.5	1366.6	1607.2
37.5°	570.2	581.9	604.2	612.0	619.9	655.2	703.6	788.6	918.0	1110.3	1377.0
40°	527.0	533.5	545.3	551.9	557.1	581.9	625.1	682.6	778.1	924.6	1170.4
42.5°	481.2	489.1	496.9	504.8	511.3	530.9	557.1	612.0	676.1	787.2	965.1
45°	436.8	442.0	451.2	456.4	465.5	481.2	504.8	542.7	600.2	670.9	814.7
47.5°	396.2	402.8	406.7	413.2	419.8	436.8	459.0	483.9	530.9	600.2	704.9
50°	359.6	367.5	372.7	374.0	379.2	394.9	413.2	440.7	470.8	524.4	615.9
52.5°	333.5	334.8	338.7	343.9	342.6	351.8	368.8	389.7	421.1	464.2	530.9
55°	303.4	307.3	309.9	311.2	311.2	319.1	328.2	347.9	372.7	408.0	464.2
57.5°	265.5	269.4	277.2	279.9	283.8	287.7	291.6	304.7	325.6	359.6	405.4
60°	226.2	228.9	236.7	241.9	244.5	255.0	260.2	270.7	282.5	307.3	350.5
62.5°	181.8	184.4	188.3	193.5	198.8	214.5	227.5	238.0	247.2	264.2	299.5
65°	158.2	159.5	162.2	163.5	164.8	171.3	183.1	197.5	214.5	227.5	248.5
67.5°	137.3	138.6	139.9	142.5	143.8	145.2	150.4	154.3	171.3	189.6	205.3
70°	117.7	120.3	121.6	121.6	122.9	125.5	128.2	133.4	138.6	147.8	167.4
72.5°	99.4	100.7	103.3	103.3	103.3	105.9	108.5	111.2	113.8	119.0	126.8
75°	82.4	85.0	85.0	85.0	86.3	86.3	88.9	91.5	94.2	98.1	100.7
77.5°	68.0	68.0	68.0	68.0	69.3	69.3	70.6	73.2	74.5	75.8	78.5
80°	51.0	52.3	52.3	52.3	53.6	53.6	53.6	56.2	57.5	57.5	60.2
82.5°	37.9	37.9	37.9	39.2	37.9	39.2	39.2	40.5	39.2	40.5	41.8
85°	23.5	23.5	23.5	24.8	24.8	24.8	24.8	24.8	24.8	24.8	26.2
87.5°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	13.1	11.8	11.8
90°	11.6	11.6	11.6	11.4	11.3	10.6	11.3	11.6	12.0	11.6	9.5
92.5°	21.8	23.3	23.6	25.0	26.4	30.3	35.6	45.4	54.3	53.6	41.6
95°	40.9	43.7	48.3	52.2	56.0	70.8	92.3	120.8	138.1	122.3	81.4
97.5°	73.3	80.3	94.1	104.6	115.2	150.8	188.8	226.9	225.1	174.0	108.2
100°	142.7	157.8	187.1	208.4	229.7	278.0	321.7	329.1	278.3	191.7	115.6
102.5°	268.5	297.0	329.4	352.3	375.2	407.3	408.7	367.1	280.1	185.0	115.9
105°	417.1	439.0	460.8	466.6	472.4	467.9	428.1	354.8	261.1	175.8	117.7
107.5°	511.6	514.7	515.1	508.0	501.0	466.5	407.3	328.7	243.4	170.9	121.5
110°	537.6	530.9	515.8	501.4	486.9	441.8	378.7	304.4	231.5	169.5	126.5

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	530.6	518.2	495.7	478.6	461.5	412.6	352.7	287.5	223.7	169.8	131.8
115°	510.1	493.9	468.9	450.8	432.6	386.5	332.2	274.1	218.4	171.2	137.0
117.5°	484.4	467.2	441.4	424.2	406.9	363.9	315.3	264.9	215.6	173.3	142.7
120°	457.7	441.1	416.4	400.4	384.4	347.0	303.3	257.9	213.1	175.5	148.3
122.5°	433.7	417.5	396.0	381.9	367.8	332.9	293.8	251.9	211.7	177.9	153.3
125°	412.2	398.8	378.4	365.2	352.0	321.0	284.7	246.3	210.0	180.4	158.5
127.5°	393.9	381.2	363.2	350.9	338.6	309.0	275.5	241.0	208.9	182.8	163.5
130°	377.3	365.3	348.1	336.5	324.8	297.0	266.7	235.7	208.2	185.7	168.1
132.5°	361.1	349.1	332.2	321.4	310.7	285.7	258.2	231.5	207.9	188.5	172.6
135°	343.5	331.9	316.7	306.8	297.0	273.7	250.5	227.6	207.5	190.6	176.5
137.5°	325.5	315.3	300.9	292.1	283.3	264.2	244.2	224.8	207.5	192.7	179.7
140°	307.2	298.1	286.8	279.0	271.3	255.1	238.2	222.3	207.2	194.1	182.1
142.5°	291.4	283.3	272.7	266.5	260.4	247.0	233.2	219.8	207.2	195.2	184.3
145°	275.9	269.9	261.4	256.3	251.2	240.3	228.7	217.7	206.5	195.9	186.0
147.5°	263.5	258.6	251.2	247.3	243.4	234.6	225.1	215.6	205.4	196.2	187.1
150°	252.3	248.0	242.7	239.6	236.4	229.0	221.3	212.8	204.3	195.9	187.8
152.5°	243.1	239.6	235.7	233.0	230.4	224.4	217.4	210.3	202.6	195.2	188.1
155°	235.0	232.5	228.7	226.8	224.8	219.5	213.9	207.2	200.5	194.5	188.5
157.5°	227.2	225.1	222.3	220.7	219.1	214.6	209.6	204.3	198.4	193.1	188.5
160°	220.2	218.4	216.0	214.8	213.5	209.6	205.7	201.2	196.2	192.0	188.5
162.5°	213.5	212.4	210.0	209.1	208.2	205.0	201.9	198.4	194.5	191.0	188.1
165°	207.2	205.7	204.3	203.6	202.9	200.5	198.0	195.2	192.0	189.5	187.4
167.5°	200.8	200.1	199.4	198.7	198.0	196.2	194.1	192.0	189.9	188.1	187.1
170°	195.9	194.8	194.5	194.2	193.8	192.4	191.3	189.5	188.1	187.1	186.4
172.5°	191.0	190.6	190.2	190.0	189.9	188.8	188.1	187.1	186.0	185.7	185.3
175°	187.4	187.1	187.1	186.9	186.7	186.4	186.0	185.0	184.6	184.3	184.6
177.5°	184.6	184.6	184.6	184.6	184.6	184.3	184.3	183.6	183.2	183.6	184.3
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1921.0	1914.5	1914.5	1910.6	1910.6	1889.7	1889.7	1896.2	1888.3	1879.2	1866.1
5°	1970.7	1956.3	1952.4	1947.2	1930.2	1904.0	1893.6	1889.7	1874.0	1854.3	1832.1
7.5°	2017.8	1994.3	1982.5	1970.7	1948.5	1911.9	1891.0	1876.6	1853.0	1823.0	1794.2
10°	2063.6	2033.5	2003.4	1989.0	1957.7	1911.9	1881.8	1858.3	1824.3	1783.7	1743.2
12.5°	2105.4	2042.7	2037.4	2008.7	1962.9	1910.6	1864.8	1830.8	1787.7	1740.6	1693.5
15°	2142.0	2078.0	2046.6	2020.4	1960.3	1894.9	1846.5	1804.7	1747.1	1693.5	1636.0
17.5°	2160.4	2091.0	2070.1	2027.0	1965.5	1880.5	1815.1	1764.1	1701.3	1637.3	1571.9
20°	2178.7	2097.6	2063.6	2033.5	1949.8	1853.0	1779.8	1721.0	1651.7	1575.8	1503.9
22.5°	2187.8	2097.6	2057.0	2015.2	1934.1	1823.0	1736.7	1667.3	1586.3	1509.1	1422.8
25°	2172.1	2089.7	2041.4	1998.2	1906.7	1786.3	1687.0	1608.5	1522.2	1434.6	1347.0
27.5°	2132.9	2071.4	2015.2	1970.7	1868.7	1739.3	1634.7	1545.7	1456.8	1358.7	1269.8
30°	2059.7	2032.2	1987.7	1938.0	1826.9	1697.4	1573.2	1481.6	1383.6	1285.5	1192.6
32.5°	1945.9	1969.4	1940.7	1897.5	1777.2	1639.9	1507.8	1415.0	1307.7	1201.8	1116.8
35°	1807.3	1891.0	1875.3	1845.2	1724.9	1578.4	1446.3	1333.9	1226.6	1119.4	1034.4
37.5°	1655.6	1782.4	1795.5	1777.2	1664.7	1515.6	1370.5	1260.6	1150.8	1042.3	955.9
40°	1447.6	1642.5	1684.3	1692.2	1602.0	1439.8	1288.1	1180.9	1072.3	966.4	861.8
42.5°	1256.7	1502.6	1554.9	1587.6	1522.2	1365.3	1212.3	1093.3	986.0	890.6	785.9
45°	1077.6	1333.9	1418.9	1460.7	1432.0	1280.3	1122.0	1010.9	912.8	825.2	724.5
47.5°	893.2	1150.8	1269.8	1336.5	1336.5	1193.9	1035.7	925.9	831.7	757.2	668.2
50°	770.2	984.7	1107.6	1195.3	1218.8	1106.3	957.3	850.0	761.1	680.0	612.0
52.5°	656.5	848.7	950.7	1042.3	1110.3	1012.2	869.6	772.9	685.2	609.4	555.8
55°	567.6	711.4	804.2	904.9	980.8	916.7	784.6	690.5	614.6	551.9	506.1
57.5°	482.5	608.1	683.9	772.9	853.9	805.6	699.6	618.6	551.9	496.9	456.4
60°	410.6	512.6	571.5	640.8	741.5	707.5	619.9	545.3	491.7	442.0	408.0
62.5°	349.2	430.2	479.9	529.6	621.2	605.5	537.5	479.9	434.2	392.3	363.5
65°	286.4	353.1	392.3	435.5	508.7	515.2	460.3	419.8	377.9	341.3	315.2
67.5°	231.5	283.8	319.1	355.7	414.5	432.9	394.9	360.9	325.6	295.5	272.0
70°	187.0	223.6	249.8	278.5	326.9	349.2	329.5	306.0	277.2	252.4	231.5
72.5°	147.8	171.3	187.0	209.2	248.5	270.7	269.4	248.5	227.5	210.5	193.5
75°	108.5	126.8	139.9	154.3	185.7	206.6	211.9	202.7	181.8	168.7	155.6
77.5°	82.4	92.8	99.4	109.8	132.1	150.4	158.2	155.6	141.2	130.8	121.6
80°	62.8	65.4	68.0	71.9	90.2	107.2	112.5	111.2	103.3	99.4	88.9
82.5°	44.5	45.8	47.1	48.4	54.9	69.3	74.5	77.2	70.6	66.7	57.5
85°	26.2	27.5	27.5	30.1	31.4	35.3	44.5	44.5	43.2	37.9	36.6
87.5°	13.1	13.1	11.8	11.8	13.1	14.4	17.0	19.6	17.0	15.7	14.4
90°	7.0	5.3	4.8	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	28.2	18.7	16.8	14.8	12.0	10.2	7.4	5.3	7.4	10.2	12.0
95°	50.7	34.5	30.3	26.1	20.4	17.3	13.7	12.3	13.7	17.3	20.4
97.5°	65.5	44.7	40.0	35.2	28.9	24.3	20.4	18.3	20.4	24.3	28.9
100°	72.6	53.9	49.0	44.0	37.0	31.4	28.2	27.1	28.2	31.4	37.0
102.5°	78.9	62.0	57.0	52.1	44.7	39.1	35.9	35.2	35.9	39.1	44.7
105°	86.3	69.8	64.8	59.9	52.1	46.9	44.4	43.0	44.4	46.9	52.1
107.5°	93.7	77.5	72.6	67.6	59.9	55.0	52.5	51.4	52.5	55.0	59.9
110°	101.1	85.6	80.5	75.4	68.0	63.4	61.3	59.9	61.3	63.4	68.0

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	108.2	93.4	88.1	82.8	75.7	71.5	69.1	67.6	69.1	71.5	75.7
115°	115.6	100.4	95.6	90.9	83.9	79.6	77.5	75.7	77.5	79.6	83.9
117.5°	122.3	108.2	103.2	98.3	91.6	87.7	85.6	84.2	85.6	87.7	91.6
120°	129.3	115.6	110.6	105.7	98.6	95.5	93.4	92.0	93.4	95.5	98.6
122.5°	136.0	123.3	118.2	113.1	106.0	102.5	100.4	99.4	100.4	102.5	106.0
125°	142.7	130.0	125.0	120.1	113.1	108.9	106.8	105.7	106.8	108.9	113.1
127.5°	149.0	136.7	131.6	126.5	119.8	115.2	112.4	111.0	112.4	115.2	119.8
130°	154.7	142.3	137.4	132.5	125.4	120.5	117.0	115.6	117.0	120.5	125.4
132.5°	159.6	148.0	143.0	138.1	130.7	125.4	121.5	119.8	121.5	125.4	130.7
135°	164.2	152.9	148.0	143.0	134.9	129.7	125.4	124.0	125.4	129.7	134.9
137.5°	168.1	156.8	152.2	147.6	139.5	133.9	129.7	127.9	129.7	133.9	139.5
140°	171.2	160.7	156.1	151.5	143.7	138.1	133.9	132.5	133.9	138.1	143.7
142.5°	173.7	163.5	159.2	155.0	147.6	142.0	138.1	137.0	138.1	142.0	147.6
145°	176.2	166.6	162.8	158.9	151.8	146.6	143.0	141.6	143.0	146.6	151.8
147.5°	178.3	169.1	165.6	162.1	156.1	151.1	147.6	146.6	147.6	151.1	156.1
150°	179.7	171.6	168.4	165.2	159.9	155.4	152.6	151.5	152.6	155.4	159.9
152.5°	181.1	174.0	171.2	168.4	163.5	159.6	156.8	156.4	156.8	159.6	163.5
155°	182.5	176.5	173.8	171.2	167.3	163.5	161.4	161.0	161.4	163.5	167.3
157.5°	183.6	178.3	176.0	173.7	170.5	167.0	165.2	164.9	165.2	167.0	170.5
160°	184.3	180.0	178.1	176.2	173.3	170.5	169.1	168.8	169.1	170.5	173.3
162.5°	184.6	181.1	179.7	178.3	175.8	173.7	172.3	172.6	172.3	173.7	175.8
165°	185.0	181.8	180.8	179.7	177.9	175.8	175.1	175.5	175.1	175.8	177.9
167.5°	185.0	182.5	181.8	181.1	179.7	178.3	177.6	177.9	177.6	178.3	179.7
170°	184.6	182.8	182.3	181.8	181.1	180.0	179.7	180.4	179.7	180.0	181.1
172.5°	184.3	183.2	182.8	182.5	182.1	181.1	181.4	181.8	181.4	181.1	182.1
175°	183.9	183.2	183.0	182.8	182.8	182.1	182.5	182.8	182.5	182.1	182.8
177.5°	183.6	183.2	183.2	183.2	183.2	182.5	182.8	183.6	182.8	182.5	183.2
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1860.9	1862.2	1866.1	1854.3	1836.0	1828.2	1804.7	1800.7	1796.8	1796.8	1800.7
5°	1819.0	1813.8	1815.1	1792.9	1766.7	1751.0	1718.3	1723.6	1706.6	1696.1	1698.7
7.5°	1773.3	1758.9	1757.6	1728.8	1696.1	1667.3	1633.3	1625.5	1609.8	1591.5	1583.6
10°	1715.7	1705.3	1685.7	1653.0	1611.1	1587.6	1541.8	1514.3	1510.4	1483.0	1472.5
12.5°	1656.9	1638.6	1619.0	1573.2	1526.1	1488.2	1454.2	1424.1	1403.2	1379.6	1364.0
15°	1588.9	1566.6	1544.4	1496.0	1441.1	1403.2	1352.2	1307.7	1246.3	1197.9	1170.4
17.5°	1514.3	1489.5	1459.4	1405.8	1352.2	1299.9	1205.7	1153.4	1110.3	1081.5	1064.5
20°	1437.2	1409.7	1379.6	1326.0	1233.2	1141.6	1089.3	1048.8	1022.6	993.9	972.9
22.5°	1356.1	1327.3	1294.6	1210.9	1112.9	1048.8	1008.3	970.3	932.4	916.7	906.3
25°	1280.3	1254.1	1212.3	1098.5	1021.3	962.5	916.7	891.9	872.2	851.3	831.7
27.5°	1201.8	1153.4	1094.6	999.1	950.7	890.6	857.9	839.6	805.6	791.2	782.0
30°	1107.6	1054.0	997.8	929.8	873.6	831.7	801.6	771.6	751.9	737.6	721.9
32.5°	1012.2	961.2	925.9	855.2	813.4	770.2	741.5	723.2	694.4	685.2	678.7
35°	929.8	886.6	855.2	797.7	758.5	719.2	698.3	670.9	652.6	635.6	625.1
37.5°	848.7	825.2	792.5	744.1	702.2	670.9	642.1	632.9	608.1	598.9	588.5
40°	792.5	757.2	729.7	687.9	652.6	618.6	600.2	579.3	562.3	547.9	544.0
42.5°	724.5	698.3	682.6	636.9	600.2	580.6	558.4	534.9	521.8	510.0	495.6
45°	673.5	649.9	627.7	591.1	558.4	533.5	513.9	498.2	476.0	470.8	448.5
47.5°	619.9	596.3	579.3	542.7	512.6	489.1	474.7	453.8	435.5	423.7	413.2
50°	566.2	546.6	530.9	499.5	473.4	448.5	428.9	408.0	400.2	380.5	374.0
52.5°	515.2	502.2	485.2	455.1	428.9	408.0	387.1	370.1	358.3	347.9	340.0
55°	472.1	451.2	443.3	410.6	388.4	366.2	347.9	337.4	323.0	316.5	309.9
57.5°	423.7	411.9	398.9	374.0	349.2	328.2	315.2	299.5	291.6	283.8	278.5
60°	381.9	364.9	354.4	333.5	311.2	291.6	279.9	268.1	257.6	251.1	240.6
62.5°	333.5	320.4	313.9	291.6	273.3	255.0	244.5	232.8	224.9	213.2	200.1
65°	291.6	281.2	273.3	255.0	238.0	221.0	210.5	196.2	185.7	179.2	177.8
67.5°	255.0	247.2	235.4	218.4	201.4	188.3	176.5	164.8	163.5	160.8	160.8
70°	214.5	206.6	200.1	181.8	167.4	153.0	150.4	146.5	142.5	141.2	138.6
72.5°	179.2	172.6	164.8	149.1	134.7	130.8	128.2	125.5	121.6	120.3	119.0
75°	145.2	136.0	130.8	116.4	112.5	109.8	107.2	103.3	100.7	99.4	96.8
77.5°	111.2	102.0	102.0	94.2	91.5	87.6	85.0	82.4	81.1	78.5	78.5
80°	78.5	78.5	75.8	71.9	68.0	66.7	62.8	61.5	60.2	61.5	58.8
82.5°	57.5	52.3	52.3	49.7	47.1	45.8	43.2	43.2	41.8	41.8	41.8
85°	32.7	32.7	31.4	28.8	27.5	27.5	26.2	26.2	24.8	24.8	23.5
87.5°	13.1	11.8	13.1	11.8	11.8	10.5	10.5	10.5	9.2	10.5	9.2
90°	4.2	4.8	5.3	7.0	9.5	11.6	12.0	11.6	11.3	10.6	11.3
92.5°	14.8	16.8	18.7	28.2	41.6	53.6	54.3	45.4	35.6	30.3	26.4
95°	26.1	30.3	34.5	50.7	81.4	122.3	138.1	120.8	92.3	70.8	56.0
97.5°	35.2	40.0	44.7	65.5	108.2	174.0	225.1	226.9	188.8	150.8	115.2
100°	44.0	49.0	53.9	72.6	115.6	191.7	278.3	329.1	321.7	278.0	229.7
102.5°	52.1	57.0	62.0	78.9	115.9	185.0	280.1	367.1	408.7	407.3	375.2
105°	59.9	64.8	69.8	86.3	117.7	175.8	261.1	354.8	428.1	467.9	472.4
107.5°	67.6	72.6	77.5	93.7	121.5	170.9	243.4	328.7	407.3	466.5	501.0
110°	75.4	80.5	85.6	101.1	126.5	169.5	231.5	304.4	378.7	441.8	486.9

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	82.8	88.1	93.4	108.2	131.8	169.8	223.7	287.5	352.7	412.6	461.5
115°	90.9	95.6	100.4	115.6	137.0	171.2	218.4	274.1	332.2	386.5	432.6
117.5°	98.3	103.2	108.2	122.3	142.7	173.3	215.6	264.9	315.3	363.9	406.9
120°	105.7	110.6	115.6	129.3	148.3	175.5	213.1	257.9	303.3	347.0	384.4
122.5°	113.1	118.2	123.3	136.0	153.3	177.9	211.7	251.9	293.8	332.9	367.8
125°	120.1	125.0	130.0	142.7	158.5	180.4	210.0	246.3	284.7	321.0	352.0
127.5°	126.5	131.6	136.7	149.0	163.5	182.8	208.9	241.0	275.5	309.0	338.6
130°	132.5	137.4	142.3	154.7	168.1	185.7	208.2	235.7	266.7	297.0	324.8
132.5°	138.1	143.0	148.0	159.6	172.6	188.5	207.9	231.5	258.2	285.7	310.7
135°	143.0	148.0	152.9	164.2	176.5	190.6	207.5	227.6	250.5	273.7	297.0
137.5°	147.6	152.2	156.8	168.1	179.7	192.7	207.5	224.8	244.2	264.2	283.3
140°	151.5	156.1	160.7	171.2	182.1	194.1	207.2	222.3	238.2	255.1	271.3
142.5°	155.0	159.2	163.5	173.7	184.3	195.2	207.2	219.8	233.2	247.0	260.4
145°	158.9	162.8	166.6	176.2	186.0	195.9	206.5	217.7	228.7	240.3	251.2
147.5°	162.1	165.6	169.1	178.3	187.1	196.2	205.4	215.6	225.1	234.6	243.4
150°	165.2	168.4	171.6	179.7	187.8	195.9	204.3	212.8	221.3	229.0	236.4
152.5°	168.4	171.2	174.0	181.1	188.1	195.2	202.6	210.3	217.4	224.4	230.4
155°	171.2	173.8	176.5	182.5	188.5	194.5	200.5	207.2	213.9	219.5	224.8
157.5°	173.7	176.0	178.3	183.6	188.5	193.1	198.4	204.3	209.6	214.6	219.1
160°	176.2	178.1	180.0	184.3	188.5	192.0	196.2	201.2	205.7	209.6	213.5
162.5°	178.3	179.7	181.1	184.6	188.1	191.0	194.5	198.4	201.9	205.0	208.2
165°	179.7	180.8	181.8	185.0	187.4	189.5	192.0	195.2	198.0	200.5	202.9
167.5°	181.1	181.8	182.5	185.0	187.1	188.1	189.9	192.0	194.1	196.2	198.0
170°	181.8	182.3	182.8	184.6	186.4	187.1	188.1	189.5	191.3	192.4	193.8
172.5°	182.5	182.8	183.2	184.3	185.3	185.7	186.0	187.1	188.1	188.8	189.9
175°	182.8	183.0	183.2	183.9	184.6	184.3	184.6	185.0	186.0	186.4	186.7
177.5°	183.2	183.2	183.2	183.6	184.3	183.6	183.2	183.6	184.3	184.3	184.6
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1800.7	1798.1	1790.3	1792.9	1789.0	1789.0	1786.3	1786.3	1786.3	1792.9	1789.0
5°	1702.7	1693.5	1684.3	1680.4	1676.5	1672.6	1672.6	1671.3	1683.0	1680.4	1690.9
7.5°	1581.0	1578.4	1560.1	1560.1	1553.6	1551.0	1557.5	1558.8	1560.1	1562.7	1569.3
10°	1472.5	1466.0	1439.8	1442.4	1438.5	1433.3	1437.2	1434.6	1443.7	1446.3	1443.7
12.5°	1344.3	1332.6	1303.8	1289.4	1273.7	1261.9	1276.3	1265.9	1302.5	1313.0	1341.7
15°	1174.3	1152.1	1132.5	1132.5	1118.1	1107.6	1114.2	1125.9	1133.8	1145.6	1150.8
17.5°	1060.6	1051.4	1035.7	1026.6	1022.6	1018.7	1018.7	1023.9	1040.9	1039.6	1050.1
20°	963.8	958.6	950.7	938.9	935.0	932.4	932.4	932.4	944.2	954.6	961.2
22.5°	897.1	893.2	887.9	872.2	864.4	861.8	868.3	872.2	881.4	889.2	895.8
25°	830.4	821.2	812.1	806.9	802.9	802.9	805.6	806.9	810.8	814.7	822.6
27.5°	775.5	768.9	755.9	741.5	741.5	737.6	740.2	742.8	751.9	765.0	771.6
30°	714.0	712.7	707.5	702.2	697.0	694.4	699.6	703.6	704.9	711.4	711.4
32.5°	669.6	660.4	651.2	646.0	643.4	642.1	643.4	648.6	648.6	656.5	665.6
35°	625.1	619.9	610.7	601.6	598.9	592.4	597.6	602.9	612.0	615.9	619.9
37.5°	576.7	570.2	566.2	563.6	558.4	559.7	555.8	563.6	571.5	570.2	572.8
40°	540.1	528.3	516.5	515.2	513.9	512.6	512.6	513.9	519.2	524.4	532.2
42.5°	493.0	489.1	478.6	468.2	465.5	462.9	460.3	465.5	476.0	485.2	489.1
45°	444.6	439.4	436.8	428.9	423.7	422.4	419.8	426.3	435.5	439.4	442.0
47.5°	400.2	398.9	391.0	392.3	388.4	389.7	388.4	392.3	392.3	396.2	398.9
50°	370.1	366.2	362.2	359.6	355.7	355.7	354.4	355.7	360.9	366.2	364.9
52.5°	340.0	333.5	332.2	330.9	328.2	330.9	326.9	328.2	333.5	336.1	334.8
55°	304.7	303.4	300.8	298.2	296.9	295.5	295.5	295.5	300.8	304.7	306.0
57.5°	277.2	270.7	265.5	265.5	260.2	258.9	261.5	262.9	266.8	269.4	272.0
60°	239.3	236.7	228.9	224.9	217.1	215.8	215.8	221.0	227.5	236.7	239.3
62.5°	198.8	194.9	193.5	193.5	193.5	193.5	193.5	193.5	193.5	194.9	194.9
65°	176.5	177.8	176.5	175.2	176.5	176.5	175.2	175.2	175.2	176.5	177.8
67.5°	158.2	156.9	158.2	156.9	155.6	155.6	154.3	155.6	156.9	158.2	158.2
70°	137.3	137.3	136.0	137.3	136.0	134.7	133.4	133.4	136.0	137.3	137.3
72.5°	117.7	117.7	116.4	116.4	113.8	113.8	115.1	113.8	113.8	117.7	117.7
75°	98.1	96.8	95.5	95.5	94.2	94.2	94.2	92.8	95.5	95.5	96.8
77.5°	77.2	77.2	77.2	75.8	75.8	74.5	74.5	75.8	75.8	75.8	77.2
80°	58.8	58.8	58.8	57.5	56.2	56.2	56.2	56.2	56.2	57.5	56.2
82.5°	40.5	40.5	40.5	40.5	40.5	39.2	39.2	39.2	40.5	40.5	39.2
85°	24.8	23.5	24.8	24.8	23.5	24.8	23.5	23.5	22.2	22.2	23.5
87.5°	10.5	9.2	7.8	7.8	9.2	7.8	7.8	7.8	9.2	7.8	7.8
90°	11.4	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.4
92.5°	25.0	23.6	23.3	21.8	22.2	21.5	22.2	21.8	23.3	23.6	25.0
95°	52.2	48.3	43.7	40.9	39.8	40.2	39.8	40.9	43.7	48.3	52.2
97.5°	104.6	94.1	80.3	73.3	69.4	67.3	69.4	73.3	80.3	94.1	104.6
100°	208.4	187.1	157.8	142.7	132.5	126.1	132.5	142.7	157.8	187.1	208.4
102.5°	352.3	329.4	297.0	268.5	255.1	245.9	255.1	268.5	297.0	329.4	352.3
105°	466.6	460.8	439.0	417.1	402.0	397.1	402.0	417.1	439.0	460.8	466.6
107.5°	508.0	515.1	514.7	511.6	507.0	498.9	507.0	511.6	514.7	515.1	508.0
110°	501.4	515.8	530.9	537.6	540.8	540.4	540.8	537.6	530.9	515.8	501.4

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	478.6	495.7	518.2	530.6	537.3	539.7	537.3	530.6	518.2	495.7	478.6
115°	450.8	468.9	493.9	510.1	519.3	522.5	519.3	510.1	493.9	468.9	450.8
117.5°	424.2	441.4	467.2	484.4	493.9	496.4	493.9	484.4	467.2	441.4	424.2
120°	400.4	416.4	441.1	457.7	467.9	471.4	467.9	457.7	441.1	416.4	400.4
122.5°	381.9	396.0	417.5	433.7	442.5	445.3	442.5	433.7	417.5	396.0	381.9
125°	365.2	378.4	398.8	412.2	421.0	423.8	421.0	412.2	398.8	378.4	365.2
127.5°	350.9	363.2	381.2	393.9	401.6	403.7	401.6	393.9	381.2	363.2	350.9
130°	336.5	348.1	365.3	377.3	384.4	387.2	384.4	377.3	365.3	348.1	336.5
132.5°	321.4	332.2	349.1	361.1	367.5	369.9	367.5	361.1	349.1	332.2	321.4
135°	306.8	316.7	331.9	343.5	349.8	351.3	349.8	343.5	331.9	316.7	306.8
137.5°	292.1	300.9	315.3	325.5	331.2	333.3	331.2	325.5	315.3	300.9	292.1
140°	279.0	286.8	298.1	307.2	312.5	314.6	312.5	307.2	298.1	286.8	279.0
142.5°	266.5	272.7	283.3	291.4	295.9	295.9	295.9	291.4	283.3	272.7	266.5
145°	256.3	261.4	269.9	275.9	279.4	280.4	279.4	275.9	269.9	261.4	256.3
147.5°	247.3	251.2	258.6	263.5	266.0	266.7	266.0	263.5	258.6	251.2	247.3
150°	239.6	242.7	248.0	252.3	254.4	254.7	254.4	252.3	248.0	242.7	239.6
152.5°	233.0	235.7	239.6	243.1	244.5	244.5	244.5	243.1	239.6	235.7	233.0
155°	226.8	228.7	232.5	235.0	236.4	235.7	236.4	235.0	232.5	228.7	226.8
157.5°	220.7	222.3	225.1	227.2	227.9	227.9	227.9	227.2	225.1	222.3	220.7
160°	214.8	216.0	218.4	220.2	220.5	220.5	220.5	220.2	218.4	216.0	214.8
162.5°	209.1	210.0	212.4	213.5	213.9	213.5	213.9	213.5	212.4	210.0	209.1
165°	203.6	204.3	205.7	207.2	207.2	206.8	207.2	207.2	205.7	204.3	203.6
167.5°	198.7	199.4	200.1	200.8	200.8	200.5	200.8	200.8	200.1	199.4	198.7
170°	194.2	194.5	194.8	195.9	195.5	194.8	195.5	195.9	194.8	194.5	194.2
172.5°	190.0	190.2	190.6	191.0	190.6	190.2	190.6	191.0	190.6	190.2	190.0
175°	186.9	187.1	187.1	187.4	187.1	186.4	187.1	187.4	187.1	187.1	186.9
177.5°	184.6	184.6	184.6	184.6	184.3	183.6	184.3	184.6	184.6	184.6	184.6
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1792.9	1799.4	1796.8	1782.4	1796.8	1800.7	1808.6	1816.4	1821.7	1829.5	1836.0
5°	1680.4	1693.5	1701.3	1693.5	1719.7	1723.6	1741.9	1752.3	1768.0	1781.1	1791.6
7.5°	1574.5	1585.0	1600.6	1603.3	1619.0	1637.3	1663.4	1689.6	1714.4	1727.5	1739.3
10°	1460.7	1479.0	1502.6	1497.3	1520.9	1549.6	1577.1	1619.0	1639.9	1663.4	1684.3
12.5°	1347.0	1358.7	1390.1	1400.6	1434.6	1456.8	1494.7	1520.9	1573.2	1600.6	1619.0
15°	1148.2	1196.6	1235.8	1282.9	1327.3	1369.2	1403.2	1450.3	1496.0	1517.0	1547.0
17.5°	1057.9	1080.2	1103.7	1127.3	1184.8	1259.3	1319.5	1370.5	1409.7	1437.2	1472.5
20°	963.8	986.0	1012.2	1034.4	1069.7	1123.3	1197.9	1285.5	1332.6	1361.3	1395.3
22.5°	897.1	918.0	935.0	954.6	982.1	1021.3	1077.6	1186.1	1248.9	1284.2	1314.3
25°	825.2	851.3	869.6	884.0	906.3	949.4	995.2	1056.6	1169.1	1196.6	1238.4
27.5°	775.5	783.3	804.2	826.5	848.7	872.2	919.3	971.6	1047.5	1107.6	1158.6
30°	716.6	736.2	755.9	765.0	784.6	818.6	847.4	903.6	962.5	1009.6	1071.0
32.5°	672.2	683.9	697.0	719.2	737.6	761.1	789.9	836.9	886.6	916.7	963.8
35°	622.5	630.3	657.8	666.9	685.2	708.8	737.6	774.2	827.8	851.3	885.3
37.5°	575.4	593.7	601.6	622.5	639.5	663.0	683.9	725.8	761.1	788.6	819.9
40°	538.8	546.6	561.0	579.3	593.7	612.0	638.2	668.2	706.2	728.4	755.9
42.5°	494.3	500.9	519.2	529.6	553.2	570.2	585.9	622.5	656.5	673.5	700.9
45°	445.9	461.6	473.4	494.3	507.4	528.3	547.9	574.1	605.5	625.1	640.8
47.5°	404.1	419.8	431.5	451.2	472.1	481.2	502.2	529.6	558.4	574.1	596.3
50°	370.1	375.3	397.5	406.7	428.9	447.2	461.6	485.2	516.5	525.7	544.0
52.5°	337.4	341.3	355.7	367.5	387.1	402.8	421.1	443.3	469.5	483.9	498.2
55°	308.6	311.2	317.8	330.9	343.9	363.5	380.5	401.5	423.7	439.4	452.5
57.5°	275.9	281.2	286.4	294.2	307.3	325.6	343.9	363.5	381.9	392.3	409.3
60°	238.0	245.9	255.0	264.2	273.3	286.4	307.3	325.6	342.6	351.8	364.9
62.5°	197.5	213.2	221.0	231.5	239.3	251.1	266.8	287.7	299.5	311.2	321.7
65°	177.8	179.2	180.5	190.9	205.3	217.1	231.5	247.2	265.5	273.3	281.2
67.5°	158.2	159.5	162.2	163.5	168.7	181.8	197.5	214.5	228.9	234.1	241.9
70°	138.6	138.6	143.8	145.2	146.5	147.8	160.8	177.8	190.9	197.5	206.6
72.5°	117.7	119.0	121.6	122.9	125.5	128.2	132.1	141.2	156.9	163.5	173.9
75°	96.8	98.1	99.4	100.7	104.6	105.9	109.8	115.1	121.6	129.5	136.0
77.5°	77.2	77.2	78.5	81.1	83.7	85.0	88.9	91.5	94.2	98.1	103.3
80°	57.5	58.8	58.8	61.5	61.5	62.8	64.1	68.0	70.6	73.2	75.8
82.5°	39.2	41.8	41.8	41.8	43.2	44.5	45.8	45.8	48.4	49.7	53.6
85°	23.5	24.8	24.8	24.8	23.5	26.2	26.2	27.5	27.5	27.5	28.8
87.5°	9.2	7.8	9.2	9.2	9.2	10.5	9.2	9.2	10.5	11.8	11.8
90°	11.3	10.6	11.3	11.6	12.0	11.6	9.5	7.0	5.3	4.8	4.2
92.5°	26.4	30.3	35.6	45.4	54.3	53.6	41.6	28.2	18.7	16.8	14.8
95°	56.0	70.8	92.3	120.8	138.1	122.3	81.4	50.7	34.5	30.3	26.1
97.5°	115.2	150.8	188.8	226.9	225.1	174.0	108.2	65.5	44.7	40.0	35.2
100°	229.7	278.0	321.7	329.1	278.3	191.7	115.6	72.6	53.9	49.0	44.0
102.5°	375.2	407.3	408.7	367.1	280.1	185.0	115.9	78.9	62.0	57.0	52.1
105°	472.4	467.9	428.1	354.8	261.1	175.8	117.7	86.3	69.8	64.8	59.9
107.5°	501.0	466.5	407.3	328.7	243.4	170.9	121.5	93.7	77.5	72.6	67.6
110°	486.9	441.8	378.7	304.4	231.5	169.5	126.5	101.1	85.6	80.5	75.4



TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	461.5	412.6	352.7	287.5	223.7	169.8	131.8	108.2	93.4	88.1	82.8
115°	432.6	386.5	332.2	274.1	218.4	171.2	137.0	115.6	100.4	95.6	90.9
117.5°	406.9	363.9	315.3	264.9	215.6	173.3	142.7	122.3	108.2	103.2	98.3
120°	384.4	347.0	303.3	257.9	213.1	175.5	148.3	129.3	115.6	110.6	105.7
122.5°	367.8	332.9	293.8	251.9	211.7	177.9	153.3	136.0	123.3	118.2	113.1
125°	352.0	321.0	284.7	246.3	210.0	180.4	158.5	142.7	130.0	125.0	120.1
127.5°	338.6	309.0	275.5	241.0	208.9	182.8	163.5	149.0	136.7	131.6	126.5
130°	324.8	297.0	266.7	235.7	208.2	185.7	168.1	154.7	142.3	137.4	132.5
132.5°	310.7	285.7	258.2	231.5	207.9	188.5	172.6	159.6	148.0	143.0	138.1
135°	297.0	273.7	250.5	227.6	207.5	190.6	176.5	164.2	152.9	148.0	143.0
137.5°	283.3	264.2	244.2	224.8	207.5	192.7	179.7	168.1	156.8	152.2	147.6
140°	271.3	255.1	238.2	222.3	207.2	194.1	182.1	171.2	160.7	156.1	151.5
142.5°	260.4	247.0	233.2	219.8	207.2	195.2	184.3	173.7	163.5	159.2	155.0
145°	251.2	240.3	228.7	217.7	206.5	195.9	186.0	176.2	166.6	162.8	158.9
147.5°	243.4	234.6	225.1	215.6	205.4	196.2	187.1	178.3	169.1	165.6	162.1
150°	236.4	229.0	221.3	212.8	204.3	195.9	187.8	179.7	171.6	168.4	165.2
152.5°	230.4	224.4	217.4	210.3	202.6	195.2	188.1	181.1	174.0	171.2	168.4
155°	224.8	219.5	213.9	207.2	200.5	194.5	188.5	182.5	176.5	173.8	171.2
157.5°	219.1	214.6	209.6	204.3	198.4	193.1	188.5	183.6	178.3	176.0	173.7
160°	213.5	209.6	205.7	201.2	196.2	192.0	188.5	184.3	180.0	178.1	176.2
162.5°	208.2	205.0	201.9	198.4	194.5	191.0	188.1	184.6	181.1	179.7	178.3
165°	202.9	200.5	198.0	195.2	192.0	189.5	187.4	185.0	181.8	180.8	179.7
167.5°	198.0	196.2	194.1	192.0	189.9	188.1	187.1	185.0	182.5	181.8	181.1
170°	193.8	192.4	191.3	189.5	188.1	187.1	186.4	184.6	182.8	182.3	181.8
172.5°	189.9	188.8	188.1	187.1	186.0	185.7	185.3	184.3	183.2	182.8	182.5
175°	186.7	186.4	186.0	185.0	184.6	184.3	184.6	183.9	183.2	183.0	182.8
177.5°	184.6	184.3	184.3	183.6	183.2	183.6	184.3	183.6	183.2	183.2	183.2
180°	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1881.8	1881.8	1881.8	1881.8
2.5°	1847.8	1843.9	1867.4	1893.6
5°	1809.9	1816.4	1846.5	1883.1
7.5°	1770.7	1785.0	1820.3	1868.7
10°	1715.7	1741.9	1795.5	1845.2
12.5°	1662.1	1697.4	1748.4	1807.3
15°	1602.0	1641.2	1704.0	1774.6
17.5°	1535.3	1579.7	1653.0	1730.1
20°	1464.6	1523.5	1600.6	1684.3
22.5°	1386.2	1456.8	1536.6	1629.4
25°	1310.3	1387.5	1467.3	1574.5
27.5°	1235.8	1311.6	1400.6	1509.1
30°	1161.3	1230.6	1326.0	1442.4
32.5°	1081.5	1153.4	1254.1	1373.1
35°	1008.3	1080.2	1174.3	1292.0
37.5°	929.8	1006.9	1097.2	1218.8
40°	838.2	928.5	1016.1	1132.5
42.5°	762.4	857.9	942.9	1052.7
45°	702.2	792.5	863.1	970.3
47.5°	646.0	719.2	791.2	890.6
50°	592.4	648.6	723.2	812.1
52.5°	537.5	585.9	649.9	733.6
55°	487.8	533.5	591.1	655.2
57.5°	442.0	474.7	532.2	589.8
60°	391.0	425.0	469.5	517.9
62.5°	347.9	374.0	415.9	456.4
65°	302.1	326.9	358.3	396.2
67.5°	260.2	282.5	307.3	337.4
70°	222.3	239.3	257.6	283.8
72.5°	181.8	200.1	217.1	238.0
75°	149.1	156.9	171.3	185.7
77.5°	115.1	125.5	133.4	145.2
80°	82.4	91.5	94.2	103.3
82.5°	54.9	60.2	65.4	68.0
85°	31.4	34.0	39.2	40.5
87.5°	11.8	13.1	15.7	18.3
90°	3.5	2.8	1.4	0.4
92.5°	12.0	10.2	7.4	5.3
95°	20.4	17.3	13.7	12.3
97.5°	28.9	24.3	20.4	18.3
100°	37.0	31.4	28.2	27.1
102.5°	44.7	39.1	35.9	35.2
105°	52.1	46.9	44.4	43.0
107.5°	59.9	55.0	52.5	51.4
110°	68.0	63.4	61.3	59.9

TEST NUMBER: P1000101

CATALOG NUMBER: SA2XXRDIP-B865D330UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	75.7	71.5	69.1	67.6
115°	83.9	79.6	77.5	75.7
117.5°	91.6	87.7	85.6	84.2
120°	98.6	95.5	93.4	92.0
122.5°	106.0	102.5	100.4	99.4
125°	113.1	108.9	106.8	105.7
127.5°	119.8	115.2	112.4	111.0
130°	125.4	120.5	117.0	115.6
132.5°	130.7	125.4	121.5	119.8
135°	134.9	129.7	125.4	124.0
137.5°	139.5	133.9	129.7	127.9
140°	143.7	138.1	133.9	132.5
142.5°	147.6	142.0	138.1	137.0
145°	151.8	146.6	143.0	141.6
147.5°	156.1	151.1	147.6	146.6
150°	159.9	155.4	152.6	151.5
152.5°	163.5	159.6	156.8	156.4
155°	167.3	163.5	161.4	161.0
157.5°	170.5	167.0	165.2	164.9
160°	173.3	170.5	169.1	168.8
162.5°	175.8	173.7	172.3	172.6
165°	177.9	175.8	175.1	175.5
167.5°	179.7	178.3	177.6	177.9
170°	181.1	180.0	179.7	180.4
172.5°	182.1	181.1	181.4	181.8
175°	182.8	182.1	182.5	182.8
177.5°	183.2	182.5	182.8	183.6
180°	183.2	183.2	183.2	183.2

(END OF REPORT)