

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999270

Luminaire Tested: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999270
REPORT IS A COMBINATION OF REPORTS P987819 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7604.0 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	99	94	91	88	91	87	84	82	74	72	70	62	60	59	51	50	49
2	90	83	78	73	83	77	72	68	66	62	59	55	53	51	46	44	42
3	83	74	67	62	76	69	63	58	59	54	51	50	46	44	41	39	37
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	37	35	33
5	70	59	52	46	65	55	49	44	48	43	39	41	37	34	34	31	29
6	65	54	46	41	60	50	43	38	44	38	34	37	33	30	31	28	26
7	61	49	41	36	56	46	39	34	40	34	31	34	30	27	29	26	24
8	56	45	37	32	52	42	35	31	37	31	28	32	27	24	27	24	21
9	53	41	34	29	49	38	32	28	34	29	25	29	25	22	25	22	20
10	49	38	31	26	46	36	29	25	31	26	23	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34688	34688	34688	34688
5°	34769	36845	34889	29434
10°	34387	38943	34630	24307
15°	33640	38956	34210	18260
20°	32742	32200	33455	15065
25°	31654	20121	32338	12815
30°	30265	12883	31088	11033
35°	28575	9901	29500	9442
40°	26691	8322	27831	8259
45°	24679	7083	25710	6933
50°	22615	6018	23672	5996
55°	20331	5230	21426	5162
60°	18301	3988	19269	3941
65°	16402	3001	17377	3405
70°	14313	2397	15430	2776
75°	12094	1836	13202	2098
80°	9604	1249	10331	1377
85°	6667	644	7317	680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 31731 cd/sqm

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.9	2.7
10°-20°	580.2	7.6
20°-30°	746.7	9.8
30°-40°	708.4	9.3
40°-50°	607.1	8.0
50°-60°	462.3	6.1
60°-70°	291.6	3.8
70°-80°	145.5	1.9
80°-90°	41.3	0.5
90°-100°	84.4	1.1
100°-110°	268.2	3.5
110°-120°	458.9	6.0
120°-130°	603.6	7.9
130°-140°	677.5	8.9
140°-150°	664.4	8.7
150°-160°	557.3	7.3
160°-170°	369.6	4.9
170°-180°	129.2	1.7
0°-30°	1534.7	20.2
0°-40°	2243.1	29.5
0°-60°	3312.6	43.6
0°-90°	3790.9	49.9
90°-120°	811.5	10.7
90°-150°	2757.0	36.3
90°-180°	3813.0	50.1
0°-180°	7604.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2191	2191	2191	2191	2191	
5°	2193	2438	2200	1948	2193	208
15°	2066	2752	2102	1290	2066	581
25°	1834	1468	1873	935	1834	842
35°	1505	723	1553	690	1505	941
45°	1130	502	1177	492	1130	872
55°	763	349	804	344	763	688
65°	461	181	489	206	461	458
75°	216	96	236	110	216	234
85°	47	27	52	29	47	54
90°	1	39	1	39	1	7
95°	60	71	60	71	60	67
105°	248	256	248	256	248	261
115°	460	460	460	460	460	455
125°	670	672	670	672	670	599
135°	867	877	867	877	867	670
145°	1052	1064	1052	1064	1052	657
155°	1203	1212	1203	1212	1203	554
165°	1309	1310	1309	1310	1309	369
175°	1362	1357	1362	1357	1362	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2205.1	2214.2	2218.8	2224.9	2238.6	2247.7	2261.4	2264.5	2263.0	2269.1	2252.3
5°	2192.9	2212.7	2231.0	2246.2	2270.6	2285.8	2302.6	2322.4	2326.9	2349.8	2336.1
7.5°	2176.2	2205.1	2231.0	2261.4	2298.0	2317.8	2343.7	2374.1	2387.8	2415.3	2422.9
10°	2148.8	2189.9	2234.0	2266.0	2316.3	2351.3	2375.7	2424.4	2456.4	2497.5	2491.4
12.5°	2104.6	2157.9	2217.3	2270.6	2336.1	2358.9	2404.6	2454.8	2496.0	2534.0	2567.5
15°	2066.5	2127.4	2192.9	2258.4	2333.0	2375.7	2421.3	2486.8	2531.0	2598.0	2626.9
17.5°	2014.7	2092.4	2170.1	2243.2	2331.5	2380.2	2436.6	2500.5	2566.0	2630.0	2652.8
20°	1961.4	2045.2	2129.0	2227.9	2328.5	2375.7	2433.5	2512.7	2576.7	2626.9	2626.9
22.5°	1897.5	1999.5	2095.5	2189.9	2299.5	2368.0	2427.4	2520.3	2566.0	2576.7	2535.6
25°	1833.5	1935.6	2040.6	2157.9	2282.8	2343.7	2410.7	2497.5	2512.7	2470.1	2363.5
27.5°	1757.4	1871.6	1990.4	2116.8	2247.7	2323.9	2384.8	2442.7	2413.7	2299.5	2133.5
30°	1679.7	1803.1	1937.1	2057.4	2215.8	2285.8	2337.6	2354.3	2263.0	2077.2	1862.5
32.5°	1599.0	1719.3	1860.9	2005.6	2165.5	2232.5	2266.0	2221.9	2054.3	1819.8	1557.9
35°	1504.6	1640.1	1787.8	1938.6	2097.0	2147.2	2167.0	2058.9	1844.2	1541.1	1280.7
37.5°	1419.3	1554.8	1713.2	1867.0	2020.8	2048.2	2028.4	1859.4	1586.8	1286.8	1032.5
40°	1318.8	1463.5	1618.8	1790.9	1917.3	1924.9	1876.2	1656.9	1318.8	1037.1	880.2
42.5°	1225.9	1372.1	1527.4	1702.6	1798.5	1772.6	1707.1	1419.3	1101.0	893.9	767.5
45°	1130.0	1268.5	1436.1	1591.4	1659.9	1599.0	1500.0	1193.9	924.4	769.0	671.6
47.5°	1037.1	1166.5	1332.5	1481.7	1493.9	1425.4	1308.1	1000.5	801.0	676.1	597.0
50°	945.7	1075.1	1230.5	1353.8	1341.6	1247.2	1114.7	869.6	695.9	597.0	531.5
52.5°	854.3	971.6	1122.3	1219.8	1168.0	1076.7	945.7	737.1	607.6	520.8	470.6
55°	763.0	872.6	1002.0	1082.8	1000.5	895.4	802.5	632.0	526.9	456.9	418.8
57.5°	686.8	773.6	892.4	941.1	842.1	759.9	679.2	543.7	456.9	406.6	362.4
60°	603.1	682.2	779.7	808.6	706.6	639.6	571.1	459.9	391.4	347.2	318.3
62.5°	531.5	597.0	671.6	671.6	581.7	531.5	479.7	385.3	328.9	293.9	280.2
65°	461.4	508.6	561.9	555.8	479.7	435.5	394.4	318.3	275.6	251.3	237.6
67.5°	392.9	429.4	464.5	443.2	388.3	350.3	312.2	257.4	228.4	211.7	193.4
70°	330.5	359.4	377.7	357.9	303.0	271.1	243.7	207.1	184.3	162.9	152.3
72.5°	277.2	289.3	295.4	271.1	225.4	207.1	187.3	161.4	141.6	131.0	127.9
75°	216.2	226.9	222.3	204.1	166.0	152.3	137.1	118.8	114.2	108.1	105.1
77.5°	169.0	169.0	161.4	144.7	118.8	108.1	102.0	92.9	88.3	86.8	83.8
80°	120.3	118.8	114.2	95.9	80.7	74.6	74.6	68.5	67.0	64.0	64.0
82.5°	79.2	79.2	73.1	57.9	53.3	51.8	50.3	47.2	47.2	45.7	45.7
85°	47.2	44.2	36.5	32.0	30.5	30.5	28.9	27.4	28.9	27.4	27.4
87.5°	21.3	16.8	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
90°	1.2	4.3	7.3	10.4	13.5	15.0	17.8	23.4	29.1	34.7	40.3
92.5°	25.3	27.3	29.4	31.4	33.5	34.5	34.6	34.9	35.2	35.4	35.7
95°	59.8	62.4	65.0	67.5	70.1	71.4	71.7	72.2	72.7	73.2	73.7
97.5°	100.1	102.4	104.7	107.0	109.3	110.5	111.0	112.0	113.1	114.1	115.1
100°	146.2	148.2	150.3	152.3	154.4	155.4	155.8	156.5	157.3	158.0	158.8
102.5°	194.5	196.0	197.6	199.1	200.6	201.4	201.9	202.9	204.0	205.0	206.0
105°	247.5	248.3	249.0	249.8	250.5	250.9	251.2	251.7	252.2	252.7	253.2
107.5°	300.4	301.4	302.4	303.5	304.5	305.0	305.0	305.0	305.0	305.0	305.0
110°	351.0	352.5	354.1	355.6	357.1	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	406.3	407.8	409.4	410.9	412.4	413.2	413.1	412.8	412.5	412.3	412.0
115°	460.4	461.9	463.5	465.0	466.5	467.3	467.0	466.5	466.0	465.5	465.0
117.5°	514.5	516.5	518.6	520.6	522.7	523.7	523.1	521.8	520.5	519.2	517.9
120°	568.6	570.6	572.7	574.7	576.8	577.8	576.8	574.7	572.7	570.6	568.6
122.5°	618.1	620.7	623.2	625.8	628.3	629.6	629.0	627.7	626.4	625.1	623.8
125°	669.8	672.1	674.4	676.7	679.0	680.2	679.8	679.1	678.3	677.6	676.8
127.5°	720.5	723.3	726.1	729.0	731.8	733.2	732.7	731.6	730.6	729.5	728.5
130°	767.7	771.0	774.3	777.6	780.9	782.6	782.3	781.8	781.3	780.8	780.3
132.5°	820.6	823.2	825.7	828.3	830.8	832.1	832.2	832.5	832.8	833.0	833.3
135°	866.7	869.5	872.3	875.1	877.9	879.3	879.6	880.1	880.6	881.1	881.6
137.5°	917.3	919.6	921.9	924.2	926.5	927.7	928.0	928.5	929.0	929.5	930.0
140°	962.2	964.5	966.8	969.1	971.4	972.5	973.1	974.4	975.7	977.0	978.3
142.5°	1008.2	1010.5	1012.8	1015.1	1017.4	1018.6	1019.0	1019.7	1020.5	1021.2	1022.0
145°	1052.0	1053.8	1055.6	1057.3	1059.1	1060.0	1060.8	1062.3	1063.8	1065.4	1066.9
147.5°	1091.1	1093.4	1095.7	1098.0	1100.3	1101.5	1102.0	1103.0	1104.1	1105.1	1106.1
150°	1131.4	1132.9	1134.5	1136.0	1137.5	1138.3	1138.8	1139.8	1140.9	1141.9	1142.9
152.5°	1167.1	1168.6	1170.2	1171.7	1173.2	1174.0	1174.6	1175.9	1177.2	1178.4	1179.7
155°	1202.7	1203.5	1204.3	1205.0	1205.8	1206.2	1206.6	1207.3	1208.1	1208.8	1209.6
157.5°	1233.8	1234.3	1234.8	1235.3	1235.8	1236.1	1236.4	1236.9	1237.4	1237.9	1238.4
160°	1261.4	1261.9	1262.4	1262.9	1263.4	1263.7	1263.8	1264.1	1264.4	1264.6	1264.9
162.5°	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.9	1287.2	1287.4	1287.7	1287.9
165°	1308.6	1308.4	1308.1	1307.9	1307.6	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
167.5°	1328.2	1327.4	1326.6	1325.9	1325.1	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7
170°	1343.2	1342.4	1341.6	1340.9	1340.1	1339.7	1339.6	1339.3	1339.0	1338.8	1338.5
172.5°	1353.5	1352.7	1352.0	1351.2	1350.5	1350.1	1350.0	1349.7	1349.4	1349.2	1348.9
175°	1361.6	1360.8	1360.0	1359.3	1358.5	1358.1	1357.8	1357.3	1356.8	1356.3	1355.8
177.5°	1366.2	1365.4	1364.6	1363.9	1363.1	1362.7	1362.4	1361.9	1361.4	1360.9	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2269.1	2272.1	2276.7	2298.0	2301.0	2307.1	2304.1	2304.1	2305.6	2302.6	2304.1
5°	2366.5	2371.1	2393.9	2419.8	2425.9	2419.8	2427.4	2438.1	2438.1	2438.1	2435.1
7.5°	2457.9	2474.6	2500.5	2538.6	2546.2	2553.8	2567.5	2558.4	2561.4	2575.2	2570.6
10°	2546.2	2570.6	2599.5	2631.5	2648.3	2658.9	2665.0	2678.7	2710.7	2674.1	2687.8
12.5°	2630.0	2665.0	2695.5	2730.5	2742.7	2756.4	2760.9	2773.1	2773.1	2771.6	2782.3
15°	2684.8	2716.8	2744.2	2767.0	2770.1	2767.0	2764.0	2765.5	2770.1	2751.8	2762.5
17.5°	2697.0	2700.0	2709.2	2700.0	2701.6	2669.6	2651.3	2646.7	2604.1	2605.6	2640.6
20°	2637.6	2585.8	2572.1	2521.9	2491.4	2409.2	2406.1	2383.3	2293.4	2320.8	2314.7
22.5°	2474.6	2386.3	2269.1	2211.2	2182.3	2095.5	2028.4	1981.2	1949.3	1917.3	1903.6
25°	2259.9	2116.8	1950.8	1836.6	1819.8	1739.1	1615.8	1557.9	1489.4	1468.0	1504.6
27.5°	1982.8	1797.0	1609.7	1434.5	1402.6	1329.5	1267.0	1225.9	1146.7	1142.1	1145.2
30°	1606.6	1419.3	1262.4	1148.2	1069.0	1035.5	994.4	964.0	932.0	944.2	947.2
32.5°	1320.3	1142.1	995.9	935.0	898.5	877.2	842.1	822.3	808.6	804.1	802.5
35°	1049.2	930.5	865.0	805.6	784.3	769.0	743.2	734.0	721.8	723.4	723.4
37.5°	898.5	799.5	750.8	720.3	700.5	692.9	676.1	667.0	659.4	656.4	660.9
40°	775.1	706.6	676.1	648.7	632.0	628.9	619.8	609.1	600.0	601.5	606.1
42.5°	685.3	645.7	609.1	587.8	575.6	571.1	563.5	555.8	555.8	551.3	549.8
45°	613.7	581.7	551.3	531.5	523.9	517.8	508.6	507.1	501.0	502.5	504.1
47.5°	549.8	523.9	501.0	481.2	473.6	472.1	462.9	456.9	456.9	455.3	453.8
50°	491.9	466.0	446.2	435.5	424.9	421.8	420.3	418.8	415.7	415.7	417.3
52.5°	444.7	418.8	403.6	394.4	388.3	385.3	385.3	383.8	383.8	383.8	382.2
55°	392.9	371.6	359.4	356.3	353.3	351.8	350.3	347.2	345.7	348.7	345.7
57.5°	344.2	336.6	325.9	322.8	315.2	315.2	310.7	307.6	304.6	307.6	307.6
60°	306.1	295.4	289.3	280.2	274.1	268.0	260.4	258.9	255.8	254.3	252.8
62.5°	266.5	257.4	242.1	228.4	219.3	213.2	210.2	208.6	208.6	207.1	207.1
65°	222.3	201.0	193.4	188.8	187.3	185.8	182.7	181.2	182.7	181.2	182.7
67.5°	173.6	170.6	166.0	162.9	161.4	159.9	159.9	158.4	158.4	158.4	158.4
70°	150.8	143.1	141.6	138.6	138.6	137.1	137.1	137.1	137.1	135.5	138.6
72.5°	124.9	120.3	118.8	117.3	117.3	117.3	115.7	115.7	115.7	114.2	115.7
75°	102.0	100.5	97.5	97.5	95.9	97.5	95.9	95.9	94.4	95.9	95.9
77.5°	82.2	80.7	79.2	79.2	77.7	77.7	77.7	77.7	77.7	77.7	79.2
80°	62.4	60.9	59.4	60.9	59.4	60.9	59.4	59.4	60.9	59.4	59.4
82.5°	45.7	44.2	44.2	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6
85°	27.4	25.9	25.9	27.4	25.9	27.4	25.9	25.9	25.9	27.4	27.4
87.5°	12.2	13.7	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	13.7
90°	39.8	39.3	38.8	38.3	38.0	38.1	38.4	38.6	38.9	39.1	38.9
92.5°	35.9	36.2	36.4	36.7	36.8	36.8	36.8	36.8	36.8	36.8	36.8
95°	73.7	73.7	73.7	73.7	73.7	73.4	72.9	72.4	71.9	71.4	71.9
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1
100°	158.8	158.8	158.8	158.8	158.8	158.7	158.4	158.2	157.9	157.7	157.9
102.5°	206.3	206.5	206.8	207.1	207.2	207.1	206.8	206.5	206.3	206.0	206.3
105°	253.7	254.2	254.7	255.2	255.5	255.5	255.5	255.5	255.5	255.5	255.5
107.5°	305.3	305.5	305.8	306.1	306.2	305.6	304.3	303.0	301.7	300.4	301.7
110°	357.9	357.9	357.9	357.9	357.9	357.5	356.8	356.0	355.3	354.5	355.3

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	411.2	410.5	409.7	409.0	408.6	408.3	407.8	407.3	406.8	406.3	406.8
115°	464.7	464.5	464.2	463.9	463.8	463.4	462.7	461.9	461.2	460.4	461.2
117.5°	517.1	516.4	515.6	514.9	514.5	514.1	513.3	512.6	511.8	511.0	511.8
120°	568.6	568.6	568.6	568.6	568.6	568.2	567.4	566.7	565.9	565.1	565.9
122.5°	623.0	622.3	621.5	620.8	620.4	620.1	619.6	619.1	618.6	618.1	618.6
125°	676.0	675.2	674.5	673.7	673.3	673.2	672.9	672.7	672.4	672.2	672.4
127.5°	727.5	726.5	725.4	724.4	723.9	723.5	722.8	722.0	721.3	720.5	721.3
130°	779.8	779.3	778.8	778.3	778.0	777.5	776.5	775.4	774.4	773.4	774.4
132.5°	832.0	830.7	829.4	828.1	827.5	827.1	826.4	825.6	824.9	824.1	824.9
135°	881.4	881.1	880.9	880.6	880.5	880.1	879.3	878.6	877.8	877.0	877.8
137.5°	929.7	929.5	929.2	928.9	928.8	928.3	927.3	926.2	925.2	924.2	925.2
140°	978.3	978.3	978.3	978.3	978.3	977.8	976.8	975.7	974.7	973.7	974.7
142.5°	1022.3	1022.5	1022.8	1023.1	1023.2	1022.7	1021.7	1020.6	1019.6	1018.6	1019.6
145°	1067.2	1067.4	1067.7	1068.0	1068.1	1067.6	1066.6	1065.5	1064.5	1063.5	1064.5
147.5°	1106.6	1107.1	1107.6	1108.1	1108.4	1107.9	1106.9	1105.8	1104.8	1103.8	1104.8
150°	1143.7	1144.4	1145.2	1145.9	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1143.7
152.5°	1180.7	1181.7	1182.8	1183.8	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1180.7
155°	1210.9	1212.2	1213.5	1214.8	1215.4	1215.0	1214.2	1213.5	1212.7	1211.9	1212.7
157.5°	1240.2	1242.0	1243.8	1245.6	1246.5	1245.9	1244.6	1243.3	1242.0	1240.7	1242.0
160°	1266.4	1268.0	1269.5	1271.0	1271.8	1271.3	1270.3	1269.2	1268.2	1267.2	1268.2
162.5°	1289.7	1291.5	1293.3	1295.1	1296.0	1295.4	1294.1	1292.8	1291.5	1290.2	1291.5
165°	1309.3	1311.1	1312.8	1314.6	1315.5	1314.9	1313.6	1312.3	1311.1	1309.8	1311.1
167.5°	1326.5	1328.3	1330.1	1331.9	1332.8	1332.2	1330.9	1329.6	1328.3	1327.0	1328.3
170°	1340.3	1342.1	1343.9	1345.7	1346.6	1345.8	1344.3	1342.8	1341.2	1339.7	1341.2
172.5°	1350.7	1352.5	1354.3	1356.1	1357.0	1356.2	1354.7	1353.2	1351.6	1350.1	1351.6
175°	1357.6	1359.4	1361.2	1363.0	1363.9	1363.1	1361.6	1360.1	1358.5	1357.0	1358.5
177.5°	1361.9	1363.5	1365.0	1366.5	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1361.9
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2310.2	2299.5	2296.5	2299.5	2296.5	2298.0	2287.3	2247.7	2258.4	2241.6	2250.8
5°	2441.1	2432.0	2412.2	2409.2	2406.1	2403.1	2387.8	2352.8	2339.1	2316.3	2314.7
7.5°	2566.0	2566.0	2550.8	2540.1	2526.4	2515.8	2496.0	2444.2	2422.9	2395.5	2380.2
10°	2689.4	2649.8	2666.5	2655.9	2622.4	2616.3	2579.7	2549.3	2508.1	2480.7	2456.4
12.5°	2777.7	2765.5	2750.3	2741.1	2732.0	2712.2	2687.8	2610.2	2588.9	2534.0	2506.6
15°	2774.6	2767.0	2771.6	2771.6	2768.6	2764.0	2744.2	2687.8	2651.3	2598.0	2550.8
17.5°	2625.4	2645.2	2665.0	2678.7	2709.2	2722.9	2741.1	2707.6	2684.8	2639.1	2588.9
20°	2365.0	2413.7	2471.6	2483.8	2511.2	2591.9	2628.5	2657.4	2666.5	2651.3	2610.2
22.5°	2002.6	2043.7	2183.8	2180.7	2220.3	2316.3	2422.9	2509.7	2578.2	2616.3	2601.0
25°	1568.5	1626.4	1701.0	1757.4	1886.8	2030.0	2162.5	2301.0	2419.8	2524.9	2550.8
27.5°	1186.3	1262.4	1321.8	1396.5	1461.9	1631.0	1801.5	2017.8	2156.4	2355.9	2459.4
30°	959.4	994.4	1053.8	1088.8	1120.8	1250.3	1443.7	1656.9	1900.5	2130.5	2308.7
32.5°	819.3	843.7	887.8	903.1	936.6	1023.4	1145.2	1340.1	1591.4	1870.1	2104.6
35°	735.5	761.4	770.6	784.3	811.7	866.5	950.3	1091.9	1318.8	1591.4	1871.6
37.5°	664.0	677.7	703.6	712.7	721.8	763.0	819.3	918.3	1069.0	1292.9	1603.6
40°	613.7	621.3	635.0	642.6	648.7	677.7	727.9	794.9	906.1	1076.7	1363.0
42.5°	560.4	569.5	578.7	587.8	595.4	618.3	648.7	712.7	787.3	916.8	1123.9
45°	508.6	514.7	525.4	531.5	542.1	560.4	587.8	632.0	699.0	781.2	948.7
47.5°	461.4	469.0	473.6	481.2	488.8	508.6	534.5	563.5	618.3	699.0	820.8
50°	418.8	427.9	434.0	435.5	441.6	459.9	481.2	513.2	548.2	610.7	717.3
52.5°	388.3	389.9	394.4	400.5	399.0	409.6	429.4	453.8	490.4	540.6	618.3
55°	353.3	357.9	360.9	362.4	362.4	371.6	382.2	405.1	434.0	475.1	540.6
57.5°	309.1	313.7	322.8	325.9	330.5	335.0	339.6	354.8	379.2	418.8	472.1
60°	263.5	266.5	275.6	281.7	284.8	297.0	303.0	315.2	328.9	357.9	408.1
62.5°	211.7	214.7	219.3	225.4	231.5	249.7	265.0	277.2	287.8	307.6	348.7
65°	184.3	185.8	188.8	190.4	191.9	199.5	213.2	230.0	249.7	265.0	289.3
67.5°	159.9	161.4	162.9	166.0	167.5	169.0	175.1	179.7	199.5	220.8	239.1
70°	137.1	140.1	141.6	141.6	143.1	146.2	149.2	155.3	161.4	172.1	194.9
72.5°	115.7	117.3	120.3	120.3	120.3	123.4	126.4	129.4	132.5	138.6	147.7
75°	95.9	99.0	99.0	99.0	100.5	100.5	103.6	106.6	109.6	114.2	117.3
77.5°	79.2	79.2	79.2	79.2	80.7	80.7	82.2	85.3	86.8	88.3	91.4
80°	59.4	60.9	60.9	60.9	62.4	62.4	62.4	65.5	67.0	67.0	70.1
82.5°	44.2	44.2	44.2	45.7	44.2	45.7	45.7	47.2	45.7	47.2	48.7
85°	27.4	27.4	27.4	28.9	28.9	28.9	28.9	28.9	28.9	28.9	30.5
87.5°	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7	15.2	13.7	13.7
90°	38.6	38.4	38.1	38.0	38.3	38.8	39.3	39.8	40.3	34.7	29.1
92.5°	36.8	36.8	36.8	36.8	36.7	36.4	36.2	35.9	35.7	35.4	35.2
95°	72.4	72.9	73.4	73.7	73.7	73.7	73.7	73.7	73.7	73.2	72.7
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	114.1	113.1
100°	158.2	158.4	158.7	158.8	158.8	158.8	158.8	158.8	158.8	158.0	157.3
102.5°	206.5	206.8	207.1	207.2	207.1	206.8	206.5	206.3	206.0	205.0	204.0
105°	255.5	255.5	255.5	255.5	255.2	254.7	254.2	253.7	253.2	252.7	252.2
107.5°	303.0	304.3	305.6	306.2	306.1	305.8	305.5	305.3	305.0	305.0	305.0
110°	356.0	356.8	357.5	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	407.3	407.8	408.3	408.6	409.0	409.7	410.5	411.2	412.0	412.3	412.5
115°	461.9	462.7	463.4	463.8	463.9	464.2	464.5	464.7	465.0	465.5	466.0
117.5°	512.6	513.3	514.1	514.5	514.9	515.6	516.4	517.1	517.9	519.2	520.5
120°	566.7	567.4	568.2	568.6	568.6	568.6	568.6	568.6	568.6	570.6	572.7
122.5°	619.1	619.6	620.1	620.4	620.8	621.5	622.3	623.0	623.8	625.1	626.4
125°	672.7	672.9	673.2	673.3	673.7	674.5	675.2	676.0	676.8	677.6	678.3
127.5°	722.0	722.8	723.5	723.9	724.4	725.4	726.5	727.5	728.5	729.5	730.6
130°	775.4	776.5	777.5	778.0	778.3	778.8	779.3	779.8	780.3	780.8	781.3
132.5°	825.6	826.4	827.1	827.5	828.1	829.4	830.7	832.0	833.3	833.0	832.8
135°	878.6	879.3	880.1	880.5	880.6	880.9	881.1	881.4	881.6	881.1	880.6
137.5°	926.2	927.3	928.3	928.8	928.9	929.2	929.5	929.7	930.0	929.5	929.0
140°	975.7	976.8	977.8	978.3	978.3	978.3	978.3	978.3	978.3	977.0	975.7
142.5°	1020.6	1021.7	1022.7	1023.2	1023.1	1022.8	1022.5	1022.3	1022.0	1021.2	1020.5
145°	1065.5	1066.6	1067.6	1068.1	1068.0	1067.7	1067.4	1067.2	1066.9	1065.4	1063.8
147.5°	1105.8	1106.9	1107.9	1108.4	1108.1	1107.6	1107.1	1106.6	1106.1	1105.1	1104.1
150°	1144.4	1145.2	1145.9	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1141.9	1140.9
152.5°	1181.7	1182.8	1183.8	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1178.4	1177.2
155°	1213.5	1214.2	1215.0	1215.4	1214.8	1213.5	1212.2	1210.9	1209.6	1208.8	1208.1
157.5°	1243.3	1244.6	1245.9	1246.5	1245.6	1243.8	1242.0	1240.2	1238.4	1237.9	1237.4
160°	1269.2	1270.3	1271.3	1271.8	1271.0	1269.5	1268.0	1266.4	1264.9	1264.6	1264.4
162.5°	1292.8	1294.1	1295.4	1296.0	1295.1	1293.3	1291.5	1289.7	1287.9	1287.7	1287.4
165°	1312.3	1313.6	1314.9	1315.5	1314.6	1312.8	1311.1	1309.3	1307.5	1307.5	1307.5
167.5°	1329.6	1330.9	1332.2	1332.8	1331.9	1330.1	1328.3	1326.5	1324.7	1324.7	1324.7
170°	1342.8	1344.3	1345.8	1346.6	1345.7	1343.9	1342.1	1340.3	1338.5	1338.8	1339.0
172.5°	1353.2	1354.7	1356.2	1357.0	1356.1	1354.3	1352.5	1350.7	1348.9	1349.2	1349.4
175°	1360.1	1361.6	1363.1	1363.9	1363.0	1361.2	1359.4	1357.6	1355.8	1356.3	1356.8
177.5°	1363.5	1365.0	1366.5	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1360.9	1361.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2237.1	2229.5	2229.5	2224.9	2224.9	2200.5	2200.5	2208.1	2199.0	2188.3	2173.1
5°	2294.9	2278.2	2273.6	2267.5	2247.7	2217.3	2205.1	2200.5	2182.3	2159.4	2133.5
7.5°	2349.8	2322.4	2308.7	2294.9	2269.1	2226.4	2202.1	2185.3	2157.9	2122.9	2089.4
10°	2403.1	2368.0	2333.0	2316.3	2279.7	2226.4	2191.4	2164.0	2124.4	2077.2	2030.0
12.5°	2451.8	2378.7	2372.6	2339.1	2285.8	2224.9	2171.6	2132.0	2081.7	2026.9	1972.1
15°	2494.4	2419.8	2383.3	2352.8	2282.8	2206.6	2150.3	2101.5	2034.5	1972.1	1905.1
17.5°	2515.8	2435.1	2410.7	2360.4	2288.9	2189.9	2113.7	2054.3	1981.2	1906.6	1830.5
20°	2537.1	2442.7	2403.1	2368.0	2270.6	2157.9	2072.6	2004.1	1923.4	1835.0	1751.3
22.5°	2547.7	2442.7	2395.5	2346.7	2252.3	2122.9	2022.4	1941.6	1847.2	1757.4	1656.9
25°	2529.5	2433.5	2377.2	2326.9	2220.3	2080.2	1964.5	1873.1	1772.6	1670.6	1568.5
27.5°	2483.8	2412.2	2346.7	2294.9	2176.2	2025.4	1903.6	1800.0	1696.5	1582.3	1478.7
30°	2398.5	2366.5	2314.7	2256.9	2127.4	1976.7	1832.0	1725.4	1611.2	1497.0	1388.8
32.5°	2266.0	2293.4	2259.9	2209.7	2069.6	1909.7	1755.9	1647.7	1522.9	1399.5	1300.5
35°	2104.6	2202.1	2183.8	2148.8	2008.7	1838.1	1684.3	1553.3	1428.4	1303.6	1204.6
37.5°	1927.9	2075.7	2090.9	2069.6	1938.6	1765.0	1596.0	1468.0	1340.1	1213.7	1113.2
40°	1685.8	1912.7	1961.4	1970.6	1865.5	1676.7	1500.0	1375.1	1248.7	1125.4	1003.6
42.5°	1463.5	1749.8	1810.7	1848.8	1772.6	1589.9	1411.7	1273.1	1148.2	1037.1	915.2
45°	1254.8	1553.3	1652.3	1701.0	1667.5	1490.9	1306.6	1177.2	1063.0	960.9	843.7
47.5°	1040.1	1340.1	1478.7	1556.4	1556.4	1390.4	1206.1	1078.2	968.5	881.7	778.2
50°	897.0	1146.7	1289.9	1391.9	1419.3	1288.3	1114.7	989.9	886.3	791.9	712.7
52.5°	764.5	988.3	1107.1	1213.7	1292.9	1178.7	1012.7	900.0	798.0	709.7	647.2
55°	660.9	828.4	936.6	1053.8	1142.1	1067.5	913.7	804.1	715.7	642.6	589.3
57.5°	561.9	708.1	796.5	900.0	994.4	938.1	814.7	720.3	642.6	578.7	531.5
60°	478.2	597.0	665.5	746.2	863.5	823.9	721.8	635.0	572.6	514.7	475.1
62.5°	406.6	501.0	558.9	616.8	723.4	705.1	625.9	558.9	505.6	456.9	423.4
65°	333.5	411.2	456.9	507.1	592.4	600.0	536.0	488.8	440.1	397.5	367.0
67.5°	269.5	330.5	371.6	414.2	482.7	504.1	459.9	420.3	379.2	344.2	316.8
70°	217.8	260.4	290.9	324.4	380.7	406.6	383.8	356.3	322.8	293.9	269.5
72.5°	172.1	199.5	217.8	243.7	289.3	315.2	313.7	289.3	265.0	245.2	225.4
75°	126.4	147.7	162.9	179.7	216.2	240.6	246.7	236.0	211.7	196.4	181.2
77.5°	95.9	108.1	115.7	127.9	153.8	175.1	184.3	181.2	164.5	152.3	141.6
80°	73.1	76.1	79.2	83.8	105.1	124.9	131.0	129.4	120.3	115.7	103.6
82.5°	51.8	53.3	54.8	56.3	64.0	80.7	86.8	89.8	82.2	77.7	67.0
85°	30.5	32.0	32.0	35.0	36.5	41.1	51.8	51.8	50.3	44.2	42.6
87.5°	15.2	15.2	13.7	13.7	15.2	16.8	19.8	22.8	19.8	18.3	16.8
90°	23.4	17.8	15.0	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	34.9	34.6	34.5	33.5	31.4	29.4	27.3	25.3	27.3	29.4	31.4
95°	72.2	71.7	71.4	70.1	67.5	65.0	62.4	59.8	62.4	65.0	67.5
97.5°	112.0	111.0	110.5	109.3	107.0	104.7	102.4	100.1	102.4	104.7	107.0
100°	156.5	155.8	155.4	154.4	152.3	150.3	148.2	146.2	148.2	150.3	152.3
102.5°	202.9	201.9	201.4	200.6	199.1	197.6	196.0	194.5	196.0	197.6	199.1
105°	251.7	251.2	250.9	250.5	249.8	249.0	248.3	247.5	248.3	249.0	249.8
107.5°	305.0	305.0	305.0	304.5	303.5	302.4	301.4	300.4	301.4	302.4	303.5
110°	357.9	357.9	357.9	357.1	355.6	354.1	352.5	351.0	352.5	354.1	355.6

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	412.8	413.1	413.2	412.4	410.9	409.4	407.8	406.3	407.8	409.4	410.9
115°	466.5	467.0	467.3	466.5	465.0	463.5	461.9	460.4	461.9	463.5	465.0
117.5°	521.8	523.1	523.7	522.7	520.6	518.6	516.5	514.5	516.5	518.6	520.6
120°	574.7	576.8	577.8	576.8	574.7	572.7	570.6	568.6	570.6	572.7	574.7
122.5°	627.7	629.0	629.6	628.3	625.8	623.2	620.7	618.1	620.7	623.2	625.8
125°	679.1	679.8	680.2	679.0	676.7	674.4	672.1	669.8	672.1	674.4	676.7
127.5°	731.6	732.7	733.2	731.8	729.0	726.1	723.3	720.5	723.3	726.1	729.0
130°	781.8	782.3	782.6	780.9	777.6	774.3	771.0	767.7	771.0	774.3	777.6
132.5°	832.5	832.2	832.1	830.8	828.3	825.7	823.2	820.6	823.2	825.7	828.3
135°	880.1	879.6	879.3	877.9	875.1	872.3	869.5	866.7	869.5	872.3	875.1
137.5°	928.5	928.0	927.7	926.5	924.2	921.9	919.6	917.3	919.6	921.9	924.2
140°	974.4	973.1	972.5	971.4	969.1	966.8	964.5	962.2	964.5	966.8	969.1
142.5°	1019.7	1019.0	1018.6	1017.4	1015.1	1012.8	1010.5	1008.2	1010.5	1012.8	1015.1
145°	1062.3	1060.8	1060.0	1059.1	1057.3	1055.6	1053.8	1052.0	1053.8	1055.6	1057.3
147.5°	1103.0	1102.0	1101.5	1100.3	1098.0	1095.7	1093.4	1091.1	1093.4	1095.7	1098.0
150°	1139.8	1138.8	1138.3	1137.5	1136.0	1134.5	1132.9	1131.4	1132.9	1134.5	1136.0
152.5°	1175.9	1174.6	1174.0	1173.2	1171.7	1170.2	1168.6	1167.1	1168.6	1170.2	1171.7
155°	1207.3	1206.6	1206.2	1205.8	1205.0	1204.3	1203.5	1202.7	1203.5	1204.3	1205.0
157.5°	1236.9	1236.4	1236.1	1235.8	1235.3	1234.8	1234.3	1233.8	1234.3	1234.8	1235.3
160°	1264.1	1263.8	1263.7	1263.4	1262.9	1262.4	1261.9	1261.4	1261.9	1262.4	1262.9
162.5°	1287.2	1286.9	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8
165°	1307.5	1307.5	1307.5	1307.6	1307.9	1308.1	1308.4	1308.6	1308.4	1308.1	1307.9
167.5°	1324.7	1324.7	1324.7	1325.1	1325.9	1326.6	1327.4	1328.2	1327.4	1326.6	1325.9
170°	1339.3	1339.6	1339.7	1340.1	1340.9	1341.6	1342.4	1343.2	1342.4	1341.6	1340.9
172.5°	1349.7	1350.0	1350.1	1350.5	1351.2	1352.0	1352.7	1353.5	1352.7	1352.0	1351.2
175°	1357.3	1357.8	1358.1	1358.5	1359.3	1360.0	1360.8	1361.6	1360.8	1360.0	1359.3
177.5°	1361.9	1362.4	1362.7	1363.1	1363.9	1364.6	1365.4	1366.2	1365.4	1364.6	1363.9
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2167.0	2168.6	2173.1	2159.4	2138.1	2129.0	2101.5	2097.0	2092.4	2092.4	2097.0
5°	2118.3	2112.2	2113.7	2087.8	2057.4	2039.1	2001.0	2007.1	1987.3	1975.1	1978.2
7.5°	2065.0	2048.2	2046.7	2013.2	1975.1	1941.6	1902.1	1892.9	1874.6	1853.3	1844.2
10°	1998.0	1985.8	1963.0	1924.9	1876.2	1848.8	1795.5	1763.5	1758.9	1726.9	1714.7
12.5°	1929.5	1908.1	1885.3	1832.0	1777.2	1733.0	1693.4	1658.4	1634.0	1606.6	1588.3
15°	1850.3	1824.4	1798.5	1742.2	1678.2	1634.0	1574.6	1522.9	1451.3	1394.9	1363.0
17.5°	1763.5	1734.5	1699.5	1637.1	1574.6	1513.7	1404.1	1343.2	1292.9	1259.4	1239.6
20°	1673.6	1641.6	1606.6	1544.2	1436.1	1329.5	1268.5	1221.3	1190.9	1157.4	1133.0
22.5°	1579.2	1545.7	1507.6	1410.2	1296.0	1221.3	1174.1	1130.0	1085.8	1067.5	1055.3
25°	1490.9	1460.4	1411.7	1279.2	1189.4	1120.8	1067.5	1038.6	1015.7	991.4	968.5
27.5°	1399.5	1343.2	1274.6	1163.5	1107.1	1037.1	999.0	977.7	938.1	921.3	910.7
30°	1289.9	1227.4	1161.9	1082.8	1017.3	968.5	933.5	898.5	875.6	858.9	840.6
32.5°	1178.7	1119.3	1078.2	995.9	947.2	897.0	863.5	842.1	808.6	798.0	790.4
35°	1082.8	1032.5	995.9	928.9	883.3	837.6	813.2	781.2	759.9	740.1	727.9
37.5°	988.3	960.9	922.9	866.5	817.8	781.2	747.7	737.1	708.1	697.5	685.3
40°	922.9	881.7	849.8	801.0	759.9	720.3	699.0	674.6	654.8	638.1	633.5
42.5°	843.7	813.2	794.9	741.6	699.0	676.1	650.3	622.8	607.6	593.9	577.2
45°	784.3	756.9	731.0	688.3	650.3	621.3	598.5	580.2	554.3	548.2	522.3
47.5°	721.8	694.4	674.6	632.0	597.0	569.5	552.8	528.4	507.1	493.4	481.2
50°	659.4	636.6	618.3	581.7	551.3	522.3	499.5	475.1	466.0	443.2	435.5
52.5°	600.0	584.8	565.0	530.0	499.5	475.1	450.8	431.0	417.3	405.1	395.9
55°	549.8	525.4	516.2	478.2	452.3	426.4	405.1	392.9	376.1	368.5	360.9
57.5°	493.4	479.7	464.5	435.5	406.6	382.2	367.0	348.7	339.6	330.5	324.4
60°	444.7	424.9	412.7	388.3	362.4	339.6	325.9	312.2	300.0	292.4	280.2
62.5°	388.3	373.1	365.5	339.6	318.3	297.0	284.8	271.1	261.9	248.2	233.0
65°	339.6	327.4	318.3	297.0	277.2	257.4	245.2	228.4	216.2	208.6	207.1
67.5°	297.0	287.8	274.1	254.3	234.5	219.3	205.6	191.9	190.4	187.3	187.3
70°	249.7	240.6	233.0	211.7	194.9	178.2	175.1	170.6	166.0	164.5	161.4
72.5°	208.6	201.0	191.9	173.6	156.9	152.3	149.2	146.2	141.6	140.1	138.6
75°	169.0	158.4	152.3	135.5	131.0	127.9	124.9	120.3	117.3	115.7	112.7
77.5°	129.4	118.8	118.8	109.6	106.6	102.0	99.0	95.9	94.4	91.4	91.4
80°	91.4	91.4	88.3	83.8	79.2	77.7	73.1	71.6	70.1	71.6	68.5
82.5°	67.0	60.9	60.9	57.9	54.8	53.3	50.3	50.3	48.7	48.7	48.7
85°	38.1	38.1	36.5	33.5	32.0	32.0	30.5	30.5	28.9	28.9	27.4
87.5°	15.2	13.7	15.2	13.7	13.7	12.2	12.2	12.2	10.7	12.2	10.7
90°	13.5	15.0	17.8	23.4	29.1	34.7	40.3	39.8	39.3	38.8	38.3
92.5°	33.5	34.5	34.6	34.9	35.2	35.4	35.7	35.9	36.2	36.4	36.7
95°	70.1	71.4	71.7	72.2	72.7	73.2	73.7	73.7	73.7	73.7	73.7
97.5°	109.3	110.5	111.0	112.0	113.1	114.1	115.1	115.1	115.1	115.1	115.1
100°	154.4	155.4	155.8	156.5	157.3	158.0	158.8	158.8	158.8	158.8	158.8
102.5°	200.6	201.4	201.9	202.9	204.0	205.0	206.0	206.3	206.5	206.8	207.1
105°	250.5	250.9	251.2	251.7	252.2	252.7	253.2	253.7	254.2	254.7	255.2
107.5°	304.5	305.0	305.0	305.0	305.0	305.0	305.0	305.3	305.5	305.8	306.1
110°	357.1	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	412.4	413.2	413.1	412.8	412.5	412.3	412.0	411.2	410.5	409.7	409.0
115°	466.5	467.3	467.0	466.5	466.0	465.5	465.0	464.7	464.5	464.2	463.9
117.5°	522.7	523.7	523.1	521.8	520.5	519.2	517.9	517.1	516.4	515.6	514.9
120°	576.8	577.8	576.8	574.7	572.7	570.6	568.6	568.6	568.6	568.6	568.6
122.5°	628.3	629.6	629.0	627.7	626.4	625.1	623.8	623.0	622.3	621.5	620.8
125°	679.0	680.2	679.8	679.1	678.3	677.6	676.8	676.0	675.2	674.5	673.7
127.5°	731.8	733.2	732.7	731.6	730.6	729.5	728.5	727.5	726.5	725.4	724.4
130°	780.9	782.6	782.3	781.8	781.3	780.8	780.3	779.8	779.3	778.8	778.3
132.5°	830.8	832.1	832.2	832.5	832.8	833.0	833.3	832.0	830.7	829.4	828.1
135°	877.9	879.3	879.6	880.1	880.6	881.1	881.6	881.4	881.1	880.9	880.6
137.5°	926.5	927.7	928.0	928.5	929.0	929.5	930.0	929.7	929.5	929.2	928.9
140°	971.4	972.5	973.1	974.4	975.7	977.0	978.3	978.3	978.3	978.3	978.3
142.5°	1017.4	1018.6	1019.0	1019.7	1020.5	1021.2	1022.0	1022.3	1022.5	1022.8	1023.1
145°	1059.1	1060.0	1060.8	1062.3	1063.8	1065.4	1066.9	1067.2	1067.4	1067.7	1068.0
147.5°	1100.3	1101.5	1102.0	1103.0	1104.1	1105.1	1106.1	1106.6	1107.1	1107.6	1108.1
150°	1137.5	1138.3	1138.8	1139.8	1140.9	1141.9	1142.9	1143.7	1144.4	1145.2	1145.9
152.5°	1173.2	1174.0	1174.6	1175.9	1177.2	1178.4	1179.7	1180.7	1181.7	1182.8	1183.8
155°	1205.8	1206.2	1206.6	1207.3	1208.1	1208.8	1209.6	1210.9	1212.2	1213.5	1214.8
157.5°	1235.8	1236.1	1236.4	1236.9	1237.4	1237.9	1238.4	1240.2	1242.0	1243.8	1245.6
160°	1263.4	1263.7	1263.8	1264.1	1264.4	1264.6	1264.9	1266.4	1268.0	1269.5	1271.0
162.5°	1286.8	1286.8	1286.9	1287.2	1287.4	1287.7	1287.9	1289.7	1291.5	1293.3	1295.1
165°	1307.6	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1309.3	1311.1	1312.8	1314.6
167.5°	1325.1	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1326.5	1328.3	1330.1	1331.9
170°	1340.1	1339.7	1339.6	1339.3	1339.0	1338.8	1338.5	1340.3	1342.1	1343.9	1345.7
172.5°	1350.5	1350.1	1350.0	1349.7	1349.4	1349.2	1348.9	1350.7	1352.5	1354.3	1356.1
175°	1358.5	1358.1	1357.8	1357.3	1356.8	1356.3	1355.8	1357.6	1359.4	1361.2	1363.0
177.5°	1363.1	1362.7	1362.4	1361.9	1361.4	1360.9	1360.4	1361.9	1363.5	1365.0	1366.5
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2097.0	2093.9	2084.8	2087.8	2083.3	2083.3	2080.2	2080.2	2080.2	2087.8	2083.3
5°	1982.8	1972.1	1961.4	1956.9	1952.3	1947.7	1947.7	1946.2	1959.9	1956.9	1969.1
7.5°	1841.1	1838.1	1816.8	1816.8	1809.2	1806.1	1813.7	1815.2	1816.8	1819.8	1827.4
10°	1714.7	1707.1	1676.7	1679.7	1675.1	1669.1	1673.6	1670.6	1681.2	1684.3	1681.2
12.5°	1565.5	1551.8	1518.3	1501.5	1483.3	1469.6	1486.3	1474.1	1516.8	1529.0	1562.5
15°	1367.5	1341.6	1318.8	1318.8	1302.0	1289.9	1297.5	1311.2	1320.3	1334.0	1340.1
17.5°	1235.0	1224.4	1206.1	1195.4	1190.9	1186.3	1186.3	1192.4	1212.2	1210.7	1222.9
20°	1122.3	1116.3	1107.1	1093.4	1088.8	1085.8	1085.8	1085.8	1099.5	1111.7	1119.3
22.5°	1044.7	1040.1	1034.0	1015.7	1006.6	1003.6	1011.2	1015.7	1026.4	1035.5	1043.2
25°	967.0	956.4	945.7	939.6	935.0	935.0	938.1	939.6	944.2	948.7	957.9
27.5°	903.1	895.4	880.2	863.5	863.5	858.9	861.9	865.0	875.6	890.9	898.5
30°	831.5	830.0	823.9	817.8	811.7	808.6	814.7	819.3	820.8	828.4	828.4
32.5°	779.7	769.0	758.4	752.3	749.2	747.7	749.2	755.3	755.3	764.5	775.1
35°	727.9	721.8	711.2	700.5	697.5	689.9	695.9	702.0	712.7	717.3	721.8
37.5°	671.6	664.0	659.4	656.4	650.3	651.8	647.2	656.4	665.5	664.0	667.0
40°	628.9	615.2	601.5	600.0	598.5	597.0	597.0	598.5	604.6	610.7	619.8
42.5°	574.1	569.5	557.4	545.2	542.1	539.1	536.0	542.1	554.3	565.0	569.5
45°	517.8	511.7	508.6	499.5	493.4	491.9	488.8	496.5	507.1	511.7	514.7
47.5°	466.0	464.5	455.3	456.9	452.3	453.8	452.3	456.9	456.9	461.4	464.5
50°	431.0	426.4	421.8	418.8	414.2	414.2	412.7	414.2	420.3	426.4	424.9
52.5°	395.9	388.3	386.8	385.3	382.2	385.3	380.7	382.2	388.3	391.4	389.9
55°	354.8	353.3	350.3	347.2	345.7	344.2	344.2	344.2	350.3	354.8	356.3
57.5°	322.8	315.2	309.1	309.1	303.0	301.5	304.6	306.1	310.7	313.7	316.8
60°	278.7	275.6	266.5	261.9	252.8	251.3	251.3	257.4	265.0	275.6	278.7
62.5°	231.5	226.9	225.4	225.4	225.4	225.4	225.4	225.4	225.4	226.9	226.9
65°	205.6	207.1	205.6	204.1	205.6	205.6	204.1	204.1	204.1	205.6	207.1
67.5°	184.3	182.7	184.3	182.7	181.2	181.2	179.7	181.2	182.7	184.3	184.3
70°	159.9	159.9	158.4	159.9	158.4	156.9	155.3	155.3	158.4	159.9	159.9
72.5°	137.1	137.1	135.5	135.5	132.5	132.5	134.0	132.5	132.5	137.1	137.1
75°	114.2	112.7	111.2	111.2	109.6	109.6	109.6	108.1	111.2	111.2	112.7
77.5°	89.8	89.8	89.8	88.3	88.3	86.8	86.8	88.3	88.3	88.3	89.8
80°	68.5	68.5	68.5	67.0	65.5	65.5	65.5	65.5	65.5	67.0	65.5
82.5°	47.2	47.2	47.2	47.2	47.2	45.7	45.7	45.7	47.2	47.2	45.7
85°	28.9	27.4	28.9	28.9	27.4	28.9	27.4	27.4	25.9	25.9	27.4
87.5°	12.2	10.7	9.1	9.1	10.7	9.1	9.1	9.1	10.7	9.1	9.1
90°	38.0	38.1	38.4	38.6	38.9	39.1	38.9	38.6	38.4	38.1	38.0
92.5°	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8
95°	73.7	73.4	72.9	72.4	71.9	71.4	71.9	72.4	72.9	73.4	73.7
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1
100°	158.8	158.7	158.4	158.2	157.9	157.7	157.9	158.2	158.4	158.7	158.8
102.5°	207.2	207.1	206.8	206.5	206.3	206.0	206.3	206.5	206.8	207.1	207.2
105°	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5
107.5°	306.2	305.6	304.3	303.0	301.7	300.4	301.7	303.0	304.3	305.6	306.2
110°	357.9	357.5	356.8	356.0	355.3	354.5	355.3	356.0	356.8	357.5	357.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	408.6	408.3	407.8	407.3	406.8	406.3	406.8	407.3	407.8	408.3	408.6
115°	463.8	463.4	462.7	461.9	461.2	460.4	461.2	461.9	462.7	463.4	463.8
117.5°	514.5	514.1	513.3	512.6	511.8	511.0	511.8	512.6	513.3	514.1	514.5
120°	568.6	568.2	567.4	566.7	565.9	565.1	565.9	566.7	567.4	568.2	568.6
122.5°	620.4	620.1	619.6	619.1	618.6	618.1	618.6	619.1	619.6	620.1	620.4
125°	673.3	673.2	672.9	672.7	672.4	672.2	672.4	672.7	672.9	673.2	673.3
127.5°	723.9	723.5	722.8	722.0	721.3	720.5	721.3	722.0	722.8	723.5	723.9
130°	778.0	777.5	776.5	775.4	774.4	773.4	774.4	775.4	776.5	777.5	778.0
132.5°	827.5	827.1	826.4	825.6	824.9	824.1	824.9	825.6	826.4	827.1	827.5
135°	880.5	880.1	879.3	878.6	877.8	877.0	877.8	878.6	879.3	880.1	880.5
137.5°	928.8	928.3	927.3	926.2	925.2	924.2	925.2	926.2	927.3	928.3	928.8
140°	978.3	977.8	976.8	975.7	974.7	973.7	974.7	975.7	976.8	977.8	978.3
142.5°	1023.2	1022.7	1021.7	1020.6	1019.6	1018.6	1019.6	1020.6	1021.7	1022.7	1023.2
145°	1068.1	1067.6	1066.6	1065.5	1064.5	1063.5	1064.5	1065.5	1066.6	1067.6	1068.1
147.5°	1108.4	1107.9	1106.9	1105.8	1104.8	1103.8	1104.8	1105.8	1106.9	1107.9	1108.4
150°	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1143.7	1144.4	1145.2	1145.9	1146.3
152.5°	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1180.7	1181.7	1182.8	1183.8	1184.3
155°	1215.4	1215.0	1214.2	1213.5	1212.7	1211.9	1212.7	1213.5	1214.2	1215.0	1215.4
157.5°	1246.5	1245.9	1244.6	1243.3	1242.0	1240.7	1242.0	1243.3	1244.6	1245.9	1246.5
160°	1271.8	1271.3	1270.3	1269.2	1268.2	1267.2	1268.2	1269.2	1270.3	1271.3	1271.8
162.5°	1296.0	1295.4	1294.1	1292.8	1291.5	1290.2	1291.5	1292.8	1294.1	1295.4	1296.0
165°	1315.5	1314.9	1313.6	1312.3	1311.1	1309.8	1311.1	1312.3	1313.6	1314.9	1315.5
167.5°	1332.8	1332.2	1330.9	1329.6	1328.3	1327.0	1328.3	1329.6	1330.9	1332.2	1332.8
170°	1346.6	1345.8	1344.3	1342.8	1341.2	1339.7	1341.2	1342.8	1344.3	1345.8	1346.6
172.5°	1357.0	1356.2	1354.7	1353.2	1351.6	1350.1	1351.6	1353.2	1354.7	1356.2	1357.0
175°	1363.9	1363.1	1361.6	1360.1	1358.5	1357.0	1358.5	1360.1	1361.6	1363.1	1363.9
177.5°	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1361.9	1363.5	1365.0	1366.5	1367.3
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2087.8	2095.5	2092.4	2075.7	2092.4	2097.0	2106.1	2115.3	2121.3	2130.5	2138.1
5°	1956.9	1972.1	1981.2	1972.1	2002.6	2007.1	2028.4	2040.6	2058.9	2074.1	2086.3
7.5°	1833.5	1845.7	1864.0	1867.0	1885.3	1906.6	1937.1	1967.5	1996.5	2011.7	2025.4
10°	1701.0	1722.4	1749.8	1743.7	1771.1	1804.6	1836.6	1885.3	1909.7	1937.1	1961.4
12.5°	1568.5	1582.3	1618.8	1631.0	1670.6	1696.5	1740.6	1771.1	1832.0	1864.0	1885.3
15°	1337.1	1393.4	1439.1	1493.9	1545.7	1594.4	1634.0	1688.9	1742.2	1766.5	1801.5
17.5°	1232.0	1257.9	1285.3	1312.7	1379.7	1466.5	1536.6	1596.0	1641.6	1673.6	1714.7
20°	1122.3	1148.2	1178.7	1204.6	1245.7	1308.1	1394.9	1497.0	1551.8	1585.3	1624.9
22.5°	1044.7	1069.0	1088.8	1111.7	1143.7	1189.4	1254.8	1381.2	1454.3	1495.4	1530.5
25°	960.9	991.4	1012.7	1029.5	1055.3	1105.6	1158.9	1230.5	1361.4	1393.4	1442.1
27.5°	903.1	912.2	936.6	962.4	988.3	1015.7	1070.6	1131.5	1219.8	1289.9	1349.3
30°	834.5	857.4	880.2	890.9	913.7	953.3	986.8	1052.3	1120.8	1175.6	1247.2
32.5°	782.7	796.5	811.7	837.6	858.9	886.3	919.8	974.6	1032.5	1067.5	1122.3
35°	724.9	734.0	766.0	776.7	798.0	825.4	858.9	901.5	964.0	991.4	1031.0
37.5°	670.1	691.4	700.5	724.9	744.7	772.1	796.5	845.2	886.3	918.3	954.8
40°	627.4	636.6	653.3	674.6	691.4	712.7	743.2	778.2	822.3	848.2	880.2
42.5°	575.6	583.3	604.6	616.8	644.2	664.0	682.2	724.9	764.5	784.3	816.3
45°	519.3	537.6	551.3	575.6	590.9	615.2	638.1	668.5	705.1	727.9	746.2
47.5°	470.6	488.8	502.5	525.4	549.8	560.4	584.8	616.8	650.3	668.5	694.4
50°	431.0	437.1	462.9	473.6	499.5	520.8	537.6	565.0	601.5	612.2	633.5
52.5°	392.9	397.5	414.2	427.9	450.8	469.0	490.4	516.2	546.7	563.5	580.2
55°	359.4	362.4	370.1	385.3	400.5	423.4	443.2	467.5	493.4	511.7	526.9
57.5°	321.3	327.4	333.5	342.6	357.9	379.2	400.5	423.4	444.7	456.9	476.7
60°	277.2	286.3	297.0	307.6	318.3	333.5	357.9	379.2	399.0	409.6	424.9
62.5°	230.0	248.2	257.4	269.5	278.7	292.4	310.7	335.0	348.7	362.4	374.6
65°	207.1	208.6	210.2	222.3	239.1	252.8	269.5	287.8	309.1	318.3	327.4
67.5°	184.3	185.8	188.8	190.4	196.4	211.7	230.0	249.7	266.5	272.6	281.7
70°	161.4	161.4	167.5	169.0	170.6	172.1	187.3	207.1	222.3	230.0	240.6
72.5°	137.1	138.6	141.6	143.1	146.2	149.2	153.8	164.5	182.7	190.4	202.5
75°	112.7	114.2	115.7	117.3	121.8	123.4	127.9	134.0	141.6	150.8	158.4
77.5°	89.8	89.8	91.4	94.4	97.5	99.0	103.6	106.6	109.6	114.2	120.3
80°	67.0	68.5	68.5	71.6	71.6	73.1	74.6	79.2	82.2	85.3	88.3
82.5°	45.7	48.7	48.7	48.7	50.3	51.8	53.3	53.3	56.3	57.9	62.4
85°	27.4	28.9	28.9	28.9	27.4	30.5	30.5	32.0	32.0	32.0	33.5
87.5°	10.7	9.1	10.7	10.7	10.7	12.2	10.7	10.7	12.2	13.7	13.7
90°	38.3	38.8	39.3	39.8	40.3	34.7	29.1	23.4	17.8	15.0	13.5
92.5°	36.7	36.4	36.2	35.9	35.7	35.4	35.2	34.9	34.6	34.5	33.5
95°	73.7	73.7	73.7	73.7	73.7	73.2	72.7	72.2	71.7	71.4	70.1
97.5°	115.1	115.1	115.1	115.1	115.1	114.1	113.1	112.0	111.0	110.5	109.3
100°	158.8	158.8	158.8	158.8	158.8	158.0	157.3	156.5	155.8	155.4	154.4
102.5°	207.1	206.8	206.5	206.3	206.0	205.0	204.0	202.9	201.9	201.4	200.6
105°	255.2	254.7	254.2	253.7	253.2	252.7	252.2	251.7	251.2	250.9	250.5
107.5°	306.1	305.8	305.5	305.3	305.0	305.0	305.0	305.0	305.0	305.0	304.5
110°	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.1

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	409.0	409.7	410.5	411.2	412.0	412.3	412.5	412.8	413.1	413.2	412.4
115°	463.9	464.2	464.5	464.7	465.0	465.5	466.0	466.5	467.0	467.3	466.5
117.5°	514.9	515.6	516.4	517.1	517.9	519.2	520.5	521.8	523.1	523.7	522.7
120°	568.6	568.6	568.6	568.6	568.6	570.6	572.7	574.7	576.8	577.8	576.8
122.5°	620.8	621.5	622.3	623.0	623.8	625.1	626.4	627.7	629.0	629.6	628.3
125°	673.7	674.5	675.2	676.0	676.8	677.6	678.3	679.1	679.8	680.2	679.0
127.5°	724.4	725.4	726.5	727.5	728.5	729.5	730.6	731.6	732.7	733.2	731.8
130°	778.3	778.8	779.3	779.8	780.3	780.8	781.3	781.8	782.3	782.6	780.9
132.5°	828.1	829.4	830.7	832.0	833.3	833.0	832.8	832.5	832.2	832.1	830.8
135°	880.6	880.9	881.1	881.4	881.6	881.1	880.6	880.1	879.6	879.3	877.9
137.5°	928.9	929.2	929.5	929.7	930.0	929.5	929.0	928.5	928.0	927.7	926.5
140°	978.3	978.3	978.3	978.3	978.3	977.0	975.7	974.4	973.1	972.5	971.4
142.5°	1023.1	1022.8	1022.5	1022.3	1022.0	1021.2	1020.5	1019.7	1019.0	1018.6	1017.4
145°	1068.0	1067.7	1067.4	1067.2	1066.9	1065.4	1063.8	1062.3	1060.8	1060.0	1059.1
147.5°	1108.1	1107.6	1107.1	1106.6	1106.1	1105.1	1104.1	1103.0	1102.0	1101.5	1100.3
150°	1145.9	1145.2	1144.4	1143.7	1142.9	1141.9	1140.9	1139.8	1138.8	1138.3	1137.5
152.5°	1183.8	1182.8	1181.7	1180.7	1179.7	1178.4	1177.2	1175.9	1174.6	1174.0	1173.2
155°	1214.8	1213.5	1212.2	1210.9	1209.6	1208.8	1208.1	1207.3	1206.6	1206.2	1205.8
157.5°	1245.6	1243.8	1242.0	1240.2	1238.4	1237.9	1237.4	1236.9	1236.4	1236.1	1235.8
160°	1271.0	1269.5	1268.0	1266.4	1264.9	1264.6	1264.4	1264.1	1263.8	1263.7	1263.4
162.5°	1295.1	1293.3	1291.5	1289.7	1287.9	1287.7	1287.4	1287.2	1286.9	1286.8	1286.8
165°	1314.6	1312.8	1311.1	1309.3	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.6
167.5°	1331.9	1330.1	1328.3	1326.5	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1325.1
170°	1345.7	1343.9	1342.1	1340.3	1338.5	1338.8	1339.0	1339.3	1339.6	1339.7	1340.1
172.5°	1356.1	1354.3	1352.5	1350.7	1348.9	1349.2	1349.4	1349.7	1350.0	1350.1	1350.5
175°	1363.0	1361.2	1359.4	1357.6	1355.8	1356.3	1356.8	1357.3	1357.8	1358.1	1358.5
177.5°	1366.5	1365.0	1363.5	1361.9	1360.4	1360.9	1361.4	1361.9	1362.4	1362.7	1363.1
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2191.4	2191.4	2191.4	2191.4
2.5°	2151.8	2147.2	2174.6	2205.1
5°	2107.6	2115.3	2150.3	2192.9
7.5°	2062.0	2078.7	2119.8	2176.2
10°	1998.0	2028.4	2090.9	2148.8
12.5°	1935.6	1976.7	2036.1	2104.6
15°	1865.5	1911.2	1984.3	2066.5
17.5°	1787.8	1839.6	1924.9	2014.7
20°	1705.6	1774.1	1864.0	1961.4
22.5°	1614.2	1696.5	1789.4	1897.5
25°	1525.9	1615.8	1708.6	1833.5
27.5°	1439.1	1527.4	1631.0	1757.4
30°	1352.3	1433.0	1544.2	1679.7
32.5°	1259.4	1343.2	1460.4	1599.0
35°	1174.1	1257.9	1367.5	1504.6
37.5°	1082.8	1172.6	1277.7	1419.3
40°	976.2	1081.2	1183.3	1318.8
42.5°	887.8	999.0	1098.0	1225.9
45°	817.8	922.9	1005.1	1130.0
47.5°	752.3	837.6	921.3	1037.1
50°	689.9	755.3	842.1	945.7
52.5°	625.9	682.2	756.9	854.3
55°	568.0	621.3	688.3	763.0
57.5°	514.7	552.8	619.8	686.8
60°	455.3	494.9	546.7	603.1
62.5°	405.1	435.5	484.3	531.5
65°	351.8	380.7	417.3	461.4
67.5°	303.0	328.9	357.9	392.9
70°	258.9	278.7	300.0	330.5
72.5°	211.7	233.0	252.8	277.2
75°	173.6	182.7	199.5	216.2
77.5°	134.0	146.2	155.3	169.0
80°	95.9	106.6	109.6	120.3
82.5°	64.0	70.1	76.1	79.2
85°	36.5	39.6	45.7	47.2
87.5°	13.7	15.2	18.3	21.3
90°	10.4	7.3	4.3	1.2
92.5°	31.4	29.4	27.3	25.3
95°	67.5	65.0	62.4	59.8
97.5°	107.0	104.7	102.4	100.1
100°	152.3	150.3	148.2	146.2
102.5°	199.1	197.6	196.0	194.5
105°	249.8	249.0	248.3	247.5
107.5°	303.5	302.4	301.4	300.4
110°	355.6	354.1	352.5	351.0

TEST NUMBER: P999270

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	410.9	409.4	407.8	406.3
115°	465.0	463.5	461.9	460.4
117.5°	520.6	518.6	516.5	514.5
120°	574.7	572.7	570.6	568.6
122.5°	625.8	623.2	620.7	618.1
125°	676.7	674.4	672.1	669.8
127.5°	729.0	726.1	723.3	720.5
130°	777.6	774.3	771.0	767.7
132.5°	828.3	825.7	823.2	820.6
135°	875.1	872.3	869.5	866.7
137.5°	924.2	921.9	919.6	917.3
140°	969.1	966.8	964.5	962.2
142.5°	1015.1	1012.8	1010.5	1008.2
145°	1057.3	1055.6	1053.8	1052.0
147.5°	1098.0	1095.7	1093.4	1091.1
150°	1136.0	1134.5	1132.9	1131.4
152.5°	1171.7	1170.2	1168.6	1167.1
155°	1205.0	1204.3	1203.5	1202.7
157.5°	1235.3	1234.8	1234.3	1233.8
160°	1262.9	1262.4	1261.9	1261.4
162.5°	1286.8	1286.8	1286.8	1286.8
165°	1307.9	1308.1	1308.4	1308.6
167.5°	1325.9	1326.6	1327.4	1328.2
170°	1340.9	1341.6	1342.4	1343.2
172.5°	1351.2	1352.0	1352.7	1353.5
175°	1359.3	1360.0	1360.8	1361.6
177.5°	1363.9	1364.6	1365.4	1366.2
180°	1363.9	1363.9	1363.9	1363.9

(END OF REPORT)