

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999271

Luminaire Tested: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999271
REPORT IS A COMBINATION OF REPORTS P987820 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7959.0 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	87	90	87	84	81	73	71	69	60	59	58	49	48	47
2	90	83	77	72	83	77	72	68	65	61	58	54	51	49	44	42	41
3	82	74	67	61	76	68	62	57	58	54	50	48	45	43	40	37	36
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	34	31
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28
6	65	53	46	40	60	50	43	38	43	37	34	36	32	29	30	27	25
7	60	48	41	36	55	45	38	34	39	34	30	33	29	26	28	25	23
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21
9	52	41	33	29	48	38	32	27	33	28	24	28	24	22	24	21	19
10	49	37	30	26	45	35	29	25	31	26	22	26	23	20	22	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34688	34688	34688	34688
5°	34769	36845	34889	29434
10°	34387	38943	34630	24307
15°	33640	38956	34210	18260
20°	32742	32200	33455	15065
25°	31654	20121	32338	12815
30°	30265	12883	31088	11033
35°	28575	9901	29500	9442
40°	26691	8322	27831	8259
45°	24679	7083	25710	6933
50°	22615	6018	23672	5996
55°	20331	5230	21426	5162
60°	18301	3988	19269	3941
65°	16402	3001	17377	3405
70°	14313	2397	15430	2776
75°	12094	1836	13202	2098
80°	9604	1249	10331	1377
85°	6667	644	7317	680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 31731 cd/sqm

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.9	2.6
10°-20°	580.2	7.3
20°-30°	746.7	9.4
30°-40°	708.4	8.9
40°-50°	607.1	7.6
50°-60°	462.3	5.8
60°-70°	291.6	3.7
70°-80°	145.5	1.8
80°-90°	41.2	0.5
90°-100°	233.3	2.9
100°-110°	821.7	10.3
110°-120°	863.0	10.8
120°-130°	709.9	8.9
130°-140°	570.3	7.2
140°-150°	430.8	5.4
150°-160°	302.9	3.8
160°-170°	178.3	2.2
170°-180°	58.0	0.7
0°-30°	1534.7	19.3
0°-40°	2243.1	28.2
0°-60°	3312.6	41.6
0°-90°	3790.8	47.6
90°-120°	1918.0	24.1
90°-150°	3629.0	45.6
90°-180°	4168.0	52.4
0°-180°	7959.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2191	2191	2191	2191	2191	
5°	2193	2438	2200	1948	2193	208
15°	2066	2752	2102	1290	2066	581
25°	1834	1468	1873	935	1834	842
35°	1505	723	1553	690	1505	941
45°	1130	502	1177	492	1130	872
55°	763	349	804	344	763	688
65°	461	181	489	206	461	458
75°	216	96	236	110	216	234
85°	47	27	52	29	47	54
90°	1	38	1	38	1	6
95°	40	131	40	131	40	42
105°	140	1297	140	1297	140	149
115°	248	1707	248	1707	248	245
125°	345	1385	345	1385	345	307
135°	405	1148	405	1148	405	313
145°	463	916	463	916	463	290
155°	526	770	526	770	526	242
165°	573	676	573	676	573	162
175°	597	609	597	609	597	57
180°	598	598	598	598	598	

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2205.1	2214.2	2218.8	2224.9	2238.6	2247.7	2261.4	2264.5	2263.0	2269.1	2252.3
5°	2192.9	2212.7	2231.0	2246.2	2270.6	2285.8	2302.6	2322.4	2326.9	2349.8	2336.1
7.5°	2176.2	2205.1	2231.0	2261.4	2298.0	2317.8	2343.7	2374.1	2387.8	2415.3	2422.9
10°	2148.8	2189.9	2234.0	2266.0	2316.3	2351.3	2375.7	2424.4	2456.4	2497.5	2491.4
12.5°	2104.6	2157.9	2217.3	2270.6	2336.1	2358.9	2404.6	2454.8	2496.0	2534.0	2567.5
15°	2066.5	2127.4	2192.9	2258.4	2333.0	2375.7	2421.3	2486.8	2531.0	2598.0	2626.9
17.5°	2014.7	2092.4	2170.1	2243.2	2331.5	2380.2	2436.6	2500.5	2566.0	2630.0	2652.8
20°	1961.4	2045.2	2129.0	2227.9	2328.5	2375.7	2433.5	2512.7	2576.7	2626.9	2626.9
22.5°	1897.5	1999.5	2095.5	2189.9	2299.5	2368.0	2427.4	2520.3	2566.0	2576.7	2535.6
25°	1833.5	1935.6	2040.6	2157.9	2282.8	2343.7	2410.7	2497.5	2512.7	2470.1	2363.5
27.5°	1757.4	1871.6	1990.4	2116.8	2247.7	2323.9	2384.8	2442.7	2413.7	2299.5	2133.5
30°	1679.7	1803.1	1937.1	2057.4	2215.8	2285.8	2337.6	2354.3	2263.0	2077.2	1862.5
32.5°	1599.0	1719.3	1860.9	2005.6	2165.5	2232.5	2266.0	2221.9	2054.3	1819.8	1557.9
35°	1504.6	1640.1	1787.8	1938.6	2097.0	2147.2	2167.0	2058.9	1844.2	1541.1	1280.7
37.5°	1419.3	1554.8	1713.2	1867.0	2020.8	2048.2	2028.4	1859.4	1586.8	1286.8	1032.5
40°	1318.8	1463.5	1618.8	1790.9	1917.3	1924.9	1876.2	1656.9	1318.8	1037.1	880.2
42.5°	1225.9	1372.1	1527.4	1702.6	1798.5	1772.6	1707.1	1419.3	1101.0	893.9	767.5
45°	1130.0	1268.5	1436.1	1591.4	1659.9	1599.0	1500.0	1193.9	924.4	769.0	671.6
47.5°	1037.1	1166.5	1332.5	1481.7	1493.9	1425.4	1308.1	1000.5	801.0	676.1	597.0
50°	945.7	1075.1	1230.5	1353.8	1341.6	1247.2	1114.7	869.6	695.9	597.0	531.5
52.5°	854.3	971.6	1122.3	1219.8	1168.0	1076.7	945.7	737.1	607.6	520.8	470.6
55°	763.0	872.6	1002.0	1082.8	1000.5	895.4	802.5	632.0	526.9	456.9	418.8
57.5°	686.8	773.6	892.4	941.1	842.1	759.9	679.2	543.7	456.9	406.6	362.4
60°	603.1	682.2	779.7	808.6	706.6	639.6	571.1	459.9	391.4	347.2	318.3
62.5°	531.5	597.0	671.6	671.6	581.7	531.5	479.7	385.3	328.9	293.9	280.2
65°	461.4	508.6	561.9	555.8	479.7	435.5	394.4	318.3	275.6	251.3	237.6
67.5°	392.9	429.4	464.5	443.2	388.3	350.3	312.2	257.4	228.4	211.7	193.4
70°	330.5	359.4	377.7	357.9	303.0	271.1	243.7	207.1	184.3	162.9	152.3
72.5°	277.2	289.3	295.4	271.1	225.4	207.1	187.3	161.4	141.6	131.0	127.9
75°	216.2	226.9	222.3	204.1	166.0	152.3	137.1	118.8	114.2	108.1	105.1
77.5°	169.0	169.0	161.4	144.7	118.8	108.1	102.0	92.9	88.3	86.8	83.8
80°	120.3	118.8	114.2	95.9	80.7	74.6	74.6	68.5	67.0	64.0	64.0
82.5°	79.2	79.2	73.1	57.9	53.3	51.8	50.3	47.2	47.2	45.7	45.7
85°	47.2	44.2	36.5	32.0	30.5	30.5	28.9	27.4	28.9	27.4	27.4
87.5°	21.3	16.8	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
90°	1.2	4.6	9.2	11.5	13.8	15.6	17.3	23.0	31.1	38.0	39.1
92.5°	17.3	24.2	33.4	39.1	48.3	54.6	61.0	92.1	135.8	175.0	177.3
95°	40.3	44.9	56.4	66.8	85.2	99.0	112.8	165.7	265.9	399.4	451.2
97.5°	59.9	66.8	79.4	94.4	115.1	130.6	146.2	214.1	353.4	568.6	735.5
100°	88.6	92.1	102.4	120.9	143.9	160.0	176.1	237.1	377.5	626.2	909.3
102.5°	115.1	117.4	127.8	146.2	170.3	186.4	202.6	257.8	378.7	604.3	915.1
105°	140.4	145.0	153.1	170.3	195.7	211.8	227.9	282.0	384.4	574.4	852.9
107.5°	168.0	171.5	179.6	195.7	221.0	237.1	253.2	306.2	397.1	558.2	795.3
110°	195.7	200.3	207.2	222.1	246.3	263.0	279.7	330.3	413.2	553.6	756.2

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	221.0	225.6	233.7	247.5	270.5	287.8	305.0	353.4	430.5	554.8	730.9
115°	247.5	253.2	260.1	273.9	297.0	312.5	328.0	377.5	447.7	559.4	713.6
117.5°	275.1	279.7	286.6	299.3	321.1	337.2	353.4	399.4	466.2	566.3	704.4
120°	300.4	305.0	311.9	322.3	345.3	361.4	377.5	422.4	484.6	573.2	696.4
122.5°	324.6	328.0	334.9	346.5	369.5	386.2	402.9	444.3	500.7	581.3	691.8
125°	345.3	348.8	355.7	369.5	392.5	408.6	424.7	466.2	518.0	589.3	686.0
127.5°	362.6	367.2	376.4	391.3	413.2	429.9	446.6	486.9	534.1	597.4	682.6
130°	377.5	382.1	393.6	409.8	432.8	448.9	465.0	505.3	549.0	606.6	680.2
132.5°	391.3	397.1	409.8	427.0	451.2	467.3	483.4	521.4	564.0	615.8	679.1
135°	405.2	409.8	423.6	440.8	467.3	483.4	499.5	536.4	576.7	622.7	677.9
137.5°	417.8	423.6	437.4	455.8	482.3	497.2	512.2	549.0	587.0	629.6	677.9
140°	432.8	437.4	451.2	469.6	494.9	509.9	524.9	559.4	595.1	634.2	676.8
142.5°	447.7	451.2	463.9	482.3	506.4	520.2	534.1	567.4	602.0	637.7	676.8
145°	462.7	467.3	478.8	496.1	519.1	531.8	544.4	575.5	607.7	640.0	674.5
147.5°	478.8	482.3	493.8	509.9	529.5	541.0	552.5	582.4	611.2	641.1	671.0
150°	494.9	498.4	507.6	522.6	539.8	550.2	560.5	587.0	613.5	640.0	667.6
152.5°	511.0	512.2	521.4	534.1	550.2	559.4	568.6	591.6	614.6	637.7	661.8
155°	526.0	527.2	534.1	546.7	559.4	568.0	576.7	596.2	615.8	635.4	654.9
157.5°	538.7	539.8	545.6	557.1	567.4	574.9	582.4	599.7	615.8	630.8	648.0
160°	551.3	552.5	557.1	566.3	575.5	581.8	588.2	602.0	615.8	627.3	641.1
162.5°	564.0	562.8	567.4	574.4	582.4	587.0	591.6	603.1	614.6	623.8	635.4
165°	573.2	572.1	574.4	581.3	587.0	590.4	593.9	604.3	612.3	619.2	627.3
167.5°	581.3	580.1	582.4	587.0	591.6	593.9	596.2	604.3	611.2	614.6	620.4
170°	589.3	587.0	588.2	591.6	593.9	595.6	597.4	603.1	608.9	611.2	614.6
172.5°	593.9	592.8	591.6	595.1	596.2	597.4	598.5	602.0	605.4	606.6	607.7
175°	597.4	596.2	595.1	597.4	597.4	598.0	598.5	600.8	603.1	602.0	603.1
177.5°	599.7	597.4	596.2	598.5	598.5	598.5	598.5	599.7	602.0	599.7	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2269.1	2272.1	2276.7	2298.0	2301.0	2307.1	2304.1	2304.1	2305.6	2302.6	2304.1
5°	2366.5	2371.1	2393.9	2419.8	2425.9	2419.8	2427.4	2438.1	2438.1	2438.1	2435.1
7.5°	2457.9	2474.6	2500.5	2538.6	2546.2	2553.8	2567.5	2558.4	2561.4	2575.2	2570.6
10°	2546.2	2570.6	2599.5	2631.5	2648.3	2658.9	2665.0	2678.7	2710.7	2674.1	2687.8
12.5°	2630.0	2665.0	2695.5	2730.5	2742.7	2756.4	2760.9	2773.1	2773.1	2771.6	2782.3
15°	2684.8	2716.8	2744.2	2767.0	2770.1	2767.0	2764.0	2765.5	2770.1	2751.8	2762.5
17.5°	2697.0	2700.0	2709.2	2700.0	2701.6	2669.6	2651.3	2646.7	2604.1	2605.6	2640.6
20°	2637.6	2585.8	2572.1	2521.9	2491.4	2409.2	2406.1	2383.3	2293.4	2320.8	2314.7
22.5°	2474.6	2386.3	2269.1	2211.2	2182.3	2095.5	2028.4	1981.2	1949.3	1917.3	1903.6
25°	2259.9	2116.8	1950.8	1836.6	1819.8	1739.1	1615.8	1557.9	1489.4	1468.0	1504.6
27.5°	1982.8	1797.0	1609.7	1434.5	1402.6	1329.5	1267.0	1225.9	1146.7	1142.1	1145.2
30°	1606.6	1419.3	1262.4	1148.2	1069.0	1035.5	994.4	964.0	932.0	944.2	947.2
32.5°	1320.3	1142.1	995.9	935.0	898.5	877.2	842.1	822.3	808.6	804.1	802.5
35°	1049.2	930.5	865.0	805.6	784.3	769.0	743.2	734.0	721.8	723.4	723.4
37.5°	898.5	799.5	750.8	720.3	700.5	692.9	676.1	667.0	659.4	656.4	660.9
40°	775.1	706.6	676.1	648.7	632.0	628.9	619.8	609.1	600.0	601.5	606.1
42.5°	685.3	645.7	609.1	587.8	575.6	571.1	563.5	555.8	555.8	551.3	549.8
45°	613.7	581.7	551.3	531.5	523.9	517.8	508.6	507.1	501.0	502.5	504.1
47.5°	549.8	523.9	501.0	481.2	473.6	472.1	462.9	456.9	456.9	455.3	453.8
50°	491.9	466.0	446.2	435.5	424.9	421.8	420.3	418.8	415.7	415.7	417.3
52.5°	444.7	418.8	403.6	394.4	388.3	385.3	385.3	383.8	383.8	383.8	382.2
55°	392.9	371.6	359.4	356.3	353.3	351.8	350.3	347.2	345.7	348.7	345.7
57.5°	344.2	336.6	325.9	322.8	315.2	315.2	310.7	307.6	304.6	307.6	307.6
60°	306.1	295.4	289.3	280.2	274.1	268.0	260.4	258.9	255.8	254.3	252.8
62.5°	266.5	257.4	242.1	228.4	219.3	213.2	210.2	208.6	208.6	207.1	207.1
65°	222.3	201.0	193.4	188.8	187.3	185.8	182.7	181.2	182.7	181.2	182.7
67.5°	173.6	170.6	166.0	162.9	161.4	159.9	159.9	158.4	158.4	158.4	158.4
70°	150.8	143.1	141.6	138.6	138.6	137.1	137.1	137.1	137.1	135.5	138.6
72.5°	124.9	120.3	118.8	117.3	117.3	117.3	115.7	115.7	115.7	114.2	115.7
75°	102.0	100.5	97.5	97.5	95.9	97.5	95.9	95.9	94.4	95.9	95.9
77.5°	82.2	80.7	79.2	79.2	77.7	77.7	77.7	77.7	77.7	77.7	79.2
80°	62.4	60.9	59.4	60.9	59.4	60.9	59.4	59.4	60.9	59.4	59.4
82.5°	45.7	44.2	44.2	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6
85°	27.4	25.9	25.9	27.4	25.9	27.4	25.9	25.9	25.9	27.4	27.4
87.5°	12.2	13.7	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	13.7
90°	38.0	36.8	34.5	36.8	37.4	38.0	38.0	38.0	38.0	38.0	38.0
92.5°	148.5	116.3	99.0	86.3	81.7	77.1	76.0	71.4	72.5	70.2	72.5
95°	394.8	301.6	231.4	183.0	170.4	157.7	142.7	133.5	130.1	131.2	130.1
97.5°	741.3	616.9	492.6	376.4	341.8	307.3	262.4	239.4	226.7	219.8	226.7
100°	1075.0	1050.9	908.1	750.5	680.8	611.2	515.7	466.2	432.8	412.1	432.8
102.5°	1199.4	1335.2	1330.6	1225.8	1151.0	1076.2	970.3	877.1	833.3	803.4	833.3
105°	1159.1	1398.5	1528.5	1543.5	1524.5	1505.5	1434.2	1362.8	1313.3	1297.2	1313.3
107.5°	1073.9	1330.6	1523.9	1636.7	1659.8	1682.8	1681.6	1671.3	1656.3	1629.8	1656.3
110°	994.5	1237.3	1443.4	1590.7	1637.9	1685.1	1734.6	1756.4	1766.8	1765.7	1766.8

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	939.2	1152.2	1347.8	1507.8	1563.6	1619.5	1693.1	1733.4	1755.3	1763.4	1755.3
115°	895.5	1085.4	1262.7	1413.4	1472.7	1532.0	1613.7	1666.7	1696.6	1707.0	1696.6
117.5°	865.6	1030.2	1189.0	1329.4	1385.8	1442.2	1526.2	1582.6	1613.7	1621.8	1613.7
120°	842.5	991.0	1133.7	1255.8	1308.2	1360.5	1441.1	1495.2	1528.5	1540.1	1528.5
122.5°	823.0	959.9	1087.7	1201.7	1247.7	1293.7	1363.9	1416.9	1445.7	1454.9	1445.7
125°	804.6	930.0	1048.6	1149.9	1193.1	1236.2	1302.9	1346.7	1375.5	1384.7	1375.5
127.5°	787.3	900.1	1009.4	1106.1	1146.4	1186.7	1245.4	1286.8	1312.2	1319.1	1312.2
130°	770.0	871.3	970.3	1061.2	1099.2	1137.2	1193.6	1232.7	1255.8	1265.0	1255.8
132.5°	756.2	843.7	933.5	1015.2	1050.3	1085.4	1140.7	1179.8	1200.5	1208.6	1200.5
135°	743.6	818.4	894.3	970.3	1002.6	1034.8	1084.3	1122.2	1143.0	1147.6	1143.0
137.5°	734.3	797.7	863.3	925.4	954.2	983.0	1030.2	1063.5	1082.0	1088.9	1082.0
140°	726.3	778.1	833.3	886.3	911.6	936.9	973.8	1003.7	1020.9	1027.9	1020.9
142.5°	718.2	762.0	806.9	850.6	870.8	890.9	925.4	951.9	966.9	966.9	966.9
145°	711.3	747.0	785.0	820.7	837.4	854.1	881.7	901.2	912.8	916.2	912.8
147.5°	704.4	735.5	766.6	795.3	808.0	820.7	844.8	861.0	869.0	871.3	869.0
150°	695.2	722.8	748.2	772.3	782.6	793.0	810.3	824.1	831.0	832.2	831.0
152.5°	687.2	710.2	733.2	752.8	761.4	770.0	782.7	794.2	798.8	798.8	798.8
155°	676.8	698.7	717.1	734.3	740.6	747.0	759.7	767.7	772.3	770.0	772.3
157.5°	667.6	684.9	701.0	715.9	721.1	726.3	735.5	742.4	744.7	744.7	744.7
160°	657.2	672.2	684.9	697.5	701.6	705.6	713.6	719.4	720.5	720.5	720.5
162.5°	648.0	659.5	669.9	680.2	683.1	686.0	694.1	697.5	698.7	697.5	698.7
165°	637.7	646.9	654.9	663.0	665.3	667.6	672.2	676.8	676.8	675.6	676.8
167.5°	627.3	634.2	641.1	646.9	649.2	651.5	653.8	656.1	656.1	654.9	656.1
170°	619.2	625.0	628.5	633.1	634.2	635.4	636.5	640.0	638.8	636.5	638.8
172.5°	611.2	614.6	616.9	620.4	621.0	621.5	622.7	623.8	622.7	621.5	622.7
175°	604.3	607.7	608.9	610.0	610.6	611.2	611.2	612.3	611.2	608.9	611.2
177.5°	599.7	602.0	602.0	603.1	603.1	603.1	603.1	603.1	602.0	599.7	602.0
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2310.2	2299.5	2296.5	2299.5	2296.5	2298.0	2287.3	2247.7	2258.4	2241.6	2250.8
5°	2441.1	2432.0	2412.2	2409.2	2406.1	2403.1	2387.8	2352.8	2339.1	2316.3	2314.7
7.5°	2566.0	2566.0	2550.8	2540.1	2526.4	2515.8	2496.0	2444.2	2422.9	2395.5	2380.2
10°	2689.4	2649.8	2666.5	2655.9	2622.4	2616.3	2579.7	2549.3	2508.1	2480.7	2456.4
12.5°	2777.7	2765.5	2750.3	2741.1	2732.0	2712.2	2687.8	2610.2	2588.9	2534.0	2506.6
15°	2774.6	2767.0	2771.6	2771.6	2768.6	2764.0	2744.2	2687.8	2651.3	2598.0	2550.8
17.5°	2625.4	2645.2	2665.0	2678.7	2709.2	2722.9	2741.1	2707.6	2684.8	2639.1	2588.9
20°	2365.0	2413.7	2471.6	2483.8	2511.2	2591.9	2628.5	2657.4	2666.5	2651.3	2610.2
22.5°	2002.6	2043.7	2183.8	2180.7	2220.3	2316.3	2422.9	2509.7	2578.2	2616.3	2601.0
25°	1568.5	1626.4	1701.0	1757.4	1886.8	2030.0	2162.5	2301.0	2419.8	2524.9	2550.8
27.5°	1186.3	1262.4	1321.8	1396.5	1461.9	1631.0	1801.5	2017.8	2156.4	2355.9	2459.4
30°	959.4	994.4	1053.8	1088.8	1120.8	1250.3	1443.7	1656.9	1900.5	2130.5	2308.7
32.5°	819.3	843.7	887.8	903.1	936.6	1023.4	1145.2	1340.1	1591.4	1870.1	2104.6
35°	735.5	761.4	770.6	784.3	811.7	866.5	950.3	1091.9	1318.8	1591.4	1871.6
37.5°	664.0	677.7	703.6	712.7	721.8	763.0	819.3	918.3	1069.0	1292.9	1603.6
40°	613.7	621.3	635.0	642.6	648.7	677.7	727.9	794.9	906.1	1076.7	1363.0
42.5°	560.4	569.5	578.7	587.8	595.4	618.3	648.7	712.7	787.3	916.8	1123.9
45°	508.6	514.7	525.4	531.5	542.1	560.4	587.8	632.0	699.0	781.2	948.7
47.5°	461.4	469.0	473.6	481.2	488.8	508.6	534.5	563.5	618.3	699.0	820.8
50°	418.8	427.9	434.0	435.5	441.6	459.9	481.2	513.2	548.2	610.7	717.3
52.5°	388.3	389.9	394.4	400.5	399.0	409.6	429.4	453.8	490.4	540.6	618.3
55°	353.3	357.9	360.9	362.4	362.4	371.6	382.2	405.1	434.0	475.1	540.6
57.5°	309.1	313.7	322.8	325.9	330.5	335.0	339.6	354.8	379.2	418.8	472.1
60°	263.5	266.5	275.6	281.7	284.8	297.0	303.0	315.2	328.9	357.9	408.1
62.5°	211.7	214.7	219.3	225.4	231.5	249.7	265.0	277.2	287.8	307.6	348.7
65°	184.3	185.8	188.8	190.4	191.9	199.5	213.2	230.0	249.7	265.0	289.3
67.5°	159.9	161.4	162.9	166.0	167.5	169.0	175.1	179.7	199.5	220.8	239.1
70°	137.1	140.1	141.6	141.6	143.1	146.2	149.2	155.3	161.4	172.1	194.9
72.5°	115.7	117.3	120.3	120.3	120.3	123.4	126.4	129.4	132.5	138.6	147.7
75°	95.9	99.0	99.0	99.0	100.5	100.5	103.6	106.6	109.6	114.2	117.3
77.5°	79.2	79.2	79.2	79.2	80.7	80.7	82.2	85.3	86.8	88.3	91.4
80°	59.4	60.9	60.9	60.9	62.4	62.4	62.4	65.5	67.0	67.0	70.1
82.5°	44.2	44.2	44.2	45.7	44.2	45.7	45.7	47.2	45.7	47.2	48.7
85°	27.4	27.4	27.4	28.9	28.9	28.9	28.9	28.9	28.9	28.9	30.5
87.5°	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7	15.2	13.7	13.7
90°	38.0	38.0	38.0	37.4	36.8	34.5	36.8	38.0	39.1	38.0	31.1
92.5°	71.4	76.0	77.1	81.7	86.3	99.0	116.3	148.5	177.3	175.0	135.8
95°	133.5	142.7	157.7	170.4	183.0	231.4	301.6	394.8	451.2	399.4	265.9
97.5°	239.4	262.4	307.3	341.8	376.4	492.6	616.9	741.3	735.5	568.6	353.4
100°	466.2	515.7	611.2	680.8	750.5	908.1	1050.9	1075.0	909.3	626.2	377.5
102.5°	877.1	970.3	1076.2	1151.0	1225.8	1330.6	1335.2	1199.4	915.1	604.3	378.7
105°	1362.8	1434.2	1505.5	1524.5	1543.5	1528.5	1398.5	1159.1	852.9	574.4	384.4
107.5°	1671.3	1681.6	1682.8	1659.8	1636.7	1523.9	1330.6	1073.9	795.3	558.2	397.1
110°	1756.4	1734.6	1685.1	1637.9	1590.7	1443.4	1237.3	994.5	756.2	553.6	413.2

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1733.4	1693.1	1619.5	1563.6	1507.8	1347.8	1152.2	939.2	730.9	554.8	430.5
115°	1666.7	1613.7	1532.0	1472.7	1413.4	1262.7	1085.4	895.5	713.6	559.4	447.7
117.5°	1582.6	1526.2	1442.2	1385.8	1329.4	1189.0	1030.2	865.6	704.4	566.3	466.2
120°	1495.2	1441.1	1360.5	1308.2	1255.8	1133.7	991.0	842.5	696.4	573.2	484.6
122.5°	1416.9	1363.9	1293.7	1247.7	1201.7	1087.7	959.9	823.0	691.8	581.3	500.7
125°	1346.7	1302.9	1236.2	1193.1	1149.9	1048.6	930.0	804.6	686.0	589.3	518.0
127.5°	1286.8	1245.4	1186.7	1146.4	1106.1	1009.4	900.1	787.3	682.6	597.4	534.1
130°	1232.7	1193.6	1137.2	1099.2	1061.2	970.3	871.3	770.0	680.2	606.6	549.0
132.5°	1179.8	1140.7	1085.4	1050.3	1015.2	933.5	843.7	756.2	679.1	615.8	564.0
135°	1122.2	1084.3	1034.8	1002.6	970.3	894.3	818.4	743.6	677.9	622.7	576.7
137.5°	1063.5	1030.2	983.0	954.2	925.4	863.3	797.7	734.3	677.9	629.6	587.0
140°	1003.7	973.8	936.9	911.6	886.3	833.3	778.1	726.3	676.8	634.2	595.1
142.5°	951.9	925.4	890.9	870.8	850.6	806.9	762.0	718.2	676.8	637.7	602.0
145°	901.2	881.7	854.1	837.4	820.7	785.0	747.0	711.3	674.5	640.0	607.7
147.5°	861.0	844.8	820.7	808.0	795.3	766.6	735.5	704.4	671.0	641.1	611.2
150°	824.1	810.3	793.0	782.6	772.3	748.2	722.8	695.2	667.6	640.0	613.5
152.5°	794.2	782.7	770.0	761.4	752.8	733.2	710.2	687.2	661.8	637.7	614.6
155°	767.7	759.7	747.0	740.6	734.3	717.1	698.7	676.8	654.9	635.4	615.8
157.5°	742.4	735.5	726.3	721.1	715.9	701.0	684.9	667.6	648.0	630.8	615.8
160°	719.4	713.6	705.6	701.6	697.5	684.9	672.2	657.2	641.1	627.3	615.8
162.5°	697.5	694.1	686.0	683.1	680.2	669.9	659.5	648.0	635.4	623.8	614.6
165°	676.8	672.2	667.6	665.3	663.0	654.9	646.9	637.7	627.3	619.2	612.3
167.5°	656.1	653.8	651.5	649.2	646.9	641.1	634.2	627.3	620.4	614.6	611.2
170°	640.0	636.5	635.4	634.2	633.1	628.5	625.0	619.2	614.6	611.2	608.9
172.5°	623.8	622.7	621.5	621.0	620.4	616.9	614.6	611.2	607.7	606.6	605.4
175°	612.3	611.2	611.2	610.6	610.0	608.9	607.7	604.3	603.1	602.0	603.1
177.5°	603.1	603.1	603.1	603.1	603.1	602.0	602.0	599.7	598.5	599.7	602.0
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2237.1	2229.5	2229.5	2224.9	2224.9	2200.5	2200.5	2208.1	2199.0	2188.3	2173.1
5°	2294.9	2278.2	2273.6	2267.5	2247.7	2217.3	2205.1	2200.5	2182.3	2159.4	2133.5
7.5°	2349.8	2322.4	2308.7	2294.9	2269.1	2226.4	2202.1	2185.3	2157.9	2122.9	2089.4
10°	2403.1	2368.0	2333.0	2316.3	2279.7	2226.4	2191.4	2164.0	2124.4	2077.2	2030.0
12.5°	2451.8	2378.7	2372.6	2339.1	2285.8	2224.9	2171.6	2132.0	2081.7	2026.9	1972.1
15°	2494.4	2419.8	2383.3	2352.8	2282.8	2206.6	2150.3	2101.5	2034.5	1972.1	1905.1
17.5°	2515.8	2435.1	2410.7	2360.4	2288.9	2189.9	2113.7	2054.3	1981.2	1906.6	1830.5
20°	2537.1	2442.7	2403.1	2368.0	2270.6	2157.9	2072.6	2004.1	1923.4	1835.0	1751.3
22.5°	2547.7	2442.7	2395.5	2346.7	2252.3	2122.9	2022.4	1941.6	1847.2	1757.4	1656.9
25°	2529.5	2433.5	2377.2	2326.9	2220.3	2080.2	1964.5	1873.1	1772.6	1670.6	1568.5
27.5°	2483.8	2412.2	2346.7	2294.9	2176.2	2025.4	1903.6	1800.0	1696.5	1582.3	1478.7
30°	2398.5	2366.5	2314.7	2256.9	2127.4	1976.7	1832.0	1725.4	1611.2	1497.0	1388.8
32.5°	2266.0	2293.4	2259.9	2209.7	2069.6	1909.7	1755.9	1647.7	1522.9	1399.5	1300.5
35°	2104.6	2202.1	2183.8	2148.8	2008.7	1838.1	1684.3	1553.3	1428.4	1303.6	1204.6
37.5°	1927.9	2075.7	2090.9	2069.6	1938.6	1765.0	1596.0	1468.0	1340.1	1213.7	1113.2
40°	1685.8	1912.7	1961.4	1970.6	1865.5	1676.7	1500.0	1375.1	1248.7	1125.4	1003.6
42.5°	1463.5	1749.8	1810.7	1848.8	1772.6	1589.9	1411.7	1273.1	1148.2	1037.1	915.2
45°	1254.8	1553.3	1652.3	1701.0	1667.5	1490.9	1306.6	1177.2	1063.0	960.9	843.7
47.5°	1040.1	1340.1	1478.7	1556.4	1556.4	1390.4	1206.1	1078.2	968.5	881.7	778.2
50°	897.0	1146.7	1289.9	1391.9	1419.3	1288.3	1114.7	989.9	886.3	791.9	712.7
52.5°	764.5	988.3	1107.1	1213.7	1292.9	1178.7	1012.7	900.0	798.0	709.7	647.2
55°	660.9	828.4	936.6	1053.8	1142.1	1067.5	913.7	804.1	715.7	642.6	589.3
57.5°	561.9	708.1	796.5	900.0	994.4	938.1	814.7	720.3	642.6	578.7	531.5
60°	478.2	597.0	665.5	746.2	863.5	823.9	721.8	635.0	572.6	514.7	475.1
62.5°	406.6	501.0	558.9	616.8	723.4	705.1	625.9	558.9	505.6	456.9	423.4
65°	333.5	411.2	456.9	507.1	592.4	600.0	536.0	488.8	440.1	397.5	367.0
67.5°	269.5	330.5	371.6	414.2	482.7	504.1	459.9	420.3	379.2	344.2	316.8
70°	217.8	260.4	290.9	324.4	380.7	406.6	383.8	356.3	322.8	293.9	269.5
72.5°	172.1	199.5	217.8	243.7	289.3	315.2	313.7	289.3	265.0	245.2	225.4
75°	126.4	147.7	162.9	179.7	216.2	240.6	246.7	236.0	211.7	196.4	181.2
77.5°	95.9	108.1	115.7	127.9	153.8	175.1	184.3	181.2	164.5	152.3	141.6
80°	73.1	76.1	79.2	83.8	105.1	124.9	131.0	129.4	120.3	115.7	103.6
82.5°	51.8	53.3	54.8	56.3	64.0	80.7	86.8	89.8	82.2	77.7	67.0
85°	30.5	32.0	32.0	35.0	36.5	41.1	51.8	51.8	50.3	44.2	42.6
87.5°	15.2	15.2	13.7	13.7	15.2	16.8	19.8	22.8	19.8	18.3	16.8
90°	23.0	17.3	15.6	13.8	11.5	9.2	4.6	1.2	4.6	9.2	11.5
92.5°	92.1	61.0	54.6	48.3	39.1	33.4	24.2	17.3	24.2	33.4	39.1
95°	165.7	112.8	99.0	85.2	66.8	56.4	44.9	40.3	44.9	56.4	66.8
97.5°	214.1	146.2	130.6	115.1	94.4	79.4	66.8	59.9	66.8	79.4	94.4
100°	237.1	176.1	160.0	143.9	120.9	102.4	92.1	88.6	92.1	102.4	120.9
102.5°	257.8	202.6	186.4	170.3	146.2	127.8	117.4	115.1	117.4	127.8	146.2
105°	282.0	227.9	211.8	195.7	170.3	153.1	145.0	140.4	145.0	153.1	170.3
107.5°	306.2	253.2	237.1	221.0	195.7	179.6	171.5	168.0	171.5	179.6	195.7
110°	330.3	279.7	263.0	246.3	222.1	207.2	200.3	195.7	200.3	207.2	222.1

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	353.4	305.0	287.8	270.5	247.5	233.7	225.6	221.0	225.6	233.7	247.5
115°	377.5	328.0	312.5	297.0	273.9	260.1	253.2	247.5	253.2	260.1	273.9
117.5°	399.4	353.4	337.2	321.1	299.3	286.6	279.7	275.1	279.7	286.6	299.3
120°	422.4	377.5	361.4	345.3	322.3	311.9	305.0	300.4	305.0	311.9	322.3
122.5°	444.3	402.9	386.2	369.5	346.5	334.9	328.0	324.6	328.0	334.9	346.5
125°	466.2	424.7	408.6	392.5	369.5	355.7	348.8	345.3	348.8	355.7	369.5
127.5°	486.9	446.6	429.9	413.2	391.3	376.4	367.2	362.6	367.2	376.4	391.3
130°	505.3	465.0	448.9	432.8	409.8	393.6	382.1	377.5	382.1	393.6	409.8
132.5°	521.4	483.4	467.3	451.2	427.0	409.8	397.1	391.3	397.1	409.8	427.0
135°	536.4	499.5	483.4	467.3	440.8	423.6	409.8	405.2	409.8	423.6	440.8
137.5°	549.0	512.2	497.2	482.3	455.8	437.4	423.6	417.8	423.6	437.4	455.8
140°	559.4	524.9	509.9	494.9	469.6	451.2	437.4	432.8	437.4	451.2	469.6
142.5°	567.4	534.1	520.2	506.4	482.3	463.9	451.2	447.7	451.2	463.9	482.3
145°	575.5	544.4	531.8	519.1	496.1	478.8	467.3	462.7	467.3	478.8	496.1
147.5°	582.4	552.5	541.0	529.5	509.9	493.8	482.3	478.8	482.3	493.8	509.9
150°	587.0	560.5	550.2	539.8	522.6	507.6	498.4	494.9	498.4	507.6	522.6
152.5°	591.6	568.6	559.4	550.2	534.1	521.4	512.2	511.0	512.2	521.4	534.1
155°	596.2	576.7	568.0	559.4	546.7	534.1	527.2	526.0	527.2	534.1	546.7
157.5°	599.7	582.4	574.9	567.4	557.1	545.6	539.8	538.7	539.8	545.6	557.1
160°	602.0	588.2	581.8	575.5	566.3	557.1	552.5	551.3	552.5	557.1	566.3
162.5°	603.1	591.6	587.0	582.4	574.4	567.4	562.8	564.0	562.8	567.4	574.4
165°	604.3	593.9	590.4	587.0	581.3	574.4	572.1	573.2	572.1	574.4	581.3
167.5°	604.3	596.2	593.9	591.6	587.0	582.4	580.1	581.3	580.1	582.4	587.0
170°	603.1	597.4	595.6	593.9	591.6	588.2	587.0	589.3	587.0	588.2	591.6
172.5°	602.0	598.5	597.4	596.2	595.1	591.6	592.8	593.9	592.8	591.6	595.1
175°	600.8	598.5	598.0	597.4	597.4	595.1	596.2	597.4	596.2	595.1	597.4
177.5°	599.7	598.5	598.5	598.5	598.5	596.2	597.4	599.7	597.4	596.2	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2167.0	2168.6	2173.1	2159.4	2138.1	2129.0	2101.5	2097.0	2092.4	2092.4	2097.0
5°	2118.3	2112.2	2113.7	2087.8	2057.4	2039.1	2001.0	2007.1	1987.3	1975.1	1978.2
7.5°	2065.0	2048.2	2046.7	2013.2	1975.1	1941.6	1902.1	1892.9	1874.6	1853.3	1844.2
10°	1998.0	1985.8	1963.0	1924.9	1876.2	1848.8	1795.5	1763.5	1758.9	1726.9	1714.7
12.5°	1929.5	1908.1	1885.3	1832.0	1777.2	1733.0	1693.4	1658.4	1634.0	1606.6	1588.3
15°	1850.3	1824.4	1798.5	1742.2	1678.2	1634.0	1574.6	1522.9	1451.3	1394.9	1363.0
17.5°	1763.5	1734.5	1699.5	1637.1	1574.6	1513.7	1404.1	1343.2	1292.9	1259.4	1239.6
20°	1673.6	1641.6	1606.6	1544.2	1436.1	1329.5	1268.5	1221.3	1190.9	1157.4	1133.0
22.5°	1579.2	1545.7	1507.6	1410.2	1296.0	1221.3	1174.1	1130.0	1085.8	1067.5	1055.3
25°	1490.9	1460.4	1411.7	1279.2	1189.4	1120.8	1067.5	1038.6	1015.7	991.4	968.5
27.5°	1399.5	1343.2	1274.6	1163.5	1107.1	1037.1	999.0	977.7	938.1	921.3	910.7
30°	1289.9	1227.4	1161.9	1082.8	1017.3	968.5	933.5	898.5	875.6	858.9	840.6
32.5°	1178.7	1119.3	1078.2	995.9	947.2	897.0	863.5	842.1	808.6	798.0	790.4
35°	1082.8	1032.5	995.9	928.9	883.3	837.6	813.2	781.2	759.9	740.1	727.9
37.5°	988.3	960.9	922.9	866.5	817.8	781.2	747.7	737.1	708.1	697.5	685.3
40°	922.9	881.7	849.8	801.0	759.9	720.3	699.0	674.6	654.8	638.1	633.5
42.5°	843.7	813.2	794.9	741.6	699.0	676.1	650.3	622.8	607.6	593.9	577.2
45°	784.3	756.9	731.0	688.3	650.3	621.3	598.5	580.2	554.3	548.2	522.3
47.5°	721.8	694.4	674.6	632.0	597.0	569.5	552.8	528.4	507.1	493.4	481.2
50°	659.4	636.6	618.3	581.7	551.3	522.3	499.5	475.1	466.0	443.2	435.5
52.5°	600.0	584.8	565.0	530.0	499.5	475.1	450.8	431.0	417.3	405.1	395.9
55°	549.8	525.4	516.2	478.2	452.3	426.4	405.1	392.9	376.1	368.5	360.9
57.5°	493.4	479.7	464.5	435.5	406.6	382.2	367.0	348.7	339.6	330.5	324.4
60°	444.7	424.9	412.7	388.3	362.4	339.6	325.9	312.2	300.0	292.4	280.2
62.5°	388.3	373.1	365.5	339.6	318.3	297.0	284.8	271.1	261.9	248.2	233.0
65°	339.6	327.4	318.3	297.0	277.2	257.4	245.2	228.4	216.2	208.6	207.1
67.5°	297.0	287.8	274.1	254.3	234.5	219.3	205.6	191.9	190.4	187.3	187.3
70°	249.7	240.6	233.0	211.7	194.9	178.2	175.1	170.6	166.0	164.5	161.4
72.5°	208.6	201.0	191.9	173.6	156.9	152.3	149.2	146.2	141.6	140.1	138.6
75°	169.0	158.4	152.3	135.5	131.0	127.9	124.9	120.3	117.3	115.7	112.7
77.5°	129.4	118.8	118.8	109.6	106.6	102.0	99.0	95.9	94.4	91.4	91.4
80°	91.4	91.4	88.3	83.8	79.2	77.7	73.1	71.6	70.1	71.6	68.5
82.5°	67.0	60.9	60.9	57.9	54.8	53.3	50.3	50.3	48.7	48.7	48.7
85°	38.1	38.1	36.5	33.5	32.0	32.0	30.5	30.5	28.9	28.9	27.4
87.5°	15.2	13.7	15.2	13.7	13.7	12.2	12.2	12.2	10.7	12.2	10.7
90°	13.8	15.6	17.3	23.0	31.1	38.0	39.1	38.0	36.8	34.5	36.8
92.5°	48.3	54.6	61.0	92.1	135.8	175.0	177.3	148.5	116.3	99.0	86.3
95°	85.2	99.0	112.8	165.7	265.9	399.4	451.2	394.8	301.6	231.4	183.0
97.5°	115.1	130.6	146.2	214.1	353.4	568.6	735.5	741.3	616.9	492.6	376.4
100°	143.9	160.0	176.1	237.1	377.5	626.2	909.3	1075.0	1050.9	908.1	750.5
102.5°	170.3	186.4	202.6	257.8	378.7	604.3	915.1	1199.4	1335.2	1330.6	1225.8
105°	195.7	211.8	227.9	282.0	384.4	574.4	852.9	1159.1	1398.5	1528.5	1543.5
107.5°	221.0	237.1	253.2	306.2	397.1	558.2	795.3	1073.9	1330.6	1523.9	1636.7
110°	246.3	263.0	279.7	330.3	413.2	553.6	756.2	994.5	1237.3	1443.4	1590.7

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	270.5	287.8	305.0	353.4	430.5	554.8	730.9	939.2	1152.2	1347.8	1507.8
115°	297.0	312.5	328.0	377.5	447.7	559.4	713.6	895.5	1085.4	1262.7	1413.4
117.5°	321.1	337.2	353.4	399.4	466.2	566.3	704.4	865.6	1030.2	1189.0	1329.4
120°	345.3	361.4	377.5	422.4	484.6	573.2	696.4	842.5	991.0	1133.7	1255.8
122.5°	369.5	386.2	402.9	444.3	500.7	581.3	691.8	823.0	959.9	1087.7	1201.7
125°	392.5	408.6	424.7	466.2	518.0	589.3	686.0	804.6	930.0	1048.6	1149.9
127.5°	413.2	429.9	446.6	486.9	534.1	597.4	682.6	787.3	900.1	1009.4	1106.1
130°	432.8	448.9	465.0	505.3	549.0	606.6	680.2	770.0	871.3	970.3	1061.2
132.5°	451.2	467.3	483.4	521.4	564.0	615.8	679.1	756.2	843.7	933.5	1015.2
135°	467.3	483.4	499.5	536.4	576.7	622.7	677.9	743.6	818.4	894.3	970.3
137.5°	482.3	497.2	512.2	549.0	587.0	629.6	677.9	734.3	797.7	863.3	925.4
140°	494.9	509.9	524.9	559.4	595.1	634.2	676.8	726.3	778.1	833.3	886.3
142.5°	506.4	520.2	534.1	567.4	602.0	637.7	676.8	718.2	762.0	806.9	850.6
145°	519.1	531.8	544.4	575.5	607.7	640.0	674.5	711.3	747.0	785.0	820.7
147.5°	529.5	541.0	552.5	582.4	611.2	641.1	671.0	704.4	735.5	766.6	795.3
150°	539.8	550.2	560.5	587.0	613.5	640.0	667.6	695.2	722.8	748.2	772.3
152.5°	550.2	559.4	568.6	591.6	614.6	637.7	661.8	687.2	710.2	733.2	752.8
155°	559.4	568.0	576.7	596.2	615.8	635.4	654.9	676.8	698.7	717.1	734.3
157.5°	567.4	574.9	582.4	599.7	615.8	630.8	648.0	667.6	684.9	701.0	715.9
160°	575.5	581.8	588.2	602.0	615.8	627.3	641.1	657.2	672.2	684.9	697.5
162.5°	582.4	587.0	591.6	603.1	614.6	623.8	635.4	648.0	659.5	669.9	680.2
165°	587.0	590.4	593.9	604.3	612.3	619.2	627.3	637.7	646.9	654.9	663.0
167.5°	591.6	593.9	596.2	604.3	611.2	614.6	620.4	627.3	634.2	641.1	646.9
170°	593.9	595.6	597.4	603.1	608.9	611.2	614.6	619.2	625.0	628.5	633.1
172.5°	596.2	597.4	598.5	602.0	605.4	606.6	607.7	611.2	614.6	616.9	620.4
175°	597.4	598.0	598.5	600.8	603.1	602.0	603.1	604.3	607.7	608.9	610.0
177.5°	598.5	598.5	598.5	599.7	602.0	599.7	598.5	599.7	602.0	602.0	603.1
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2097.0	2093.9	2084.8	2087.8	2083.3	2083.3	2080.2	2080.2	2080.2	2087.8	2083.3
5°	1982.8	1972.1	1961.4	1956.9	1952.3	1947.7	1947.7	1946.2	1959.9	1956.9	1969.1
7.5°	1841.1	1838.1	1816.8	1816.8	1809.2	1806.1	1813.7	1815.2	1816.8	1819.8	1827.4
10°	1714.7	1707.1	1676.7	1679.7	1675.1	1669.1	1673.6	1670.6	1681.2	1684.3	1681.2
12.5°	1565.5	1551.8	1518.3	1501.5	1483.3	1469.6	1486.3	1474.1	1516.8	1529.0	1562.5
15°	1367.5	1341.6	1318.8	1318.8	1302.0	1289.9	1297.5	1311.2	1320.3	1334.0	1340.1
17.5°	1235.0	1224.4	1206.1	1195.4	1190.9	1186.3	1186.3	1192.4	1212.2	1210.7	1222.9
20°	1122.3	1116.3	1107.1	1093.4	1088.8	1085.8	1085.8	1085.8	1099.5	1111.7	1119.3
22.5°	1044.7	1040.1	1034.0	1015.7	1006.6	1003.6	1011.2	1015.7	1026.4	1035.5	1043.2
25°	967.0	956.4	945.7	939.6	935.0	935.0	938.1	939.6	944.2	948.7	957.9
27.5°	903.1	895.4	880.2	863.5	863.5	858.9	861.9	865.0	875.6	890.9	898.5
30°	831.5	830.0	823.9	817.8	811.7	808.6	814.7	819.3	820.8	828.4	828.4
32.5°	779.7	769.0	758.4	752.3	749.2	747.7	749.2	755.3	755.3	764.5	775.1
35°	727.9	721.8	711.2	700.5	697.5	689.9	695.9	702.0	712.7	717.3	721.8
37.5°	671.6	664.0	659.4	656.4	650.3	651.8	647.2	656.4	665.5	664.0	667.0
40°	628.9	615.2	601.5	600.0	598.5	597.0	597.0	598.5	604.6	610.7	619.8
42.5°	574.1	569.5	557.4	545.2	542.1	539.1	536.0	542.1	554.3	565.0	569.5
45°	517.8	511.7	508.6	499.5	493.4	491.9	488.8	496.5	507.1	511.7	514.7
47.5°	466.0	464.5	455.3	456.9	452.3	453.8	452.3	456.9	456.9	461.4	464.5
50°	431.0	426.4	421.8	418.8	414.2	414.2	412.7	414.2	420.3	426.4	424.9
52.5°	395.9	388.3	386.8	385.3	382.2	385.3	380.7	382.2	388.3	391.4	389.9
55°	354.8	353.3	350.3	347.2	345.7	344.2	344.2	344.2	350.3	354.8	356.3
57.5°	322.8	315.2	309.1	309.1	303.0	301.5	304.6	306.1	310.7	313.7	316.8
60°	278.7	275.6	266.5	261.9	252.8	251.3	251.3	257.4	265.0	275.6	278.7
62.5°	231.5	226.9	225.4	225.4	225.4	225.4	225.4	225.4	225.4	226.9	226.9
65°	205.6	207.1	205.6	204.1	205.6	205.6	204.1	204.1	204.1	205.6	207.1
67.5°	184.3	182.7	184.3	182.7	181.2	181.2	179.7	181.2	182.7	184.3	184.3
70°	159.9	159.9	158.4	159.9	158.4	156.9	155.3	155.3	158.4	159.9	159.9
72.5°	137.1	137.1	135.5	135.5	132.5	132.5	134.0	132.5	132.5	137.1	137.1
75°	114.2	112.7	111.2	111.2	109.6	109.6	109.6	108.1	111.2	111.2	112.7
77.5°	89.8	89.8	89.8	88.3	88.3	86.8	86.8	88.3	88.3	88.3	89.8
80°	68.5	68.5	68.5	67.0	65.5	65.5	65.5	65.5	65.5	67.0	65.5
82.5°	47.2	47.2	47.2	47.2	47.2	45.7	45.7	45.7	47.2	47.2	45.7
85°	28.9	27.4	28.9	28.9	27.4	28.9	27.4	27.4	25.9	25.9	27.4
87.5°	12.2	10.7	9.1	9.1	10.7	9.1	9.1	9.1	10.7	9.1	9.1
90°	37.4	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.4
92.5°	81.7	77.1	76.0	71.4	72.5	70.2	72.5	71.4	76.0	77.1	81.7
95°	170.4	157.7	142.7	133.5	130.1	131.2	130.1	133.5	142.7	157.7	170.4
97.5°	341.8	307.3	262.4	239.4	226.7	219.8	226.7	239.4	262.4	307.3	341.8
100°	680.8	611.2	515.7	466.2	432.8	412.1	432.8	466.2	515.7	611.2	680.8
102.5°	1151.0	1076.2	970.3	877.1	833.3	803.4	833.3	877.1	970.3	1076.2	1151.0
105°	1524.5	1505.5	1434.2	1362.8	1313.3	1297.2	1313.3	1362.8	1434.2	1505.5	1524.5
107.5°	1659.8	1682.8	1681.6	1671.3	1656.3	1629.8	1656.3	1671.3	1681.6	1682.8	1659.8
110°	1637.9	1685.1	1734.6	1756.4	1766.8	1765.7	1766.8	1756.4	1734.6	1685.1	1637.9

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1563.6	1619.5	1693.1	1733.4	1755.3	1763.4	1755.3	1733.4	1693.1	1619.5	1563.6
115°	1472.7	1532.0	1613.7	1666.7	1696.6	1707.0	1696.6	1666.7	1613.7	1532.0	1472.7
117.5°	1385.8	1442.2	1526.2	1582.6	1613.7	1621.8	1613.7	1582.6	1526.2	1442.2	1385.8
120°	1308.2	1360.5	1441.1	1495.2	1528.5	1540.1	1528.5	1495.2	1441.1	1360.5	1308.2
122.5°	1247.7	1293.7	1363.9	1416.9	1445.7	1454.9	1445.7	1416.9	1363.9	1293.7	1247.7
125°	1193.1	1236.2	1302.9	1346.7	1375.5	1384.7	1375.5	1346.7	1302.9	1236.2	1193.1
127.5°	1146.4	1186.7	1245.4	1286.8	1312.2	1319.1	1312.2	1286.8	1245.4	1186.7	1146.4
130°	1099.2	1137.2	1193.6	1232.7	1255.8	1265.0	1255.8	1232.7	1193.6	1137.2	1099.2
132.5°	1050.3	1085.4	1140.7	1179.8	1200.5	1208.6	1200.5	1179.8	1140.7	1085.4	1050.3
135°	1002.6	1034.8	1084.3	1122.2	1143.0	1147.6	1143.0	1122.2	1084.3	1034.8	1002.6
137.5°	954.2	983.0	1030.2	1063.5	1082.0	1088.9	1082.0	1063.5	1030.2	983.0	954.2
140°	911.6	936.9	973.8	1003.7	1020.9	1027.9	1020.9	1003.7	973.8	936.9	911.6
142.5°	870.8	890.9	925.4	951.9	966.9	966.9	966.9	951.9	925.4	890.9	870.8
145°	837.4	854.1	881.7	901.2	912.8	916.2	912.8	901.2	881.7	854.1	837.4
147.5°	808.0	820.7	844.8	861.0	869.0	871.3	869.0	861.0	844.8	820.7	808.0
150°	782.6	793.0	810.3	824.1	831.0	832.2	831.0	824.1	810.3	793.0	782.6
152.5°	761.4	770.0	782.7	794.2	798.8	798.8	798.8	794.2	782.7	770.0	761.4
155°	740.6	747.0	759.7	767.7	772.3	770.0	772.3	767.7	759.7	747.0	740.6
157.5°	721.1	726.3	735.5	742.4	744.7	744.7	744.7	742.4	735.5	726.3	721.1
160°	701.6	705.6	713.6	719.4	720.5	720.5	720.5	719.4	713.6	705.6	701.6
162.5°	683.1	686.0	694.1	697.5	698.7	697.5	698.7	697.5	694.1	686.0	683.1
165°	665.3	667.6	672.2	676.8	676.8	675.6	676.8	676.8	672.2	667.6	665.3
167.5°	649.2	651.5	653.8	656.1	656.1	654.9	656.1	656.1	653.8	651.5	649.2
170°	634.2	635.4	636.5	640.0	638.8	636.5	638.8	640.0	636.5	635.4	634.2
172.5°	621.0	621.5	622.7	623.8	622.7	621.5	622.7	623.8	622.7	621.5	621.0
175°	610.6	611.2	611.2	612.3	611.2	608.9	611.2	612.3	611.2	611.2	610.6
177.5°	603.1	603.1	603.1	603.1	602.0	599.7	602.0	603.1	603.1	603.1	603.1
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2087.8	2095.5	2092.4	2075.7	2092.4	2097.0	2106.1	2115.3	2121.3	2130.5	2138.1
5°	1956.9	1972.1	1981.2	1972.1	2002.6	2007.1	2028.4	2040.6	2058.9	2074.1	2086.3
7.5°	1833.5	1845.7	1864.0	1867.0	1885.3	1906.6	1937.1	1967.5	1996.5	2011.7	2025.4
10°	1701.0	1722.4	1749.8	1743.7	1771.1	1804.6	1836.6	1885.3	1909.7	1937.1	1961.4
12.5°	1568.5	1582.3	1618.8	1631.0	1670.6	1696.5	1740.6	1771.1	1832.0	1864.0	1885.3
15°	1337.1	1393.4	1439.1	1493.9	1545.7	1594.4	1634.0	1688.9	1742.2	1766.5	1801.5
17.5°	1232.0	1257.9	1285.3	1312.7	1379.7	1466.5	1536.6	1596.0	1641.6	1673.6	1714.7
20°	1122.3	1148.2	1178.7	1204.6	1245.7	1308.1	1394.9	1497.0	1551.8	1585.3	1624.9
22.5°	1044.7	1069.0	1088.8	1111.7	1143.7	1189.4	1254.8	1381.2	1454.3	1495.4	1530.5
25°	960.9	991.4	1012.7	1029.5	1055.3	1105.6	1158.9	1230.5	1361.4	1393.4	1442.1
27.5°	903.1	912.2	936.6	962.4	988.3	1015.7	1070.6	1131.5	1219.8	1289.9	1349.3
30°	834.5	857.4	880.2	890.9	913.7	953.3	986.8	1052.3	1120.8	1175.6	1247.2
32.5°	782.7	796.5	811.7	837.6	858.9	886.3	919.8	974.6	1032.5	1067.5	1122.3
35°	724.9	734.0	766.0	776.7	798.0	825.4	858.9	901.5	964.0	991.4	1031.0
37.5°	670.1	691.4	700.5	724.9	744.7	772.1	796.5	845.2	886.3	918.3	954.8
40°	627.4	636.6	653.3	674.6	691.4	712.7	743.2	778.2	822.3	848.2	880.2
42.5°	575.6	583.3	604.6	616.8	644.2	664.0	682.2	724.9	764.5	784.3	816.3
45°	519.3	537.6	551.3	575.6	590.9	615.2	638.1	668.5	705.1	727.9	746.2
47.5°	470.6	488.8	502.5	525.4	549.8	560.4	584.8	616.8	650.3	668.5	694.4
50°	431.0	437.1	462.9	473.6	499.5	520.8	537.6	565.0	601.5	612.2	633.5
52.5°	392.9	397.5	414.2	427.9	450.8	469.0	490.4	516.2	546.7	563.5	580.2
55°	359.4	362.4	370.1	385.3	400.5	423.4	443.2	467.5	493.4	511.7	526.9
57.5°	321.3	327.4	333.5	342.6	357.9	379.2	400.5	423.4	444.7	456.9	476.7
60°	277.2	286.3	297.0	307.6	318.3	333.5	357.9	379.2	399.0	409.6	424.9
62.5°	230.0	248.2	257.4	269.5	278.7	292.4	310.7	335.0	348.7	362.4	374.6
65°	207.1	208.6	210.2	222.3	239.1	252.8	269.5	287.8	309.1	318.3	327.4
67.5°	184.3	185.8	188.8	190.4	196.4	211.7	230.0	249.7	266.5	272.6	281.7
70°	161.4	161.4	167.5	169.0	170.6	172.1	187.3	207.1	222.3	230.0	240.6
72.5°	137.1	138.6	141.6	143.1	146.2	149.2	153.8	164.5	182.7	190.4	202.5
75°	112.7	114.2	115.7	117.3	121.8	123.4	127.9	134.0	141.6	150.8	158.4
77.5°	89.8	89.8	91.4	94.4	97.5	99.0	103.6	106.6	109.6	114.2	120.3
80°	67.0	68.5	68.5	71.6	71.6	73.1	74.6	79.2	82.2	85.3	88.3
82.5°	45.7	48.7	48.7	48.7	50.3	51.8	53.3	53.3	56.3	57.9	62.4
85°	27.4	28.9	28.9	28.9	27.4	30.5	30.5	32.0	32.0	32.0	33.5
87.5°	10.7	9.1	10.7	10.7	10.7	12.2	10.7	10.7	12.2	13.7	13.7
90°	36.8	34.5	36.8	38.0	39.1	38.0	31.1	23.0	17.3	15.6	13.8
92.5°	86.3	99.0	116.3	148.5	177.3	175.0	135.8	92.1	61.0	54.6	48.3
95°	183.0	231.4	301.6	394.8	451.2	399.4	265.9	165.7	112.8	99.0	85.2
97.5°	376.4	492.6	616.9	741.3	735.5	568.6	353.4	214.1	146.2	130.6	115.1
100°	750.5	908.1	1050.9	1075.0	909.3	626.2	377.5	237.1	176.1	160.0	143.9
102.5°	1225.8	1330.6	1335.2	1199.4	915.1	604.3	378.7	257.8	202.6	186.4	170.3
105°	1543.5	1528.5	1398.5	1159.1	852.9	574.4	384.4	282.0	227.9	211.8	195.7
107.5°	1636.7	1523.9	1330.6	1073.9	795.3	558.2	397.1	306.2	253.2	237.1	221.0
110°	1590.7	1443.4	1237.3	994.5	756.2	553.6	413.2	330.3	279.7	263.0	246.3

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1507.8	1347.8	1152.2	939.2	730.9	554.8	430.5	353.4	305.0	287.8	270.5
115°	1413.4	1262.7	1085.4	895.5	713.6	559.4	447.7	377.5	328.0	312.5	297.0
117.5°	1329.4	1189.0	1030.2	865.6	704.4	566.3	466.2	399.4	353.4	337.2	321.1
120°	1255.8	1133.7	991.0	842.5	696.4	573.2	484.6	422.4	377.5	361.4	345.3
122.5°	1201.7	1087.7	959.9	823.0	691.8	581.3	500.7	444.3	402.9	386.2	369.5
125°	1149.9	1048.6	930.0	804.6	686.0	589.3	518.0	466.2	424.7	408.6	392.5
127.5°	1106.1	1009.4	900.1	787.3	682.6	597.4	534.1	486.9	446.6	429.9	413.2
130°	1061.2	970.3	871.3	770.0	680.2	606.6	549.0	505.3	465.0	448.9	432.8
132.5°	1015.2	933.5	843.7	756.2	679.1	615.8	564.0	521.4	483.4	467.3	451.2
135°	970.3	894.3	818.4	743.6	677.9	622.7	576.7	536.4	499.5	483.4	467.3
137.5°	925.4	863.3	797.7	734.3	677.9	629.6	587.0	549.0	512.2	497.2	482.3
140°	886.3	833.3	778.1	726.3	676.8	634.2	595.1	559.4	524.9	509.9	494.9
142.5°	850.6	806.9	762.0	718.2	676.8	637.7	602.0	567.4	534.1	520.2	506.4
145°	820.7	785.0	747.0	711.3	674.5	640.0	607.7	575.5	544.4	531.8	519.1
147.5°	795.3	766.6	735.5	704.4	671.0	641.1	611.2	582.4	552.5	541.0	529.5
150°	772.3	748.2	722.8	695.2	667.6	640.0	613.5	587.0	560.5	550.2	539.8
152.5°	752.8	733.2	710.2	687.2	661.8	637.7	614.6	591.6	568.6	559.4	550.2
155°	734.3	717.1	698.7	676.8	654.9	635.4	615.8	596.2	576.7	568.0	559.4
157.5°	715.9	701.0	684.9	667.6	648.0	630.8	615.8	599.7	582.4	574.9	567.4
160°	697.5	684.9	672.2	657.2	641.1	627.3	615.8	602.0	588.2	581.8	575.5
162.5°	680.2	669.9	659.5	648.0	635.4	623.8	614.6	603.1	591.6	587.0	582.4
165°	663.0	654.9	646.9	637.7	627.3	619.2	612.3	604.3	593.9	590.4	587.0
167.5°	646.9	641.1	634.2	627.3	620.4	614.6	611.2	604.3	596.2	593.9	591.6
170°	633.1	628.5	625.0	619.2	614.6	611.2	608.9	603.1	597.4	595.6	593.9
172.5°	620.4	616.9	614.6	611.2	607.7	606.6	605.4	602.0	598.5	597.4	596.2
175°	610.0	608.9	607.7	604.3	603.1	602.0	603.1	600.8	598.5	598.0	597.4
177.5°	603.1	602.0	602.0	599.7	598.5	599.7	602.0	599.7	598.5	598.5	598.5
180°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5

TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2191.4	2191.4	2191.4	2191.4
2.5°	2151.8	2147.2	2174.6	2205.1
5°	2107.6	2115.3	2150.3	2192.9
7.5°	2062.0	2078.7	2119.8	2176.2
10°	1998.0	2028.4	2090.9	2148.8
12.5°	1935.6	1976.7	2036.1	2104.6
15°	1865.5	1911.2	1984.3	2066.5
17.5°	1787.8	1839.6	1924.9	2014.7
20°	1705.6	1774.1	1864.0	1961.4
22.5°	1614.2	1696.5	1789.4	1897.5
25°	1525.9	1615.8	1708.6	1833.5
27.5°	1439.1	1527.4	1631.0	1757.4
30°	1352.3	1433.0	1544.2	1679.7
32.5°	1259.4	1343.2	1460.4	1599.0
35°	1174.1	1257.9	1367.5	1504.6
37.5°	1082.8	1172.6	1277.7	1419.3
40°	976.2	1081.2	1183.3	1318.8
42.5°	887.8	999.0	1098.0	1225.9
45°	817.8	922.9	1005.1	1130.0
47.5°	752.3	837.6	921.3	1037.1
50°	689.9	755.3	842.1	945.7
52.5°	625.9	682.2	756.9	854.3
55°	568.0	621.3	688.3	763.0
57.5°	514.7	552.8	619.8	686.8
60°	455.3	494.9	546.7	603.1
62.5°	405.1	435.5	484.3	531.5
65°	351.8	380.7	417.3	461.4
67.5°	303.0	328.9	357.9	392.9
70°	258.9	278.7	300.0	330.5
72.5°	211.7	233.0	252.8	277.2
75°	173.6	182.7	199.5	216.2
77.5°	134.0	146.2	155.3	169.0
80°	95.9	106.6	109.6	120.3
82.5°	64.0	70.1	76.1	79.2
85°	36.5	39.6	45.7	47.2
87.5°	13.7	15.2	18.3	21.3
90°	11.5	9.2	4.6	1.2
92.5°	39.1	33.4	24.2	17.3
95°	66.8	56.4	44.9	40.3
97.5°	94.4	79.4	66.8	59.9
100°	120.9	102.4	92.1	88.6
102.5°	146.2	127.8	117.4	115.1
105°	170.3	153.1	145.0	140.4
107.5°	195.7	179.6	171.5	168.0
110°	222.1	207.2	200.3	195.7



TEST NUMBER: P999271

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	247.5	233.7	225.6	221.0
115°	273.9	260.1	253.2	247.5
117.5°	299.3	286.6	279.7	275.1
120°	322.3	311.9	305.0	300.4
122.5°	346.5	334.9	328.0	324.6
125°	369.5	355.7	348.8	345.3
127.5°	391.3	376.4	367.2	362.6
130°	409.8	393.6	382.1	377.5
132.5°	427.0	409.8	397.1	391.3
135°	440.8	423.6	409.8	405.2
137.5°	455.8	437.4	423.6	417.8
140°	469.6	451.2	437.4	432.8
142.5°	482.3	463.9	451.2	447.7
145°	496.1	478.8	467.3	462.7
147.5°	509.9	493.8	482.3	478.8
150°	522.6	507.6	498.4	494.9
152.5°	534.1	521.4	512.2	511.0
155°	546.7	534.1	527.2	526.0
157.5°	557.1	545.6	539.8	538.7
160°	566.3	557.1	552.5	551.3
162.5°	574.4	567.4	562.8	564.0
165°	581.3	574.4	572.1	573.2
167.5°	587.0	582.4	580.1	581.3
170°	591.6	588.2	587.0	589.3
172.5°	595.1	591.6	592.8	593.9
175°	597.4	595.1	596.2	597.4
177.5°	598.5	596.2	597.4	599.7
180°	598.5	598.5	598.5	598.5

(END OF REPORT)