

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000131

Luminaire Tested: SA2XXRDIP-B865D330UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000131
REPORT IS A COMBINATION OF REPORTS P988691 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D330UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4153.0 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000131

CATALOG NUMBER: SA2XXRDIP-B865D330UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000131

CATALOG NUMBER: SA2XXRDIP-B865D330UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	56
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	49	46	43
5	74	62	54	48	70	59	52	47	54	48	44	49	44	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25
10	52	40	32	27	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22945	22945	22945
5°	22982	21828	21666
10°	22755	20703	20020
15°	22442	19374	18143
20°	22028	17863	16179
25°	21605	16312	14383
30°	21034	14804	12420
35°	20477	13280	10736
40°	19911	11786	9001
45°	19252	10242	7487
50°	18569	8753	6096
55°	17861	7265	4840
60°	17035	5811	3662
65°	16086	4429	2976
70°	14941	3214	2367
75°	13504	2450	1807
80°	11417	1660	1213
85°	7967	759	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19252 cd/sqm

TEST NUMBER: P1000131

CATALOG NUMBER: SA2XXRDIP-B865D330UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	3.3
10°-20°	372.9	9.0
20°-30°	523.6	12.6
30°-40°	570.7	13.7
40°-50°	524.5	12.6
50°-60°	412.0	9.9
60°-70°	268.1	6.5
70°-80°	138.0	3.3
80°-90°	36.5	0.9
90°-100°	25.9	0.6
100°-110°	82.3	2.0
110°-120°	140.9	3.4
120°-130°	185.3	4.5
130°-140°	208.0	5.0
140°-150°	204.0	4.9
150°-160°	171.1	4.1
160°-170°	113.5	2.7
170°-180°	39.7	1.0
0°-30°	1032.3	24.9
0°-40°	1603.1	38.6
0°-60°	2539.6	61.2
0°-90°	2982.2	71.8
90°-120°	249.2	6.0
90°-150°	846.5	20.4
90°-180°	1171.0	28.2
0°-180°	4153.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1450	1450	1450	1450	1450	
5°	1450	1443	1426	1438	1434	137
15°	1379	1364	1320	1295	1282	388
25°	1251	1209	1123	1069	1049	576
35°	1078	1011	896	813	784	675
45°	882	794	656	563	531	681
55°	670	568	426	348	323	599
65°	452	346	228	184	180	449
75°	241	150	105	96	94	255
85°	56	29	25	25	25	65
90°	0	5	12	12	12	4
95°	18	22	23	23	22	21
105°	76	77	78	78	78	80
115°	141	144	143	142	141	140
125°	206	209	208	207	206	184
135°	266	270	271	270	269	206
145°	323	326	328	328	326	202
155°	369	370	371	373	372	170
165°	402	402	402	404	402	113
175°	418	417	416	419	417	40
180°	419	419	419	419	419	

TEST NUMBER: P1000131

CATALOG NUMBER: SA2XXRDIP-B865D330UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1449.5	1449.5	1449.5	1449.5	1449.5
2.5°	1456.0	1449.5	1435.0	1448.1	1445.5
5°	1449.5	1442.9	1425.8	1437.7	1433.7
7.5°	1437.7	1429.8	1411.4	1416.7	1410.1
10°	1421.9	1412.7	1386.5	1382.6	1374.7
12.5°	1402.2	1390.4	1355.0	1347.1	1332.7
15°	1378.6	1364.2	1319.6	1294.7	1281.6
17.5°	1351.1	1330.1	1275.0	1246.1	1225.2
20°	1319.6	1293.4	1227.8	1195.0	1166.1
22.5°	1285.5	1255.3	1179.2	1134.6	1115.0
25°	1251.4	1209.4	1122.8	1069.1	1049.4
27.5°	1210.7	1166.1	1070.4	1008.7	978.5
30°	1167.4	1117.6	1012.7	945.8	910.3
32.5°	1125.5	1065.1	957.6	878.9	846.1
35°	1078.2	1011.3	895.9	813.3	784.4
37.5°	1032.3	960.2	838.2	747.7	714.9
40°	983.8	905.1	777.9	684.7	650.6
42.5°	934.0	850.0	717.5	620.4	587.7
45°	881.5	793.6	655.9	562.7	531.2
47.5°	831.6	738.5	596.8	503.7	474.8
50°	776.5	683.4	539.1	448.6	421.1
52.5°	722.8	624.4	484.0	397.5	372.5
55°	670.3	568.0	426.3	347.6	322.7
57.5°	616.5	511.6	375.2	301.7	280.7
60°	561.4	456.5	321.4	254.5	233.5
62.5°	507.6	402.7	275.5	212.5	202.0
65°	452.5	346.3	228.2	183.6	179.7
67.5°	400.1	293.8	183.6	161.3	157.4
70°	345.0	242.7	152.2	139.0	133.8
72.5°	292.5	195.4	127.2	116.7	114.1
75°	241.4	149.5	104.9	95.8	94.4
77.5°	190.2	106.2	82.6	77.4	74.8
80°	143.0	76.1	63.0	57.7	57.7
82.5°	99.7	51.2	43.3	40.7	40.7
85°	56.4	28.9	24.9	24.9	24.9
87.5°	21.0	10.5	10.5	9.2	9.2
90°	0.4	4.6	12.4	11.7	12.0
92.5°	7.8	10.6	11.0	11.3	11.3
95°	18.4	21.9	22.6	22.6	21.9
97.5°	30.7	33.9	35.3	35.3	35.3
100°	44.9	47.7	48.8	48.8	48.4
102.5°	59.7	61.8	63.3	63.6	63.3
105°	76.0	77.0	77.7	78.5	78.5
107.5°	92.2	93.6	93.6	94.0	92.2
110°	107.8	109.9	109.9	109.9	108.8



TEST NUMBER: P1000131

CATALOG NUMBER: SA2XXRDIP-B865D330UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	124.7	126.9	126.5	125.5	124.7
115°	141.4	143.5	142.8	142.4	141.4
117.5°	158.0	160.8	159.0	158.0	156.9
120°	174.6	177.4	174.6	174.6	173.5
122.5°	189.8	193.3	191.5	190.5	189.8
125°	205.7	208.9	207.8	206.7	206.4
127.5°	221.2	225.1	223.7	222.3	221.2
130°	235.7	240.3	239.6	238.9	237.5
132.5°	252.0	255.5	255.9	254.1	253.0
135°	266.1	270.0	270.7	270.3	269.3
137.5°	281.7	284.8	285.5	285.2	283.8
140°	295.4	298.6	300.4	300.4	299.0
142.5°	309.6	312.8	313.8	314.2	312.8
145°	323.0	325.5	327.6	328.0	326.5
147.5°	335.0	338.2	339.6	340.3	338.9
150°	347.4	349.5	350.9	352.0	350.9
152.5°	358.3	360.5	362.2	363.6	362.2
155°	369.3	370.4	371.4	373.2	372.1
157.5°	378.8	379.5	380.3	382.7	381.0
160°	387.3	388.0	388.4	390.5	389.1
162.5°	395.1	395.1	395.4	397.9	396.2
165°	401.8	401.5	401.5	403.9	402.2
167.5°	407.8	406.8	406.8	409.2	407.5
170°	412.4	411.4	411.0	413.5	411.4
172.5°	415.6	414.5	414.2	416.7	414.5
175°	418.1	417.0	416.3	418.8	416.7
177.5°	419.5	418.4	417.7	419.8	417.7
180°	418.8	418.8	418.8	418.8	418.8

(END OF REPORT)