

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999292

Luminaire Tested: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999292
REPORT IS A COMBINATION OF REPORTS P987841 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7702.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	99	94	91	88	91	87	84	82	74	72	70	62	60	59	51	50	49	49	49	44
2	90	83	78	73	83	77	72	68	66	62	59	55	53	51	46	44	42	42	42	38
3	83	74	67	62	76	69	63	58	59	54	51	50	46	44	41	39	37	37	37	33
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	37	35	33	33	33	29
5	70	59	52	46	65	55	49	44	48	43	39	41	37	34	34	31	29	29	29	26
6	65	54	46	41	60	50	43	38	44	38	34	37	33	30	31	28	26	26	26	23
7	61	49	41	36	56	46	39	34	40	34	31	34	30	27	29	26	24	24	24	21
8	56	45	37	32	52	42	35	31	37	31	28	32	27	24	27	24	21	21	21	19
9	53	41	34	29	49	38	32	28	34	29	25	29	25	22	25	22	20	20	20	18
10	49	38	31	26	46	36	29	25	31	26	23	27	23	20	23	20	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35136	35136	35136	35136
5°	35219	37321	35341	29815
10°	34832	39447	35078	24620
15°	34076	39460	34652	18497
20°	33166	32618	33887	15259
25°	32063	20381	32758	12981
30°	30656	13049	31490	11176
35°	28945	10028	29881	9564
40°	27037	8430	28191	8366
45°	24998	7174	26042	7022
50°	22907	6096	23978	6075
55°	20592	5297	21703	5228
60°	18538	4040	19518	3991
65°	16616	3041	17604	3448
70°	14495	2429	15634	2811
75°	12251	1860	13375	2126
80°	9732	1266	10467	1394
85°	6752	654	7402	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 32142 cd/sqm

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.5	2.7
10°-20°	587.7	7.6
20°-30°	756.4	9.8
30°-40°	717.5	9.3
40°-50°	615.0	8.0
50°-60°	468.3	6.1
60°-70°	295.3	3.8
70°-80°	147.3	1.9
80°-90°	41.8	0.5
90°-100°	85.5	1.1
100°-110°	271.7	3.5
110°-120°	464.8	6.0
120°-130°	611.3	7.9
130°-140°	686.2	8.9
140°-150°	672.9	8.7
150°-160°	564.5	7.3
160°-170°	374.4	4.9
170°-180°	130.8	1.7
0°-30°	1554.6	20.2
0°-40°	2272.1	29.5
0°-60°	3355.4	43.6
0°-90°	3839.9	49.9
90°-120°	822.0	10.7
90°-150°	2792.4	36.3
90°-180°	3862.0	50.1
0°-180°	7702.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2220	2220	2220	2220	2220	
5°	2221	2470	2229	1973	2221	211
15°	2093	2787	2129	1307	2093	589
25°	1857	1487	1897	947	1857	853
35°	1524	733	1573	699	1524	954
45°	1145	509	1192	498	1145	883
55°	773	353	814	349	773	696
65°	467	184	495	208	467	464
75°	219	97	239	111	219	237
85°	48	28	52	29	48	54
90°	1	40	1	40	1	7
95°	61	72	61	72	61	68
105°	251	259	251	259	251	265
115°	466	466	466	466	466	461
125°	678	681	678	681	678	606
135°	878	888	878	888	878	678
145°	1066	1077	1066	1077	1066	666
155°	1218	1228	1218	1228	1218	561
165°	1325	1327	1325	1327	1325	374
175°	1379	1374	1379	1374	1379	131
180°	1381	1381	1381	1381	1381	

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2233.6	2242.9	2247.5	2253.7	2267.6	2276.8	2290.7	2293.8	2292.2	2298.4	2281.5
5°	2221.3	2241.3	2259.9	2275.3	2300.0	2315.4	2332.4	2352.4	2357.0	2380.2	2366.3
7.5°	2204.3	2233.6	2259.9	2290.7	2327.7	2347.8	2374.0	2404.9	2418.7	2446.5	2454.2
10°	2176.6	2218.2	2262.9	2295.3	2346.2	2381.7	2406.4	2455.8	2488.2	2529.8	2523.6
12.5°	2131.8	2185.8	2246.0	2300.0	2366.3	2389.4	2435.7	2486.6	2528.3	2566.8	2600.8
15°	2093.3	2155.0	2221.3	2287.6	2363.2	2406.4	2452.7	2519.0	2563.7	2631.6	2660.9
17.5°	2040.8	2119.5	2198.2	2272.2	2361.7	2411.0	2468.1	2532.9	2599.2	2664.0	2687.1
20°	1986.8	2071.7	2156.5	2256.8	2358.6	2406.4	2465.0	2545.2	2610.0	2660.9	2660.9
22.5°	1922.0	2025.4	2122.6	2218.2	2329.3	2398.7	2458.8	2552.9	2599.2	2610.0	2568.4
25°	1857.2	1960.6	2067.0	2185.8	2312.3	2374.0	2441.9	2529.8	2545.2	2502.0	2394.1
27.5°	1780.1	1895.8	2016.1	2144.2	2276.8	2354.0	2415.7	2474.3	2445.0	2329.3	2161.1
30°	1701.4	1826.4	1962.1	2084.0	2244.4	2315.4	2367.8	2384.8	2292.2	2104.1	1886.6
32.5°	1619.7	1741.6	1885.0	2031.6	2193.5	2261.4	2295.3	2250.6	2080.9	1843.4	1578.0
35°	1524.1	1661.3	1811.0	1963.7	2124.1	2175.0	2195.1	2085.5	1868.0	1561.1	1297.3
37.5°	1437.7	1575.0	1735.4	1891.2	2047.0	2074.7	2054.7	1883.5	1607.4	1303.5	1045.9
40°	1335.9	1482.4	1639.7	1814.1	1942.1	1949.8	1900.4	1678.3	1335.9	1050.5	891.6
42.5°	1241.8	1389.8	1547.2	1724.6	1821.8	1795.5	1729.2	1437.7	1115.3	905.5	777.5
45°	1144.6	1285.0	1454.6	1612.0	1681.4	1619.7	1519.4	1209.4	936.3	779.0	680.3
47.5°	1050.5	1181.6	1349.7	1500.9	1513.3	1443.8	1325.1	1013.5	811.4	684.9	604.7
50°	957.9	1089.0	1246.4	1371.3	1359.0	1263.4	1129.2	880.8	705.0	604.7	538.4
52.5°	865.4	984.2	1136.9	1235.6	1183.1	1090.6	957.9	746.6	615.5	527.6	476.7
55°	772.8	883.9	1015.0	1096.8	1013.5	907.0	812.9	640.2	533.7	462.8	424.2
57.5°	695.7	783.6	903.9	953.3	853.0	769.7	688.0	550.7	462.8	411.9	367.1
60°	610.9	691.1	789.8	819.1	715.7	647.9	578.5	465.9	396.4	351.7	322.4
62.5°	538.4	604.7	680.3	680.3	589.3	538.4	485.9	390.3	333.2	297.7	283.8
65°	467.4	515.2	569.2	563.0	485.9	441.2	399.5	322.4	279.2	254.5	240.6
67.5°	398.0	435.0	470.5	448.9	393.4	354.8	316.2	260.7	231.4	214.4	195.9
70°	334.7	364.0	382.6	362.5	307.0	274.6	246.8	209.8	186.7	165.1	154.3
72.5°	280.7	293.1	299.3	274.6	228.3	209.8	189.7	163.5	143.5	132.7	129.6
75°	219.0	229.8	225.2	206.7	168.1	154.3	138.8	120.3	115.7	109.5	106.4
77.5°	171.2	171.2	163.5	146.5	120.3	109.5	103.4	94.1	89.5	87.9	84.8
80°	121.9	120.3	115.7	97.2	81.8	75.6	75.6	69.4	67.9	64.8	64.8
82.5°	80.2	80.2	74.0	58.6	54.0	52.4	50.9	47.8	47.8	46.3	46.3
85°	47.8	44.7	37.0	32.4	30.9	30.9	29.3	27.8	29.3	27.8	27.8
87.5°	21.6	17.0	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
90°	1.2	4.3	7.4	10.5	13.6	15.2	18.0	23.7	29.4	35.1	40.8
92.5°	25.6	27.7	29.8	31.9	34.0	35.0	35.1	35.4	35.6	35.9	36.1
95°	60.6	63.2	65.8	68.4	71.0	72.3	72.6	73.1	73.6	74.1	74.6
97.5°	101.4	103.7	106.1	108.4	110.7	111.9	112.4	113.5	114.5	115.6	116.6
100°	148.0	150.1	152.2	154.3	156.4	157.4	157.8	158.6	159.3	160.1	160.9
102.5°	197.0	198.6	200.1	201.7	203.2	204.0	204.5	205.6	206.6	207.7	208.7
105°	250.6	251.4	252.2	252.9	253.7	254.1	254.4	254.9	255.4	256.0	256.5
107.5°	304.3	305.3	306.3	307.4	308.4	308.9	308.9	308.9	308.9	308.9	308.9
110°	355.5	357.1	358.6	360.2	361.7	362.5	362.5	362.5	362.5	362.5	362.5

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	411.5	413.1	414.6	416.2	417.7	418.5	418.4	418.1	417.8	417.6	417.3
115°	466.3	467.9	469.4	471.0	472.5	473.3	473.0	472.5	472.0	471.5	471.0
117.5°	521.1	523.2	525.2	527.3	529.4	530.4	529.8	528.5	527.2	525.9	524.6
120°	575.9	578.0	580.0	582.1	584.2	585.2	584.2	582.1	580.0	578.0	575.9
122.5°	626.0	628.6	631.2	633.7	636.3	637.6	637.0	635.7	634.4	633.1	631.8
125°	678.4	680.7	683.1	685.4	687.7	688.9	688.5	687.7	687.0	686.2	685.4
127.5°	729.7	732.6	735.4	738.3	741.2	742.6	742.1	741.0	740.0	738.9	737.9
130°	777.5	780.9	784.3	787.6	791.0	792.7	792.4	791.9	791.4	790.9	790.4
132.5°	831.2	833.8	836.4	838.9	841.5	842.8	842.9	843.2	843.5	843.7	844.0
135°	877.8	880.6	883.5	886.3	889.2	890.6	890.9	891.4	891.9	892.4	892.9
137.5°	929.1	931.4	933.8	936.1	938.4	939.6	939.9	940.4	940.9	941.4	941.9
140°	974.5	976.8	979.2	981.5	983.8	985.0	985.7	987.0	988.3	989.6	990.9
142.5°	1021.2	1023.5	1025.9	1028.2	1030.5	1031.7	1032.1	1032.9	1033.6	1034.4	1035.2
145°	1065.5	1067.3	1069.1	1070.9	1072.7	1073.6	1074.4	1075.9	1077.5	1079.0	1080.6
147.5°	1105.1	1107.4	1109.8	1112.1	1114.4	1115.6	1116.1	1117.2	1118.2	1119.3	1120.3
150°	1145.9	1147.5	1149.0	1150.6	1152.1	1152.9	1153.4	1154.5	1155.5	1156.6	1157.6
152.5°	1182.0	1183.6	1185.1	1186.7	1188.2	1189.0	1189.7	1191.0	1192.3	1193.6	1194.9
155°	1218.2	1219.0	1219.8	1220.5	1221.3	1221.7	1222.1	1222.9	1223.6	1224.4	1225.2
157.5°	1249.7	1250.2	1250.7	1251.2	1251.7	1252.0	1252.3	1252.8	1253.3	1253.8	1254.3
160°	1277.6	1278.1	1278.7	1279.2	1279.7	1280.0	1280.1	1280.4	1280.6	1280.9	1281.1
162.5°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.4	1303.7	1303.9	1304.2	1304.4
165°	1325.4	1325.2	1324.9	1324.7	1324.4	1324.3	1324.3	1324.3	1324.3	1324.3	1324.3
167.5°	1345.2	1344.4	1343.6	1342.9	1342.1	1341.7	1341.7	1341.7	1341.7	1341.7	1341.7
170°	1360.4	1359.6	1358.8	1358.1	1357.3	1356.9	1356.8	1356.5	1356.2	1356.0	1355.7
172.5°	1370.9	1370.1	1369.3	1368.6	1367.8	1367.4	1367.3	1367.0	1366.7	1366.5	1366.2
175°	1379.0	1378.2	1377.4	1376.7	1375.9	1375.5	1375.2	1374.7	1374.2	1373.7	1373.2
177.5°	1383.7	1382.9	1382.1	1381.4	1380.6	1380.2	1379.9	1379.4	1378.9	1378.4	1377.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2298.4	2301.5	2306.1	2327.7	2330.8	2337.0	2333.9	2333.9	2335.4	2332.4	2333.9
5°	2397.1	2401.8	2424.9	2451.1	2457.3	2451.1	2458.8	2469.6	2469.6	2469.6	2466.6
7.5°	2489.7	2506.7	2532.9	2571.5	2579.2	2586.9	2600.8	2591.5	2594.6	2608.5	2603.8
10°	2579.2	2603.8	2633.2	2665.5	2682.5	2693.3	2699.5	2713.4	2745.8	2708.7	2722.6
12.5°	2664.0	2699.5	2730.3	2765.8	2778.2	2792.0	2796.7	2809.0	2809.0	2807.5	2818.3
15°	2719.5	2751.9	2779.7	2802.8	2805.9	2802.8	2799.8	2801.3	2805.9	2787.4	2798.2
17.5°	2731.9	2735.0	2744.2	2735.0	2736.5	2704.1	2685.6	2681.0	2637.8	2639.3	2674.8
20°	2671.7	2619.3	2605.4	2554.5	2523.6	2440.3	2437.2	2414.1	2323.1	2350.9	2344.7
22.5°	2506.7	2417.2	2298.4	2239.8	2210.5	2122.6	2054.7	2006.9	1974.5	1942.1	1928.2
25°	2289.2	2144.2	1976.0	1860.3	1843.4	1761.6	1636.7	1578.0	1508.6	1487.0	1524.1
27.5°	2008.4	1820.2	1630.5	1453.1	1420.7	1346.7	1283.4	1241.8	1161.5	1156.9	1160.0
30°	1627.4	1437.7	1278.8	1163.1	1082.9	1048.9	1007.3	976.4	944.0	956.4	959.5
32.5°	1337.4	1156.9	1008.8	947.1	910.1	888.5	853.0	833.0	819.1	814.5	812.9
35°	1062.8	942.5	876.2	816.0	794.4	779.0	752.8	743.5	731.2	732.7	732.7
37.5°	910.1	809.8	760.5	729.6	709.6	701.9	684.9	675.6	667.9	664.8	669.5
40°	785.2	715.7	684.9	657.1	640.2	637.1	627.8	617.0	607.8	609.3	613.9
42.5°	694.2	654.0	617.0	595.4	583.1	578.5	570.7	563.0	563.0	558.4	556.9
45°	621.7	589.3	558.4	538.4	530.6	524.5	515.2	513.7	507.5	509.0	510.6
47.5°	556.9	530.6	507.5	487.4	479.7	478.2	468.9	462.8	462.8	461.2	459.7
50°	498.2	472.0	452.0	441.2	430.4	427.3	425.7	424.2	421.1	421.1	422.7
52.5°	450.4	424.2	408.8	399.5	393.4	390.3	390.3	388.7	388.7	388.7	387.2
55°	398.0	376.4	364.0	361.0	357.9	356.3	354.8	351.7	350.2	353.2	350.2
57.5°	348.6	340.9	330.1	327.0	319.3	319.3	314.7	311.6	308.5	311.6	311.6
60°	310.1	299.3	293.1	283.8	277.7	271.5	263.8	262.2	259.2	257.6	256.1
62.5°	269.9	260.7	245.3	231.4	222.1	216.0	212.9	211.3	211.3	209.8	209.8
65°	225.2	203.6	195.9	191.3	189.7	188.2	185.1	183.6	185.1	183.6	185.1
67.5°	175.9	172.8	168.1	165.1	163.5	162.0	162.0	160.4	160.4	160.4	160.4
70°	152.7	145.0	143.5	140.4	140.4	138.8	138.8	138.8	138.8	137.3	140.4
72.5°	126.5	121.9	120.3	118.8	118.8	118.8	117.2	117.2	117.2	115.7	117.2
75°	103.4	101.8	98.7	98.7	97.2	98.7	97.2	97.2	95.6	97.2	97.2
77.5°	83.3	81.8	80.2	80.2	78.7	78.7	78.7	78.7	78.7	78.7	80.2
80°	63.2	61.7	60.2	61.7	60.2	61.7	60.2	60.2	61.7	60.2	60.2
82.5°	46.3	44.7	44.7	43.2	43.2	43.2	43.2	43.2	43.2	43.2	43.2
85°	27.8	26.2	26.2	27.8	26.2	27.8	26.2	26.2	26.2	27.8	27.8
87.5°	12.3	13.9	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	13.9
90°	40.3	39.8	39.3	38.8	38.5	38.6	38.9	39.1	39.4	39.6	39.4
92.5°	36.4	36.6	36.9	37.2	37.3	37.3	37.3	37.3	37.3	37.3	37.3
95°	74.6	74.6	74.6	74.6	74.6	74.3	73.8	73.3	72.8	72.3	72.8
97.5°	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6
100°	160.9	160.9	160.9	160.9	160.9	160.8	160.5	160.2	160.0	159.7	160.0
102.5°	208.9	209.2	209.4	209.7	209.8	209.7	209.4	209.2	208.9	208.7	208.9
105°	257.0	257.5	258.0	258.5	258.8	258.8	258.8	258.8	258.8	258.8	258.8
107.5°	309.2	309.4	309.7	310.0	310.1	309.5	308.2	306.9	305.6	304.3	305.6
110°	362.5	362.5	362.5	362.5	362.5	362.1	361.3	360.6	359.8	359.0	359.8

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	416.5	415.7	415.0	414.2	413.8	413.5	413.0	412.5	412.0	411.5	412.0
115°	470.7	470.5	470.2	469.9	469.8	469.4	468.6	467.9	467.1	466.3	467.1
117.5°	523.8	523.0	522.3	521.5	521.1	520.7	519.9	519.2	518.4	517.6	518.4
120°	575.9	575.9	575.9	575.9	575.9	575.5	574.7	574.0	573.2	572.4	573.2
122.5°	631.0	630.2	629.5	628.7	628.3	628.0	627.5	627.0	626.5	626.0	626.5
125°	684.6	683.8	683.1	682.3	681.9	681.8	681.5	681.3	681.0	680.8	681.0
127.5°	736.9	735.8	734.8	733.7	733.2	732.8	732.0	731.3	730.5	729.7	730.5
130°	789.9	789.3	788.8	788.3	788.0	787.5	786.5	785.4	784.4	783.4	784.4
132.5°	842.7	841.4	840.1	838.8	838.2	837.8	837.0	836.3	835.5	834.7	835.5
135°	892.7	892.4	892.2	891.9	891.8	891.4	890.6	889.9	889.1	888.3	889.1
137.5°	941.6	941.4	941.1	940.8	940.7	940.2	939.2	938.1	937.1	936.1	937.1
140°	990.9	990.9	990.9	990.9	990.9	990.4	989.3	988.3	987.2	986.2	987.2
142.5°	1035.4	1035.7	1035.9	1036.2	1036.3	1035.8	1034.8	1033.7	1032.7	1031.7	1032.7
145°	1080.9	1081.1	1081.4	1081.7	1081.8	1081.3	1080.2	1079.2	1078.1	1077.1	1078.1
147.5°	1120.8	1121.3	1121.8	1122.3	1122.6	1122.1	1121.0	1120.0	1118.9	1117.9	1118.9
150°	1158.4	1159.2	1159.9	1160.7	1161.1	1160.7	1159.9	1159.2	1158.4	1157.6	1158.4
152.5°	1195.9	1196.9	1198.0	1199.0	1199.5	1199.0	1198.0	1196.9	1195.9	1194.9	1195.9
155°	1226.5	1227.8	1229.1	1230.4	1231.0	1230.6	1229.8	1229.1	1228.3	1227.5	1228.3
157.5°	1256.1	1257.9	1259.8	1261.6	1262.5	1261.8	1260.5	1259.2	1257.9	1256.6	1257.9
160°	1282.7	1284.2	1285.8	1287.3	1288.1	1287.6	1286.6	1285.5	1284.5	1283.5	1284.5
162.5°	1306.2	1308.0	1309.9	1311.7	1312.6	1312.0	1310.7	1309.4	1308.1	1306.8	1308.1
165°	1326.1	1327.9	1329.7	1331.5	1332.4	1331.8	1330.5	1329.2	1327.9	1326.6	1327.9
167.5°	1343.5	1345.3	1347.2	1349.0	1349.9	1349.3	1348.0	1346.7	1345.4	1344.1	1345.4
170°	1357.5	1359.3	1361.2	1363.0	1363.9	1363.1	1361.6	1360.0	1358.5	1356.9	1358.5
172.5°	1368.0	1369.8	1371.7	1373.5	1374.4	1373.6	1372.1	1370.5	1369.0	1367.4	1369.0
175°	1375.0	1376.8	1378.7	1380.5	1381.4	1380.6	1379.1	1377.5	1376.0	1374.4	1376.0
177.5°	1379.5	1381.0	1382.6	1384.1	1384.9	1384.1	1382.6	1381.0	1379.5	1377.9	1379.5
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2340.1	2329.3	2326.2	2329.3	2326.2	2327.7	2316.9	2276.8	2287.6	2270.7	2279.9
5°	2472.7	2463.5	2443.4	2440.3	2437.2	2434.2	2418.7	2383.3	2369.4	2346.2	2344.7
7.5°	2599.2	2599.2	2583.8	2573.0	2559.1	2548.3	2528.3	2475.8	2454.2	2426.5	2411.0
10°	2724.2	2684.1	2701.0	2690.2	2656.3	2650.1	2613.1	2582.3	2540.6	2512.8	2488.2
12.5°	2813.6	2801.3	2785.9	2776.6	2767.4	2747.3	2722.6	2644.0	2622.4	2566.8	2539.1
15°	2810.5	2802.8	2807.5	2807.5	2804.4	2799.8	2779.7	2722.6	2685.6	2631.6	2583.8
17.5°	2659.4	2679.4	2699.5	2713.4	2744.2	2758.1	2776.6	2742.7	2719.5	2673.3	2622.4
20°	2395.6	2445.0	2503.6	2515.9	2543.7	2625.4	2662.5	2691.8	2701.0	2685.6	2644.0
22.5°	2028.5	2070.1	2212.0	2209.0	2249.1	2346.2	2454.2	2542.1	2611.6	2650.1	2634.7
25°	1588.8	1647.5	1723.0	1780.1	1911.2	2056.2	2190.4	2330.8	2451.1	2557.6	2583.8
27.5°	1201.7	1278.8	1338.9	1414.5	1480.9	1652.1	1824.9	2043.9	2184.3	2386.3	2491.2
30°	971.8	1007.3	1067.5	1102.9	1135.3	1266.4	1462.3	1678.3	1925.1	2158.0	2338.5
32.5°	829.9	854.6	899.3	914.7	948.7	1036.6	1160.0	1357.5	1612.0	1894.3	2131.8
35°	745.1	771.3	780.5	794.4	822.2	877.7	962.6	1106.0	1335.9	1612.0	1895.8
37.5°	672.6	686.4	712.7	721.9	731.2	772.8	829.9	930.2	1082.9	1309.6	1624.3
40°	621.7	629.4	643.2	651.0	657.1	686.4	737.3	805.2	917.8	1090.6	1380.6
42.5°	567.7	576.9	586.2	595.4	603.1	626.3	657.1	721.9	797.5	928.6	1138.4
45°	515.2	521.4	532.2	538.4	549.2	567.7	595.4	640.2	708.0	791.3	961.0
47.5°	467.4	475.1	479.7	487.4	495.2	515.2	541.4	570.7	626.3	708.0	831.4
50°	424.2	433.5	439.6	441.2	447.3	465.9	487.4	519.8	555.3	618.6	726.5
52.5°	393.4	394.9	399.5	405.7	404.2	414.9	435.0	459.7	496.7	547.6	626.3
55°	357.9	362.5	365.6	367.1	367.1	376.4	387.2	410.3	439.6	481.3	547.6
57.5°	313.1	317.8	327.0	330.1	334.7	339.4	344.0	359.4	384.1	424.2	478.2
60°	266.9	269.9	279.2	285.4	288.5	300.8	307.0	319.3	333.2	362.5	413.4
62.5°	214.4	217.5	222.1	228.3	234.5	253.0	268.4	280.7	291.5	311.6	353.2
65°	186.7	188.2	191.3	192.8	194.4	202.1	216.0	232.9	253.0	268.4	293.1
67.5°	162.0	163.5	165.1	168.1	169.7	171.2	177.4	182.0	202.1	223.7	242.2
70°	138.8	141.9	143.5	143.5	145.0	148.1	151.2	157.3	163.5	174.3	197.4
72.5°	117.2	118.8	121.9	121.9	121.9	124.9	128.0	131.1	134.2	140.4	149.6
75°	97.2	100.3	100.3	100.3	101.8	101.8	104.9	108.0	111.1	115.7	118.8
77.5°	80.2	80.2	80.2	80.2	81.8	81.8	83.3	86.4	87.9	89.5	92.6
80°	60.2	61.7	61.7	61.7	63.2	63.2	63.2	66.3	67.9	67.9	71.0
82.5°	44.7	44.7	44.7	46.3	44.7	46.3	46.3	47.8	46.3	47.8	49.4
85°	27.8	27.8	27.8	29.3	29.3	29.3	29.3	29.3	29.3	29.3	30.9
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	15.4	13.9	13.9
90°	39.1	38.9	38.6	38.5	38.8	39.3	39.8	40.3	40.8	35.1	29.4
92.5°	37.3	37.3	37.3	37.3	37.2	36.9	36.6	36.4	36.1	35.9	35.6
95°	73.3	73.8	74.3	74.6	74.6	74.6	74.6	74.6	74.6	74.1	73.6
97.5°	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	115.6	114.5
100°	160.2	160.5	160.8	160.9	160.9	160.9	160.9	160.9	160.9	160.1	159.3
102.5°	209.2	209.4	209.7	209.8	209.7	209.4	209.2	208.9	208.7	207.7	206.6
105°	258.8	258.8	258.8	258.8	258.5	258.0	257.5	257.0	256.5	256.0	255.4
107.5°	306.9	308.2	309.5	310.1	310.0	309.7	309.4	309.2	308.9	308.9	308.9
110°	360.6	361.3	362.1	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	412.5	413.0	413.5	413.8	414.2	415.0	415.7	416.5	417.3	417.6	417.8
115°	467.9	468.6	469.4	469.8	469.9	470.2	470.5	470.7	471.0	471.5	472.0
117.5°	519.2	519.9	520.7	521.1	521.5	522.3	523.0	523.8	524.6	525.9	527.2
120°	574.0	574.7	575.5	575.9	575.9	575.9	575.9	575.9	575.9	578.0	580.0
122.5°	627.0	627.5	628.0	628.3	628.7	629.5	630.2	631.0	631.8	633.1	634.4
125°	681.3	681.5	681.8	681.9	682.3	683.1	683.8	684.6	685.4	686.2	687.0
127.5°	731.3	732.0	732.8	733.2	733.7	734.8	735.8	736.9	737.9	738.9	740.0
130°	785.4	786.5	787.5	788.0	788.3	788.8	789.3	789.9	790.4	790.9	791.4
132.5°	836.3	837.0	837.8	838.2	838.8	840.1	841.4	842.7	844.0	843.7	843.5
135°	889.9	890.6	891.4	891.8	891.9	892.2	892.4	892.7	892.9	892.4	891.9
137.5°	938.1	939.2	940.2	940.7	940.8	941.1	941.4	941.6	941.9	941.4	940.9
140°	988.3	989.3	990.4	990.9	990.9	990.9	990.9	990.9	990.9	989.6	988.3
142.5°	1033.7	1034.8	1035.8	1036.3	1036.2	1035.9	1035.7	1035.4	1035.2	1034.4	1033.6
145°	1079.2	1080.2	1081.3	1081.8	1081.7	1081.4	1081.1	1080.9	1080.6	1079.0	1077.5
147.5°	1120.0	1121.0	1122.1	1122.6	1122.3	1121.8	1121.3	1120.8	1120.3	1119.3	1118.2
150°	1159.2	1159.9	1160.7	1161.1	1160.7	1159.9	1159.2	1158.4	1157.6	1156.6	1155.5
152.5°	1196.9	1198.0	1199.0	1199.5	1199.0	1198.0	1196.9	1195.9	1194.9	1193.6	1192.3
155°	1229.1	1229.8	1230.6	1231.0	1230.4	1229.1	1227.8	1226.5	1225.2	1224.4	1223.6
157.5°	1259.2	1260.5	1261.8	1262.5	1261.6	1259.8	1257.9	1256.1	1254.3	1253.8	1253.3
160°	1285.5	1286.6	1287.6	1288.1	1287.3	1285.8	1284.2	1282.7	1281.1	1280.9	1280.6
162.5°	1309.4	1310.7	1312.0	1312.6	1311.7	1309.9	1308.0	1306.2	1304.4	1304.2	1303.9
165°	1329.2	1330.5	1331.8	1332.4	1331.5	1329.7	1327.9	1326.1	1324.3	1324.3	1324.3
167.5°	1346.7	1348.0	1349.3	1349.9	1349.0	1347.2	1345.3	1343.5	1341.7	1341.7	1341.7
170°	1360.0	1361.6	1363.1	1363.9	1363.0	1361.2	1359.3	1357.5	1355.7	1356.0	1356.2
172.5°	1370.5	1372.1	1373.6	1374.4	1373.5	1371.7	1369.8	1368.0	1366.2	1366.5	1366.7
175°	1377.5	1379.1	1380.6	1381.4	1380.5	1378.7	1376.8	1375.0	1373.2	1373.7	1374.2
177.5°	1381.0	1382.6	1384.1	1384.9	1384.1	1382.6	1381.0	1379.5	1377.9	1378.4	1378.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2266.0	2258.3	2258.3	2253.7	2253.7	2229.0	2229.0	2236.7	2227.5	2216.7	2201.2
5°	2324.6	2307.7	2303.0	2296.9	2276.8	2246.0	2233.6	2229.0	2210.5	2187.4	2161.1
7.5°	2380.2	2352.4	2338.5	2324.6	2298.4	2255.2	2230.5	2213.6	2185.8	2150.3	2116.4
10°	2434.2	2398.7	2363.2	2346.2	2309.2	2255.2	2219.7	2192.0	2151.9	2104.1	2056.2
12.5°	2483.5	2409.5	2403.3	2369.4	2315.4	2253.7	2199.7	2159.6	2108.7	2053.2	1997.6
15°	2526.7	2451.1	2414.1	2383.3	2312.3	2235.2	2178.1	2128.7	2060.9	1997.6	1929.7
17.5°	2548.3	2466.6	2441.9	2391.0	2318.5	2218.2	2141.1	2080.9	2006.9	1931.3	1854.2
20°	2569.9	2474.3	2434.2	2398.7	2300.0	2185.8	2099.4	2030.0	1948.3	1858.8	1773.9
22.5°	2580.7	2474.3	2426.5	2377.1	2281.5	2150.3	2048.5	1966.8	1871.1	1780.1	1678.3
25°	2562.2	2465.0	2407.9	2357.0	2249.1	2107.1	1989.9	1897.4	1795.5	1692.2	1588.8
27.5°	2515.9	2443.4	2377.1	2324.6	2204.3	2051.6	1928.2	1823.3	1718.4	1602.7	1497.8
30°	2429.5	2397.1	2344.7	2286.1	2155.0	2002.2	1855.7	1747.7	1632.0	1516.3	1406.8
32.5°	2295.3	2323.1	2289.2	2238.3	2096.3	1934.4	1778.6	1669.1	1542.6	1417.6	1317.3
35°	2131.8	2230.5	2212.0	2176.6	2034.6	1861.9	1706.1	1573.4	1446.9	1320.4	1220.2
37.5°	1952.9	2102.5	2117.9	2096.3	1963.7	1787.8	1616.6	1487.0	1357.5	1229.4	1127.6
40°	1707.6	1937.5	1986.8	1996.1	1889.6	1698.4	1519.4	1392.9	1264.9	1140.0	1016.5
42.5°	1482.4	1772.4	1834.1	1872.7	1795.5	1610.4	1430.0	1289.6	1163.1	1050.5	927.1
45°	1271.1	1573.4	1673.7	1723.0	1689.1	1510.2	1323.5	1192.4	1076.7	973.4	854.6
47.5°	1053.6	1357.5	1497.8	1576.5	1576.5	1408.4	1221.7	1092.1	981.1	893.1	788.2
50°	908.6	1161.5	1306.6	1409.9	1437.7	1305.0	1129.2	1002.7	897.8	802.1	721.9
52.5°	774.4	1001.1	1121.4	1229.4	1309.6	1193.9	1025.8	911.7	808.3	718.8	655.6
55°	669.5	839.2	948.7	1067.5	1156.9	1081.3	925.5	814.5	725.0	651.0	597.0
57.5°	569.2	717.3	806.8	911.7	1007.3	950.2	825.3	729.6	651.0	586.2	538.4
60°	484.4	604.7	674.1	755.9	874.6	834.5	731.2	643.2	580.0	521.4	481.3
62.5°	411.9	507.5	566.1	624.7	732.7	714.2	634.0	566.1	512.1	462.8	428.8
65°	337.8	416.5	462.8	513.7	600.1	607.8	543.0	495.2	445.8	402.6	371.8
67.5°	273.0	334.7	376.4	419.6	489.0	510.6	465.9	425.7	384.1	348.6	320.9
70°	220.6	263.8	294.6	328.6	385.6	411.9	388.7	361.0	327.0	297.7	273.0
72.5°	174.3	202.1	220.6	246.8	293.1	319.3	317.8	293.1	268.4	248.4	228.3
75°	128.0	149.6	165.1	182.0	219.0	243.7	249.9	239.1	214.4	199.0	183.6
77.5°	97.2	109.5	117.2	129.6	155.8	177.4	186.7	183.6	166.6	154.3	143.5
80°	74.0	77.1	80.2	84.8	106.4	126.5	132.7	131.1	121.9	117.2	104.9
82.5°	52.4	54.0	55.5	57.1	64.8	81.8	87.9	91.0	83.3	78.7	67.9
85°	30.9	32.4	32.4	35.5	37.0	41.6	52.4	52.4	50.9	44.7	43.2
87.5°	15.4	15.4	13.9	13.9	15.4	17.0	20.1	23.1	20.1	18.5	17.0
90°	23.7	18.0	15.2	13.6	10.5	7.4	4.3	1.2	4.3	7.4	10.5
92.5°	35.4	35.1	35.0	34.0	31.9	29.8	27.7	25.6	27.7	29.8	31.9
95°	73.1	72.6	72.3	71.0	68.4	65.8	63.2	60.6	63.2	65.8	68.4
97.5°	113.5	112.4	111.9	110.7	108.4	106.1	103.7	101.4	103.7	106.1	108.4
100°	158.6	157.8	157.4	156.4	154.3	152.2	150.1	148.0	150.1	152.2	154.3
102.5°	205.6	204.5	204.0	203.2	201.7	200.1	198.6	197.0	198.6	200.1	201.7
105°	254.9	254.4	254.1	253.7	252.9	252.2	251.4	250.6	251.4	252.2	252.9
107.5°	308.9	308.9	308.9	308.4	307.4	306.3	305.3	304.3	305.3	306.3	307.4
110°	362.5	362.5	362.5	361.7	360.2	358.6	357.1	355.5	357.1	358.6	360.2

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	418.1	418.4	418.5	417.7	416.2	414.6	413.1	411.5	413.1	414.6	416.2
115°	472.5	473.0	473.3	472.5	471.0	469.4	467.9	466.3	467.9	469.4	471.0
117.5°	528.5	529.8	530.4	529.4	527.3	525.2	523.2	521.1	523.2	525.2	527.3
120°	582.1	584.2	585.2	584.2	582.1	580.0	578.0	575.9	578.0	580.0	582.1
122.5°	635.7	637.0	637.6	636.3	633.7	631.2	628.6	626.0	628.6	631.2	633.7
125°	687.7	688.5	688.9	687.7	685.4	683.1	680.7	678.4	680.7	683.1	685.4
127.5°	741.0	742.1	742.6	741.2	738.3	735.4	732.6	729.7	732.6	735.4	738.3
130°	791.9	792.4	792.7	791.0	787.6	784.3	780.9	777.5	780.9	784.3	787.6
132.5°	843.2	842.9	842.8	841.5	838.9	836.4	833.8	831.2	833.8	836.4	838.9
135°	891.4	890.9	890.6	889.2	886.3	883.5	880.6	877.8	880.6	883.5	886.3
137.5°	940.4	939.9	939.6	938.4	936.1	933.8	931.4	929.1	931.4	933.8	936.1
140°	987.0	985.7	985.0	983.8	981.5	979.2	976.8	974.5	976.8	979.2	981.5
142.5°	1032.9	1032.1	1031.7	1030.5	1028.2	1025.9	1023.5	1021.2	1023.5	1025.9	1028.2
145°	1075.9	1074.4	1073.6	1072.7	1070.9	1069.1	1067.3	1065.5	1067.3	1069.1	1070.9
147.5°	1117.2	1116.1	1115.6	1114.4	1112.1	1109.8	1107.4	1105.1	1107.4	1109.8	1112.1
150°	1154.5	1153.4	1152.9	1152.1	1150.6	1149.0	1147.5	1145.9	1147.5	1149.0	1150.6
152.5°	1191.0	1189.7	1189.0	1188.2	1186.7	1185.1	1183.6	1182.0	1183.6	1185.1	1186.7
155°	1222.9	1222.1	1221.7	1221.3	1220.5	1219.8	1219.0	1218.2	1219.0	1219.8	1220.5
157.5°	1252.8	1252.3	1252.0	1251.7	1251.2	1250.7	1250.2	1249.7	1250.2	1250.7	1251.2
160°	1280.4	1280.1	1280.0	1279.7	1279.2	1278.7	1278.1	1277.6	1278.1	1278.7	1279.2
162.5°	1303.7	1303.4	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3
165°	1324.3	1324.3	1324.3	1324.4	1324.7	1324.9	1325.2	1325.4	1325.2	1324.9	1324.7
167.5°	1341.7	1341.7	1341.7	1342.1	1342.9	1343.6	1344.4	1345.2	1344.4	1343.6	1342.9
170°	1356.5	1356.8	1356.9	1357.3	1358.1	1358.8	1359.6	1360.4	1359.6	1358.8	1358.1
172.5°	1367.0	1367.3	1367.4	1367.8	1368.6	1369.3	1370.1	1370.9	1370.1	1369.3	1368.6
175°	1374.7	1375.2	1375.5	1375.9	1376.7	1377.4	1378.2	1379.0	1378.2	1377.4	1376.7
177.5°	1379.4	1379.9	1380.2	1380.6	1381.4	1382.1	1382.9	1383.7	1382.9	1382.1	1381.4
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2195.1	2196.6	2201.2	2187.4	2165.8	2156.5	2128.7	2124.1	2119.5	2119.5	2124.1
5°	2145.7	2139.5	2141.1	2114.9	2084.0	2065.5	2026.9	2033.1	2013.0	2000.7	2003.8
7.5°	2091.7	2074.7	2073.2	2039.3	2000.7	1966.8	1926.7	1917.4	1898.9	1877.3	1868.0
10°	2023.8	2011.5	1988.4	1949.8	1900.4	1872.7	1818.7	1786.3	1781.7	1749.3	1736.9
12.5°	1954.4	1932.8	1909.7	1855.7	1800.2	1755.4	1715.3	1679.9	1655.2	1627.4	1608.9
15°	1874.2	1848.0	1821.8	1764.7	1699.9	1655.2	1595.0	1542.6	1470.1	1413.0	1380.6
17.5°	1786.3	1757.0	1721.5	1658.3	1595.0	1533.3	1422.2	1360.5	1309.6	1275.7	1255.6
20°	1695.3	1662.9	1627.4	1564.2	1454.6	1346.7	1285.0	1237.1	1206.3	1172.3	1147.7
22.5°	1599.6	1565.7	1527.1	1428.4	1312.7	1237.1	1189.3	1144.6	1099.8	1081.3	1069.0
25°	1510.2	1479.3	1430.0	1295.8	1204.7	1135.3	1081.3	1052.0	1028.9	1004.2	981.1
27.5°	1417.6	1360.5	1291.1	1178.5	1121.4	1050.5	1011.9	990.3	950.2	933.3	922.5
30°	1306.6	1243.3	1177.0	1096.8	1030.4	981.1	945.6	910.1	887.0	870.0	851.5
32.5°	1193.9	1133.8	1092.1	1008.8	959.5	908.6	874.6	853.0	819.1	808.3	800.6
35°	1096.8	1045.9	1008.8	941.0	894.7	848.4	823.7	791.3	769.7	749.7	737.3
37.5°	1001.1	973.4	934.8	877.7	828.4	791.3	757.4	746.6	717.3	706.5	694.2
40°	934.8	893.1	860.8	811.4	769.7	729.6	708.0	683.4	663.3	646.3	641.7
42.5°	854.6	823.7	805.2	751.2	708.0	684.9	658.7	630.9	615.5	601.6	584.6
45°	794.4	766.7	740.4	697.2	658.7	629.4	606.2	587.7	561.5	555.3	529.1
47.5°	731.2	703.4	683.4	640.2	604.7	576.9	560.0	535.3	513.7	499.8	487.4
50°	667.9	644.8	626.3	589.3	558.4	529.1	506.0	481.3	472.0	448.9	441.2
52.5°	607.8	592.3	572.3	536.8	506.0	481.3	456.6	436.5	422.7	410.3	401.1
55°	556.9	532.2	522.9	484.4	458.1	431.9	410.3	398.0	381.0	373.3	365.6
57.5°	499.8	485.9	470.5	441.2	411.9	387.2	371.8	353.2	344.0	334.7	328.6
60°	450.4	430.4	418.0	393.4	367.1	344.0	330.1	316.2	303.9	296.2	283.8
62.5°	393.4	377.9	370.2	344.0	322.4	300.8	288.5	274.6	265.3	251.4	236.0
65°	344.0	331.7	322.4	300.8	280.7	260.7	248.4	231.4	219.0	211.3	209.8
67.5°	300.8	291.5	277.7	257.6	237.6	222.1	208.2	194.4	192.8	189.7	189.7
70°	253.0	243.7	236.0	214.4	197.4	180.5	177.4	172.8	168.1	166.6	163.5
72.5°	211.3	203.6	194.4	175.9	158.9	154.3	151.2	148.1	143.5	141.9	140.4
75°	171.2	160.4	154.3	137.3	132.7	129.6	126.5	121.9	118.8	117.2	114.1
77.5°	131.1	120.3	120.3	111.1	108.0	103.4	100.3	97.2	95.6	92.6	92.6
80°	92.6	92.6	89.5	84.8	80.2	78.7	74.0	72.5	71.0	72.5	69.4
82.5°	67.9	61.7	61.7	58.6	55.5	54.0	50.9	50.9	49.4	49.4	49.4
85°	38.6	38.6	37.0	33.9	32.4	32.4	30.9	30.9	29.3	29.3	27.8
87.5°	15.4	13.9	15.4	13.9	13.9	12.3	12.3	12.3	10.8	12.3	10.8
90°	13.6	15.2	18.0	23.7	29.4	35.1	40.8	40.3	39.8	39.3	38.8
92.5°	34.0	35.0	35.1	35.4	35.6	35.9	36.1	36.4	36.6	36.9	37.2
95°	71.0	72.3	72.6	73.1	73.6	74.1	74.6	74.6	74.6	74.6	74.6
97.5°	110.7	111.9	112.4	113.5	114.5	115.6	116.6	116.6	116.6	116.6	116.6
100°	156.4	157.4	157.8	158.6	159.3	160.1	160.9	160.9	160.9	160.9	160.9
102.5°	203.2	204.0	204.5	205.6	206.6	207.7	208.7	208.9	209.2	209.4	209.7
105°	253.7	254.1	254.4	254.9	255.4	256.0	256.5	257.0	257.5	258.0	258.5
107.5°	308.4	308.9	308.9	308.9	308.9	308.9	308.9	309.2	309.4	309.7	310.0
110°	361.7	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	417.7	418.5	418.4	418.1	417.8	417.6	417.3	416.5	415.7	415.0	414.2
115°	472.5	473.3	473.0	472.5	472.0	471.5	471.0	470.7	470.5	470.2	469.9
117.5°	529.4	530.4	529.8	528.5	527.2	525.9	524.6	523.8	523.0	522.3	521.5
120°	584.2	585.2	584.2	582.1	580.0	578.0	575.9	575.9	575.9	575.9	575.9
122.5°	636.3	637.6	637.0	635.7	634.4	633.1	631.8	631.0	630.2	629.5	628.7
125°	687.7	688.9	688.5	687.7	687.0	686.2	685.4	684.6	683.8	683.1	682.3
127.5°	741.2	742.6	742.1	741.0	740.0	738.9	737.9	736.9	735.8	734.8	733.7
130°	791.0	792.7	792.4	791.9	791.4	790.9	790.4	789.9	789.3	788.8	788.3
132.5°	841.5	842.8	842.9	843.2	843.5	843.7	844.0	842.7	841.4	840.1	838.8
135°	889.2	890.6	890.9	891.4	891.9	892.4	892.9	892.7	892.4	892.2	891.9
137.5°	938.4	939.6	939.9	940.4	940.9	941.4	941.9	941.6	941.4	941.1	940.8
140°	983.8	985.0	985.7	987.0	988.3	989.6	990.9	990.9	990.9	990.9	990.9
142.5°	1030.5	1031.7	1032.1	1032.9	1033.6	1034.4	1035.2	1035.4	1035.7	1035.9	1036.2
145°	1072.7	1073.6	1074.4	1075.9	1077.5	1079.0	1080.6	1080.9	1081.1	1081.4	1081.7
147.5°	1114.4	1115.6	1116.1	1117.2	1118.2	1119.3	1120.3	1120.8	1121.3	1121.8	1122.3
150°	1152.1	1152.9	1153.4	1154.5	1155.5	1156.6	1157.6	1158.4	1159.2	1159.9	1160.7
152.5°	1188.2	1189.0	1189.7	1191.0	1192.3	1193.6	1194.9	1195.9	1196.9	1198.0	1199.0
155°	1221.3	1221.7	1222.1	1222.9	1223.6	1224.4	1225.2	1226.5	1227.8	1229.1	1230.4
157.5°	1251.7	1252.0	1252.3	1252.8	1253.3	1253.8	1254.3	1256.1	1257.9	1259.8	1261.6
160°	1279.7	1280.0	1280.1	1280.4	1280.6	1280.9	1281.1	1282.7	1284.2	1285.8	1287.3
162.5°	1303.3	1303.3	1303.4	1303.7	1303.9	1304.2	1304.4	1306.2	1308.0	1309.9	1311.7
165°	1324.4	1324.3	1324.3	1324.3	1324.3	1324.3	1324.3	1326.1	1327.9	1329.7	1331.5
167.5°	1342.1	1341.7	1341.7	1341.7	1341.7	1341.7	1341.7	1343.5	1345.3	1347.2	1349.0
170°	1357.3	1356.9	1356.8	1356.5	1356.2	1356.0	1355.7	1357.5	1359.3	1361.2	1363.0
172.5°	1367.8	1367.4	1367.3	1367.0	1366.7	1366.5	1366.2	1368.0	1369.8	1371.7	1373.5
175°	1375.9	1375.5	1375.2	1374.7	1374.2	1373.7	1373.2	1375.0	1376.8	1378.7	1380.5
177.5°	1380.6	1380.2	1379.9	1379.4	1378.9	1378.4	1377.9	1379.5	1381.0	1382.6	1384.1
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2124.1	2121.0	2111.8	2114.9	2110.2	2110.2	2107.1	2107.1	2107.1	2114.9	2110.2
5°	2008.4	1997.6	1986.8	1982.2	1977.6	1972.9	1972.9	1971.4	1985.3	1982.2	1994.5
7.5°	1865.0	1861.9	1840.3	1840.3	1832.6	1829.5	1837.2	1838.7	1840.3	1843.4	1851.1
10°	1736.9	1729.2	1698.4	1701.4	1696.8	1690.6	1695.3	1692.2	1703.0	1706.1	1703.0
12.5°	1585.8	1571.9	1537.9	1521.0	1502.5	1488.6	1505.5	1493.2	1536.4	1548.7	1582.7
15°	1385.2	1359.0	1335.9	1335.9	1318.9	1306.6	1314.3	1328.1	1337.4	1351.3	1357.5
17.5°	1251.0	1240.2	1221.7	1210.9	1206.3	1201.7	1201.7	1207.8	1227.9	1226.3	1238.7
20°	1136.9	1130.7	1121.4	1107.6	1102.9	1099.8	1099.8	1099.8	1113.7	1126.1	1133.8
22.5°	1058.2	1053.6	1047.4	1028.9	1019.6	1016.5	1024.3	1028.9	1039.7	1048.9	1056.7
25°	979.5	968.7	957.9	951.8	947.1	947.1	950.2	951.8	956.4	961.0	970.3
27.5°	914.7	907.0	891.6	874.6	874.6	870.0	873.1	876.2	887.0	902.4	910.1
30°	842.2	840.7	834.5	828.4	822.2	819.1	825.3	829.9	831.4	839.2	839.2
32.5°	789.8	779.0	768.2	762.0	758.9	757.4	758.9	765.1	765.1	774.4	785.2
35°	737.3	731.2	720.4	709.6	706.5	698.8	705.0	711.1	721.9	726.5	731.2
37.5°	680.3	672.6	667.9	664.8	658.7	660.2	655.6	664.8	674.1	672.6	675.6
40°	637.1	623.2	609.3	607.8	606.2	604.7	604.7	606.2	612.4	618.6	627.8
42.5°	581.5	576.9	564.6	552.2	549.2	546.1	543.0	549.2	561.5	572.3	576.9
45°	524.5	518.3	515.2	506.0	499.8	498.2	495.2	502.9	513.7	518.3	521.4
47.5°	472.0	470.5	461.2	462.8	458.1	459.7	458.1	462.8	462.8	467.4	470.5
50°	436.5	431.9	427.3	424.2	419.6	419.6	418.0	419.6	425.7	431.9	430.4
52.5°	401.1	393.4	391.8	390.3	387.2	390.3	385.6	387.2	393.4	396.4	394.9
55°	359.4	357.9	354.8	351.7	350.2	348.6	348.6	348.6	354.8	359.4	361.0
57.5°	327.0	319.3	313.1	313.1	307.0	305.4	308.5	310.1	314.7	317.8	320.9
60°	282.3	279.2	269.9	265.3	256.1	254.5	254.5	260.7	268.4	279.2	282.3
62.5°	234.5	229.8	228.3	228.3	228.3	228.3	228.3	228.3	228.3	229.8	229.8
65°	208.2	209.8	208.2	206.7	208.2	208.2	206.7	206.7	206.7	208.2	209.8
67.5°	186.7	185.1	186.7	185.1	183.6	183.6	182.0	183.6	185.1	186.7	186.7
70°	162.0	162.0	160.4	162.0	160.4	158.9	157.3	157.3	160.4	162.0	162.0
72.5°	138.8	138.8	137.3	137.3	134.2	134.2	135.7	134.2	134.2	138.8	138.8
75°	115.7	114.1	112.6	112.6	111.1	111.1	111.1	109.5	112.6	112.6	114.1
77.5°	91.0	91.0	91.0	89.5	89.5	87.9	87.9	89.5	89.5	89.5	91.0
80°	69.4	69.4	69.4	67.9	66.3	66.3	66.3	66.3	66.3	67.9	66.3
82.5°	47.8	47.8	47.8	47.8	47.8	46.3	46.3	46.3	47.8	47.8	46.3
85°	29.3	27.8	29.3	29.3	27.8	29.3	27.8	27.8	26.2	26.2	27.8
87.5°	12.3	10.8	9.3	9.3	10.8	9.3	9.3	9.3	10.8	9.3	9.3
90°	38.5	38.6	38.9	39.1	39.4	39.6	39.4	39.1	38.9	38.6	38.5
92.5°	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3
95°	74.6	74.3	73.8	73.3	72.8	72.3	72.8	73.3	73.8	74.3	74.6
97.5°	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6
100°	160.9	160.8	160.5	160.2	160.0	159.7	160.0	160.2	160.5	160.8	160.9
102.5°	209.8	209.7	209.4	209.2	208.9	208.7	208.9	209.2	209.4	209.7	209.8
105°	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8
107.5°	310.1	309.5	308.2	306.9	305.6	304.3	305.6	306.9	308.2	309.5	310.1
110°	362.5	362.1	361.3	360.6	359.8	359.0	359.8	360.6	361.3	362.1	362.5

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	413.8	413.5	413.0	412.5	412.0	411.5	412.0	412.5	413.0	413.5	413.8
115°	469.8	469.4	468.6	467.9	467.1	466.3	467.1	467.9	468.6	469.4	469.8
117.5°	521.1	520.7	519.9	519.2	518.4	517.6	518.4	519.2	519.9	520.7	521.1
120°	575.9	575.5	574.7	574.0	573.2	572.4	573.2	574.0	574.7	575.5	575.9
122.5°	628.3	628.0	627.5	627.0	626.5	626.0	626.5	627.0	627.5	628.0	628.3
125°	681.9	681.8	681.5	681.3	681.0	680.8	681.0	681.3	681.5	681.8	681.9
127.5°	733.2	732.8	732.0	731.3	730.5	729.7	730.5	731.3	732.0	732.8	733.2
130°	788.0	787.5	786.5	785.4	784.4	783.4	784.4	785.4	786.5	787.5	788.0
132.5°	838.2	837.8	837.0	836.3	835.5	834.7	835.5	836.3	837.0	837.8	838.2
135°	891.8	891.4	890.6	889.9	889.1	888.3	889.1	889.9	890.6	891.4	891.8
137.5°	940.7	940.2	939.2	938.1	937.1	936.1	937.1	938.1	939.2	940.2	940.7
140°	990.9	990.4	989.3	988.3	987.2	986.2	987.2	988.3	989.3	990.4	990.9
142.5°	1036.3	1035.8	1034.8	1033.7	1032.7	1031.7	1032.7	1033.7	1034.8	1035.8	1036.3
145°	1081.8	1081.3	1080.2	1079.2	1078.1	1077.1	1078.1	1079.2	1080.2	1081.3	1081.8
147.5°	1122.6	1122.1	1121.0	1120.0	1118.9	1117.9	1118.9	1120.0	1121.0	1122.1	1122.6
150°	1161.1	1160.7	1159.9	1159.2	1158.4	1157.6	1158.4	1159.2	1159.9	1160.7	1161.1
152.5°	1199.5	1199.0	1198.0	1196.9	1195.9	1194.9	1195.9	1196.9	1198.0	1199.0	1199.5
155°	1231.0	1230.6	1229.8	1229.1	1228.3	1227.5	1228.3	1229.1	1229.8	1230.6	1231.0
157.5°	1262.5	1261.8	1260.5	1259.2	1257.9	1256.6	1257.9	1259.2	1260.5	1261.8	1262.5
160°	1288.1	1287.6	1286.6	1285.5	1284.5	1283.5	1284.5	1285.5	1286.6	1287.6	1288.1
162.5°	1312.6	1312.0	1310.7	1309.4	1308.1	1306.8	1308.1	1309.4	1310.7	1312.0	1312.6
165°	1332.4	1331.8	1330.5	1329.2	1327.9	1326.6	1327.9	1329.2	1330.5	1331.8	1332.4
167.5°	1349.9	1349.3	1348.0	1346.7	1345.4	1344.1	1345.4	1346.7	1348.0	1349.3	1349.9
170°	1363.9	1363.1	1361.6	1360.0	1358.5	1356.9	1358.5	1360.0	1361.6	1363.1	1363.9
172.5°	1374.4	1373.6	1372.1	1370.5	1369.0	1367.4	1369.0	1370.5	1372.1	1373.6	1374.4
175°	1381.4	1380.6	1379.1	1377.5	1376.0	1374.4	1376.0	1377.5	1379.1	1380.6	1381.4
177.5°	1384.9	1384.1	1382.6	1381.0	1379.5	1377.9	1379.5	1381.0	1382.6	1384.1	1384.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2114.9	2122.6	2119.5	2102.5	2119.5	2124.1	2133.4	2142.6	2148.8	2158.0	2165.8
5°	1982.2	1997.6	2006.9	1997.6	2028.5	2033.1	2054.7	2067.0	2085.5	2101.0	2113.3
7.5°	1857.2	1869.6	1888.1	1891.2	1909.7	1931.3	1962.1	1993.0	2022.3	2037.7	2051.6
10°	1723.0	1744.6	1772.4	1766.2	1794.0	1827.9	1860.3	1909.7	1934.4	1962.1	1986.8
12.5°	1588.8	1602.7	1639.7	1652.1	1692.2	1718.4	1763.1	1794.0	1855.7	1888.1	1909.7
15°	1354.4	1411.4	1457.7	1513.3	1565.7	1615.1	1655.2	1710.7	1764.7	1789.4	1824.9
17.5°	1247.9	1274.2	1301.9	1329.7	1397.6	1485.5	1556.4	1616.6	1662.9	1695.3	1736.9
20°	1136.9	1163.1	1193.9	1220.2	1261.8	1325.1	1413.0	1516.3	1571.9	1605.8	1645.9
22.5°	1058.2	1082.9	1102.9	1126.1	1158.5	1204.7	1271.1	1399.1	1473.1	1514.8	1550.3
25°	973.4	1004.2	1025.8	1042.8	1069.0	1119.9	1173.9	1246.4	1379.1	1411.4	1460.8
27.5°	914.7	924.0	948.7	974.9	1001.1	1028.9	1084.4	1146.1	1235.6	1306.6	1366.7
30°	845.3	868.5	891.6	902.4	925.5	965.6	999.6	1065.9	1135.3	1190.9	1263.4
32.5°	792.9	806.8	822.2	848.4	870.0	897.8	931.7	987.2	1045.9	1081.3	1136.9
35°	734.3	743.5	775.9	786.7	808.3	836.1	870.0	913.2	976.4	1004.2	1044.3
37.5°	678.7	700.3	709.6	734.3	754.3	782.1	806.8	856.1	897.8	930.2	967.2
40°	635.5	644.8	661.8	683.4	700.3	721.9	752.8	788.2	833.0	859.2	891.6
42.5°	583.1	590.8	612.4	624.7	652.5	672.6	691.1	734.3	774.4	794.4	826.8
45°	526.0	544.5	558.4	583.1	598.5	623.2	646.3	677.2	714.2	737.3	755.9
47.5°	476.7	495.2	509.0	532.2	556.9	567.7	592.3	624.7	658.7	677.2	703.4
50°	436.5	442.7	468.9	479.7	506.0	527.6	544.5	572.3	609.3	620.1	641.7
52.5°	398.0	402.6	419.6	433.5	456.6	475.1	496.7	522.9	553.8	570.7	587.7
55°	364.0	367.1	374.8	390.3	405.7	428.8	448.9	473.6	499.8	518.3	533.7
57.5°	325.5	331.7	337.8	347.1	362.5	384.1	405.7	428.8	450.4	462.8	482.8
60°	280.7	290.0	300.8	311.6	322.4	337.8	362.5	384.1	404.2	414.9	430.4
62.5°	232.9	251.4	260.7	273.0	282.3	296.2	314.7	339.4	353.2	367.1	379.5
65°	209.8	211.3	212.9	225.2	242.2	256.1	273.0	291.5	313.1	322.4	331.7
67.5°	186.7	188.2	191.3	192.8	199.0	214.4	232.9	253.0	269.9	276.1	285.4
70°	163.5	163.5	169.7	171.2	172.8	174.3	189.7	209.8	225.2	232.9	243.7
72.5°	138.8	140.4	143.5	145.0	148.1	151.2	155.8	166.6	185.1	192.8	205.2
75°	114.1	115.7	117.2	118.8	123.4	124.9	129.6	135.7	143.5	152.7	160.4
77.5°	91.0	91.0	92.6	95.6	98.7	100.3	104.9	108.0	111.1	115.7	121.9
80°	67.9	69.4	69.4	72.5	72.5	74.0	75.6	80.2	83.3	86.4	89.5
82.5°	46.3	49.4	49.4	49.4	50.9	52.4	54.0	54.0	57.1	58.6	63.2
85°	27.8	29.3	29.3	29.3	27.8	30.9	30.9	32.4	32.4	32.4	33.9
87.5°	10.8	9.3	10.8	10.8	10.8	12.3	10.8	10.8	12.3	13.9	13.9
90°	38.8	39.3	39.8	40.3	40.8	35.1	29.4	23.7	18.0	15.2	13.6
92.5°	37.2	36.9	36.6	36.4	36.1	35.9	35.6	35.4	35.1	35.0	34.0
95°	74.6	74.6	74.6	74.6	74.6	74.1	73.6	73.1	72.6	72.3	71.0
97.5°	116.6	116.6	116.6	116.6	116.6	115.6	114.5	113.5	112.4	111.9	110.7
100°	160.9	160.9	160.9	160.9	160.9	160.1	159.3	158.6	157.8	157.4	156.4
102.5°	209.7	209.4	209.2	208.9	208.7	207.7	206.6	205.6	204.5	204.0	203.2
105°	258.5	258.0	257.5	257.0	256.5	256.0	255.4	254.9	254.4	254.1	253.7
107.5°	310.0	309.7	309.4	309.2	308.9	308.9	308.9	308.9	308.9	308.9	308.4
110°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	361.7

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	414.2	415.0	415.7	416.5	417.3	417.6	417.8	418.1	418.4	418.5	417.7
115°	469.9	470.2	470.5	470.7	471.0	471.5	472.0	472.5	473.0	473.3	472.5
117.5°	521.5	522.3	523.0	523.8	524.6	525.9	527.2	528.5	529.8	530.4	529.4
120°	575.9	575.9	575.9	575.9	575.9	578.0	580.0	582.1	584.2	585.2	584.2
122.5°	628.7	629.5	630.2	631.0	631.8	633.1	634.4	635.7	637.0	637.6	636.3
125°	682.3	683.1	683.8	684.6	685.4	686.2	687.0	687.7	688.5	688.9	687.7
127.5°	733.7	734.8	735.8	736.9	737.9	738.9	740.0	741.0	742.1	742.6	741.2
130°	788.3	788.8	789.3	789.9	790.4	790.9	791.4	791.9	792.4	792.7	791.0
132.5°	838.8	840.1	841.4	842.7	844.0	843.7	843.5	843.2	842.9	842.8	841.5
135°	891.9	892.2	892.4	892.7	892.9	892.4	891.9	891.4	890.9	890.6	889.2
137.5°	940.8	941.1	941.4	941.6	941.9	941.4	940.9	940.4	939.9	939.6	938.4
140°	990.9	990.9	990.9	990.9	990.9	989.6	988.3	987.0	985.7	985.0	983.8
142.5°	1036.2	1035.9	1035.7	1035.4	1035.2	1034.4	1033.6	1032.9	1032.1	1031.7	1030.5
145°	1081.7	1081.4	1081.1	1080.9	1080.6	1079.0	1077.5	1075.9	1074.4	1073.6	1072.7
147.5°	1122.3	1121.8	1121.3	1120.8	1120.3	1119.3	1118.2	1117.2	1116.1	1115.6	1114.4
150°	1160.7	1159.9	1159.2	1158.4	1157.6	1156.6	1155.5	1154.5	1153.4	1152.9	1152.1
152.5°	1199.0	1198.0	1196.9	1195.9	1194.9	1193.6	1192.3	1191.0	1189.7	1189.0	1188.2
155°	1230.4	1229.1	1227.8	1226.5	1225.2	1224.4	1223.6	1222.9	1222.1	1221.7	1221.3
157.5°	1261.6	1259.8	1257.9	1256.1	1254.3	1253.8	1253.3	1252.8	1252.3	1252.0	1251.7
160°	1287.3	1285.8	1284.2	1282.7	1281.1	1280.9	1280.6	1280.4	1280.1	1280.0	1279.7
162.5°	1311.7	1309.9	1308.0	1306.2	1304.4	1304.2	1303.9	1303.7	1303.4	1303.3	1303.3
165°	1331.5	1329.7	1327.9	1326.1	1324.3	1324.3	1324.3	1324.3	1324.3	1324.3	1324.4
167.5°	1349.0	1347.2	1345.3	1343.5	1341.7	1341.7	1341.7	1341.7	1341.7	1341.7	1342.1
170°	1363.0	1361.2	1359.3	1357.5	1355.7	1356.0	1356.2	1356.5	1356.8	1356.9	1357.3
172.5°	1373.5	1371.7	1369.8	1368.0	1366.2	1366.5	1366.7	1367.0	1367.3	1367.4	1367.8
175°	1380.5	1378.7	1376.8	1375.0	1373.2	1373.7	1374.2	1374.7	1375.2	1375.5	1375.9
177.5°	1384.1	1382.6	1381.0	1379.5	1377.9	1378.4	1378.9	1379.4	1379.9	1380.2	1380.6
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2219.7	2219.7	2219.7	2219.7
2.5°	2179.6	2175.0	2202.8	2233.6
5°	2134.9	2142.6	2178.1	2221.3
7.5°	2088.6	2105.6	2147.2	2204.3
10°	2023.8	2054.7	2117.9	2176.6
12.5°	1960.6	2002.2	2062.4	2131.8
15°	1889.6	1935.9	2010.0	2093.3
17.5°	1811.0	1863.4	1949.8	2040.8
20°	1727.7	1797.1	1888.1	1986.8
22.5°	1635.1	1718.4	1812.5	1922.0
25°	1545.6	1636.7	1730.8	1857.2
27.5°	1457.7	1547.2	1652.1	1780.1
30°	1369.8	1451.6	1564.2	1701.4
32.5°	1275.7	1360.5	1479.3	1619.7
35°	1189.3	1274.2	1385.2	1524.1
37.5°	1096.8	1187.8	1294.2	1437.7
40°	988.8	1095.2	1198.6	1335.9
42.5°	899.3	1011.9	1112.2	1241.8
45°	828.4	934.8	1018.1	1144.6
47.5°	762.0	848.4	933.3	1050.5
50°	698.8	765.1	853.0	957.9
52.5°	634.0	691.1	766.7	865.4
55°	575.4	629.4	697.2	772.8
57.5°	521.4	560.0	627.8	695.7
60°	461.2	501.3	553.8	610.9
62.5°	410.3	441.2	490.5	538.4
65°	356.3	385.6	422.7	467.4
67.5°	307.0	333.2	362.5	398.0
70°	262.2	282.3	303.9	334.7
72.5°	214.4	236.0	256.1	280.7
75°	175.9	185.1	202.1	219.0
77.5°	135.7	148.1	157.3	171.2
80°	97.2	108.0	111.1	121.9
82.5°	64.8	71.0	77.1	80.2
85°	37.0	40.1	46.3	47.8
87.5°	13.9	15.4	18.5	21.6
90°	10.5	7.4	4.3	1.2
92.5°	31.9	29.8	27.7	25.6
95°	68.4	65.8	63.2	60.6
97.5°	108.4	106.1	103.7	101.4
100°	154.3	152.2	150.1	148.0
102.5°	201.7	200.1	198.6	197.0
105°	252.9	252.2	251.4	250.6
107.5°	307.4	306.3	305.3	304.3
110°	360.2	358.6	357.1	355.5

TEST NUMBER: P999292

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	416.2	414.6	413.1	411.5
115°	471.0	469.4	467.9	466.3
117.5°	527.3	525.2	523.2	521.1
120°	582.1	580.0	578.0	575.9
122.5°	633.7	631.2	628.6	626.0
125°	685.4	683.1	680.7	678.4
127.5°	738.3	735.4	732.6	729.7
130°	787.6	784.3	780.9	777.5
132.5°	838.9	836.4	833.8	831.2
135°	886.3	883.5	880.6	877.8
137.5°	936.1	933.8	931.4	929.1
140°	981.5	979.2	976.8	974.5
142.5°	1028.2	1025.9	1023.5	1021.2
145°	1070.9	1069.1	1067.3	1065.5
147.5°	1112.1	1109.8	1107.4	1105.1
150°	1150.6	1149.0	1147.5	1145.9
152.5°	1186.7	1185.1	1183.6	1182.0
155°	1220.5	1219.8	1219.0	1218.2
157.5°	1251.2	1250.7	1250.2	1249.7
160°	1279.2	1278.7	1278.1	1277.6
162.5°	1303.3	1303.3	1303.3	1303.3
165°	1324.7	1324.9	1325.2	1325.4
167.5°	1342.9	1343.6	1344.4	1345.2
170°	1358.1	1358.8	1359.6	1360.4
172.5°	1368.6	1369.3	1370.1	1370.9
175°	1376.7	1377.4	1378.2	1379.0
177.5°	1381.4	1382.1	1382.9	1383.7
180°	1381.4	1381.4	1381.4	1381.4

(END OF REPORT)