

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999296

Luminaire Tested: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999296
REPORT IS A COMBINATION OF REPORTS P987845 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7736.9 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999296

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999296

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	86	82	80	71	69	67	58	57	56	46	46	45
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	48	50	45	41	41	38	35	33	31	29
5	69	57	50	44	63	53	46	41	45	40	36	37	34	31	30	28	25
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26984	26984	26984
5°	27028	25673	25482
10°	26762	24349	23545
15°	26394	22786	21338
20°	25908	21009	19029
25°	25410	19186	16916
30°	24739	17410	14609
35°	24083	15619	12627
40°	23419	13860	10586
45°	22642	12045	8806
50°	21840	10295	7169
55°	21005	8545	5692
60°	20037	6834	4306
65°	18919	5209	3501
70°	17570	3780	2785
75°	15881	2882	2126
80°	13429	1953	1427
85°	9365	893	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22642 cd/sqm

TEST NUMBER: P999296

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.8	2.1
10°-20°	438.6	5.7
20°-30°	615.8	8.0
30°-40°	671.2	8.7
40°-50°	616.9	8.0
50°-60°	484.5	6.3
60°-70°	315.4	4.1
70°-80°	162.4	2.1
80°-90°	45.3	0.6
90°-100°	245.8	3.2
100°-110°	830.9	10.7
110°-120°	873.4	11.3
120°-130°	718.2	9.3
130°-140°	577.1	7.5
140°-150°	436.0	5.6
150°-160°	306.5	4.0
160°-170°	180.5	2.3
170°-180°	58.7	0.8
0°-30°	1214.2	15.7
0°-40°	1885.4	24.4
0°-60°	2986.8	38.6
0°-90°	3509.9	45.4
90°-120°	1950.0	25.2
90°-150°	3681.3	47.6
90°-180°	4227.0	54.6
0°-180°	7736.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1705	1697	1677	1691	1686	162
15°	1621	1604	1552	1523	1507	457
25°	1472	1422	1321	1257	1234	677
35°	1268	1190	1054	956	923	794
45°	1037	933	771	662	625	801
55°	788	668	501	409	380	704
65°	532	407	268	216	211	528
75°	284	176	123	113	111	300
85°	66	34	29	29	29	76
90°	1	16	40	38	38	6
95°	41	100	457	173	133	42
105°	142	215	864	1544	1314	151
115°	251	317	723	1492	1729	249
125°	350	414	695	1208	1403	311
135°	410	490	687	1016	1162	317
145°	469	539	683	848	928	294
155°	533	575	663	750	780	245
165°	581	598	635	674	684	164
175°	605	606	611	618	617	57
180°	606	606	606	606	606	

TEST NUMBER: P999296

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1704.7	1704.7	1704.7	1704.7	1704.7
2.5°	1712.4	1704.7	1687.8	1703.2	1700.1
5°	1704.7	1697.0	1677.0	1690.8	1686.2
7.5°	1690.8	1681.6	1660.0	1666.2	1658.4
10°	1672.3	1661.5	1630.7	1626.1	1616.8
12.5°	1649.2	1635.3	1593.7	1584.4	1567.4
15°	1621.4	1604.5	1552.0	1522.7	1507.3
17.5°	1589.0	1564.3	1499.5	1465.6	1440.9
20°	1552.0	1521.1	1444.0	1405.4	1371.5
22.5°	1511.9	1476.4	1386.9	1334.5	1311.3
25°	1471.8	1422.4	1320.6	1257.3	1234.2
27.5°	1424.0	1371.5	1258.9	1186.4	1150.9
30°	1373.0	1314.4	1191.0	1112.3	1070.7
32.5°	1323.7	1252.7	1126.2	1033.6	995.1
35°	1268.1	1189.5	1053.7	956.5	922.6
37.5°	1214.1	1129.3	985.8	879.4	840.8
40°	1157.1	1064.5	914.8	805.3	765.2
42.5°	1098.4	999.7	843.9	729.7	691.1
45°	1036.7	933.4	771.4	661.8	624.8
47.5°	978.1	868.6	701.9	592.4	558.5
50°	913.3	803.8	634.1	527.6	495.2
52.5°	850.1	734.3	569.3	467.5	438.1
55°	788.3	668.0	501.4	408.8	379.5
57.5°	725.1	601.7	441.2	354.8	330.1
60°	660.3	536.9	378.0	299.3	274.6
62.5°	597.0	473.6	324.0	249.9	237.6
65°	532.2	407.3	268.4	216.0	211.4
67.5°	470.5	345.6	216.0	189.8	185.1
70°	405.7	285.4	179.0	163.5	157.4
72.5°	344.0	229.9	149.6	137.3	134.2
75°	283.9	175.9	123.4	112.6	111.1
77.5°	223.7	125.0	97.2	91.0	87.9
80°	168.2	89.5	74.1	67.9	67.9
82.5°	117.2	60.2	50.9	47.8	47.8
85°	66.3	33.9	29.3	29.3	29.3
87.5°	24.7	12.3	12.3	10.8	10.8
90°	1.2	15.8	39.6	37.9	38.5
92.5°	17.5	55.4	179.6	82.8	71.1
95°	40.8	100.3	457.0	172.6	132.9
97.5°	60.6	132.4	745.0	346.3	222.7
100°	89.8	162.0	921.1	689.7	417.4
102.5°	116.6	188.9	926.9	1165.9	813.8
105°	142.2	214.6	863.9	1544.2	1314.0
107.5°	170.2	240.2	805.6	1681.2	1650.9
110°	198.2	266.4	766.0	1659.1	1788.5

TEST NUMBER: P999296

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	291.5	740.4	1583.8	1786.2
115°	250.7	316.6	722.9	1491.8	1729.0
117.5°	278.7	341.6	713.5	1403.8	1642.8
120°	304.3	366.1	705.4	1325.0	1560.0
122.5°	328.8	391.2	700.7	1263.8	1473.7
125°	349.8	413.9	694.9	1208.4	1402.6
127.5°	367.3	435.5	691.4	1161.2	1336.1
130°	382.4	454.7	689.1	1113.4	1281.3
132.5°	396.4	473.4	687.9	1063.9	1224.2
135°	410.4	489.7	686.7	1015.6	1162.4
137.5°	423.2	503.6	686.7	966.6	1103.0
140°	438.4	516.5	685.6	923.4	1041.2
142.5°	453.5	527.0	685.6	882.0	979.4
145°	468.7	538.6	683.2	848.2	928.1
147.5°	485.0	548.0	679.7	818.4	882.6
150°	501.3	557.3	676.2	792.8	843.0
152.5°	517.7	566.6	670.4	771.2	809.1
155°	532.8	575.4	663.4	750.3	780.0
157.5°	545.6	582.4	656.4	730.4	754.3
160°	558.5	589.4	649.4	710.6	729.9
162.5°	571.3	594.6	643.6	692.0	706.5
165°	580.6	598.1	635.4	673.9	684.4
167.5°	588.8	601.6	628.4	657.6	663.4
170°	596.9	603.4	622.6	642.4	644.7
172.5°	601.6	605.1	615.6	629.0	629.6
175°	605.1	605.7	610.9	618.5	616.8
177.5°	607.4	606.3	606.3	610.9	607.4
180°	606.3	606.3	606.3	606.3	606.3

(END OF REPORT)