

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999305

Luminaire Tested: SA2XXRDIP-B1005D1080UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999305
REPORT IS A COMBINATION OF REPORTS P987856 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D1080UB50-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7057.9 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999305

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999305

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	87	90	86	83	80	73	70	68	60	58	57	48	47	46
2	89	82	76	71	82	76	71	67	64	60	57	53	51	48	43	41	40
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	32	29	26
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25830	25830	25830
5°	25872	24574	24392
10°	25617	23307	22538
15°	25266	21811	20425
20°	24800	20110	18215
25°	24322	18365	16192
30°	23681	16665	13984
35°	23054	14951	12087
40°	22417	13268	10134
45°	21674	11530	8430
50°	20905	9854	6862
55°	20107	8179	5449
60°	19178	6541	4123
65°	18112	4988	3351
70°	16820	3618	2664
75°	15199	2759	2035
80°	12854	1868	1367
85°	8970	857	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21674 cd/sqm

TEST NUMBER: P999305

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.9	2.2
10°-20°	419.8	5.9
20°-30°	589.4	8.4
30°-40°	642.5	9.1
40°-50°	590.5	8.4
50°-60°	463.8	6.6
60°-70°	301.9	4.3
70°-80°	155.4	2.2
80°-90°	43.5	0.6
90°-100°	81.8	1.2
100°-110°	260.1	3.7
110°-120°	445.1	6.3
120°-130°	585.4	8.3
130°-140°	657.1	9.3
140°-150°	644.4	9.1
150°-160°	540.5	7.7
160°-170°	358.5	5.1
170°-180°	125.3	1.8
0°-30°	1162.2	16.5
0°-40°	1804.7	25.6
0°-60°	2859.0	40.5
0°-90°	3359.7	47.6
90°-120°	787.0	11.2
90°-150°	2673.9	37.9
90°-180°	3698.0	52.4
0°-180°	7057.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1632	1632	1632	1632	1632	
5°	1632	1624	1605	1618	1614	155
15°	1552	1536	1486	1458	1443	437
25°	1409	1362	1264	1204	1181	648
35°	1214	1139	1009	916	883	760
45°	992	893	738	634	598	766
55°	755	639	480	391	363	674
65°	510	390	257	207	202	505
75°	272	168	118	108	106	287
85°	64	32	28	28	28	73
90°	1	14	39	37	38	7
95°	58	69	71	71	69	65
105°	240	243	246	248	248	253
115°	446	453	451	450	446	442
125°	650	660	656	653	652	581
135°	840	853	855	854	851	650
145°	1020	1028	1035	1036	1031	637
155°	1166	1170	1173	1179	1175	537
165°	1269	1268	1268	1276	1270	358
175°	1320	1317	1315	1323	1316	125
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P999305

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.8	1631.8	1631.8	1631.8	1631.8
2.5°	1639.2	1631.8	1615.6	1630.3	1627.4
5°	1631.8	1624.4	1605.2	1618.5	1614.1
7.5°	1618.5	1609.6	1589.0	1594.9	1587.5
10°	1600.8	1590.4	1560.9	1556.5	1547.6
12.5°	1578.6	1565.3	1525.5	1516.6	1500.4
15°	1552.1	1535.8	1485.6	1457.5	1442.8
17.5°	1521.0	1497.4	1435.4	1402.9	1379.3
20°	1485.6	1456.1	1382.2	1345.3	1312.8
22.5°	1447.2	1413.2	1327.6	1277.4	1255.2
25°	1408.8	1361.6	1264.1	1203.5	1181.4
27.5°	1363.0	1312.8	1205.0	1135.6	1101.6
30°	1314.3	1258.2	1140.0	1064.7	1024.9
32.5°	1267.0	1199.1	1078.0	989.4	952.5
35°	1213.9	1138.6	1008.6	915.6	883.1
37.5°	1162.2	1081.0	943.6	841.7	804.8
40°	1107.6	1019.0	875.7	770.9	732.5
42.5°	1051.4	956.9	807.8	698.5	661.6
45°	992.4	893.4	738.4	633.5	598.1
47.5°	936.3	831.4	671.9	567.1	534.6
50°	874.2	769.4	606.9	505.0	474.0
52.5°	813.7	702.9	544.9	447.5	419.4
55°	754.6	639.4	479.9	391.3	363.3
57.5°	694.1	575.9	422.3	339.7	316.0
60°	632.0	513.9	361.8	286.5	262.9
62.5°	571.5	453.4	310.1	239.2	227.4
65°	509.5	389.9	257.0	206.7	202.3
67.5°	450.4	330.8	206.7	181.6	177.2
70°	388.4	273.2	171.3	156.5	150.6
72.5°	329.3	220.0	143.2	131.4	128.5
75°	271.7	168.3	118.1	107.8	106.3
77.5°	214.1	119.6	93.0	87.1	84.2
80°	161.0	85.7	70.9	65.0	65.0
82.5°	112.2	57.6	48.7	45.8	45.8
85°	63.5	32.5	28.1	28.1	28.1
87.5°	23.6	11.8	11.8	10.3	10.3
90°	1.1	14.5	39.1	36.8	38.0
92.5°	24.6	33.5	34.6	35.7	35.7
95°	58.0	69.2	71.4	71.4	69.2
97.5°	97.1	107.2	111.6	111.6	111.6
100°	141.8	150.7	154.0	154.0	152.9
102.5°	188.6	195.3	199.8	200.9	199.8
105°	240.0	243.3	245.6	247.8	247.8
107.5°	291.3	295.8	295.8	296.9	291.3
110°	340.5	347.2	347.2	347.2	343.8

TEST NUMBER: P999305

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	394.0	400.7	399.6	396.3	394.0
115°	446.5	453.2	451.0	449.9	446.5
117.5°	499.0	507.9	502.3	499.0	495.6
120°	551.4	560.4	551.4	551.4	548.1
122.5°	599.4	610.6	605.0	601.7	599.4
125°	649.7	659.7	656.4	653.0	651.9
127.5°	698.8	711.1	706.6	702.1	698.8
130°	744.6	759.1	756.8	754.6	750.1
132.5°	795.9	807.1	808.2	802.6	799.2
135°	840.5	852.8	855.1	853.9	850.6
137.5°	889.7	899.7	901.9	900.8	896.4
140°	933.2	943.2	948.8	948.8	944.4
142.5°	977.9	987.9	991.2	992.4	987.9
145°	1020.3	1028.1	1034.8	1035.9	1031.4
147.5°	1058.2	1068.3	1072.7	1075.0	1070.5
150°	1097.3	1104.0	1108.5	1111.8	1108.5
152.5°	1131.9	1138.6	1144.2	1148.6	1144.2
155°	1166.5	1169.8	1173.2	1178.8	1175.4
157.5°	1196.6	1198.9	1201.1	1208.9	1203.3
160°	1223.4	1225.7	1226.8	1233.5	1229.0
162.5°	1248.0	1248.0	1249.1	1256.9	1251.3
165°	1269.2	1268.1	1268.1	1275.9	1270.3
167.5°	1288.2	1284.8	1284.8	1292.6	1287.1
170°	1302.7	1299.3	1298.2	1306.0	1299.3
172.5°	1312.7	1309.4	1308.3	1316.1	1309.4
175°	1320.5	1317.2	1315.0	1322.8	1316.1
177.5°	1325.0	1321.7	1319.4	1326.1	1319.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)