

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999345

Luminaire Tested: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999345
REPORT IS A COMBINATION OF REPORTS P987896 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4489.0 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999345

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999345

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79
1	104	100	96	93	99	95	92	89	86	84	81	78	76	75	71	69	68
2	95	88	82	77	91	84	79	74	77	72	69	70	66	63	63	61	58
3	88	78	71	65	83	75	68	63	68	63	59	62	58	55	57	53	51
4	81	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44
5	74	63	55	49	71	60	53	47	55	49	44	51	46	42	47	42	39
6	69	57	49	43	65	54	47	42	50	44	39	46	41	37	43	38	35
7	64	52	44	38	61	50	42	37	46	40	35	42	37	33	39	35	31
8	60	47	39	34	57	45	38	33	42	36	32	39	34	30	36	32	28
9	56	43	36	31	53	42	35	30	39	33	29	36	31	27	33	29	26
10	52	40	33	28	50	39	32	27	36	30	26	34	28	25	31	27	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25830	25830	25830
5°	25872	24574	24392
10°	25617	23307	22538
15°	25266	21811	20425
20°	24800	20110	18215
25°	24322	18365	16192
30°	23681	16665	13984
35°	23054	14951	12087
40°	22417	13268	10134
45°	21674	11530	8430
50°	20905	9854	6862
55°	20107	8179	5449
60°	19178	6541	4123
65°	18112	4988	3351
70°	16820	3618	2664
75°	15199	2759	2035
80°	12854	1868	1367
85°	8970	857	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21674 cd/sqm

TEST NUMBER: P999345

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.9	3.4
10°-20°	419.8	9.4
20°-30°	589.4	13.1
30°-40°	642.5	14.3
40°-50°	590.5	13.2
50°-60°	463.8	10.3
60°-70°	301.9	6.7
70°-80°	155.4	3.5
80°-90°	40.8	0.9
90°-100°	25.0	0.6
100°-110°	79.6	1.8
110°-120°	136.2	3.0
120°-130°	179.2	4.0
130°-140°	201.1	4.5
140°-150°	197.2	4.4
150°-160°	165.4	3.7
160°-170°	109.7	2.4
170°-180°	38.3	0.9
0°-30°	1162.2	25.9
0°-40°	1804.7	40.2
0°-60°	2859.0	63.7
0°-90°	3357.1	74.8
90°-120°	240.9	5.4
90°-150°	818.4	18.2
90°-180°	1132.0	25.2
0°-180°	4489.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1632	1632	1632	1632	1632	
5°	1632	1624	1605	1618	1614	155
15°	1552	1536	1486	1458	1443	437
25°	1409	1362	1264	1204	1181	648
35°	1214	1139	1009	916	883	760
45°	992	893	738	634	598	766
55°	755	639	480	391	363	674
65°	510	390	257	207	202	505
75°	272	168	118	108	106	287
85°	64	32	28	28	28	73
90°	0	4	12	11	12	4
95°	18	21	22	22	21	20
105°	74	74	75	76	76	78
115°	137	139	138	138	137	135
125°	199	202	201	200	200	178
135°	257	261	262	261	260	199
145°	312	315	317	317	316	195
155°	357	358	359	361	360	164
165°	388	388	388	390	389	110
175°	404	403	402	405	403	38
180°	405	405	405	405	405	

TEST NUMBER: P999345

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.8	1631.8	1631.8	1631.8	1631.8
2.5°	1639.2	1631.8	1615.6	1630.3	1627.4
5°	1631.8	1624.4	1605.2	1618.5	1614.1
7.5°	1618.5	1609.6	1589.0	1594.9	1587.5
10°	1600.8	1590.4	1560.9	1556.5	1547.6
12.5°	1578.6	1565.3	1525.5	1516.6	1500.4
15°	1552.1	1535.8	1485.6	1457.5	1442.8
17.5°	1521.0	1497.4	1435.4	1402.9	1379.3
20°	1485.6	1456.1	1382.2	1345.3	1312.8
22.5°	1447.2	1413.2	1327.6	1277.4	1255.2
25°	1408.8	1361.6	1264.1	1203.5	1181.4
27.5°	1363.0	1312.8	1205.0	1135.6	1101.6
30°	1314.3	1258.2	1140.0	1064.7	1024.9
32.5°	1267.0	1199.1	1078.0	989.4	952.5
35°	1213.9	1138.6	1008.6	915.6	883.1
37.5°	1162.2	1081.0	943.6	841.7	804.8
40°	1107.6	1019.0	875.7	770.9	732.5
42.5°	1051.4	956.9	807.8	698.5	661.6
45°	992.4	893.4	738.4	633.5	598.1
47.5°	936.3	831.4	671.9	567.1	534.6
50°	874.2	769.4	606.9	505.0	474.0
52.5°	813.7	702.9	544.9	447.5	419.4
55°	754.6	639.4	479.9	391.3	363.3
57.5°	694.1	575.9	422.3	339.7	316.0
60°	632.0	513.9	361.8	286.5	262.9
62.5°	571.5	453.4	310.1	239.2	227.4
65°	509.5	389.9	257.0	206.7	202.3
67.5°	450.4	330.8	206.7	181.6	177.2
70°	388.4	273.2	171.3	156.5	150.6
72.5°	329.3	220.0	143.2	131.4	128.5
75°	271.7	168.3	118.1	107.8	106.3
77.5°	214.1	119.6	93.0	87.1	84.2
80°	161.0	85.7	70.9	65.0	65.0
82.5°	112.2	57.6	48.7	45.8	45.8
85°	63.5	32.5	28.1	28.1	28.1
87.5°	23.6	11.8	11.8	10.3	10.3
90°	0.3	4.4	12.0	11.3	11.6
92.5°	7.5	10.2	10.6	10.9	10.9
95°	17.8	21.2	21.9	21.9	21.2
97.5°	29.7	32.8	34.2	34.2	34.2
100°	43.4	46.1	47.1	47.1	46.8
102.5°	57.7	59.8	61.2	61.5	61.2
105°	73.5	74.5	75.2	75.8	75.8
107.5°	89.2	90.5	90.5	90.9	89.2
110°	104.2	106.2	106.2	106.2	105.2

TEST NUMBER: P999345

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	120.6	122.6	122.3	121.3	120.6
115°	136.7	138.7	138.0	137.7	136.7
117.5°	152.7	155.4	153.7	152.7	151.7
120°	168.8	171.5	168.8	168.8	167.7
122.5°	183.5	186.9	185.2	184.1	183.5
125°	198.8	201.9	200.9	199.9	199.5
127.5°	213.9	217.6	216.3	214.9	213.9
130°	227.9	232.3	231.6	230.9	229.6
132.5°	243.6	247.0	247.3	245.6	244.6
135°	257.3	261.0	261.7	261.4	260.3
137.5°	272.3	275.4	276.0	275.7	274.3
140°	285.6	288.7	290.4	290.4	289.0
142.5°	299.3	302.3	303.4	303.7	302.3
145°	312.3	314.6	316.7	317.0	315.7
147.5°	323.9	326.9	328.3	329.0	327.6
150°	335.8	337.9	339.2	340.3	339.2
152.5°	346.4	348.5	350.2	351.5	350.2
155°	357.0	358.0	359.1	360.8	359.7
157.5°	366.2	366.9	367.6	370.0	368.3
160°	374.4	375.1	375.5	377.5	376.1
162.5°	381.9	381.9	382.3	384.7	383.0
165°	388.4	388.1	388.1	390.5	388.8
167.5°	394.2	393.2	393.2	395.6	393.9
170°	398.7	397.7	397.3	399.7	397.7
172.5°	401.8	400.7	400.4	402.8	400.7
175°	404.2	403.1	402.4	404.8	402.8
177.5°	405.5	404.5	403.8	405.9	403.8
180°	404.8	404.8	404.8	404.8	404.8

(END OF REPORT)