

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000178

Luminaire Tested: SA2XXRDIP-B865D530UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000178
REPORT IS A COMBINATION OF REPORTS P988738 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D530UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4876.3 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000178

CATALOG NUMBER: SA2XXRDIP-B865D530UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000178

CATALOG NUMBER: SA2XXRDIP-B865D530UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	35	32
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22182	22182	22182
5°	22218	21103	20947
10°	21999	20016	19354
15°	21696	18731	17540
20°	21297	17270	15642
25°	20886	15770	13905
30°	20337	14311	12008
35°	19797	12840	10380
40°	19249	11394	8702
45°	18612	9901	7239
50°	17954	8462	5894
55°	17267	7025	4679
60°	16471	5617	3539
65°	15553	4283	2877
70°	14443	3107	2289
75°	13051	2371	1748
80°	11034	1605	1173
85°	7698	735	567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18612 cd/sqm

TEST NUMBER: P1000178

CATALOG NUMBER: SA2XXRDIP-B865D530UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.7
10°-20°	360.5	7.4
20°-30°	506.2	10.4
30°-40°	551.8	11.3
40°-50°	507.1	10.4
50°-60°	398.3	8.2
60°-70°	259.2	5.3
70°-80°	133.5	2.7
80°-90°	35.9	0.7
90°-100°	115.8	2.4
100°-110°	391.6	8.0
110°-120°	411.7	8.4
120°-130°	338.5	6.9
130°-140°	272.0	5.6
140°-150°	205.5	4.2
150°-160°	144.5	3.0
160°-170°	85.1	1.7
170°-180°	27.7	0.6
0°-30°	998.1	20.5
0°-40°	1549.8	31.8
0°-60°	2455.2	50.4
0°-90°	2883.8	59.1
90°-120°	919.2	18.8
90°-150°	1735.2	35.6
90°-180°	1992.0	40.9
0°-180°	4876.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1401	1401	1401	1401	1401	
5°	1401	1395	1378	1390	1386	133
15°	1333	1319	1276	1252	1239	376
25°	1210	1169	1086	1034	1014	556
35°	1042	978	866	786	758	652
45°	852	767	634	544	514	658
55°	648	549	412	336	312	579
65°	438	335	221	178	174	434
75°	233	145	102	93	91	247
85°	54	28	24	24	24	63
90°	0	7	19	18	18	4
95°	19	47	215	81	63	20
105°	67	101	407	728	619	71
115°	118	149	341	703	815	117
125°	165	195	328	570	661	147
135°	193	231	324	479	548	149
145°	221	254	322	400	438	139
155°	251	271	313	354	368	116
165°	274	282	300	318	323	77
175°	285	286	288	292	291	27
180°	286	286	286	286	286	

TEST NUMBER: P1000178

CATALOG NUMBER: SA2XXRDIP-B865D530UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1401.3	1401.3	1401.3	1401.3	1401.3
2.5°	1407.7	1401.3	1387.4	1400.1	1397.5
5°	1401.3	1395.0	1378.5	1389.9	1386.1
7.5°	1389.9	1382.3	1364.5	1369.6	1363.3
10°	1374.7	1365.8	1340.5	1336.6	1329.0
12.5°	1355.7	1344.3	1310.0	1302.4	1288.5
15°	1332.8	1318.9	1275.8	1251.7	1239.0
17.5°	1306.2	1285.9	1232.7	1204.8	1184.5
20°	1275.8	1250.4	1187.0	1155.3	1127.4
22.5°	1242.8	1213.6	1140.1	1097.0	1077.9
25°	1209.8	1169.2	1085.5	1033.6	1014.5
27.5°	1170.5	1127.4	1034.8	975.2	946.1
30°	1128.7	1080.5	979.0	914.3	880.1
32.5°	1088.1	1029.8	925.8	849.7	818.0
35°	1042.4	977.8	866.2	786.3	758.4
37.5°	998.0	928.3	810.4	722.9	691.2
40°	951.1	875.0	752.0	662.0	629.0
42.5°	902.9	821.8	693.7	599.8	568.1
45°	852.2	767.2	634.1	544.0	513.6
47.5°	804.0	714.0	577.0	487.0	459.1
50°	750.8	660.7	521.2	433.7	407.1
52.5°	698.8	603.6	468.0	384.3	360.2
55°	648.0	549.1	412.2	336.1	312.0
57.5°	596.0	494.6	362.7	291.7	271.4
60°	542.8	441.3	310.7	246.0	225.7
62.5°	490.8	389.3	266.3	205.4	195.3
65°	437.5	334.8	220.7	177.5	173.7
67.5°	386.8	284.1	177.5	156.0	152.2
70°	333.5	234.6	147.1	134.4	129.4
72.5°	282.8	189.0	123.0	112.9	110.3
75°	233.3	144.6	101.5	92.6	91.3
77.5°	183.9	102.7	79.9	74.8	72.3
80°	138.2	73.6	60.9	55.8	55.8
82.5°	96.4	49.5	41.8	39.3	39.3
85°	54.5	27.9	24.1	24.1	24.1
87.5°	20.3	10.1	10.1	8.9	8.9
90°	0.5	7.4	18.7	17.8	18.1
92.5°	8.2	26.1	84.6	39.0	33.5
95°	19.2	47.3	215.4	81.4	62.7
97.5°	28.6	62.4	351.2	163.2	105.0
100°	42.3	76.4	434.2	325.0	196.7
102.5°	55.0	89.0	436.9	549.6	383.6
105°	67.0	101.1	407.2	727.9	619.4
107.5°	80.2	113.2	379.8	792.5	778.2
110°	93.4	125.6	361.1	782.0	843.0



TEST NUMBER: P1000178

CATALOG NUMBER: SA2XXRDIP-B865D530UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.5	137.4	349.0	746.6	841.9
115°	118.2	149.2	340.7	703.2	815.0
117.5°	131.3	161.0	336.3	661.7	774.3
120°	143.4	172.6	332.5	624.6	735.3
122.5°	155.0	184.4	330.3	595.8	694.7
125°	164.9	195.1	327.5	569.6	661.1
127.5°	173.1	205.2	325.9	547.4	629.8
130°	180.3	214.3	324.8	524.8	604.0
132.5°	186.9	223.1	324.2	501.4	577.1
135°	193.4	230.8	323.7	478.7	547.9
137.5°	199.5	237.4	323.7	455.6	519.9
140°	206.6	243.4	323.1	435.3	490.8
142.5°	213.8	248.4	323.1	415.8	461.6
145°	220.9	253.9	322.0	399.8	437.5
147.5°	228.6	258.3	320.4	385.8	416.0
150°	236.3	262.6	318.8	373.8	397.3
152.5°	244.0	267.1	316.0	363.5	381.4
155°	251.2	271.2	312.7	353.6	367.7
157.5°	257.2	274.5	309.4	344.3	355.6
160°	263.2	277.8	306.1	335.0	344.0
162.5°	269.3	280.3	303.4	326.2	333.0
165°	273.7	282.0	299.5	317.7	322.6
167.5°	277.5	283.6	296.2	310.0	312.7
170°	281.4	284.4	293.5	302.8	303.9
172.5°	283.6	285.2	290.2	296.5	296.8
175°	285.2	285.5	288.0	291.6	290.7
177.5°	286.3	285.8	285.8	288.0	286.3
180°	285.8	285.8	285.8	285.8	285.8

(END OF REPORT)