

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999346

Luminaire Tested: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999346
REPORT IS A COMBINATION OF REPORTS P987897 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4596.4 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999346

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999346

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	104	99	96	92	98	95	91	88	85	83	81	77	75	73	69	68	67
2	95	88	82	77	90	84	78	74	76	72	68	69	65	62	62	59	57
3	87	78	71	65	83	74	68	62	68	62	58	61	57	54	56	52	50
4	80	69	62	56	76	66	59	54	61	55	50	55	51	47	50	46	43
5	74	62	54	48	70	60	52	47	55	49	44	50	45	41	46	42	38
6	68	56	48	42	65	54	47	41	50	43	39	45	40	36	42	37	34
7	64	51	43	38	60	49	42	37	45	39	35	42	36	33	38	34	31
8	59	47	39	34	56	45	38	33	42	35	31	38	33	29	35	31	28
9	55	43	36	30	53	41	34	30	38	32	28	35	30	27	33	28	25
10	52	40	32	28	49	38	32	27	36	30	26	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25830	25830	25830
5°	25872	24574	24392
10°	25617	23307	22538
15°	25266	21811	20425
20°	24800	20110	18215
25°	24322	18365	16192
30°	23681	16665	13984
35°	23054	14951	12087
40°	22417	13268	10134
45°	21674	11530	8430
50°	20905	9854	6862
55°	20107	8179	5449
60°	19178	6541	4123
65°	18112	4988	3351
70°	16820	3618	2664
75°	15199	2759	2035
80°	12854	1868	1367
85°	8970	857	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21674 cd/sqm

TEST NUMBER: P999346

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.9	3.3
10°-20°	419.8	9.1
20°-30°	589.4	12.8
30°-40°	642.5	14.0
40°-50°	590.5	12.8
50°-60°	463.8	10.1
60°-70°	301.9	6.6
70°-80°	155.4	3.4
80°-90°	40.8	0.9
90°-100°	72.1	1.6
100°-110°	243.6	5.3
110°-120°	256.1	5.6
120°-130°	210.5	4.6
130°-140°	169.2	3.7
140°-150°	127.8	2.8
150°-160°	89.9	2.0
160°-170°	52.9	1.2
170°-180°	17.2	0.4
0°-30°	1162.2	25.3
0°-40°	1804.7	39.3
0°-60°	2859.0	62.2
0°-90°	3357.1	73.0
90°-120°	571.7	12.4
90°-150°	1079.3	23.5
90°-180°	1239.0	27.0
0°-180°	4596.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1632	1632	1632	1632	1632	
5°	1632	1624	1605	1618	1614	155
15°	1552	1536	1486	1458	1443	437
25°	1409	1362	1264	1204	1181	648
35°	1214	1139	1009	916	883	760
45°	992	893	738	634	598	766
55°	755	639	480	391	363	674
65°	510	390	257	207	202	505
75°	272	168	118	108	106	287
85°	64	32	28	28	28	73
90°	0	5	12	11	11	4
95°	12	29	134	51	39	12
105°	42	63	253	453	385	44
115°	74	93	212	437	507	73
125°	102	121	204	354	411	91
135°	120	144	201	298	341	93
145°	137	158	200	249	272	86
155°	156	169	194	220	229	72
165°	170	175	186	198	201	48
175°	177	178	179	181	181	17
180°	178	178	178	178	178	

TEST NUMBER: P999346

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.8	1631.8	1631.8	1631.8	1631.8
2.5°	1639.2	1631.8	1615.6	1630.3	1627.4
5°	1631.8	1624.4	1605.2	1618.5	1614.1
7.5°	1618.5	1609.6	1589.0	1594.9	1587.5
10°	1600.8	1590.4	1560.9	1556.5	1547.6
12.5°	1578.6	1565.3	1525.5	1516.6	1500.4
15°	1552.1	1535.8	1485.6	1457.5	1442.8
17.5°	1521.0	1497.4	1435.4	1402.9	1379.3
20°	1485.6	1456.1	1382.2	1345.3	1312.8
22.5°	1447.2	1413.2	1327.6	1277.4	1255.2
25°	1408.8	1361.6	1264.1	1203.5	1181.4
27.5°	1363.0	1312.8	1205.0	1135.6	1101.6
30°	1314.3	1258.2	1140.0	1064.7	1024.9
32.5°	1267.0	1199.1	1078.0	989.4	952.5
35°	1213.9	1138.6	1008.6	915.6	883.1
37.5°	1162.2	1081.0	943.6	841.7	804.8
40°	1107.6	1019.0	875.7	770.9	732.5
42.5°	1051.4	956.9	807.8	698.5	661.6
45°	992.4	893.4	738.4	633.5	598.1
47.5°	936.3	831.4	671.9	567.1	534.6
50°	874.2	769.4	606.9	505.0	474.0
52.5°	813.7	702.9	544.9	447.5	419.4
55°	754.6	639.4	479.9	391.3	363.3
57.5°	694.1	575.9	422.3	339.7	316.0
60°	632.0	513.9	361.8	286.5	262.9
62.5°	571.5	453.4	310.1	239.2	227.4
65°	509.5	389.9	257.0	206.7	202.3
67.5°	450.4	330.8	206.7	181.6	177.2
70°	388.4	273.2	171.3	156.5	150.6
72.5°	329.3	220.0	143.2	131.4	128.5
75°	271.7	168.3	118.1	107.8	106.3
77.5°	214.1	119.6	93.0	87.1	84.2
80°	161.0	85.7	70.9	65.0	65.0
82.5°	112.2	57.6	48.7	45.8	45.8
85°	63.5	32.5	28.1	28.1	28.1
87.5°	23.6	11.8	11.8	10.3	10.3
90°	0.3	4.6	11.6	11.1	11.3
92.5°	5.1	16.2	52.6	24.2	20.9
95°	12.0	29.4	134.0	50.6	39.0
97.5°	17.8	38.8	218.4	101.6	65.3
100°	26.3	47.5	270.0	202.2	122.4
102.5°	34.2	55.4	271.8	341.8	238.6
105°	41.7	62.9	253.3	452.8	385.2
107.5°	49.9	70.4	236.2	493.0	484.0
110°	58.1	78.2	224.6	486.4	524.4

TEST NUMBER: P999346

CATALOG NUMBER: SA2XXRDIP-B1005D330UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.6	85.4	217.1	464.4	523.7
115°	73.5	92.8	211.9	437.4	506.9
117.5°	81.7	100.2	209.2	411.6	481.6
120°	89.2	107.3	206.8	388.4	457.4
122.5°	96.4	114.6	205.4	370.5	432.1
125°	102.5	121.4	203.7	354.3	411.2
127.5°	107.7	127.6	202.7	340.4	391.7
130°	112.1	133.3	202.0	326.4	375.7
132.5°	116.2	138.8	201.7	311.9	358.9
135°	120.3	143.6	201.3	297.8	340.8
137.5°	124.1	147.6	201.3	283.4	323.4
140°	128.5	151.4	201.0	270.7	305.3
142.5°	133.0	154.5	201.0	258.6	287.1
145°	137.4	158.0	200.3	248.6	272.1
147.5°	142.2	160.6	199.3	240.0	258.8
150°	147.0	163.4	198.3	232.4	247.1
152.5°	151.8	166.2	196.6	226.2	237.2
155°	156.2	168.7	194.5	220.0	228.7
157.5°	160.0	170.8	192.4	214.2	221.2
160°	163.7	172.8	190.4	208.3	214.0
162.5°	167.5	174.4	188.7	202.8	207.1
165°	170.2	175.4	186.3	197.6	200.7
167.5°	172.6	176.4	184.2	192.8	194.5
170°	175.0	176.9	182.5	188.4	189.0
172.5°	176.4	177.4	180.5	184.4	184.6
175°	177.4	177.6	179.1	181.4	180.8
177.5°	178.1	177.8	177.8	179.1	178.1
180°	177.8	177.8	177.8	177.8	177.8

(END OF REPORT)