

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999368

Luminaire Tested: SA2XXRDIP-B1005D530UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999368
REPORT IS A COMBINATION OF REPORTS P987919 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D530UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5564.4 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999368

CATALOG NUMBER: SA2XXRDIP-B1005D530UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999368

CATALOG NUMBER: SA2XXRDIP-B1005D530UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	59
2	93	85	80	75	87	80	75	71	71	67	64	62	59	57	54	52	50
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	45	41	37	40	36	34
6	67	55	47	41	62	52	45	39	46	40	36	41	37	33	36	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24
9	54	42	34	29	50	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26869	26869	26869
5°	26912	25563	25373
10°	26648	24245	23445
15°	26282	22689	21246
20°	25798	20919	18947
25°	25301	19103	16843
30°	24634	17336	14546
35°	23981	15553	12573
40°	23317	13801	10541
45°	22545	11994	8768
50°	21747	10251	7139
55°	20917	8508	5668
60°	19952	6805	4287
65°	18841	5188	3486
70°	17496	3764	2772
75°	15814	2871	2117
80°	13365	1942	1421
85°	9337	890	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22545 cd/sqm

TEST NUMBER: P999368

CATALOG NUMBER: SA2XXRDIP-B1005D530UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	2.9
10°-20°	436.7	7.8
20°-30°	613.1	11.0
30°-40°	668.4	12.0
40°-50°	614.3	11.0
50°-60°	482.4	8.7
60°-70°	314.0	5.6
70°-80°	161.7	2.9
80°-90°	43.2	0.8
90°-100°	120.5	2.2
100°-110°	407.2	7.3
110°-120°	428.0	7.7
120°-130°	352.0	6.3
130°-140°	282.8	5.1
140°-150°	213.7	3.8
150°-160°	150.2	2.7
160°-170°	88.4	1.6
170°-180°	28.8	0.5
0°-30°	1209.0	21.7
0°-40°	1877.3	33.7
0°-60°	2974.0	53.4
0°-90°	3492.9	62.8
90°-120°	955.6	17.2
90°-150°	1804.1	32.4
90°-180°	2071.0	37.2
0°-180°	5564.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1697	1690	1670	1684	1679	161
15°	1614	1598	1545	1516	1501	455
25°	1466	1416	1315	1252	1229	674
35°	1263	1184	1049	952	919	790
45°	1032	929	768	659	622	797
55°	785	665	499	407	378	701
65°	530	406	267	215	210	525
75°	283	175	123	112	111	299
85°	66	34	29	29	29	76
90°	1	8	19	19	19	5
95°	20	49	224	85	65	21
105°	70	105	423	757	644	74
115°	123	155	354	731	847	122
125°	171	203	340	592	687	152
135°	201	240	336	498	570	155
145°	230	264	335	416	455	144
155°	261	282	325	368	382	120
165°	284	293	311	330	335	80
175°	296	297	299	303	302	28
180°	297	297	297	297	297	

TEST NUMBER: P999368

CATALOG NUMBER: SA2XXRDIP-B1005D530UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1697.4	1697.4	1697.4	1697.4	1697.4
2.5°	1705.1	1697.4	1680.5	1695.9	1692.8
5°	1697.4	1689.8	1669.8	1683.6	1679.0
7.5°	1683.6	1674.4	1652.9	1659.0	1651.4
10°	1665.2	1654.4	1623.7	1619.1	1609.9
12.5°	1642.1	1628.3	1586.8	1577.6	1560.7
15°	1614.5	1597.6	1545.4	1516.2	1500.8
17.5°	1582.2	1557.6	1493.1	1459.3	1434.8
20°	1545.4	1514.6	1437.8	1399.4	1365.6
22.5°	1505.4	1470.1	1381.0	1328.8	1305.7
25°	1465.5	1416.3	1314.9	1252.0	1228.9
27.5°	1417.9	1365.6	1253.5	1181.3	1146.0
30°	1367.2	1308.8	1185.9	1107.6	1066.1
32.5°	1318.0	1247.3	1121.4	1029.2	990.8
35°	1262.7	1184.4	1049.2	952.4	918.6
37.5°	1208.9	1124.5	981.6	875.6	837.2
40°	1152.1	1059.9	910.9	801.9	761.9
42.5°	1093.7	995.4	840.3	726.6	688.2
45°	1032.3	929.4	768.1	659.0	622.1
47.5°	973.9	864.8	698.9	589.9	556.1
50°	909.4	800.3	631.4	525.4	493.1
52.5°	846.4	731.2	566.8	465.5	436.3
55°	785.0	665.2	499.2	407.1	377.9
57.5°	722.0	599.1	439.3	353.3	328.7
60°	657.5	534.6	376.4	298.0	273.4
62.5°	594.5	471.6	322.6	248.9	236.6
65°	530.0	405.5	267.3	215.1	210.5
67.5°	468.5	344.1	215.1	188.9	184.3
70°	404.0	284.2	178.2	162.8	156.7
72.5°	342.6	228.9	149.0	136.7	133.6
75°	282.7	175.1	122.9	112.1	110.6
77.5°	222.7	124.4	96.8	90.6	87.6
80°	167.4	89.1	73.7	67.6	67.6
82.5°	116.7	59.9	50.7	47.6	47.6
85°	66.1	33.8	29.2	29.2	29.2
87.5°	24.6	12.3	12.3	10.8	10.8
90°	0.6	7.8	19.4	18.6	18.9
92.5°	8.6	27.2	88.0	40.6	34.9
95°	20.0	49.2	224.0	84.6	65.1
97.5°	29.7	64.8	365.1	169.7	109.1
100°	44.0	79.4	451.4	338.0	204.5
102.5°	57.1	92.6	454.2	571.4	398.8
105°	69.7	105.1	423.4	756.8	643.9
107.5°	83.4	117.7	394.8	823.9	809.1
110°	97.1	130.6	375.4	813.0	876.5



TEST NUMBER: P999368

CATALOG NUMBER: SA2XXRDIP-B1005D530UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.7	142.9	362.8	776.2	875.3
115°	122.8	155.1	354.2	731.0	847.3
117.5°	136.6	167.4	349.7	687.9	805.1
120°	149.1	179.4	345.7	649.4	764.5
122.5°	161.1	191.7	343.4	619.4	722.2
125°	171.4	202.8	340.5	592.2	687.4
127.5°	180.0	213.4	338.8	569.1	654.8
130°	187.4	222.8	337.7	545.6	627.9
132.5°	194.3	232.0	337.1	521.3	599.9
135°	201.1	240.0	336.5	497.7	569.7
137.5°	207.4	246.8	336.5	473.6	540.5
140°	214.8	253.1	336.0	452.6	510.2
142.5°	222.3	258.2	336.0	432.2	479.9
145°	229.7	264.0	334.8	415.7	454.8
147.5°	237.7	268.6	333.1	401.1	432.5
150°	245.7	273.2	331.4	388.5	413.1
152.5°	253.7	277.7	328.5	378.0	396.5
155°	261.1	282.0	325.1	367.6	382.2
157.5°	267.4	285.4	321.7	358.0	369.7
160°	273.7	288.8	318.3	348.2	357.7
162.5°	280.0	291.4	315.4	339.1	346.2
165°	284.5	293.1	311.4	330.2	335.4
167.5°	288.5	294.8	308.0	322.2	325.1
170°	292.5	295.6	305.1	314.8	316.0
172.5°	294.8	296.6	301.7	308.2	308.5
175°	296.5	296.8	299.4	303.1	302.3
177.5°	297.7	297.1	297.1	299.4	297.7
180°	297.1	297.1	297.1	297.1	297.1

(END OF REPORT)