

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999385

Luminaire Tested: SA2XXRDIP-B1005D530UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999385
REPORT IS A COMBINATION OF REPORTS P987936 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D530UB50-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5178.0 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999385

CATALOG NUMBER: SA2XXRDIP-B1005D530UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999385

CATALOG NUMBER: SA2XXRDIP-B1005D530UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	102	98	94	90	96	92	89	86	81	79	77	72	70	68	63	61	60
2	93	86	80	75	87	81	76	71	72	68	64	64	61	58	56	54	52
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45
4	79	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39
5	72	61	53	47	68	58	51	45	52	46	41	46	42	38	41	37	34
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	37	34	31
7	62	50	42	36	58	47	40	35	43	37	33	39	34	30	34	31	28
8	58	46	38	33	54	43	36	31	39	33	29	35	31	27	32	28	25
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	29	26	23
10	51	39	31	27	48	37	30	26	34	28	24	30	26	22	27	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25830	25830	25830
5°	25872	24574	24392
10°	25617	23307	22538
15°	25266	21811	20425
20°	24800	20110	18215
25°	24322	18365	16192
30°	23681	16665	13984
35°	23054	14951	12087
40°	22417	13268	10134
45°	21674	11530	8430
50°	20905	9854	6862
55°	20107	8179	5449
60°	19178	6541	4123
65°	18112	4988	3351
70°	16820	3618	2664
75°	15199	2759	2035
80°	12854	1868	1367
85°	8970	857	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21674 cd/sqm

TEST NUMBER: P999385

CATALOG NUMBER: SA2XXRDIP-B1005D530UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.9	3.0
10°-20°	419.8	8.1
20°-30°	589.4	11.4
30°-40°	642.5	12.4
40°-50°	590.5	11.4
50°-60°	463.8	9.0
60°-70°	301.9	5.8
70°-80°	155.4	3.0
80°-90°	41.5	0.8
90°-100°	40.3	0.8
100°-110°	128.0	2.5
110°-120°	219.1	4.2
120°-130°	288.1	5.6
130°-140°	323.4	6.2
140°-150°	317.1	6.1
150°-160°	266.0	5.1
160°-170°	176.4	3.4
170°-180°	61.7	1.2
0°-30°	1162.2	22.4
0°-40°	1804.7	34.9
0°-60°	2859.0	55.2
0°-90°	3357.8	64.8
90°-120°	387.4	7.5
90°-150°	1316.0	25.4
90°-180°	1820.0	35.1
0°-180°	5178.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1632	1632	1632	1632	1632	
5°	1632	1624	1605	1618	1614	155
15°	1552	1536	1486	1458	1443	437
25°	1409	1362	1264	1204	1181	648
35°	1214	1139	1009	916	883	760
45°	992	893	738	634	598	766
55°	755	639	480	391	363	674
65°	510	390	257	207	202	505
75°	272	168	118	108	106	287
85°	64	32	28	28	28	73
90°	0	7	19	18	19	5
95°	29	34	35	35	34	32
105°	118	120	121	122	122	125
115°	220	223	222	221	220	217
125°	320	325	323	321	321	286
135°	414	420	421	420	419	320
145°	502	506	509	510	508	314
155°	574	576	577	580	578	264
165°	625	624	624	628	625	176
175°	650	648	647	651	648	62
180°	651	651	651	651	651	

TEST NUMBER: P999385

CATALOG NUMBER: SA2XXRDIP-B1005D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.8	1631.8	1631.8	1631.8	1631.8
2.5°	1639.2	1631.8	1615.6	1630.3	1627.4
5°	1631.8	1624.4	1605.2	1618.5	1614.1
7.5°	1618.5	1609.6	1589.0	1594.9	1587.5
10°	1600.8	1590.4	1560.9	1556.5	1547.6
12.5°	1578.6	1565.3	1525.5	1516.6	1500.4
15°	1552.1	1535.8	1485.6	1457.5	1442.8
17.5°	1521.0	1497.4	1435.4	1402.9	1379.3
20°	1485.6	1456.1	1382.2	1345.3	1312.8
22.5°	1447.2	1413.2	1327.6	1277.4	1255.2
25°	1408.8	1361.6	1264.1	1203.5	1181.4
27.5°	1363.0	1312.8	1205.0	1135.6	1101.6
30°	1314.3	1258.2	1140.0	1064.7	1024.9
32.5°	1267.0	1199.1	1078.0	989.4	952.5
35°	1213.9	1138.6	1008.6	915.6	883.1
37.5°	1162.2	1081.0	943.6	841.7	804.8
40°	1107.6	1019.0	875.7	770.9	732.5
42.5°	1051.4	956.9	807.8	698.5	661.6
45°	992.4	893.4	738.4	633.5	598.1
47.5°	936.3	831.4	671.9	567.1	534.6
50°	874.2	769.4	606.9	505.0	474.0
52.5°	813.7	702.9	544.9	447.5	419.4
55°	754.6	639.4	479.9	391.3	363.3
57.5°	694.1	575.9	422.3	339.7	316.0
60°	632.0	513.9	361.8	286.5	262.9
62.5°	571.5	453.4	310.1	239.2	227.4
65°	509.5	389.9	257.0	206.7	202.3
67.5°	450.4	330.8	206.7	181.6	177.2
70°	388.4	273.2	171.3	156.5	150.6
72.5°	329.3	220.0	143.2	131.4	128.5
75°	271.7	168.3	118.1	107.8	106.3
77.5°	214.1	119.6	93.0	87.1	84.2
80°	161.0	85.7	70.9	65.0	65.0
82.5°	112.2	57.6	48.7	45.8	45.8
85°	63.5	32.5	28.1	28.1	28.1
87.5°	23.6	11.8	11.8	10.3	10.3
90°	0.5	7.1	19.2	18.1	18.7
92.5°	12.1	16.5	17.0	17.6	17.6
95°	28.6	34.1	35.2	35.2	34.1
97.5°	47.8	52.7	54.9	54.9	54.9
100°	69.8	74.2	75.8	75.8	75.3
102.5°	92.8	96.1	98.3	98.9	98.3
105°	118.1	119.8	120.9	122.0	122.0
107.5°	143.4	145.6	145.6	146.1	143.4
110°	167.6	170.9	170.9	170.9	169.2

TEST NUMBER: P999385

CATALOG NUMBER: SA2XXRDIP-B1005D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	193.9	197.2	196.7	195.0	193.9
115°	219.8	223.1	222.0	221.4	219.8
117.5°	245.6	250.0	247.2	245.6	243.9
120°	271.4	275.8	271.4	271.4	269.8
122.5°	295.0	300.5	297.8	296.1	295.0
125°	319.7	324.7	323.0	321.4	320.8
127.5°	343.9	350.0	347.8	345.6	343.9
130°	366.4	373.6	372.5	371.4	369.2
132.5°	391.7	397.2	397.8	395.0	393.4
135°	413.7	419.7	420.8	420.3	418.6
137.5°	437.9	442.8	443.9	443.4	441.2
140°	459.3	464.2	467.0	467.0	464.8
142.5°	481.3	486.2	487.9	488.4	486.2
145°	502.1	506.0	509.3	509.8	507.6
147.5°	520.8	525.8	528.0	529.1	526.9
150°	540.1	543.3	545.5	547.2	545.5
152.5°	557.1	560.4	563.1	565.3	563.1
155°	574.1	575.8	577.4	580.2	578.5
157.5°	588.9	590.0	591.1	595.0	592.2
160°	602.1	603.2	603.8	607.1	604.9
162.5°	614.2	614.2	614.8	618.6	615.9
165°	624.7	624.1	624.1	628.0	625.2
167.5°	634.0	632.3	632.3	636.2	633.4
170°	641.1	639.5	638.9	642.8	639.5
172.5°	646.1	644.4	643.9	647.7	644.4
175°	649.9	648.3	647.2	651.0	647.7
177.5°	652.1	650.5	649.4	652.7	649.4
180°	651.0	651.0	651.0	651.0	651.0

(END OF REPORT)