

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000223

Luminaire Tested: SA2XXRDIP-B865D925UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000223
REPORT IS A COMBINATION OF REPORTS P988783 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D925UB27-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6220.0 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000223

CATALOG NUMBER: SA2XXRDIP-B865D925UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000223

CATALOG NUMBER: SA2XXRDIP-B865D925UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	98	94	90	87	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	82	76	71	82	76	71	67	64	61	57	53	51	48	43	42	40
3	82	73	66	60	75	67	61	56	57	52	49	48	44	41	39	36	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	58	50	44	63	54	47	42	46	41	36	39	35	31	32	29	27
6	64	52	44	39	59	48	41	36	41	36	32	35	31	28	29	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	23	21
8	55	43	35	30	51	40	33	29	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22875	22875	22875
5°	22912	21762	21601
10°	22686	20640	19959
15°	22375	19315	18088
20°	21962	17809	16131
25°	21539	16263	14339
30°	20971	14759	12384
35°	20416	13240	10703
40°	19851	11750	8975
45°	19193	10211	7465
50°	18514	8727	6077
55°	17808	7243	4825
60°	16984	5793	3651
65°	16040	4417	2968
70°	14893	3204	2360
75°	13459	2443	1803
80°	11377	1655	1209
85°	7939	756	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19193 cd/sqm

TEST NUMBER: P1000223

CATALOG NUMBER: SA2XXRDIP-B865D925UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	2.2
10°-20°	371.8	6.0
20°-30°	522.0	8.4
30°-40°	569.0	9.1
40°-50°	523.0	8.4
50°-60°	410.7	6.6
60°-70°	267.3	4.3
70°-80°	137.6	2.2
80°-90°	38.5	0.6
90°-100°	71.8	1.2
100°-110°	228.2	3.7
110°-120°	390.5	6.3
120°-130°	513.6	8.3
130°-140°	576.5	9.3
140°-150°	565.4	9.1
150°-160°	474.2	7.6
160°-170°	314.5	5.1
170°-180°	109.9	1.8
0°-30°	1029.2	16.5
0°-40°	1598.2	25.7
0°-60°	2531.9	40.7
0°-90°	2975.3	47.8
90°-120°	690.5	11.1
90°-150°	2346.0	37.7
90°-180°	3245.0	52.2
0°-180°	6220.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1438	1422	1433	1429	137
15°	1374	1360	1316	1291	1278	387
25°	1248	1206	1119	1066	1046	574
35°	1075	1008	893	811	782	673
45°	879	791	654	561	530	679
55°	668	566	425	347	322	597
65°	451	345	228	183	179	447
75°	241	149	105	96	94	254
85°	56	29	25	25	25	65
90°	1	13	34	32	33	6
95°	51	61	63	63	61	57
105°	211	214	216	217	217	222
115°	392	398	396	395	392	388
125°	570	579	576	573	572	509
135°	738	748	750	749	746	570
145°	895	902	908	909	905	559
155°	1023	1026	1029	1034	1031	471
165°	1114	1113	1113	1119	1114	314
175°	1159	1156	1154	1161	1155	110
180°	1161	1161	1161	1161	1161	

TEST NUMBER: P1000223

CATALOG NUMBER: SA2XXRDIP-B865D925UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1445.1	1445.1	1445.1	1445.1	1445.1
2.5°	1451.6	1445.1	1430.7	1443.8	1441.2
5°	1445.1	1438.5	1421.5	1433.3	1429.4
7.5°	1433.3	1425.5	1407.2	1412.4	1405.9
10°	1417.6	1408.5	1382.3	1378.4	1370.5
12.5°	1398.0	1386.2	1350.9	1343.1	1328.7
15°	1374.5	1360.1	1315.6	1290.8	1277.7
17.5°	1347.0	1326.1	1271.2	1242.4	1221.5
20°	1315.6	1289.5	1224.1	1191.4	1162.6
22.5°	1281.6	1251.5	1175.7	1131.2	1111.6
25°	1247.6	1205.8	1119.4	1065.8	1046.2
27.5°	1207.1	1162.6	1067.1	1005.7	975.6
30°	1163.9	1114.2	1009.6	942.9	907.6
32.5°	1122.1	1061.9	954.7	876.2	843.5
35°	1075.0	1008.3	893.2	810.8	782.0
37.5°	1029.2	957.3	835.7	745.4	712.7
40°	980.8	902.4	775.5	682.7	648.7
42.5°	931.1	847.4	715.3	618.6	585.9
45°	878.8	791.2	653.9	561.0	529.6
47.5°	829.1	736.3	595.0	502.2	473.4
50°	774.2	681.3	537.5	447.3	419.8
52.5°	720.6	622.5	482.6	396.3	371.4
55°	668.3	566.3	425.0	346.6	321.7
57.5°	614.7	510.0	374.0	300.8	279.9
60°	559.7	455.1	320.4	253.7	232.8
62.5°	506.1	401.5	274.6	211.9	201.4
65°	451.2	345.3	227.6	183.1	179.2
67.5°	398.9	292.9	183.1	160.9	156.9
70°	343.9	241.9	151.7	138.6	133.4
72.5°	291.6	194.9	126.9	116.4	113.8
75°	240.6	149.1	104.6	95.5	94.2
77.5°	189.6	105.9	82.4	77.2	74.5
80°	142.5	75.9	62.8	57.5	57.5
82.5°	99.4	51.0	43.2	40.5	40.5
85°	56.2	28.8	24.8	24.8	24.8
87.5°	20.9	10.5	10.5	9.2	9.2
90°	1.0	12.7	34.3	32.3	33.3
92.5°	21.5	29.4	30.4	31.3	31.3
95°	50.9	60.7	62.7	62.7	60.7
97.5°	85.2	94.0	97.9	97.9	97.9
100°	124.4	132.2	135.2	135.2	134.2
102.5°	165.5	171.4	175.3	176.3	175.3
105°	210.6	213.5	215.5	217.4	217.4
107.5°	255.6	259.5	259.5	260.5	255.6
110°	298.7	304.6	304.6	304.6	301.6

TEST NUMBER: P1000223

CATALOG NUMBER: SA2XXRDIP-B865D925UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	345.7	351.6	350.6	347.7	345.7
115°	391.7	397.6	395.7	394.7	391.7
117.5°	437.8	445.6	440.7	437.8	434.8
120°	483.8	491.6	483.8	483.8	480.9
122.5°	525.9	535.7	530.8	527.9	525.9
125°	570.0	578.8	575.9	572.9	572.0
127.5°	613.1	623.9	619.9	616.0	613.1
130°	653.2	666.0	664.0	662.1	658.1
132.5°	698.3	708.1	709.1	704.2	701.2
135°	737.5	748.2	750.2	749.2	746.3
137.5°	780.6	789.4	791.3	790.4	786.4
140°	818.8	827.6	832.5	832.5	828.5
142.5°	857.9	866.7	869.7	870.7	866.7
145°	895.1	902.0	907.9	908.9	904.9
147.5°	928.4	937.3	941.2	943.1	939.2
150°	962.7	968.6	972.5	975.5	972.5
152.5°	993.1	999.0	1003.9	1007.8	1003.9
155°	1023.4	1026.4	1029.3	1034.2	1031.3
157.5°	1049.9	1051.8	1053.8	1060.7	1055.8
160°	1073.4	1075.4	1076.3	1082.2	1078.3
162.5°	1094.9	1094.9	1095.9	1102.8	1097.9
165°	1113.5	1112.6	1112.6	1119.4	1114.5
167.5°	1130.2	1127.3	1127.3	1134.1	1129.2
170°	1142.9	1140.0	1139.0	1145.9	1140.0
172.5°	1151.7	1148.8	1147.8	1154.7	1148.8
175°	1158.6	1155.7	1153.7	1160.6	1154.7
177.5°	1162.5	1159.6	1157.6	1163.5	1157.6
180°	1160.6	1160.6	1160.6	1160.6	1160.6

(END OF REPORT)