

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999408

Luminaire Tested: SA2XXRDIP-B1005D725UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999408
REPORT IS A COMBINATION OF REPORTS P987959 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D725UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6261.2 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999408

CATALOG NUMBER: SA2XXRDIP-B1005D725UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999408

CATALOG NUMBER: SA2XXRDIP-B1005D725UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45
3	84	74	67	62	77	69	63	58	60	56	52	52	48	45	44	41	39
4	77	66	58	53	71	62	55	50	54	49	45	47	43	39	40	37	34
5	71	59	51	45	66	56	49	43	49	43	39	42	38	34	36	33	30
6	65	53	45	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	60	48	41	35	56	46	39	34	40	34	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	24	28	24	22
9	53	40	33	28	49	38	31	27	34	28	25	30	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26869	26869	26869
5°	26912	25563	25373
10°	26648	24245	23445
15°	26282	22689	21246
20°	25798	20919	18947
25°	25301	19103	16843
30°	24634	17336	14546
35°	23981	15553	12573
40°	23317	13801	10541
45°	22545	11994	8768
50°	21747	10251	7139
55°	20917	8508	5668
60°	19952	6805	4287
65°	18841	5188	3486
70°	17496	3764	2772
75°	15814	2871	2117
80°	13365	1942	1421
85°	9337	890	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22545 cd/sqm

TEST NUMBER: P999408

CATALOG NUMBER: SA2XXRDIP-B1005D725UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	2.5
10°-20°	436.7	7.0
20°-30°	613.1	9.8
30°-40°	668.4	10.7
40°-50°	614.3	9.8
50°-60°	482.4	7.7
60°-70°	314.0	5.0
70°-80°	161.7	2.6
80°-90°	43.8	0.7
90°-100°	160.9	2.6
100°-110°	544.0	8.7
110°-120°	571.8	9.1
120°-130°	470.2	7.5
130°-140°	377.9	6.0
140°-150°	285.5	4.6
150°-160°	200.7	3.2
160°-170°	118.2	1.9
170°-180°	38.4	0.6
0°-30°	1209.0	19.3
0°-40°	1877.3	30.0
0°-60°	2974.0	47.5
0°-90°	3493.5	55.8
90°-120°	1276.8	20.4
90°-150°	2410.4	38.5
90°-180°	2768.0	44.2
0°-180°	6261.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1697	1690	1670	1684	1679	161
15°	1614	1598	1545	1516	1501	455
25°	1466	1416	1315	1252	1229	674
35°	1263	1184	1049	952	919	790
45°	1032	929	768	659	622	797
55°	785	665	499	407	378	701
65°	530	406	267	215	210	525
75°	283	175	123	112	111	299
85°	66	34	29	29	29	76
90°	1	10	26	25	25	5
95°	27	66	299	113	87	28
105°	93	140	566	1011	860	99
115°	164	207	473	977	1132	163
125°	229	271	455	791	918	204
135°	269	321	450	665	761	208
145°	307	353	447	555	608	193
155°	349	377	434	491	511	161
165°	380	392	416	441	448	107
175°	396	397	400	405	404	38
180°	397	397	397	397	397	

TEST NUMBER: P999408

CATALOG NUMBER: SA2XXRDIP-B1005D725UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1697.4	1697.4	1697.4	1697.4	1697.4
2.5°	1705.1	1697.4	1680.5	1695.9	1692.8
5°	1697.4	1689.8	1669.8	1683.6	1679.0
7.5°	1683.6	1674.4	1652.9	1659.0	1651.4
10°	1665.2	1654.4	1623.7	1619.1	1609.9
12.5°	1642.1	1628.3	1586.8	1577.6	1560.7
15°	1614.5	1597.6	1545.4	1516.2	1500.8
17.5°	1582.2	1557.6	1493.1	1459.3	1434.8
20°	1545.4	1514.6	1437.8	1399.4	1365.6
22.5°	1505.4	1470.1	1381.0	1328.8	1305.7
25°	1465.5	1416.3	1314.9	1252.0	1228.9
27.5°	1417.9	1365.6	1253.5	1181.3	1146.0
30°	1367.2	1308.8	1185.9	1107.6	1066.1
32.5°	1318.0	1247.3	1121.4	1029.2	990.8
35°	1262.7	1184.4	1049.2	952.4	918.6
37.5°	1208.9	1124.5	981.6	875.6	837.2
40°	1152.1	1059.9	910.9	801.9	761.9
42.5°	1093.7	995.4	840.3	726.6	688.2
45°	1032.3	929.4	768.1	659.0	622.1
47.5°	973.9	864.8	698.9	589.9	556.1
50°	909.4	800.3	631.4	525.4	493.1
52.5°	846.4	731.2	566.8	465.5	436.3
55°	785.0	665.2	499.2	407.1	377.9
57.5°	722.0	599.1	439.3	353.3	328.7
60°	657.5	534.6	376.4	298.0	273.4
62.5°	594.5	471.6	322.6	248.9	236.6
65°	530.0	405.5	267.3	215.1	210.5
67.5°	468.5	344.1	215.1	188.9	184.3
70°	404.0	284.2	178.2	162.8	156.7
72.5°	342.6	228.9	149.0	136.7	133.6
75°	282.7	175.1	122.9	112.1	110.6
77.5°	222.7	124.4	96.8	90.6	87.6
80°	167.4	89.1	73.7	67.6	67.6
82.5°	116.7	59.9	50.7	47.6	47.6
85°	66.1	33.8	29.2	29.2	29.2
87.5°	24.6	12.3	12.3	10.8	10.8
90°	0.8	10.4	26.0	24.8	25.2
92.5°	11.5	36.3	117.6	54.2	46.6
95°	26.7	65.6	299.2	113.0	87.0
97.5°	39.7	86.6	487.8	226.7	145.8
100°	58.8	106.1	603.1	451.6	273.3
102.5°	76.3	123.7	606.9	763.4	532.8
105°	93.1	140.5	565.7	1011.1	860.3
107.5°	111.5	157.2	527.5	1100.8	1081.0
110°	129.8	174.4	501.5	1086.3	1171.0

TEST NUMBER: P999408

CATALOG NUMBER: SA2XXRDIP-B1005D725UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	146.6	190.9	484.8	1037.0	1169.5
115°	164.1	207.3	473.3	976.8	1132.1
117.5°	182.4	223.7	467.2	919.1	1075.6
120°	199.2	239.7	461.8	867.6	1021.4
122.5°	215.3	256.1	458.8	827.5	964.9
125°	229.0	271.0	455.0	791.2	918.4
127.5°	240.5	285.2	452.7	760.4	874.8
130°	250.4	297.7	451.2	729.0	839.0
132.5°	259.6	309.9	450.4	696.6	801.6
135°	268.7	320.6	449.6	664.9	761.1
137.5°	277.1	329.8	449.6	632.8	722.2
140°	287.0	338.2	448.9	604.6	681.7
142.5°	297.0	345.0	448.9	577.5	641.2
145°	306.9	352.7	447.3	555.3	607.7
147.5°	317.6	358.8	445.1	535.9	577.9
150°	328.3	364.9	442.8	519.1	551.9
152.5°	338.9	371.0	438.9	505.0	529.8
155°	348.9	376.8	434.4	491.2	510.7
157.5°	357.3	381.3	429.8	478.2	493.9
160°	365.7	385.9	425.2	465.3	477.9
162.5°	374.1	389.4	421.4	453.1	462.6
165°	380.2	391.6	416.0	441.2	448.1
167.5°	385.5	393.9	411.5	430.6	434.4
170°	390.9	395.0	407.6	420.6	422.2
172.5°	393.9	396.2	403.1	411.8	412.2
175°	396.2	396.6	400.0	405.0	403.8
177.5°	397.7	397.0	397.0	400.0	397.7
180°	397.0	397.0	397.0	397.0	397.0

(END OF REPORT)