

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000246

Luminaire Tested: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000246
REPORT IS A COMBINATION OF REPORTS P988806 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6611.2 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000246

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000246

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46	46	46
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45	39	39	39
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38	34	34	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29	29	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25	25	25
5	69	57	50	44	63	53	46	41	45	40	36	37	34	31	30	28	26	22	22	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	25	23	20	18	18	18
8	54	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14	14	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23168	23168	23168
5°	23205	22040	21878
10°	22975	20905	20215
15°	22660	19562	18318
20°	22242	18036	16337
25°	21815	16472	14523
30°	21240	14947	12542
35°	20676	13409	10840
40°	20106	11900	9088
45°	19440	10340	7560
50°	18751	8839	6156
55°	18034	7337	4886
60°	17202	5867	3698
65°	16243	4474	3006
70°	15084	3244	2390
75°	13633	2476	1826
80°	11529	1676	1226
85°	8052	768	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19440 cd/sqm

TEST NUMBER: P1000246

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	2.1
10°-20°	376.6	5.7
20°-30°	528.7	8.0
30°-40°	576.3	8.7
40°-50°	529.7	8.0
50°-60°	416.0	6.3
60°-70°	270.7	4.1
70°-80°	139.4	2.1
80°-90°	38.9	0.6
90°-100°	209.2	3.2
100°-110°	707.2	10.7
110°-120°	743.4	11.2
120°-130°	611.3	9.2
130°-140°	491.2	7.4
140°-150°	371.1	5.6
150°-160°	260.9	3.9
160°-170°	153.6	2.3
170°-180°	50.0	0.8
0°-30°	1042.4	15.8
0°-40°	1618.7	24.5
0°-60°	2564.3	38.8
0°-90°	3013.3	45.6
90°-120°	1659.8	25.1
90°-150°	3133.4	47.4
90°-180°	3598.0	54.4
0°-180°	6611.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1464	1464	1464	1464	1464	
5°	1464	1457	1440	1452	1448	139
15°	1392	1378	1332	1307	1294	392
25°	1264	1221	1134	1080	1060	581
35°	1089	1021	905	821	792	681
45°	890	801	662	568	536	687
55°	677	574	430	351	326	605
65°	457	350	230	185	182	453
75°	244	151	106	97	95	258
85°	57	29	25	25	25	65
90°	1	13	34	32	33	5
95°	35	85	389	147	113	36
105°	121	183	735	1314	1118	129
115°	213	269	615	1270	1472	212
125°	298	352	592	1029	1194	265
135°	349	417	584	864	989	270
145°	399	458	582	722	790	250
155°	454	490	565	639	664	209
165°	494	509	541	574	582	139
175°	515	516	520	526	525	49
180°	516	516	516	516	516	

TEST NUMBER: P1000246

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1463.6	1463.6	1463.6	1463.6	1463.6
2.5°	1470.2	1463.6	1449.0	1462.2	1459.6
5°	1463.6	1456.9	1439.7	1451.6	1447.7
7.5°	1451.6	1443.7	1425.2	1430.4	1423.8
10°	1435.7	1426.5	1400.0	1396.0	1388.1
12.5°	1415.9	1404.0	1368.2	1360.3	1345.7
15°	1392.0	1377.5	1332.4	1307.3	1294.0
17.5°	1364.2	1343.0	1287.4	1258.3	1237.1
20°	1332.4	1305.9	1239.7	1206.6	1177.5
22.5°	1298.0	1267.5	1190.7	1145.7	1125.8
25°	1263.6	1221.2	1133.8	1079.5	1059.6
27.5°	1222.5	1177.5	1080.8	1018.5	988.1
30°	1178.8	1128.5	1022.5	955.0	919.2
32.5°	1136.4	1075.5	966.9	887.4	854.3
35°	1088.7	1021.2	904.6	821.2	792.0
37.5°	1042.4	969.5	846.3	755.0	721.8
40°	993.4	913.9	785.4	691.4	656.9
42.5°	943.0	858.3	724.5	626.5	593.4
45°	890.1	801.3	662.2	568.2	536.4
47.5°	839.7	745.7	602.6	508.6	479.5
50°	784.1	690.1	544.4	453.0	425.2
52.5°	729.8	630.5	488.7	401.3	376.2
55°	676.8	573.5	430.5	351.0	325.8
57.5°	622.5	516.6	378.8	304.6	283.4
60°	566.9	460.9	324.5	257.0	235.8
62.5°	512.6	406.6	278.1	214.6	204.0
65°	456.9	349.7	230.5	185.4	181.5
67.5°	404.0	296.7	185.4	162.9	158.9
70°	348.3	245.0	153.6	140.4	135.1
72.5°	295.4	197.3	128.5	117.9	115.2
75°	243.7	151.0	106.0	96.7	95.4
77.5°	192.1	107.3	83.4	78.1	75.5
80°	144.4	76.8	63.6	58.3	58.3
82.5°	100.7	51.7	43.7	41.1	41.1
85°	57.0	29.1	25.2	25.2	25.2
87.5°	21.2	10.6	10.6	9.3	9.3
90°	1.0	13.4	33.7	32.2	32.7
92.5°	14.9	47.2	152.8	70.4	60.5
95°	34.7	85.4	389.0	146.9	113.1
97.5°	51.6	112.6	634.1	294.8	189.5
100°	76.4	137.9	784.0	587.0	355.3
102.5°	99.2	160.8	788.9	992.4	692.7
105°	121.1	182.6	735.4	1314.4	1118.4
107.5°	144.9	204.4	685.7	1431.1	1405.2
110°	168.7	226.8	652.0	1412.2	1522.3

TEST NUMBER: P1000246

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	190.5	248.1	630.2	1348.2	1520.3
115°	213.4	269.4	615.3	1269.8	1471.7
117.5°	237.2	290.8	607.3	1194.8	1398.3
120°	259.0	311.6	600.4	1127.8	1327.8
122.5°	279.8	333.0	596.4	1075.7	1254.4
125°	297.7	352.3	591.5	1028.6	1193.8
127.5°	312.6	370.6	588.5	988.4	1137.3
130°	325.5	387.0	586.5	947.8	1090.6
132.5°	337.4	402.9	585.5	905.6	1042.0
135°	349.3	416.8	584.5	864.4	989.4
137.5°	360.2	428.7	584.5	822.7	938.8
140°	373.1	439.6	583.5	786.0	886.2
142.5°	386.0	448.6	583.5	750.8	833.6
145°	398.9	458.5	581.5	722.0	789.9
147.5°	412.8	466.4	578.6	696.7	751.2
150°	426.7	474.4	575.6	674.8	717.5
152.5°	440.6	482.3	570.6	656.4	688.7
155°	453.5	489.8	564.7	638.6	663.9
157.5°	464.4	495.6	558.7	621.8	642.1
160°	475.3	501.6	552.8	604.8	621.2
162.5°	486.3	506.1	547.8	589.0	601.4
165°	494.2	509.1	540.8	573.6	582.5
167.5°	501.1	512.1	534.9	559.7	564.7
170°	508.1	513.6	529.9	546.8	548.8
172.5°	512.1	515.0	524.0	535.4	535.9
175°	515.0	515.5	520.0	526.5	525.0
177.5°	517.0	516.0	516.0	520.0	517.0
180°	516.0	516.0	516.0	516.0	516.0

(END OF REPORT)