

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999448

Luminaire Tested: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999448
REPORT IS A COMBINATION OF REPORTS P987999 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7076.2 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999448

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999448

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	44	43	41
3	82	73	66	60	76	68	62	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	52	46	42	43	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	25	21	26	21	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26869	26869	26869
5°	26912	25563	25373
10°	26648	24245	23445
15°	26282	22689	21246
20°	25798	20919	18947
25°	25301	19103	16843
30°	24634	17336	14546
35°	23981	15553	12573
40°	23317	13801	10541
45°	22545	11994	8768
50°	21747	10251	7139
55°	20917	8508	5668
60°	19952	6805	4287
65°	18841	5188	3486
70°	17496	3764	2772
75°	15814	2871	2117
80°	13365	1942	1421
85°	9337	890	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22545 cd/sqm

TEST NUMBER: P999448

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	2.2
10°-20°	436.7	6.2
20°-30°	613.1	8.7
30°-40°	668.4	9.4
40°-50°	614.3	8.7
50°-60°	482.4	6.8
60°-70°	314.0	4.4
70°-80°	161.7	2.3
80°-90°	44.6	0.6
90°-100°	208.3	2.9
100°-110°	704.1	10.0
110°-120°	740.1	10.5
120°-130°	608.6	8.6
130°-140°	489.0	6.9
140°-150°	369.4	5.2
150°-160°	259.7	3.7
160°-170°	152.9	2.2
170°-180°	49.7	0.7
0°-30°	1209.0	17.1
0°-40°	1877.3	26.5
0°-60°	2974.0	42.0
0°-90°	3494.3	49.4
90°-120°	1652.4	23.4
90°-150°	3119.5	44.1
90°-180°	3582.0	50.6
0°-180°	7076.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1697	1690	1670	1684	1679	161
15°	1614	1598	1545	1516	1501	455
25°	1466	1416	1315	1252	1229	674
35°	1263	1184	1049	952	919	790
45°	1032	929	768	659	622	797
55°	785	665	499	407	378	701
65°	530	406	267	215	210	525
75°	283	175	123	112	111	299
85°	66	34	29	29	29	76
90°	1	13	34	32	33	6
95°	35	85	387	146	113	36
105°	120	182	732	1309	1113	128
115°	212	268	612	1264	1465	211
125°	296	351	589	1024	1188	263
135°	348	415	582	861	985	269
145°	397	456	579	719	786	249
155°	452	488	562	636	661	208
165°	492	507	538	571	580	139
175°	513	513	518	524	523	49
180°	514	514	514	514	514	

TEST NUMBER: P999448

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1697.4	1697.4	1697.4	1697.4	1697.4
2.5°	1705.1	1697.4	1680.5	1695.9	1692.8
5°	1697.4	1689.8	1669.8	1683.6	1679.0
7.5°	1683.6	1674.4	1652.9	1659.0	1651.4
10°	1665.2	1654.4	1623.7	1619.1	1609.9
12.5°	1642.1	1628.3	1586.8	1577.6	1560.7
15°	1614.5	1597.6	1545.4	1516.2	1500.8
17.5°	1582.2	1557.6	1493.1	1459.3	1434.8
20°	1545.4	1514.6	1437.8	1399.4	1365.6
22.5°	1505.4	1470.1	1381.0	1328.8	1305.7
25°	1465.5	1416.3	1314.9	1252.0	1228.9
27.5°	1417.9	1365.6	1253.5	1181.3	1146.0
30°	1367.2	1308.8	1185.9	1107.6	1066.1
32.5°	1318.0	1247.3	1121.4	1029.2	990.8
35°	1262.7	1184.4	1049.2	952.4	918.6
37.5°	1208.9	1124.5	981.6	875.6	837.2
40°	1152.1	1059.9	910.9	801.9	761.9
42.5°	1093.7	995.4	840.3	726.6	688.2
45°	1032.3	929.4	768.1	659.0	622.1
47.5°	973.9	864.8	698.9	589.9	556.1
50°	909.4	800.3	631.4	525.4	493.1
52.5°	846.4	731.2	566.8	465.5	436.3
55°	785.0	665.2	499.2	407.1	377.9
57.5°	722.0	599.1	439.3	353.3	328.7
60°	657.5	534.6	376.4	298.0	273.4
62.5°	594.5	471.6	322.6	248.9	236.6
65°	530.0	405.5	267.3	215.1	210.5
67.5°	468.5	344.1	215.1	188.9	184.3
70°	404.0	284.2	178.2	162.8	156.7
72.5°	342.6	228.9	149.0	136.7	133.6
75°	282.7	175.1	122.9	112.1	110.6
77.5°	222.7	124.4	96.8	90.6	87.6
80°	167.4	89.1	73.7	67.6	67.6
82.5°	116.7	59.9	50.7	47.6	47.6
85°	66.1	33.8	29.2	29.2	29.2
87.5°	24.6	12.3	12.3	10.8	10.8
90°	1.0	13.4	33.6	32.1	32.6
92.5°	14.8	47.0	152.1	70.2	60.3
95°	34.6	84.9	387.3	146.2	112.6
97.5°	51.4	112.2	631.3	293.5	188.7
100°	76.1	137.4	780.5	584.4	353.7
102.5°	98.8	160.0	785.4	988.0	689.6
105°	120.5	181.8	732.1	1308.6	1113.4
107.5°	144.2	203.6	682.7	1424.6	1399.0
110°	168.0	225.8	649.1	1405.9	1515.5

TEST NUMBER: P999448

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	189.7	247.0	627.4	1342.2	1513.6
115°	212.4	268.2	612.5	1264.1	1465.1
117.5°	236.1	289.5	604.6	1189.5	1392.0
120°	257.9	310.2	597.7	1122.8	1321.9
122.5°	278.6	331.5	593.8	1071.0	1248.8
125°	296.4	350.8	588.8	1024.0	1188.5
127.5°	311.2	369.0	585.9	984.0	1132.2
130°	324.1	385.3	583.9	943.5	1085.8
132.5°	335.9	401.1	582.9	901.5	1037.4
135°	347.8	415.0	581.9	860.6	985.0
137.5°	358.6	426.8	581.9	819.0	934.6
140°	371.5	437.6	580.9	782.4	882.2
142.5°	384.3	446.6	580.9	747.4	829.9
145°	397.2	456.4	578.9	718.8	786.4
147.5°	411.0	464.4	576.0	693.6	747.9
150°	424.8	472.2	573.0	671.8	714.3
152.5°	438.7	480.2	568.1	653.5	685.6
155°	451.5	487.6	562.2	635.8	660.9
157.5°	462.4	493.5	556.2	619.0	639.2
160°	473.2	499.4	550.3	602.2	618.5
162.5°	484.1	503.8	545.4	586.3	598.7
165°	492.0	506.8	538.4	571.0	579.9
167.5°	498.9	509.8	532.5	557.2	562.2
170°	505.8	511.3	527.6	544.4	546.3
172.5°	509.8	512.8	521.6	533.0	533.5
175°	512.8	513.2	517.7	524.1	522.6
177.5°	514.7	513.7	513.7	517.7	514.7
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)