

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999451

Luminaire Tested: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999451
REPORT IS A COMBINATION OF REPORTS P988002 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7433.0 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	50	50	45
2	91	84	78	73	84	78	73	69	67	63	60	56	54	52	47	45	44	44	44	39
3	83	75	68	62	77	69	63	59	60	55	52	51	47	45	42	40	38	38	38	34
4	77	67	59	53	71	62	56	50	54	49	45	46	42	39	39	36	34	34	34	30
5	71	60	52	46	66	56	49	44	49	43	39	42	38	35	35	32	30	30	30	27
6	66	54	46	41	61	51	44	39	44	39	35	38	34	31	32	29	27	27	27	24
7	61	49	42	36	56	46	39	35	40	35	31	35	31	28	30	27	24	24	24	22
8	57	45	38	32	53	42	36	31	37	32	28	32	28	25	28	25	22	22	22	20
9	53	41	34	29	49	39	32	28	34	29	25	30	26	23	26	23	20	20	20	18
10	50	38	31	27	46	36	30	25	32	27	23	28	24	21	24	21	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35136	35136	35136	35136
5°	35219	37321	35341	29815
10°	34832	39447	35078	24620
15°	34076	39460	34652	18497
20°	33166	32618	33887	15259
25°	32063	20381	32758	12981
30°	30656	13049	31490	11176
35°	28945	10028	29881	9564
40°	27037	8430	28191	8366
45°	24998	7174	26042	7022
50°	22907	6096	23978	6075
55°	20592	5297	21703	5228
60°	18538	4040	19518	3991
65°	16616	3041	17604	3448
70°	14495	2429	15634	2811
75°	12251	1860	13375	2126
80°	9732	1266	10467	1394
85°	6752	654	7402	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 32142 cd/sqm

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.5	2.8
10°-20°	587.7	7.9
20°-30°	756.4	10.2
30°-40°	717.5	9.7
40°-50°	615.0	8.3
50°-60°	468.3	6.3
60°-70°	295.3	4.0
70°-80°	147.3	2.0
80°-90°	41.2	0.6
90°-100°	201.2	2.7
100°-110°	708.4	9.5
110°-120°	744.0	10.0
120°-130°	612.1	8.2
130°-140°	491.7	6.6
140°-150°	371.4	5.0
150°-160°	261.1	3.5
160°-170°	153.7	2.1
170°-180°	50.0	0.7
0°-30°	1554.6	20.9
0°-40°	2272.1	30.6
0°-60°	3355.4	45.1
0°-90°	3839.3	51.7
90°-120°	1653.6	22.2
90°-150°	3128.9	42.1
90°-180°	3594.0	48.4
0°-180°	7433.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2220	2220	2220	2220	2220	
5°	2221	2470	2229	1973	2221	211
15°	2093	2787	2129	1307	2093	589
25°	1857	1487	1897	947	1857	853
35°	1524	733	1573	699	1524	954
45°	1145	509	1192	498	1145	883
55°	773	353	814	349	773	696
65°	467	184	495	208	467	464
75°	219	97	239	111	219	237
85°	48	28	52	29	48	54
90°	1	33	1	33	1	5
95°	35	113	35	113	35	36
105°	121	1118	121	1118	121	129
115°	213	1472	213	1472	213	212
125°	298	1194	298	1194	298	265
135°	349	989	349	989	349	270
145°	399	790	399	790	399	250
155°	454	664	454	664	454	209
165°	494	582	494	582	494	139
175°	515	525	515	525	515	49
180°	516	516	516	516	516	

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2233.6	2242.9	2247.5	2253.7	2267.6	2276.8	2290.7	2293.8	2292.2	2298.4	2281.5
5°	2221.3	2241.3	2259.9	2275.3	2300.0	2315.4	2332.4	2352.4	2357.0	2380.2	2366.3
7.5°	2204.3	2233.6	2259.9	2290.7	2327.7	2347.8	2374.0	2404.9	2418.7	2446.5	2454.2
10°	2176.6	2218.2	2262.9	2295.3	2346.2	2381.7	2406.4	2455.8	2488.2	2529.8	2523.6
12.5°	2131.8	2185.8	2246.0	2300.0	2366.3	2389.4	2435.7	2486.6	2528.3	2566.8	2600.8
15°	2093.3	2155.0	2221.3	2287.6	2363.2	2406.4	2452.7	2519.0	2563.7	2631.6	2660.9
17.5°	2040.8	2119.5	2198.2	2272.2	2361.7	2411.0	2468.1	2532.9	2599.2	2664.0	2687.1
20°	1986.8	2071.7	2156.5	2256.8	2358.6	2406.4	2465.0	2545.2	2610.0	2660.9	2660.9
22.5°	1922.0	2025.4	2122.6	2218.2	2329.3	2398.7	2458.8	2552.9	2599.2	2610.0	2568.4
25°	1857.2	1960.6	2067.0	2185.8	2312.3	2374.0	2441.9	2529.8	2545.2	2502.0	2394.1
27.5°	1780.1	1895.8	2016.1	2144.2	2276.8	2354.0	2415.7	2474.3	2445.0	2329.3	2161.1
30°	1701.4	1826.4	1962.1	2084.0	2244.4	2315.4	2367.8	2384.8	2292.2	2104.1	1886.6
32.5°	1619.7	1741.6	1885.0	2031.6	2193.5	2261.4	2295.3	2250.6	2080.9	1843.4	1578.0
35°	1524.1	1661.3	1811.0	1963.7	2124.1	2175.0	2195.1	2085.5	1868.0	1561.1	1297.3
37.5°	1437.7	1575.0	1735.4	1891.2	2047.0	2074.7	2054.7	1883.5	1607.4	1303.5	1045.9
40°	1335.9	1482.4	1639.7	1814.1	1942.1	1949.8	1900.4	1678.3	1335.9	1050.5	891.6
42.5°	1241.8	1389.8	1547.2	1724.6	1821.8	1795.5	1729.2	1437.7	1115.3	905.5	777.5
45°	1144.6	1285.0	1454.6	1612.0	1681.4	1619.7	1519.4	1209.4	936.3	779.0	680.3
47.5°	1050.5	1181.6	1349.7	1500.9	1513.3	1443.8	1325.1	1013.5	811.4	684.9	604.7
50°	957.9	1089.0	1246.4	1371.3	1359.0	1263.4	1129.2	880.8	705.0	604.7	538.4
52.5°	865.4	984.2	1136.9	1235.6	1183.1	1090.6	957.9	746.6	615.5	527.6	476.7
55°	772.8	883.9	1015.0	1096.8	1013.5	907.0	812.9	640.2	533.7	462.8	424.2
57.5°	695.7	783.6	903.9	953.3	853.0	769.7	688.0	550.7	462.8	411.9	367.1
60°	610.9	691.1	789.8	819.1	715.7	647.9	578.5	465.9	396.4	351.7	322.4
62.5°	538.4	604.7	680.3	680.3	589.3	538.4	485.9	390.3	333.2	297.7	283.8
65°	467.4	515.2	569.2	563.0	485.9	441.2	399.5	322.4	279.2	254.5	240.6
67.5°	398.0	435.0	470.5	448.9	393.4	354.8	316.2	260.7	231.4	214.4	195.9
70°	334.7	364.0	382.6	362.5	307.0	274.6	246.8	209.8	186.7	165.1	154.3
72.5°	280.7	293.1	299.3	274.6	228.3	209.8	189.7	163.5	143.5	132.7	129.6
75°	219.0	229.8	225.2	206.7	168.1	154.3	138.8	120.3	115.7	109.5	106.4
77.5°	171.2	171.2	163.5	146.5	120.3	109.5	103.4	94.1	89.5	87.9	84.8
80°	121.9	120.3	115.7	97.2	81.8	75.6	75.6	69.4	67.9	64.8	64.8
82.5°	80.2	80.2	74.0	58.6	54.0	52.4	50.9	47.8	47.8	46.3	46.3
85°	47.8	44.7	37.0	32.4	30.9	30.9	29.3	27.8	29.3	27.8	27.8
87.5°	21.6	17.0	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
90°	1.0	4.0	7.9	9.9	11.9	13.4	14.9	19.8	26.8	32.7	33.7
92.5°	14.9	20.8	28.8	33.7	41.7	47.2	52.6	79.4	117.1	150.8	152.8
95°	34.7	38.7	48.6	57.6	73.4	85.4	97.3	142.9	229.2	344.4	389.0
97.5°	51.6	57.6	68.5	81.4	99.2	112.6	126.0	184.6	304.7	490.2	634.1
100°	76.4	79.4	88.3	104.2	124.0	137.9	151.8	204.4	325.5	539.9	784.0
102.5°	99.2	101.2	110.2	126.0	146.9	160.8	174.7	222.3	326.5	521.0	788.9
105°	121.1	125.0	132.0	146.9	168.7	182.6	196.5	243.1	331.5	495.2	735.4
107.5°	144.9	147.9	154.8	168.7	190.5	204.4	218.3	264.0	342.4	481.3	685.7
110°	168.7	172.7	178.6	191.5	212.4	226.8	241.1	284.8	356.3	477.3	652.0

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	190.5	194.5	201.5	213.4	233.2	248.1	263.0	304.7	371.1	478.3	630.2
115°	213.4	218.3	224.3	236.2	256.0	269.4	282.8	325.5	386.0	482.3	615.3
117.5°	237.2	241.1	247.1	258.0	276.9	290.8	304.7	344.4	401.9	488.2	607.3
120°	259.0	263.0	268.9	277.9	297.7	311.6	325.5	364.2	417.8	494.2	600.4
122.5°	279.8	282.8	288.8	298.7	318.6	333.0	347.3	383.1	431.7	501.1	596.4
125°	297.7	300.7	306.6	318.6	338.4	352.3	366.2	401.9	446.6	508.1	591.5
127.5°	312.6	316.6	324.5	337.4	356.3	370.6	385.0	419.8	460.5	515.0	588.5
130°	325.5	329.5	339.4	353.3	373.1	387.0	400.9	435.7	473.4	523.0	586.5
132.5°	337.4	342.4	353.3	368.2	389.0	402.9	416.8	449.5	486.3	530.9	585.5
135°	349.3	353.3	365.2	380.1	402.9	416.8	430.7	462.4	497.2	536.9	584.5
137.5°	360.2	365.2	377.1	393.0	415.8	428.7	441.6	473.4	506.1	542.8	584.5
140°	373.1	377.1	389.0	404.9	426.7	439.6	452.5	482.3	513.1	546.8	583.5
142.5°	386.0	389.0	399.9	415.8	436.6	448.6	460.5	489.2	519.0	549.8	583.5
145°	398.9	402.9	412.8	427.7	447.6	458.5	469.4	496.2	524.0	551.8	581.5
147.5°	412.8	415.8	425.7	439.6	456.5	466.4	476.3	502.1	527.0	552.8	578.6
150°	426.7	429.7	437.6	450.5	465.4	474.4	483.3	506.1	528.9	551.8	575.6
152.5°	440.6	441.6	449.5	460.5	474.4	482.3	490.2	510.1	529.9	549.8	570.6
155°	453.5	454.5	460.5	471.4	482.3	489.8	497.2	514.1	530.9	547.8	564.7
157.5°	464.4	465.4	470.4	480.3	489.2	495.6	502.1	517.0	530.9	543.8	558.7
160°	475.3	476.3	480.3	488.2	496.2	501.6	507.1	519.0	530.9	540.8	552.8
162.5°	486.3	485.3	489.2	495.2	502.1	506.1	510.1	520.0	529.9	537.9	547.8
165°	494.2	493.2	495.2	501.1	506.1	509.1	512.1	521.0	527.9	533.9	540.8
167.5°	501.1	500.2	502.1	506.1	510.1	512.1	514.1	521.0	527.0	529.9	534.9
170°	508.1	506.1	507.1	510.1	512.1	513.6	515.0	520.0	525.0	527.0	529.9
172.5°	512.1	511.1	510.1	513.1	514.1	515.0	516.0	519.0	522.0	523.0	524.0
175°	515.0	514.1	513.1	515.0	515.0	515.5	516.0	518.0	520.0	519.0	520.0
177.5°	517.0	515.0	514.1	516.0	516.0	516.0	516.0	517.0	519.0	517.0	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2298.4	2301.5	2306.1	2327.7	2330.8	2337.0	2333.9	2333.9	2335.4	2332.4	2333.9
5°	2397.1	2401.8	2424.9	2451.1	2457.3	2451.1	2458.8	2469.6	2469.6	2469.6	2466.6
7.5°	2489.7	2506.7	2532.9	2571.5	2579.2	2586.9	2600.8	2591.5	2594.6	2608.5	2603.8
10°	2579.2	2603.8	2633.2	2665.5	2682.5	2693.3	2699.5	2713.4	2745.8	2708.7	2722.6
12.5°	2664.0	2699.5	2730.3	2765.8	2778.2	2792.0	2796.7	2809.0	2809.0	2807.5	2818.3
15°	2719.5	2751.9	2779.7	2802.8	2805.9	2802.8	2799.8	2801.3	2805.9	2787.4	2798.2
17.5°	2731.9	2735.0	2744.2	2735.0	2736.5	2704.1	2685.6	2681.0	2637.8	2639.3	2674.8
20°	2671.7	2619.3	2605.4	2554.5	2523.6	2440.3	2437.2	2414.1	2323.1	2350.9	2344.7
22.5°	2506.7	2417.2	2298.4	2239.8	2210.5	2122.6	2054.7	2006.9	1974.5	1942.1	1928.2
25°	2289.2	2144.2	1976.0	1860.3	1843.4	1761.6	1636.7	1578.0	1508.6	1487.0	1524.1
27.5°	2008.4	1820.2	1630.5	1453.1	1420.7	1346.7	1283.4	1241.8	1161.5	1156.9	1160.0
30°	1627.4	1437.7	1278.8	1163.1	1082.9	1048.9	1007.3	976.4	944.0	956.4	959.5
32.5°	1337.4	1156.9	1008.8	947.1	910.1	888.5	853.0	833.0	819.1	814.5	812.9
35°	1062.8	942.5	876.2	816.0	794.4	779.0	752.8	743.5	731.2	732.7	732.7
37.5°	910.1	809.8	760.5	729.6	709.6	701.9	684.9	675.6	667.9	664.8	669.5
40°	785.2	715.7	684.9	657.1	640.2	637.1	627.8	617.0	607.8	609.3	613.9
42.5°	694.2	654.0	617.0	595.4	583.1	578.5	570.7	563.0	563.0	558.4	556.9
45°	621.7	589.3	558.4	538.4	530.6	524.5	515.2	513.7	507.5	509.0	510.6
47.5°	556.9	530.6	507.5	487.4	479.7	478.2	468.9	462.8	462.8	461.2	459.7
50°	498.2	472.0	452.0	441.2	430.4	427.3	425.7	424.2	421.1	421.1	422.7
52.5°	450.4	424.2	408.8	399.5	393.4	390.3	390.3	388.7	388.7	388.7	387.2
55°	398.0	376.4	364.0	361.0	357.9	356.3	354.8	351.7	350.2	353.2	350.2
57.5°	348.6	340.9	330.1	327.0	319.3	319.3	314.7	311.6	308.5	311.6	311.6
60°	310.1	299.3	293.1	283.8	277.7	271.5	263.8	262.2	259.2	257.6	256.1
62.5°	269.9	260.7	245.3	231.4	222.1	216.0	212.9	211.3	211.3	209.8	209.8
65°	225.2	203.6	195.9	191.3	189.7	188.2	185.1	183.6	185.1	183.6	185.1
67.5°	175.9	172.8	168.1	165.1	163.5	162.0	162.0	160.4	160.4	160.4	160.4
70°	152.7	145.0	143.5	140.4	140.4	138.8	138.8	138.8	138.8	137.3	140.4
72.5°	126.5	121.9	120.3	118.8	118.8	118.8	117.2	117.2	117.2	115.7	117.2
75°	103.4	101.8	98.7	98.7	97.2	98.7	97.2	97.2	95.6	97.2	97.2
77.5°	83.3	81.8	80.2	80.2	78.7	78.7	78.7	78.7	78.7	78.7	80.2
80°	63.2	61.7	60.2	61.7	60.2	61.7	60.2	60.2	61.7	60.2	60.2
82.5°	46.3	44.7	44.7	43.2	43.2	43.2	43.2	43.2	43.2	43.2	43.2
85°	27.8	26.2	26.2	27.8	26.2	27.8	26.2	26.2	26.2	27.8	27.8
87.5°	12.3	13.9	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	13.9
90°	32.7	31.8	29.8	31.8	32.2	32.7	32.7	32.7	32.7	32.7	32.7
92.5°	128.0	100.2	85.3	74.4	70.4	66.5	65.5	61.5	62.5	60.5	62.5
95°	340.4	260.0	199.5	157.8	146.9	136.0	123.1	115.1	112.1	113.1	112.1
97.5°	639.1	531.9	424.7	324.5	294.8	265.0	226.3	206.4	195.5	189.5	195.5
100°	926.9	906.0	783.0	647.0	587.0	527.0	444.6	401.9	373.1	355.3	373.1
102.5°	1034.1	1151.2	1147.2	1056.9	992.4	927.9	836.6	756.2	718.5	692.7	718.5
105°	999.3	1205.7	1317.9	1330.8	1314.4	1298.0	1236.5	1175.0	1132.3	1118.4	1132.3
107.5°	925.9	1147.2	1313.9	1411.2	1431.1	1450.9	1449.9	1440.9	1428.0	1405.2	1428.0
110°	857.4	1066.8	1244.4	1371.5	1412.2	1452.8	1495.5	1514.4	1523.3	1522.3	1523.3

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	809.8	993.4	1162.1	1300.0	1348.2	1396.3	1459.8	1494.5	1513.4	1520.3	1513.4
115°	772.1	935.8	1088.6	1218.6	1269.8	1320.9	1391.3	1437.0	1462.8	1471.7	1462.8
117.5°	746.3	888.2	1025.1	1146.2	1194.8	1243.4	1315.9	1364.5	1391.3	1398.3	1391.3
120°	726.4	854.4	977.5	1082.7	1127.8	1173.0	1242.5	1289.1	1317.9	1327.8	1317.9
122.5°	709.5	827.6	937.8	1036.0	1075.7	1115.4	1176.0	1221.6	1246.4	1254.4	1246.4
125°	693.7	801.8	904.1	991.4	1028.6	1065.8	1123.4	1161.1	1185.9	1193.8	1185.9
127.5°	678.8	776.0	870.3	953.7	988.4	1023.1	1073.8	1109.5	1131.3	1137.3	1131.3
130°	663.9	751.2	836.6	915.0	947.8	980.5	1029.1	1062.8	1082.7	1090.6	1082.7
132.5°	652.0	727.4	804.8	875.3	905.6	935.8	983.4	1017.2	1035.0	1042.0	1035.0
135°	641.1	705.6	771.1	836.6	864.4	892.1	934.8	967.6	985.4	989.4	985.4
137.5°	633.1	687.7	744.3	797.9	822.7	847.5	888.2	917.0	932.8	938.8	932.8
140°	626.2	670.8	718.5	764.1	786.0	807.8	839.5	865.4	880.2	886.2	880.2
142.5°	619.2	657.0	695.7	733.4	750.8	768.1	797.9	820.7	833.6	833.6	833.6
145°	613.3	644.1	676.8	707.6	722.0	736.3	760.2	777.0	787.0	789.9	787.0
147.5°	607.3	634.1	660.9	685.7	696.7	707.6	728.4	742.3	749.2	751.2	749.2
150°	599.4	623.2	645.0	665.9	674.8	683.7	698.6	710.5	716.5	717.5	716.5
152.5°	592.4	612.3	632.1	649.0	656.4	663.9	674.8	684.7	688.7	688.7	688.7
155°	583.5	602.4	618.2	633.1	638.6	644.1	655.0	661.9	665.9	663.9	665.9
157.5°	575.6	590.5	604.4	617.3	621.8	626.2	634.1	640.1	642.1	642.1	642.1
160°	566.6	579.5	590.5	601.4	604.8	608.3	615.3	620.2	621.2	621.2	621.2
162.5°	558.7	568.6	577.6	586.5	589.0	591.5	598.4	601.4	602.4	601.4	602.4
165°	549.8	557.7	564.7	571.6	573.6	575.6	579.5	583.5	583.5	582.5	583.5
167.5°	540.8	546.8	552.8	557.7	559.7	561.7	563.7	565.7	565.7	564.7	565.7
170°	533.9	538.9	541.8	545.8	546.8	547.8	548.8	551.8	550.8	548.8	550.8
172.5°	527.0	529.9	531.9	534.9	535.4	535.9	536.9	537.9	536.9	535.9	536.9
175°	521.0	524.0	525.0	526.0	526.5	527.0	527.0	527.9	527.0	525.0	527.0
177.5°	517.0	519.0	519.0	520.0	520.0	520.0	520.0	520.0	519.0	517.0	519.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2340.1	2329.3	2326.2	2329.3	2326.2	2327.7	2316.9	2276.8	2287.6	2270.7	2279.9
5°	2472.7	2463.5	2443.4	2440.3	2437.2	2434.2	2418.7	2383.3	2369.4	2346.2	2344.7
7.5°	2599.2	2599.2	2583.8	2573.0	2559.1	2548.3	2528.3	2475.8	2454.2	2426.5	2411.0
10°	2724.2	2684.1	2701.0	2690.2	2656.3	2650.1	2613.1	2582.3	2540.6	2512.8	2488.2
12.5°	2813.6	2801.3	2785.9	2776.6	2767.4	2747.3	2722.6	2644.0	2622.4	2566.8	2539.1
15°	2810.5	2802.8	2807.5	2807.5	2804.4	2799.8	2779.7	2722.6	2685.6	2631.6	2583.8
17.5°	2659.4	2679.4	2699.5	2713.4	2744.2	2758.1	2776.6	2742.7	2719.5	2673.3	2622.4
20°	2395.6	2445.0	2503.6	2515.9	2543.7	2625.4	2662.5	2691.8	2701.0	2685.6	2644.0
22.5°	2028.5	2070.1	2212.0	2209.0	2249.1	2346.2	2454.2	2542.1	2611.6	2650.1	2634.7
25°	1588.8	1647.5	1723.0	1780.1	1911.2	2056.2	2190.4	2330.8	2451.1	2557.6	2583.8
27.5°	1201.7	1278.8	1338.9	1414.5	1480.9	1652.1	1824.9	2043.9	2184.3	2386.3	2491.2
30°	971.8	1007.3	1067.5	1102.9	1135.3	1266.4	1462.3	1678.3	1925.1	2158.0	2338.5
32.5°	829.9	854.6	899.3	914.7	948.7	1036.6	1160.0	1357.5	1612.0	1894.3	2131.8
35°	745.1	771.3	780.5	794.4	822.2	877.7	962.6	1106.0	1335.9	1612.0	1895.8
37.5°	672.6	686.4	712.7	721.9	731.2	772.8	829.9	930.2	1082.9	1309.6	1624.3
40°	621.7	629.4	643.2	651.0	657.1	686.4	737.3	805.2	917.8	1090.6	1380.6
42.5°	567.7	576.9	586.2	595.4	603.1	626.3	657.1	721.9	797.5	928.6	1138.4
45°	515.2	521.4	532.2	538.4	549.2	567.7	595.4	640.2	708.0	791.3	961.0
47.5°	467.4	475.1	479.7	487.4	495.2	515.2	541.4	570.7	626.3	708.0	831.4
50°	424.2	433.5	439.6	441.2	447.3	465.9	487.4	519.8	555.3	618.6	726.5
52.5°	393.4	394.9	399.5	405.7	404.2	414.9	435.0	459.7	496.7	547.6	626.3
55°	357.9	362.5	365.6	367.1	367.1	376.4	387.2	410.3	439.6	481.3	547.6
57.5°	313.1	317.8	327.0	330.1	334.7	339.4	344.0	359.4	384.1	424.2	478.2
60°	266.9	269.9	279.2	285.4	288.5	300.8	307.0	319.3	333.2	362.5	413.4
62.5°	214.4	217.5	222.1	228.3	234.5	253.0	268.4	280.7	291.5	311.6	353.2
65°	186.7	188.2	191.3	192.8	194.4	202.1	216.0	232.9	253.0	268.4	293.1
67.5°	162.0	163.5	165.1	168.1	169.7	171.2	177.4	182.0	202.1	223.7	242.2
70°	138.8	141.9	143.5	143.5	145.0	148.1	151.2	157.3	163.5	174.3	197.4
72.5°	117.2	118.8	121.9	121.9	121.9	124.9	128.0	131.1	134.2	140.4	149.6
75°	97.2	100.3	100.3	100.3	101.8	101.8	104.9	108.0	111.1	115.7	118.8
77.5°	80.2	80.2	80.2	80.2	81.8	81.8	83.3	86.4	87.9	89.5	92.6
80°	60.2	61.7	61.7	61.7	63.2	63.2	63.2	66.3	67.9	67.9	71.0
82.5°	44.7	44.7	44.7	46.3	44.7	46.3	46.3	47.8	46.3	47.8	49.4
85°	27.8	27.8	27.8	29.3	29.3	29.3	29.3	29.3	29.3	29.3	30.9
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	15.4	13.9	13.9
90°	32.7	32.7	32.7	32.2	31.8	29.8	31.8	32.7	33.7	32.7	26.8
92.5°	61.5	65.5	66.5	70.4	74.4	85.3	100.2	128.0	152.8	150.8	117.1
95°	115.1	123.1	136.0	146.9	157.8	199.5	260.0	340.4	389.0	344.4	229.2
97.5°	206.4	226.3	265.0	294.8	324.5	424.7	531.9	639.1	634.1	490.2	304.7
100°	401.9	444.6	527.0	587.0	647.0	783.0	906.0	926.9	784.0	539.9	325.5
102.5°	756.2	836.6	927.9	992.4	1056.9	1147.2	1151.2	1034.1	788.9	521.0	326.5
105°	1175.0	1236.5	1298.0	1314.4	1330.8	1317.9	1205.7	999.3	735.4	495.2	331.5
107.5°	1440.9	1449.9	1450.9	1431.1	1411.2	1313.9	1147.2	925.9	685.7	481.3	342.4
110°	1514.4	1495.5	1452.8	1412.2	1371.5	1244.4	1066.8	857.4	652.0	477.3	356.3

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1494.5	1459.8	1396.3	1348.2	1300.0	1162.1	993.4	809.8	630.2	478.3	371.1
115°	1437.0	1391.3	1320.9	1269.8	1218.6	1088.6	935.8	772.1	615.3	482.3	386.0
117.5°	1364.5	1315.9	1243.4	1194.8	1146.2	1025.1	888.2	746.3	607.3	488.2	401.9
120°	1289.1	1242.5	1173.0	1127.8	1082.7	977.5	854.4	726.4	600.4	494.2	417.8
122.5°	1221.6	1176.0	1115.4	1075.7	1036.0	937.8	827.6	709.5	596.4	501.1	431.7
125°	1161.1	1123.4	1065.8	1028.6	991.4	904.1	801.8	693.7	591.5	508.1	446.6
127.5°	1109.5	1073.8	1023.1	988.4	953.7	870.3	776.0	678.8	588.5	515.0	460.5
130°	1062.8	1029.1	980.5	947.8	915.0	836.6	751.2	663.9	586.5	523.0	473.4
132.5°	1017.2	983.4	935.8	905.6	875.3	804.8	727.4	652.0	585.5	530.9	486.3
135°	967.6	934.8	892.1	864.4	836.6	771.1	705.6	641.1	584.5	536.9	497.2
137.5°	917.0	888.2	847.5	822.7	797.9	744.3	687.7	633.1	584.5	542.8	506.1
140°	865.4	839.5	807.8	786.0	764.1	718.5	670.8	626.2	583.5	546.8	513.1
142.5°	820.7	797.9	768.1	750.8	733.4	695.7	657.0	619.2	583.5	549.8	519.0
145°	777.0	760.2	736.3	722.0	707.6	676.8	644.1	613.3	581.5	551.8	524.0
147.5°	742.3	728.4	707.6	696.7	685.7	660.9	634.1	607.3	578.6	552.8	527.0
150°	710.5	698.6	683.7	674.8	665.9	645.0	623.2	599.4	575.6	551.8	528.9
152.5°	684.7	674.8	663.9	656.4	649.0	632.1	612.3	592.4	570.6	549.8	529.9
155°	661.9	655.0	644.1	638.6	633.1	618.2	602.4	583.5	564.7	547.8	530.9
157.5°	640.1	634.1	626.2	621.8	617.3	604.4	590.5	575.6	558.7	543.8	530.9
160°	620.2	615.3	608.3	604.8	601.4	590.5	579.5	566.6	552.8	540.8	530.9
162.5°	601.4	598.4	591.5	589.0	586.5	577.6	568.6	558.7	547.8	537.9	529.9
165°	583.5	579.5	575.6	573.6	571.6	564.7	557.7	549.8	540.8	533.9	527.9
167.5°	565.7	563.7	561.7	559.7	557.7	552.8	546.8	540.8	534.9	529.9	527.0
170°	551.8	548.8	547.8	546.8	545.8	541.8	538.9	533.9	529.9	527.0	525.0
172.5°	537.9	536.9	535.9	535.4	534.9	531.9	529.9	527.0	524.0	523.0	522.0
175°	527.9	527.0	527.0	526.5	526.0	525.0	524.0	521.0	520.0	519.0	520.0
177.5°	520.0	520.0	520.0	520.0	520.0	519.0	519.0	517.0	516.0	517.0	519.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2266.0	2258.3	2258.3	2253.7	2253.7	2229.0	2229.0	2236.7	2227.5	2216.7	2201.2
5°	2324.6	2307.7	2303.0	2296.9	2276.8	2246.0	2233.6	2229.0	2210.5	2187.4	2161.1
7.5°	2380.2	2352.4	2338.5	2324.6	2298.4	2255.2	2230.5	2213.6	2185.8	2150.3	2116.4
10°	2434.2	2398.7	2363.2	2346.2	2309.2	2255.2	2219.7	2192.0	2151.9	2104.1	2056.2
12.5°	2483.5	2409.5	2403.3	2369.4	2315.4	2253.7	2199.7	2159.6	2108.7	2053.2	1997.6
15°	2526.7	2451.1	2414.1	2383.3	2312.3	2235.2	2178.1	2128.7	2060.9	1997.6	1929.7
17.5°	2548.3	2466.6	2441.9	2391.0	2318.5	2218.2	2141.1	2080.9	2006.9	1931.3	1854.2
20°	2569.9	2474.3	2434.2	2398.7	2300.0	2185.8	2099.4	2030.0	1948.3	1858.8	1773.9
22.5°	2580.7	2474.3	2426.5	2377.1	2281.5	2150.3	2048.5	1966.8	1871.1	1780.1	1678.3
25°	2562.2	2465.0	2407.9	2357.0	2249.1	2107.1	1989.9	1897.4	1795.5	1692.2	1588.8
27.5°	2515.9	2443.4	2377.1	2324.6	2204.3	2051.6	1928.2	1823.3	1718.4	1602.7	1497.8
30°	2429.5	2397.1	2344.7	2286.1	2155.0	2002.2	1855.7	1747.7	1632.0	1516.3	1406.8
32.5°	2295.3	2323.1	2289.2	2238.3	2096.3	1934.4	1778.6	1669.1	1542.6	1417.6	1317.3
35°	2131.8	2230.5	2212.0	2176.6	2034.6	1861.9	1706.1	1573.4	1446.9	1320.4	1220.2
37.5°	1952.9	2102.5	2117.9	2096.3	1963.7	1787.8	1616.6	1487.0	1357.5	1229.4	1127.6
40°	1707.6	1937.5	1986.8	1996.1	1889.6	1698.4	1519.4	1392.9	1264.9	1140.0	1016.5
42.5°	1482.4	1772.4	1834.1	1872.7	1795.5	1610.4	1430.0	1289.6	1163.1	1050.5	927.1
45°	1271.1	1573.4	1673.7	1723.0	1689.1	1510.2	1323.5	1192.4	1076.7	973.4	854.6
47.5°	1053.6	1357.5	1497.8	1576.5	1576.5	1408.4	1221.7	1092.1	981.1	893.1	788.2
50°	908.6	1161.5	1306.6	1409.9	1437.7	1305.0	1129.2	1002.7	897.8	802.1	721.9
52.5°	774.4	1001.1	1121.4	1229.4	1309.6	1193.9	1025.8	911.7	808.3	718.8	655.6
55°	669.5	839.2	948.7	1067.5	1156.9	1081.3	925.5	814.5	725.0	651.0	597.0
57.5°	569.2	717.3	806.8	911.7	1007.3	950.2	825.3	729.6	651.0	586.2	538.4
60°	484.4	604.7	674.1	755.9	874.6	834.5	731.2	643.2	580.0	521.4	481.3
62.5°	411.9	507.5	566.1	624.7	732.7	714.2	634.0	566.1	512.1	462.8	428.8
65°	337.8	416.5	462.8	513.7	600.1	607.8	543.0	495.2	445.8	402.6	371.8
67.5°	273.0	334.7	376.4	419.6	489.0	510.6	465.9	425.7	384.1	348.6	320.9
70°	220.6	263.8	294.6	328.6	385.6	411.9	388.7	361.0	327.0	297.7	273.0
72.5°	174.3	202.1	220.6	246.8	293.1	319.3	317.8	293.1	268.4	248.4	228.3
75°	128.0	149.6	165.1	182.0	219.0	243.7	249.9	239.1	214.4	199.0	183.6
77.5°	97.2	109.5	117.2	129.6	155.8	177.4	186.7	183.6	166.6	154.3	143.5
80°	74.0	77.1	80.2	84.8	106.4	126.5	132.7	131.1	121.9	117.2	104.9
82.5°	52.4	54.0	55.5	57.1	64.8	81.8	87.9	91.0	83.3	78.7	67.9
85°	30.9	32.4	32.4	35.5	37.0	41.6	52.4	52.4	50.9	44.7	43.2
87.5°	15.4	15.4	13.9	13.9	15.4	17.0	20.1	23.1	20.1	18.5	17.0
90°	19.8	14.9	13.4	11.9	9.9	7.9	4.0	1.0	4.0	7.9	9.9
92.5°	79.4	52.6	47.2	41.7	33.7	28.8	20.8	14.9	20.8	28.8	33.7
95°	142.9	97.3	85.4	73.4	57.6	48.6	38.7	34.7	38.7	48.6	57.6
97.5°	184.6	126.0	112.6	99.2	81.4	68.5	57.6	51.6	57.6	68.5	81.4
100°	204.4	151.8	137.9	124.0	104.2	88.3	79.4	76.4	79.4	88.3	104.2
102.5°	222.3	174.7	160.8	146.9	126.0	110.2	101.2	99.2	101.2	110.2	126.0
105°	243.1	196.5	182.6	168.7	146.9	132.0	125.0	121.1	125.0	132.0	146.9
107.5°	264.0	218.3	204.4	190.5	168.7	154.8	147.9	144.9	147.9	154.8	168.7
110°	284.8	241.1	226.8	212.4	191.5	178.6	172.7	168.7	172.7	178.6	191.5



TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	304.7	263.0	248.1	233.2	213.4	201.5	194.5	190.5	194.5	201.5	213.4
115°	325.5	282.8	269.4	256.0	236.2	224.3	218.3	213.4	218.3	224.3	236.2
117.5°	344.4	304.7	290.8	276.9	258.0	247.1	241.1	237.2	241.1	247.1	258.0
120°	364.2	325.5	311.6	297.7	277.9	268.9	263.0	259.0	263.0	268.9	277.9
122.5°	383.1	347.3	333.0	318.6	298.7	288.8	282.8	279.8	282.8	288.8	298.7
125°	401.9	366.2	352.3	338.4	318.6	306.6	300.7	297.7	300.7	306.6	318.6
127.5°	419.8	385.0	370.6	356.3	337.4	324.5	316.6	312.6	316.6	324.5	337.4
130°	435.7	400.9	387.0	373.1	353.3	339.4	329.5	325.5	329.5	339.4	353.3
132.5°	449.5	416.8	402.9	389.0	368.2	353.3	342.4	337.4	342.4	353.3	368.2
135°	462.4	430.7	416.8	402.9	380.1	365.2	353.3	349.3	353.3	365.2	380.1
137.5°	473.4	441.6	428.7	415.8	393.0	377.1	365.2	360.2	365.2	377.1	393.0
140°	482.3	452.5	439.6	426.7	404.9	389.0	377.1	373.1	377.1	389.0	404.9
142.5°	489.2	460.5	448.6	436.6	415.8	399.9	389.0	386.0	389.0	399.9	415.8
145°	496.2	469.4	458.5	447.6	427.7	412.8	402.9	398.9	402.9	412.8	427.7
147.5°	502.1	476.3	466.4	456.5	439.6	425.7	415.8	412.8	415.8	425.7	439.6
150°	506.1	483.3	474.4	465.4	450.5	437.6	429.7	426.7	429.7	437.6	450.5
152.5°	510.1	490.2	482.3	474.4	460.5	449.5	441.6	440.6	441.6	449.5	460.5
155°	514.1	497.2	489.8	482.3	471.4	460.5	454.5	453.5	454.5	460.5	471.4
157.5°	517.0	502.1	495.6	489.2	480.3	470.4	465.4	464.4	465.4	470.4	480.3
160°	519.0	507.1	501.6	496.2	488.2	480.3	476.3	475.3	476.3	480.3	488.2
162.5°	520.0	510.1	506.1	502.1	495.2	489.2	485.3	486.3	485.3	489.2	495.2
165°	521.0	512.1	509.1	506.1	501.1	495.2	493.2	494.2	493.2	495.2	501.1
167.5°	521.0	514.1	512.1	510.1	506.1	502.1	500.2	501.1	500.2	502.1	506.1
170°	520.0	515.0	513.6	512.1	510.1	507.1	506.1	508.1	506.1	507.1	510.1
172.5°	519.0	516.0	515.0	514.1	513.1	510.1	511.1	512.1	511.1	510.1	513.1
175°	518.0	516.0	515.5	515.0	515.0	513.1	514.1	515.0	514.1	513.1	515.0
177.5°	517.0	516.0	516.0	516.0	516.0	514.1	515.0	517.0	515.0	514.1	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2195.1	2196.6	2201.2	2187.4	2165.8	2156.5	2128.7	2124.1	2119.5	2119.5	2124.1
5°	2145.7	2139.5	2141.1	2114.9	2084.0	2065.5	2026.9	2033.1	2013.0	2000.7	2003.8
7.5°	2091.7	2074.7	2073.2	2039.3	2000.7	1966.8	1926.7	1917.4	1898.9	1877.3	1868.0
10°	2023.8	2011.5	1988.4	1949.8	1900.4	1872.7	1818.7	1786.3	1781.7	1749.3	1736.9
12.5°	1954.4	1932.8	1909.7	1855.7	1800.2	1755.4	1715.3	1679.9	1655.2	1627.4	1608.9
15°	1874.2	1848.0	1821.8	1764.7	1699.9	1655.2	1595.0	1542.6	1470.1	1413.0	1380.6
17.5°	1786.3	1757.0	1721.5	1658.3	1595.0	1533.3	1422.2	1360.5	1309.6	1275.7	1255.6
20°	1695.3	1662.9	1627.4	1564.2	1454.6	1346.7	1285.0	1237.1	1206.3	1172.3	1147.7
22.5°	1599.6	1565.7	1527.1	1428.4	1312.7	1237.1	1189.3	1144.6	1099.8	1081.3	1069.0
25°	1510.2	1479.3	1430.0	1295.8	1204.7	1135.3	1081.3	1052.0	1028.9	1004.2	981.1
27.5°	1417.6	1360.5	1291.1	1178.5	1121.4	1050.5	1011.9	990.3	950.2	933.3	922.5
30°	1306.6	1243.3	1177.0	1096.8	1030.4	981.1	945.6	910.1	887.0	870.0	851.5
32.5°	1193.9	1133.8	1092.1	1008.8	959.5	908.6	874.6	853.0	819.1	808.3	800.6
35°	1096.8	1045.9	1008.8	941.0	894.7	848.4	823.7	791.3	769.7	749.7	737.3
37.5°	1001.1	973.4	934.8	877.7	828.4	791.3	757.4	746.6	717.3	706.5	694.2
40°	934.8	893.1	860.8	811.4	769.7	729.6	708.0	683.4	663.3	646.3	641.7
42.5°	854.6	823.7	805.2	751.2	708.0	684.9	658.7	630.9	615.5	601.6	584.6
45°	794.4	766.7	740.4	697.2	658.7	629.4	606.2	587.7	561.5	555.3	529.1
47.5°	731.2	703.4	683.4	640.2	604.7	576.9	560.0	535.3	513.7	499.8	487.4
50°	667.9	644.8	626.3	589.3	558.4	529.1	506.0	481.3	472.0	448.9	441.2
52.5°	607.8	592.3	572.3	536.8	506.0	481.3	456.6	436.5	422.7	410.3	401.1
55°	556.9	532.2	522.9	484.4	458.1	431.9	410.3	398.0	381.0	373.3	365.6
57.5°	499.8	485.9	470.5	441.2	411.9	387.2	371.8	353.2	344.0	334.7	328.6
60°	450.4	430.4	418.0	393.4	367.1	344.0	330.1	316.2	303.9	296.2	283.8
62.5°	393.4	377.9	370.2	344.0	322.4	300.8	288.5	274.6	265.3	251.4	236.0
65°	344.0	331.7	322.4	300.8	280.7	260.7	248.4	231.4	219.0	211.3	209.8
67.5°	300.8	291.5	277.7	257.6	237.6	222.1	208.2	194.4	192.8	189.7	189.7
70°	253.0	243.7	236.0	214.4	197.4	180.5	177.4	172.8	168.1	166.6	163.5
72.5°	211.3	203.6	194.4	175.9	158.9	154.3	151.2	148.1	143.5	141.9	140.4
75°	171.2	160.4	154.3	137.3	132.7	129.6	126.5	121.9	118.8	117.2	114.1
77.5°	131.1	120.3	120.3	111.1	108.0	103.4	100.3	97.2	95.6	92.6	92.6
80°	92.6	92.6	89.5	84.8	80.2	78.7	74.0	72.5	71.0	72.5	69.4
82.5°	67.9	61.7	61.7	58.6	55.5	54.0	50.9	50.9	49.4	49.4	49.4
85°	38.6	38.6	37.0	33.9	32.4	32.4	30.9	30.9	29.3	29.3	27.8
87.5°	15.4	13.9	15.4	13.9	13.9	12.3	12.3	12.3	10.8	12.3	10.8
90°	11.9	13.4	14.9	19.8	26.8	32.7	33.7	32.7	31.8	29.8	31.8
92.5°	41.7	47.2	52.6	79.4	117.1	150.8	152.8	128.0	100.2	85.3	74.4
95°	73.4	85.4	97.3	142.9	229.2	344.4	389.0	340.4	260.0	199.5	157.8
97.5°	99.2	112.6	126.0	184.6	304.7	490.2	634.1	639.1	531.9	424.7	324.5
100°	124.0	137.9	151.8	204.4	325.5	539.9	784.0	926.9	906.0	783.0	647.0
102.5°	146.9	160.8	174.7	222.3	326.5	521.0	788.9	1034.1	1151.2	1147.2	1056.9
105°	168.7	182.6	196.5	243.1	331.5	495.2	735.4	999.3	1205.7	1317.9	1330.8
107.5°	190.5	204.4	218.3	264.0	342.4	481.3	685.7	925.9	1147.2	1313.9	1411.2
110°	212.4	226.8	241.1	284.8	356.3	477.3	652.0	857.4	1066.8	1244.4	1371.5

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	233.2	248.1	263.0	304.7	371.1	478.3	630.2	809.8	993.4	1162.1	1300.0
115°	256.0	269.4	282.8	325.5	386.0	482.3	615.3	772.1	935.8	1088.6	1218.6
117.5°	276.9	290.8	304.7	344.4	401.9	488.2	607.3	746.3	888.2	1025.1	1146.2
120°	297.7	311.6	325.5	364.2	417.8	494.2	600.4	726.4	854.4	977.5	1082.7
122.5°	318.6	333.0	347.3	383.1	431.7	501.1	596.4	709.5	827.6	937.8	1036.0
125°	338.4	352.3	366.2	401.9	446.6	508.1	591.5	693.7	801.8	904.1	991.4
127.5°	356.3	370.6	385.0	419.8	460.5	515.0	588.5	678.8	776.0	870.3	953.7
130°	373.1	387.0	400.9	435.7	473.4	523.0	586.5	663.9	751.2	836.6	915.0
132.5°	389.0	402.9	416.8	449.5	486.3	530.9	585.5	652.0	727.4	804.8	875.3
135°	402.9	416.8	430.7	462.4	497.2	536.9	584.5	641.1	705.6	771.1	836.6
137.5°	415.8	428.7	441.6	473.4	506.1	542.8	584.5	633.1	687.7	744.3	797.9
140°	426.7	439.6	452.5	482.3	513.1	546.8	583.5	626.2	670.8	718.5	764.1
142.5°	436.6	448.6	460.5	489.2	519.0	549.8	583.5	619.2	657.0	695.7	733.4
145°	447.6	458.5	469.4	496.2	524.0	551.8	581.5	613.3	644.1	676.8	707.6
147.5°	456.5	466.4	476.3	502.1	527.0	552.8	578.6	607.3	634.1	660.9	685.7
150°	465.4	474.4	483.3	506.1	528.9	551.8	575.6	599.4	623.2	645.0	665.9
152.5°	474.4	482.3	490.2	510.1	529.9	549.8	570.6	592.4	612.3	632.1	649.0
155°	482.3	489.8	497.2	514.1	530.9	547.8	564.7	583.5	602.4	618.2	633.1
157.5°	489.2	495.6	502.1	517.0	530.9	543.8	558.7	575.6	590.5	604.4	617.3
160°	496.2	501.6	507.1	519.0	530.9	540.8	552.8	566.6	579.5	590.5	601.4
162.5°	502.1	506.1	510.1	520.0	529.9	537.9	547.8	558.7	568.6	577.6	586.5
165°	506.1	509.1	512.1	521.0	527.9	533.9	540.8	549.8	557.7	564.7	571.6
167.5°	510.1	512.1	514.1	521.0	527.0	529.9	534.9	540.8	546.8	552.8	557.7
170°	512.1	513.6	515.0	520.0	525.0	527.0	529.9	533.9	538.9	541.8	545.8
172.5°	514.1	515.0	516.0	519.0	522.0	523.0	524.0	527.0	529.9	531.9	534.9
175°	515.0	515.5	516.0	518.0	520.0	519.0	520.0	521.0	524.0	525.0	526.0
177.5°	516.0	516.0	516.0	517.0	519.0	517.0	516.0	517.0	519.0	519.0	520.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2124.1	2121.0	2111.8	2114.9	2110.2	2110.2	2107.1	2107.1	2107.1	2114.9	2110.2
5°	2008.4	1997.6	1986.8	1982.2	1977.6	1972.9	1972.9	1971.4	1985.3	1982.2	1994.5
7.5°	1865.0	1861.9	1840.3	1840.3	1832.6	1829.5	1837.2	1838.7	1840.3	1843.4	1851.1
10°	1736.9	1729.2	1698.4	1701.4	1696.8	1690.6	1695.3	1692.2	1703.0	1706.1	1703.0
12.5°	1585.8	1571.9	1537.9	1521.0	1502.5	1488.6	1505.5	1493.2	1536.4	1548.7	1582.7
15°	1385.2	1359.0	1335.9	1335.9	1318.9	1306.6	1314.3	1328.1	1337.4	1351.3	1357.5
17.5°	1251.0	1240.2	1221.7	1210.9	1206.3	1201.7	1201.7	1207.8	1227.9	1226.3	1238.7
20°	1136.9	1130.7	1121.4	1107.6	1102.9	1099.8	1099.8	1099.8	1113.7	1126.1	1133.8
22.5°	1058.2	1053.6	1047.4	1028.9	1019.6	1016.5	1024.3	1028.9	1039.7	1048.9	1056.7
25°	979.5	968.7	957.9	951.8	947.1	947.1	950.2	951.8	956.4	961.0	970.3
27.5°	914.7	907.0	891.6	874.6	874.6	870.0	873.1	876.2	887.0	902.4	910.1
30°	842.2	840.7	834.5	828.4	822.2	819.1	825.3	829.9	831.4	839.2	839.2
32.5°	789.8	779.0	768.2	762.0	758.9	757.4	758.9	765.1	765.1	774.4	785.2
35°	737.3	731.2	720.4	709.6	706.5	698.8	705.0	711.1	721.9	726.5	731.2
37.5°	680.3	672.6	667.9	664.8	658.7	660.2	655.6	664.8	674.1	672.6	675.6
40°	637.1	623.2	609.3	607.8	606.2	604.7	604.7	606.2	612.4	618.6	627.8
42.5°	581.5	576.9	564.6	552.2	549.2	546.1	543.0	549.2	561.5	572.3	576.9
45°	524.5	518.3	515.2	506.0	499.8	498.2	495.2	502.9	513.7	518.3	521.4
47.5°	472.0	470.5	461.2	462.8	458.1	459.7	458.1	462.8	462.8	467.4	470.5
50°	436.5	431.9	427.3	424.2	419.6	419.6	418.0	419.6	425.7	431.9	430.4
52.5°	401.1	393.4	391.8	390.3	387.2	390.3	385.6	387.2	393.4	396.4	394.9
55°	359.4	357.9	354.8	351.7	350.2	348.6	348.6	348.6	354.8	359.4	361.0
57.5°	327.0	319.3	313.1	313.1	307.0	305.4	308.5	310.1	314.7	317.8	320.9
60°	282.3	279.2	269.9	265.3	256.1	254.5	254.5	260.7	268.4	279.2	282.3
62.5°	234.5	229.8	228.3	228.3	228.3	228.3	228.3	228.3	228.3	229.8	229.8
65°	208.2	209.8	208.2	206.7	208.2	208.2	206.7	206.7	206.7	208.2	209.8
67.5°	186.7	185.1	186.7	185.1	183.6	183.6	182.0	183.6	185.1	186.7	186.7
70°	162.0	162.0	160.4	162.0	160.4	158.9	157.3	157.3	160.4	162.0	162.0
72.5°	138.8	138.8	137.3	137.3	134.2	134.2	135.7	134.2	134.2	138.8	138.8
75°	115.7	114.1	112.6	112.6	111.1	111.1	111.1	109.5	112.6	112.6	114.1
77.5°	91.0	91.0	91.0	89.5	89.5	87.9	87.9	89.5	89.5	89.5	91.0
80°	69.4	69.4	69.4	67.9	66.3	66.3	66.3	66.3	66.3	67.9	66.3
82.5°	47.8	47.8	47.8	47.8	47.8	46.3	46.3	46.3	47.8	47.8	46.3
85°	29.3	27.8	29.3	29.3	27.8	29.3	27.8	27.8	26.2	26.2	27.8
87.5°	12.3	10.8	9.3	9.3	10.8	9.3	9.3	9.3	10.8	9.3	9.3
90°	32.2	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.2
92.5°	70.4	66.5	65.5	61.5	62.5	60.5	62.5	61.5	65.5	66.5	70.4
95°	146.9	136.0	123.1	115.1	112.1	113.1	112.1	115.1	123.1	136.0	146.9
97.5°	294.8	265.0	226.3	206.4	195.5	189.5	195.5	206.4	226.3	265.0	294.8
100°	587.0	527.0	444.6	401.9	373.1	355.3	373.1	401.9	444.6	527.0	587.0
102.5°	992.4	927.9	836.6	756.2	718.5	692.7	718.5	756.2	836.6	927.9	992.4
105°	1314.4	1298.0	1236.5	1175.0	1132.3	1118.4	1132.3	1175.0	1236.5	1298.0	1314.4
107.5°	1431.1	1450.9	1449.9	1440.9	1428.0	1405.2	1428.0	1440.9	1449.9	1450.9	1431.1
110°	1412.2	1452.8	1495.5	1514.4	1523.3	1522.3	1523.3	1514.4	1495.5	1452.8	1412.2

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1348.2	1396.3	1459.8	1494.5	1513.4	1520.3	1513.4	1494.5	1459.8	1396.3	1348.2
115°	1269.8	1320.9	1391.3	1437.0	1462.8	1471.7	1462.8	1437.0	1391.3	1320.9	1269.8
117.5°	1194.8	1243.4	1315.9	1364.5	1391.3	1398.3	1391.3	1364.5	1315.9	1243.4	1194.8
120°	1127.8	1173.0	1242.5	1289.1	1317.9	1327.8	1317.9	1289.1	1242.5	1173.0	1127.8
122.5°	1075.7	1115.4	1176.0	1221.6	1246.4	1254.4	1246.4	1221.6	1176.0	1115.4	1075.7
125°	1028.6	1065.8	1123.4	1161.1	1185.9	1193.8	1185.9	1161.1	1123.4	1065.8	1028.6
127.5°	988.4	1023.1	1073.8	1109.5	1131.3	1137.3	1131.3	1109.5	1073.8	1023.1	988.4
130°	947.8	980.5	1029.1	1062.8	1082.7	1090.6	1082.7	1062.8	1029.1	980.5	947.8
132.5°	905.6	935.8	983.4	1017.2	1035.0	1042.0	1035.0	1017.2	983.4	935.8	905.6
135°	864.4	892.1	934.8	967.6	985.4	989.4	985.4	967.6	934.8	892.1	864.4
137.5°	822.7	847.5	888.2	917.0	932.8	938.8	932.8	917.0	888.2	847.5	822.7
140°	786.0	807.8	839.5	865.4	880.2	886.2	880.2	865.4	839.5	807.8	786.0
142.5°	750.8	768.1	797.9	820.7	833.6	833.6	833.6	820.7	797.9	768.1	750.8
145°	722.0	736.3	760.2	777.0	787.0	789.9	787.0	777.0	760.2	736.3	722.0
147.5°	696.7	707.6	728.4	742.3	749.2	751.2	749.2	742.3	728.4	707.6	696.7
150°	674.8	683.7	698.6	710.5	716.5	717.5	716.5	710.5	698.6	683.7	674.8
152.5°	656.4	663.9	674.8	684.7	688.7	688.7	688.7	684.7	674.8	663.9	656.4
155°	638.6	644.1	655.0	661.9	665.9	663.9	665.9	661.9	655.0	644.1	638.6
157.5°	621.8	626.2	634.1	640.1	642.1	642.1	642.1	640.1	634.1	626.2	621.8
160°	604.8	608.3	615.3	620.2	621.2	621.2	621.2	620.2	615.3	608.3	604.8
162.5°	589.0	591.5	598.4	601.4	602.4	601.4	602.4	601.4	598.4	591.5	589.0
165°	573.6	575.6	579.5	583.5	583.5	582.5	583.5	583.5	579.5	575.6	573.6
167.5°	559.7	561.7	563.7	565.7	565.7	564.7	565.7	565.7	563.7	561.7	559.7
170°	546.8	547.8	548.8	551.8	550.8	548.8	550.8	551.8	548.8	547.8	546.8
172.5°	535.4	535.9	536.9	537.9	536.9	535.9	536.9	537.9	536.9	535.9	535.4
175°	526.5	527.0	527.0	527.9	527.0	525.0	527.0	527.9	527.0	527.0	526.5
177.5°	520.0	520.0	520.0	520.0	519.0	517.0	519.0	520.0	520.0	520.0	520.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7	2219.7
2.5°	2114.9	2122.6	2119.5	2102.5	2119.5	2124.1	2133.4	2142.6	2148.8	2158.0	2165.8
5°	1982.2	1997.6	2006.9	1997.6	2028.5	2033.1	2054.7	2067.0	2085.5	2101.0	2113.3
7.5°	1857.2	1869.6	1888.1	1891.2	1909.7	1931.3	1962.1	1993.0	2022.3	2037.7	2051.6
10°	1723.0	1744.6	1772.4	1766.2	1794.0	1827.9	1860.3	1909.7	1934.4	1962.1	1986.8
12.5°	1588.8	1602.7	1639.7	1652.1	1692.2	1718.4	1763.1	1794.0	1855.7	1888.1	1909.7
15°	1354.4	1411.4	1457.7	1513.3	1565.7	1615.1	1655.2	1710.7	1764.7	1789.4	1824.9
17.5°	1247.9	1274.2	1301.9	1329.7	1397.6	1485.5	1556.4	1616.6	1662.9	1695.3	1736.9
20°	1136.9	1163.1	1193.9	1220.2	1261.8	1325.1	1413.0	1516.3	1571.9	1605.8	1645.9
22.5°	1058.2	1082.9	1102.9	1126.1	1158.5	1204.7	1271.1	1399.1	1473.1	1514.8	1550.3
25°	973.4	1004.2	1025.8	1042.8	1069.0	1119.9	1173.9	1246.4	1379.1	1411.4	1460.8
27.5°	914.7	924.0	948.7	974.9	1001.1	1028.9	1084.4	1146.1	1235.6	1306.6	1366.7
30°	845.3	868.5	891.6	902.4	925.5	965.6	999.6	1065.9	1135.3	1190.9	1263.4
32.5°	792.9	806.8	822.2	848.4	870.0	897.8	931.7	987.2	1045.9	1081.3	1136.9
35°	734.3	743.5	775.9	786.7	808.3	836.1	870.0	913.2	976.4	1004.2	1044.3
37.5°	678.7	700.3	709.6	734.3	754.3	782.1	806.8	856.1	897.8	930.2	967.2
40°	635.5	644.8	661.8	683.4	700.3	721.9	752.8	788.2	833.0	859.2	891.6
42.5°	583.1	590.8	612.4	624.7	652.5	672.6	691.1	734.3	774.4	794.4	826.8
45°	526.0	544.5	558.4	583.1	598.5	623.2	646.3	677.2	714.2	737.3	755.9
47.5°	476.7	495.2	509.0	532.2	556.9	567.7	592.3	624.7	658.7	677.2	703.4
50°	436.5	442.7	468.9	479.7	506.0	527.6	544.5	572.3	609.3	620.1	641.7
52.5°	398.0	402.6	419.6	433.5	456.6	475.1	496.7	522.9	553.8	570.7	587.7
55°	364.0	367.1	374.8	390.3	405.7	428.8	448.9	473.6	499.8	518.3	533.7
57.5°	325.5	331.7	337.8	347.1	362.5	384.1	405.7	428.8	450.4	462.8	482.8
60°	280.7	290.0	300.8	311.6	322.4	337.8	362.5	384.1	404.2	414.9	430.4
62.5°	232.9	251.4	260.7	273.0	282.3	296.2	314.7	339.4	353.2	367.1	379.5
65°	209.8	211.3	212.9	225.2	242.2	256.1	273.0	291.5	313.1	322.4	331.7
67.5°	186.7	188.2	191.3	192.8	199.0	214.4	232.9	253.0	269.9	276.1	285.4
70°	163.5	163.5	169.7	171.2	172.8	174.3	189.7	209.8	225.2	232.9	243.7
72.5°	138.8	140.4	143.5	145.0	148.1	151.2	155.8	166.6	185.1	192.8	205.2
75°	114.1	115.7	117.2	118.8	123.4	124.9	129.6	135.7	143.5	152.7	160.4
77.5°	91.0	91.0	92.6	95.6	98.7	100.3	104.9	108.0	111.1	115.7	121.9
80°	67.9	69.4	69.4	72.5	72.5	74.0	75.6	80.2	83.3	86.4	89.5
82.5°	46.3	49.4	49.4	49.4	50.9	52.4	54.0	54.0	57.1	58.6	63.2
85°	27.8	29.3	29.3	29.3	27.8	30.9	30.9	32.4	32.4	32.4	33.9
87.5°	10.8	9.3	10.8	10.8	10.8	12.3	10.8	10.8	12.3	13.9	13.9
90°	31.8	29.8	31.8	32.7	33.7	32.7	26.8	19.8	14.9	13.4	11.9
92.5°	74.4	85.3	100.2	128.0	152.8	150.8	117.1	79.4	52.6	47.2	41.7
95°	157.8	199.5	260.0	340.4	389.0	344.4	229.2	142.9	97.3	85.4	73.4
97.5°	324.5	424.7	531.9	639.1	634.1	490.2	304.7	184.6	126.0	112.6	99.2
100°	647.0	783.0	906.0	926.9	784.0	539.9	325.5	204.4	151.8	137.9	124.0
102.5°	1056.9	1147.2	1151.2	1034.1	788.9	521.0	326.5	222.3	174.7	160.8	146.9
105°	1330.8	1317.9	1205.7	999.3	735.4	495.2	331.5	243.1	196.5	182.6	168.7
107.5°	1411.2	1313.9	1147.2	925.9	685.7	481.3	342.4	264.0	218.3	204.4	190.5
110°	1371.5	1244.4	1066.8	857.4	652.0	477.3	356.3	284.8	241.1	226.8	212.4

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1300.0	1162.1	993.4	809.8	630.2	478.3	371.1	304.7	263.0	248.1	233.2
115°	1218.6	1088.6	935.8	772.1	615.3	482.3	386.0	325.5	282.8	269.4	256.0
117.5°	1146.2	1025.1	888.2	746.3	607.3	488.2	401.9	344.4	304.7	290.8	276.9
120°	1082.7	977.5	854.4	726.4	600.4	494.2	417.8	364.2	325.5	311.6	297.7
122.5°	1036.0	937.8	827.6	709.5	596.4	501.1	431.7	383.1	347.3	333.0	318.6
125°	991.4	904.1	801.8	693.7	591.5	508.1	446.6	401.9	366.2	352.3	338.4
127.5°	953.7	870.3	776.0	678.8	588.5	515.0	460.5	419.8	385.0	370.6	356.3
130°	915.0	836.6	751.2	663.9	586.5	523.0	473.4	435.7	400.9	387.0	373.1
132.5°	875.3	804.8	727.4	652.0	585.5	530.9	486.3	449.5	416.8	402.9	389.0
135°	836.6	771.1	705.6	641.1	584.5	536.9	497.2	462.4	430.7	416.8	402.9
137.5°	797.9	744.3	687.7	633.1	584.5	542.8	506.1	473.4	441.6	428.7	415.8
140°	764.1	718.5	670.8	626.2	583.5	546.8	513.1	482.3	452.5	439.6	426.7
142.5°	733.4	695.7	657.0	619.2	583.5	549.8	519.0	489.2	460.5	448.6	436.6
145°	707.6	676.8	644.1	613.3	581.5	551.8	524.0	496.2	469.4	458.5	447.6
147.5°	685.7	660.9	634.1	607.3	578.6	552.8	527.0	502.1	476.3	466.4	456.5
150°	665.9	645.0	623.2	599.4	575.6	551.8	528.9	506.1	483.3	474.4	465.4
152.5°	649.0	632.1	612.3	592.4	570.6	549.8	529.9	510.1	490.2	482.3	474.4
155°	633.1	618.2	602.4	583.5	564.7	547.8	530.9	514.1	497.2	489.8	482.3
157.5°	617.3	604.4	590.5	575.6	558.7	543.8	530.9	517.0	502.1	495.6	489.2
160°	601.4	590.5	579.5	566.6	552.8	540.8	530.9	519.0	507.1	501.6	496.2
162.5°	586.5	577.6	568.6	558.7	547.8	537.9	529.9	520.0	510.1	506.1	502.1
165°	571.6	564.7	557.7	549.8	540.8	533.9	527.9	521.0	512.1	509.1	506.1
167.5°	557.7	552.8	546.8	540.8	534.9	529.9	527.0	521.0	514.1	512.1	510.1
170°	545.8	541.8	538.9	533.9	529.9	527.0	525.0	520.0	515.0	513.6	512.1
172.5°	534.9	531.9	529.9	527.0	524.0	523.0	522.0	519.0	516.0	515.0	514.1
175°	526.0	525.0	524.0	521.0	520.0	519.0	520.0	518.0	516.0	515.5	515.0
177.5°	520.0	519.0	519.0	517.0	516.0	517.0	519.0	517.0	516.0	516.0	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2219.7	2219.7	2219.7	2219.7
2.5°	2179.6	2175.0	2202.8	2233.6
5°	2134.9	2142.6	2178.1	2221.3
7.5°	2088.6	2105.6	2147.2	2204.3
10°	2023.8	2054.7	2117.9	2176.6
12.5°	1960.6	2002.2	2062.4	2131.8
15°	1889.6	1935.9	2010.0	2093.3
17.5°	1811.0	1863.4	1949.8	2040.8
20°	1727.7	1797.1	1888.1	1986.8
22.5°	1635.1	1718.4	1812.5	1922.0
25°	1545.6	1636.7	1730.8	1857.2
27.5°	1457.7	1547.2	1652.1	1780.1
30°	1369.8	1451.6	1564.2	1701.4
32.5°	1275.7	1360.5	1479.3	1619.7
35°	1189.3	1274.2	1385.2	1524.1
37.5°	1096.8	1187.8	1294.2	1437.7
40°	988.8	1095.2	1198.6	1335.9
42.5°	899.3	1011.9	1112.2	1241.8
45°	828.4	934.8	1018.1	1144.6
47.5°	762.0	848.4	933.3	1050.5
50°	698.8	765.1	853.0	957.9
52.5°	634.0	691.1	766.7	865.4
55°	575.4	629.4	697.2	772.8
57.5°	521.4	560.0	627.8	695.7
60°	461.2	501.3	553.8	610.9
62.5°	410.3	441.2	490.5	538.4
65°	356.3	385.6	422.7	467.4
67.5°	307.0	333.2	362.5	398.0
70°	262.2	282.3	303.9	334.7
72.5°	214.4	236.0	256.1	280.7
75°	175.9	185.1	202.1	219.0
77.5°	135.7	148.1	157.3	171.2
80°	97.2	108.0	111.1	121.9
82.5°	64.8	71.0	77.1	80.2
85°	37.0	40.1	46.3	47.8
87.5°	13.9	15.4	18.5	21.6
90°	9.9	7.9	4.0	1.0
92.5°	33.7	28.8	20.8	14.9
95°	57.6	48.6	38.7	34.7
97.5°	81.4	68.5	57.6	51.6
100°	104.2	88.3	79.4	76.4
102.5°	126.0	110.2	101.2	99.2
105°	146.9	132.0	125.0	121.1
107.5°	168.7	154.8	147.9	144.9
110°	191.5	178.6	172.7	168.7

TEST NUMBER: P999451

CATALOG NUMBER: SA2XXRDIP-B1005D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	213.4	201.5	194.5	190.5
115°	236.2	224.3	218.3	213.4
117.5°	258.0	247.1	241.1	237.2
120°	277.9	268.9	263.0	259.0
122.5°	298.7	288.8	282.8	279.8
125°	318.6	306.6	300.7	297.7
127.5°	337.4	324.5	316.6	312.6
130°	353.3	339.4	329.5	325.5
132.5°	368.2	353.3	342.4	337.4
135°	380.1	365.2	353.3	349.3
137.5°	393.0	377.1	365.2	360.2
140°	404.9	389.0	377.1	373.1
142.5°	415.8	399.9	389.0	386.0
145°	427.7	412.8	402.9	398.9
147.5°	439.6	425.7	415.8	412.8
150°	450.5	437.6	429.7	426.7
152.5°	460.5	449.5	441.6	440.6
155°	471.4	460.5	454.5	453.5
157.5°	480.3	470.4	465.4	464.4
160°	488.2	480.3	476.3	475.3
162.5°	495.2	489.2	485.3	486.3
165°	501.1	495.2	493.2	494.2
167.5°	506.1	502.1	500.2	501.1
170°	510.1	507.1	506.1	508.1
172.5°	513.1	510.1	511.1	512.1
175°	515.0	513.1	514.1	515.0
177.5°	516.0	514.1	515.0	517.0
180°	516.0	516.0	516.0	516.0

(END OF REPORT)