

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999460

Luminaire Tested: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999460
REPORT IS A COMBINATION OF REPORTS P988011 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7036.0 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999460

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999460

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	44	43	41
3	82	73	66	60	76	68	62	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	52	46	42	43	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	25	21	26	21	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26715	26715	26715
5°	26759	25416	25228
10°	26494	24106	23311
15°	26130	22559	21124
20°	25649	20799	18839
25°	25156	18994	16748
30°	24492	17236	14463
35°	23844	15464	12501
40°	23184	13722	10481
45°	22417	11925	8719
50°	21623	10191	7098
55°	20797	8460	5635
60°	19836	6765	4264
65°	18731	5159	3465
70°	17396	3742	2756
75°	15719	2854	2105
80°	13293	1932	1413
85°	9281	884	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22417 cd/sqm

TEST NUMBER: P999460

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.2	2.2
10°-20°	434.2	6.2
20°-30°	609.6	8.7
30°-40°	664.5	9.4
40°-50°	610.8	8.7
50°-60°	479.7	6.8
60°-70°	312.2	4.4
70°-80°	160.7	2.3
80°-90°	44.3	0.6
90°-100°	207.1	2.9
100°-110°	700.1	10.0
110°-120°	735.9	10.5
120°-130°	605.2	8.6
130°-140°	486.3	6.9
140°-150°	367.4	5.2
150°-160°	258.3	3.7
160°-170°	152.1	2.2
170°-180°	49.5	0.7
0°-30°	1202.0	17.1
0°-40°	1866.6	26.5
0°-60°	2957.0	42.0
0°-90°	3474.3	49.4
90°-120°	1643.2	23.4
90°-150°	3102.0	44.1
90°-180°	3562.0	50.6
0°-180°	7036.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1688	1688	1688	1688	1688	
5°	1688	1680	1660	1674	1669	160
15°	1605	1588	1536	1508	1492	452
25°	1457	1408	1307	1245	1222	670
35°	1256	1178	1043	947	913	786
45°	1026	924	764	655	619	793
55°	780	661	496	405	376	697
65°	527	403	266	214	209	522
75°	281	174	122	112	110	297
85°	66	34	29	29	29	75
90°	1	13	33	32	32	6
95°	34	84	385	145	112	36
105°	120	181	728	1301	1107	127
115°	211	267	609	1257	1457	209
125°	295	349	586	1018	1182	262
135°	346	413	579	856	980	267
145°	395	454	576	715	782	248
155°	449	485	559	632	657	207
165°	489	504	535	568	577	138
175°	510	510	515	521	520	48
180°	511	511	511	511	511	

TEST NUMBER: P999460

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1687.7	1687.7	1687.7	1687.7	1687.7
2.5°	1695.4	1687.7	1670.9	1686.2	1683.1
5°	1687.7	1680.1	1660.2	1674.0	1669.4
7.5°	1674.0	1664.8	1643.4	1649.5	1641.9
10°	1655.6	1644.9	1614.4	1609.8	1600.7
12.5°	1632.7	1619.0	1577.7	1568.6	1551.8
15°	1605.2	1588.4	1536.5	1507.5	1492.2
17.5°	1573.2	1548.7	1484.6	1451.0	1426.5
20°	1536.5	1506.0	1429.6	1391.4	1357.8
22.5°	1496.8	1461.7	1373.1	1321.2	1298.2
25°	1457.1	1408.2	1307.4	1244.8	1221.9
27.5°	1409.7	1357.8	1246.3	1174.5	1139.4
30°	1359.3	1301.3	1179.1	1101.2	1060.0
32.5°	1310.5	1240.2	1115.0	1023.3	985.1
35°	1255.5	1177.6	1043.2	947.0	913.4
37.5°	1202.0	1118.0	976.0	870.6	832.4
40°	1145.5	1053.9	905.7	797.3	757.6
42.5°	1087.5	989.7	835.5	722.4	684.2
45°	1026.4	924.0	763.7	655.2	618.6
47.5°	968.3	859.9	694.9	586.5	552.9
50°	904.2	795.7	627.7	522.4	490.3
52.5°	841.6	727.0	563.6	462.8	433.8
55°	780.5	661.3	496.4	404.7	375.7
57.5°	717.9	595.7	436.8	351.3	326.9
60°	653.7	531.5	374.2	296.3	271.9
62.5°	591.1	468.9	320.7	247.4	235.2
65°	526.9	403.2	265.8	213.8	209.2
67.5°	465.8	342.1	213.8	187.9	183.3
70°	401.7	282.6	177.2	161.9	155.8
72.5°	340.6	227.6	148.2	135.9	132.9
75°	281.0	174.1	122.2	111.5	110.0
77.5°	221.5	123.7	96.2	90.1	87.1
80°	166.5	88.6	73.3	67.2	67.2
82.5°	116.1	59.6	50.4	47.3	47.3
85°	65.7	33.6	29.0	29.0	29.0
87.5°	24.4	12.2	12.2	10.7	10.7
90°	1.0	13.2	33.4	31.9	32.4
92.5°	14.7	46.7	151.3	69.8	59.9
95°	34.4	84.5	385.1	145.4	112.0
97.5°	51.1	111.5	627.8	291.8	187.6
100°	75.6	136.6	776.1	581.2	351.7
102.5°	98.2	159.2	781.0	982.4	685.7
105°	119.9	180.8	728.0	1301.2	1107.2
107.5°	143.4	202.4	678.9	1416.6	1391.1
110°	167.0	224.4	645.5	1398.0	1507.1



TEST NUMBER: P999460

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.6	245.6	623.9	1334.6	1505.1
115°	211.2	266.8	609.1	1257.0	1457.0
117.5°	234.8	287.8	601.3	1182.8	1384.3
120°	256.4	308.4	594.4	1116.5	1314.5
122.5°	277.0	329.6	590.4	1065.0	1241.8
125°	294.7	348.8	585.5	1018.3	1181.9
127.5°	309.5	367.0	582.6	978.5	1125.9
130°	322.2	383.2	580.6	938.2	1079.7
132.5°	334.0	398.8	579.6	896.4	1031.6
135°	345.8	412.6	578.7	855.7	979.5
137.5°	356.6	424.4	578.7	814.4	929.4
140°	369.4	435.2	577.7	778.1	877.3
142.5°	382.2	444.1	577.7	743.2	825.3
145°	394.9	453.9	575.7	714.8	782.0
147.5°	408.7	461.8	572.8	689.7	743.7
150°	422.5	469.6	569.8	668.0	710.3
152.5°	436.2	477.4	564.9	649.9	681.8
155°	449.0	484.8	559.0	632.2	657.3
157.5°	459.8	490.7	553.1	615.5	635.6
160°	470.6	496.6	547.2	598.8	615.0
162.5°	481.4	501.0	542.3	583.0	595.4
165°	489.3	504.0	535.4	567.8	576.7
167.5°	496.1	507.0	529.5	554.1	559.0
170°	503.0	508.4	524.6	541.3	543.3
172.5°	506.9	509.9	518.7	530.0	530.5
175°	509.9	510.4	514.8	521.2	519.7
177.5°	511.9	510.9	510.9	514.8	511.9
180°	510.9	510.9	510.9	510.9	510.9

(END OF REPORT)