

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999464

Luminaire Tested: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999464
REPORT IS A COMBINATION OF REPORTS P988015 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6880.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999464

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P999464

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49		
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47	42		
2	90	82	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36		
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	39	37	35	31		
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27		
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24		
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24	21		
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19		
8	55	43	35	30	51	40	33	29	35	29	26	30	26	22	25	22	19	17		
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16		
10	48	36	29	24	44	34	28	23	30	24	21	25	21	18	21	18	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25830	25830	25830
5°	25872	24574	24392
10°	25617	23307	22538
15°	25266	21811	20425
20°	24800	20110	18215
25°	24322	18365	16192
30°	23681	16665	13984
35°	23054	14951	12087
40°	22417	13268	10134
45°	21674	11530	8430
50°	20905	9854	6862
55°	20107	8179	5449
60°	19178	6541	4123
65°	18112	4988	3351
70°	16820	3618	2664
75°	15199	2759	2035
80°	12854	1868	1367
85°	8970	857	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21674 cd/sqm

TEST NUMBER: P999464

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.9	2.2
10°-20°	419.8	6.1
20°-30°	589.4	8.6
30°-40°	642.5	9.3
40°-50°	590.5	8.6
50°-60°	463.8	6.7
60°-70°	301.9	4.4
70°-80°	155.4	2.3
80°-90°	41.8	0.6
90°-100°	39.6	0.6
100°-110°	147.7	2.1
110°-120°	391.6	5.7
120°-130°	649.6	9.4
130°-140°	690.0	10.0
140°-150°	641.3	9.3
150°-160°	515.6	7.5
160°-170°	332.2	4.8
170°-180°	114.3	1.7
0°-30°	1162.2	16.9
0°-40°	1804.7	26.2
0°-60°	2859.0	41.6
0°-90°	3358.1	48.8
90°-120°	578.9	8.4
90°-150°	2559.8	37.2
90°-180°	3522.0	51.2
0°-180°	6880.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1632	1632	1632	1632	1632	
5°	1632	1624	1605	1618	1614	155
15°	1552	1536	1486	1458	1443	437
25°	1409	1362	1264	1204	1181	648
35°	1214	1139	1009	916	883	760
45°	992	893	738	634	598	766
55°	755	639	480	391	363	674
65°	510	390	257	207	202	505
75°	272	168	118	108	106	287
85°	64	32	28	28	28	73
90°	1	10	17	22	24	6
95°	56	28	34	38	37	67
105°	264	290	53	63	66	282
115°	500	515	536	134	71	492
125°	707	718	734	741	743	630
135°	874	888	896	905	903	676
145°	1014	1014	1028	1034	1030	634
155°	1117	1109	1120	1125	1118	515
165°	1177	1172	1174	1180	1174	333
175°	1204	1198	1200	1206	1197	115
180°	1201	1201	1201	1201	1201	

TEST NUMBER: P999464

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.8	1631.8	1631.8	1631.8	1631.8
2.5°	1639.2	1631.8	1615.6	1630.3	1627.4
5°	1631.8	1624.4	1605.2	1618.5	1614.1
7.5°	1618.5	1609.6	1589.0	1594.9	1587.5
10°	1600.8	1590.4	1560.9	1556.5	1547.6
12.5°	1578.6	1565.3	1525.5	1516.6	1500.4
15°	1552.1	1535.8	1485.6	1457.5	1442.8
17.5°	1521.0	1497.4	1435.4	1402.9	1379.3
20°	1485.6	1456.1	1382.2	1345.3	1312.8
22.5°	1447.2	1413.2	1327.6	1277.4	1255.2
25°	1408.8	1361.6	1264.1	1203.5	1181.4
27.5°	1363.0	1312.8	1205.0	1135.6	1101.6
30°	1314.3	1258.2	1140.0	1064.7	1024.9
32.5°	1267.0	1199.1	1078.0	989.4	952.5
35°	1213.9	1138.6	1008.6	915.6	883.1
37.5°	1162.2	1081.0	943.6	841.7	804.8
40°	1107.6	1019.0	875.7	770.9	732.5
42.5°	1051.4	956.9	807.8	698.5	661.6
45°	992.4	893.4	738.4	633.5	598.1
47.5°	936.3	831.4	671.9	567.1	534.6
50°	874.2	769.4	606.9	505.0	474.0
52.5°	813.7	702.9	544.9	447.5	419.4
55°	754.6	639.4	479.9	391.3	363.3
57.5°	694.1	575.9	422.3	339.7	316.0
60°	632.0	513.9	361.8	286.5	262.9
62.5°	571.5	453.4	310.1	239.2	227.4
65°	509.5	389.9	257.0	206.7	202.3
67.5°	450.4	330.8	206.7	181.6	177.2
70°	388.4	273.2	171.3	156.5	150.6
72.5°	329.3	220.0	143.2	131.4	128.5
75°	271.7	168.3	118.1	107.8	106.3
77.5°	214.1	119.6	93.0	87.1	84.2
80°	161.0	85.7	70.9	65.0	65.0
82.5°	112.2	57.6	48.7	45.8	45.8
85°	63.5	32.5	28.1	28.1	28.1
87.5°	23.6	11.8	11.8	10.3	10.3
90°	0.9	10.4	17.4	21.7	23.5
92.5°	21.7	18.3	20.9	22.6	23.5
95°	56.5	27.8	33.9	38.2	37.4
97.5°	101.7	30.4	44.3	46.9	47.8
100°	153.9	34.8	49.5	56.5	58.2
102.5°	211.2	209.5	51.3	60.8	63.5
105°	264.3	290.3	53.0	62.6	66.1
107.5°	326.0	347.7	54.8	64.3	67.8
110°	385.1	403.3	152.1	65.2	68.7



TEST NUMBER: P999464

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	440.7	456.4	441.6	66.9	69.5
115°	499.8	514.6	536.3	133.9	71.3
117.5°	551.1	568.5	583.3	459.0	231.2
120°	608.5	621.5	637.2	647.6	530.3
122.5°	657.2	671.1	688.5	693.7	694.5
125°	706.7	718.0	734.5	740.6	743.2
127.5°	751.9	764.1	777.1	785.8	786.7
130°	794.5	808.4	818.0	827.5	826.7
132.5°	838.0	849.3	858.8	866.7	865.8
135°	874.5	888.4	896.2	904.9	903.2
137.5°	912.7	923.2	931.9	940.6	937.9
140°	950.1	957.1	966.6	974.5	970.1
142.5°	981.4	987.5	998.8	1005.7	1001.4
145°	1014.4	1013.6	1028.3	1034.4	1030.1
147.5°	1043.1	1040.5	1055.3	1059.6	1056.2
150°	1070.9	1064.9	1078.8	1084.0	1079.6
152.5°	1094.4	1087.5	1100.5	1105.7	1099.6
155°	1117.0	1109.2	1119.6	1124.8	1117.9
157.5°	1135.3	1128.3	1136.1	1142.2	1135.3
160°	1150.9	1145.7	1150.9	1156.1	1150.0
162.5°	1164.8	1159.6	1164.0	1170.0	1162.2
165°	1177.0	1171.8	1174.4	1180.5	1174.4
167.5°	1186.6	1181.3	1183.9	1190.0	1182.2
170°	1194.4	1189.2	1190.9	1197.0	1189.2
172.5°	1199.6	1194.4	1196.1	1202.2	1194.4
175°	1203.9	1197.9	1199.6	1205.7	1197.0
177.5°	1205.7	1199.6	1200.5	1206.5	1198.7
180°	1201.3	1201.3	1201.3	1201.3	1201.3

(END OF REPORT)